

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332627

Luminaire Tested: **SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332627  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5913.7 lumens  
Efficiency: N/A  
Efficacy: 135.9 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332627  
CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78				
1	104	100	96	92	99	96	92	89	87	85	82	80	78	76	73	71	70	66				
2	95	88	82	76	91	84	78	74	77	73	69	71	67	64	65	62	59	56				
3	87	78	70	64	83	74	68	62	68	63	58	63	58	54	58	54	51	48				
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	52	48	44	41				
5	74	62	53	47	70	59	52	46	55	48	44	51	45	41	47	42	39	36				
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	43	38	34	32				
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	31	28				
8	59	46	38	33	56	45	37	32	41	35	30	39	33	29	36	31	28	25				
9	55	42	35	29	52	41	34	29	38	32	27	36	30	26	33	28	25	23				
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13472	13472	13472	13472
5°	15866	13507	11921	13507
10°	18996	13448	10733	13448
15°	22476	13312	9857	13312
20°	25027	13173	9075	13173
25°	25432	12968	8535	12968
30°	21640	12773	8364	12773
35°	16638	12454	8366	12454
40°	12968	12079	8524	12079
45°	10813	11515	8667	11515
50°	9516	10827	8960	10827
55°	8718	10003	9322	10003
60°	8170	9265	9755	9265
65°	7607	8437	10115	8437
70°	6951	7619	10346	7619
75°	6210	6706	10221	6706
80°	5207	5495	9898	5495
85°	3844	3974	9476	3974



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.6	2.7
10°-20°	501.1	8.5
20°-30°	794.6	13.4
30°-40°	884.3	15.0
40°-50°	805.0	13.6
50°-60°	657.8	11.1
60°-70°	469.6	7.9
70°-80°	258.6	4.4
80°-90°	71.6	1.2
90°-100°	129.9	2.2
100°-110°	270.4	4.6
110°-120°	242.2	4.1
120°-130°	203.7	3.4
130°-140°	169.9	2.9
140°-150°	129.8	2.2
150°-160°	91.2	1.5
160°-170°	53.7	0.9
170°-180°	17.5	0.3
0°-30°	1458.3	24.7
0°-40°	2342.7	39.6
0°-60°	3805.5	64.4
0°-90°	4605.3	77.9
90°-120°	642.6	10.9
90°-150°	1146.0	19.4
90°-180°	1308.0	22.1
0°-180°	5913.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1669	1669	1669	1669	1669	
5°	1958	1667	1471	1667	1958	199
15°	2689	1593	1179	1593	2689	760
25°	2855	1456	958	1456	2855	1259
35°	1688	1264	849	1264	1688	1072
45°	947	1009	759	1009	947	746
55°	619	711	662	711	619	560
65°	398	442	530	442	398	394
75°	199	215	328	215	199	212
85°	42	43	102	43	42	51
90°	7	0	7	0	7	8
95°	86	12	86	12	86	134
105°	497	41	497	41	497	492
115°	478	73	478	73	478	474
125°	381	101	381	101	381	346
135°	341	120	341	120	341	263
145°	278	139	278	139	278	176
155°	233	158	233	158	233	109
165°	203	172	203	172	203	58
175°	183	180	183	180	183	18
180°	180	180	180	180	180	



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1776.1	1775.6	1770.0	1768.9	1765.0	1760.1	1759.0	1750.1	1732.4	1724.1	1721.9
5°	1957.8	1971.6	1953.6	1950.2	1948.1	1925.3	1913.5	1899.7	1867.9	1849.2	1834.7
7.5°	2174.6	2176.2	2168.4	2162.0	2144.4	2124.5	2094.7	2062.9	2025.0	1985.6	1955.8
10°	2317.3	2322.8	2313.8	2312.4	2277.2	2255.0	2210.8	2173.5	2130.6	2082.9	2039.4
12.5°	2467.7	2459.9	2455.4	2425.8	2419.3	2378.9	2327.5	2289.1	2223.0	2168.1	2110.1
15°	2689.2	2674.0	2664.3	2623.5	2603.5	2547.5	2492.8	2450.7	2364.3	2282.0	2219.8
17.5°	2819.1	2834.4	2812.0	2795.2	2743.4	2704.1	2648.3	2559.8	2492.2	2390.0	2311.5
20°	2913.2	2914.5	2902.1	2884.8	2844.0	2794.3	2733.4	2636.6	2555.8	2454.1	2346.3
22.5°	2938.6	2938.9	2933.6	2917.4	2886.6	2846.2	2784.9	2704.1	2606.1	2495.6	2387.8
25°	2855.1	2852.3	2858.6	2876.5	2864.8	2852.3	2817.1	2756.9	2665.7	2548.8	2432.7
27.5°	2544.8	2563.9	2599.0	2643.3	2685.9	2718.4	2727.5	2715.2	2658.6	2562.5	2440.9
30°	2321.4	2344.9	2371.2	2415.4	2501.1	2550.2	2604.2	2644.9	2622.1	2545.4	2432.0
32.5°	2075.9	2081.7	2120.7	2171.0	2249.5	2343.9	2429.4	2512.2	2539.7	2499.5	2404.9
35°	1688.2	1697.8	1740.0	1789.8	1885.9	2001.3	2129.9	2244.7	2339.4	2377.4	2329.0
37.5°	1377.6	1405.4	1435.2	1488.7	1573.3	1677.2	1810.8	1959.3	2100.5	2195.0	2211.1
40°	1230.5	1247.8	1269.2	1310.0	1381.9	1484.2	1599.0	1769.1	1919.1	2054.6	2098.8
42.5°	1114.4	1124.5	1137.6	1174.5	1229.3	1331.0	1435.8	1585.4	1736.0	1898.0	1972.2
45°	947.1	957.5	979.6	1001.0	1042.5	1113.0	1210.5	1333.5	1484.9	1641.2	1778.0
47.5°	826.2	832.9	846.0	869.0	904.2	950.7	1030.0	1132.8	1273.1	1424.8	1570.6
50°	757.7	763.2	773.6	794.3	821.3	862.7	927.7	1023.8	1133.7	1286.5	1429.6
52.5°	703.5	705.7	713.3	727.4	748.8	783.7	837.0	916.5	1018.7	1154.9	1297.4
55°	619.4	622.2	629.1	639.5	658.1	680.2	721.0	780.5	869.7	987.9	1111.6
57.5°	550.3	552.2	558.0	562.0	577.4	595.4	626.7	669.2	736.8	837.0	947.5
60°	506.0	504.7	511.6	515.0	525.4	540.6	564.8	605.6	664.3	745.2	846.8
62.5°	462.9	461.0	466.8	471.3	477.3	490.3	510.0	542.0	589.7	662.8	750.6
65°	398.2	395.4	398.9	404.4	409.9	416.9	431.4	459.7	497.7	550.3	617.3
67.5°	333.2	336.1	336.7	339.4	342.6	352.0	362.0	382.0	408.8	450.9	507.7
70°	294.5	295.2	298.0	298.0	300.0	308.3	316.6	328.4	354.6	393.4	439.7
72.5°	255.8	258.7	257.6	259.8	261.3	266.8	272.9	284.1	306.5	335.3	374.4
75°	199.1	201.2	201.2	201.9	203.9	206.0	210.8	219.1	235.0	256.5	283.4
77.5°	145.2	145.5	146.4	148.9	148.9	152.2	155.8	162.5	170.3	185.0	201.4
80°	112.0	113.4	112.7	114.1	114.1	116.8	118.2	126.5	130.0	139.6	152.8
82.5°	82.1	83.5	83.4	85.3	86.4	87.0	88.9	92.2	95.7	104.2	109.6
85°	41.5	42.9	41.5	42.9	44.9	45.6	47.7	48.4	51.2	53.2	58.1
87.5°	13.7	15.3	15.4	15.9	16.9	17.5	17.9	17.3	19.5	20.1	22.1
90°	7.4	7.4	7.8	7.4	7.1	7.1	6.7	6.4	6.0	6.4	5.7
92.5°	27.2	27.2	28.4	30.3	34.5	41.6	52.2	69.4	93.4	112.1	98.1
95°	86.2	90.8	97.2	108.1	125.5	159.7	207.1	261.9	296.2	288.0	217.4
97.5°	230.5	237.9	248.5	269.7	295.1	332.0	366.6	386.9	372.1	303.4	203.4
100°	324.1	326.9	337.5	359.1	389.8	416.0	433.3	426.2	374.6	284.2	184.5
102.5°	405.5	407.8	419.0	434.6	453.4	464.3	459.3	424.3	353.4	260.1	171.8
105°	497.3	499.4	504.3	507.2	506.5	492.0	457.0	395.8	314.9	231.8	160.8
107.5°	531.3	530.4	526.9	518.8	501.4	469.8	420.6	355.5	283.8	216.0	158.8
110°	531.9	528.7	522.4	507.5	482.4	443.6	392.3	331.2	268.3	210.6	159.4



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	515.2	510.1	501.2	483.2	454.7	415.8	367.4	313.3	259.5	208.1	161.1
115°	477.5	474.7	463.3	442.1	414.2	380.3	338.9	295.5	251.3	206.8	164.3
117.5°	439.2	437.0	425.6	407.8	384.0	355.2	322.7	286.7	247.6	206.4	167.8
120°	417.8	413.9	404.7	389.1	369.0	343.9	315.6	282.7	245.6	206.4	170.4
122.5°	400.8	396.9	389.1	375.8	358.8	336.8	311.1	279.3	243.4	206.1	172.9
125°	381.0	378.9	372.2	361.9	347.8	328.3	303.9	273.6	239.6	205.7	176.7
127.5°	369.4	367.3	361.6	352.5	338.3	319.9	295.5	266.5	234.6	204.9	179.8
130°	362.6	360.5	354.8	346.0	331.5	312.8	288.8	260.8	231.5	204.6	182.0
132.5°	355.0	352.9	347.5	337.5	323.3	304.6	281.1	254.9	228.7	204.4	184.0
135°	340.7	338.6	332.9	323.0	308.9	291.2	269.7	246.7	224.4	203.9	187.0
137.5°	323.0	320.5	315.8	306.1	292.8	276.9	258.7	239.3	220.8	203.9	188.7
140°	310.3	307.5	302.5	294.8	282.4	267.5	251.6	235.0	218.8	203.6	190.1
142.5°	296.7	294.8	290.4	283.2	272.2	259.3	245.7	231.1	217.1	203.6	191.3
145°	278.1	276.4	272.8	266.8	258.0	248.1	237.5	225.5	214.2	202.9	191.9
147.5°	261.7	261.0	258.4	253.2	246.7	238.9	230.4	220.9	211.6	201.6	192.3
150°	252.3	252.0	249.9	245.3	239.6	233.3	226.2	218.1	209.6	200.7	192.3
152.5°	243.9	243.5	242.2	238.5	233.7	228.5	222.0	215.0	207.3	199.3	191.7
155°	232.9	232.9	231.8	229.0	225.5	221.2	215.9	210.3	203.9	197.2	190.9
157.5°	223.3	223.3	222.7	220.5	217.9	214.5	210.0	205.3	200.5	195.0	189.9
160°	217.4	217.4	217.0	214.9	212.8	209.9	206.0	202.2	197.9	193.3	189.1
162.5°	211.7	212.0	211.6	209.5	208.0	205.4	202.4	199.1	195.7	191.6	188.2
165°	203.2	203.6	203.9	202.5	201.1	199.3	196.9	194.7	191.9	189.1	186.6
167.5°	196.5	196.8	196.9	195.9	195.2	194.2	192.2	190.6	188.5	186.5	184.9
170°	192.3	192.3	192.6	192.3	191.6	190.5	189.1	188.0	186.3	184.8	183.8
172.5°	188.0	188.6	188.9	188.6	188.2	187.4	186.5	185.8	184.3	183.1	182.7
175°	183.1	183.8	184.5	183.8	183.8	183.8	183.1	182.7	182.0	181.3	181.3
177.5°	180.2	180.7	181.3	181.0	181.3	181.0	181.0	180.7	180.5	180.2	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1722.5	1714.7	1709.2	1704.8	1692.6	1685.4	1679.9	1672.1	1663.3	1653.9	1642.3
5°	1820.2	1796.7	1779.4	1753.2	1728.3	1707.5	1686.1	1666.7	1643.2	1617.7	1599.0
7.5°	1922.9	1888.0	1843.2	1804.3	1760.6	1722.6	1688.6	1653.7	1617.5	1582.4	1550.2
10°	1988.2	1943.3	1893.5	1834.7	1779.4	1730.3	1684.7	1640.5	1597.6	1554.7	1518.1
12.5°	2058.4	2002.4	1928.9	1860.2	1798.2	1732.6	1677.5	1623.3	1571.6	1526.5	1483.8
15°	2152.7	2071.8	1986.8	1894.9	1813.3	1736.6	1661.2	1592.8	1534.7	1475.2	1433.8
17.5°	2210.7	2110.6	2013.4	1917.3	1818.5	1721.8	1640.5	1561.5	1488.8	1429.8	1377.5
20°	2248.8	2149.3	2028.3	1932.2	1814.7	1715.1	1621.1	1533.3	1457.3	1394.4	1340.4
22.5°	2282.0	2167.0	2046.0	1919.5	1802.5	1696.9	1594.0	1505.7	1428.0	1361.7	1310.0
25°	2300.0	2167.9	2036.6	1910.8	1778.0	1652.9	1559.6	1455.9	1372.9	1303.1	1247.8
27.5°	2301.9	2160.7	2012.1	1872.3	1735.3	1618.8	1501.0	1408.3	1322.2	1248.4	1195.3
30°	2295.8	2148.6	1988.9	1837.5	1699.9	1573.4	1471.1	1370.2	1282.4	1209.1	1153.8
32.5°	2276.5	2123.1	1959.0	1798.8	1656.2	1532.5	1426.9	1330.9	1245.3	1173.1	1115.1
35°	2220.5	2069.1	1894.2	1727.6	1581.7	1456.6	1361.2	1263.7	1178.0	1109.5	1053.6
37.5°	2133.0	1996.1	1818.3	1645.9	1502.6	1376.9	1282.4	1194.3	1117.0	1047.5	990.1
40°	2056.6	1936.3	1758.0	1590.0	1435.2	1315.6	1227.1	1146.2	1069.5	1003.8	949.2
42.5°	1968.7	1863.9	1699.4	1521.4	1372.1	1252.0	1165.7	1093.1	1020.8	960.1	905.5
45°	1811.9	1742.8	1587.9	1423.4	1267.9	1154.5	1072.2	1008.6	947.8	888.3	842.7
47.5°	1631.6	1597.3	1467.0	1310.7	1163.1	1051.3	980.0	921.2	867.9	817.5	777.3
50°	1510.5	1493.9	1381.2	1230.5	1089.5	984.4	912.5	862.1	816.4	772.2	734.2
52.5°	1391.0	1390.5	1288.9	1150.9	1020.4	919.2	847.8	800.7	761.1	725.2	691.0
55°	1208.4	1227.8	1148.3	1025.2	908.4	817.1	752.8	710.7	683.0	653.3	627.7
57.5°	1040.7	1072.8	1007.2	898.8	801.4	717.3	661.3	629.6	600.2	582.2	563.6
60°	931.2	961.6	910.5	819.2	727.3	655.4	602.1	573.8	548.2	535.8	522.6
62.5°	833.9	861.0	823.1	738.5	658.7	589.5	544.6	517.4	500.1	486.5	477.8
65°	694.8	717.6	685.1	623.6	555.1	499.8	463.2	441.7	425.2	419.6	409.9
67.5°	561.6	582.4	564.8	512.5	457.6	415.8	387.1	366.5	356.7	351.9	345.0
70°	482.5	503.3	484.6	439.0	396.8	361.6	334.6	322.8	312.5	310.4	300.7
72.5°	415.6	429.7	411.1	375.4	339.3	309.6	288.7	276.4	271.0	267.3	262.0
75°	311.8	324.2	311.8	284.1	258.5	237.8	219.8	215.0	208.8	206.7	203.2
77.5°	220.7	231.4	221.9	204.6	185.5	169.5	159.8	153.6	152.2	148.6	150.3
80°	168.7	175.6	166.6	154.9	139.6	128.6	121.7	118.2	114.1	112.7	115.4
82.5°	121.1	124.2	119.6	111.7	100.4	93.2	88.5	84.5	83.6	83.9	83.9
85°	62.9	62.2	61.5	54.6	51.2	46.3	43.6	42.9	42.2	43.6	44.9
87.5°	22.0	22.6	21.6	19.4	17.6	15.9	15.1	14.4	15.1	15.9	16.5
90°	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	71.4	44.0	26.0	18.7	13.5	9.2	5.9	4.0	5.9	9.2	13.5
95°	132.9	74.9	44.2	29.3	20.9	16.3	12.7	11.7	12.7	16.3	20.9
97.5°	119.5	71.6	47.9	35.5	28.2	24.0	20.9	20.9	20.9	24.0	28.2
100°	112.4	72.5	51.6	40.3	33.6	29.3	26.9	26.9	26.9	29.3	33.6
102.5°	110.4	75.3	56.4	45.7	39.2	35.3	33.1	32.5	33.1	35.3	39.2
105°	111.3	82.0	65.0	54.8	48.4	44.2	42.4	41.4	42.4	44.2	48.4
107.5°	116.6	89.8	74.3	64.2	58.1	53.6	51.8	51.1	51.8	53.6	58.1
110°	120.5	95.8	80.2	70.7	64.3	60.1	58.3	57.6	58.3	60.1	64.3





TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	124.8	101.4	86.4	76.9	70.5	66.6	64.5	63.8	64.5	66.6	70.5
115°	131.5	110.3	96.1	86.6	79.9	76.3	73.9	72.8	73.9	76.3	79.9
117.5°	138.3	118.8	105.4	95.5	89.2	85.3	83.1	82.1	83.1	85.3	89.2
120°	143.1	124.8	111.3	101.4	95.4	91.5	89.1	88.4	89.1	91.5	95.4
122.5°	147.7	130.4	117.0	107.4	100.8	97.2	94.7	94.0	94.7	97.2	100.8
125°	154.4	138.2	125.5	115.6	108.9	105.0	102.8	101.4	102.8	105.0	108.9
127.5°	160.3	145.4	133.1	123.1	116.1	111.7	109.1	108.0	109.1	111.7	116.1
130°	164.0	150.2	138.2	127.9	121.2	115.9	113.1	111.7	113.1	115.9	121.2
132.5°	167.7	154.2	142.1	132.5	125.2	120.2	116.5	115.4	116.5	120.2	125.2
135°	172.5	159.7	148.1	138.9	131.5	125.5	121.9	120.5	121.9	125.5	131.5
137.5°	175.9	164.0	153.1	144.3	136.6	130.9	127.0	125.7	127.0	130.9	136.6
140°	178.1	166.8	156.2	147.7	140.3	134.3	130.4	129.4	130.4	134.3	140.3
142.5°	179.8	169.4	159.0	150.8	143.7	138.0	134.4	133.3	134.4	138.0	143.7
145°	181.7	172.1	162.9	155.2	148.4	143.5	140.0	138.9	140.0	143.5	148.4
147.5°	183.3	174.9	166.3	159.3	153.7	148.7	145.5	145.2	145.5	148.7	153.7
150°	184.1	176.4	168.6	161.9	156.6	152.3	149.5	149.1	149.5	152.3	156.6
152.5°	184.7	177.5	170.6	164.4	159.7	155.7	152.9	152.8	152.9	155.7	159.7
155°	185.2	179.2	173.2	167.9	164.0	160.5	158.3	158.0	158.3	160.5	164.0
157.5°	185.2	180.4	175.3	171.1	167.7	165.0	163.0	163.0	163.0	165.0	167.7
160°	185.2	181.0	176.7	172.8	170.0	167.5	166.1	166.1	166.1	167.5	170.0
162.5°	185.2	181.5	177.6	174.5	172.0	169.8	168.7	168.9	168.7	169.8	172.0
165°	184.5	181.7	178.5	176.4	174.6	172.8	172.1	172.1	172.1	172.8	174.6
167.5°	183.6	181.6	179.3	177.6	176.6	175.3	174.9	175.3	174.9	175.3	176.6
170°	183.1	181.3	179.5	178.5	177.8	176.7	176.4	176.7	176.4	176.7	177.8
172.5°	182.5	181.0	179.8	179.0	178.6	177.8	177.8	178.1	177.8	177.8	178.6
175°	181.7	180.6	179.9	179.9	179.5	179.2	179.2	179.5	179.2	179.2	179.5
177.5°	180.7	180.2	179.9	179.9	179.9	179.6	179.9	180.2	179.9	179.6	179.9
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1636.7	1631.8	1624.6	1614.6	1606.3	1597.5	1595.3	1591.9	1598.6	1593.0	1591.4
5°	1583.1	1568.6	1549.9	1528.5	1516.0	1498.1	1494.6	1487.7	1480.8	1480.1	1473.2
7.5°	1526.3	1505.0	1480.5	1458.7	1438.5	1418.8	1406.0	1403.2	1393.0	1387.0	1380.1
10°	1489.8	1463.5	1435.2	1414.4	1390.9	1370.2	1355.7	1347.4	1340.4	1332.8	1325.9
12.5°	1446.6	1418.7	1395.3	1372.9	1345.0	1329.2	1305.3	1290.9	1289.6	1289.7	1271.7
15°	1396.4	1368.8	1332.8	1301.0	1285.8	1255.4	1242.3	1225.7	1215.3	1204.9	1196.7
17.5°	1339.1	1304.6	1276.6	1240.1	1211.0	1186.8	1169.6	1159.6	1144.0	1129.3	1118.7
20°	1303.1	1266.5	1236.7	1198.0	1166.2	1136.5	1122.0	1108.2	1096.4	1084.0	1072.2
22.5°	1266.6	1228.3	1191.9	1154.3	1124.8	1093.4	1079.4	1060.6	1049.4	1042.5	1030.7
25°	1209.1	1167.6	1126.1	1090.2	1059.8	1032.1	1013.5	998.9	986.5	981.0	973.4
27.5°	1146.6	1105.4	1065.3	1024.5	990.0	969.9	955.0	944.0	936.9	929.5	926.1
30°	1106.8	1063.9	1021.1	983.0	951.2	931.2	917.4	909.8	904.2	900.8	897.3
32.5°	1066.4	1024.1	979.0	944.3	915.8	898.0	887.5	879.9	877.1	875.9	874.6
35°	1001.7	958.8	917.4	886.3	859.3	852.4	843.4	839.2	837.9	842.7	844.8
37.5°	939.1	899.3	861.1	830.9	813.3	803.2	800.1	800.3	805.2	809.5	814.5
40°	898.7	860.0	824.0	797.8	781.2	775.0	773.6	777.0	782.6	787.4	792.9
42.5°	859.4	821.3	788.6	764.0	752.4	746.7	747.6	751.0	758.8	764.7	773.0
45°	798.5	766.7	734.9	714.8	705.1	706.5	706.5	712.7	720.3	729.3	738.3
47.5°	741.1	709.0	682.9	666.0	661.0	659.8	663.7	671.8	682.7	693.8	706.4
50°	702.4	671.9	649.1	633.9	628.4	630.5	636.0	643.6	656.7	670.6	683.7
52.5°	663.1	635.4	614.3	600.2	596.3	600.1	605.6	617.6	629.1	644.0	659.9
55°	602.1	578.6	562.0	551.7	550.3	552.4	558.6	571.7	588.3	607.0	622.2
57.5°	541.4	521.8	506.6	499.4	500.1	502.0	512.3	527.9	545.6	565.5	585.1
60°	500.5	482.5	470.1	464.6	465.2	469.4	481.8	496.4	518.5	537.8	558.6
62.5°	461.8	446.0	434.1	429.2	428.2	437.3	449.2	464.3	486.4	508.0	530.4
65°	399.6	387.1	377.5	374.7	376.8	383.7	398.9	418.9	437.6	460.4	483.9
67.5°	338.7	328.5	321.9	323.1	325.6	335.8	348.6	365.8	387.0	410.6	433.9
70°	300.0	290.3	284.8	285.5	289.7	302.1	313.2	330.4	353.3	377.5	396.8
72.5°	260.2	253.8	248.9	251.8	255.9	264.5	278.3	295.6	315.7	338.2	358.6
75°	199.8	199.8	197.0	199.1	205.3	213.6	224.0	242.0	262.0	280.0	296.6
77.5°	148.2	146.7	148.5	151.0	154.6	164.4	176.3	189.1	204.2	222.2	235.9
80°	113.4	114.1	117.5	121.7	123.1	130.7	143.1	154.9	166.6	181.8	194.9
82.5°	85.2	85.9	87.7	92.9	94.3	102.5	110.5	122.2	132.9	143.1	154.0
85°	46.3	46.3	49.8	51.8	55.3	60.8	65.7	72.6	82.3	89.2	99.5
87.5°	18.3	18.3	20.9	22.0	23.8	26.7	27.7	33.9	36.2	39.0	44.0
90°	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4	6.7	7.1	7.1
92.5°	18.7	26.0	44.0	71.4	98.1	112.1	93.4	69.4	52.2	41.6	34.5
95°	29.3	44.2	74.9	132.9	217.4	288.0	296.2	261.9	207.1	159.7	125.5
97.5°	35.5	47.9	71.6	119.5	203.4	303.4	372.1	386.9	366.6	332.0	295.1
100°	40.3	51.6	72.5	112.4	184.5	284.2	374.6	426.2	433.3	416.0	389.8
102.5°	45.7	56.4	75.3	110.4	171.8	260.1	353.4	424.3	459.3	464.3	453.4
105°	54.8	65.0	82.0	111.3	160.8	231.8	314.9	395.8	457.0	492.0	506.5
107.5°	64.2	74.3	89.8	116.6	158.8	216.0	283.8	355.5	420.6	469.8	501.4
110°	70.7	80.2	95.8	120.5	159.4	210.6	268.3	331.2	392.3	443.6	482.4



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	76.9	86.4	101.4	124.8	161.1	208.1	259.5	313.3	367.4	415.8	454.7
115°	86.6	96.1	110.3	131.5	164.3	206.8	251.3	295.5	338.9	380.3	414.2
117.5°	95.5	105.4	118.8	138.3	167.8	206.4	247.6	286.7	322.7	355.2	384.0
120°	101.4	111.3	124.8	143.1	170.4	206.4	245.6	282.7	315.6	343.9	369.0
122.5°	107.4	117.0	130.4	147.7	172.9	206.1	243.4	279.3	311.1	336.8	358.8
125°	115.6	125.5	138.2	154.4	176.7	205.7	239.6	273.6	303.9	328.3	347.8
127.5°	123.1	133.1	145.4	160.3	179.8	204.9	234.6	266.5	295.5	319.9	338.3
130°	127.9	138.2	150.2	164.0	182.0	204.6	231.5	260.8	288.8	312.8	331.5
132.5°	132.5	142.1	154.2	167.7	184.0	204.4	228.7	254.9	281.1	304.6	323.3
135°	138.9	148.1	159.7	172.5	187.0	203.9	224.4	246.7	269.7	291.2	308.9
137.5°	144.3	153.1	164.0	175.9	188.7	203.9	220.8	239.3	258.7	276.9	292.8
140°	147.7	156.2	166.8	178.1	190.1	203.6	218.8	235.0	251.6	267.5	282.4
142.5°	150.8	159.0	169.4	179.8	191.3	203.6	217.1	231.1	245.7	259.3	272.2
145°	155.2	162.9	172.1	181.7	191.9	202.9	214.2	225.5	237.5	248.1	258.0
147.5°	159.3	166.3	174.9	183.3	192.3	201.6	211.6	220.9	230.4	238.9	246.7
150°	161.9	168.6	176.4	184.1	192.3	200.7	209.6	218.1	226.2	233.3	239.6
152.5°	164.4	170.6	177.5	184.7	191.7	199.3	207.3	215.0	222.0	228.5	233.7
155°	167.9	173.2	179.2	185.2	190.9	197.2	203.9	210.3	215.9	221.2	225.5
157.5°	171.1	175.3	180.4	185.2	189.9	195.0	200.5	205.3	210.0	214.5	217.9
160°	172.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2	206.0	209.9	212.8
162.5°	174.5	177.6	181.5	185.2	188.2	191.6	195.7	199.1	202.4	205.4	208.0
165°	176.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7	196.9	199.3	201.1
167.5°	177.6	179.3	181.6	183.6	184.9	186.5	188.5	190.6	192.2	194.2	195.2
170°	178.5	179.5	181.3	183.1	183.8	184.8	186.3	188.0	189.1	190.5	191.6
172.5°	179.0	179.8	181.0	182.5	182.7	183.1	184.3	185.8	186.5	187.4	188.2
175°	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7	183.1	183.8	183.8
177.5°	179.9	179.9	180.2	180.7	180.2	180.2	180.5	180.7	181.0	181.0	181.3
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1590.3	1589.2	1585.3	1584.8	1585.3	1589.2	1590.3	1591.4	1593.0	1598.6	1591.9
5°	1469.0	1465.6	1463.5	1471.1	1463.5	1465.6	1469.0	1473.2	1480.1	1480.8	1487.7
7.5°	1377.6	1374.9	1368.8	1366.9	1368.8	1374.9	1377.6	1380.1	1387.0	1393.0	1403.2
10°	1319.0	1316.2	1310.7	1309.3	1310.7	1316.2	1319.0	1325.9	1332.8	1340.4	1347.4
12.5°	1262.6	1257.1	1256.0	1257.3	1256.0	1257.1	1262.6	1271.7	1289.7	1289.6	1290.9
15°	1187.7	1184.9	1177.3	1179.4	1177.3	1184.9	1187.7	1196.7	1204.9	1215.3	1225.7
17.5°	1113.8	1110.5	1101.3	1109.4	1101.3	1110.5	1113.8	1118.7	1129.3	1144.0	1159.6
20°	1067.4	1061.8	1057.0	1056.3	1057.0	1061.8	1067.4	1072.2	1084.0	1096.4	1108.2
22.5°	1023.1	1018.2	1017.7	1013.2	1017.7	1018.2	1023.1	1030.7	1042.5	1049.4	1060.6
25°	967.8	963.0	961.6	958.2	961.6	963.0	967.8	973.4	981.0	986.5	998.9
27.5°	925.4	923.0	920.5	921.6	920.5	923.0	925.4	926.1	929.5	936.9	944.0
30°	899.4	898.7	897.3	897.3	897.3	898.7	899.4	897.3	900.8	904.2	909.8
32.5°	877.8	877.7	878.5	878.5	878.5	877.7	877.8	874.6	875.9	877.1	879.9
35°	847.5	849.6	851.0	848.9	851.0	849.6	847.5	844.8	842.7	837.9	839.2
37.5°	820.2	822.2	824.2	826.5	824.2	822.2	820.2	814.5	809.5	805.2	800.3
40°	799.1	804.0	805.4	808.8	805.4	804.0	799.1	792.9	787.4	782.6	777.0
42.5°	779.2	784.6	788.2	788.9	788.2	784.6	779.2	773.0	764.7	758.8	751.0
45°	748.7	754.2	759.1	759.1	759.1	754.2	748.7	738.3	729.3	720.3	712.7
47.5°	717.0	725.0	729.9	731.1	729.9	725.0	717.0	706.4	693.8	682.7	671.8
50°	695.5	705.1	710.0	713.4	710.0	705.1	695.5	683.7	670.6	656.7	643.6
52.5°	674.4	684.1	690.6	692.4	690.6	684.1	674.4	659.9	644.0	629.1	617.6
55°	638.1	651.9	659.5	662.3	659.5	651.9	638.1	622.2	607.0	588.3	571.7
57.5°	603.8	616.5	625.4	627.4	625.4	616.5	603.8	585.1	565.5	545.6	527.9
60°	577.2	591.1	602.1	604.2	602.1	591.1	577.2	558.6	537.8	518.5	496.4
62.5°	550.1	564.5	574.5	579.9	574.5	564.5	550.1	530.4	508.0	486.4	464.3
65°	503.3	517.8	527.5	529.5	527.5	517.8	503.3	483.9	460.4	437.6	418.9
67.5°	452.1	466.6	473.0	477.0	473.0	466.6	452.1	433.9	410.6	387.0	365.8
70°	416.2	427.9	434.8	438.3	434.8	427.9	416.2	396.8	377.5	353.3	330.4
72.5°	375.2	387.5	395.6	396.3	395.6	387.5	375.2	358.6	338.2	315.7	295.6
75°	312.5	323.5	327.7	327.7	327.7	323.5	312.5	296.6	280.0	262.0	242.0
77.5°	247.3	253.0	258.3	259.4	258.3	253.0	247.3	235.9	222.2	204.2	189.1
80°	205.3	208.8	212.9	212.9	212.9	208.8	205.3	194.9	181.8	166.6	154.9
82.5°	162.2	165.1	169.2	168.7	169.2	165.1	162.2	154.0	143.1	132.9	122.2
85°	98.2	104.4	103.7	102.3	103.7	104.4	98.2	99.5	89.2	82.3	72.6
87.5°	45.7	46.4	47.9	49.0	47.9	46.4	45.7	44.0	39.0	36.2	33.9
90°	7.4	7.8	7.4	7.4	7.4	7.8	7.4	7.1	7.1	6.7	6.4
92.5°	30.3	28.4	27.2	27.2	27.2	28.4	30.3	34.5	41.6	52.2	69.4
95°	108.1	97.2	90.8	86.2	90.8	97.2	108.1	125.5	159.7	207.1	261.9
97.5°	269.7	248.5	237.9	230.5	237.9	248.5	269.7	295.1	332.0	366.6	386.9
100°	359.1	337.5	326.9	324.1	326.9	337.5	359.1	389.8	416.0	433.3	426.2
102.5°	434.6	419.0	407.8	405.5	407.8	419.0	434.6	453.4	464.3	459.3	424.3
105°	507.2	504.3	499.4	497.3	499.4	504.3	507.2	506.5	492.0	457.0	395.8
107.5°	518.8	526.9	530.4	531.3	530.4	526.9	518.8	501.4	469.8	420.6	355.5
110°	507.5	522.4	528.7	531.9	528.7	522.4	507.5	482.4	443.6	392.3	331.2



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	483.2	501.2	510.1	515.2	510.1	501.2	483.2	454.7	415.8	367.4	313.3
115°	442.1	463.3	474.7	477.5	474.7	463.3	442.1	414.2	380.3	338.9	295.5
117.5°	407.8	425.6	437.0	439.2	437.0	425.6	407.8	384.0	355.2	322.7	286.7
120°	389.1	404.7	413.9	417.8	413.9	404.7	389.1	369.0	343.9	315.6	282.7
122.5°	375.8	389.1	396.9	400.8	396.9	389.1	375.8	358.8	336.8	311.1	279.3
125°	361.9	372.2	378.9	381.0	378.9	372.2	361.9	347.8	328.3	303.9	273.6
127.5°	352.5	361.6	367.3	369.4	367.3	361.6	352.5	338.3	319.9	295.5	266.5
130°	346.0	354.8	360.5	362.6	360.5	354.8	346.0	331.5	312.8	288.8	260.8
132.5°	337.5	347.5	352.9	355.0	352.9	347.5	337.5	323.3	304.6	281.1	254.9
135°	323.0	332.9	338.6	340.7	338.6	332.9	323.0	308.9	291.2	269.7	246.7
137.5°	306.1	315.8	320.5	323.0	320.5	315.8	306.1	292.8	276.9	258.7	239.3
140°	294.8	302.5	307.5	310.3	307.5	302.5	294.8	282.4	267.5	251.6	235.0
142.5°	283.2	290.4	294.8	296.7	294.8	290.4	283.2	272.2	259.3	245.7	231.1
145°	266.8	272.8	276.4	278.1	276.4	272.8	266.8	258.0	248.1	237.5	225.5
147.5°	253.2	258.4	261.0	261.7	261.0	258.4	253.2	246.7	238.9	230.4	220.9
150°	245.3	249.9	252.0	252.3	252.0	249.9	245.3	239.6	233.3	226.2	218.1
152.5°	238.5	242.2	243.5	243.9	243.5	242.2	238.5	233.7	228.5	222.0	215.0
155°	229.0	231.8	232.9	232.9	232.9	231.8	229.0	225.5	221.2	215.9	210.3
157.5°	220.5	222.7	223.3	223.3	223.3	222.7	220.5	217.9	214.5	210.0	205.3
160°	214.9	217.0	217.4	217.4	217.4	217.0	214.9	212.8	209.9	206.0	202.2
162.5°	209.5	211.6	212.0	211.7	212.0	211.6	209.5	208.0	205.4	202.4	199.1
165°	202.5	203.9	203.6	203.2	203.6	203.9	202.5	201.1	199.3	196.9	194.7
167.5°	195.9	196.9	196.8	196.5	196.8	196.9	195.9	195.2	194.2	192.2	190.6
170°	192.3	192.6	192.3	192.3	192.3	192.6	192.3	191.6	190.5	189.1	188.0
172.5°	188.6	188.9	188.6	188.0	188.6	188.9	188.6	188.2	187.4	186.5	185.8
175°	183.8	184.5	183.8	183.1	183.8	184.5	183.8	183.8	183.8	183.1	182.7
177.5°	181.0	181.3	180.7	180.2	180.7	181.3	181.0	181.3	181.0	181.0	180.7
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1595.3	1597.5	1606.3	1614.6	1624.6	1631.8	1636.7	1642.3	1653.9	1663.3	1672.1
5°	1494.6	1498.1	1516.0	1528.5	1549.9	1568.6	1583.1	1599.0	1617.7	1643.2	1666.7
7.5°	1406.0	1418.8	1438.5	1458.7	1480.5	1505.0	1526.3	1550.2	1582.4	1617.5	1653.7
10°	1355.7	1370.2	1390.9	1414.4	1435.2	1463.5	1489.8	1518.1	1554.7	1597.6	1640.5
12.5°	1305.3	1329.2	1345.0	1372.9	1395.3	1418.7	1446.6	1483.8	1526.5	1571.6	1623.3
15°	1242.3	1255.4	1285.8	1301.0	1332.8	1368.8	1396.4	1433.8	1475.2	1534.7	1592.8
17.5°	1169.6	1186.8	1211.0	1240.1	1276.6	1304.6	1339.1	1377.5	1429.8	1488.8	1561.5
20°	1122.0	1136.5	1166.2	1198.0	1236.7	1266.5	1303.1	1340.4	1394.4	1457.3	1533.3
22.5°	1079.4	1093.4	1124.8	1154.3	1191.9	1228.3	1266.6	1310.0	1361.7	1428.0	1505.7
25°	1013.5	1032.1	1059.8	1090.2	1126.1	1167.6	1209.1	1247.8	1303.1	1372.9	1455.9
27.5°	955.0	969.9	990.0	1024.5	1065.3	1105.4	1146.6	1195.3	1248.4	1322.2	1408.3
30°	917.4	931.2	951.2	983.0	1021.1	1063.9	1106.8	1153.8	1209.1	1282.4	1370.2
32.5°	887.5	898.0	915.8	944.3	979.0	1024.1	1066.4	1115.1	1173.1	1245.3	1330.9
35°	843.4	852.4	859.3	886.3	917.4	958.8	1001.7	1053.6	1109.5	1178.0	1263.7
37.5°	800.1	803.2	813.3	830.9	861.1	899.3	939.1	990.1	1047.5	1117.0	1194.3
40°	773.6	775.0	781.2	797.8	824.0	860.0	898.7	949.2	1003.8	1069.5	1146.2
42.5°	747.6	746.7	752.4	764.0	788.6	821.3	859.4	905.5	960.1	1020.8	1093.1
45°	706.5	706.5	705.1	714.8	734.9	766.7	798.5	842.7	888.3	947.8	1008.6
47.5°	663.7	659.8	661.0	666.0	682.9	709.0	741.1	777.3	817.5	867.9	921.2
50°	636.0	630.5	628.4	633.9	649.1	671.9	702.4	734.2	772.2	816.4	862.1
52.5°	605.6	600.1	596.3	600.2	614.3	635.4	663.1	691.0	725.2	761.1	800.7
55°	558.6	552.4	550.3	551.7	562.0	578.6	602.1	627.7	653.3	683.0	710.7
57.5°	512.3	502.0	500.1	499.4	506.6	521.8	541.4	563.6	582.2	600.2	629.6
60°	481.8	469.4	465.2	464.6	470.1	482.5	500.5	522.6	535.8	548.2	573.8
62.5°	449.2	437.3	428.2	429.2	434.1	446.0	461.8	477.8	486.5	500.1	517.4
65°	398.9	383.7	376.8	374.7	377.5	387.1	399.6	409.9	419.6	425.2	441.7
67.5°	348.6	335.8	325.6	323.1	321.9	328.5	338.7	345.0	351.9	356.7	366.5
70°	313.2	302.1	289.7	285.5	284.8	290.3	300.0	300.7	310.4	312.5	322.8
72.5°	278.3	264.5	255.9	251.8	248.9	253.8	260.2	262.0	267.3	271.0	276.4
75°	224.0	213.6	205.3	199.1	197.0	199.8	199.8	203.2	206.7	208.8	215.0
77.5°	176.3	164.4	154.6	151.0	148.5	146.7	148.2	150.3	148.6	152.2	153.6
80°	143.1	130.7	123.1	121.7	117.5	114.1	113.4	115.4	112.7	114.1	118.2
82.5°	110.5	102.5	94.3	92.9	87.7	85.9	85.2	83.9	83.9	83.6	84.5
85°	65.7	60.8	55.3	51.8	49.8	46.3	46.3	44.9	43.6	42.2	42.9
87.5°	27.7	26.7	23.8	22.0	20.9	18.3	18.3	16.5	15.9	15.1	14.4
90°	6.0	6.4	5.7	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4
92.5°	93.4	112.1	98.1	71.4	44.0	26.0	18.7	13.5	9.2	5.9	4.0
95°	296.2	288.0	217.4	132.9	74.9	44.2	29.3	20.9	16.3	12.7	11.7
97.5°	372.1	303.4	203.4	119.5	71.6	47.9	35.5	28.2	24.0	20.9	20.9
100°	374.6	284.2	184.5	112.4	72.5	51.6	40.3	33.6	29.3	26.9	26.9
102.5°	353.4	260.1	171.8	110.4	75.3	56.4	45.7	39.2	35.3	33.1	32.5
105°	314.9	231.8	160.8	111.3	82.0	65.0	54.8	48.4	44.2	42.4	41.4
107.5°	283.8	216.0	158.8	116.6	89.8	74.3	64.2	58.1	53.6	51.8	51.1
110°	268.3	210.6	159.4	120.5	95.8	80.2	70.7	64.3	60.1	58.3	57.6



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	259.5	208.1	161.1	124.8	101.4	86.4	76.9	70.5	66.6	64.5	63.8
115°	251.3	206.8	164.3	131.5	110.3	96.1	86.6	79.9	76.3	73.9	72.8
117.5°	247.6	206.4	167.8	138.3	118.8	105.4	95.5	89.2	85.3	83.1	82.1
120°	245.6	206.4	170.4	143.1	124.8	111.3	101.4	95.4	91.5	89.1	88.4
122.5°	243.4	206.1	172.9	147.7	130.4	117.0	107.4	100.8	97.2	94.7	94.0
125°	239.6	205.7	176.7	154.4	138.2	125.5	115.6	108.9	105.0	102.8	101.4
127.5°	234.6	204.9	179.8	160.3	145.4	133.1	123.1	116.1	111.7	109.1	108.0
130°	231.5	204.6	182.0	164.0	150.2	138.2	127.9	121.2	115.9	113.1	111.7
132.5°	228.7	204.4	184.0	167.7	154.2	142.1	132.5	125.2	120.2	116.5	115.4
135°	224.4	203.9	187.0	172.5	159.7	148.1	138.9	131.5	125.5	121.9	120.5
137.5°	220.8	203.9	188.7	175.9	164.0	153.1	144.3	136.6	130.9	127.0	125.7
140°	218.8	203.6	190.1	178.1	166.8	156.2	147.7	140.3	134.3	130.4	129.4
142.5°	217.1	203.6	191.3	179.8	169.4	159.0	150.8	143.7	138.0	134.4	133.3
145°	214.2	202.9	191.9	181.7	172.1	162.9	155.2	148.4	143.5	140.0	138.9
147.5°	211.6	201.6	192.3	183.3	174.9	166.3	159.3	153.7	148.7	145.5	145.2
150°	209.6	200.7	192.3	184.1	176.4	168.6	161.9	156.6	152.3	149.5	149.1
152.5°	207.3	199.3	191.7	184.7	177.5	170.6	164.4	159.7	155.7	152.9	152.8
155°	203.9	197.2	190.9	185.2	179.2	173.2	167.9	164.0	160.5	158.3	158.0
157.5°	200.5	195.0	189.9	185.2	180.4	175.3	171.1	167.7	165.0	163.0	163.0
160°	197.9	193.3	189.1	185.2	181.0	176.7	172.8	170.0	167.5	166.1	166.1
162.5°	195.7	191.6	188.2	185.2	181.5	177.6	174.5	172.0	169.8	168.7	168.9
165°	191.9	189.1	186.6	184.5	181.7	178.5	176.4	174.6	172.8	172.1	172.1
167.5°	188.5	186.5	184.9	183.6	181.6	179.3	177.6	176.6	175.3	174.9	175.3
170°	186.3	184.8	183.8	183.1	181.3	179.5	178.5	177.8	176.7	176.4	176.7
172.5°	184.3	183.1	182.7	182.5	181.0	179.8	179.0	178.6	177.8	177.8	178.1
175°	182.0	181.3	181.3	181.7	180.6	179.9	179.9	179.5	179.2	179.2	179.5
177.5°	180.5	180.2	180.2	180.7	180.2	179.9	179.9	179.9	179.6	179.9	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1679.9	1685.4	1692.6	1704.8	1709.2	1714.7	1722.5	1721.9	1724.1	1732.4	1750.1
5°	1686.1	1707.5	1728.3	1753.2	1779.4	1796.7	1820.2	1834.7	1849.2	1867.9	1899.7
7.5°	1688.6	1722.6	1760.6	1804.3	1843.2	1888.0	1922.9	1955.8	1985.6	2025.0	2062.9
10°	1684.7	1730.3	1779.4	1834.7	1893.5	1943.3	1988.2	2039.4	2082.9	2130.6	2173.5
12.5°	1677.5	1732.6	1798.2	1860.2	1928.9	2002.4	2058.4	2110.1	2168.1	2223.0	2289.1
15°	1661.2	1736.6	1813.3	1894.9	1986.8	2071.8	2152.7	2219.8	2282.0	2364.3	2450.7
17.5°	1640.5	1721.8	1818.5	1917.3	2013.4	2110.6	2210.7	2311.5	2390.0	2492.2	2559.8
20°	1621.1	1715.1	1814.7	1932.2	2028.3	2149.3	2248.8	2346.3	2454.1	2555.8	2636.6
22.5°	1594.0	1696.9	1802.5	1919.5	2046.0	2167.0	2282.0	2387.8	2495.6	2606.1	2704.1
25°	1559.6	1652.9	1778.0	1910.8	2036.6	2167.9	2300.0	2432.7	2548.8	2665.7	2756.9
27.5°	1501.0	1618.8	1735.3	1872.3	2012.1	2160.7	2301.9	2440.9	2562.5	2658.6	2715.2
30°	1471.1	1573.4	1699.9	1837.5	1988.9	2148.6	2295.8	2432.0	2545.4	2622.1	2644.9
32.5°	1426.9	1532.5	1656.2	1798.8	1959.0	2123.1	2276.5	2404.9	2499.5	2539.7	2512.2
35°	1361.2	1456.6	1581.7	1727.6	1894.2	2069.1	2220.5	2329.0	2377.4	2339.4	2244.7
37.5°	1282.4	1376.9	1502.6	1645.9	1818.3	1996.1	2133.0	2211.1	2195.0	2100.5	1959.3
40°	1227.1	1315.6	1435.2	1590.0	1758.0	1936.3	2056.6	2098.8	2054.6	1919.1	1769.1
42.5°	1165.7	1252.0	1372.1	1521.4	1699.4	1863.9	1968.7	1972.2	1898.0	1736.0	1585.4
45°	1072.2	1154.5	1267.9	1423.4	1587.9	1742.8	1811.9	1778.0	1641.2	1484.9	1333.5
47.5°	980.0	1051.3	1163.1	1310.7	1467.0	1597.3	1631.6	1570.6	1424.8	1273.1	1132.8
50°	912.5	984.4	1089.5	1230.5	1381.2	1493.9	1510.5	1429.6	1286.5	1133.7	1023.8
52.5°	847.8	919.2	1020.4	1150.9	1288.9	1390.5	1391.0	1297.4	1154.9	1018.7	916.5
55°	752.8	817.1	908.4	1025.2	1148.3	1227.8	1208.4	1111.6	987.9	869.7	780.5
57.5°	661.3	717.3	801.4	898.8	1007.2	1072.8	1040.7	947.5	837.0	736.8	669.2
60°	602.1	655.4	727.3	819.2	910.5	961.6	931.2	846.8	745.2	664.3	605.6
62.5°	544.6	589.5	658.7	738.5	823.1	861.0	833.9	750.6	662.8	589.7	542.0
65°	463.2	499.8	555.1	623.6	685.1	717.6	694.8	617.3	550.3	497.7	459.7
67.5°	387.1	415.8	457.6	512.5	564.8	582.4	561.6	507.7	450.9	408.8	382.0
70°	334.6	361.6	396.8	439.0	484.6	503.3	482.5	439.7	393.4	354.6	328.4
72.5°	288.7	309.6	339.3	375.4	411.1	429.7	415.6	374.4	335.3	306.5	284.1
75°	219.8	237.8	258.5	284.1	311.8	324.2	311.8	283.4	256.5	235.0	219.1
77.5°	159.8	169.5	185.5	204.6	221.9	231.4	220.7	201.4	185.0	170.3	162.5
80°	121.7	128.6	139.6	154.9	166.6	175.6	168.7	152.8	139.6	130.0	126.5
82.5°	88.5	93.2	100.4	111.7	119.6	124.2	121.1	109.6	104.2	95.7	92.2
85°	43.6	46.3	51.2	54.6	61.5	62.2	62.9	58.1	53.2	51.2	48.4
87.5°	15.1	15.9	17.6	19.4	21.6	22.6	22.0	22.1	20.1	19.5	17.3
90°	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4
92.5°	5.9	9.2	13.5	18.7	26.0	44.0	71.4	98.1	112.1	93.4	69.4
95°	12.7	16.3	20.9	29.3	44.2	74.9	132.9	217.4	288.0	296.2	261.9
97.5°	20.9	24.0	28.2	35.5	47.9	71.6	119.5	203.4	303.4	372.1	386.9
100°	26.9	29.3	33.6	40.3	51.6	72.5	112.4	184.5	284.2	374.6	426.2
102.5°	33.1	35.3	39.2	45.7	56.4	75.3	110.4	171.8	260.1	353.4	424.3
105°	42.4	44.2	48.4	54.8	65.0	82.0	111.3	160.8	231.8	314.9	395.8
107.5°	51.8	53.6	58.1	64.2	74.3	89.8	116.6	158.8	216.0	283.8	355.5
110°	58.3	60.1	64.3	70.7	80.2	95.8	120.5	159.4	210.6	268.3	331.2





TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	64.5	66.6	70.5	76.9	86.4	101.4	124.8	161.1	208.1	259.5	313.3
115°	73.9	76.3	79.9	86.6	96.1	110.3	131.5	164.3	206.8	251.3	295.5
117.5°	83.1	85.3	89.2	95.5	105.4	118.8	138.3	167.8	206.4	247.6	286.7
120°	89.1	91.5	95.4	101.4	111.3	124.8	143.1	170.4	206.4	245.6	282.7
122.5°	94.7	97.2	100.8	107.4	117.0	130.4	147.7	172.9	206.1	243.4	279.3
125°	102.8	105.0	108.9	115.6	125.5	138.2	154.4	176.7	205.7	239.6	273.6
127.5°	109.1	111.7	116.1	123.1	133.1	145.4	160.3	179.8	204.9	234.6	266.5
130°	113.1	115.9	121.2	127.9	138.2	150.2	164.0	182.0	204.6	231.5	260.8
132.5°	116.5	120.2	125.2	132.5	142.1	154.2	167.7	184.0	204.4	228.7	254.9
135°	121.9	125.5	131.5	138.9	148.1	159.7	172.5	187.0	203.9	224.4	246.7
137.5°	127.0	130.9	136.6	144.3	153.1	164.0	175.9	188.7	203.9	220.8	239.3
140°	130.4	134.3	140.3	147.7	156.2	166.8	178.1	190.1	203.6	218.8	235.0
142.5°	134.4	138.0	143.7	150.8	159.0	169.4	179.8	191.3	203.6	217.1	231.1
145°	140.0	143.5	148.4	155.2	162.9	172.1	181.7	191.9	202.9	214.2	225.5
147.5°	145.5	148.7	153.7	159.3	166.3	174.9	183.3	192.3	201.6	211.6	220.9
150°	149.5	152.3	156.6	161.9	168.6	176.4	184.1	192.3	200.7	209.6	218.1
152.5°	152.9	155.7	159.7	164.4	170.6	177.5	184.7	191.7	199.3	207.3	215.0
155°	158.3	160.5	164.0	167.9	173.2	179.2	185.2	190.9	197.2	203.9	210.3
157.5°	163.0	165.0	167.7	171.1	175.3	180.4	185.2	189.9	195.0	200.5	205.3
160°	166.1	167.5	170.0	172.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2
162.5°	168.7	169.8	172.0	174.5	177.6	181.5	185.2	188.2	191.6	195.7	199.1
165°	172.1	172.8	174.6	176.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7
167.5°	174.9	175.3	176.6	177.6	179.3	181.6	183.6	184.9	186.5	188.5	190.6
170°	176.4	176.7	177.8	178.5	179.5	181.3	183.1	183.8	184.8	186.3	188.0
172.5°	177.8	177.8	178.6	179.0	179.8	181.0	182.5	182.7	183.1	184.3	185.8
175°	179.2	179.2	179.5	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7
177.5°	179.9	179.6	179.9	179.9	179.9	180.2	180.7	180.2	180.2	180.5	180.7
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1759.0	1760.1	1765.0	1768.9	1770.0	1775.6	1776.1
5°	1913.5	1925.3	1948.1	1950.2	1953.6	1971.6	1957.8
7.5°	2094.7	2124.5	2144.4	2162.0	2168.4	2176.2	2174.6
10°	2210.8	2255.0	2277.2	2312.4	2313.8	2322.8	2317.3
12.5°	2327.5	2378.9	2419.3	2425.8	2455.4	2459.9	2467.7
15°	2492.8	2547.5	2603.5	2623.5	2664.3	2674.0	2689.2
17.5°	2648.3	2704.1	2743.4	2795.2	2812.0	2834.4	2819.1
20°	2733.4	2794.3	2844.0	2884.8	2902.1	2914.5	2913.2
22.5°	2784.9	2846.2	2886.6	2917.4	2933.6	2938.9	2938.6
25°	2817.1	2852.3	2864.8	2876.5	2858.6	2852.3	2855.1
27.5°	2727.5	2718.4	2685.9	2643.3	2599.0	2563.9	2544.8
30°	2604.2	2550.2	2501.1	2415.4	2371.2	2344.9	2321.4
32.5°	2429.4	2343.9	2249.5	2171.0	2120.7	2081.7	2075.9
35°	2129.9	2001.3	1885.9	1789.8	1740.0	1697.8	1688.2
37.5°	1810.8	1677.2	1573.3	1488.7	1435.2	1405.4	1377.6
40°	1599.0	1484.2	1381.9	1310.0	1269.2	1247.8	1230.5
42.5°	1435.8	1331.0	1229.3	1174.5	1137.6	1124.5	1114.4
45°	1210.5	1113.0	1042.5	1001.0	979.6	957.5	947.1
47.5°	1030.0	950.7	904.2	869.0	846.0	832.9	826.2
50°	927.7	862.7	821.3	794.3	773.6	763.2	757.7
52.5°	837.0	783.7	748.8	727.4	713.3	705.7	703.5
55°	721.0	680.2	658.1	639.5	629.1	622.2	619.4
57.5°	626.7	595.4	577.4	562.0	558.0	552.2	550.3
60°	564.8	540.6	525.4	515.0	511.6	504.7	506.0
62.5°	510.0	490.3	477.3	471.3	466.8	461.0	462.9
65°	431.4	416.9	409.9	404.4	398.9	395.4	398.2
67.5°	362.0	352.0	342.6	339.4	336.7	336.1	333.2
70°	316.6	308.3	300.0	298.0	298.0	295.2	294.5
72.5°	272.9	266.8	261.3	259.8	257.6	258.7	255.8
75°	210.8	206.0	203.9	201.9	201.2	201.2	199.1
77.5°	155.8	152.2	148.9	148.9	146.4	145.5	145.2
80°	118.2	116.8	114.1	114.1	112.7	113.4	112.0
82.5°	88.9	87.0	86.4	85.3	83.4	83.5	82.1
85°	47.7	45.6	44.9	42.9	41.5	42.9	41.5
87.5°	17.9	17.5	16.9	15.9	15.4	15.3	13.7
90°	6.7	7.1	7.1	7.4	7.8	7.4	7.4
92.5°	52.2	41.6	34.5	30.3	28.4	27.2	27.2
95°	207.1	159.7	125.5	108.1	97.2	90.8	86.2
97.5°	366.6	332.0	295.1	269.7	248.5	237.9	230.5
100°	433.3	416.0	389.8	359.1	337.5	326.9	324.1
102.5°	459.3	464.3	453.4	434.6	419.0	407.8	405.5
105°	457.0	492.0	506.5	507.2	504.3	499.4	497.3
107.5°	420.6	469.8	501.4	518.8	526.9	530.4	531.3
110°	392.3	443.6	482.4	507.5	522.4	528.7	531.9



TEST NUMBER: P332627

CATALOG NUMBER: SA4XXDIP-C1020D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	367.4	415.8	454.7	483.2	501.2	510.1	515.2
115°	338.9	380.3	414.2	442.1	463.3	474.7	477.5
117.5°	322.7	355.2	384.0	407.8	425.6	437.0	439.2
120°	315.6	343.9	369.0	389.1	404.7	413.9	417.8
122.5°	311.1	336.8	358.8	375.8	389.1	396.9	400.8
125°	303.9	328.3	347.8	361.9	372.2	378.9	381.0
127.5°	295.5	319.9	338.3	352.5	361.6	367.3	369.4
130°	288.8	312.8	331.5	346.0	354.8	360.5	362.6
132.5°	281.1	304.6	323.3	337.5	347.5	352.9	355.0
135°	269.7	291.2	308.9	323.0	332.9	338.6	340.7
137.5°	258.7	276.9	292.8	306.1	315.8	320.5	323.0
140°	251.6	267.5	282.4	294.8	302.5	307.5	310.3
142.5°	245.7	259.3	272.2	283.2	290.4	294.8	296.7
145°	237.5	248.1	258.0	266.8	272.8	276.4	278.1
147.5°	230.4	238.9	246.7	253.2	258.4	261.0	261.7
150°	226.2	233.3	239.6	245.3	249.9	252.0	252.3
152.5°	222.0	228.5	233.7	238.5	242.2	243.5	243.9
155°	215.9	221.2	225.5	229.0	231.8	232.9	232.9
157.5°	210.0	214.5	217.9	220.5	222.7	223.3	223.3
160°	206.0	209.9	212.8	214.9	217.0	217.4	217.4
162.5°	202.4	205.4	208.0	209.5	211.6	212.0	211.7
165°	196.9	199.3	201.1	202.5	203.9	203.6	203.2
167.5°	192.2	194.2	195.2	195.9	196.9	196.8	196.5
170°	189.1	190.5	191.6	192.3	192.6	192.3	192.3
172.5°	186.5	187.4	188.2	188.6	188.9	188.6	188.0
175°	183.1	183.8	183.8	183.8	184.5	183.8	183.1
177.5°	181.0	181.0	181.3	181.0	181.3	180.7	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)