

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333008-940

Luminaire Tested: **SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P333008-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7594.4 lumens  
Efficiency: N/A  
Efficacy: 113.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333008-940  
CATALOG NUMBER: SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333008-940

CATALOG NUMBER: SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	92	88	93	89	86	83	77	74	72	66	64	62	55	54	53	48
2	91	84	78	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	39	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	26
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	30	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	27	24	29	25	21	25	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P333008-940

CATALOG NUMBER: SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	2.3
10°-20°	487.1	6.4
20°-30°	703.4	9.3
30°-40°	797.3	10.5
40°-50°	770.0	10.1
50°-60°	640.3	8.4
60°-70°	442.1	5.8
70°-80°	224.1	3.0
80°-90°	60.0	0.8
90°-100°	327.3	4.3
100°-110°	681.1	9.0
110°-120°	610.1	8.0
120°-130°	513.2	6.8
130°-140°	427.9	5.6
140°-150°	326.9	4.3
150°-160°	229.8	3.0
160°-170°	135.2	1.8
170°-180°	44.0	0.6
0°-30°	1365.2	18.0
0°-40°	2162.6	28.5
0°-60°	3572.8	47.0
0°-90°	4299.0	56.6
90°-120°	1618.5	21.3
90°-150°	2886.5	38.0
90°-180°	3295.0	43.4
0°-180°	7594.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	86
90°	1	7	16	18	19	5
95°	29	93	726	359	217	33
105°	104	151	584	1257	1252	111
115°	183	230	521	1001	1203	182
125°	256	304	518	851	960	227
135°	304	361	514	756	858	235
145°	350	401	511	637	701	220
155°	398	430	497	563	587	183
165°	434	447	476	504	512	122
175°	452	453	457	463	461	43
180°	453	453	453	453	453	



TEST NUMBER: P333008-940

CATALOG NUMBER: SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.4	24.7	23.2	21.4	19.5	18.4	19.2	18.9	19.1	19.2	18.7
90°	0.9	2.7	5.4	6.2	7.1	7.1	12.5	12.5	14.3	16.1	15.2
92.5°	10.2	14.8	23.2	34.0	47.0	65.5	110.8	179.9	247.1	282.4	235.2
95°	29.3	32.0	40.9	52.5	73.9	111.3	188.7	334.7	547.5	725.5	746.0
97.5°	52.7	52.7	60.4	71.1	89.3	120.7	180.4	300.9	512.4	764.1	937.2
100°	67.7	67.7	73.9	84.5	101.5	130.0	182.5	283.1	464.7	715.7	943.6
102.5°	81.9	83.3	88.8	98.8	115.0	142.0	189.6	278.1	432.7	655.2	890.2
105°	104.2	106.8	111.3	122.0	137.9	163.8	206.5	280.4	405.0	584.0	793.2
107.5°	128.8	130.5	134.9	146.3	161.7	187.1	226.3	293.6	400.0	544.1	714.8
110°	145.1	146.9	151.3	162.0	178.1	202.1	241.2	303.5	401.4	530.6	675.6



TEST NUMBER: P333008-940

CATALOG NUMBER: SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.8	162.6	167.7	177.7	193.7	217.8	255.5	314.2	405.7	524.1	653.6
115°	183.4	186.0	192.3	201.2	218.1	242.1	277.8	331.2	413.9	520.8	632.9
117.5°	206.9	209.4	214.9	224.7	240.5	265.5	299.3	348.4	422.7	519.9	623.7
120°	222.6	224.4	230.6	240.3	255.5	280.4	314.2	360.5	429.1	519.9	618.7
122.5°	236.8	238.5	244.8	253.9	270.5	294.6	328.5	371.9	435.5	519.2	613.0
125°	255.5	259.0	264.4	274.2	291.1	316.0	348.0	389.1	445.1	518.1	603.6
127.5°	272.1	274.9	281.3	292.5	310.1	335.3	366.2	403.8	452.7	516.1	590.9
130°	281.3	284.9	291.9	305.3	322.3	348.0	378.4	413.0	458.4	515.4	583.1
132.5°	290.5	293.4	302.6	315.3	333.7	358.0	388.3	422.3	463.4	514.7	576.0
135°	303.5	307.1	316.0	331.2	349.8	373.0	402.3	434.4	470.9	513.6	565.3
137.5°	316.6	319.9	329.8	344.1	363.6	385.7	413.0	443.0	475.4	513.4	556.0
140°	325.8	328.5	338.3	353.4	372.1	393.5	420.2	448.6	478.9	512.7	551.1
142.5°	335.8	338.5	347.5	361.9	380.0	400.6	426.6	452.9	481.8	512.7	546.8
145°	349.8	352.5	361.4	373.9	390.8	410.4	433.5	457.5	483.4	511.0	539.5
147.5°	365.7	366.6	374.4	387.3	401.3	418.9	440.7	461.6	484.3	507.7	532.9
150°	375.7	376.6	383.7	394.4	407.7	424.6	444.3	463.8	484.3	505.6	527.9
152.5°	385.0	385.1	392.3	402.2	414.1	429.6	447.1	465.2	482.9	502.0	522.2
155°	397.9	398.8	404.1	413.0	422.8	436.2	451.3	466.5	480.7	496.8	513.6
157.5°	410.5	410.5	415.5	422.5	431.1	441.6	454.3	466.5	478.4	491.2	504.9
160°	418.4	418.4	422.0	428.2	435.3	445.1	455.8	466.5	476.3	487.0	498.6
162.5°	425.5	424.8	427.7	433.2	439.6	447.3	457.2	466.5	474.1	482.7	492.8
165°	433.5	433.5	435.3	439.8	444.3	449.5	457.5	464.7	470.0	476.3	483.4
167.5°	441.6	440.7	441.6	445.0	447.5	451.5	457.4	462.5	465.7	469.8	474.8
170°	445.1	444.3	445.1	447.8	449.5	452.2	456.6	461.1	462.9	465.6	469.1
172.5°	448.6	447.8	447.9	449.9	450.9	452.9	455.9	459.7	460.0	461.3	464.1
175°	452.2	451.3	451.3	452.2	453.1	453.1	454.9	457.5	456.6	456.6	458.4
177.5°	453.8	453.1	452.4	453.1	453.1	453.1	453.8	455.2	453.8	453.8	454.5
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P333008-940

CATALOG NUMBER: SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	18.6	18.5	18.5	18.5	18.9	19.4	19.4	19.7
90°	16.1	16.9	17.8	17.8	18.7	19.6	18.7	18.7
92.5°	174.9	131.6	104.7	86.9	76.4	71.6	68.6	68.6
95°	659.6	521.7	402.3	316.0	272.4	244.8	228.8	217.2
97.5°	974.6	923.3	836.2	743.3	679.4	625.8	599.1	580.6
100°	1073.6	1091.4	1047.8	981.9	904.5	850.2	823.4	816.4
102.5°	1068.6	1156.9	1169.6	1142.1	1094.6	1055.3	1027.2	1021.5
105°	997.0	1151.0	1239.1	1275.7	1277.5	1270.3	1257.8	1252.5
107.5°	895.4	1059.4	1183.5	1262.8	1306.8	1327.1	1336.1	1338.4
110°	834.1	988.1	1117.2	1215.1	1278.4	1315.7	1331.8	1339.8





TEST NUMBER: P333008-940

CATALOG NUMBER: SA4XXRDIP-C1195D1035U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	789.3	925.4	1047.4	1145.3	1217.1	1262.3	1284.8	1297.7
115°	744.2	853.7	957.9	1043.3	1113.7	1167.1	1195.5	1202.7
117.5°	722.1	812.8	894.7	967.1	1027.2	1072.0	1100.8	1106.3
120°	712.1	795.0	866.2	929.3	980.1	1019.3	1042.4	1052.2
122.5°	703.6	783.5	848.4	903.7	946.6	980.1	999.7	1009.5
125°	689.0	765.5	827.0	875.9	911.6	937.4	954.3	959.7
127.5°	671.2	744.4	805.7	852.1	887.9	910.9	925.1	930.4
130°	657.0	727.3	787.8	835.0	871.5	893.8	908.0	913.4
132.5°	642.0	708.1	767.1	814.4	850.2	875.2	888.8	894.1
135°	621.3	679.2	733.5	778.0	813.7	838.6	852.8	858.2
137.5°	602.7	651.7	697.4	737.6	770.9	795.5	807.3	813.7
140°	592.0	633.8	673.9	711.2	742.4	762.1	774.5	781.6
142.5°	582.0	618.8	653.3	685.6	713.2	731.4	742.4	747.4
145°	567.9	598.2	624.9	649.9	672.1	687.2	696.2	700.6
147.5°	556.3	580.4	601.8	621.3	637.8	650.8	657.5	659.1
150°	549.3	569.7	587.5	603.6	617.8	629.4	634.7	635.6
152.5°	541.4	559.0	575.4	588.6	600.7	610.1	613.3	614.2
155°	529.7	543.9	557.2	567.9	576.8	584.0	586.7	586.7
157.5°	517.0	529.0	540.2	548.8	555.4	560.8	562.4	562.4
160°	509.2	519.0	528.8	535.9	541.3	546.6	547.5	547.5
162.5°	501.3	509.7	517.4	523.8	527.7	533.1	534.0	533.2
165°	490.5	495.9	502.0	506.5	510.1	513.6	512.7	511.8
167.5°	480.0	484.1	489.1	491.8	493.6	495.9	495.7	495.0
170°	473.6	476.3	479.8	482.5	484.3	485.2	484.3	484.3
172.5°	467.9	469.8	472.0	473.9	475.0	475.9	475.0	473.6
175°	460.2	461.1	462.9	462.9	462.9	464.7	462.9	461.1
177.5°	455.2	455.9	455.9	456.6	455.9	456.6	455.2	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1

(END OF REPORT)