

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332641

Luminaire Tested: **SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332641
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6476.1 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332641
CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332641

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62	58
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44	41
4	78	66	58	52	73	63	56	50	56	50	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332641

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.5
10°-20°	457.8	7.1
20°-30°	673.9	10.4
30°-40°	783.4	12.1
40°-50°	783.4	12.1
50°-60°	685.3	10.6
60°-70°	508.9	7.9
70°-80°	289.1	4.5
80°-90°	85.7	1.3
90°-100°	48.6	0.8
100°-110°	144.1	2.2
110°-120°	244.6	3.8
120°-130°	322.5	5.0
130°-140°	362.2	5.6
140°-150°	355.9	5.5
150°-160°	299.3	4.6
160°-170°	199.1	3.1
170°-180°	69.7	1.1
0°-30°	1294.2	20.0
0°-40°	2077.6	32.1
0°-60°	3546.4	54.8
0°-90°	4430.1	68.4
90°-120°	437.3	6.8
90°-150°	1477.8	22.8
90°-180°	2046.0	31.6
0°-180°	6476.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	2	8	12	16	17	6
95°	34	39	43	45	45	38
105°	133	134	136	137	139	141
115°	249	249	248	247	246	245
125°	362	362	362	360	359	323
135°	467	470	470	469	468	361
145°	568	570	570	570	568	355
155°	650	650	650	652	650	299
165°	708	706	705	708	706	199
175°	736	734	733	736	733	70
180°	738	738	738	738	738	



TEST NUMBER: P332641

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.1	29.1	29.2	29.2	29.2	29.2	29.2	29.1	29.1	29.1	29.2
90°	1.7	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3
92.5°	12.2	13.8	15.4	17.0	18.6	19.7	20.5	21.2	21.9	22.6	23.0
95°	34.2	35.4	36.5	37.6	38.8	39.8	40.7	41.6	42.5	43.3	43.7
97.5°	59.8	60.7	61.6	62.5	63.4	64.4	65.4	66.5	67.5	68.6	69.0
100°	79.8	80.4	80.9	81.4	81.9	82.7	83.8	85.0	86.1	87.3	87.5
102.5°	100.8	101.0	101.2	101.4	101.6	102.3	103.3	104.3	105.4	106.4	106.8
105°	132.9	133.0	133.1	133.3	133.4	133.7	134.2	134.7	135.2	135.7	136.1
107.5°	166.5	166.7	166.8	167.0	167.2	167.3	167.3	167.4	167.5	167.6	167.9
110°	189.4	189.6	189.9	190.1	190.4	190.4	190.3	190.2	190.1	189.9	189.7



TEST NUMBER: P332641

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.1	213.1	213.2	213.2	213.3	213.2	213.0	212.7	212.5	212.3	212.2
115°	248.7	248.7	248.7	248.7	248.7	248.5	248.3	248.0	247.8	247.5	247.4
117.5°	282.2	282.3	282.4	282.5	282.6	282.6	282.4	282.2	282.0	281.9	281.4
120°	304.6	305.1	305.6	306.1	306.6	306.7	306.3	305.9	305.5	305.1	304.5
122.5°	327.8	328.0	328.2	328.4	328.6	328.7	328.5	328.3	328.1	328.0	327.5
125°	362.2	362.2	362.2	362.2	362.2	362.1	362.0	361.9	361.7	361.6	361.3
127.5°	393.3	393.7	394.1	394.5	394.8	394.9	394.7	394.5	394.3	394.1	393.9
130°	415.2	415.6	416.0	416.4	416.7	416.9	416.9	416.9	416.9	416.9	416.7
132.5°	437.6	437.9	438.1	438.4	438.7	438.8	438.7	438.6	438.5	438.4	438.1
135°	467.1	467.9	468.6	469.4	470.2	470.5	470.5	470.5	470.5	470.5	470.3
137.5°	499.3	499.6	500.0	500.3	500.7	501.0	501.2	501.4	501.6	501.8	501.5
140°	520.7	521.0	521.2	521.5	521.7	521.9	521.9	521.9	521.9	521.9	521.7
142.5°	540.3	540.6	540.9	541.1	541.4	541.4	541.3	541.2	541.1	541.0	541.0
145°	567.5	568.0	568.5	569.0	569.5	569.8	570.0	570.1	570.2	570.3	570.2
147.5°	594.4	595.0	595.6	596.2	596.9	597.1	597.0	596.9	596.8	596.7	596.6
150°	610.8	611.4	611.9	612.4	612.9	613.1	613.1	613.1	613.1	613.1	613.1
152.5°	626.4	626.7	627.0	627.3	627.6	627.8	627.9	628.0	628.1	628.2	628.5
155°	650.2	650.2	650.2	650.2	650.2	650.1	650.0	649.9	649.8	649.6	650.1
157.5°	670.3	670.0	669.8	669.6	669.4	669.2	669.2	669.2	669.2	669.1	669.5
160°	682.1	682.0	681.9	681.8	681.6	681.5	681.4	681.3	681.1	681.0	681.4
162.5°	693.1	692.8	692.4	692.1	691.8	691.5	691.4	691.3	691.2	691.0	691.7
165°	707.8	707.4	707.0	706.7	706.3	706.0	705.7	705.5	705.2	705.0	705.7
167.5°	719.1	718.6	718.0	717.5	717.0	716.7	716.7	716.8	716.8	716.8	717.6
170°	725.5	724.9	724.2	723.6	722.9	722.7	722.8	722.9	723.1	723.2	724.0
172.5°	730.0	729.5	729.0	728.5	727.9	727.7	727.7	727.7	727.7	727.8	728.6
175°	736.3	735.7	735.1	734.4	733.8	733.4	733.3	733.2	733.0	732.9	733.8
177.5°	738.4	737.9	737.4	736.9	736.3	736.1	736.1	736.1	736.1	736.1	736.8
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332641

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	29.4	29.5	29.7	29.8	29.8	29.9	29.9	30.0
90°	14.1	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	23.5	24.0	24.4	24.7	24.9	25.0	25.2	25.3
95°	44.1	44.5	44.9	45.1	45.1	45.1	45.1	45.1
97.5°	69.5	69.9	70.4	70.6	70.6	70.6	70.6	70.6
100°	87.8	88.0	88.3	88.4	88.4	88.4	88.4	88.4
102.5°	107.1	107.5	107.8	108.1	108.2	108.3	108.4	108.5
105°	136.5	136.9	137.3	137.6	138.0	138.4	138.8	139.2
107.5°	168.3	168.6	169.0	169.2	169.1	169.1	169.1	169.1
110°	189.4	189.2	188.9	189.0	189.4	189.7	190.1	190.5



TEST NUMBER: P332641

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.2	212.1	212.1	212.1	212.2	212.2	212.3	212.4
115°	247.3	247.2	247.0	246.9	246.8	246.6	246.5	246.4
117.5°	281.0	280.6	280.1	279.8	279.5	279.3	279.0	278.8
120°	303.9	303.2	302.6	302.4	302.7	302.9	303.2	303.4
122.5°	327.1	326.7	326.2	325.8	325.3	324.9	324.4	324.0
125°	361.1	360.8	360.6	360.3	360.1	359.8	359.6	359.3
127.5°	393.6	393.4	393.1	392.9	392.7	392.5	392.3	392.1
130°	416.4	416.2	415.9	415.5	415.0	414.5	414.0	413.5
132.5°	437.9	437.6	437.4	437.1	436.9	436.7	436.5	436.3
135°	470.0	469.8	469.5	469.2	468.8	468.4	468.1	467.7
137.5°	501.1	500.8	500.5	500.3	500.4	500.5	500.6	500.7
140°	521.6	521.5	521.4	521.2	521.1	521.0	520.9	520.7
142.5°	541.0	541.0	540.9	540.9	540.9	540.9	540.8	540.8
145°	570.1	570.0	569.8	569.6	569.2	568.8	568.4	568.1
147.5°	596.5	596.4	596.3	596.2	596.1	595.9	595.8	595.7
150°	613.1	613.1	613.1	613.1	612.9	612.8	612.7	612.6
152.5°	628.8	629.1	629.4	629.4	629.1	628.7	628.4	628.1
155°	650.6	651.1	651.7	651.7	651.1	650.6	650.1	649.6
157.5°	669.9	670.3	670.7	670.6	670.2	669.8	669.3	668.9
160°	681.8	682.1	682.5	682.4	681.8	681.1	680.5	679.9
162.5°	692.4	693.1	693.8	693.8	693.2	692.5	691.9	691.3
165°	706.5	707.2	708.0	708.1	707.6	707.1	706.6	706.1
167.5°	718.3	719.1	719.9	719.8	719.1	718.3	717.5	716.7
170°	724.7	725.5	726.2	726.2	725.3	724.4	723.5	722.6
172.5°	729.5	730.4	731.2	731.2	730.3	729.4	728.5	727.7
175°	734.7	735.6	736.4	736.4	735.6	734.7	733.8	732.9
177.5°	737.5	738.2	738.9	738.9	738.1	737.3	736.4	735.6
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5

(END OF REPORT)