

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332996-940

Luminaire Tested: **SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332996-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6181.0 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332996-940

CATALOG NUMBER: SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332996-940

CATALOG NUMBER: SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70				
1	103	98	94	91	97	93	90	87	83	81	78	74	72	71	66	65	63	59				
2	94	86	80	75	88	82	76	72	73	69	65	66	62	60	59	56	54	50				
3	86	76	69	63	81	72	66	60	65	60	56	58	54	51	52	49	46	43				
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40	37				
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	32				
6	67	55	46	40	63	52	45	39	47	41	36	43	38	34	39	34	31	29				
7	62	50	41	36	59	47	40	35	43	37	32	39	34	30	35	31	28	26				
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	33	28	25	23				
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21				
10	50	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P332996-940

CATALOG NUMBER: SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	2.8
10°-20°	487.1	7.9
20°-30°	703.4	11.4
30°-40°	797.3	12.9
40°-50°	770.0	12.5
50°-60°	640.3	10.4
60°-70°	442.1	7.2
70°-80°	224.1	3.6
80°-90°	58.9	1.0
90°-100°	187.0	3.0
100°-110°	389.2	6.3
110°-120°	348.6	5.6
120°-130°	293.2	4.7
130°-140°	244.5	4.0
140°-150°	186.8	3.0
150°-160°	131.3	2.1
160°-170°	77.2	1.2
170°-180°	25.1	0.4
0°-30°	1365.2	22.1
0°-40°	2162.6	35.0
0°-60°	3572.8	57.8
0°-90°	4297.9	69.5
90°-120°	924.8	15.0
90°-150°	1649.4	26.7
90°-180°	1883.0	30.5
0°-180°	6181.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	86
90°	0	4	9	10	11	5
95°	17	53	415	205	124	19
105°	60	86	334	719	716	63
115°	105	132	298	572	687	104
125°	146	173	296	486	548	130
135°	173	206	294	432	490	134
145°	200	229	292	364	400	125
155°	227	245	284	321	335	105
165°	248	255	272	288	292	70
175°	258	259	261	264	264	25
180°	259	259	259	259	259	



TEST NUMBER: P332996-940

CATALOG NUMBER: SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.3	24.5	22.7	20.9	18.9	17.7	18.1	17.8	17.8	17.7	17.4
90°	0.5	1.5	3.0	3.6	4.1	4.1	7.1	7.1	8.1	9.2	8.6
92.5°	5.8	8.5	13.2	19.4	26.8	37.5	63.3	102.7	141.2	161.3	134.4
95°	16.8	18.3	23.4	30.1	42.2	63.6	107.8	191.3	312.8	414.6	426.2
97.5°	30.1	30.1	34.5	40.6	51.1	69.0	103.1	171.9	292.8	436.7	535.6
100°	38.7	38.7	42.2	48.3	58.0	74.3	104.2	161.8	265.6	408.9	539.2
102.5°	46.8	47.6	50.7	56.4	65.7	81.1	108.3	158.9	247.2	374.4	508.6
105°	59.5	61.1	63.6	69.7	78.8	93.6	118.0	160.2	231.5	333.7	453.3
107.5°	73.6	74.5	77.1	83.6	92.4	106.9	129.3	167.7	228.6	310.9	408.5
110°	82.9	83.9	86.5	92.6	101.7	115.5	137.9	173.4	229.4	303.2	386.1



TEST NUMBER: P332996-940

CATALOG NUMBER: SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	91.8	92.9	95.9	101.6	110.7	124.4	146.0	179.6	231.8	299.5	373.4
115°	104.8	106.3	109.9	114.9	124.7	138.4	158.7	189.2	236.6	297.6	361.7
117.5°	118.2	119.7	122.8	128.4	137.4	151.7	171.0	199.1	241.5	297.0	356.4
120°	127.2	128.2	131.7	137.3	146.0	160.2	179.6	206.0	245.2	297.0	353.6
122.5°	135.3	136.3	139.9	145.1	154.5	168.4	187.7	212.5	248.9	296.7	350.3
125°	146.0	148.0	151.1	156.7	166.3	180.6	198.9	222.3	254.3	296.0	344.9
127.5°	155.4	157.1	160.8	167.1	177.2	191.5	209.3	230.8	258.7	294.9	337.7
130°	160.8	162.7	166.8	174.5	184.1	198.9	216.2	236.0	262.0	294.5	333.1
132.5°	166.0	167.6	173.0	180.2	190.6	204.6	221.9	241.3	264.8	294.1	329.1
135°	173.4	175.5	180.6	189.2	199.9	213.1	229.9	248.3	269.1	293.5	323.0
137.5°	180.9	182.8	188.4	196.6	207.8	220.3	236.0	253.2	271.6	293.4	317.7
140°	186.2	187.7	193.3	202.0	212.6	224.8	240.1	256.4	273.7	293.0	314.9
142.5°	191.9	193.4	198.6	206.8	217.1	228.9	243.8	258.8	275.3	293.0	312.5
145°	199.9	201.4	206.5	213.7	223.3	234.5	247.7	261.4	276.3	291.9	308.3
147.5°	208.9	209.5	213.9	221.2	229.3	239.4	251.8	263.8	276.7	290.2	304.5
150°	214.6	215.2	219.3	225.3	233.0	242.6	253.9	265.0	276.7	288.9	301.7
152.5°	220.0	220.1	224.1	229.8	236.7	245.5	255.5	265.8	275.9	286.9	298.4
155°	227.4	227.9	231.0	236.0	241.7	249.2	257.9	266.5	274.6	283.8	293.5
157.5°	234.6	234.6	237.5	241.4	246.3	252.3	259.7	266.5	273.4	280.7	288.6
160°	239.1	239.1	241.1	244.7	248.7	254.3	260.5	266.5	272.2	278.2	284.9
162.5°	243.2	242.7	244.3	247.5	251.2	255.6	261.3	266.5	270.9	275.8	281.6
165°	247.7	247.7	248.7	251.3	253.9	256.9	261.4	265.6	268.6	272.2	276.3
167.5°	252.3	251.8	252.3	254.2	255.7	258.0	261.4	264.3	266.2	268.5	271.3
170°	254.3	253.9	254.3	255.8	256.9	258.4	260.9	263.5	264.5	266.0	268.0
172.5°	256.4	255.8	255.9	257.1	257.7	258.8	260.6	262.7	262.9	263.6	265.2
175°	258.4	257.9	257.9	258.4	259.0	259.0	259.9	261.4	260.9	260.9	262.0
177.5°	259.3	259.0	258.5	259.0	259.0	259.0	259.3	260.1	259.3	259.3	259.8
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332996-940

CATALOG NUMBER: SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	17.3	17.1	16.9	16.9	17.3	17.7	17.8	18.1
90°	9.2	9.6	10.2	10.2	10.7	11.1	10.7	10.7
92.5°	99.9	75.2	59.8	49.7	43.6	40.9	39.1	39.1
95°	376.9	298.1	229.9	180.6	155.7	139.9	130.7	124.1
97.5°	556.9	527.6	477.9	424.7	388.3	357.6	342.3	331.7
100°	613.5	623.7	598.7	561.1	516.8	485.8	470.6	466.5
102.5°	610.6	661.1	668.3	652.6	625.4	603.0	586.9	583.6
105°	569.7	657.7	708.1	729.0	730.0	725.9	718.7	715.7
107.5°	511.7	605.3	676.3	721.6	746.7	758.3	763.4	764.7
110°	476.6	564.6	638.4	694.4	730.5	751.8	761.0	765.5





TEST NUMBER: P332996-940

CATALOG NUMBER: SA4XXRDIP-C1195D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.0	528.8	598.5	654.4	695.4	721.3	734.1	741.5
115°	425.3	487.9	547.3	596.2	636.3	666.9	683.1	687.2
117.5°	412.6	464.4	511.2	552.6	586.9	612.5	629.0	632.2
120°	407.0	454.2	494.9	531.0	560.1	582.5	595.7	601.3
122.5°	402.1	447.7	484.7	516.4	540.9	560.1	571.2	576.8
125°	393.7	437.5	472.5	500.5	520.8	535.7	545.3	548.3
127.5°	383.5	425.3	460.4	486.9	507.4	520.5	528.6	531.6
130°	375.4	415.6	450.1	477.2	498.0	510.7	518.9	521.9
132.5°	366.8	404.6	438.4	465.3	485.8	500.2	507.8	511.0
135°	355.1	388.2	419.1	444.6	464.9	479.2	487.3	490.4
137.5°	344.4	372.4	398.5	421.5	440.5	454.6	461.3	464.9
140°	338.2	362.2	385.0	406.4	424.3	435.4	442.6	446.7
142.5°	332.6	353.7	373.3	391.8	407.5	417.9	424.3	427.0
145°	324.5	341.8	357.1	371.3	384.1	392.7	397.8	400.3
147.5°	317.9	331.6	343.8	355.1	364.4	371.8	375.7	376.7
150°	313.9	325.6	335.7	344.9	353.0	359.6	362.7	363.2
152.5°	309.3	319.4	328.8	336.4	343.2	348.7	350.4	351.0
155°	302.6	310.8	318.4	324.5	329.7	333.7	335.2	335.2
157.5°	295.4	302.3	308.6	313.5	317.4	320.5	321.4	321.4
160°	291.0	296.6	302.1	306.2	309.2	312.4	312.8	312.8
162.5°	286.5	291.2	295.6	299.3	301.6	304.6	305.1	304.7
165°	280.3	283.3	286.9	289.4	291.5	293.5	293.0	292.5
167.5°	274.3	276.6	279.5	281.0	282.0	283.3	283.2	282.9
170°	270.6	272.2	274.2	275.7	276.7	277.2	276.7	276.7
172.5°	267.3	268.5	269.7	270.8	271.4	272.0	271.4	270.6
175°	263.0	263.5	264.5	264.5	264.5	265.6	264.5	263.5
177.5°	260.1	260.6	260.6	260.9	260.6	260.9	260.1	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)