

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333000-940

Luminaire Tested: **SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P333000-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7182.7 lumens  
Efficiency: N/A  
Efficacy: 118.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333000-940  
CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333000-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	35	56	45	38	33	40	34	30	36	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P333000-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	2.4
10°-20°	487.1	6.8
20°-30°	703.4	9.8
30°-40°	797.3	11.1
40°-50°	770.0	10.7
50°-60°	640.3	8.9
60°-70°	442.1	6.2
70°-80°	224.1	3.1
80°-90°	60.2	0.8
90°-100°	31.9	0.4
100°-110°	203.3	2.8
110°-120°	388.9	5.4
120°-130°	493.7	6.9
130°-140°	528.2	7.4
140°-150°	493.9	6.9
150°-160°	398.3	5.5
160°-170°	256.9	3.6
170°-180°	88.5	1.2
0°-30°	1365.2	19.0
0°-40°	2162.6	30.1
0°-60°	3572.8	49.7
0°-90°	4299.2	59.9
90°-120°	624.1	8.7
90°-150°	2139.8	29.8
90°-180°	2884.0	40.2
0°-180°	7182.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	87
90°	2	10	15	19	21	5
95°	38	16	15	19	20	49
105°	210	214	218	222	199	220
115°	392	394	393	395	395	385
125°	551	553	552	554	555	492
135°	683	683	685	687	688	526
145°	788	790	790	791	792	492
155°	864	864	862	865	863	398
165°	911	908	908	913	907	257
175°	932	928	929	934	927	89
180°	932	932	932	932	932	



TEST NUMBER: P333000-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.7	25.0	23.3	21.6	19.9	19.0	19.0	19.0	19.0	19.0	18.9
90°	2.1	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2
92.5°	8.8	8.9	9.0	9.1	9.2	9.8	11.1	12.3	13.6	14.8	15.7
95°	38.3	33.1	27.8	22.6	17.3	14.7	14.9	15.1	15.2	15.3	16.2
97.5°	81.4	84.7	88.0	91.3	94.6	87.6	70.3	53.0	35.7	18.4	18.5
100°	114.3	117.2	119.9	122.7	125.5	116.2	94.8	73.5	52.1	30.7	28.0
102.5°	151.1	153.2	155.2	157.3	159.3	159.0	156.1	153.4	150.6	147.8	119.4
105°	209.8	210.8	211.7	212.7	213.6	214.5	215.2	216.0	216.8	217.5	218.9
107.5°	264.4	264.8	265.3	265.8	266.3	267.0	268.0	269.1	270.2	271.3	271.9
110°	301.2	301.7	302.1	302.6	303.1	303.7	304.7	305.6	306.6	307.5	307.8



TEST NUMBER: P333000-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.9	337.7	338.6	339.4	340.3	340.9	341.3	341.7	342.1	342.6	342.6
115°	391.8	392.3	392.8	393.2	393.7	393.9	393.7	393.5	393.4	393.2	393.5
117.5°	441.3	441.9	442.6	443.2	443.8	444.3	444.6	445.0	445.3	445.7	445.6
120°	474.8	475.5	476.1	476.7	477.2	477.5	477.3	477.2	477.1	476.9	477.2
122.5°	506.0	506.4	506.8	507.1	507.6	507.8	508.0	508.3	508.5	508.7	508.9
125°	550.8	551.4	552.1	552.7	553.3	553.4	553.1	552.9	552.5	552.2	552.7
127.5°	593.2	593.3	593.5	593.7	593.8	594.2	594.9	595.7	596.4	597.1	597.0
130°	620.5	620.7	620.8	621.0	621.2	621.4	621.9	622.4	622.9	623.3	623.5
132.5°	645.6	645.9	646.2	646.5	646.8	647.2	647.7	648.4	648.9	649.5	649.7
135°	683.3	683.1	683.0	682.8	682.7	682.9	683.5	684.1	684.7	685.4	685.6
137.5°	716.6	716.7	716.8	716.8	716.8	717.2	717.9	718.6	719.3	720.0	720.3
140°	738.3	738.7	739.0	739.3	739.6	739.9	740.2	740.6	740.8	741.1	741.6
142.5°	757.9	758.4	759.0	759.6	760.1	760.5	760.6	760.9	761.1	761.3	761.6
145°	787.8	788.4	788.8	789.3	789.7	790.0	790.0	790.0	790.0	790.0	790.1
147.5°	811.7	812.6	813.4	814.3	815.2	815.6	815.4	815.2	815.0	814.9	815.0
150°	829.0	829.6	830.3	830.9	831.4	831.7	831.5	831.4	831.3	831.1	831.1
152.5°	843.5	844.0	844.5	845.0	845.5	845.6	845.3	845.1	844.7	844.5	844.7
155°	863.9	864.0	864.2	864.3	864.5	864.3	863.9	863.4	862.9	862.5	863.1
157.5°	881.0	880.9	880.8	880.7	880.7	880.3	879.8	879.3	878.8	878.2	879.0
160°	891.1	890.6	890.1	889.7	889.2	888.9	888.8	888.6	888.4	888.2	889.2
162.5°	900.0	899.4	898.8	898.2	897.6	897.2	897.1	897.0	896.8	896.6	897.6
165°	911.2	910.5	909.7	908.9	908.2	907.8	907.8	907.8	907.8	907.8	909.0
167.5°	920.2	919.4	918.6	917.7	916.9	916.5	916.4	916.3	916.2	916.1	917.5
170°	925.2	924.3	923.4	922.4	921.5	921.1	921.2	921.4	921.6	921.8	922.9
172.5°	928.5	927.6	926.7	925.8	924.9	924.4	924.6	924.8	924.9	925.1	926.3
175°	932.2	931.2	930.3	929.4	928.4	928.1	928.3	928.4	928.5	928.7	930.1
177.5°	933.9	933.0	932.1	931.2	930.4	930.1	930.3	930.6	930.9	931.0	932.0
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P333000-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	18.9	18.8	18.7	18.9	19.2	19.5	19.8	20.2
90°	17.2	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	16.7	17.6	18.5	19.0	19.1	19.1	19.2	19.3
95°	17.2	18.1	19.1	19.6	19.8	19.9	20.1	20.2
97.5°	18.6	18.7	18.8	18.9	19.1	19.2	19.4	19.5
100°	25.4	22.7	20.2	18.9	19.1	19.2	19.4	19.5
102.5°	91.0	62.6	34.2	20.0	20.0	20.0	20.1	20.1
105°	220.3	221.7	223.1	221.1	215.4	209.8	204.3	198.7
107.5°	272.6	273.2	273.9	274.6	275.2	275.7	276.3	277.0
110°	308.1	308.4	308.7	309.1	309.6	310.0	310.5	310.9





TEST NUMBER: P333000-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.5	342.4	342.3	342.6	343.2	343.8	344.4	345.0
115°	393.9	394.1	394.5	394.7	394.7	394.7	394.7	394.7
117.5°	445.5	445.5	445.4	445.3	445.3	445.2	445.1	445.1
120°	477.5	477.9	478.1	478.1	477.9	477.5	477.2	476.9
122.5°	509.1	509.3	509.4	509.3	509.1	508.7	508.5	508.1
125°	553.1	553.6	554.0	554.4	554.6	554.6	554.8	555.0
127.5°	596.9	596.8	596.7	596.6	596.5	596.4	596.3	596.1
130°	623.7	623.8	623.9	624.0	624.0	624.0	624.0	624.0
132.5°	649.9	650.0	650.1	650.1	650.1	649.9	649.8	649.7
135°	686.0	686.3	686.6	686.9	687.2	687.5	687.9	688.1
137.5°	720.6	720.9	721.3	721.4	721.3	721.2	721.1	721.0
140°	742.1	742.5	743.0	743.3	743.5	743.6	743.8	744.0
142.5°	761.9	762.2	762.6	762.8	762.8	762.9	762.9	762.9
145°	790.2	790.4	790.6	790.8	791.1	791.4	791.8	792.0
147.5°	815.2	815.3	815.4	815.6	815.7	815.8	816.0	816.2
150°	831.1	831.1	831.1	831.2	831.3	831.4	831.6	831.8
152.5°	845.0	845.3	845.4	845.5	845.4	845.3	845.3	845.2
155°	863.7	864.3	865.0	865.0	864.5	864.1	863.6	863.2
157.5°	879.9	880.7	881.5	881.5	880.7	879.9	879.0	878.2
160°	890.1	891.1	892.0	892.0	891.1	890.1	889.2	888.2
162.5°	898.5	899.4	900.4	900.3	899.2	898.1	897.2	896.1
165°	910.3	911.5	912.8	912.7	911.2	909.9	908.5	907.0
167.5°	918.9	920.2	921.6	921.5	920.0	918.4	916.9	915.3
170°	924.2	925.4	926.7	926.5	925.0	923.5	921.9	920.3
172.5°	927.6	928.8	930.1	929.8	928.2	926.5	924.8	923.1
175°	931.5	932.9	934.2	934.1	932.2	930.3	928.4	926.6
177.5°	933.1	934.1	935.0	934.8	933.3	931.8	930.3	928.8
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2

(END OF REPORT)