

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333001-940

Luminaire Tested: **SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P333001-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6800.0 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333001-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333001-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	86	80	75	70	71	66	63	62	59	56	54	52	50	46
3	84	75	68	62	79	71	64	59	63	57	53	55	51	48	48	45	43	39
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	60	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32	30
6	66	54	45	40	62	51	43	38	45	39	35	40	35	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	26	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P333001-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	2.6
10°-20°	487.1	7.2
20°-30°	703.4	10.3
30°-40°	797.3	11.7
40°-50°	770.0	11.3
50°-60°	640.3	9.4
60°-70°	442.1	6.5
70°-80°	224.1	3.3
80°-90°	60.2	0.9
90°-100°	59.5	0.9
100°-110°	176.1	2.6
110°-120°	298.9	4.4
120°-130°	394.2	5.8
130°-140°	442.7	6.5
140°-150°	435.0	6.4
150°-160°	365.9	5.4
160°-170°	243.4	3.6
170°-180°	85.2	1.3
0°-30°	1365.2	20.1
0°-40°	2162.6	31.8
0°-60°	3572.8	52.5
0°-90°	4299.2	63.2
90°-120°	534.5	7.9
90°-150°	1806.3	26.6
90°-180°	2501.0	36.8
0°-180°	6800.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	87
90°	2	10	15	19	21	6
95°	42	48	53	55	55	47
105°	162	163	166	168	170	172
115°	304	304	303	302	301	300
125°	443	443	442	441	439	394
135°	571	575	575	574	572	442
145°	694	696	697	696	694	434
155°	795	795	794	796	794	366
165°	865	863	862	865	863	244
175°	900	897	896	900	896	85
180°	901	901	901	901	901	



TEST NUMBER: P333001-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.7	25.0	23.3	21.6	19.9	19.0	19.0	19.0	19.0	19.0	18.9
90°	2.1	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2
92.5°	14.9	16.9	18.8	20.8	22.7	24.2	25.0	25.9	26.8	27.6	28.2
95°	41.8	43.2	44.6	46.0	47.4	48.7	49.8	50.8	51.9	53.0	53.4
97.5°	73.0	74.2	75.3	76.4	77.5	78.7	80.0	81.2	82.5	83.8	84.4
100°	97.6	98.2	98.8	99.4	100.0	101.1	102.5	103.9	105.2	106.6	107.0
102.5°	123.2	123.5	123.8	124.0	124.2	125.0	126.3	127.5	128.9	130.1	130.5
105°	162.5	162.6	162.7	162.9	163.1	163.5	164.1	164.7	165.3	165.9	166.4
107.5°	203.6	203.8	203.9	204.1	204.3	204.5	204.6	204.6	204.7	204.8	205.3
110°	231.5	231.8	232.0	232.4	232.6	232.7	232.6	232.5	232.3	232.1	231.8



TEST NUMBER: P333001-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.5	260.5	260.6	260.6	260.7	260.6	260.3	260.0	259.8	259.5	259.4
115°	304.0	304.0	304.0	304.0	304.0	303.8	303.4	303.2	302.8	302.6	302.4
117.5°	344.9	345.1	345.2	345.3	345.4	345.4	345.2	344.9	344.7	344.6	344.0
120°	372.3	372.9	373.5	374.2	374.8	374.8	374.3	373.9	373.4	373.0	372.2
122.5°	400.7	400.9	401.2	401.4	401.7	401.7	401.5	401.3	401.1	400.8	400.3
125°	442.6	442.6	442.6	442.6	442.6	442.6	442.5	442.3	442.1	442.0	441.7
127.5°	480.7	481.2	481.7	482.1	482.6	482.7	482.4	482.2	482.0	481.7	481.4
130°	507.5	508.0	508.5	508.9	509.3	509.6	509.6	509.6	509.6	509.6	509.3
132.5°	534.8	535.2	535.6	535.8	536.2	536.3	536.2	536.1	535.9	535.8	535.5
135°	571.0	571.9	572.8	573.7	574.7	575.2	575.2	575.2	575.2	575.2	574.8
137.5°	610.3	610.7	611.1	611.5	612.0	612.3	612.6	612.9	613.1	613.3	613.0
140°	636.5	636.8	637.1	637.4	637.8	637.8	637.8	637.8	637.8	637.8	637.8
142.5°	660.5	660.8	661.1	661.4	661.7	661.8	661.6	661.6	661.4	661.3	661.3
145°	693.7	694.3	694.9	695.5	696.2	696.5	696.7	696.8	697.0	697.1	697.0
147.5°	726.6	727.3	728.0	728.8	729.5	729.9	729.7	729.6	729.4	729.3	729.2
150°	746.6	747.3	747.9	748.5	749.1	749.4	749.4	749.4	749.4	749.4	749.4
152.5°	765.6	766.0	766.3	766.7	767.0	767.3	767.4	767.6	767.7	767.9	768.2
155°	794.7	794.7	794.7	794.7	794.7	794.6	794.5	794.3	794.2	794.1	794.6
157.5°	819.3	818.9	818.7	818.4	818.1	818.0	818.0	818.0	817.9	817.9	818.3
160°	833.7	833.6	833.5	833.3	833.1	832.9	832.9	832.7	832.5	832.4	832.9
162.5°	847.1	846.8	846.3	846.0	845.5	845.3	845.1	845.0	844.8	844.6	845.5
165°	865.1	864.7	864.2	863.7	863.3	862.9	862.6	862.3	861.9	861.7	862.6
167.5°	879.0	878.2	877.6	877.0	876.4	876.0	876.0	876.1	876.1	876.1	877.1
170°	886.7	886.0	885.2	884.4	883.7	883.3	883.5	883.7	883.8	884.0	884.8
172.5°	892.3	891.7	891.0	890.4	889.7	889.4	889.5	889.5	889.5	889.6	890.6
175°	900.0	899.2	898.4	897.7	896.9	896.4	896.3	896.1	896.0	895.8	896.9
177.5°	902.5	901.9	901.3	900.6	900.0	899.7	899.7	899.7	899.7	899.7	900.5
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P333001-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	18.9	18.8	18.7	18.9	19.2	19.5	19.8	20.2
90°	17.2	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	28.7	29.2	29.9	30.2	30.4	30.6	30.8	30.9
95°	53.9	54.4	54.8	55.1	55.1	55.1	55.1	55.1
97.5°	84.9	85.4	86.1	86.3	86.3	86.3	86.3	86.3
100°	107.3	107.6	107.9	108.1	108.1	108.1	108.1	108.1
102.5°	131.0	131.3	131.8	132.1	132.2	132.3	132.5	132.6
105°	166.8	167.3	167.7	168.3	168.7	169.2	169.6	170.1
107.5°	205.7	206.1	206.5	206.8	206.7	206.7	206.7	206.6
110°	231.5	231.2	230.9	231.0	231.5	231.9	232.4	232.8



TEST NUMBER: P333001-940

CATALOG NUMBER: SA4XXRDIP-C1195D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	259.3	259.3	259.2	259.2	259.3	259.4	259.5	259.6
115°	302.2	302.1	301.9	301.8	301.7	301.5	301.3	301.1
117.5°	343.5	343.0	342.4	342.0	341.7	341.3	341.1	340.7
120°	371.4	370.6	369.9	369.6	370.0	370.2	370.6	370.9
122.5°	399.8	399.3	398.8	398.2	397.6	397.1	396.5	396.0
125°	441.4	441.0	440.8	440.4	440.1	439.8	439.5	439.2
127.5°	481.1	480.8	480.5	480.2	479.9	479.7	479.5	479.2
130°	509.0	508.6	508.4	507.9	507.3	506.7	506.0	505.4
132.5°	535.2	534.8	534.6	534.3	534.0	533.8	533.5	533.3
135°	574.5	574.2	573.9	573.5	573.0	572.6	572.1	571.7
137.5°	612.5	612.2	611.7	611.5	611.6	611.7	611.8	612.0
140°	637.6	637.4	637.2	637.1	636.9	636.8	636.6	636.5
142.5°	661.2	661.2	661.2	661.1	661.1	661.1	661.0	661.0
145°	696.8	696.7	696.5	696.2	695.7	695.3	694.8	694.4
147.5°	729.1	729.0	728.8	728.7	728.5	728.3	728.3	728.1
150°	749.4	749.4	749.4	749.3	749.2	749.0	748.9	748.7
152.5°	768.6	768.9	769.3	769.3	768.9	768.5	768.1	767.7
155°	795.2	795.9	796.5	796.5	795.9	795.2	794.6	794.1
157.5°	818.8	819.3	819.7	819.7	819.2	818.7	818.1	817.6
160°	833.3	833.7	834.2	834.1	833.3	832.5	831.8	831.0
162.5°	846.3	847.1	848.0	848.0	847.2	846.5	845.7	844.9
165°	863.5	864.4	865.4	865.5	864.9	864.2	863.6	863.1
167.5°	878.0	879.0	879.9	879.9	878.9	877.9	877.0	876.0
170°	885.8	886.7	887.7	887.6	886.5	885.5	884.3	883.2
172.5°	891.6	892.7	893.8	893.8	892.7	891.5	890.5	889.4
175°	898.0	899.0	900.2	900.2	899.0	898.0	896.9	895.8
177.5°	901.4	902.3	903.2	903.1	902.1	901.2	900.2	899.1
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3

(END OF REPORT)