

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332706

Luminaire Tested: **SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332706
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10127.7 lumens
Efficiency: N/A
Efficacy: 141.3 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332706
CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53		
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45		
2	90	83	77	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38		
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32		
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31	28		
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24		
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22		
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19		
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17		
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16		
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15560	15560	15560	15560
5°	18323	15600	13768	15600
10°	21939	15531	12396	15531
15°	25957	15374	11384	15374
20°	28905	15214	10481	15214
25°	29372	14978	9857	14978
30°	24993	14752	9660	14752
35°	19215	14384	9662	14384
40°	14977	13951	9844	13951
45°	12488	13300	10009	13300
50°	10991	12504	10349	12504
55°	10069	11553	10766	11553
60°	9436	10700	11267	10700
65°	8785	9746	11683	9746
70°	8028	8802	11948	8802
75°	7171	7745	11803	7745
80°	6011	6346	11432	6346
85°	4437	4585	10948	4585



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.8	1.9
10°-20°	578.8	5.7
20°-30°	917.8	9.1
30°-40°	1021.3	10.1
40°-50°	929.7	9.2
50°-60°	759.7	7.5
60°-70°	542.4	5.4
70°-80°	298.7	2.9
80°-90°	86.0	0.8
90°-100°	53.1	0.5
100°-110°	338.8	3.3
110°-120°	648.1	6.4
120°-130°	822.7	8.1
130°-140°	880.2	8.7
140°-150°	823.1	8.1
150°-160°	663.8	6.6
160°-170°	428.1	4.2
170°-180°	147.6	1.5
0°-30°	1684.3	16.6
0°-40°	2705.6	26.7
0°-60°	4395.1	43.4
0°-90°	5322.1	52.6
90°-120°	1040.0	10.3
90°-150°	3566.1	35.2
90°-180°	4806.0	47.5
0°-180°	10127.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1927	1927	1927	1927	1927	
5°	2261	1925	1699	1925	2261	230
15°	3106	1840	1362	1840	3106	878
25°	3297	1682	1107	1682	3297	1454
35°	1950	1460	980	1460	1950	1238
45°	1094	1165	877	1165	1094	862
55°	715	821	765	821	715	646
65°	460	510	612	510	460	455
75°	230	248	378	248	230	244
85°	48	50	118	50	48	59
90°	35	4	35	4	35	17
95°	34	64	34	64	34	27
105°	331	350	331	350	331	289
115°	658	653	658	653	658	651
125°	925	918	925	918	925	824
135°	1147	1139	1147	1139	1147	883
145°	1320	1313	1320	1313	1320	825
155°	1438	1440	1438	1440	1438	663
165°	1512	1519	1512	1519	1512	427
175°	1544	1554	1544	1554	1544	147
180°	1554	1554	1554	1554	1554	



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2051.3	2050.6	2044.3	2043.0	2038.5	2032.8	2031.5	2021.3	2000.8	1991.2	1988.7
5°	2261.1	2277.1	2256.3	2252.3	2249.9	2223.6	2210.0	2194.0	2157.3	2135.8	2119.0
7.5°	2511.5	2513.4	2504.3	2497.0	2476.7	2453.7	2419.2	2382.5	2338.7	2293.2	2258.9
10°	2676.3	2682.7	2672.3	2670.7	2630.0	2604.4	2553.3	2510.2	2460.7	2405.6	2355.3
12.5°	2850.0	2841.1	2835.8	2801.6	2794.1	2747.5	2688.1	2643.7	2567.4	2504.0	2437.1
15°	3105.8	3088.3	3077.1	3030.0	3006.8	2942.1	2879.1	2830.4	2730.6	2635.6	2563.7
17.5°	3255.9	3273.5	3247.6	3228.3	3168.4	3123.1	3058.6	2956.4	2878.3	2760.3	2669.6
20°	3364.5	3366.1	3351.7	3331.8	3284.7	3227.2	3156.9	3045.1	2951.7	2834.4	2709.8
22.5°	3393.9	3394.2	3388.1	3369.5	3333.8	3287.2	3216.3	3123.1	3009.9	2882.3	2757.7
25°	3297.4	3294.2	3301.4	3322.2	3308.6	3294.2	3253.5	3184.1	3078.7	2943.7	2809.6
27.5°	2939.1	2961.1	3001.7	3052.8	3102.0	3139.5	3150.1	3135.8	3070.5	2959.6	2819.0
30°	2681.1	2708.2	2738.6	2789.6	2888.7	2945.3	3007.6	3054.7	3028.4	2939.8	2808.8
32.5°	2397.5	2404.2	2449.2	2507.3	2598.0	2707.1	2805.8	2901.4	2933.2	2886.7	2777.5
35°	1949.7	1960.9	2009.6	2067.1	2178.1	2311.4	2459.9	2592.4	2701.8	2745.7	2689.8
37.5°	1591.1	1623.2	1657.5	1719.3	1817.0	1937.1	2091.4	2262.9	2425.9	2535.1	2553.6
40°	1421.2	1441.1	1465.9	1513.0	1596.0	1714.2	1846.7	2043.1	2216.4	2372.9	2424.0
42.5°	1287.0	1298.7	1313.9	1356.5	1419.7	1537.3	1658.3	1831.1	2005.0	2192.1	2277.7
45°	1093.8	1105.8	1131.3	1156.1	1204.0	1285.4	1398.0	1540.1	1715.0	1895.4	2053.5
47.5°	954.3	961.9	977.1	1003.6	1044.3	1098.0	1189.6	1308.3	1470.4	1645.5	1814.0
50°	875.1	881.4	893.4	917.4	948.5	996.4	1071.5	1182.4	1309.4	1485.8	1651.1
52.5°	812.5	815.0	823.8	840.1	864.8	905.1	966.7	1058.5	1176.5	1333.8	1498.5
55°	715.4	718.6	726.6	738.5	760.1	785.6	832.7	901.4	1004.4	1140.9	1283.8
57.5°	635.5	637.8	644.5	649.1	666.8	687.6	723.8	772.9	850.9	966.7	1094.3
60°	584.4	582.8	590.8	594.8	606.8	624.4	652.3	699.4	767.3	860.7	978.1
62.5°	534.6	532.4	539.1	544.4	551.2	566.2	589.1	626.0	681.0	765.5	866.9
65°	459.9	456.7	460.7	467.1	473.5	481.4	498.2	530.9	574.9	635.5	713.0
67.5°	384.8	388.2	388.8	392.0	395.7	406.6	418.0	441.2	472.2	520.7	586.4
70°	340.1	340.9	344.1	344.1	346.5	356.1	365.7	379.2	409.6	454.3	507.8
72.5°	295.4	298.8	297.5	300.0	301.8	308.2	315.2	328.1	354.0	387.2	432.4
75°	229.9	232.3	232.3	233.1	235.5	237.9	243.5	253.1	271.5	296.2	327.3
77.5°	167.7	168.0	169.1	172.0	172.0	175.8	180.0	187.6	196.7	213.7	232.7
80°	129.3	130.9	130.1	131.7	131.7	134.9	136.5	146.1	150.1	161.3	176.4
82.5°	94.9	96.4	96.3	98.5	99.8	100.4	102.7	106.5	110.5	120.4	126.6
85°	47.9	49.5	47.9	49.5	51.9	52.7	55.1	55.9	59.1	61.5	67.1
87.5°	21.0	22.8	22.7	23.3	24.4	24.9	25.2	24.3	26.5	26.8	29.0
90°	34.9	34.3	33.8	33.3	32.8	31.8	30.2	28.7	27.1	25.6	23.5
92.5°	32.1	32.0	31.9	31.8	31.7	30.8	29.3	27.7	26.2	24.6	22.6
95°	33.7	33.4	33.2	32.9	32.7	31.8	30.2	28.7	27.1	25.6	25.3
97.5°	32.5	32.3	32.0	31.8	31.5	31.3	31.1	31.0	30.8	30.7	59.5
100°	32.5	32.3	32.0	31.8	31.5	33.6	38.0	42.3	46.7	51.1	86.8
102.5°	33.5	33.4	33.4	33.3	33.3	56.9	104.3	151.6	199.0	246.3	251.0
105°	331.2	340.5	349.7	359.0	368.3	371.8	369.5	367.2	364.9	362.5	361.2
107.5°	461.5	460.5	459.6	458.6	457.6	456.5	455.4	454.3	453.1	452.0	450.2
110°	518.2	517.5	516.7	515.9	515.1	514.5	514.0	513.5	512.9	512.4	510.9



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	574.9	574.0	573.0	572.0	571.0	570.6	570.7	570.8	570.9	571.0	570.3
115°	657.7	657.7	657.7	657.7	657.7	657.4	656.9	656.4	655.9	655.3	655.6
117.5°	741.8	741.9	742.0	742.1	742.2	742.3	742.4	742.5	742.6	742.7	742.2
120°	794.8	795.3	795.8	796.3	796.8	796.8	796.3	795.8	795.3	794.8	795.0
122.5°	846.8	847.3	847.9	848.4	848.9	849.0	848.7	848.4	848.1	847.8	847.4
125°	924.9	924.7	924.4	924.1	923.9	923.4	922.6	921.8	921.0	920.3	920.8
127.5°	993.5	993.7	993.9	994.1	994.3	994.5	994.6	994.8	994.9	995.1	993.9
130°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.8	1039.6	1039.3	1039.0	1038.8	1038.0
132.5°	1082.7	1082.9	1083.1	1083.3	1083.5	1083.5	1083.3	1083.0	1082.7	1082.5	1081.5
135°	1146.8	1146.3	1145.8	1145.3	1144.8	1144.3	1143.7	1143.2	1142.7	1142.2	1141.2
137.5°	1201.7	1201.8	1202.0	1202.2	1202.3	1202.1	1201.5	1201.0	1200.4	1199.8	1198.7
140°	1239.8	1239.5	1239.3	1239.0	1238.8	1238.3	1237.5	1236.7	1235.9	1235.2	1234.6
142.5°	1271.4	1271.4	1271.3	1271.3	1271.2	1270.9	1270.3	1269.8	1269.2	1268.6	1268.3
145°	1320.0	1319.5	1318.9	1318.4	1317.9	1317.5	1317.3	1317.0	1316.8	1316.5	1316.5
147.5°	1360.2	1359.9	1359.7	1359.4	1359.1	1358.9	1358.7	1358.5	1358.3	1358.1	1358.3
150°	1386.2	1386.0	1385.7	1385.4	1385.2	1385.0	1385.0	1385.0	1385.0	1385.0	1385.3
152.5°	1408.5	1408.7	1408.8	1409.0	1409.1	1409.0	1408.6	1408.2	1407.8	1407.4	1407.8
155°	1438.5	1439.3	1440.0	1440.8	1441.6	1441.5	1440.4	1439.4	1438.4	1437.3	1438.1
157.5°	1463.6	1464.9	1466.3	1467.6	1469.0	1469.0	1467.6	1466.3	1464.9	1463.6	1464.5
160°	1480.3	1481.9	1483.4	1485.0	1486.5	1486.5	1485.0	1483.4	1481.9	1480.3	1480.6
162.5°	1493.3	1495.1	1496.9	1498.6	1500.4	1500.5	1498.9	1497.4	1495.8	1494.3	1494.5
165°	1511.7	1514.0	1516.3	1518.7	1521.0	1521.1	1519.1	1517.0	1514.9	1512.9	1512.9
167.5°	1525.4	1528.0	1530.6	1533.2	1535.7	1535.9	1533.6	1531.4	1529.1	1526.8	1527.0
170°	1533.8	1536.4	1538.9	1541.5	1544.1	1544.4	1542.3	1540.2	1538.2	1536.1	1535.8
172.5°	1538.4	1541.2	1544.0	1546.8	1549.6	1549.9	1547.9	1545.8	1543.7	1541.7	1541.4
175°	1544.2	1547.3	1550.4	1553.5	1556.6	1557.0	1554.7	1552.4	1550.0	1547.7	1547.5
177.5°	1548.0	1550.4	1552.9	1555.4	1557.9	1558.3	1556.6	1555.0	1553.3	1551.7	1551.3
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1989.3	1980.4	1974.0	1968.9	1954.8	1946.5	1940.1	1931.2	1921.0	1910.1	1896.7
5°	2102.2	2075.1	2055.1	2024.8	1996.0	1972.1	1947.3	1925.0	1897.8	1868.3	1846.7
7.5°	2220.9	2180.5	2128.7	2083.9	2033.4	1989.5	1950.2	1910.0	1868.1	1827.6	1790.4
10°	2296.2	2244.3	2186.8	2119.0	2055.1	1998.4	1945.7	1894.6	1845.1	1795.6	1753.3
12.5°	2377.4	2312.7	2227.7	2148.4	2076.8	2001.0	1937.4	1874.8	1815.1	1763.1	1713.7
15°	2486.3	2392.8	2294.6	2188.4	2094.2	2005.6	1918.6	1839.5	1772.5	1703.8	1655.9
17.5°	2553.2	2437.6	2325.3	2214.3	2100.3	1988.5	1894.6	1803.5	1719.5	1651.3	1590.9
20°	2597.2	2482.3	2342.5	2231.6	2095.8	1980.9	1872.3	1770.9	1683.1	1610.4	1548.1
22.5°	2635.6	2502.7	2363.0	2216.9	2081.8	1959.8	1841.0	1738.9	1649.2	1572.7	1513.0
25°	2656.3	2503.8	2352.1	2206.8	2053.5	1909.0	1801.2	1681.5	1585.6	1505.0	1441.1
27.5°	2658.6	2495.5	2323.9	2162.4	2004.2	1869.6	1733.5	1626.5	1527.0	1441.8	1380.5
30°	2651.5	2481.5	2297.0	2122.2	1963.3	1817.2	1699.0	1582.5	1481.1	1396.4	1332.5
32.5°	2629.2	2452.1	2262.5	2077.5	1912.8	1769.9	1647.9	1537.1	1438.3	1354.9	1287.8
35°	2564.5	2389.6	2187.6	1995.2	1826.8	1682.3	1572.1	1459.5	1360.5	1281.5	1216.8
37.5°	2463.4	2305.3	2100.0	1900.9	1735.4	1590.3	1481.1	1379.3	1290.1	1209.8	1143.5
40°	2375.3	2236.4	2030.4	1836.3	1657.5	1519.4	1417.2	1323.8	1235.1	1159.3	1096.2
42.5°	2273.7	2152.7	1962.7	1757.1	1584.7	1445.9	1346.3	1262.4	1178.9	1108.8	1045.8
45°	2092.6	2012.8	1834.0	1643.9	1464.3	1333.3	1238.3	1164.9	1094.6	1026.0	973.3
47.5°	1884.4	1844.8	1694.2	1513.8	1343.2	1214.2	1131.8	1064.0	1002.3	944.2	897.7
50°	1744.5	1725.4	1595.2	1421.2	1258.3	1136.9	1053.9	995.6	942.9	891.8	847.9
52.5°	1606.6	1605.9	1488.6	1329.2	1178.5	1061.6	979.2	924.7	879.1	837.5	798.1
55°	1395.6	1418.0	1326.2	1184.0	1049.1	943.7	869.5	820.8	788.8	754.5	725.0
57.5°	1201.9	1239.0	1163.3	1038.1	925.5	828.4	763.8	727.2	693.2	672.4	650.9
60°	1075.5	1110.6	1051.5	946.1	839.9	756.9	695.4	662.7	633.1	618.8	603.6
62.5°	963.0	994.3	950.6	852.9	760.7	680.9	629.0	597.5	577.6	561.9	551.9
65°	802.4	828.8	791.2	720.2	641.1	577.3	534.9	510.2	491.0	484.6	473.5
67.5°	648.6	672.6	652.3	591.9	528.5	480.2	447.1	423.3	412.0	406.4	398.4
70°	557.3	581.2	559.7	507.0	458.3	417.6	386.4	372.9	360.9	358.5	347.3
72.5°	480.0	496.3	474.7	433.5	391.9	357.5	333.4	319.2	313.0	308.7	302.6
75°	360.1	374.5	360.1	328.1	298.6	274.7	253.9	248.3	241.1	238.7	234.7
77.5°	254.9	267.3	256.3	236.3	214.3	195.8	184.6	177.4	175.8	171.7	173.6
80°	194.8	202.8	192.4	178.8	161.3	148.5	140.5	136.5	131.7	130.1	133.3
82.5°	139.9	143.4	138.1	129.0	115.9	107.6	102.2	97.6	96.6	96.9	96.9
85°	72.7	71.9	71.1	63.1	59.1	53.5	50.3	49.5	48.7	50.3	51.9
87.5°	28.6	28.8	27.7	24.7	22.2	19.7	18.5	17.3	18.5	19.7	20.9
90°	21.4	19.4	17.3	14.8	12.0	9.2	6.3	3.5	6.3	9.2	12.0
92.5°	20.5	18.4	16.4	15.3	15.1	15.0	14.8	14.6	14.8	15.0	15.1
95°	25.0	24.8	24.5	28.8	37.6	46.3	55.1	63.9	55.1	46.3	37.6
97.5°	88.3	117.1	145.9	157.6	152.1	146.7	141.2	135.7	141.2	146.7	152.1
100°	122.4	158.0	193.7	209.2	204.5	199.9	195.2	190.6	195.2	199.9	204.5
102.5°	255.6	260.3	264.9	265.5	262.1	258.7	255.3	251.9	255.3	258.7	262.1
105°	359.9	358.7	357.4	355.9	354.4	352.8	351.3	349.7	351.3	352.8	354.4
107.5°	448.5	446.7	445.0	443.7	442.9	442.2	441.4	440.6	441.4	442.2	442.9
110°	509.3	507.8	506.2	505.1	504.3	503.5	502.7	502.0	502.7	503.5	504.3



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	569.5	568.8	568.1	567.0	565.6	564.2	562.9	561.5	562.9	564.2	565.6
115°	655.9	656.1	656.4	656.1	655.3	654.6	653.8	653.0	653.8	654.6	655.3
117.5°	741.6	741.0	740.4	739.6	738.6	737.6	736.5	735.5	736.5	737.6	738.6
120°	795.3	795.6	795.8	795.4	794.4	793.4	792.3	791.3	792.3	793.4	794.4
122.5°	847.0	846.7	846.3	845.8	845.2	844.6	844.0	843.3	844.0	844.6	845.2
125°	921.3	921.8	922.3	922.1	921.0	920.0	919.0	917.9	919.0	920.0	921.0
127.5°	992.7	991.5	990.3	989.6	989.4	989.1	988.8	988.6	988.8	989.1	989.4
130°	1037.2	1036.5	1035.7	1035.2	1034.9	1034.7	1034.4	1034.1	1034.4	1034.7	1034.9
132.5°	1080.5	1079.5	1078.6	1077.8	1077.4	1076.9	1076.4	1076.0	1076.4	1076.9	1077.4
135°	1140.1	1139.1	1138.1	1137.7	1137.9	1138.2	1138.5	1138.7	1138.5	1138.2	1137.9
137.5°	1197.6	1196.4	1195.3	1194.7	1194.6	1194.5	1194.4	1194.3	1194.4	1194.5	1194.6
140°	1234.1	1233.6	1233.1	1232.6	1232.1	1231.5	1231.0	1230.5	1231.0	1231.5	1232.1
142.5°	1268.0	1267.7	1267.4	1266.8	1265.8	1264.9	1264.0	1263.0	1264.0	1264.9	1265.8
145°	1316.5	1316.5	1316.5	1316.1	1315.3	1314.6	1313.8	1313.0	1313.8	1314.6	1315.3
147.5°	1358.6	1358.9	1359.1	1358.5	1357.1	1355.6	1354.2	1352.7	1354.2	1355.6	1357.1
150°	1385.6	1385.8	1386.1	1385.7	1384.7	1383.6	1382.6	1381.6	1382.6	1383.6	1384.7
152.5°	1408.3	1408.8	1409.2	1409.0	1408.2	1407.4	1406.6	1405.7	1406.6	1407.4	1408.2
155°	1438.9	1439.7	1440.4	1440.7	1440.4	1440.2	1439.9	1439.7	1439.9	1440.2	1440.4
157.5°	1465.4	1466.2	1467.1	1467.6	1467.8	1467.9	1468.1	1468.2	1468.1	1467.9	1467.8
160°	1480.8	1481.1	1481.4	1481.9	1482.7	1483.4	1484.2	1485.0	1484.2	1483.4	1482.7
162.5°	1494.8	1495.0	1495.3	1495.9	1496.9	1497.9	1498.9	1499.8	1498.9	1497.9	1496.9
165°	1512.9	1512.9	1512.9	1513.5	1514.8	1516.1	1517.4	1518.7	1517.4	1516.1	1514.8
167.5°	1527.1	1527.3	1527.4	1528.2	1529.5	1530.9	1532.2	1533.5	1532.2	1530.9	1529.5
170°	1535.6	1535.3	1535.1	1535.7	1537.3	1538.8	1540.4	1541.9	1540.4	1538.8	1537.3
172.5°	1541.2	1540.9	1540.6	1541.3	1542.8	1544.4	1545.9	1547.5	1545.9	1544.4	1542.8
175°	1547.2	1546.9	1546.7	1547.3	1548.9	1550.4	1552.0	1553.5	1552.0	1550.4	1548.9
177.5°	1550.8	1550.4	1550.0	1550.5	1552.0	1553.4	1554.9	1556.3	1554.9	1553.4	1552.0
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1890.3	1884.6	1876.3	1864.8	1855.2	1845.0	1842.4	1838.6	1846.2	1839.9	1837.9
5°	1828.4	1811.6	1790.0	1765.3	1750.9	1730.2	1726.2	1718.2	1710.2	1709.4	1701.4
7.5°	1762.7	1738.1	1709.9	1684.6	1661.3	1638.7	1623.8	1620.6	1608.8	1601.9	1593.9
10°	1720.6	1690.2	1657.5	1633.6	1606.4	1582.5	1565.7	1556.1	1548.1	1539.3	1531.4
12.5°	1670.8	1638.5	1611.5	1585.6	1553.4	1535.2	1507.6	1491.0	1489.4	1489.5	1468.8
15°	1612.8	1580.9	1539.3	1502.6	1485.0	1449.9	1434.7	1415.6	1403.6	1391.6	1382.1
17.5°	1546.5	1506.8	1474.3	1432.2	1398.7	1370.7	1350.8	1339.3	1321.2	1304.3	1292.0
20°	1505.0	1462.7	1428.4	1383.6	1346.9	1312.6	1295.8	1279.9	1266.3	1251.9	1238.3
22.5°	1462.8	1418.6	1376.6	1333.2	1299.0	1262.8	1246.6	1224.9	1212.0	1204.0	1190.4
25°	1396.4	1348.5	1300.6	1259.1	1224.0	1192.0	1170.5	1153.7	1139.3	1132.9	1124.2
27.5°	1324.2	1276.7	1230.4	1183.2	1143.3	1120.2	1102.9	1090.3	1082.0	1073.5	1069.6
30°	1278.3	1228.8	1179.3	1135.3	1098.6	1075.5	1059.5	1050.7	1044.3	1040.3	1036.3
32.5°	1231.6	1182.8	1130.7	1090.6	1057.7	1037.1	1025.0	1016.2	1013.0	1011.6	1010.2
35°	1156.9	1107.4	1059.5	1023.6	992.4	984.4	974.1	969.3	967.7	973.3	975.7
37.5°	1084.6	1038.6	994.5	959.7	939.3	927.6	924.1	924.2	930.0	934.9	940.7
40°	1037.9	993.2	951.7	921.4	902.2	895.0	893.4	897.4	903.8	909.4	915.8
42.5°	992.6	948.5	910.8	882.4	869.0	862.4	863.4	867.4	876.3	883.2	892.8
45°	922.2	885.4	848.7	825.6	814.4	816.0	816.0	823.2	831.9	842.3	852.7
47.5°	855.9	818.9	788.7	769.2	763.4	762.0	766.5	775.9	788.5	801.3	815.8
50°	811.2	776.1	749.7	732.1	725.8	728.2	734.5	743.3	758.5	774.5	789.6
52.5°	765.8	733.9	709.5	693.2	688.7	693.0	699.4	713.3	726.6	743.8	762.2
55°	695.4	668.3	649.1	637.1	635.5	637.9	645.1	660.3	679.4	701.0	718.6
57.5°	625.3	602.6	585.1	576.8	577.6	579.8	591.6	609.7	630.1	653.1	675.8
60°	578.0	557.3	542.9	536.5	537.3	542.1	556.5	573.3	598.8	621.2	645.1
62.5°	533.3	515.1	501.4	495.7	494.5	505.1	518.8	536.2	561.8	586.7	612.5
65°	461.5	447.1	435.9	432.7	435.1	443.1	460.7	483.8	505.4	531.7	558.9
67.5°	391.2	379.4	371.7	373.2	376.1	387.9	402.6	422.5	447.0	474.3	501.1
70°	346.5	335.3	328.9	329.7	334.5	348.9	361.7	381.6	408.0	435.9	458.3
72.5°	300.5	293.2	287.4	290.8	295.6	305.5	321.4	341.4	364.6	390.6	414.2
75°	230.7	230.7	227.5	229.9	237.1	246.7	258.7	279.4	302.6	323.4	342.5
77.5°	171.2	169.4	171.5	174.4	178.5	189.9	203.6	218.4	235.9	256.6	272.4
80°	130.9	131.7	135.7	140.5	142.1	150.9	165.3	178.8	192.4	210.0	225.2
82.5°	98.4	99.2	101.2	107.3	108.9	118.3	127.6	141.2	153.5	165.3	177.9
85°	53.5	53.5	57.5	59.9	63.9	70.3	75.8	83.8	95.0	103.0	115.0
87.5°	23.4	23.9	26.9	28.6	30.9	34.5	36.1	43.4	46.3	49.8	55.7
90°	14.8	17.3	19.4	21.4	23.5	25.6	27.1	28.7	30.2	31.8	32.8
92.5°	15.3	16.4	18.4	20.5	22.6	24.6	26.2	27.7	29.3	30.8	31.7
95°	28.8	24.5	24.8	25.0	25.3	25.6	27.1	28.7	30.2	31.8	32.7
97.5°	157.6	145.9	117.1	88.3	59.5	30.7	30.8	31.0	31.1	31.3	31.5
100°	209.2	193.7	158.0	122.4	86.8	51.1	46.7	42.3	38.0	33.6	31.5
102.5°	265.5	264.9	260.3	255.6	251.0	246.3	199.0	151.6	104.3	56.9	33.3
105°	355.9	357.4	358.7	359.9	361.2	362.5	364.9	367.2	369.5	371.8	368.3
107.5°	443.7	445.0	446.7	448.5	450.2	452.0	453.1	454.3	455.4	456.5	457.6
110°	505.1	506.2	507.8	509.3	510.9	512.4	512.9	513.5	514.0	514.5	515.1



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	567.0	568.1	568.8	569.5	570.3	571.0	570.9	570.8	570.7	570.6	571.0
115°	656.1	656.4	656.1	655.9	655.6	655.3	655.9	656.4	656.9	657.4	657.7
117.5°	739.6	740.4	741.0	741.6	742.2	742.7	742.6	742.5	742.4	742.3	742.2
120°	795.4	795.8	795.6	795.3	795.0	794.8	795.3	795.8	796.3	796.8	796.8
122.5°	845.8	846.3	846.7	847.0	847.4	847.8	848.1	848.4	848.7	849.0	848.9
125°	922.1	922.3	921.8	921.3	920.8	920.3	921.0	921.8	922.6	923.4	923.9
127.5°	989.6	990.3	991.5	992.7	993.9	995.1	994.9	994.8	994.6	994.5	994.3
130°	1035.2	1035.7	1036.5	1037.2	1038.0	1038.8	1039.0	1039.3	1039.6	1039.8	1039.9
132.5°	1077.8	1078.6	1079.5	1080.5	1081.5	1082.5	1082.7	1083.0	1083.3	1083.5	1083.5
135°	1137.7	1138.1	1139.1	1140.1	1141.2	1142.2	1142.7	1143.2	1143.7	1144.3	1144.8
137.5°	1194.7	1195.3	1196.4	1197.6	1198.7	1199.8	1200.4	1201.0	1201.5	1202.1	1202.3
140°	1232.6	1233.1	1233.6	1234.1	1234.6	1235.2	1235.9	1236.7	1237.5	1238.3	1238.8
142.5°	1266.8	1267.4	1267.7	1268.0	1268.3	1268.6	1269.2	1269.8	1270.3	1270.9	1271.2
145°	1316.1	1316.5	1316.5	1316.5	1316.5	1316.5	1316.8	1317.0	1317.3	1317.5	1317.9
147.5°	1358.5	1359.1	1358.9	1358.6	1358.3	1358.1	1358.3	1358.5	1358.7	1358.9	1359.1
150°	1385.7	1386.1	1385.8	1385.6	1385.3	1385.0	1385.0	1385.0	1385.0	1385.0	1385.2
152.5°	1409.0	1409.2	1408.8	1408.3	1407.8	1407.4	1407.8	1408.2	1408.6	1409.0	1409.1
155°	1440.7	1440.4	1439.7	1438.9	1438.1	1437.3	1438.4	1439.4	1440.4	1441.5	1441.6
157.5°	1467.6	1467.1	1466.2	1465.4	1464.5	1463.6	1464.9	1466.3	1467.6	1469.0	1469.0
160°	1481.9	1481.4	1481.1	1480.8	1480.6	1480.3	1481.9	1483.4	1485.0	1486.5	1486.5
162.5°	1495.9	1495.3	1495.0	1494.8	1494.5	1494.3	1495.8	1497.4	1498.9	1500.5	1500.4
165°	1513.5	1512.9	1512.9	1512.9	1512.9	1512.9	1514.9	1517.0	1519.1	1521.1	1521.0
167.5°	1528.2	1527.4	1527.3	1527.1	1527.0	1526.8	1529.1	1531.4	1533.6	1535.9	1535.7
170°	1535.7	1535.1	1535.3	1535.6	1535.8	1536.1	1538.2	1540.2	1542.3	1544.4	1544.1
172.5°	1541.3	1540.6	1540.9	1541.2	1541.4	1541.7	1543.7	1545.8	1547.9	1549.9	1549.6
175°	1547.3	1546.7	1546.9	1547.2	1547.5	1547.7	1550.0	1552.4	1554.7	1557.0	1556.6
177.5°	1550.5	1550.0	1550.4	1550.8	1551.3	1551.7	1553.3	1555.0	1556.6	1558.3	1557.9
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1836.7	1835.4	1830.9	1830.3	1830.9	1835.4	1836.7	1837.9	1839.9	1846.2	1838.6
5°	1696.6	1692.6	1690.2	1699.0	1690.2	1692.6	1696.6	1701.4	1709.4	1710.2	1718.2
7.5°	1591.1	1587.9	1580.9	1578.6	1580.9	1587.9	1591.1	1593.9	1601.9	1608.8	1620.6
10°	1523.4	1520.2	1513.8	1512.2	1513.8	1520.2	1523.4	1531.4	1539.3	1548.1	1556.1
12.5°	1458.2	1451.8	1450.6	1452.2	1450.6	1451.8	1458.2	1468.8	1489.5	1489.4	1491.0
15°	1371.7	1368.5	1359.7	1362.1	1359.7	1368.5	1371.7	1382.1	1391.6	1403.6	1415.6
17.5°	1286.4	1282.6	1271.9	1281.3	1271.9	1282.6	1286.4	1292.0	1304.3	1321.2	1339.3
20°	1232.7	1226.4	1220.8	1220.0	1220.8	1226.4	1232.7	1238.3	1251.9	1266.3	1279.9
22.5°	1181.6	1175.9	1175.4	1170.2	1175.4	1175.9	1181.6	1190.4	1204.0	1212.0	1224.9
25°	1117.8	1112.2	1110.6	1106.6	1110.6	1112.2	1117.8	1124.2	1132.9	1139.3	1153.7
27.5°	1068.8	1066.0	1063.2	1064.4	1063.2	1066.0	1068.8	1069.6	1073.5	1082.0	1090.3
30°	1038.7	1037.9	1036.3	1036.3	1036.3	1037.9	1038.7	1036.3	1040.3	1044.3	1050.7
32.5°	1013.8	1013.7	1014.6	1014.6	1014.6	1013.7	1013.8	1010.2	1011.6	1013.0	1016.2
35°	978.9	981.2	982.8	980.4	982.8	981.2	978.9	975.7	973.3	967.7	969.3
37.5°	947.2	949.6	951.9	954.6	951.9	949.6	947.2	940.7	934.9	930.0	924.2
40°	923.0	928.6	930.1	934.1	930.1	928.6	923.0	915.8	909.4	903.8	897.4
42.5°	900.0	906.2	910.3	911.1	910.3	906.2	900.0	892.8	883.2	876.3	867.4
45°	864.7	871.1	876.7	876.7	876.7	871.1	864.7	852.7	842.3	831.9	823.2
47.5°	828.1	837.4	843.0	844.4	843.0	837.4	828.1	815.8	801.3	788.5	775.9
50°	803.2	814.4	820.0	824.0	820.0	814.4	803.2	789.6	774.5	758.5	743.3
52.5°	778.9	790.1	797.6	799.7	797.6	790.1	778.9	762.2	743.8	726.6	713.3
55°	736.9	752.9	761.7	764.9	761.7	752.9	736.9	718.6	701.0	679.4	660.3
57.5°	697.3	712.0	722.2	724.6	722.2	712.0	697.3	675.8	653.1	630.1	609.7
60°	666.7	682.6	695.4	697.8	695.4	682.6	666.7	645.1	621.2	598.8	573.3
62.5°	635.4	652.0	663.5	669.7	663.5	652.0	635.4	612.5	586.7	561.8	536.2
65°	581.2	598.0	609.2	611.6	609.2	598.0	581.2	558.9	531.7	505.4	483.8
67.5°	522.2	538.9	546.3	550.9	546.3	538.9	522.2	501.1	474.3	447.0	422.5
70°	480.6	494.2	502.2	506.2	502.2	494.2	480.6	458.3	435.9	408.0	381.6
72.5°	433.4	447.6	456.9	457.6	456.9	447.6	433.4	414.2	390.6	364.6	341.4
75°	360.9	373.7	378.4	378.4	378.4	373.7	360.9	342.5	323.4	302.6	279.4
77.5°	285.7	292.2	298.3	299.6	298.3	292.2	285.7	272.4	256.6	235.9	218.4
80°	237.1	241.1	245.9	245.9	245.9	241.1	237.1	225.2	210.0	192.4	178.8
82.5°	187.3	190.7	195.5	194.8	195.5	190.7	187.3	177.9	165.3	153.5	141.2
85°	113.4	120.6	119.8	118.2	119.8	120.6	113.4	115.0	103.0	95.0	83.8
87.5°	57.8	58.5	60.5	61.9	60.5	58.5	57.8	55.7	49.8	46.3	43.4
90°	33.3	33.8	34.3	34.9	34.3	33.8	33.3	32.8	31.8	30.2	28.7
92.5°	31.8	31.9	32.0	32.1	32.0	31.9	31.8	31.7	30.8	29.3	27.7
95°	32.9	33.2	33.4	33.7	33.4	33.2	32.9	32.7	31.8	30.2	28.7
97.5°	31.8	32.0	32.3	32.5	32.3	32.0	31.8	31.5	31.3	31.1	31.0
100°	31.8	32.0	32.3	32.5	32.3	32.0	31.8	31.5	33.6	38.0	42.3
102.5°	33.3	33.4	33.4	33.5	33.4	33.4	33.3	33.3	56.9	104.3	151.6
105°	359.0	349.7	340.5	331.2	340.5	349.7	359.0	368.3	371.8	369.5	367.2
107.5°	458.6	459.6	460.5	461.5	460.5	459.6	458.6	457.6	456.5	455.4	454.3
110°	515.9	516.7	517.5	518.2	517.5	516.7	515.9	515.1	514.5	514.0	513.5



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	572.0	573.0	574.0	574.9	574.0	573.0	572.0	571.0	570.6	570.7	570.8
115°	657.7	657.7	657.7	657.7	657.7	657.7	657.7	657.7	657.4	656.9	656.4
117.5°	742.1	742.0	741.9	741.8	741.9	742.0	742.1	742.2	742.3	742.4	742.5
120°	796.3	795.8	795.3	794.8	795.3	795.8	796.3	796.8	796.8	796.3	795.8
122.5°	848.4	847.9	847.3	846.8	847.3	847.9	848.4	848.9	849.0	848.7	848.4
125°	924.1	924.4	924.7	924.9	924.7	924.4	924.1	923.9	923.4	922.6	921.8
127.5°	994.1	993.9	993.7	993.5	993.7	993.9	994.1	994.3	994.5	994.6	994.8
130°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.8	1039.6	1039.3
132.5°	1083.3	1083.1	1082.9	1082.7	1082.9	1083.1	1083.3	1083.5	1083.5	1083.3	1083.0
135°	1145.3	1145.8	1146.3	1146.8	1146.3	1145.8	1145.3	1144.8	1144.3	1143.7	1143.2
137.5°	1202.2	1202.0	1201.8	1201.7	1201.8	1202.0	1202.2	1202.3	1202.1	1201.5	1201.0
140°	1239.0	1239.3	1239.5	1239.8	1239.5	1239.3	1239.0	1238.8	1238.3	1237.5	1236.7
142.5°	1271.3	1271.3	1271.4	1271.4	1271.4	1271.3	1271.3	1271.2	1270.9	1270.3	1269.8
145°	1318.4	1318.9	1319.5	1320.0	1319.5	1318.9	1318.4	1317.9	1317.5	1317.3	1317.0
147.5°	1359.4	1359.7	1359.9	1360.2	1359.9	1359.7	1359.4	1359.1	1358.9	1358.7	1358.5
150°	1385.4	1385.7	1386.0	1386.2	1386.0	1385.7	1385.4	1385.2	1385.0	1385.0	1385.0
152.5°	1409.0	1408.8	1408.7	1408.5	1408.7	1408.8	1409.0	1409.1	1409.0	1408.6	1408.2
155°	1440.8	1440.0	1439.3	1438.5	1439.3	1440.0	1440.8	1441.6	1441.5	1440.4	1439.4
157.5°	1467.6	1466.3	1464.9	1463.6	1464.9	1466.3	1467.6	1469.0	1469.0	1467.6	1466.3
160°	1485.0	1483.4	1481.9	1480.3	1481.9	1483.4	1485.0	1486.5	1486.5	1485.0	1483.4
162.5°	1498.6	1496.9	1495.1	1493.3	1495.1	1496.9	1498.6	1500.4	1500.5	1498.9	1497.4
165°	1518.7	1516.3	1514.0	1511.7	1514.0	1516.3	1518.7	1521.0	1521.1	1519.1	1517.0
167.5°	1533.2	1530.6	1528.0	1525.4	1528.0	1530.6	1533.2	1535.7	1535.9	1533.6	1531.4
170°	1541.5	1538.9	1536.4	1533.8	1536.4	1538.9	1541.5	1544.1	1544.4	1542.3	1540.2
172.5°	1546.8	1544.0	1541.2	1538.4	1541.2	1544.0	1546.8	1549.6	1549.9	1547.9	1545.8
175°	1553.5	1550.4	1547.3	1544.2	1547.3	1550.4	1553.5	1556.6	1557.0	1554.7	1552.4
177.5°	1555.4	1552.9	1550.4	1548.0	1550.4	1552.9	1555.4	1557.9	1558.3	1556.6	1555.0
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1842.4	1845.0	1855.2	1864.8	1876.3	1884.6	1890.3	1896.7	1910.1	1921.0	1931.2
5°	1726.2	1730.2	1750.9	1765.3	1790.0	1811.6	1828.4	1846.7	1868.3	1897.8	1925.0
7.5°	1623.8	1638.7	1661.3	1684.6	1709.9	1738.1	1762.7	1790.4	1827.6	1868.1	1910.0
10°	1565.7	1582.5	1606.4	1633.6	1657.5	1690.2	1720.6	1753.3	1795.6	1845.1	1894.6
12.5°	1507.6	1535.2	1553.4	1585.6	1611.5	1638.5	1670.8	1713.7	1763.1	1815.1	1874.8
15°	1434.7	1449.9	1485.0	1502.6	1539.3	1580.9	1612.8	1655.9	1703.8	1772.5	1839.5
17.5°	1350.8	1370.7	1398.7	1432.2	1474.3	1506.8	1546.5	1590.9	1651.3	1719.5	1803.5
20°	1295.8	1312.6	1346.9	1383.6	1428.4	1462.7	1505.0	1548.1	1610.4	1683.1	1770.9
22.5°	1246.6	1262.8	1299.0	1333.2	1376.6	1418.6	1462.8	1513.0	1572.7	1649.2	1738.9
25°	1170.5	1192.0	1224.0	1259.1	1300.6	1348.5	1396.4	1441.1	1505.0	1585.6	1681.5
27.5°	1102.9	1120.2	1143.3	1183.2	1230.4	1276.7	1324.2	1380.5	1441.8	1527.0	1626.5
30°	1059.5	1075.5	1098.6	1135.3	1179.3	1228.8	1278.3	1332.5	1396.4	1481.1	1582.5
32.5°	1025.0	1037.1	1057.7	1090.6	1130.7	1182.8	1231.6	1287.8	1354.9	1438.3	1537.1
35°	974.1	984.4	992.4	1023.6	1059.5	1107.4	1156.9	1216.8	1281.5	1360.5	1459.5
37.5°	924.1	927.6	939.3	959.7	994.5	1038.6	1084.6	1143.5	1209.8	1290.1	1379.3
40°	893.4	895.0	902.2	921.4	951.7	993.2	1037.9	1096.2	1159.3	1235.1	1323.8
42.5°	863.4	862.4	869.0	882.4	910.8	948.5	992.6	1045.8	1108.8	1178.9	1262.4
45°	816.0	816.0	814.4	825.6	848.7	885.4	922.2	973.3	1026.0	1094.6	1164.9
47.5°	766.5	762.0	763.4	769.2	788.7	818.9	855.9	897.7	944.2	1002.3	1064.0
50°	734.5	728.2	725.8	732.1	749.7	776.1	811.2	847.9	891.8	942.9	995.6
52.5°	699.4	693.0	688.7	693.2	709.5	733.9	765.8	798.1	837.5	879.1	924.7
55°	645.1	637.9	635.5	637.1	649.1	668.3	695.4	725.0	754.5	788.8	820.8
57.5°	591.6	579.8	577.6	576.8	585.1	602.6	625.3	650.9	672.4	693.2	727.2
60°	556.5	542.1	537.3	536.5	542.9	557.3	578.0	603.6	618.8	633.1	662.7
62.5°	518.8	505.1	494.5	495.7	501.4	515.1	533.3	551.9	561.9	577.6	597.5
65°	460.7	443.1	435.1	432.7	435.9	447.1	461.5	473.5	484.6	491.0	510.2
67.5°	402.6	387.9	376.1	373.2	371.7	379.4	391.2	398.4	406.4	412.0	423.3
70°	361.7	348.9	334.5	329.7	328.9	335.3	346.5	347.3	358.5	360.9	372.9
72.5°	321.4	305.5	295.6	290.8	287.4	293.2	300.5	302.6	308.7	313.0	319.2
75°	258.7	246.7	237.1	229.9	227.5	230.7	230.7	234.7	238.7	241.1	248.3
77.5°	203.6	189.9	178.5	174.4	171.5	169.4	171.2	173.6	171.7	175.8	177.4
80°	165.3	150.9	142.1	140.5	135.7	131.7	130.9	133.3	130.1	131.7	136.5
82.5°	127.6	118.3	108.9	107.3	101.2	99.2	98.4	96.9	96.9	96.6	97.6
85°	75.8	70.3	63.9	59.9	57.5	53.5	53.5	51.9	50.3	48.7	49.5
87.5°	36.1	34.5	30.9	28.6	26.9	23.9	23.4	20.9	19.7	18.5	17.3
90°	27.1	25.6	23.5	21.4	19.4	17.3	14.8	12.0	9.2	6.3	3.5
92.5°	26.2	24.6	22.6	20.5	18.4	16.4	15.3	15.1	15.0	14.8	14.6
95°	27.1	25.6	25.3	25.0	24.8	24.5	28.8	37.6	46.3	55.1	63.9
97.5°	30.8	30.7	59.5	88.3	117.1	145.9	157.6	152.1	146.7	141.2	135.7
100°	46.7	51.1	86.8	122.4	158.0	193.7	209.2	204.5	199.9	195.2	190.6
102.5°	199.0	246.3	251.0	255.6	260.3	264.9	265.5	262.1	258.7	255.3	251.9
105°	364.9	362.5	361.2	359.9	358.7	357.4	355.9	354.4	352.8	351.3	349.7
107.5°	453.1	452.0	450.2	448.5	446.7	445.0	443.7	442.9	442.2	441.4	440.6
110°	512.9	512.4	510.9	509.3	507.8	506.2	505.1	504.3	503.5	502.7	502.0



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	570.9	571.0	570.3	569.5	568.8	568.1	567.0	565.6	564.2	562.9	561.5
115°	655.9	655.3	655.6	655.9	656.1	656.4	656.1	655.3	654.6	653.8	653.0
117.5°	742.6	742.7	742.2	741.6	741.0	740.4	739.6	738.6	737.6	736.5	735.5
120°	795.3	794.8	795.0	795.3	795.6	795.8	795.4	794.4	793.4	792.3	791.3
122.5°	848.1	847.8	847.4	847.0	846.7	846.3	845.8	845.2	844.6	844.0	843.3
125°	921.0	920.3	920.8	921.3	921.8	922.3	922.1	921.0	920.0	919.0	917.9
127.5°	994.9	995.1	993.9	992.7	991.5	990.3	989.6	989.4	989.1	988.8	988.6
130°	1039.0	1038.8	1038.0	1037.2	1036.5	1035.7	1035.2	1034.9	1034.7	1034.4	1034.1
132.5°	1082.7	1082.5	1081.5	1080.5	1079.5	1078.6	1077.8	1077.4	1076.9	1076.4	1076.0
135°	1142.7	1142.2	1141.2	1140.1	1139.1	1138.1	1137.7	1137.9	1138.2	1138.5	1138.7
137.5°	1200.4	1199.8	1198.7	1197.6	1196.4	1195.3	1194.7	1194.6	1194.5	1194.4	1194.3
140°	1235.9	1235.2	1234.6	1234.1	1233.6	1233.1	1232.6	1232.1	1231.5	1231.0	1230.5
142.5°	1269.2	1268.6	1268.3	1268.0	1267.7	1267.4	1266.8	1265.8	1264.9	1264.0	1263.0
145°	1316.8	1316.5	1316.5	1316.5	1316.5	1316.5	1316.1	1315.3	1314.6	1313.8	1313.0
147.5°	1358.3	1358.1	1358.3	1358.6	1358.9	1359.1	1358.5	1357.1	1355.6	1354.2	1352.7
150°	1385.0	1385.0	1385.3	1385.6	1385.8	1386.1	1385.7	1384.7	1383.6	1382.6	1381.6
152.5°	1407.8	1407.4	1407.8	1408.3	1408.8	1409.2	1409.0	1408.2	1407.4	1406.6	1405.7
155°	1438.4	1437.3	1438.1	1438.9	1439.7	1440.4	1440.7	1440.4	1440.2	1439.9	1439.7
157.5°	1464.9	1463.6	1464.5	1465.4	1466.2	1467.1	1467.6	1467.8	1467.9	1468.1	1468.2
160°	1481.9	1480.3	1480.6	1480.8	1481.1	1481.4	1481.9	1482.7	1483.4	1484.2	1485.0
162.5°	1495.8	1494.3	1494.5	1494.8	1495.0	1495.3	1495.9	1496.9	1497.9	1498.9	1499.8
165°	1514.9	1512.9	1512.9	1512.9	1512.9	1512.9	1513.5	1514.8	1516.1	1517.4	1518.7
167.5°	1529.1	1526.8	1527.0	1527.1	1527.3	1527.4	1528.2	1529.5	1530.9	1532.2	1533.5
170°	1538.2	1536.1	1535.8	1535.6	1535.3	1535.1	1535.7	1537.3	1538.8	1540.4	1541.9
172.5°	1543.7	1541.7	1541.4	1541.2	1540.9	1540.6	1541.3	1542.8	1544.4	1545.9	1547.5
175°	1550.0	1547.7	1547.5	1547.2	1546.9	1546.7	1547.3	1548.9	1550.4	1552.0	1553.5
177.5°	1553.3	1551.7	1551.3	1550.8	1550.4	1550.0	1550.5	1552.0	1553.4	1554.9	1556.3
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1940.1	1946.5	1954.8	1968.9	1974.0	1980.4	1989.3	1988.7	1991.2	2000.8	2021.3
5°	1947.3	1972.1	1996.0	2024.8	2055.1	2075.1	2102.2	2119.0	2135.8	2157.3	2194.0
7.5°	1950.2	1989.5	2033.4	2083.9	2128.7	2180.5	2220.9	2258.9	2293.2	2338.7	2382.5
10°	1945.7	1998.4	2055.1	2119.0	2186.8	2244.3	2296.2	2355.3	2405.6	2460.7	2510.2
12.5°	1937.4	2001.0	2076.8	2148.4	2227.7	2312.7	2377.4	2437.1	2504.0	2567.4	2643.7
15°	1918.6	2005.6	2094.2	2188.4	2294.6	2392.8	2486.3	2563.7	2635.6	2730.6	2830.4
17.5°	1894.6	1988.5	2100.3	2214.3	2325.3	2437.6	2553.2	2669.6	2760.3	2878.3	2956.4
20°	1872.3	1980.9	2095.8	2231.6	2342.5	2482.3	2597.2	2709.8	2834.4	2951.7	3045.1
22.5°	1841.0	1959.8	2081.8	2216.9	2363.0	2502.7	2635.6	2757.7	2882.3	3009.9	3123.1
25°	1801.2	1909.0	2053.5	2206.8	2352.1	2503.8	2656.3	2809.6	2943.7	3078.7	3184.1
27.5°	1733.5	1869.6	2004.2	2162.4	2323.9	2495.5	2658.6	2819.0	2959.6	3070.5	3135.8
30°	1699.0	1817.2	1963.3	2122.2	2297.0	2481.5	2651.5	2808.8	2939.8	3028.4	3054.7
32.5°	1647.9	1769.9	1912.8	2077.5	2262.5	2452.1	2629.2	2777.5	2886.7	2933.2	2901.4
35°	1572.1	1682.3	1826.8	1995.2	2187.6	2389.6	2564.5	2689.8	2745.7	2701.8	2592.4
37.5°	1481.1	1590.3	1735.4	1900.9	2100.0	2305.3	2463.4	2553.6	2535.1	2425.9	2262.9
40°	1417.2	1519.4	1657.5	1836.3	2030.4	2236.4	2375.3	2424.0	2372.9	2216.4	2043.1
42.5°	1346.3	1445.9	1584.7	1757.1	1962.7	2152.7	2273.7	2277.7	2192.1	2005.0	1831.1
45°	1238.3	1333.3	1464.3	1643.9	1834.0	2012.8	2092.6	2053.5	1895.4	1715.0	1540.1
47.5°	1131.8	1214.2	1343.2	1513.8	1694.2	1844.8	1884.4	1814.0	1645.5	1470.4	1308.3
50°	1053.9	1136.9	1258.3	1421.2	1595.2	1725.4	1744.5	1651.1	1485.8	1309.4	1182.4
52.5°	979.2	1061.6	1178.5	1329.2	1488.6	1605.9	1606.6	1498.5	1333.8	1176.5	1058.5
55°	869.5	943.7	1049.1	1184.0	1326.2	1418.0	1395.6	1283.8	1140.9	1004.4	901.4
57.5°	763.8	828.4	925.5	1038.1	1163.3	1239.0	1201.9	1094.3	966.7	850.9	772.9
60°	695.4	756.9	839.9	946.1	1051.5	1110.6	1075.5	978.1	860.7	767.3	699.4
62.5°	629.0	680.9	760.7	852.9	950.6	994.3	963.0	866.9	765.5	681.0	626.0
65°	534.9	577.3	641.1	720.2	791.2	828.8	802.4	713.0	635.5	574.9	530.9
67.5°	447.1	480.2	528.5	591.9	652.3	672.6	648.6	586.4	520.7	472.2	441.2
70°	386.4	417.6	458.3	507.0	559.7	581.2	557.3	507.8	454.3	409.6	379.2
72.5°	333.4	357.5	391.9	433.5	474.7	496.3	480.0	432.4	387.2	354.0	328.1
75°	253.9	274.7	298.6	328.1	360.1	374.5	360.1	327.3	296.2	271.5	253.1
77.5°	184.6	195.8	214.3	236.3	256.3	267.3	254.9	232.7	213.7	196.7	187.6
80°	140.5	148.5	161.3	178.8	192.4	202.8	194.8	176.4	161.3	150.1	146.1
82.5°	102.2	107.6	115.9	129.0	138.1	143.4	139.9	126.6	120.4	110.5	106.5
85°	50.3	53.5	59.1	63.1	71.1	71.9	72.7	67.1	61.5	59.1	55.9
87.5°	18.5	19.7	22.2	24.7	27.7	28.8	28.6	29.0	26.8	26.5	24.3
90°	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1	28.7
92.5°	14.8	15.0	15.1	15.3	16.4	18.4	20.5	22.6	24.6	26.2	27.7
95°	55.1	46.3	37.6	28.8	24.5	24.8	25.0	25.3	25.6	27.1	28.7
97.5°	141.2	146.7	152.1	157.6	145.9	117.1	88.3	59.5	30.7	30.8	31.0
100°	195.2	199.9	204.5	209.2	193.7	158.0	122.4	86.8	51.1	46.7	42.3
102.5°	255.3	258.7	262.1	265.5	264.9	260.3	255.6	251.0	246.3	199.0	151.6
105°	351.3	352.8	354.4	355.9	357.4	358.7	359.9	361.2	362.5	364.9	367.2
107.5°	441.4	442.2	442.9	443.7	445.0	446.7	448.5	450.2	452.0	453.1	454.3
110°	502.7	503.5	504.3	505.1	506.2	507.8	509.3	510.9	512.4	512.9	513.5



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	562.9	564.2	565.6	567.0	568.1	568.8	569.5	570.3	571.0	570.9	570.8
115°	653.8	654.6	655.3	656.1	656.4	656.1	655.9	655.6	655.3	655.9	656.4
117.5°	736.5	737.6	738.6	739.6	740.4	741.0	741.6	742.2	742.7	742.6	742.5
120°	792.3	793.4	794.4	795.4	795.8	795.6	795.3	795.0	794.8	795.3	795.8
122.5°	844.0	844.6	845.2	845.8	846.3	846.7	847.0	847.4	847.8	848.1	848.4
125°	919.0	920.0	921.0	922.1	922.3	921.8	921.3	920.8	920.3	921.0	921.8
127.5°	988.8	989.1	989.4	989.6	990.3	991.5	992.7	993.9	995.1	994.9	994.8
130°	1034.4	1034.7	1034.9	1035.2	1035.7	1036.5	1037.2	1038.0	1038.8	1039.0	1039.3
132.5°	1076.4	1076.9	1077.4	1077.8	1078.6	1079.5	1080.5	1081.5	1082.5	1082.7	1083.0
135°	1138.5	1138.2	1137.9	1137.7	1138.1	1139.1	1140.1	1141.2	1142.2	1142.7	1143.2
137.5°	1194.4	1194.5	1194.6	1194.7	1195.3	1196.4	1197.6	1198.7	1199.8	1200.4	1201.0
140°	1231.0	1231.5	1232.1	1232.6	1233.1	1233.6	1234.1	1234.6	1235.2	1235.9	1236.7
142.5°	1264.0	1264.9	1265.8	1266.8	1267.4	1267.7	1268.0	1268.3	1268.6	1269.2	1269.8
145°	1313.8	1314.6	1315.3	1316.1	1316.5	1316.5	1316.5	1316.5	1316.5	1316.8	1317.0
147.5°	1354.2	1355.6	1357.1	1358.5	1359.1	1358.9	1358.6	1358.3	1358.1	1358.3	1358.5
150°	1382.6	1383.6	1384.7	1385.7	1386.1	1385.8	1385.6	1385.3	1385.0	1385.0	1385.0
152.5°	1406.6	1407.4	1408.2	1409.0	1409.2	1408.8	1408.3	1407.8	1407.4	1407.8	1408.2
155°	1439.9	1440.2	1440.4	1440.7	1440.4	1439.7	1438.9	1438.1	1437.3	1438.4	1439.4
157.5°	1468.1	1467.9	1467.8	1467.6	1467.1	1466.2	1465.4	1464.5	1463.6	1464.9	1466.3
160°	1484.2	1483.4	1482.7	1481.9	1481.4	1481.1	1480.8	1480.6	1480.3	1481.9	1483.4
162.5°	1498.9	1497.9	1496.9	1495.9	1495.3	1495.0	1494.8	1494.5	1494.3	1495.8	1497.4
165°	1517.4	1516.1	1514.8	1513.5	1512.9	1512.9	1512.9	1512.9	1512.9	1514.9	1517.0
167.5°	1532.2	1530.9	1529.5	1528.2	1527.4	1527.3	1527.1	1527.0	1526.8	1529.1	1531.4
170°	1540.4	1538.8	1537.3	1535.7	1535.1	1535.3	1535.6	1535.8	1536.1	1538.2	1540.2
172.5°	1545.9	1544.4	1542.8	1541.3	1540.6	1540.9	1541.2	1541.4	1541.7	1543.7	1545.8
175°	1552.0	1550.4	1548.9	1547.3	1546.7	1546.9	1547.2	1547.5	1547.7	1550.0	1552.4
177.5°	1554.9	1553.4	1552.0	1550.5	1550.0	1550.4	1550.8	1551.3	1551.7	1553.3	1555.0
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2031.5	2032.8	2038.5	2043.0	2044.3	2050.6	2051.3
5°	2210.0	2223.6	2249.9	2252.3	2256.3	2277.1	2261.1
7.5°	2419.2	2453.7	2476.7	2497.0	2504.3	2513.4	2511.5
10°	2553.3	2604.4	2630.0	2670.7	2672.3	2682.7	2676.3
12.5°	2688.1	2747.5	2794.1	2801.6	2835.8	2841.1	2850.0
15°	2879.1	2942.1	3006.8	3030.0	3077.1	3088.3	3105.8
17.5°	3058.6	3123.1	3168.4	3228.3	3247.6	3273.5	3255.9
20°	3156.9	3227.2	3284.7	3331.8	3351.7	3366.1	3364.5
22.5°	3216.3	3287.2	3333.8	3369.5	3388.1	3394.2	3393.9
25°	3253.5	3294.2	3308.6	3322.2	3301.4	3294.2	3297.4
27.5°	3150.1	3139.5	3102.0	3052.8	3001.7	2961.1	2939.1
30°	3007.6	2945.3	2888.7	2789.6	2738.6	2708.2	2681.1
32.5°	2805.8	2707.1	2598.0	2507.3	2449.2	2404.2	2397.5
35°	2459.9	2311.4	2178.1	2067.1	2009.6	1960.9	1949.7
37.5°	2091.4	1937.1	1817.0	1719.3	1657.5	1623.2	1591.1
40°	1846.7	1714.2	1596.0	1513.0	1465.9	1441.1	1421.2
42.5°	1658.3	1537.3	1419.7	1356.5	1313.9	1298.7	1287.0
45°	1398.0	1285.4	1204.0	1156.1	1131.3	1105.8	1093.8
47.5°	1189.6	1098.0	1044.3	1003.6	977.1	961.9	954.3
50°	1071.5	996.4	948.5	917.4	893.4	881.4	875.1
52.5°	966.7	905.1	864.8	840.1	823.8	815.0	812.5
55°	832.7	785.6	760.1	738.5	726.6	718.6	715.4
57.5°	723.8	687.6	666.8	649.1	644.5	637.8	635.5
60°	652.3	624.4	606.8	594.8	590.8	582.8	584.4
62.5°	589.1	566.2	551.2	544.4	539.1	532.4	534.6
65°	498.2	481.4	473.5	467.1	460.7	456.7	459.9
67.5°	418.0	406.6	395.7	392.0	388.8	388.2	384.8
70°	365.7	356.1	346.5	344.1	344.1	340.9	340.1
72.5°	315.2	308.2	301.8	300.0	297.5	298.8	295.4
75°	243.5	237.9	235.5	233.1	232.3	232.3	229.9
77.5°	180.0	175.8	172.0	172.0	169.1	168.0	167.7
80°	136.5	134.9	131.7	131.7	130.1	130.9	129.3
82.5°	102.7	100.4	99.8	98.5	96.3	96.4	94.9
85°	55.1	52.7	51.9	49.5	47.9	49.5	47.9
87.5°	25.2	24.9	24.4	23.3	22.7	22.8	21.0
90°	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	29.3	30.8	31.7	31.8	31.9	32.0	32.1
95°	30.2	31.8	32.7	32.9	33.2	33.4	33.7
97.5°	31.1	31.3	31.5	31.8	32.0	32.3	32.5
100°	38.0	33.6	31.5	31.8	32.0	32.3	32.5
102.5°	104.3	56.9	33.3	33.3	33.4	33.4	33.5
105°	369.5	371.8	368.3	359.0	349.7	340.5	331.2
107.5°	455.4	456.5	457.6	458.6	459.6	460.5	461.5
110°	514.0	514.5	515.1	515.9	516.7	517.5	518.2



TEST NUMBER: P332706

CATALOG NUMBER: SA4XXDIP-C1195D1205U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	570.7	570.6	571.0	572.0	573.0	574.0	574.9
115°	656.9	657.4	657.7	657.7	657.7	657.7	657.7
117.5°	742.4	742.3	742.2	742.1	742.0	741.9	741.8
120°	796.3	796.8	796.8	796.3	795.8	795.3	794.8
122.5°	848.7	849.0	848.9	848.4	847.9	847.3	846.8
125°	922.6	923.4	923.9	924.1	924.4	924.7	924.9
127.5°	994.6	994.5	994.3	994.1	993.9	993.7	993.5
130°	1039.6	1039.8	1039.9	1039.9	1039.9	1039.9	1039.9
132.5°	1083.3	1083.5	1083.5	1083.3	1083.1	1082.9	1082.7
135°	1143.7	1144.3	1144.8	1145.3	1145.8	1146.3	1146.8
137.5°	1201.5	1202.1	1202.3	1202.2	1202.0	1201.8	1201.7
140°	1237.5	1238.3	1238.8	1239.0	1239.3	1239.5	1239.8
142.5°	1270.3	1270.9	1271.2	1271.3	1271.3	1271.4	1271.4
145°	1317.3	1317.5	1317.9	1318.4	1318.9	1319.5	1320.0
147.5°	1358.7	1358.9	1359.1	1359.4	1359.7	1359.9	1360.2
150°	1385.0	1385.0	1385.2	1385.4	1385.7	1386.0	1386.2
152.5°	1408.6	1409.0	1409.1	1409.0	1408.8	1408.7	1408.5
155°	1440.4	1441.5	1441.6	1440.8	1440.0	1439.3	1438.5
157.5°	1467.6	1469.0	1469.0	1467.6	1466.3	1464.9	1463.6
160°	1485.0	1486.5	1486.5	1485.0	1483.4	1481.9	1480.3
162.5°	1498.9	1500.5	1500.4	1498.6	1496.9	1495.1	1493.3
165°	1519.1	1521.1	1521.0	1518.7	1516.3	1514.0	1511.7
167.5°	1533.6	1535.9	1535.7	1533.2	1530.6	1528.0	1525.4
170°	1542.3	1544.4	1544.1	1541.5	1538.9	1536.4	1533.8
172.5°	1547.9	1549.9	1549.6	1546.8	1544.0	1541.2	1538.4
175°	1554.7	1557.0	1556.6	1553.5	1550.4	1547.3	1544.2
177.5°	1556.6	1558.3	1557.9	1555.4	1552.9	1550.4	1548.0
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5

(END OF REPORT)