

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332673

Luminaire Tested: **SA4XXDIP-C1195D365U835-4F0-1E-UDD-D**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332673  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D365U835-4F0-1E-UDD-D  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6323.9 lumens  
Efficiency: N/A  
Efficacy: 127.0 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39  
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')  
CIE Type: Semi-Direct

Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332673  
CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-D

### Luminous Intensity Polar Plot





TEST NUMBER: P332673

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-D

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	71	
1	101	96	91	87	95	91	87	83	81	78	75	73	70	68	64	63	61	61	61	61	57	
2	91	83	76	70	86	79	72	67	70	65	61	63	59	56	56	53	50	50	50	50	46	
3	83	73	64	58	78	69	61	55	62	56	51	55	50	46	49	45	42	42	42	42	39	
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	39	36	36	36	36	33	
5	70	57	48	41	65	54	46	40	49	42	37	44	38	34	39	35	31	31	31	31	28	
6	64	51	42	36	60	49	40	35	44	37	32	39	34	30	35	31	27	27	27	27	24	
7	59	46	37	31	56	44	36	30	40	33	28	36	30	26	32	28	24	24	24	24	22	
8	55	42	34	28	52	40	32	27	36	30	25	33	27	23	30	25	21	21	21	21	19	
9	51	38	30	25	48	37	29	24	33	27	22	30	25	21	27	23	19	19	19	19	17	
10	48	35	27	22	45	34	26	22	31	24	20	28	23	19	25	21	17	17	17	17	16	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11512	11512	11512
5°	11547	11251	11283
10°	11477	11067	11058
15°	11374	10854	10794
20°	11219	10619	10537
25°	11044	10355	10254
30°	10854	10093	9964
35°	10640	9824	9710
40°	10469	9569	9445
45°	10215	9334	9218
50°	10000	9062	8977
55°	9778	8806	8695
60°	9431	8480	8438
65°	9051	8130	8122
70°	8591	7730	7753
75°	7950	7291	7421
80°	7239	6868	7093
85°	6329	6495	6901



TEST NUMBER: P332673

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-D

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.0	2.1
10°-20°	386.9	6.1
20°-30°	585.0	9.3
30°-40°	707.8	11.2
40°-50°	748.3	11.8
50°-60°	704.2	11.1
60°-70°	584.3	9.2
70°-80°	410.4	6.5
80°-90°	233.4	3.7
90°-100°	153.9	2.4
100°-110°	205.0	3.2
110°-120°	265.6	4.2
120°-130°	288.8	4.6
130°-140°	284.4	4.5
140°-150°	253.7	4.0
150°-160°	201.9	3.2
160°-170°	130.2	2.1
170°-180°	44.9	0.7
0°-30°	1106.9	17.5
0°-40°	1814.7	28.7
0°-60°	3267.3	51.7
0°-90°	4495.4	71.1
90°-120°	624.5	9.9
90°-150°	1451.5	23.0
90°-180°	1829.0	28.9
0°-180°	6323.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1426	1426	1426	1426	1426	
5°	1428	1422	1412	1424	1423	135
15°	1368	1370	1365	1379	1378	385
25°	1252	1261	1266	1283	1285	576
35°	1095	1114	1130	1152	1158	686
45°	913	944	974	1000	1009	706
55°	715	750	797	828	838	637
65°	495	546	600	639	653	490
75°	275	334	401	444	460	292
85°	85	152	224	270	287	90
90°	27	95	166	212	228	18
95°	40	82	147	190	207	41
105°	121	156	216	256	259	127
115°	208	226	274	309	321	206
125°	286	288	325	355	366	255
135°	350	350	362	387	398	270
145°	401	400	400	410	417	251
155°	438	438	437	438	438	202
165°	462	460	460	463	460	130
175°	472	470	471	474	470	45
180°	472	472	472	472	472	



TEST NUMBER: P332673

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0
2.5°	1431.1	1430.2	1429.4	1428.5	1427.7	1426.1	1423.8	1421.6	1419.3	1417.0	1419.0
5°	1427.5	1426.5	1425.4	1424.4	1423.3	1421.5	1419.0	1416.5	1414.1	1411.6	1414.4
7.5°	1415.4	1414.8	1414.1	1413.5	1412.9	1411.5	1409.5	1407.4	1405.3	1403.3	1406.5
10°	1405.2	1404.8	1404.5	1404.1	1403.8	1402.7	1400.9	1399.2	1397.4	1395.6	1398.8
12.5°	1391.1	1391.1	1391.0	1390.9	1390.9	1390.2	1389.0	1387.8	1386.6	1385.4	1388.3
15°	1368.5	1368.8	1369.2	1369.5	1369.9	1369.5	1368.5	1367.4	1366.3	1365.3	1368.5
17.5°	1337.5	1338.6	1339.6	1340.7	1341.7	1342.2	1342.0	1341.7	1341.5	1341.3	1344.6
20°	1315.8	1316.8	1317.9	1319.0	1320.0	1320.7	1321.1	1321.5	1321.8	1322.2	1325.7
22.5°	1291.5	1292.8	1294.2	1295.5	1296.9	1297.9	1298.5	1299.2	1299.8	1300.4	1304.0
25°	1251.9	1254.0	1256.2	1258.3	1260.4	1262.0	1263.1	1264.1	1265.2	1266.3	1270.2
27.5°	1207.8	1211.0	1214.1	1217.2	1220.3	1222.7	1224.3	1226.0	1227.6	1229.2	1232.8
30°	1178.4	1181.3	1184.1	1187.0	1189.8	1192.5	1194.9	1197.4	1199.9	1202.4	1206.3
32.5°	1146.5	1149.9	1153.3	1156.7	1160.1	1163.2	1166.0	1168.8	1171.5	1174.3	1178.8
35°	1095.4	1099.7	1103.9	1108.2	1112.4	1116.3	1119.9	1123.4	1127.0	1130.5	1135.5
37.5°	1044.0	1048.9	1053.8	1058.7	1063.6	1068.2	1072.6	1077.0	1081.4	1085.8	1090.9
40°	1010.8	1015.4	1020.0	1024.6	1029.2	1034.0	1039.0	1044.0	1048.9	1053.9	1059.2
42.5°	972.5	977.6	982.8	988.0	993.2	998.7	1004.5	1010.3	1016.1	1022.0	1027.9
45°	913.4	920.1	926.9	933.6	940.3	947.1	953.8	960.6	967.3	974.1	980.1
47.5°	856.8	863.8	870.8	877.7	884.7	892.1	899.9	907.7	915.5	923.3	929.5
50°	816.0	823.8	831.6	839.4	847.2	855.0	862.8	870.6	878.4	886.2	893.3
52.5°	775.1	782.9	790.7	798.5	806.3	814.7	823.6	832.6	841.5	850.5	857.6
55°	715.4	722.8	730.3	737.7	745.2	754.2	764.9	775.5	786.2	796.8	803.9
57.5°	648.6	657.9	667.1	676.3	685.5	695.4	706.0	716.6	727.2	737.7	746.2
60°	605.2	614.4	623.6	632.9	642.1	652.6	664.3	676.0	687.7	699.4	707.6
62.5°	563.0	573.1	583.2	593.3	603.3	614.2	626.0	637.7	649.4	661.1	669.2
65°	495.0	506.4	517.7	529.1	540.4	552.1	564.2	576.3	588.3	600.4	609.3
67.5°	429.5	441.6	453.7	465.7	477.8	490.3	503.2	516.1	529.0	542.0	551.0
70°	384.8	396.9	409.0	421.0	433.1	445.9	459.3	472.8	486.3	499.8	509.4
72.5°	341.4	353.7	366.1	378.4	390.8	404.1	418.5	432.8	447.1	461.5	470.8
75°	274.7	287.8	300.9	314.0	327.2	341.2	356.1	371.0	385.9	400.8	410.7
77.5°	212.4	226.3	240.2	254.1	268.0	282.8	298.4	314.0	329.6	345.2	355.3
80°	174.1	188.2	202.4	216.6	230.8	245.7	261.3	277.0	292.6	308.2	318.8
82.5°	135.7	150.5	165.3	180.0	194.8	210.0	225.6	241.2	256.8	272.4	283.3
85°	84.6	99.5	114.4	129.3	144.2	159.7	175.6	191.6	207.6	223.6	234.2
87.5°	47.5	62.1	76.8	91.4	106.1	121.2	136.9	152.6	168.2	183.9	194.3
90°	26.6	41.7	56.7	71.8	86.8	102.3	118.2	134.1	150.0	165.9	176.6
92.5°	28.7	41.5	54.4	67.2	80.0	94.4	110.3	126.1	142.0	157.9	168.4
95°	40.2	49.2	58.3	67.3	76.4	88.2	102.8	117.4	132.1	146.7	156.7
97.5°	60.1	71.9	83.6	95.3	107.1	115.8	121.4	127.1	132.7	138.4	147.7
100°	75.5	86.2	96.8	107.4	118.1	124.9	127.9	130.9	133.9	136.9	145.2
102.5°	94.2	103.3	112.4	121.6	130.7	141.3	153.5	165.6	177.8	189.9	184.8
105°	120.7	128.3	135.9	143.5	151.0	161.6	175.1	188.6	202.1	215.7	225.2
107.5°	148.1	154.1	160.2	166.2	172.3	181.8	194.7	207.7	220.7	233.6	242.7
110°	165.4	170.7	175.9	181.1	186.3	195.3	208.2	221.1	234.0	246.9	255.2



TEST NUMBER: P332673

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	182.3	187.1	191.9	196.7	201.6	210.0	222.1	234.2	246.2	258.3	266.1
115°	208.2	211.6	215.1	218.5	221.9	229.3	240.5	251.8	263.1	274.4	282.3
117.5°	233.0	235.2	237.4	239.7	241.9	248.4	259.1	269.9	280.6	291.4	298.7
120°	248.7	250.0	251.4	252.8	254.2	260.0	270.2	280.4	290.6	300.8	308.1
122.5°	264.5	264.9	265.3	265.7	266.1	271.2	281.0	290.9	300.7	310.5	317.7
125°	285.6	285.5	285.5	285.5	285.4	289.8	298.5	307.2	315.9	324.6	331.6
127.5°	306.8	306.5	306.2	305.9	305.6	309.1	316.3	323.4	330.6	337.8	344.1
130°	319.3	319.1	318.8	318.5	318.2	321.0	327.0	332.9	338.8	344.7	351.2
132.5°	332.1	331.8	331.6	331.4	331.2	333.5	338.4	343.2	348.0	352.9	359.1
135°	349.5	349.5	349.4	349.3	349.2	350.6	353.4	356.2	359.0	361.8	367.6
137.5°	366.4	366.1	365.8	365.5	365.1	365.8	367.3	368.9	370.4	372.0	377.3
140°	377.5	377.3	377.1	376.9	376.7	376.8	377.3	377.8	378.4	378.9	383.7
142.5°	386.1	386.3	386.5	386.7	386.9	387.0	386.9	386.7	386.6	386.5	390.7
145°	401.0	400.8	400.7	400.6	400.5	400.4	400.4	400.4	400.4	400.4	402.6
147.5°	413.0	413.1	413.2	413.3	413.4	413.4	413.3	413.2	413.1	413.1	413.4
150°	421.8	421.8	421.7	421.7	421.6	421.6	421.5	421.4	421.3	421.3	421.3
152.5°	427.9	428.1	428.2	428.4	428.6	428.6	428.5	428.3	428.2	428.1	428.2
155°	437.9	438.0	438.0	438.1	438.2	438.1	437.9	437.6	437.4	437.2	437.5
157.5°	446.6	446.5	446.5	446.4	446.4	446.2	446.0	445.7	445.4	445.2	445.6
160°	451.7	451.4	451.2	451.0	450.7	450.6	450.5	450.4	450.3	450.2	450.7
162.5°	456.2	455.9	455.6	455.3	455.0	454.8	454.7	454.6	454.6	454.5	455.0
165°	461.9	461.5	461.1	460.7	460.3	460.1	460.1	460.1	460.1	460.1	460.8
167.5°	466.4	466.0	465.6	465.2	464.8	464.6	464.5	464.5	464.4	464.4	465.1
170°	469.0	468.5	468.0	467.6	467.1	466.9	467.0	467.1	467.1	467.2	467.8
172.5°	470.7	470.2	469.7	469.3	468.8	468.6	468.7	468.8	468.8	468.9	469.5
175°	472.5	472.0	471.6	471.1	470.6	470.4	470.5	470.6	470.7	470.7	471.5
177.5°	473.4	472.9	472.5	472.0	471.6	471.4	471.6	471.7	471.8	471.9	472.5
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5



TEST NUMBER: P332673

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0	1426.0
2.5°	1421.0	1423.0	1425.0	1425.8	1425.5	1425.2	1425.0	1424.7
5°	1417.3	1420.1	1422.9	1424.2	1423.8	1423.5	1423.1	1422.8
7.5°	1409.7	1412.9	1416.1	1417.5	1417.1	1416.8	1416.4	1416.1
10°	1402.0	1405.2	1408.4	1409.8	1409.5	1409.1	1408.7	1408.4
12.5°	1391.2	1394.1	1397.0	1398.5	1398.4	1398.3	1398.2	1398.2
15°	1371.7	1374.9	1378.0	1379.5	1379.1	1378.8	1378.4	1378.0
17.5°	1347.9	1351.1	1354.4	1355.9	1355.6	1355.3	1355.0	1354.7
20°	1329.3	1332.8	1336.4	1338.1	1338.1	1338.1	1338.1	1338.1
22.5°	1307.5	1311.1	1314.6	1316.7	1317.3	1317.8	1318.4	1319.0
25°	1274.1	1278.0	1281.9	1284.0	1284.4	1284.7	1285.1	1285.4
27.5°	1236.5	1240.1	1243.7	1245.7	1246.2	1246.6	1247.0	1247.4
30°	1210.2	1214.1	1218.0	1220.3	1221.0	1221.7	1222.4	1223.2
32.5°	1183.2	1187.7	1192.2	1194.8	1195.5	1196.2	1196.9	1197.6
35°	1140.5	1145.4	1150.4	1153.4	1154.5	1155.6	1156.6	1157.7
37.5°	1095.9	1100.9	1106.0	1109.1	1110.2	1111.3	1112.5	1113.6
40°	1064.5	1069.9	1075.2	1078.6	1080.0	1081.4	1082.8	1084.2
42.5°	1033.7	1039.6	1045.5	1049.0	1050.2	1051.3	1052.4	1053.6
45°	986.1	992.2	998.2	1002.1	1003.9	1005.6	1007.4	1009.2
47.5°	935.8	942.0	948.3	952.4	954.6	956.7	958.8	961.0
50°	900.4	907.5	914.6	919.2	921.4	923.5	925.6	927.7
52.5°	864.7	871.8	878.8	883.5	885.6	887.7	889.8	892.0
55°	811.0	818.1	825.2	829.8	831.9	834.1	836.2	838.3
57.5°	754.6	763.1	771.5	776.7	778.7	780.7	782.7	784.7
60°	715.7	723.9	732.0	737.5	740.4	743.2	746.1	748.9
62.5°	677.4	685.6	693.7	699.2	702.1	704.9	707.7	710.6
65°	618.1	627.0	635.9	641.7	644.6	647.4	650.3	653.1
67.5°	560.0	569.0	578.0	583.9	586.7	589.4	592.2	595.0
70°	519.0	528.5	538.1	544.2	546.6	549.1	551.6	554.1
72.5°	480.1	489.4	498.7	504.7	507.5	510.2	513.0	515.8
75°	420.7	430.6	440.5	447.1	450.3	453.5	456.7	459.9
77.5°	365.4	375.5	385.5	392.3	395.7	399.1	402.5	405.9
80°	329.5	340.1	350.8	357.5	360.3	363.2	366.0	368.9
82.5°	294.3	305.2	316.1	323.2	326.3	329.4	332.5	335.6
85°	244.8	255.5	266.1	273.2	276.8	280.3	283.9	287.4
87.5°	204.7	215.1	225.5	232.2	235.4	238.5	241.7	244.8
90°	187.4	198.1	208.9	215.8	218.8	221.8	224.8	227.8
92.5°	178.9	189.3	199.8	206.5	209.4	212.2	215.1	218.0
95°	166.8	176.9	186.9	193.6	196.8	200.1	203.4	206.7
97.5°	157.0	166.4	175.7	182.0	185.1	188.2	191.4	194.5
100°	153.4	161.6	169.9	175.3	177.9	180.4	183.0	185.5
102.5°	179.7	174.6	169.5	168.3	171.1	173.9	176.7	179.4
105°	234.8	244.4	254.0	258.8	258.8	258.8	258.8	258.8
107.5°	251.8	260.8	269.9	275.9	278.7	281.6	284.4	287.3
110°	263.5	271.8	280.1	285.8	288.9	292.0	295.1	298.1





TEST NUMBER: P332673

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.0	281.8	289.7	295.2	298.3	301.4	304.6	307.7
115°	290.3	298.3	306.2	311.5	313.9	316.4	318.9	321.4
117.5°	306.1	313.4	320.8	325.8	328.7	331.5	334.3	337.1
120°	315.3	322.6	329.8	334.8	337.5	340.2	342.8	345.5
122.5°	324.9	332.1	339.3	344.1	346.5	348.9	351.3	353.7
125°	338.6	345.5	352.5	357.1	359.3	361.5	363.7	365.9
127.5°	350.5	356.8	363.2	367.5	369.8	372.2	374.5	376.9
130°	357.6	364.1	370.6	374.9	377.0	379.1	381.2	383.4
132.5°	365.2	371.4	377.6	381.7	383.8	385.9	387.9	390.0
135°	373.4	379.3	385.1	389.2	391.5	393.7	396.0	398.3
137.5°	382.7	388.0	393.4	396.9	398.6	400.4	402.1	403.8
140°	388.6	393.4	398.3	401.6	403.5	405.3	407.2	409.0
142.5°	394.9	399.1	403.4	406.2	407.7	409.2	410.7	412.3
145°	404.8	407.0	409.2	411.1	412.7	414.3	415.9	417.4
147.5°	413.8	414.1	414.5	415.2	416.5	417.7	418.9	420.1
150°	421.3	421.3	421.3	421.3	421.4	421.5	421.5	421.6
152.5°	428.3	428.4	428.6	428.6	428.5	428.5	428.5	428.4
155°	437.8	438.1	438.4	438.5	438.2	438.0	437.8	437.5
157.5°	446.0	446.4	446.8	446.8	446.4	446.0	445.6	445.2
160°	451.2	451.7	452.1	452.1	451.7	451.2	450.7	450.2
162.5°	455.4	455.9	456.4	456.3	455.8	455.3	454.7	454.2
165°	461.4	462.0	462.7	462.6	461.9	461.2	460.5	459.8
167.5°	465.8	466.5	467.1	467.1	466.3	465.5	464.7	464.0
170°	468.5	469.1	469.7	469.6	468.9	468.1	467.3	466.5
172.5°	470.2	470.8	471.4	471.3	470.5	469.6	468.8	467.9
175°	472.2	472.9	473.6	473.5	472.5	471.6	470.6	469.7
177.5°	473.0	473.5	474.0	473.8	473.1	472.3	471.6	470.8
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5

(END OF REPORT)