

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332685

Luminaire Tested: **SA4XXDIP-C1195D590U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332685
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7475.2 lumens
Efficiency: N/A
Efficacy: 135.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332685
CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332685

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68				
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	65	63	62	58				
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48				
3	85	75	67	61	80	71	64	59	64	58	54	57	52	49	50	47	44	41				
4	78	66	58	52	73	63	56	50	56	51	46	51	46	42	45	41	38	35				
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	36	33	30				
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27				
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24				
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21				
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19				
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332685

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	2.5
10°-20°	528.8	7.1
20°-30°	778.3	10.4
30°-40°	904.8	12.1
40°-50°	904.8	12.1
50°-60°	791.5	10.6
60°-70°	587.8	7.9
70°-80°	333.9	4.5
80°-90°	98.6	1.3
90°-100°	26.1	0.3
100°-110°	166.3	2.2
110°-120°	318.2	4.3
120°-130°	403.9	5.4
130°-140°	432.1	5.8
140°-150°	404.1	5.4
150°-160°	325.9	4.4
160°-170°	210.2	2.8
170°-180°	72.4	1.0
0°-30°	1494.7	20.0
0°-40°	2399.5	32.1
0°-60°	4095.8	54.8
0°-90°	5116.1	68.4
90°-120°	510.6	6.8
90°-150°	1750.6	23.4
90°-180°	2359.0	31.6
0°-180°	7475.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	2	8	12	16	17	6
95°	31	13	12	16	16	40
105°	172	175	178	182	163	180
115°	321	322	322	323	323	315
125°	451	453	452	453	454	402
135°	559	559	561	562	563	431
145°	645	646	646	647	648	403
155°	707	707	706	708	706	326
165°	746	743	743	747	742	211
175°	763	759	760	764	758	73
180°	763	763	763	763	763	



TEST NUMBER: P332685

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.6	33.6	33.5	33.5	33.5	33.5	33.4	33.3	33.2	33.2	33.3
90°	1.7	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3
92.5°	7.2	7.3	7.3	7.4	7.5	8.0	9.1	10.1	11.1	12.1	12.9
95°	31.4	27.1	22.8	18.4	14.1	12.0	12.2	12.3	12.4	12.5	13.3
97.5°	66.6	69.3	72.0	74.7	77.4	71.6	57.5	43.4	29.2	15.1	15.1
100°	93.5	95.8	98.1	100.4	102.7	95.1	77.6	60.1	42.6	25.1	22.9
102.5°	123.7	125.3	127.0	128.7	130.4	130.1	127.8	125.5	123.2	120.9	97.7
105°	171.7	172.5	173.2	174.0	174.7	175.4	176.1	176.7	177.3	178.0	179.1
107.5°	216.3	216.7	217.1	217.4	217.8	218.4	219.3	220.2	221.0	221.9	222.5
110°	246.4	246.8	247.2	247.6	247.9	248.5	249.3	250.0	250.8	251.6	251.8



TEST NUMBER: P332685

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.6	276.3	277.0	277.7	278.4	278.9	279.2	279.6	280.0	280.3	280.3
115°	320.6	321.0	321.3	321.7	322.1	322.2	322.1	322.0	321.8	321.7	322.0
117.5°	361.1	361.6	362.1	362.6	363.1	363.5	363.8	364.1	364.3	364.6	364.6
120°	388.5	389.0	389.5	390.0	390.5	390.7	390.6	390.4	390.3	390.2	390.4
122.5°	414.0	414.3	414.6	414.9	415.2	415.5	415.7	415.8	416.0	416.2	416.3
125°	450.6	451.1	451.7	452.2	452.7	452.8	452.5	452.3	452.0	451.8	452.2
127.5°	485.3	485.4	485.6	485.7	485.8	486.2	486.8	487.3	487.9	488.5	488.4
130°	507.7	507.8	507.9	508.1	508.2	508.4	508.8	509.2	509.6	510.0	510.1
132.5°	528.2	528.4	528.7	528.9	529.1	529.5	530.0	530.4	530.9	531.4	531.5
135°	559.0	558.9	558.8	558.6	558.5	558.7	559.2	559.7	560.2	560.7	561.0
137.5°	586.3	586.3	586.4	586.4	586.5	586.8	587.3	587.9	588.5	589.0	589.3
140°	604.1	604.3	604.6	604.8	605.1	605.3	605.6	605.9	606.1	606.4	606.7
142.5°	620.1	620.5	621.0	621.4	621.9	622.2	622.3	622.5	622.6	622.8	623.1
145°	644.6	645.0	645.3	645.7	646.1	646.3	646.3	646.3	646.3	646.3	646.4
147.5°	664.1	664.8	665.5	666.2	666.9	667.2	667.1	667.0	666.8	666.7	666.8
150°	678.2	678.7	679.3	679.8	680.3	680.5	680.3	680.2	680.1	679.9	679.9
152.5°	690.1	690.5	690.9	691.3	691.7	691.8	691.6	691.4	691.1	690.9	691.1
155°	706.8	706.9	707.0	707.1	707.3	707.1	706.8	706.4	706.0	705.6	706.1
157.5°	720.8	720.7	720.6	720.6	720.5	720.2	719.8	719.4	718.9	718.5	719.2
160°	729.0	728.6	728.2	727.9	727.5	727.2	727.1	727.0	726.8	726.7	727.5
162.5°	736.3	735.8	735.3	734.9	734.4	734.1	733.9	733.8	733.7	733.6	734.3
165°	745.5	744.9	744.3	743.6	743.0	742.7	742.7	742.7	742.7	742.7	743.7
167.5°	752.8	752.2	751.5	750.9	750.2	749.8	749.8	749.7	749.6	749.5	750.7
170°	757.0	756.2	755.4	754.7	753.9	753.6	753.7	753.8	754.0	754.1	755.1
172.5°	759.7	758.9	758.2	757.4	756.7	756.3	756.5	756.6	756.7	756.8	757.9
175°	762.7	761.9	761.1	760.4	759.6	759.3	759.4	759.6	759.7	759.8	760.9
177.5°	764.0	763.3	762.6	761.9	761.2	760.9	761.1	761.3	761.5	761.7	762.6
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332685

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	33.5	33.6	33.8	33.9	33.9	34.0	34.0	34.1
90°	14.1	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	13.6	14.4	15.1	15.5	15.6	15.6	15.7	15.7
95°	14.1	14.8	15.6	16.0	16.2	16.3	16.4	16.5
97.5°	15.2	15.3	15.4	15.5	15.6	15.7	15.8	16.0
100°	20.8	18.6	16.5	15.5	15.6	15.7	15.8	16.0
102.5°	74.4	51.2	27.9	16.3	16.4	16.4	16.4	16.4
105°	180.3	181.4	182.5	180.8	176.3	171.7	167.1	162.6
107.5°	223.0	223.6	224.1	224.6	225.1	225.6	226.1	226.6
110°	252.1	252.3	252.6	252.9	253.3	253.6	254.0	254.4



TEST NUMBER: P332685

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	280.2	280.2	280.1	280.3	280.8	281.3	281.8	282.2
115°	322.2	322.5	322.7	322.9	322.9	322.9	322.9	322.9
117.5°	364.5	364.5	364.4	364.4	364.3	364.3	364.2	364.2
120°	390.7	390.9	391.2	391.2	390.9	390.7	390.4	390.2
122.5°	416.5	416.6	416.8	416.7	416.5	416.2	416.0	415.7
125°	452.5	452.9	453.3	453.6	453.7	453.8	453.9	454.1
127.5°	488.4	488.3	488.2	488.1	488.0	487.9	487.8	487.7
130°	510.2	510.3	510.5	510.5	510.5	510.5	510.5	510.5
132.5°	531.7	531.8	531.9	531.9	531.8	531.7	531.6	531.5
135°	561.2	561.5	561.7	562.0	562.2	562.5	562.8	563.0
137.5°	589.6	589.9	590.1	590.2	590.2	590.1	590.0	589.9
140°	607.1	607.5	607.9	608.1	608.3	608.4	608.5	608.6
142.5°	623.3	623.6	623.9	624.1	624.1	624.1	624.1	624.2
145°	646.5	646.7	646.8	647.0	647.2	647.5	647.8	648.0
147.5°	666.9	667.0	667.1	667.2	667.4	667.5	667.6	667.7
150°	679.9	679.9	679.9	680.0	680.1	680.3	680.4	680.5
152.5°	691.3	691.5	691.7	691.8	691.7	691.6	691.5	691.5
155°	706.6	707.1	707.6	707.7	707.3	706.9	706.6	706.2
157.5°	719.8	720.5	721.1	721.1	720.5	719.8	719.2	718.5
160°	728.2	729.0	729.8	729.8	729.0	728.2	727.5	726.7
162.5°	735.1	735.8	736.6	736.6	735.7	734.8	734.0	733.1
165°	744.7	745.7	746.8	746.7	745.5	744.4	743.3	742.1
167.5°	751.8	752.9	754.0	753.9	752.7	751.4	750.1	748.9
170°	756.1	757.1	758.2	758.0	756.8	755.5	754.2	753.0
172.5°	758.9	759.9	760.9	760.7	759.4	758.0	756.6	755.2
175°	762.1	763.2	764.4	764.2	762.7	761.1	759.6	758.1
177.5°	763.4	764.2	765.0	764.8	763.6	762.4	761.1	759.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7

(END OF REPORT)