

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332912-940

Luminaire Tested: **SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332912-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4676.9 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332912-940

CATALOG NUMBER: SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332912-940

CATALOG NUMBER: SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				38
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	41	39	37	32				32
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				28
4	74	63	56	50	68	58	52	47	49	44	40	40	37	34	32	30	28	24				24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21				21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				18
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19	16				16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	15				15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13				13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P332912-940

CATALOG NUMBER: SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	1.8
10°-20°	237.4	5.1
20°-30°	342.8	7.3
30°-40°	388.6	8.3
40°-50°	375.2	8.0
50°-60°	312.0	6.7
60°-70°	215.4	4.6
70°-80°	109.2	2.3
80°-90°	30.0	0.6
90°-100°	256.3	5.5
100°-110°	533.5	11.4
110°-120°	477.9	10.2
120°-130°	402.0	8.6
130°-140°	335.1	7.2
140°-150°	256.1	5.5
150°-160°	180.0	3.8
160°-170°	105.9	2.3
170°-180°	34.4	0.7
0°-30°	665.3	14.2
0°-40°	1053.9	22.5
0°-60°	1741.1	37.2
0°-90°	2095.7	44.8
90°-120°	1267.7	27.1
90°-150°	2260.9	48.3
90°-180°	2581.0	55.2
0°-180°	4676.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	1	6	13	14	15	3
95°	23	72	568	281	170	26
105°	82	118	457	985	981	87
115°	144	180	408	784	942	142
125°	200	238	406	667	752	178
135°	238	283	402	592	672	184
145°	274	314	400	499	549	172
155°	312	336	389	441	460	144
165°	340	350	373	395	401	96
175°	354	355	358	363	361	34
180°	355	355	355	355	355	



TEST NUMBER: P332912-940

CATALOG NUMBER: SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	12.9	12.2	11.6	10.8	9.9	9.4	10.1	10.0	10.2	10.3	10.0
90°	0.7	2.1	4.2	4.9	5.6	5.6	9.7	9.7	11.1	12.6	11.9
92.5°	7.9	11.6	18.1	26.7	36.8	51.3	86.8	140.8	193.6	221.1	184.2
95°	23.0	25.1	32.1	41.1	57.9	87.1	147.8	262.2	428.8	568.3	584.3
97.5°	41.3	41.3	47.3	55.6	70.0	94.5	141.2	235.7	401.4	598.5	734.1
100°	53.0	53.0	57.9	66.3	79.5	101.8	142.9	221.8	364.0	560.6	739.0
102.5°	64.1	65.3	69.6	77.4	90.1	111.3	148.5	217.8	338.9	513.2	697.2
105°	81.6	83.6	87.1	95.5	108.1	128.3	161.8	219.6	317.3	457.4	621.3
107.5°	100.9	102.2	105.7	114.6	126.6	146.6	177.3	230.0	313.3	426.1	559.9
110°	113.7	115.0	118.5	126.9	139.5	158.3	189.0	237.7	314.4	415.5	529.2



TEST NUMBER: P332912-940

CATALOG NUMBER: SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.9	127.3	131.3	139.2	151.7	170.6	200.1	246.1	317.8	410.5	511.9
115°	143.7	145.7	150.6	157.6	170.9	189.7	217.6	259.4	324.2	407.9	495.7
117.5°	162.0	164.0	168.4	176.0	188.4	207.9	234.4	272.9	331.1	407.2	488.5
120°	174.3	175.7	180.6	188.2	200.1	219.6	246.1	282.4	336.1	407.2	484.6
122.5°	185.5	186.9	191.7	198.9	211.8	230.8	257.3	291.3	341.1	406.6	480.1
125°	200.1	202.9	207.1	214.7	228.0	247.5	272.6	304.7	348.7	405.8	472.7
127.5°	213.1	215.3	220.3	229.1	242.9	262.6	286.9	316.3	354.6	404.3	462.8
130°	220.3	223.1	228.7	239.2	252.4	272.6	296.3	323.5	359.1	403.7	456.7
132.5°	227.6	229.8	237.1	247.0	261.4	280.4	304.2	330.7	363.0	403.1	451.1
135°	237.7	240.6	247.5	259.4	274.0	292.1	315.1	340.3	368.8	402.3	442.7
137.5°	248.0	250.6	258.2	269.6	284.7	302.0	323.5	347.0	372.3	402.2	435.5
140°	255.2	257.3	264.9	276.8	291.4	308.2	329.1	351.4	375.1	401.6	431.6
142.5°	263.0	265.1	272.2	283.5	297.6	313.8	334.1	354.7	377.4	401.6	428.3
145°	274.0	276.1	283.1	292.8	306.1	321.5	339.6	358.4	378.6	400.2	422.5
147.5°	286.4	287.1	293.3	303.3	314.3	328.1	345.2	361.6	379.3	397.7	417.4
150°	294.3	295.0	300.5	308.9	319.3	332.6	347.9	363.3	379.3	396.0	413.5
152.5°	301.5	301.7	307.2	315.0	324.4	336.5	350.2	364.4	378.2	393.2	409.0
155°	311.7	312.4	316.6	323.5	331.2	341.6	353.5	365.3	376.5	389.1	402.3
157.5°	321.6	321.6	325.5	330.9	337.6	345.8	355.9	365.3	374.7	384.8	395.5
160°	327.7	327.7	330.5	335.4	341.0	348.7	357.0	365.3	373.0	381.4	390.5
162.5°	333.3	332.7	334.9	339.3	344.3	350.3	358.1	365.3	371.4	378.1	386.0
165°	339.6	339.6	341.0	344.5	347.9	352.1	358.4	364.0	368.2	373.0	378.6
167.5°	345.8	345.2	345.8	348.5	350.4	353.7	358.3	362.3	364.8	368.0	371.9
170°	348.7	347.9	348.7	350.7	352.1	354.2	357.7	361.1	362.6	364.6	367.5
172.5°	351.4	350.7	350.9	352.4	353.2	354.7	357.1	360.1	360.3	361.3	363.6
175°	354.2	353.5	353.5	354.2	354.9	354.9	356.3	358.4	357.7	357.7	359.1
177.5°	355.4	354.9	354.4	354.9	354.9	354.9	355.4	356.6	355.4	355.4	356.0
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332912-940

CATALOG NUMBER: SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	10.1	10.1	10.1	10.1	10.3	10.6	10.6	10.7
90°	12.6	13.3	13.9	13.9	14.6	15.3	14.6	14.6
92.5°	137.0	103.1	82.0	68.0	59.8	56.1	53.7	53.7
95°	516.7	408.6	315.1	247.5	213.4	191.7	179.2	170.1
97.5°	763.3	723.2	655.0	582.2	532.2	490.2	469.2	454.8
100°	840.9	854.8	820.6	769.1	708.4	665.8	645.0	639.4
102.5°	837.0	906.2	916.1	894.6	857.4	826.5	804.5	800.0
105°	781.0	901.5	970.5	999.2	1000.6	995.0	985.3	981.1
107.5°	701.3	829.7	926.9	989.1	1023.6	1039.5	1046.4	1048.2
110°	653.4	773.9	875.0	951.7	1001.2	1030.6	1043.1	1049.4



TEST NUMBER: P332912-940

CATALOG NUMBER: SA4XXRDIP-C575D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	618.2	724.9	820.4	897.1	953.2	988.7	1006.3	1016.5
115°	582.9	668.7	750.2	817.2	872.3	914.1	936.4	942.0
117.5°	565.6	636.6	700.7	757.5	804.5	839.6	862.2	866.6
120°	557.8	622.7	678.4	727.9	767.7	798.3	816.5	824.1
122.5°	551.1	613.7	664.5	707.8	741.5	767.7	783.0	790.7
125°	539.7	599.7	647.7	686.1	714.0	734.2	747.4	751.6
127.5°	525.8	583.0	631.0	667.4	695.4	713.5	724.6	728.8
130°	514.6	569.6	617.1	654.0	682.6	700.1	711.2	715.4
132.5°	502.8	554.6	600.9	637.8	665.8	685.5	696.2	700.3
135°	486.7	532.0	574.5	609.4	637.3	656.8	668.0	672.2
137.5°	472.1	510.4	546.3	577.7	603.8	623.0	632.2	637.3
140°	463.7	496.4	527.8	557.1	581.5	596.8	606.6	612.2
142.5°	455.8	484.7	511.7	537.0	558.7	572.8	581.5	585.4
145°	444.9	468.6	489.5	509.0	526.5	538.2	545.3	548.8
147.5°	435.8	454.6	471.4	486.7	499.5	509.7	515.0	516.2
150°	430.2	446.2	460.2	472.7	483.9	492.9	497.1	497.8
152.5°	424.1	437.8	450.7	461.0	470.5	477.9	480.4	481.1
155°	414.8	426.1	436.5	444.9	451.8	457.4	459.5	459.5
157.5°	404.9	414.3	423.1	429.8	435.1	439.3	440.5	440.5
160°	398.9	406.5	414.2	419.7	423.9	428.1	428.8	428.8
162.5°	392.7	399.2	405.3	410.3	413.3	417.5	418.2	417.7
165°	384.1	388.3	393.2	396.7	399.5	402.3	401.6	400.9
167.5°	375.9	379.2	383.1	385.1	386.6	388.3	388.3	387.6
170°	371.0	373.0	375.9	377.9	379.3	380.0	379.3	379.3
172.5°	366.5	368.0	369.7	371.2	372.0	372.7	372.0	371.0
175°	360.5	361.1	362.6	362.6	362.6	364.0	362.6	361.1
177.5°	356.6	357.1	357.1	357.7	357.1	357.7	356.6	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9

(END OF REPORT)