

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332686

Luminaire Tested: **SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332686
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7162.1 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332686
CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332686

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71	71	71	71	
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	60	60	60	60	
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50	50	50	50	
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43	43	43	43	
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37	37	37	37	
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32	32	32	32	
6	66	54	45	39	62	51	43	38	47	40	35	42	37	33	38	34	30	28	28	28	28	
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	30	27	25	25	25	25	
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22	22	22	22	
9	53	41	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20	20	20	20	
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18	18	18	18	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332686

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	2.6
10°-20°	528.8	7.4
20°-30°	778.3	10.9
30°-40°	904.8	12.6
40°-50°	904.8	12.6
50°-60°	791.5	11.1
60°-70°	587.8	8.2
70°-80°	333.9	4.7
80°-90°	98.6	1.4
90°-100°	48.6	0.7
100°-110°	144.1	2.0
110°-120°	244.6	3.4
120°-130°	322.5	4.5
130°-140°	362.2	5.1
140°-150°	355.9	5.0
150°-160°	299.3	4.2
160°-170°	199.1	2.8
170°-180°	69.7	1.0
0°-30°	1494.7	20.9
0°-40°	2399.5	33.5
0°-60°	4095.8	57.2
0°-90°	5116.1	71.4
90°-120°	437.3	6.1
90°-150°	1477.8	20.6
90°-180°	2046.0	28.6
0°-180°	7162.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	2	8	12	16	17	7
95°	34	39	43	45	45	38
105°	133	134	136	137	139	141
115°	249	249	248	247	246	245
125°	362	362	362	360	359	323
135°	467	470	470	469	468	361
145°	568	570	570	570	568	355
155°	650	650	650	652	650	299
165°	708	706	705	708	706	199
175°	736	734	733	736	733	70
180°	738	738	738	738	738	



TEST NUMBER: P332686

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.6	33.6	33.5	33.5	33.5	33.5	33.4	33.3	33.2	33.2	33.3
90°	1.7	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3
92.5°	12.2	13.8	15.4	17.0	18.6	19.7	20.5	21.2	21.9	22.6	23.0
95°	34.2	35.4	36.5	37.6	38.8	39.8	40.7	41.6	42.5	43.3	43.7
97.5°	59.8	60.7	61.6	62.5	63.4	64.4	65.4	66.5	67.5	68.6	69.0
100°	79.8	80.4	80.9	81.4	81.9	82.7	83.8	85.0	86.1	87.3	87.5
102.5°	100.8	101.0	101.2	101.4	101.6	102.3	103.3	104.3	105.4	106.4	106.8
105°	132.9	133.0	133.1	133.3	133.4	133.7	134.2	134.7	135.2	135.7	136.1
107.5°	166.5	166.7	166.8	167.0	167.2	167.3	167.3	167.4	167.5	167.6	167.9
110°	189.4	189.6	189.9	190.1	190.4	190.4	190.3	190.2	190.1	189.9	189.7



TEST NUMBER: P332686

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.1	213.1	213.2	213.2	213.3	213.2	213.0	212.7	212.5	212.3	212.2
115°	248.7	248.7	248.7	248.7	248.7	248.5	248.3	248.0	247.8	247.5	247.4
117.5°	282.2	282.3	282.4	282.5	282.6	282.6	282.4	282.2	282.0	281.9	281.4
120°	304.6	305.1	305.6	306.1	306.6	306.7	306.3	305.9	305.5	305.1	304.5
122.5°	327.8	328.0	328.2	328.4	328.6	328.7	328.5	328.3	328.1	328.0	327.5
125°	362.2	362.2	362.2	362.2	362.2	362.1	362.0	361.9	361.7	361.6	361.3
127.5°	393.3	393.7	394.1	394.5	394.8	394.9	394.7	394.5	394.3	394.1	393.9
130°	415.2	415.6	416.0	416.4	416.7	416.9	416.9	416.9	416.9	416.9	416.7
132.5°	437.6	437.9	438.1	438.4	438.7	438.8	438.7	438.6	438.5	438.4	438.1
135°	467.1	467.9	468.6	469.4	470.2	470.5	470.5	470.5	470.5	470.5	470.3
137.5°	499.3	499.6	500.0	500.3	500.7	501.0	501.2	501.4	501.6	501.8	501.5
140°	520.7	521.0	521.2	521.5	521.7	521.9	521.9	521.9	521.9	521.9	521.7
142.5°	540.3	540.6	540.9	541.1	541.4	541.4	541.3	541.2	541.1	541.0	541.0
145°	567.5	568.0	568.5	569.0	569.5	569.8	570.0	570.1	570.2	570.3	570.2
147.5°	594.4	595.0	595.6	596.2	596.9	597.1	597.0	596.9	596.8	596.7	596.6
150°	610.8	611.4	611.9	612.4	612.9	613.1	613.1	613.1	613.1	613.1	613.1
152.5°	626.4	626.7	627.0	627.3	627.6	627.8	627.9	628.0	628.1	628.2	628.5
155°	650.2	650.2	650.2	650.2	650.2	650.1	650.0	649.9	649.8	649.6	650.1
157.5°	670.3	670.0	669.8	669.6	669.4	669.2	669.2	669.2	669.2	669.1	669.5
160°	682.1	682.0	681.9	681.8	681.6	681.5	681.4	681.3	681.1	681.0	681.4
162.5°	693.1	692.8	692.4	692.1	691.8	691.5	691.4	691.3	691.2	691.0	691.7
165°	707.8	707.4	707.0	706.7	706.3	706.0	705.7	705.5	705.2	705.0	705.7
167.5°	719.1	718.6	718.0	717.5	717.0	716.7	716.7	716.8	716.8	716.8	717.6
170°	725.5	724.9	724.2	723.6	722.9	722.7	722.8	722.9	723.1	723.2	724.0
172.5°	730.0	729.5	729.0	728.5	727.9	727.7	727.7	727.7	727.7	727.8	728.6
175°	736.3	735.7	735.1	734.4	733.8	733.4	733.3	733.2	733.0	732.9	733.8
177.5°	738.4	737.9	737.4	736.9	736.3	736.1	736.1	736.1	736.1	736.1	736.8
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332686

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	33.5	33.6	33.8	33.9	33.9	34.0	34.0	34.1
90°	14.1	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	23.5	24.0	24.4	24.7	24.9	25.0	25.2	25.3
95°	44.1	44.5	44.9	45.1	45.1	45.1	45.1	45.1
97.5°	69.5	69.9	70.4	70.6	70.6	70.6	70.6	70.6
100°	87.8	88.0	88.3	88.4	88.4	88.4	88.4	88.4
102.5°	107.1	107.5	107.8	108.1	108.2	108.3	108.4	108.5
105°	136.5	136.9	137.3	137.6	138.0	138.4	138.8	139.2
107.5°	168.3	168.6	169.0	169.2	169.1	169.1	169.1	169.1
110°	189.4	189.2	188.9	189.0	189.4	189.7	190.1	190.5



TEST NUMBER: P332686

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.2	212.1	212.1	212.1	212.2	212.2	212.3	212.4
115°	247.3	247.2	247.0	246.9	246.8	246.6	246.5	246.4
117.5°	281.0	280.6	280.1	279.8	279.5	279.3	279.0	278.8
120°	303.9	303.2	302.6	302.4	302.7	302.9	303.2	303.4
122.5°	327.1	326.7	326.2	325.8	325.3	324.9	324.4	324.0
125°	361.1	360.8	360.6	360.3	360.1	359.8	359.6	359.3
127.5°	393.6	393.4	393.1	392.9	392.7	392.5	392.3	392.1
130°	416.4	416.2	415.9	415.5	415.0	414.5	414.0	413.5
132.5°	437.9	437.6	437.4	437.1	436.9	436.7	436.5	436.3
135°	470.0	469.8	469.5	469.2	468.8	468.4	468.1	467.7
137.5°	501.1	500.8	500.5	500.3	500.4	500.5	500.6	500.7
140°	521.6	521.5	521.4	521.2	521.1	521.0	520.9	520.7
142.5°	541.0	541.0	540.9	540.9	540.9	540.9	540.8	540.8
145°	570.1	570.0	569.8	569.6	569.2	568.8	568.4	568.1
147.5°	596.5	596.4	596.3	596.2	596.1	595.9	595.8	595.7
150°	613.1	613.1	613.1	613.1	612.9	612.8	612.7	612.6
152.5°	628.8	629.1	629.4	629.4	629.1	628.7	628.4	628.1
155°	650.6	651.1	651.7	651.7	651.1	650.6	650.1	649.6
157.5°	669.9	670.3	670.7	670.6	670.2	669.8	669.3	668.9
160°	681.8	682.1	682.5	682.4	681.8	681.1	680.5	679.9
162.5°	692.4	693.1	693.8	693.8	693.2	692.5	691.9	691.3
165°	706.5	707.2	708.0	708.1	707.6	707.1	706.6	706.1
167.5°	718.3	719.1	719.9	719.8	719.1	718.3	717.5	716.7
170°	724.7	725.5	726.2	726.2	725.3	724.4	723.5	722.6
172.5°	729.5	730.4	731.2	731.2	730.3	729.4	728.5	727.7
175°	734.7	735.6	736.4	736.4	735.6	734.7	733.8	732.9
177.5°	737.5	738.2	738.9	738.9	738.1	737.3	736.4	735.6
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5

(END OF REPORT)