

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332934-940

Luminaire Tested: **SA4XXRDIP-C795D590U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332934-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D590U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4967.6 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332934-940

CATALOG NUMBER: SA4XXRDIP-C795D590U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332934-940

CATALOG NUMBER: SA4XXRDIP-C795D590U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58																												
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49																												
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42																												
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	36																												
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34	31																												
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27																												
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	27	24																												
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21																												
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21	19																												
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17																												
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P332934-940

CATALOG NUMBER: SA4XXRDIP-C795D590U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.4	2.3
10°-20°	324.5	6.5
20°-30°	468.6	9.4
30°-40°	531.1	10.7
40°-50°	512.9	10.3
50°-60°	426.5	8.6
60°-70°	294.5	5.9
70°-80°	149.3	3.0
80°-90°	40.3	0.8
90°-100°	23.3	0.5
100°-110°	148.3	3.0
110°-120°	283.7	5.7
120°-130°	360.1	7.2
130°-140°	385.3	7.8
140°-150°	360.3	7.3
150°-160°	290.6	5.8
160°-170°	187.4	3.8
170°-180°	64.6	1.3
0°-30°	909.4	18.3
0°-40°	1440.5	29.0
0°-60°	2379.9	47.9
0°-90°	2863.9	57.7
90°-120°	455.3	9.2
90°-150°	1561.1	31.4
90°-180°	2104.0	42.4
0°-180°	4967.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	2	7	11	14	15	4
95°	28	12	11	14	15	36
105°	153	156	159	162	145	160
115°	286	287	287	288	288	281
125°	402	404	403	404	405	359
135°	498	498	500	501	502	384
145°	575	576	576	577	578	359
155°	630	631	629	631	630	290
165°	665	662	662	666	662	188
175°	680	677	678	682	676	65
180°	680	680	680	680	680	



TEST NUMBER: P332934-940

CATALOG NUMBER: SA4XXRDIP-C795D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	17.7	16.7	15.5	14.4	13.4	12.8	12.8	12.8	12.8	12.8	12.8
90°	1.5	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9
92.5°	6.4	6.5	6.5	6.6	6.7	7.1	8.1	9.0	9.9	10.8	11.5
95°	28.0	24.2	20.3	16.4	12.6	10.7	10.9	11.0	11.1	11.1	11.9
97.5°	59.4	61.8	64.2	66.6	69.0	63.8	51.3	38.7	26.0	13.5	13.5
100°	83.4	85.4	87.5	89.5	91.6	84.8	69.2	53.6	38.0	22.4	20.4
102.5°	110.3	111.7	113.2	114.8	116.3	116.0	114.0	111.9	109.9	107.8	87.1
105°	153.1	153.8	154.4	155.2	155.8	156.4	157.0	157.6	158.1	158.7	159.7
107.5°	192.9	193.2	193.6	193.9	194.2	194.7	195.6	196.4	197.1	197.9	198.4
110°	219.7	220.1	220.4	220.8	221.1	221.6	222.3	222.9	223.6	224.4	224.5



TEST NUMBER: P332934-940

CATALOG NUMBER: SA4XXRDIP-C795D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.8	246.4	247.0	247.6	248.3	248.7	249.0	249.3	249.7	249.9	249.9
115°	285.9	286.2	286.5	286.9	287.2	287.3	287.2	287.1	287.0	286.9	287.1
117.5°	322.0	322.4	322.9	323.3	323.8	324.1	324.4	324.7	324.9	325.1	325.1
120°	346.4	346.9	347.3	347.8	348.2	348.4	348.3	348.1	348.0	347.9	348.1
122.5°	369.2	369.4	369.7	370.0	370.2	370.5	370.7	370.8	371.0	371.1	371.2
125°	401.8	402.3	402.8	403.2	403.7	403.8	403.5	403.3	403.1	402.9	403.2
127.5°	432.7	432.8	433.0	433.1	433.2	433.5	434.1	434.5	435.1	435.6	435.5
130°	452.7	452.8	452.9	453.1	453.2	453.3	453.7	454.1	454.4	454.8	454.9
132.5°	471.0	471.2	471.4	471.6	471.8	472.2	472.6	473.0	473.4	473.9	473.9
135°	498.5	498.4	498.3	498.1	498.0	498.2	498.6	499.1	499.5	500.0	500.2
137.5°	522.8	522.8	522.9	522.9	523.0	523.3	523.7	524.2	524.8	525.2	525.5
140°	538.7	538.9	539.1	539.3	539.6	539.8	540.0	540.3	540.5	540.7	541.0
142.5°	552.9	553.3	553.8	554.1	554.6	554.8	554.9	555.1	555.2	555.4	555.6
145°	574.8	575.2	575.4	575.8	576.1	576.3	576.3	576.3	576.3	576.3	576.4
147.5°	592.2	592.8	593.4	594.1	594.7	594.9	594.9	594.8	594.6	594.5	594.6
150°	604.8	605.2	605.7	606.2	606.6	606.8	606.6	606.5	606.5	606.3	606.3
152.5°	615.4	615.7	616.1	616.4	616.8	616.9	616.7	616.5	616.3	616.1	616.3
155°	630.3	630.4	630.4	630.5	630.7	630.5	630.3	629.9	629.5	629.2	629.6
157.5°	642.7	642.7	642.6	642.6	642.5	642.2	641.9	641.5	641.1	640.7	641.3
160°	650.1	649.7	649.3	649.1	648.7	648.5	648.4	648.3	648.1	648.0	648.7
162.5°	656.6	656.1	655.7	655.3	654.9	654.6	654.4	654.3	654.2	654.2	654.8
165°	664.8	664.2	663.7	663.1	662.5	662.3	662.3	662.3	662.3	662.3	663.2
167.5°	671.3	670.7	670.1	669.6	669.0	668.6	668.6	668.5	668.4	668.3	669.4
170°	675.0	674.3	673.6	673.0	672.3	672.0	672.1	672.2	672.3	672.4	673.3
172.5°	677.4	676.7	676.1	675.4	674.8	674.4	674.6	674.7	674.8	674.8	675.8
175°	680.1	679.4	678.7	678.1	677.3	677.1	677.2	677.3	677.4	677.5	678.5
177.5°	681.3	680.6	680.0	679.4	678.8	678.5	678.7	678.9	679.0	679.2	680.0
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332934-940

CATALOG NUMBER: SA4XXRDIP-C795D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	12.8	12.8	12.8	12.8	13.0	13.3	13.5	13.6
90°	12.6	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	12.1	12.8	13.5	13.8	13.9	13.9	14.0	14.0
95°	12.6	13.2	13.9	14.3	14.4	14.5	14.6	14.7
97.5°	13.6	13.6	13.7	13.8	13.9	14.0	14.1	14.3
100°	18.5	16.6	14.7	13.8	13.9	14.0	14.1	14.3
102.5°	66.3	45.7	24.9	14.5	14.6	14.6	14.6	14.6
105°	160.8	161.8	162.7	161.2	157.2	153.1	149.0	145.0
107.5°	198.9	199.4	199.8	200.3	200.7	201.2	201.6	202.1
110°	224.8	225.0	225.2	225.5	225.9	226.1	226.5	226.9



TEST NUMBER: P332934-940

CATALOG NUMBER: SA4XXRDIP-C795D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	249.9	249.9	249.8	249.9	250.4	250.8	251.3	251.6
115°	287.3	287.6	287.8	287.9	287.9	287.9	287.9	287.9
117.5°	325.0	325.0	324.9	324.9	324.9	324.9	324.8	324.8
120°	348.4	348.6	348.8	348.8	348.6	348.4	348.1	347.9
122.5°	371.4	371.5	371.7	371.6	371.4	371.1	371.0	370.7
125°	403.5	403.9	404.2	404.5	404.6	404.7	404.7	404.9
127.5°	435.5	435.4	435.3	435.2	435.2	435.1	435.0	434.9
130°	455.0	455.0	455.2	455.2	455.2	455.2	455.2	455.2
132.5°	474.1	474.2	474.3	474.3	474.2	474.1	474.0	473.9
135°	500.4	500.7	500.9	501.1	501.3	501.6	501.9	502.0
137.5°	525.8	526.0	526.2	526.3	526.3	526.2	526.1	526.0
140°	541.4	541.7	542.1	542.2	542.4	542.5	542.6	542.7
142.5°	555.8	556.1	556.3	556.5	556.5	556.5	556.5	556.6
145°	576.5	576.7	576.8	576.9	577.1	577.4	577.7	577.8
147.5°	594.7	594.8	594.9	594.9	595.1	595.2	595.3	595.4
150°	606.3	606.3	606.3	606.4	606.5	606.6	606.7	606.8
152.5°	616.4	616.6	616.8	616.9	616.8	616.7	616.6	616.6
155°	630.1	630.5	631.0	631.1	630.7	630.4	630.1	629.7
157.5°	641.9	642.5	643.0	643.0	642.5	641.9	641.3	640.7
160°	649.3	650.1	650.8	650.8	650.1	649.3	648.7	648.0
162.5°	655.5	656.1	656.8	656.8	656.0	655.2	654.5	653.7
165°	664.1	664.9	665.9	665.8	664.8	663.8	662.8	661.7
167.5°	670.4	671.4	672.3	672.3	671.2	670.0	668.9	667.8
170°	674.2	675.1	676.1	675.9	674.8	673.7	672.5	671.5
172.5°	676.7	677.6	678.5	678.3	677.2	675.9	674.7	673.4
175°	679.6	680.6	681.6	681.4	680.1	678.7	677.3	676.0
177.5°	680.7	681.4	682.2	682.0	680.9	679.8	678.7	677.6
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1

(END OF REPORT)