

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332942-940

Luminaire Tested: **SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332942-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5445.1 lumens  
Efficiency: N/A  
Efficacy: 118.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332942-940

CATALOG NUMBER: SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332942-940

CATALOG NUMBER: SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	62	56	58	54	50	49	46	43	41	39	36	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	33	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P332942-940

CATALOG NUMBER: SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.4	2.1
10°-20°	324.5	6.0
20°-30°	468.6	8.6
30°-40°	531.1	9.8
40°-50°	512.9	9.4
50°-60°	426.5	7.8
60°-70°	294.5	5.4
70°-80°	149.3	2.7
80°-90°	40.3	0.7
90°-100°	256.3	4.7
100°-110°	533.5	9.8
110°-120°	477.9	8.8
120°-130°	402.0	7.4
130°-140°	335.1	6.2
140°-150°	256.1	4.7
150°-160°	180.0	3.3
160°-170°	105.9	1.9
170°-180°	34.4	0.6
0°-30°	909.4	16.7
0°-40°	1440.5	26.5
0°-60°	2379.9	43.7
0°-90°	2863.9	52.6
90°-120°	1267.7	23.3
90°-150°	2260.9	41.5
90°-180°	2581.0	47.4
0°-180°	5445.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	1	6	13	14	15	4
95°	23	72	568	281	170	26
105°	82	118	457	985	981	87
115°	144	180	408	784	942	142
125°	200	238	406	667	752	178
135°	238	283	402	592	672	184
145°	274	314	400	499	549	172
155°	312	336	389	441	460	144
165°	340	350	373	395	401	96
175°	354	355	358	363	361	34
180°	355	355	355	355	355	



TEST NUMBER: P332942-940

CATALOG NUMBER: SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	17.6	16.5	15.6	14.4	13.2	12.4	13.1	12.9	13.0	13.1	12.8
90°	0.7	2.1	4.2	4.9	5.6	5.6	9.7	9.7	11.1	12.6	11.9
92.5°	7.9	11.6	18.1	26.7	36.8	51.3	86.8	140.8	193.6	221.1	184.2
95°	23.0	25.1	32.1	41.1	57.9	87.1	147.8	262.2	428.8	568.3	584.3
97.5°	41.3	41.3	47.3	55.6	70.0	94.5	141.2	235.7	401.4	598.5	734.1
100°	53.0	53.0	57.9	66.3	79.5	101.8	142.9	221.8	364.0	560.6	739.0
102.5°	64.1	65.3	69.6	77.4	90.1	111.3	148.5	217.8	338.9	513.2	697.2
105°	81.6	83.6	87.1	95.5	108.1	128.3	161.8	219.6	317.3	457.4	621.3
107.5°	100.9	102.2	105.7	114.6	126.6	146.6	177.3	230.0	313.3	426.1	559.9
110°	113.7	115.0	118.5	126.9	139.5	158.3	189.0	237.7	314.4	415.5	529.2



TEST NUMBER: P332942-940

CATALOG NUMBER: SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.9	127.3	131.3	139.2	151.7	170.6	200.1	246.1	317.8	410.5	511.9
115°	143.7	145.7	150.6	157.6	170.9	189.7	217.6	259.4	324.2	407.9	495.7
117.5°	162.0	164.0	168.4	176.0	188.4	207.9	234.4	272.9	331.1	407.2	488.5
120°	174.3	175.7	180.6	188.2	200.1	219.6	246.1	282.4	336.1	407.2	484.6
122.5°	185.5	186.9	191.7	198.9	211.8	230.8	257.3	291.3	341.1	406.6	480.1
125°	200.1	202.9	207.1	214.7	228.0	247.5	272.6	304.7	348.7	405.8	472.7
127.5°	213.1	215.3	220.3	229.1	242.9	262.6	286.9	316.3	354.6	404.3	462.8
130°	220.3	223.1	228.7	239.2	252.4	272.6	296.3	323.5	359.1	403.7	456.7
132.5°	227.6	229.8	237.1	247.0	261.4	280.4	304.2	330.7	363.0	403.1	451.1
135°	237.7	240.6	247.5	259.4	274.0	292.1	315.1	340.3	368.8	402.3	442.7
137.5°	248.0	250.6	258.2	269.6	284.7	302.0	323.5	347.0	372.3	402.2	435.5
140°	255.2	257.3	264.9	276.8	291.4	308.2	329.1	351.4	375.1	401.6	431.6
142.5°	263.0	265.1	272.2	283.5	297.6	313.8	334.1	354.7	377.4	401.6	428.3
145°	274.0	276.1	283.1	292.8	306.1	321.5	339.6	358.4	378.6	400.2	422.5
147.5°	286.4	287.1	293.3	303.3	314.3	328.1	345.2	361.6	379.3	397.7	417.4
150°	294.3	295.0	300.5	308.9	319.3	332.6	347.9	363.3	379.3	396.0	413.5
152.5°	301.5	301.7	307.2	315.0	324.4	336.5	350.2	364.4	378.2	393.2	409.0
155°	311.7	312.4	316.6	323.5	331.2	341.6	353.5	365.3	376.5	389.1	402.3
157.5°	321.6	321.6	325.5	330.9	337.6	345.8	355.9	365.3	374.7	384.8	395.5
160°	327.7	327.7	330.5	335.4	341.0	348.7	357.0	365.3	373.0	381.4	390.5
162.5°	333.3	332.7	334.9	339.3	344.3	350.3	358.1	365.3	371.4	378.1	386.0
165°	339.6	339.6	341.0	344.5	347.9	352.1	358.4	364.0	368.2	373.0	378.6
167.5°	345.8	345.2	345.8	348.5	350.4	353.7	358.3	362.3	364.8	368.0	371.9
170°	348.7	347.9	348.7	350.7	352.1	354.2	357.7	361.1	362.6	364.6	367.5
172.5°	351.4	350.7	350.9	352.4	353.2	354.7	357.1	360.1	360.3	361.3	363.6
175°	354.2	353.5	353.5	354.2	354.9	354.9	356.3	358.4	357.7	357.7	359.1
177.5°	355.4	354.9	354.4	354.9	354.9	354.9	355.4	356.6	355.4	355.4	356.0
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332942-940

CATALOG NUMBER: SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	12.8	12.8	12.8	12.8	13.0	13.4	13.4	13.6
90°	12.6	13.3	13.9	13.9	14.6	15.3	14.6	14.6
92.5°	137.0	103.1	82.0	68.0	59.8	56.1	53.7	53.7
95°	516.7	408.6	315.1	247.5	213.4	191.7	179.2	170.1
97.5°	763.3	723.2	655.0	582.2	532.2	490.2	469.2	454.8
100°	840.9	854.8	820.6	769.1	708.4	665.8	645.0	639.4
102.5°	837.0	906.2	916.1	894.6	857.4	826.5	804.5	800.0
105°	781.0	901.5	970.5	999.2	1000.6	995.0	985.3	981.1
107.5°	701.3	829.7	926.9	989.1	1023.6	1039.5	1046.4	1048.2
110°	653.4	773.9	875.0	951.7	1001.2	1030.6	1043.1	1049.4





TEST NUMBER: P332942-940

CATALOG NUMBER: SA4XXRDIP-C795D810U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	618.2	724.9	820.4	897.1	953.2	988.7	1006.3	1016.5
115°	582.9	668.7	750.2	817.2	872.3	914.1	936.4	942.0
117.5°	565.6	636.6	700.7	757.5	804.5	839.6	862.2	866.6
120°	557.8	622.7	678.4	727.9	767.7	798.3	816.5	824.1
122.5°	551.1	613.7	664.5	707.8	741.5	767.7	783.0	790.7
125°	539.7	599.7	647.7	686.1	714.0	734.2	747.4	751.6
127.5°	525.8	583.0	631.0	667.4	695.4	713.5	724.6	728.8
130°	514.6	569.6	617.1	654.0	682.6	700.1	711.2	715.4
132.5°	502.8	554.6	600.9	637.8	665.8	685.5	696.2	700.3
135°	486.7	532.0	574.5	609.4	637.3	656.8	668.0	672.2
137.5°	472.1	510.4	546.3	577.7	603.8	623.0	632.2	637.3
140°	463.7	496.4	527.8	557.1	581.5	596.8	606.6	612.2
142.5°	455.8	484.7	511.7	537.0	558.7	572.8	581.5	585.4
145°	444.9	468.6	489.5	509.0	526.5	538.2	545.3	548.8
147.5°	435.8	454.6	471.4	486.7	499.5	509.7	515.0	516.2
150°	430.2	446.2	460.2	472.7	483.9	492.9	497.1	497.8
152.5°	424.1	437.8	450.7	461.0	470.5	477.9	480.4	481.1
155°	414.8	426.1	436.5	444.9	451.8	457.4	459.5	459.5
157.5°	404.9	414.3	423.1	429.8	435.1	439.3	440.5	440.5
160°	398.9	406.5	414.2	419.7	423.9	428.1	428.8	428.8
162.5°	392.7	399.2	405.3	410.3	413.3	417.5	418.2	417.7
165°	384.1	388.3	393.2	396.7	399.5	402.3	401.6	400.9
167.5°	375.9	379.2	383.1	385.1	386.6	388.3	388.3	387.6
170°	371.0	373.0	375.9	377.9	379.3	380.0	379.3	379.3
172.5°	366.5	368.0	369.7	371.2	372.0	372.7	372.0	371.0
175°	360.5	361.1	362.6	362.6	362.6	364.0	362.6	361.1
177.5°	356.6	357.1	357.1	357.7	357.1	357.7	356.6	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9

(END OF REPORT)