

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332515

Luminaire Tested: **SA4XXDIP-C350D810U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332515
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D810U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4323.4 lumens
Efficiency: N/A
Efficacy: 138.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332515
CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332515

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	29				
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25				
3	78	69	62	56	71	63	57	52	51	46	43	40	36	34	29	27	26	21				
4	72	61	53	47	64	56	49	44	45	40	36	35	32	29	26	24	22	18				
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16				
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11				
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10				
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4769	4769	4769
5°	4783	4725	4760
10°	4753	4687	4710
15°	4695	4621	4633
20°	4619	4538	4542
25°	4532	4444	4431
30°	4426	4333	4294
35°	4315	4217	4161
40°	4200	4086	4011
45°	4080	3956	3881
50°	3947	3841	3721
55°	3804	3690	3571
60°	3660	3523	3416
65°	3500	3364	3228
70°	3319	3151	3028
75°	3041	2895	2820
80°	2706	2599	2529
85°	2371	2279	2232



TEST NUMBER: P332515

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.3
10°-20°	156.7	3.6
20°-30°	230.7	5.3
30°-40°	268.2	6.2
40°-50°	268.2	6.2
50°-60°	234.6	5.4
60°-70°	174.2	4.0
70°-80°	99.0	2.3
80°-90°	31.6	0.7
90°-100°	66.7	1.5
100°-110°	197.5	4.6
110°-120°	335.2	7.8
120°-130°	442.0	10.2
130°-140°	496.4	11.5
140°-150°	487.8	11.3
150°-160°	410.3	9.5
160°-170°	273.0	6.3
170°-180°	95.6	2.2
0°-30°	443.1	10.2
0°-40°	711.3	16.5
0°-60°	1214.1	28.1
0°-90°	1518.9	35.1
90°-120°	599.4	13.9
90°-150°	2025.7	46.9
90°-180°	2805.0	64.9
0°-180°	4323.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	591	591	591	591	591	
5°	590	588	583	588	587	56
15°	562	560	553	555	554	158
25°	509	505	499	499	498	234
35°	438	434	428	425	422	274
45°	357	354	346	342	340	275
55°	270	269	262	257	254	242
65°	183	181	176	172	169	181
75°	98	95	93	91	90	104
85°	26	26	25	25	24	28
90°	2	11	17	22	24	4
95°	47	54	59	62	62	52
105°	182	183	186	188	191	193
115°	341	341	339	338	338	336
125°	496	496	496	494	492	442
135°	640	645	645	643	641	495
145°	778	781	782	781	779	487
155°	891	891	890	893	890	410
165°	970	968	966	971	968	273
175°	1009	1006	1005	1010	1005	96
180°	1011	1011	1011	1011	1011	



TEST NUMBER: P332515

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	592.2	592.0	591.7	591.5	591.2	590.6	589.7	588.8	587.9	586.9	587.8
5°	590.2	589.8	589.4	589.0	588.6	587.8	586.6	585.5	584.3	583.1	584.3
7.5°	584.8	584.3	583.9	583.5	583.1	582.2	580.9	579.7	578.4	577.1	578.0
10°	579.8	579.4	579.0	578.6	578.2	577.3	575.9	574.5	573.2	571.8	572.6
12.5°	573.4	573.0	572.6	572.1	571.7	570.8	569.3	567.9	566.4	565.0	565.9
15°	561.8	561.4	561.0	560.6	560.2	559.2	557.6	556.0	554.4	552.9	553.5
17.5°	547.9	547.4	546.9	546.4	545.8	544.8	543.3	541.8	540.3	538.8	539.2
20°	537.7	537.2	536.7	536.1	535.6	534.6	533.0	531.4	529.8	528.2	528.6
22.5°	526.7	526.0	525.3	524.6	523.9	522.8	521.2	519.7	518.1	516.5	517.1
25°	508.8	508.1	507.4	506.6	505.9	504.8	503.3	501.8	500.4	498.9	499.0
27.5°	488.4	487.6	486.9	486.1	485.4	484.3	482.9	481.6	480.2	478.8	478.6
30°	474.8	473.9	473.1	472.2	471.4	470.3	468.9	467.5	466.2	464.8	464.4
32.5°	460.4	459.6	458.8	458.1	457.3	456.2	454.8	453.3	451.9	450.4	449.9
35°	437.8	437.1	436.4	435.6	434.9	433.8	432.3	430.8	429.4	427.9	427.2
37.5°	414.1	413.4	412.7	412.1	411.4	410.3	408.7	407.1	405.5	403.9	403.1
40°	398.5	397.7	396.9	396.0	395.2	394.0	392.4	390.8	389.2	387.7	386.6
42.5°	381.9	381.4	380.9	380.4	379.9	378.7	377.0	375.2	373.5	371.8	370.5
45°	357.4	356.6	355.9	355.2	354.4	353.2	351.5	349.8	348.2	346.5	345.3
47.5°	331.7	331.2	330.7	330.2	329.7	328.7	327.1	325.5	324.0	322.4	321.1
50°	314.3	313.9	313.5	313.0	312.6	311.7	310.2	308.7	307.2	305.8	304.3
52.5°	297.3	296.7	296.2	295.7	295.2	294.2	292.6	291.1	289.5	288.0	286.7
55°	270.3	270.0	269.6	269.3	269.0	268.1	266.6	265.2	263.7	262.2	261.0
57.5°	244.5	244.2	243.8	243.5	243.1	242.2	240.7	239.3	237.8	236.4	235.2
60°	226.7	226.2	225.7	225.1	224.6	223.7	222.3	220.9	219.6	218.2	217.3
62.5°	209.3	208.9	208.4	208.0	207.5	206.6	205.1	203.7	202.2	200.8	199.9
65°	183.2	182.7	182.1	181.6	181.1	180.3	179.2	178.2	177.1	176.1	175.0
67.5°	156.9	156.4	155.9	155.4	154.9	154.2	153.2	152.2	151.2	150.1	149.1
70°	140.6	139.8	139.1	138.4	137.6	136.8	136.0	135.2	134.3	133.5	132.6
72.5°	123.2	122.4	121.7	121.0	120.2	119.5	118.8	118.2	117.5	116.8	116.1
75°	97.5	97.0	96.5	95.9	95.4	94.9	94.4	93.8	93.3	92.8	92.4
77.5°	73.0	72.8	72.5	72.3	72.1	71.7	71.3	70.8	70.3	69.9	69.7
80°	58.2	57.9	57.6	57.3	57.0	56.7	56.5	56.3	56.1	55.9	55.6
82.5°	43.8	43.7	43.5	43.4	43.2	43.1	43.1	43.1	43.0	43.0	42.9
85°	25.6	25.6	25.6	25.6	25.6	25.5	25.2	25.0	24.8	24.6	24.6
87.5°	10.3	10.6	10.9	11.2	11.5	11.8	11.9	12.1	12.3	12.5	12.7
90°	2.3	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2
92.5°	16.7	18.9	21.1	23.3	25.5	27.1	28.0	29.0	30.0	31.0	31.6
95°	46.9	48.5	50.0	51.6	53.2	54.6	55.8	57.0	58.2	59.4	59.9
97.5°	81.9	83.2	84.4	85.7	86.9	88.3	89.7	91.1	92.5	94.0	94.6
100°	109.5	110.1	110.8	111.5	112.2	113.4	114.9	116.5	118.0	119.6	120.0
102.5°	138.2	138.5	138.8	139.1	139.3	140.2	141.6	143.0	144.5	145.9	146.4
105°	182.2	182.3	182.5	182.7	182.9	183.3	184.0	184.7	185.4	186.1	186.6
107.5°	228.3	228.5	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	230.2
110°	259.6	259.9	260.2	260.6	260.9	261.0	260.9	260.7	260.5	260.3	260.0



TEST NUMBER: P332515

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.1	292.1	292.2	292.3	292.4	292.2	291.9	291.6	291.3	291.0	290.9
115°	340.9	340.9	340.9	340.9	340.9	340.7	340.3	340.0	339.6	339.3	339.1
117.5°	386.8	387.0	387.1	387.2	387.4	387.3	387.1	386.8	386.6	386.4	385.8
120°	417.5	418.2	418.9	419.6	420.3	420.3	419.8	419.3	418.8	418.3	417.4
122.5°	449.4	449.6	449.9	450.2	450.5	450.5	450.3	450.0	449.8	449.5	448.9
125°	496.4	496.4	496.4	496.4	496.4	496.3	496.2	496.0	495.8	495.7	495.3
127.5°	539.1	539.6	540.2	540.7	541.2	541.3	541.0	540.8	540.5	540.2	539.9
130°	569.1	569.7	570.2	570.7	571.2	571.5	571.5	571.5	571.5	571.5	571.1
132.5°	599.8	600.2	600.6	600.9	601.3	601.4	601.3	601.2	601.0	600.9	600.5
135°	640.3	641.3	642.4	643.4	644.5	645.0	645.0	645.0	645.0	645.0	644.6
137.5°	684.4	684.9	685.3	685.8	686.3	686.7	687.0	687.3	687.5	687.8	687.4
140°	713.8	714.1	714.5	714.8	715.2	715.3	715.3	715.3	715.3	715.3	715.2
142.5°	740.7	741.0	741.4	741.7	742.1	742.2	742.0	741.9	741.7	741.6	741.6
145°	777.9	778.6	779.3	780.0	780.7	781.1	781.3	781.4	781.6	781.8	781.6
147.5°	814.8	815.6	816.4	817.3	818.1	818.5	818.3	818.2	818.0	817.9	817.8
150°	837.3	838.0	838.7	839.4	840.1	840.4	840.4	840.4	840.4	840.4	840.4
152.5°	858.6	859.0	859.4	859.8	860.2	860.5	860.6	860.8	860.9	861.1	861.5
155°	891.2	891.2	891.2	891.2	891.2	891.1	891.0	890.8	890.6	890.5	891.1
157.5°	918.8	918.4	918.1	917.8	917.5	917.3	917.3	917.3	917.2	917.2	917.7
160°	935.0	934.8	934.7	934.5	934.3	934.1	934.0	933.8	933.6	933.5	934.0
162.5°	950.0	949.6	949.1	948.7	948.2	947.9	947.7	947.6	947.4	947.2	948.2
165°	970.2	969.7	969.2	968.6	968.1	967.7	967.3	967.0	966.6	966.3	967.3
167.5°	985.7	984.9	984.2	983.5	982.8	982.4	982.4	982.5	982.5	982.5	983.6
170°	994.4	993.6	992.7	991.8	991.0	990.6	990.8	991.0	991.1	991.3	992.3
172.5°	1000.7	1000.0	999.2	998.5	997.8	997.4	997.5	997.5	997.5	997.6	998.7
175°	1009.3	1008.4	1007.5	1006.7	1005.8	1005.3	1005.1	1004.9	1004.8	1004.6	1005.8
177.5°	1012.1	1011.4	1010.7	1010.0	1009.3	1009.0	1009.0	1009.0	1009.0	1009.0	1009.9
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332515

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	588.6	589.5	590.3	590.7	590.6	590.5	590.4	590.3
5°	585.5	586.6	587.8	588.2	588.0	587.8	587.6	587.4
7.5°	578.9	579.9	580.8	581.2	581.1	580.9	580.8	580.7
10°	573.5	574.3	575.2	575.5	575.3	575.0	574.8	574.6
12.5°	566.8	567.7	568.7	569.0	568.7	568.4	568.1	567.8
15°	554.1	554.7	555.4	555.5	555.2	554.9	554.6	554.3
17.5°	539.6	540.0	540.4	540.5	540.3	540.1	539.9	539.7
20°	528.9	529.2	529.5	529.6	529.3	529.1	528.9	528.7
22.5°	517.6	518.2	518.8	518.9	518.5	518.1	517.7	517.4
25°	499.1	499.2	499.3	499.2	498.7	498.3	497.9	497.5
27.5°	478.3	478.1	477.8	477.4	476.9	476.4	475.8	475.3
30°	464.0	463.6	463.1	462.7	462.1	461.6	461.1	460.6
32.5°	449.4	448.9	448.4	447.9	447.4	446.8	446.3	445.8
35°	426.4	425.7	424.9	424.3	423.8	423.3	422.7	422.2
37.5°	402.3	401.5	400.7	400.0	399.3	398.6	397.9	397.2
40°	385.6	384.5	383.5	382.7	382.1	381.6	381.1	380.6
42.5°	369.3	368.1	366.9	366.1	365.7	365.4	365.0	364.7
45°	344.2	343.0	341.9	341.1	340.8	340.5	340.2	339.9
47.5°	319.8	318.5	317.2	316.2	315.4	314.6	313.8	313.0
50°	302.8	301.4	299.9	298.8	298.2	297.6	296.9	296.3
52.5°	285.4	284.1	282.8	281.7	280.9	280.1	279.3	278.5
55°	259.7	258.4	257.2	256.2	255.6	255.0	254.3	253.7
57.5°	234.0	232.8	231.6	230.7	230.1	229.5	228.9	228.2
60°	216.3	215.4	214.4	213.7	213.2	212.6	212.1	211.6
62.5°	199.1	198.2	197.3	196.6	196.1	195.6	195.1	194.5
65°	174.0	172.9	171.9	171.1	170.6	170.0	169.5	169.0
67.5°	148.1	147.1	146.1	145.5	145.4	145.2	145.1	144.9
70°	131.8	131.0	130.1	129.5	129.2	128.9	128.6	128.3
72.5°	115.5	114.8	114.1	113.6	113.3	113.0	112.7	112.4
75°	91.9	91.5	91.1	90.8	90.7	90.6	90.5	90.4
77.5°	69.6	69.5	69.4	69.2	68.9	68.6	68.3	68.1
80°	55.4	55.2	55.0	54.9	54.7	54.6	54.5	54.4
82.5°	42.7	42.6	42.5	42.4	42.3	42.1	42.0	41.9
85°	24.6	24.6	24.6	24.6	24.5	24.4	24.2	24.1
87.5°	12.9	13.2	13.4	13.5	13.6	13.6	13.7	13.8
90°	19.3	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	32.2	32.8	33.5	33.9	34.1	34.3	34.5	34.7
95°	60.5	61.0	61.5	61.8	61.8	61.8	61.8	61.8
97.5°	95.2	95.8	96.5	96.8	96.8	96.8	96.8	96.8
100°	120.3	120.7	121.0	121.2	121.2	121.2	121.2	121.2
102.5°	146.9	147.3	147.8	148.1	148.3	148.4	148.6	148.7
105°	187.1	187.6	188.1	188.7	189.2	189.7	190.2	190.8
107.5°	230.7	231.1	231.6	231.9	231.8	231.8	231.8	231.7
110°	259.6	259.3	258.9	259.0	259.6	260.1	260.6	261.1



TEST NUMBER: P332515

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	290.8	290.8	290.7	290.7	290.8	290.9	291.0	291.1
115°	338.9	338.8	338.6	338.4	338.3	338.1	337.9	337.7
117.5°	385.2	384.6	384.0	383.5	383.2	382.8	382.5	382.1
120°	416.5	415.6	414.8	414.5	414.9	415.2	415.6	415.9
122.5°	448.3	447.8	447.2	446.6	445.9	445.3	444.7	444.1
125°	495.0	494.6	494.3	493.9	493.6	493.2	492.9	492.5
127.5°	539.5	539.2	538.8	538.5	538.2	538.0	537.7	537.4
130°	570.8	570.4	570.1	569.6	568.9	568.2	567.5	566.8
132.5°	600.2	599.8	599.5	599.2	598.9	598.6	598.3	598.1
135°	644.3	643.9	643.6	643.1	642.6	642.1	641.6	641.1
137.5°	686.9	686.5	686.0	685.8	685.9	686.0	686.1	686.3
140°	715.0	714.8	714.6	714.5	714.3	714.1	713.9	713.8
142.5°	741.5	741.5	741.5	741.4	741.4	741.4	741.3	741.3
145°	781.4	781.3	781.1	780.7	780.2	779.7	779.2	778.7
147.5°	817.6	817.5	817.3	817.2	817.0	816.8	816.7	816.5
150°	840.4	840.4	840.4	840.3	840.2	840.0	839.8	839.6
152.5°	861.9	862.3	862.7	862.7	862.3	861.8	861.4	860.9
155°	891.8	892.5	893.2	893.2	892.5	891.8	891.1	890.5
157.5°	918.2	918.8	919.3	919.2	918.7	918.1	917.5	916.9
160°	934.5	935.0	935.5	935.4	934.5	933.6	932.8	931.9
162.5°	949.1	950.0	951.0	951.0	950.1	949.3	948.4	947.5
165°	968.4	969.4	970.5	970.6	969.9	969.2	968.5	967.9
167.5°	984.6	985.7	986.7	986.7	985.6	984.5	983.5	982.4
170°	993.4	994.4	995.5	995.4	994.2	993.0	991.7	990.5
172.5°	999.9	1001.1	1002.3	1002.3	1001.1	999.8	998.6	997.4
175°	1007.0	1008.2	1009.5	1009.5	1008.2	1007.0	1005.8	1004.6
177.5°	1010.9	1011.9	1012.9	1012.8	1011.7	1010.6	1009.5	1008.3
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8

(END OF REPORT)