

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334248

Luminaire Tested: **SA4XXRDP-C1020D927-4F0-1E-UDD-F**

Issue Date: 10/11/2019

Test Information

Test Method: LM-79-08
Report Number: P334248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)
Test Lab: INNOVATIONS CENTER
Issue Date: 10/11/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDP-C1020D927-4F0-1E-UDD-F
Description: DEFINE 4 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER
PENDANT/SURFACE/WALL MOUNT, 1020 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3048.5 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 34.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P334248
CATALOG NUMBER: SA4XXRDP-C1020D927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P334248

CATALOG NUMBER: SA4XXRDP-C1020D927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	74	72
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	54
5	78	66	57	51	76	65	56	50	62	55	50	61	54	49	59	53	49	47
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41
7	67	54	46	40	65	53	45	40	52	45	39	50	44	39	49	43	39	37
8	63	50	41	36	61	49	41	36	48	40	35	46	40	35	45	39	35	33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30
10	55	42	35	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10651	10651	10651
5°	10675	10545	10610
10°	10608	10418	10418
15°	10486	10200	10124
20°	10320	9911	9729
25°	10106	9575	9332
30°	9897	9219	8833
35°	9667	8851	8334
40°	9390	8432	7793
45°	9135	8016	7243
50°	8843	7537	6661
55°	8531	7039	6028
60°	8188	6492	5383
65°	7874	5809	4747
70°	7416	5056	4029
75°	6837	4192	3278
80°	5965	3194	3008
85°	5057	2899	2714



TEST NUMBER: P334248

CATALOG NUMBER: SA4XXRDP-C1020D927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	4.1
10°-20°	345.9	11.3
20°-30°	499.4	16.4
30°-40°	566.0	18.6
40°-50°	546.5	17.9
50°-60°	454.3	14.9
60°-70°	313.6	10.3
70°-80°	158.5	5.2
80°-90°	40.2	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.4	31.8
0°-40°	1535.4	50.4
0°-60°	2536.2	83.2
0°-90°	3048.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3048.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1317	1313	1301	1311	1309	125
15°	1255	1246	1220	1218	1211	354
25°	1134	1116	1075	1058	1048	523
35°	981	949	898	864	846	613
45°	800	763	702	653	634	617
55°	606	566	500	448	428	542
65°	412	369	304	261	248	407
75°	219	182	134	111	105	231
85°	55	34	31	29	29	63
90°	0	0	0	0	0	



TEST NUMBER: P334248

CATALOG NUMBER: SA4XXRDP-C1020D927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.4	1319.4	1319.4	1319.4	1319.4
2.5°	1323.4	1319.4	1308.2	1319.4	1318.3
5°	1317.3	1313.3	1301.2	1311.3	1309.3
7.5°	1308.2	1304.2	1289.0	1296.1	1293.1
10°	1294.1	1289.0	1270.9	1274.9	1270.9
12.5°	1275.9	1269.9	1247.6	1249.7	1243.6
15°	1254.7	1245.6	1220.4	1218.3	1211.3
17.5°	1230.5	1217.3	1188.0	1183.0	1172.9
20°	1201.2	1188.0	1153.7	1145.6	1132.5
22.5°	1168.8	1153.7	1116.3	1103.2	1093.1
25°	1134.5	1116.3	1074.9	1057.7	1047.6
27.5°	1099.1	1076.9	1033.5	1013.3	999.1
30°	1061.7	1036.5	989.0	963.8	947.6
32.5°	1022.3	993.1	943.6	913.2	898.1
35°	980.9	948.6	898.1	863.7	845.6
37.5°	937.5	904.2	848.6	811.2	793.0
40°	891.0	857.7	800.1	757.7	739.5
42.5°	846.6	811.2	750.6	707.2	688.0
45°	800.1	762.7	702.1	652.6	634.4
47.5°	752.6	714.2	651.6	600.1	579.9
50°	704.1	664.7	600.1	549.6	530.4
52.5°	654.6	616.2	549.6	498.0	477.8
55°	606.1	565.7	500.1	447.5	428.3
57.5°	558.7	516.2	451.6	398.0	383.9
60°	507.1	466.7	402.1	349.5	333.4
62.5°	460.7	418.2	351.6	304.1	292.0
65°	412.2	368.7	304.1	260.6	248.5
67.5°	361.7	320.2	259.6	221.2	207.1
70°	314.2	271.8	214.2	180.8	170.7
72.5°	263.7	226.3	172.7	145.5	136.4
75°	219.2	181.8	134.4	111.1	105.1
77.5°	172.7	140.4	100.0	83.8	81.8
80°	128.3	99.0	68.7	65.7	64.7
82.5°	89.9	63.6	49.5	47.5	46.5
85°	54.6	34.3	31.3	29.3	29.3
87.5°	23.2	15.2	14.1	13.1	14.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)