

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332562

Luminaire Tested: **SA4XXDIP-C575D1035U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332562  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6723.9 lumens  
Efficiency: N/A  
Efficacy: 151.1 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332562  
CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19	16
7	57	45	37	32	51	41	34	30	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7582	7582	7582	7582
5°	8930	7602	6710	7602
10°	10691	7569	6041	7569
15°	12649	7492	5548	7492
20°	14086	7414	5107	7414
25°	14313	7299	4804	7299
30°	12179	7189	4708	7189
35°	9363	7009	4709	7009
40°	7299	6798	4797	6798
45°	6085	6481	4877	6481
50°	5355	6094	5043	6094
55°	4906	5630	5246	5630
60°	4598	5214	5491	5214
65°	4281	4749	5692	4749
70°	3911	4289	5823	4289
75°	3497	3774	5752	3774
80°	2929	3092	5570	3092
85°	2158	2232	5335	2232



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.5	1.4
10°-20°	282.0	4.2
20°-30°	447.2	6.7
30°-40°	497.7	7.4
40°-50°	453.1	6.7
50°-60°	370.2	5.5
60°-70°	264.3	3.9
70°-80°	145.5	2.2
80°-90°	43.6	0.6
90°-100°	45.7	0.7
100°-110°	291.1	4.3
110°-120°	556.8	8.3
120°-130°	706.8	10.5
130°-140°	756.2	11.2
140°-150°	707.2	10.5
150°-160°	570.3	8.5
160°-170°	367.8	5.5
170°-180°	126.8	1.9
0°-30°	820.8	12.2
0°-40°	1318.5	19.6
0°-60°	2141.8	31.9
0°-90°	2595.3	38.6
90°-120°	893.5	13.3
90°-150°	3063.7	45.6
90°-180°	4129.0	61.4
0°-180°	6723.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	939	939	939	939	939	
5°	1102	938	828	938	1102	112
15°	1514	896	664	896	1514	428
25°	1607	819	539	819	1607	708
35°	950	711	478	711	950	603
45°	533	568	427	568	533	420
55°	349	400	373	400	349	315
65°	224	249	298	249	224	222
75°	112	121	184	121	112	119
85°	23	24	58	24	23	29
90°	30	3	30	3	30	14
95°	29	55	29	55	29	23
105°	284	300	284	300	284	248
115°	565	561	565	561	565	559
125°	795	789	795	789	795	708
135°	985	978	985	978	985	758
145°	1134	1128	1134	1128	1134	709
155°	1236	1237	1236	1237	1236	570
165°	1299	1305	1299	1305	1299	367
175°	1327	1335	1327	1335	1327	126
180°	1335	1335	1335	1335	1335	



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	999.6	999.3	996.2	995.6	993.4	990.6	990.0	985.0	975.0	970.4	969.1
5°	1101.9	1109.7	1099.5	1097.6	1096.4	1083.6	1077.0	1069.2	1051.3	1040.8	1032.6
7.5°	1223.9	1224.8	1220.4	1216.8	1206.9	1195.7	1178.9	1161.0	1139.7	1117.5	1100.8
10°	1304.2	1307.3	1302.3	1301.5	1281.6	1269.2	1244.3	1223.3	1199.1	1172.3	1147.8
12.5°	1388.9	1384.5	1381.9	1365.3	1361.6	1338.9	1310.0	1288.3	1251.1	1220.2	1187.6
15°	1513.5	1505.0	1499.5	1476.6	1465.3	1433.8	1403.0	1379.3	1330.7	1284.4	1249.3
17.5°	1586.7	1595.2	1582.6	1573.2	1544.0	1521.9	1490.5	1440.7	1402.6	1345.1	1300.9
20°	1639.6	1640.4	1633.4	1623.6	1600.7	1572.7	1538.4	1484.0	1438.4	1381.2	1320.5
22.5°	1653.9	1654.1	1651.1	1642.0	1624.6	1601.9	1567.4	1521.9	1466.8	1404.6	1343.9
25°	1606.9	1605.4	1608.9	1619.0	1612.4	1605.4	1585.5	1551.7	1500.3	1434.5	1369.2
27.5°	1432.3	1443.0	1462.8	1487.7	1511.7	1529.9	1535.1	1528.2	1496.3	1442.2	1373.8
30°	1306.5	1319.8	1334.5	1359.5	1407.7	1435.3	1465.7	1488.6	1475.8	1432.6	1368.8
32.5°	1168.3	1171.6	1193.5	1221.9	1266.1	1319.2	1367.3	1413.9	1429.4	1406.8	1353.5
35°	950.1	955.6	979.3	1007.3	1061.4	1126.4	1198.8	1263.3	1316.7	1338.1	1310.8
37.5°	775.4	791.0	807.7	837.8	885.5	944.0	1019.2	1102.7	1182.2	1235.4	1244.4
40°	692.6	702.3	714.4	737.3	777.8	835.4	899.9	995.7	1080.1	1156.4	1181.3
42.5°	627.2	632.9	640.3	661.0	691.9	749.1	808.1	892.3	977.1	1068.3	1110.0
45°	533.0	538.9	551.3	563.4	586.7	626.4	681.3	750.5	835.7	923.7	1000.7
47.5°	465.0	468.8	476.2	489.1	508.9	535.1	579.7	637.5	716.5	801.9	884.0
50°	426.4	429.5	435.4	447.1	462.2	485.6	522.1	576.2	638.1	724.1	804.6
52.5°	395.9	397.2	401.5	409.4	421.5	441.1	471.1	515.8	573.4	650.0	730.2
55°	348.6	350.2	354.1	359.9	370.4	382.9	405.8	439.3	489.5	556.0	625.6
57.5°	309.7	310.8	314.1	316.3	325.0	335.1	352.7	376.6	414.7	471.1	533.3
60°	284.8	284.0	287.9	289.9	295.7	304.3	317.9	340.8	373.9	419.4	476.6
62.5°	260.5	259.4	262.7	265.3	268.6	275.9	287.1	305.0	331.9	373.1	422.5
65°	224.1	222.6	224.5	227.6	230.7	234.6	242.8	258.7	280.1	309.7	347.4
67.5°	187.5	189.2	189.5	191.0	192.8	198.1	203.7	215.0	230.1	253.8	285.7
70°	165.7	166.1	167.7	167.7	168.9	173.5	178.2	184.8	199.6	221.4	247.5
72.5°	144.0	145.6	145.0	146.2	147.1	150.2	153.6	159.9	172.5	188.7	210.7
75°	112.1	113.2	113.2	113.6	114.8	115.9	118.7	123.3	132.3	144.3	159.5
77.5°	81.7	81.9	82.4	83.8	83.8	85.7	87.7	91.4	95.9	104.1	113.4
80°	63.0	63.8	63.4	64.2	64.2	65.8	66.5	71.2	73.1	78.6	86.0
82.5°	46.2	47.0	46.9	48.0	48.6	48.9	50.0	51.9	53.8	58.7	61.7
85°	23.3	24.1	23.3	24.1	25.3	25.7	26.8	27.2	28.8	30.0	32.7
87.5°	12.8	13.7	13.6	13.8	14.4	14.5	14.5	14.0	14.9	15.0	15.9
90°	29.9	29.5	29.1	28.6	28.2	27.3	26.0	24.6	23.3	22.0	20.2
92.5°	27.6	27.5	27.4	27.3	27.2	26.5	25.2	23.8	22.5	21.2	19.4
95°	28.9	28.7	28.5	28.3	28.1	27.3	26.0	24.6	23.3	22.0	21.7
97.5°	28.0	27.7	27.5	27.3	27.1	26.9	26.8	26.6	26.5	26.4	51.1
100°	28.0	27.7	27.5	27.3	27.1	28.8	32.6	36.4	40.2	43.9	74.5
102.5°	28.8	28.7	28.7	28.6	28.6	48.9	89.6	130.3	170.9	211.6	215.6
105°	284.5	292.5	300.5	308.5	316.5	319.4	317.4	315.5	313.5	311.5	310.4
107.5°	396.5	395.7	394.8	394.0	393.1	392.2	391.3	390.3	389.3	388.3	386.8
110°	445.2	444.6	443.9	443.2	442.6	442.0	441.6	441.1	440.7	440.2	438.9



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	493.9	493.1	492.3	491.4	490.6	490.2	490.3	490.4	490.5	490.5	489.9
115°	565.0	565.0	565.0	565.0	565.0	564.8	564.4	563.9	563.5	563.0	563.2
117.5°	637.3	637.4	637.5	637.6	637.7	637.7	637.8	637.9	638.0	638.1	637.6
120°	682.8	683.3	683.7	684.1	684.6	684.6	684.1	683.7	683.3	682.8	683.0
122.5°	727.5	728.0	728.4	728.9	729.3	729.4	729.1	728.9	728.6	728.3	728.0
125°	794.6	794.4	794.2	794.0	793.7	793.3	792.6	792.0	791.3	790.6	791.1
127.5°	853.5	853.7	853.9	854.1	854.2	854.4	854.5	854.7	854.8	854.9	853.9
130°	893.5	893.5	893.5	893.5	893.5	893.3	893.1	892.9	892.7	892.5	891.8
132.5°	930.2	930.4	930.5	930.7	930.9	930.9	930.7	930.4	930.2	930.0	929.1
135°	985.3	984.8	984.4	984.0	983.5	983.1	982.6	982.2	981.7	981.3	980.4
137.5°	1032.4	1032.5	1032.7	1032.8	1032.9	1032.8	1032.3	1031.8	1031.3	1030.8	1029.8
140°	1065.2	1064.9	1064.7	1064.5	1064.3	1063.8	1063.2	1062.5	1061.8	1061.2	1060.7
142.5°	1092.3	1092.3	1092.2	1092.2	1092.1	1091.9	1091.4	1090.9	1090.4	1089.9	1089.6
145°	1134.0	1133.6	1133.1	1132.7	1132.3	1131.9	1131.7	1131.5	1131.3	1131.0	1131.0
147.5°	1168.6	1168.4	1168.1	1167.9	1167.7	1167.5	1167.3	1167.1	1167.0	1166.8	1167.0
150°	1190.9	1190.7	1190.5	1190.3	1190.0	1189.9	1189.9	1189.9	1189.9	1189.9	1190.2
152.5°	1210.1	1210.2	1210.4	1210.5	1210.6	1210.5	1210.2	1209.8	1209.5	1209.1	1209.5
155°	1235.9	1236.5	1237.2	1237.9	1238.5	1238.4	1237.5	1236.6	1235.7	1234.9	1235.5
157.5°	1257.4	1258.6	1259.7	1260.9	1262.0	1262.0	1260.9	1259.7	1258.6	1257.4	1258.2
160°	1271.8	1273.1	1274.5	1275.8	1277.1	1277.1	1275.8	1274.5	1273.1	1271.8	1272.0
162.5°	1283.0	1284.5	1286.0	1287.5	1289.0	1289.1	1287.8	1286.4	1285.1	1283.8	1284.0
165°	1298.7	1300.7	1302.7	1304.7	1306.7	1306.8	1305.1	1303.3	1301.5	1299.7	1299.7
167.5°	1310.5	1312.7	1315.0	1317.2	1319.4	1319.5	1317.6	1315.6	1313.7	1311.7	1311.9
170°	1317.7	1319.9	1322.2	1324.4	1326.6	1326.8	1325.0	1323.3	1321.5	1319.7	1319.5
172.5°	1321.7	1324.1	1326.5	1328.9	1331.3	1331.6	1329.8	1328.1	1326.3	1324.5	1324.3
175°	1326.7	1329.4	1332.0	1334.7	1337.3	1337.7	1335.7	1333.7	1331.7	1329.7	1329.5
177.5°	1329.9	1332.0	1334.2	1336.3	1338.4	1338.8	1337.3	1335.9	1334.5	1333.1	1332.7
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	969.4	965.1	962.0	959.5	952.6	948.6	945.5	941.1	936.1	930.8	924.3
5°	1024.5	1011.2	1001.5	986.7	972.7	961.0	949.0	938.1	924.8	910.5	899.9
7.5°	1082.3	1062.6	1037.4	1015.5	990.9	969.5	950.4	930.8	910.4	890.6	872.5
10°	1119.0	1093.7	1065.7	1032.6	1001.5	973.9	948.2	923.3	899.2	875.0	854.4
12.5°	1158.5	1127.0	1085.6	1046.9	1012.1	975.1	944.1	913.6	884.5	859.2	835.1
15°	1211.6	1166.1	1118.2	1066.5	1020.6	977.4	935.0	896.4	863.8	830.3	807.0
17.5°	1244.2	1187.9	1133.2	1079.1	1023.5	969.0	923.3	878.9	837.9	804.7	775.3
20°	1265.7	1209.7	1141.6	1087.5	1021.3	965.3	912.4	863.0	820.2	784.8	754.4
22.5°	1284.4	1219.6	1151.5	1080.3	1014.5	955.0	897.1	847.4	803.7	766.4	737.3
25°	1294.5	1220.2	1146.2	1075.4	1000.7	930.3	877.8	819.4	772.7	733.4	702.3
27.5°	1295.6	1216.1	1132.5	1053.8	976.7	911.1	844.8	792.6	744.2	702.6	672.7
30°	1292.1	1209.3	1119.4	1034.2	956.8	885.5	828.0	771.2	721.7	680.5	649.4
32.5°	1281.2	1194.9	1102.6	1012.4	932.2	862.5	803.1	749.1	700.9	660.3	627.6
35°	1249.7	1164.5	1066.1	972.3	890.2	819.8	766.1	711.2	663.0	624.5	593.0
37.5°	1200.5	1123.4	1023.4	926.3	845.7	775.0	721.7	672.2	628.7	589.5	557.2
40°	1157.5	1089.8	989.4	894.9	807.7	740.4	690.6	645.1	601.9	564.9	534.2
42.5°	1108.0	1049.0	956.4	856.3	772.2	704.6	656.1	615.2	574.5	540.4	509.6
45°	1019.8	980.9	893.7	801.1	713.6	649.8	603.5	567.7	533.4	500.0	474.3
47.5°	918.3	899.0	825.6	737.7	654.6	591.7	551.6	518.5	488.5	460.1	437.5
50°	850.1	840.8	777.4	692.6	613.2	554.1	513.6	485.2	459.5	434.6	413.2
52.5°	782.9	782.6	725.4	647.7	574.3	517.3	477.2	450.6	428.4	408.1	388.9
55°	680.1	691.0	646.3	577.0	511.3	459.9	423.7	400.0	384.4	367.7	353.3
57.5°	585.7	603.8	566.9	505.9	451.0	403.7	372.2	354.4	337.8	327.7	317.2
60°	524.1	541.2	512.4	461.1	409.3	368.8	338.9	322.9	308.5	301.5	294.1
62.5°	469.3	484.6	463.2	415.6	370.7	331.8	306.5	291.2	281.5	273.8	268.9
65°	391.0	403.9	385.6	351.0	312.4	281.3	260.7	248.6	239.3	236.2	230.7
67.5°	316.1	327.8	317.9	288.5	257.6	234.0	217.9	206.3	200.8	198.0	194.2
70°	271.6	283.3	272.7	247.1	223.3	203.5	188.3	181.7	175.9	174.7	169.3
72.5°	233.9	241.9	231.3	211.3	191.0	174.2	162.5	155.6	152.5	150.4	147.5
75°	175.5	182.5	175.5	159.9	145.5	133.8	123.7	121.0	117.5	116.3	114.4
77.5°	124.2	130.3	124.9	115.2	104.4	95.4	90.0	86.5	85.7	83.7	84.6
80°	94.9	98.8	93.8	87.2	78.6	72.4	68.5	66.5	64.2	63.4	65.0
82.5°	68.2	69.9	67.3	62.9	56.5	52.4	49.8	47.5	47.1	47.2	47.2
85°	35.4	35.0	34.6	30.7	28.8	26.1	24.5	24.1	23.7	24.5	25.3
87.5°	15.5	15.5	14.8	13.1	11.7	10.3	9.5	8.7	9.5	10.3	11.1
90°	18.4	16.6	14.9	12.8	10.3	7.9	5.4	3.0	5.4	7.9	10.3
92.5°	17.6	15.8	14.1	13.1	13.0	12.8	12.7	12.6	12.7	12.8	13.0
95°	21.5	21.3	21.1	24.7	32.3	39.8	47.4	54.9	47.4	39.8	32.3
97.5°	75.9	100.6	125.4	135.4	130.7	126.0	121.3	116.6	121.3	126.0	130.7
100°	105.2	135.8	166.4	179.7	175.7	171.7	167.7	163.7	167.7	171.7	175.7
102.5°	219.6	223.6	227.6	228.1	225.2	222.3	219.4	216.4	219.4	222.3	225.2
105°	309.2	308.1	307.0	305.8	304.5	303.1	301.8	300.5	301.8	303.1	304.5
107.5°	385.3	383.8	382.3	381.2	380.5	379.9	379.2	378.5	379.2	379.9	380.5
110°	437.6	436.2	434.9	433.9	433.2	432.6	431.9	431.3	431.9	432.6	433.2





TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	489.3	488.7	488.1	487.2	486.0	484.8	483.6	482.4	483.6	484.8	486.0
115°	563.5	563.7	563.9	563.7	563.0	562.4	561.7	561.0	561.7	562.4	563.0
117.5°	637.1	636.6	636.1	635.5	634.6	633.7	632.8	631.9	632.8	633.7	634.6
120°	683.3	683.5	683.7	683.4	682.5	681.6	680.7	679.8	680.7	681.6	682.5
122.5°	727.7	727.4	727.1	726.7	726.1	725.6	725.1	724.5	725.1	725.6	726.1
125°	791.5	792.0	792.4	792.2	791.3	790.4	789.5	788.6	789.5	790.4	791.3
127.5°	852.9	851.9	850.8	850.2	850.0	849.8	849.5	849.3	849.5	849.8	850.0
130°	891.1	890.5	889.8	889.3	889.1	888.9	888.7	888.5	888.7	888.9	889.1
132.5°	928.3	927.5	926.6	926.0	925.6	925.2	924.8	924.4	924.8	925.2	925.6
135°	979.5	978.6	977.7	977.4	977.6	977.9	978.1	978.3	978.1	977.9	977.6
137.5°	1028.9	1027.9	1026.9	1026.4	1026.3	1026.2	1026.1	1026.0	1026.1	1026.2	1026.3
140°	1060.3	1059.8	1059.4	1058.9	1058.5	1058.1	1057.6	1057.2	1057.6	1058.1	1058.5
142.5°	1089.4	1089.1	1088.8	1088.3	1087.5	1086.7	1085.9	1085.1	1085.9	1086.7	1087.5
145°	1131.0	1131.0	1131.0	1130.7	1130.0	1129.4	1128.7	1128.0	1128.7	1129.4	1130.0
147.5°	1167.2	1167.4	1167.7	1167.2	1165.9	1164.7	1163.4	1162.2	1163.4	1164.7	1165.9
150°	1190.4	1190.6	1190.8	1190.5	1189.6	1188.7	1187.8	1186.9	1187.8	1188.7	1189.6
152.5°	1209.9	1210.3	1210.7	1210.5	1209.8	1209.1	1208.4	1207.7	1208.4	1209.1	1209.8
155°	1236.2	1236.9	1237.5	1237.7	1237.5	1237.3	1237.1	1236.9	1237.1	1237.3	1237.5
157.5°	1258.9	1259.7	1260.4	1260.9	1261.0	1261.1	1261.3	1261.4	1261.3	1261.1	1261.0
160°	1272.2	1272.5	1272.7	1273.1	1273.8	1274.5	1275.1	1275.8	1275.1	1274.5	1273.8
162.5°	1284.2	1284.4	1284.7	1285.2	1286.0	1286.9	1287.7	1288.6	1287.7	1286.9	1286.0
165°	1299.7	1299.7	1299.7	1300.3	1301.4	1302.5	1303.6	1304.7	1303.6	1302.5	1301.4
167.5°	1312.0	1312.1	1312.3	1312.9	1314.1	1315.2	1316.4	1317.5	1316.4	1315.2	1314.1
170°	1319.3	1319.0	1318.8	1319.4	1320.7	1322.0	1323.4	1324.7	1323.4	1322.0	1320.7
172.5°	1324.1	1323.8	1323.6	1324.2	1325.5	1326.8	1328.2	1329.5	1328.2	1326.8	1325.5
175°	1329.3	1329.0	1328.8	1329.4	1330.7	1332.0	1333.4	1334.7	1333.4	1332.0	1330.7
177.5°	1332.4	1332.0	1331.7	1332.1	1333.4	1334.6	1335.8	1337.1	1335.8	1334.6	1333.4
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	921.2	918.4	914.3	908.7	904.1	899.1	897.8	896.0	899.7	896.6	895.7
5°	891.0	882.8	872.3	860.3	853.3	843.1	841.2	837.3	833.4	833.0	829.1
7.5°	859.0	847.0	833.3	821.0	809.6	798.6	791.3	789.8	784.0	780.7	776.8
10°	838.5	823.7	807.7	796.1	782.8	771.2	763.0	758.3	754.4	750.1	746.3
12.5°	814.2	798.5	785.3	772.7	757.0	748.1	734.7	726.6	725.8	725.9	715.8
15°	785.9	770.4	750.1	732.3	723.7	706.6	699.2	689.8	684.0	678.2	673.5
17.5°	753.7	734.3	718.5	697.9	681.6	668.0	658.2	652.6	643.9	635.6	629.6
20°	733.4	712.8	696.1	674.3	656.4	639.7	631.5	623.7	617.1	610.1	603.5
22.5°	712.9	691.3	670.9	649.7	633.0	615.4	607.5	596.9	590.6	586.7	580.1
25°	680.5	657.2	633.8	613.6	596.5	580.9	570.4	562.2	555.2	552.1	547.8
27.5°	645.3	622.1	599.6	576.6	557.2	545.9	537.5	531.3	527.3	523.2	521.2
30°	622.9	598.8	574.7	553.3	535.4	524.1	516.3	512.0	508.9	507.0	505.0
32.5°	600.2	576.4	551.0	531.5	515.5	505.4	499.5	495.2	493.7	493.0	492.3
35°	563.8	539.7	516.3	498.8	483.6	479.7	474.7	472.3	471.6	474.3	475.5
37.5°	528.5	506.1	484.6	467.7	457.7	452.0	450.3	450.4	453.2	455.6	458.4
40°	505.8	484.0	463.8	449.0	439.7	436.2	435.4	437.3	440.4	443.2	446.3
42.5°	483.7	462.2	443.9	430.0	423.5	420.3	420.8	422.7	427.1	430.4	435.1
45°	449.4	431.5	413.6	402.3	396.9	397.6	397.6	401.1	405.4	410.5	415.5
47.5°	417.1	399.0	384.3	374.8	372.0	371.3	373.5	378.1	384.3	390.5	397.6
50°	395.3	378.2	365.3	356.8	353.7	354.8	358.0	362.2	369.6	377.4	384.8
52.5°	373.2	357.6	345.7	337.8	335.6	337.7	340.8	347.6	354.1	362.5	371.4
55°	338.9	325.7	316.3	310.5	309.7	310.9	314.4	321.8	331.1	341.6	350.2
57.5°	304.7	293.7	285.1	281.1	281.5	282.6	288.3	297.1	307.1	318.3	329.3
60°	281.7	271.6	264.6	261.5	261.9	264.2	271.2	279.4	291.8	302.7	314.4
62.5°	259.9	251.0	244.3	241.5	241.0	246.1	252.8	261.3	273.8	285.9	298.5
65°	224.9	217.9	212.4	210.9	212.0	215.9	224.5	235.8	246.3	259.1	272.4
67.5°	190.6	184.9	181.2	181.9	183.3	189.0	196.2	205.9	217.8	231.1	244.2
70°	168.9	163.4	160.3	160.7	163.0	170.0	176.3	186.0	198.8	212.4	223.3
72.5°	146.5	142.9	140.1	141.7	144.0	148.9	156.6	166.4	177.7	190.3	201.9
75°	112.4	112.4	110.9	112.1	115.6	120.2	126.1	136.2	147.5	157.6	166.9
77.5°	83.4	82.6	83.6	85.0	87.0	92.5	99.2	106.5	114.9	125.1	132.8
80°	63.8	64.2	66.1	68.5	69.3	73.5	80.5	87.2	93.8	102.3	109.7
82.5°	47.9	48.3	49.3	52.3	53.1	57.7	62.2	68.8	74.8	80.5	86.7
85°	26.1	26.1	28.0	29.2	31.1	34.2	37.0	40.9	46.3	50.2	56.0
87.5°	12.5	12.9	14.5	15.5	16.8	18.7	19.6	23.3	24.8	26.6	29.6
90°	12.8	14.9	16.6	18.4	20.2	22.0	23.3	24.6	26.0	27.3	28.2
92.5°	13.1	14.1	15.8	17.6	19.4	21.2	22.5	23.8	25.2	26.5	27.2
95°	24.7	21.1	21.3	21.5	21.7	22.0	23.3	24.6	26.0	27.3	28.1
97.5°	135.4	125.4	100.6	75.9	51.1	26.4	26.5	26.6	26.8	26.9	27.1
100°	179.7	166.4	135.8	105.2	74.5	43.9	40.2	36.4	32.6	28.8	27.1
102.5°	228.1	227.6	223.6	219.6	215.6	211.6	170.9	130.3	89.6	48.9	28.6
105°	305.8	307.0	308.1	309.2	310.4	311.5	313.5	315.5	317.4	319.4	316.5
107.5°	381.2	382.3	383.8	385.3	386.8	388.3	389.3	390.3	391.3	392.2	393.1
110°	433.9	434.9	436.2	437.6	438.9	440.2	440.7	441.1	441.6	442.0	442.6



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	487.2	488.1	488.7	489.3	489.9	490.5	490.5	490.4	490.3	490.2	490.6
115°	563.7	563.9	563.7	563.5	563.2	563.0	563.5	563.9	564.4	564.8	565.0
117.5°	635.5	636.1	636.6	637.1	637.6	638.1	638.0	637.9	637.8	637.7	637.7
120°	683.4	683.7	683.5	683.3	683.0	682.8	683.3	683.7	684.1	684.6	684.6
122.5°	726.7	727.1	727.4	727.7	728.0	728.3	728.6	728.9	729.1	729.4	729.3
125°	792.2	792.4	792.0	791.5	791.1	790.6	791.3	792.0	792.6	793.3	793.7
127.5°	850.2	850.8	851.9	852.9	853.9	854.9	854.8	854.7	854.5	854.4	854.2
130°	889.3	889.8	890.5	891.1	891.8	892.5	892.7	892.9	893.1	893.3	893.5
132.5°	926.0	926.6	927.5	928.3	929.1	930.0	930.2	930.4	930.7	930.9	930.9
135°	977.4	977.7	978.6	979.5	980.4	981.3	981.7	982.2	982.6	983.1	983.5
137.5°	1026.4	1026.9	1027.9	1028.9	1029.8	1030.8	1031.3	1031.8	1032.3	1032.8	1032.9
140°	1058.9	1059.4	1059.8	1060.3	1060.7	1061.2	1061.8	1062.5	1063.2	1063.8	1064.3
142.5°	1088.3	1088.8	1089.1	1089.4	1089.6	1089.9	1090.4	1090.9	1091.4	1091.9	1092.1
145°	1130.7	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3	1131.5	1131.7	1131.9	1132.3
147.5°	1167.2	1167.7	1167.4	1167.2	1167.0	1166.8	1167.0	1167.1	1167.3	1167.5	1167.7
150°	1190.5	1190.8	1190.6	1190.4	1190.2	1189.9	1189.9	1189.9	1189.9	1189.9	1190.0
152.5°	1210.5	1210.7	1210.3	1209.9	1209.5	1209.1	1209.5	1209.8	1210.2	1210.5	1210.6
155°	1237.7	1237.5	1236.9	1236.2	1235.5	1234.9	1235.7	1236.6	1237.5	1238.4	1238.5
157.5°	1260.9	1260.4	1259.7	1258.9	1258.2	1257.4	1258.6	1259.7	1260.9	1262.0	1262.0
160°	1273.1	1272.7	1272.5	1272.2	1272.0	1271.8	1273.1	1274.5	1275.8	1277.1	1277.1
162.5°	1285.2	1284.7	1284.4	1284.2	1284.0	1283.8	1285.1	1286.4	1287.8	1289.1	1289.0
165°	1300.3	1299.7	1299.7	1299.7	1299.7	1299.7	1301.5	1303.3	1305.1	1306.8	1306.7
167.5°	1312.9	1312.3	1312.1	1312.0	1311.9	1311.7	1313.7	1315.6	1317.6	1319.5	1319.4
170°	1319.4	1318.8	1319.0	1319.3	1319.5	1319.7	1321.5	1323.3	1325.0	1326.8	1326.6
172.5°	1324.2	1323.6	1323.8	1324.1	1324.3	1324.5	1326.3	1328.1	1329.8	1331.6	1331.3
175°	1329.4	1328.8	1329.0	1329.3	1329.5	1329.7	1331.7	1333.7	1335.7	1337.7	1337.3
177.5°	1332.1	1331.7	1332.0	1332.4	1332.7	1333.1	1334.5	1335.9	1337.3	1338.8	1338.4
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	895.0	894.4	892.2	891.9	892.2	894.4	895.0	895.7	896.6	899.7	896.0
5°	826.8	824.9	823.7	828.0	823.7	824.9	826.8	829.1	833.0	833.4	837.3
7.5°	775.4	773.8	770.4	769.3	770.4	773.8	775.4	776.8	780.7	784.0	789.8
10°	742.4	740.8	737.7	736.9	737.7	740.8	742.4	746.3	750.1	754.4	758.3
12.5°	710.6	707.5	706.9	707.7	706.9	707.5	710.6	715.8	725.9	725.8	726.6
15°	668.4	666.9	662.6	663.8	662.6	666.9	668.4	673.5	678.2	684.0	689.8
17.5°	626.9	625.0	619.8	624.4	619.8	625.0	626.9	629.6	635.6	643.9	652.6
20°	600.7	597.6	594.9	594.5	594.9	597.6	600.7	603.5	610.1	617.1	623.7
22.5°	575.8	573.0	572.8	570.2	572.8	573.0	575.8	580.1	586.7	590.6	596.9
25°	544.7	542.0	541.2	539.3	541.2	542.0	544.7	547.8	552.1	555.2	562.2
27.5°	520.8	519.5	518.1	518.7	518.1	519.5	520.8	521.2	523.2	527.3	531.3
30°	506.2	505.8	505.0	505.0	505.0	505.8	506.2	505.0	507.0	508.9	512.0
32.5°	494.1	494.0	494.4	494.4	494.4	494.0	494.1	492.3	493.0	493.7	495.2
35°	477.0	478.2	479.0	477.8	479.0	478.2	477.0	475.5	474.3	471.6	472.3
37.5°	461.6	462.8	463.9	465.2	463.9	462.8	461.6	458.4	455.6	453.2	450.4
40°	449.8	452.5	453.3	455.2	453.3	452.5	449.8	446.3	443.2	440.4	437.3
42.5°	438.6	441.6	443.6	444.0	443.6	441.6	438.6	435.1	430.4	427.1	422.7
45°	421.4	424.5	427.2	427.2	427.2	424.5	421.4	415.5	410.5	405.4	401.1
47.5°	403.6	408.1	410.8	411.5	410.8	408.1	403.6	397.6	390.5	384.3	378.1
50°	391.4	396.9	399.6	401.5	399.6	396.9	391.4	384.8	377.4	369.6	362.2
52.5°	379.6	385.0	388.7	389.7	388.7	385.0	379.6	371.4	362.5	354.1	347.6
55°	359.1	366.9	371.2	372.7	371.2	366.9	359.1	350.2	341.6	331.1	321.8
57.5°	339.8	347.0	352.0	353.1	352.0	347.0	339.8	329.3	318.3	307.1	297.1
60°	324.9	332.7	338.9	340.1	338.9	332.7	324.9	314.4	302.7	291.8	279.4
62.5°	309.6	317.7	323.3	326.4	323.3	317.7	309.6	298.5	285.9	273.8	261.3
65°	283.3	291.4	296.9	298.0	296.9	291.4	283.3	272.4	259.1	246.3	235.8
67.5°	254.5	262.6	266.2	268.5	266.2	262.6	254.5	244.2	231.1	217.8	205.9
70°	234.2	240.8	244.7	246.7	244.7	240.8	234.2	223.3	212.4	198.8	186.0
72.5°	211.2	218.1	222.6	223.0	222.6	218.1	211.2	201.9	190.3	177.7	166.4
75°	175.9	182.1	184.4	184.4	184.4	182.1	175.9	166.9	157.6	147.5	136.2
77.5°	139.2	142.4	145.4	146.0	145.4	142.4	139.2	132.8	125.1	114.9	106.5
80°	115.6	117.5	119.8	119.8	119.8	117.5	115.6	109.7	102.3	93.8	87.2
82.5°	91.3	92.9	95.2	94.9	95.2	92.9	91.3	86.7	80.5	74.8	68.8
85°	55.2	58.8	58.4	57.6	58.4	58.8	55.2	56.0	50.2	46.3	40.9
87.5°	30.6	31.0	32.0	32.8	32.0	31.0	30.6	29.6	26.6	24.8	23.3
90°	28.6	29.1	29.5	29.9	29.5	29.1	28.6	28.2	27.3	26.0	24.6
92.5°	27.3	27.4	27.5	27.6	27.5	27.4	27.3	27.2	26.5	25.2	23.8
95°	28.3	28.5	28.7	28.9	28.7	28.5	28.3	28.1	27.3	26.0	24.6
97.5°	27.3	27.5	27.7	28.0	27.7	27.5	27.3	27.1	26.9	26.8	26.6
100°	27.3	27.5	27.7	28.0	27.7	27.5	27.3	27.1	28.8	32.6	36.4
102.5°	28.6	28.7	28.7	28.8	28.7	28.7	28.6	28.6	48.9	89.6	130.3
105°	308.5	300.5	292.5	284.5	292.5	300.5	308.5	316.5	319.4	317.4	315.5
107.5°	394.0	394.8	395.7	396.5	395.7	394.8	394.0	393.1	392.2	391.3	390.3
110°	443.2	443.9	444.6	445.2	444.6	443.9	443.2	442.6	442.0	441.6	441.1



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	491.4	492.3	493.1	493.9	493.1	492.3	491.4	490.6	490.2	490.3	490.4
115°	565.0	565.0	565.0	565.0	565.0	565.0	565.0	565.0	564.8	564.4	563.9
117.5°	637.6	637.5	637.4	637.3	637.4	637.5	637.6	637.7	637.7	637.8	637.9
120°	684.1	683.7	683.3	682.8	683.3	683.7	684.1	684.6	684.6	684.1	683.7
122.5°	728.9	728.4	728.0	727.5	728.0	728.4	728.9	729.3	729.4	729.1	728.9
125°	794.0	794.2	794.4	794.6	794.4	794.2	794.0	793.7	793.3	792.6	792.0
127.5°	854.1	853.9	853.7	853.5	853.7	853.9	854.1	854.2	854.4	854.5	854.7
130°	893.5	893.5	893.5	893.5	893.5	893.5	893.5	893.5	893.3	893.1	892.9
132.5°	930.7	930.5	930.4	930.2	930.4	930.5	930.7	930.9	930.9	930.7	930.4
135°	984.0	984.4	984.8	985.3	984.8	984.4	984.0	983.5	983.1	982.6	982.2
137.5°	1032.8	1032.7	1032.5	1032.4	1032.5	1032.7	1032.8	1032.9	1032.8	1032.3	1031.8
140°	1064.5	1064.7	1064.9	1065.2	1064.9	1064.7	1064.5	1064.3	1063.8	1063.2	1062.5
142.5°	1092.2	1092.2	1092.3	1092.3	1092.3	1092.2	1092.2	1092.1	1091.9	1091.4	1090.9
145°	1132.7	1133.1	1133.6	1134.0	1133.6	1133.1	1132.7	1132.3	1131.9	1131.7	1131.5
147.5°	1167.9	1168.1	1168.4	1168.6	1168.4	1168.1	1167.9	1167.7	1167.5	1167.3	1167.1
150°	1190.3	1190.5	1190.7	1190.9	1190.7	1190.5	1190.3	1190.0	1189.9	1189.9	1189.9
152.5°	1210.5	1210.4	1210.2	1210.1	1210.2	1210.4	1210.5	1210.6	1210.5	1210.2	1209.8
155°	1237.9	1237.2	1236.5	1235.9	1236.5	1237.2	1237.9	1238.5	1238.4	1237.5	1236.6
157.5°	1260.9	1259.7	1258.6	1257.4	1258.6	1259.7	1260.9	1262.0	1262.0	1260.9	1259.7
160°	1275.8	1274.5	1273.1	1271.8	1273.1	1274.5	1275.8	1277.1	1277.1	1275.8	1274.5
162.5°	1287.5	1286.0	1284.5	1283.0	1284.5	1286.0	1287.5	1289.0	1289.1	1287.8	1286.4
165°	1304.7	1302.7	1300.7	1298.7	1300.7	1302.7	1304.7	1306.7	1306.8	1305.1	1303.3
167.5°	1317.2	1315.0	1312.7	1310.5	1312.7	1315.0	1317.2	1319.4	1319.5	1317.6	1315.6
170°	1324.4	1322.2	1319.9	1317.7	1319.9	1322.2	1324.4	1326.6	1326.8	1325.0	1323.3
172.5°	1328.9	1326.5	1324.1	1321.7	1324.1	1326.5	1328.9	1331.3	1331.6	1329.8	1328.1
175°	1334.7	1332.0	1329.4	1326.7	1329.4	1332.0	1334.7	1337.3	1337.7	1335.7	1333.7
177.5°	1336.3	1334.2	1332.0	1329.9	1332.0	1334.2	1336.3	1338.4	1338.8	1337.3	1335.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	897.8	899.1	904.1	908.7	914.3	918.4	921.2	924.3	930.8	936.1	941.1
5°	841.2	843.1	853.3	860.3	872.3	882.8	891.0	899.9	910.5	924.8	938.1
7.5°	791.3	798.6	809.6	821.0	833.3	847.0	859.0	872.5	890.6	910.4	930.8
10°	763.0	771.2	782.8	796.1	807.7	823.7	838.5	854.4	875.0	899.2	923.3
12.5°	734.7	748.1	757.0	772.7	785.3	798.5	814.2	835.1	859.2	884.5	913.6
15°	699.2	706.6	723.7	732.3	750.1	770.4	785.9	807.0	830.3	863.8	896.4
17.5°	658.2	668.0	681.6	697.9	718.5	734.3	753.7	775.3	804.7	837.9	878.9
20°	631.5	639.7	656.4	674.3	696.1	712.8	733.4	754.4	784.8	820.2	863.0
22.5°	607.5	615.4	633.0	649.7	670.9	691.3	712.9	737.3	766.4	803.7	847.4
25°	570.4	580.9	596.5	613.6	633.8	657.2	680.5	702.3	733.4	772.7	819.4
27.5°	537.5	545.9	557.2	576.6	599.6	622.1	645.3	672.7	702.6	744.2	792.6
30°	516.3	524.1	535.4	553.3	574.7	598.8	622.9	649.4	680.5	721.7	771.2
32.5°	499.5	505.4	515.5	531.5	551.0	576.4	600.2	627.6	660.3	700.9	749.1
35°	474.7	479.7	483.6	498.8	516.3	539.7	563.8	593.0	624.5	663.0	711.2
37.5°	450.3	452.0	457.7	467.7	484.6	506.1	528.5	557.2	589.5	628.7	672.2
40°	435.4	436.2	439.7	449.0	463.8	484.0	505.8	534.2	564.9	601.9	645.1
42.5°	420.8	420.3	423.5	430.0	443.9	462.2	483.7	509.6	540.4	574.5	615.2
45°	397.6	397.6	396.9	402.3	413.6	431.5	449.4	474.3	500.0	533.4	567.7
47.5°	373.5	371.3	372.0	374.8	384.3	399.0	417.1	437.5	460.1	488.5	518.5
50°	358.0	354.8	353.7	356.8	365.3	378.2	395.3	413.2	434.6	459.5	485.2
52.5°	340.8	337.7	335.6	337.8	345.7	357.6	373.2	388.9	408.1	428.4	450.6
55°	314.4	310.9	309.7	310.5	316.3	325.7	338.9	353.3	367.7	384.4	400.0
57.5°	288.3	282.6	281.5	281.1	285.1	293.7	304.7	317.2	327.7	337.8	354.4
60°	271.2	264.2	261.9	261.5	264.6	271.6	281.7	294.1	301.5	308.5	322.9
62.5°	252.8	246.1	241.0	241.5	244.3	251.0	259.9	268.9	273.8	281.5	291.2
65°	224.5	215.9	212.0	210.9	212.4	217.9	224.9	230.7	236.2	239.3	248.6
67.5°	196.2	189.0	183.3	181.9	181.2	184.9	190.6	194.2	198.0	200.8	206.3
70°	176.3	170.0	163.0	160.7	160.3	163.4	168.9	169.3	174.7	175.9	181.7
72.5°	156.6	148.9	144.0	141.7	140.1	142.9	146.5	147.5	150.4	152.5	155.6
75°	126.1	120.2	115.6	112.1	110.9	112.4	112.4	114.4	116.3	117.5	121.0
77.5°	99.2	92.5	87.0	85.0	83.6	82.6	83.4	84.6	83.7	85.7	86.5
80°	80.5	73.5	69.3	68.5	66.1	64.2	63.8	65.0	63.4	64.2	66.5
82.5°	62.2	57.7	53.1	52.3	49.3	48.3	47.9	47.2	47.2	47.1	47.5
85°	37.0	34.2	31.1	29.2	28.0	26.1	26.1	25.3	24.5	23.7	24.1
87.5°	19.6	18.7	16.8	15.5	14.5	12.9	12.5	11.1	10.3	9.5	8.7
90°	23.3	22.0	20.2	18.4	16.6	14.9	12.8	10.3	7.9	5.4	3.0
92.5°	22.5	21.2	19.4	17.6	15.8	14.1	13.1	13.0	12.8	12.7	12.6
95°	23.3	22.0	21.7	21.5	21.3	21.1	24.7	32.3	39.8	47.4	54.9
97.5°	26.5	26.4	51.1	75.9	100.6	125.4	135.4	130.7	126.0	121.3	116.6
100°	40.2	43.9	74.5	105.2	135.8	166.4	179.7	175.7	171.7	167.7	163.7
102.5°	170.9	211.6	215.6	219.6	223.6	227.6	228.1	225.2	222.3	219.4	216.4
105°	313.5	311.5	310.4	309.2	308.1	307.0	305.8	304.5	303.1	301.8	300.5
107.5°	389.3	388.3	386.8	385.3	383.8	382.3	381.2	380.5	379.9	379.2	378.5
110°	440.7	440.2	438.9	437.6	436.2	434.9	433.9	433.2	432.6	431.9	431.3



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	490.5	490.5	489.9	489.3	488.7	488.1	487.2	486.0	484.8	483.6	482.4
115°	563.5	563.0	563.2	563.5	563.7	563.9	563.7	563.0	562.4	561.7	561.0
117.5°	638.0	638.1	637.6	637.1	636.6	636.1	635.5	634.6	633.7	632.8	631.9
120°	683.3	682.8	683.0	683.3	683.5	683.7	683.4	682.5	681.6	680.7	679.8
122.5°	728.6	728.3	728.0	727.7	727.4	727.1	726.7	726.1	725.6	725.1	724.5
125°	791.3	790.6	791.1	791.5	792.0	792.4	792.2	791.3	790.4	789.5	788.6
127.5°	854.8	854.9	853.9	852.9	851.9	850.8	850.2	850.0	849.8	849.5	849.3
130°	892.7	892.5	891.8	891.1	890.5	889.8	889.3	889.1	888.9	888.7	888.5
132.5°	930.2	930.0	929.1	928.3	927.5	926.6	926.0	925.6	925.2	924.8	924.4
135°	981.7	981.3	980.4	979.5	978.6	977.7	977.4	977.6	977.9	978.1	978.3
137.5°	1031.3	1030.8	1029.8	1028.9	1027.9	1026.9	1026.4	1026.3	1026.2	1026.1	1026.0
140°	1061.8	1061.2	1060.7	1060.3	1059.8	1059.4	1058.9	1058.5	1058.1	1057.6	1057.2
142.5°	1090.4	1089.9	1089.6	1089.4	1089.1	1088.8	1088.3	1087.5	1086.7	1085.9	1085.1
145°	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1130.7	1130.0	1129.4	1128.7	1128.0
147.5°	1167.0	1166.8	1167.0	1167.2	1167.4	1167.7	1167.2	1165.9	1164.7	1163.4	1162.2
150°	1189.9	1189.9	1190.2	1190.4	1190.6	1190.8	1190.5	1189.6	1188.7	1187.8	1186.9
152.5°	1209.5	1209.1	1209.5	1209.9	1210.3	1210.7	1210.5	1209.8	1209.1	1208.4	1207.7
155°	1235.7	1234.9	1235.5	1236.2	1236.9	1237.5	1237.7	1237.5	1237.3	1237.1	1236.9
157.5°	1258.6	1257.4	1258.2	1258.9	1259.7	1260.4	1260.9	1261.0	1261.1	1261.3	1261.4
160°	1273.1	1271.8	1272.0	1272.2	1272.5	1272.7	1273.1	1273.8	1274.5	1275.1	1275.8
162.5°	1285.1	1283.8	1284.0	1284.2	1284.4	1284.7	1285.2	1286.0	1286.9	1287.7	1288.6
165°	1301.5	1299.7	1299.7	1299.7	1299.7	1299.7	1300.3	1301.4	1302.5	1303.6	1304.7
167.5°	1313.7	1311.7	1311.9	1312.0	1312.1	1312.3	1312.9	1314.1	1315.2	1316.4	1317.5
170°	1321.5	1319.7	1319.5	1319.3	1319.0	1318.8	1319.4	1320.7	1322.0	1323.4	1324.7
172.5°	1326.3	1324.5	1324.3	1324.1	1323.8	1323.6	1324.2	1325.5	1326.8	1328.2	1329.5
175°	1331.7	1329.7	1329.5	1329.3	1329.0	1328.8	1329.4	1330.7	1332.0	1333.4	1334.7
177.5°	1334.5	1333.1	1332.7	1332.4	1332.0	1331.7	1332.1	1333.4	1334.6	1335.8	1337.1
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	945.5	948.6	952.6	959.5	962.0	965.1	969.4	969.1	970.4	975.0	985.0
5°	949.0	961.0	972.7	986.7	1001.5	1011.2	1024.5	1032.6	1040.8	1051.3	1069.2
7.5°	950.4	969.5	990.9	1015.5	1037.4	1062.6	1082.3	1100.8	1117.5	1139.7	1161.0
10°	948.2	973.9	1001.5	1032.6	1065.7	1093.7	1119.0	1147.8	1172.3	1199.1	1223.3
12.5°	944.1	975.1	1012.1	1046.9	1085.6	1127.0	1158.5	1187.6	1220.2	1251.1	1288.3
15°	935.0	977.4	1020.6	1066.5	1118.2	1166.1	1211.6	1249.3	1284.4	1330.7	1379.3
17.5°	923.3	969.0	1023.5	1079.1	1133.2	1187.9	1244.2	1300.9	1345.1	1402.6	1440.7
20°	912.4	965.3	1021.3	1087.5	1141.6	1209.7	1265.7	1320.5	1381.2	1438.4	1484.0
22.5°	897.1	955.0	1014.5	1080.3	1151.5	1219.6	1284.4	1343.9	1404.6	1466.8	1521.9
25°	877.8	930.3	1000.7	1075.4	1146.2	1220.2	1294.5	1369.2	1434.5	1500.3	1551.7
27.5°	844.8	911.1	976.7	1053.8	1132.5	1216.1	1295.6	1373.8	1442.2	1496.3	1528.2
30°	828.0	885.5	956.8	1034.2	1119.4	1209.3	1292.1	1368.8	1432.6	1475.8	1488.6
32.5°	803.1	862.5	932.2	1012.4	1102.6	1194.9	1281.2	1353.5	1406.8	1429.4	1413.9
35°	766.1	819.8	890.2	972.3	1066.1	1164.5	1249.7	1310.8	1338.1	1316.7	1263.3
37.5°	721.7	775.0	845.7	926.3	1023.4	1123.4	1200.5	1244.4	1235.4	1182.2	1102.7
40°	690.6	740.4	807.7	894.9	989.4	1089.8	1157.5	1181.3	1156.4	1080.1	995.7
42.5°	656.1	704.6	772.2	856.3	956.4	1049.0	1108.0	1110.0	1068.3	977.1	892.3
45°	603.5	649.8	713.6	801.1	893.7	980.9	1019.8	1000.7	923.7	835.7	750.5
47.5°	551.6	591.7	654.6	737.7	825.6	899.0	918.3	884.0	801.9	716.5	637.5
50°	513.6	554.1	613.2	692.6	777.4	840.8	850.1	804.6	724.1	638.1	576.2
52.5°	477.2	517.3	574.3	647.7	725.4	782.6	782.9	730.2	650.0	573.4	515.8
55°	423.7	459.9	511.3	577.0	646.3	691.0	680.1	625.6	556.0	489.5	439.3
57.5°	372.2	403.7	451.0	505.9	566.9	603.8	585.7	533.3	471.1	414.7	376.6
60°	338.9	368.8	409.3	461.1	512.4	541.2	524.1	476.6	419.4	373.9	340.8
62.5°	306.5	331.8	370.7	415.6	463.2	484.6	469.3	422.5	373.1	331.9	305.0
65°	260.7	281.3	312.4	351.0	385.6	403.9	391.0	347.4	309.7	280.1	258.7
67.5°	217.9	234.0	257.6	288.5	317.9	327.8	316.1	285.7	253.8	230.1	215.0
70°	188.3	203.5	223.3	247.1	272.7	283.3	271.6	247.5	221.4	199.6	184.8
72.5°	162.5	174.2	191.0	211.3	231.3	241.9	233.9	210.7	188.7	172.5	159.9
75°	123.7	133.8	145.5	159.9	175.5	182.5	175.5	159.5	144.3	132.3	123.3
77.5°	90.0	95.4	104.4	115.2	124.9	130.3	124.2	113.4	104.1	95.9	91.4
80°	68.5	72.4	78.6	87.2	93.8	98.8	94.9	86.0	78.6	73.1	71.2
82.5°	49.8	52.4	56.5	62.9	67.3	69.9	68.2	61.7	58.7	53.8	51.9
85°	24.5	26.1	28.8	30.7	34.6	35.0	35.4	32.7	30.0	28.8	27.2
87.5°	9.5	10.3	11.7	13.1	14.8	15.5	15.5	15.9	15.0	14.9	14.0
90°	5.4	7.9	10.3	12.8	14.9	16.6	18.4	20.2	22.0	23.3	24.6
92.5°	12.7	12.8	13.0	13.1	14.1	15.8	17.6	19.4	21.2	22.5	23.8
95°	47.4	39.8	32.3	24.7	21.1	21.3	21.5	21.7	22.0	23.3	24.6
97.5°	121.3	126.0	130.7	135.4	125.4	100.6	75.9	51.1	26.4	26.5	26.6
100°	167.7	171.7	175.7	179.7	166.4	135.8	105.2	74.5	43.9	40.2	36.4
102.5°	219.4	222.3	225.2	228.1	227.6	223.6	219.6	215.6	211.6	170.9	130.3
105°	301.8	303.1	304.5	305.8	307.0	308.1	309.2	310.4	311.5	313.5	315.5
107.5°	379.2	379.9	380.5	381.2	382.3	383.8	385.3	386.8	388.3	389.3	390.3
110°	431.9	432.6	433.2	433.9	434.9	436.2	437.6	438.9	440.2	440.7	441.1





TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	483.6	484.8	486.0	487.2	488.1	488.7	489.3	489.9	490.5	490.5	490.4
115°	561.7	562.4	563.0	563.7	563.9	563.7	563.5	563.2	563.0	563.5	563.9
117.5°	632.8	633.7	634.6	635.5	636.1	636.6	637.1	637.6	638.1	638.0	637.9
120°	680.7	681.6	682.5	683.4	683.7	683.5	683.3	683.0	682.8	683.3	683.7
122.5°	725.1	725.6	726.1	726.7	727.1	727.4	727.7	728.0	728.3	728.6	728.9
125°	789.5	790.4	791.3	792.2	792.4	792.0	791.5	791.1	790.6	791.3	792.0
127.5°	849.5	849.8	850.0	850.2	850.8	851.9	852.9	853.9	854.9	854.8	854.7
130°	888.7	888.9	889.1	889.3	889.8	890.5	891.1	891.8	892.5	892.7	892.9
132.5°	924.8	925.2	925.6	926.0	926.6	927.5	928.3	929.1	930.0	930.2	930.4
135°	978.1	977.9	977.6	977.4	977.7	978.6	979.5	980.4	981.3	981.7	982.2
137.5°	1026.1	1026.2	1026.3	1026.4	1026.9	1027.9	1028.9	1029.8	1030.8	1031.3	1031.8
140°	1057.6	1058.1	1058.5	1058.9	1059.4	1059.8	1060.3	1060.7	1061.2	1061.8	1062.5
142.5°	1085.9	1086.7	1087.5	1088.3	1088.8	1089.1	1089.4	1089.6	1089.9	1090.4	1090.9
145°	1128.7	1129.4	1130.0	1130.7	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3	1131.5
147.5°	1163.4	1164.7	1165.9	1167.2	1167.7	1167.4	1167.2	1167.0	1166.8	1167.0	1167.1
150°	1187.8	1188.7	1189.6	1190.5	1190.8	1190.6	1190.4	1190.2	1189.9	1189.9	1189.9
152.5°	1208.4	1209.1	1209.8	1210.5	1210.7	1210.3	1209.9	1209.5	1209.1	1209.5	1209.8
155°	1237.1	1237.3	1237.5	1237.7	1237.5	1236.9	1236.2	1235.5	1234.9	1235.7	1236.6
157.5°	1261.3	1261.1	1261.0	1260.9	1260.4	1259.7	1258.9	1258.2	1257.4	1258.6	1259.7
160°	1275.1	1274.5	1273.8	1273.1	1272.7	1272.5	1272.2	1272.0	1271.8	1273.1	1274.5
162.5°	1287.7	1286.9	1286.0	1285.2	1284.7	1284.4	1284.2	1284.0	1283.8	1285.1	1286.4
165°	1303.6	1302.5	1301.4	1300.3	1299.7	1299.7	1299.7	1299.7	1299.7	1301.5	1303.3
167.5°	1316.4	1315.2	1314.1	1312.9	1312.3	1312.1	1312.0	1311.9	1311.7	1313.7	1315.6
170°	1323.4	1322.0	1320.7	1319.4	1318.8	1319.0	1319.3	1319.5	1319.7	1321.5	1323.3
172.5°	1328.2	1326.8	1325.5	1324.2	1323.6	1323.8	1324.1	1324.3	1324.5	1326.3	1328.1
175°	1333.4	1332.0	1330.7	1329.4	1328.8	1329.0	1329.3	1329.5	1329.7	1331.7	1333.7
177.5°	1335.8	1334.6	1333.4	1332.1	1331.7	1332.0	1332.4	1332.7	1333.1	1334.5	1335.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	939.2	939.2	939.2	939.2	939.2	939.2	939.2
2.5°	990.0	990.6	993.4	995.6	996.2	999.3	999.6
5°	1077.0	1083.6	1096.4	1097.6	1099.5	1109.7	1101.9
7.5°	1178.9	1195.7	1206.9	1216.8	1220.4	1224.8	1223.9
10°	1244.3	1269.2	1281.6	1301.5	1302.3	1307.3	1304.2
12.5°	1310.0	1338.9	1361.6	1365.3	1381.9	1384.5	1388.9
15°	1403.0	1433.8	1465.3	1476.6	1499.5	1505.0	1513.5
17.5°	1490.5	1521.9	1544.0	1573.2	1582.6	1595.2	1586.7
20°	1538.4	1572.7	1600.7	1623.6	1633.4	1640.4	1639.6
22.5°	1567.4	1601.9	1624.6	1642.0	1651.1	1654.1	1653.9
25°	1585.5	1605.4	1612.4	1619.0	1608.9	1605.4	1606.9
27.5°	1535.1	1529.9	1511.7	1487.7	1462.8	1443.0	1432.3
30°	1465.7	1435.3	1407.7	1359.5	1334.5	1319.8	1306.5
32.5°	1367.3	1319.2	1266.1	1221.9	1193.5	1171.6	1168.3
35°	1198.8	1126.4	1061.4	1007.3	979.3	955.6	950.1
37.5°	1019.2	944.0	885.5	837.8	807.7	791.0	775.4
40°	899.9	835.4	777.8	737.3	714.4	702.3	692.6
42.5°	808.1	749.1	691.9	661.0	640.3	632.9	627.2
45°	681.3	626.4	586.7	563.4	551.3	538.9	533.0
47.5°	579.7	535.1	508.9	489.1	476.2	468.8	465.0
50°	522.1	485.6	462.2	447.1	435.4	429.5	426.4
52.5°	471.1	441.1	421.5	409.4	401.5	397.2	395.9
55°	405.8	382.9	370.4	359.9	354.1	350.2	348.6
57.5°	352.7	335.1	325.0	316.3	314.1	310.8	309.7
60°	317.9	304.3	295.7	289.9	287.9	284.0	284.8
62.5°	287.1	275.9	268.6	265.3	262.7	259.4	260.5
65°	242.8	234.6	230.7	227.6	224.5	222.6	224.1
67.5°	203.7	198.1	192.8	191.0	189.5	189.2	187.5
70°	178.2	173.5	168.9	167.7	167.7	166.1	165.7
72.5°	153.6	150.2	147.1	146.2	145.0	145.6	144.0
75°	118.7	115.9	114.8	113.6	113.2	113.2	112.1
77.5°	87.7	85.7	83.8	83.8	82.4	81.9	81.7
80°	66.5	65.8	64.2	64.2	63.4	63.8	63.0
82.5°	50.0	48.9	48.6	48.0	46.9	47.0	46.2
85°	26.8	25.7	25.3	24.1	23.3	24.1	23.3
87.5°	14.5	14.5	14.4	13.8	13.6	13.7	12.8
90°	26.0	27.3	28.2	28.6	29.1	29.5	29.9
92.5°	25.2	26.5	27.2	27.3	27.4	27.5	27.6
95°	26.0	27.3	28.1	28.3	28.5	28.7	28.9
97.5°	26.8	26.9	27.1	27.3	27.5	27.7	28.0
100°	32.6	28.8	27.1	27.3	27.5	27.7	28.0
102.5°	89.6	48.9	28.6	28.6	28.7	28.7	28.8
105°	317.4	319.4	316.5	308.5	300.5	292.5	284.5
107.5°	391.3	392.2	393.1	394.0	394.8	395.7	396.5
110°	441.6	442.0	442.6	443.2	443.9	444.6	445.2



TEST NUMBER: P332562

CATALOG NUMBER: SA4XXDIP-C575D1035U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	490.3	490.2	490.6	491.4	492.3	493.1	493.9
115°	564.4	564.8	565.0	565.0	565.0	565.0	565.0
117.5°	637.8	637.7	637.7	637.6	637.5	637.4	637.3
120°	684.1	684.6	684.6	684.1	683.7	683.3	682.8
122.5°	729.1	729.4	729.3	728.9	728.4	728.0	727.5
125°	792.6	793.3	793.7	794.0	794.2	794.4	794.6
127.5°	854.5	854.4	854.2	854.1	853.9	853.7	853.5
130°	893.1	893.3	893.5	893.5	893.5	893.5	893.5
132.5°	930.7	930.9	930.9	930.7	930.5	930.4	930.2
135°	982.6	983.1	983.5	984.0	984.4	984.8	985.3
137.5°	1032.3	1032.8	1032.9	1032.8	1032.7	1032.5	1032.4
140°	1063.2	1063.8	1064.3	1064.5	1064.7	1064.9	1065.2
142.5°	1091.4	1091.9	1092.1	1092.2	1092.2	1092.3	1092.3
145°	1131.7	1131.9	1132.3	1132.7	1133.1	1133.6	1134.0
147.5°	1167.3	1167.5	1167.7	1167.9	1168.1	1168.4	1168.6
150°	1189.9	1189.9	1190.0	1190.3	1190.5	1190.7	1190.9
152.5°	1210.2	1210.5	1210.6	1210.5	1210.4	1210.2	1210.1
155°	1237.5	1238.4	1238.5	1237.9	1237.2	1236.5	1235.9
157.5°	1260.9	1262.0	1262.0	1260.9	1259.7	1258.6	1257.4
160°	1275.8	1277.1	1277.1	1275.8	1274.5	1273.1	1271.8
162.5°	1287.8	1289.1	1289.0	1287.5	1286.0	1284.5	1283.0
165°	1305.1	1306.8	1306.7	1304.7	1302.7	1300.7	1298.7
167.5°	1317.6	1319.5	1319.4	1317.2	1315.0	1312.7	1310.5
170°	1325.0	1326.8	1326.6	1324.4	1322.2	1319.9	1317.7
172.5°	1329.8	1331.6	1331.3	1328.9	1326.5	1324.1	1321.7
175°	1335.7	1337.7	1337.3	1334.7	1332.0	1329.4	1326.7
177.5°	1337.3	1338.8	1338.4	1336.3	1334.2	1332.0	1329.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7

(END OF REPORT)