

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332552

Luminaire Tested: **SA4XXDIP-C575D590U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332552
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D590U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4605.4 lumens
Efficiency: N/A
Efficacy: 140.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332552
CATALOG NUMBER: SA4XXDIP-C575D590U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332552

CATALOG NUMBER: SA4XXDIP-C575D590U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54				
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51	46				
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	44	43	38				
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	39	36	32				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28				
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24				
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	28	24	21	19				
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332552

CATALOG NUMBER: SA4XXDIP-C575D590U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.0
10°-20°	257.7	5.6
20°-30°	379.3	8.2
30°-40°	440.9	9.6
40°-50°	440.9	9.6
50°-60°	385.7	8.4
60°-70°	286.4	6.2
70°-80°	162.7	3.5
80°-90°	48.6	1.1
90°-100°	209.7	4.6
100°-110°	436.5	9.5
110°-120°	391.0	8.5
120°-130°	328.9	7.1
130°-140°	274.2	6.0
140°-150°	209.5	4.5
150°-160°	147.2	3.2
160°-170°	86.6	1.9
170°-180°	28.2	0.6
0°-30°	728.4	15.8
0°-40°	1169.3	25.4
0°-60°	1996.0	43.3
0°-90°	2493.7	54.1
90°-120°	1037.2	22.5
90°-150°	1849.7	40.2
90°-180°	2112.0	45.9
0°-180°	4605.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	1	5	10	11	12	3
95°	19	59	465	230	139	21
105°	67	97	374	806	803	71
115°	118	148	334	641	771	117
125°	164	194	332	546	615	146
135°	194	232	329	484	550	150
145°	224	257	327	408	449	141
155°	255	275	318	360	376	118
165°	278	286	305	323	328	78
175°	290	290	293	297	296	27
180°	290	290	290	290	290	



TEST NUMBER: P332552

CATALOG NUMBER: SA4XXDIP-C575D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.3	16.4	16.6	16.6	16.5	16.4	17.0	16.8	16.9	17.0	16.9
90°	0.6	1.7	3.4	4.0	4.6	4.6	8.0	8.0	9.1	10.3	9.7
92.5°	6.5	9.5	14.8	21.8	30.1	42.0	71.0	115.2	158.4	180.9	150.7
95°	18.8	20.5	26.2	33.7	47.3	71.3	120.9	214.5	350.8	464.9	478.0
97.5°	33.8	33.8	38.7	45.5	57.3	77.4	115.6	192.8	328.4	489.7	600.6
100°	43.4	43.4	47.3	54.2	65.0	83.3	116.9	181.4	297.8	458.6	604.7
102.5°	52.5	53.4	56.9	63.3	73.7	91.0	121.5	178.2	277.2	419.9	570.4
105°	66.7	68.5	71.3	78.2	88.4	105.0	132.3	179.7	259.6	374.2	508.3
107.5°	82.5	83.6	86.5	93.8	103.6	119.9	145.0	188.1	256.4	348.7	458.1
110°	93.0	94.1	97.0	103.8	114.1	129.5	154.6	194.5	257.3	340.0	433.0



TEST NUMBER: P332552

CATALOG NUMBER: SA4XXDIP-C575D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	103.0	104.2	107.5	113.9	124.1	139.5	163.7	201.4	260.0	335.9	418.8
115°	117.5	119.2	123.2	128.9	139.8	155.2	178.0	212.2	265.3	333.7	405.6
117.5°	132.6	134.2	137.7	144.0	154.1	170.1	191.8	223.3	270.8	333.1	399.7
120°	142.6	143.8	147.7	154.0	163.7	179.7	201.4	231.0	275.0	333.1	396.5
122.5°	151.7	152.9	156.9	162.7	173.3	188.8	210.5	238.3	279.1	332.7	392.8
125°	163.7	166.0	169.4	175.7	186.5	202.5	223.0	249.3	285.2	332.0	386.8
127.5°	174.3	176.2	180.3	187.4	198.7	214.8	234.7	258.8	290.1	330.7	378.7
130°	180.3	182.5	187.1	195.7	206.5	223.0	242.4	264.7	293.8	330.3	373.6
132.5°	186.2	188.0	194.0	202.1	213.8	229.4	248.8	270.6	297.0	329.8	369.1
135°	194.5	196.8	202.5	212.2	224.2	239.0	257.8	278.4	301.8	329.1	362.2
137.5°	202.9	205.0	211.3	220.5	233.0	247.1	264.7	283.9	304.6	329.0	356.3
140°	208.8	210.5	216.8	226.5	238.4	252.1	269.3	287.5	306.9	328.6	353.1
142.5°	215.2	216.9	222.7	231.9	243.5	256.7	273.4	290.2	308.7	328.6	350.4
145°	224.2	225.9	231.6	239.6	250.4	263.0	277.8	293.2	309.8	327.4	345.7
147.5°	234.3	234.9	239.9	248.1	257.2	268.5	282.4	295.8	310.3	325.4	341.5
150°	240.7	241.3	245.9	252.7	261.3	272.1	284.7	297.2	310.3	324.0	338.3
152.5°	246.7	246.8	251.3	257.7	265.4	275.3	286.5	298.1	309.4	321.7	334.6
155°	255.0	255.6	259.0	264.7	271.0	279.5	289.2	298.9	308.0	318.3	329.1
157.5°	263.1	263.1	266.3	270.7	276.2	282.9	291.2	298.9	306.6	314.8	323.6
160°	268.1	268.1	270.4	274.4	278.9	285.2	292.1	298.9	305.2	312.0	319.5
162.5°	272.7	272.2	274.0	277.6	281.7	286.6	293.0	298.9	303.8	309.3	315.8
165°	277.8	277.8	278.9	281.8	284.7	288.1	293.2	297.8	301.2	305.2	309.8
167.5°	282.9	282.4	282.9	285.1	286.7	289.3	293.1	296.4	298.5	301.1	304.3
170°	285.2	284.7	285.2	286.9	288.1	289.8	292.6	295.5	296.6	298.3	300.6
172.5°	287.5	286.9	287.0	288.3	289.0	290.2	292.2	294.6	294.8	295.6	297.4
175°	289.8	289.2	289.2	289.8	290.4	290.4	291.5	293.2	292.6	292.6	293.8
177.5°	290.8	290.4	289.9	290.4	290.4	290.4	290.8	291.7	290.8	290.8	291.3
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332552

CATALOG NUMBER: SA4XXDIP-C575D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	17.0	17.1	17.2	17.2	17.3	17.5	17.3	17.3
90°	10.3	10.8	11.4	11.4	12.0	12.5	12.0	12.0
92.5°	112.0	84.3	67.1	55.7	48.9	45.9	43.9	43.9
95°	422.7	334.3	257.8	202.5	174.6	156.9	146.6	139.2
97.5°	624.5	591.7	535.9	476.3	435.4	401.0	383.9	372.0
100°	688.0	699.4	671.4	629.2	579.6	544.8	527.7	523.1
102.5°	684.8	741.4	749.5	731.9	701.4	676.2	658.2	654.5
105°	638.9	737.6	794.1	817.5	818.6	814.0	806.0	802.6
107.5°	573.8	678.8	758.4	809.2	837.4	850.4	856.1	857.6
110°	534.5	633.2	715.9	778.7	819.2	843.1	853.4	858.5



TEST NUMBER: P332552

CATALOG NUMBER: SA4XXDIP-C575D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	505.8	593.0	671.2	733.9	779.9	808.9	823.3	831.6
115°	476.9	547.1	613.8	668.6	713.6	747.9	766.1	770.7
117.5°	462.7	520.8	573.3	619.7	658.2	686.9	705.4	709.0
120°	456.4	509.4	555.0	595.5	628.1	653.2	668.0	674.3
122.5°	450.9	502.1	543.6	579.1	606.6	628.1	640.6	646.9
125°	441.5	490.6	529.9	561.3	584.1	600.7	611.5	614.9
127.5°	430.1	477.0	516.3	546.0	569.0	583.7	592.8	596.2
130°	421.0	466.1	504.8	535.1	558.5	572.7	581.9	585.3
132.5°	411.4	453.7	491.6	521.8	544.8	560.9	569.5	573.0
135°	398.2	435.3	470.0	498.6	521.4	537.4	546.5	549.9
137.5°	386.2	417.6	446.9	472.7	494.0	509.8	517.3	521.4
140°	379.3	406.2	431.8	455.8	475.8	488.3	496.3	500.9
142.5°	373.0	396.6	418.6	439.4	457.0	468.7	475.8	478.9
145°	363.9	383.3	400.5	416.4	430.7	440.4	446.1	448.9
147.5°	356.5	371.9	385.6	398.2	408.7	417.0	421.3	422.4
150°	352.0	365.1	376.5	386.8	395.9	403.3	406.7	407.3
152.5°	346.9	358.2	368.7	377.2	384.9	391.0	393.0	393.6
155°	339.4	348.5	357.1	363.9	369.7	374.2	375.9	375.9
157.5°	331.3	339.0	346.1	351.6	356.0	359.4	360.4	360.4
160°	326.3	332.6	338.8	343.4	346.8	350.3	350.8	350.8
162.5°	321.3	326.6	331.5	335.7	338.2	341.6	342.2	341.7
165°	314.3	317.7	321.7	324.6	326.9	329.1	328.6	328.0
167.5°	307.6	310.2	313.4	315.1	316.3	317.7	317.6	317.2
170°	303.5	305.2	307.5	309.2	310.3	310.9	310.3	310.3
172.5°	299.8	301.1	302.5	303.7	304.4	305.0	304.4	303.5
175°	294.9	295.5	296.6	296.6	296.6	297.8	296.6	295.5
177.5°	291.7	292.2	292.2	292.6	292.2	292.6	291.7	290.8
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4

(END OF REPORT)