

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332559

Luminaire Tested: **SA4XXDIP-C575D810U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332559  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D810U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5728.8 lumens  
Efficiency: N/A  
Efficacy: 149.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332559  
CATALOG NUMBER: SA4XXDIP-C575D810U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332559

CATALOG NUMBER: SA4XXDIP-C575D810U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42				37	
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36				31	
3	80	71	63	58	73	65	58	53	54	49	45	44	41	38	35	32	30				26	
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26				22	
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23				19	
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20				17	
7	57	45	37	32	52	41	34	29	35	29	26	29	25	22	23	20	18				15	
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16				13	
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14				12	
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13				11	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332559

CATALOG NUMBER: SA4XXDIP-C575D810U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.5	1.6
10°-20°	257.7	4.5
20°-30°	379.3	6.6
30°-40°	440.9	7.7
40°-50°	440.9	7.7
50°-60°	385.7	6.7
60°-70°	286.4	5.0
70°-80°	162.7	2.8
80°-90°	50.0	0.9
90°-100°	35.8	0.6
100°-110°	228.0	4.0
110°-120°	436.1	7.6
120°-130°	553.6	9.7
130°-140°	592.3	10.3
140°-150°	553.9	9.7
150°-160°	446.7	7.8
160°-170°	288.1	5.0
170°-180°	99.3	1.7
0°-30°	728.4	12.7
0°-40°	1169.3	20.4
0°-60°	1996.0	34.8
0°-90°	2495.1	43.6
90°-120°	699.8	12.2
90°-150°	2399.6	41.9
90°-180°	3234.0	56.5
0°-180°	5728.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	2	11	17	22	24	4
95°	43	18	17	22	23	55
105°	235	240	244	249	223	246
115°	439	442	441	442	443	432
125°	618	621	619	622	622	551
135°	766	766	769	770	772	590
145°	884	886	886	887	888	552
155°	969	969	967	970	968	446
165°	1022	1018	1018	1024	1017	289
175°	1045	1041	1042	1048	1039	100
180°	1045	1045	1045	1045	1045	



TEST NUMBER: P332559

CATALOG NUMBER: SA4XXDIP-C575D810U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.7	16.9	17.1	17.4	17.6	17.8	18.0	18.1	18.2	18.4	18.6
90°	2.3	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2
92.5°	9.9	10.0	10.1	10.2	10.3	11.0	12.4	13.8	15.2	16.6	17.6
95°	43.0	37.1	31.2	25.3	19.4	16.5	16.7	16.9	17.0	17.2	18.2
97.5°	91.3	95.0	98.7	102.4	106.1	98.2	78.8	59.4	40.0	20.6	20.7
100°	128.2	131.4	134.5	137.6	140.7	130.3	106.3	82.4	58.4	34.4	31.4
102.5°	169.5	171.8	174.1	176.4	178.7	178.3	175.1	172.0	168.9	165.8	133.9
105°	235.3	236.4	237.4	238.5	239.5	240.5	241.3	242.2	243.1	243.9	245.5
107.5°	296.5	297.0	297.5	298.1	298.6	299.4	300.6	301.8	303.0	304.2	304.9
110°	337.8	338.3	338.8	339.3	339.9	340.6	341.7	342.7	343.8	344.8	345.2



TEST NUMBER: P332559

CATALOG NUMBER: SA4XXDIP-C575D810U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.8	378.7	379.7	380.6	381.6	382.3	382.8	383.2	383.7	384.2	384.2
115°	439.4	439.9	440.5	441.0	441.5	441.7	441.5	441.3	441.2	441.0	441.3
117.5°	494.9	495.6	496.3	497.0	497.7	498.3	498.6	499.0	499.4	499.8	499.7
120°	532.5	533.2	533.9	534.6	535.2	535.5	535.3	535.2	535.0	534.8	535.2
122.5°	567.5	567.9	568.3	568.7	569.2	569.5	569.7	570.0	570.2	570.5	570.7
125°	617.7	618.4	619.1	619.8	620.5	620.6	620.3	620.0	619.6	619.3	619.8
127.5°	665.2	665.4	665.6	665.8	665.9	666.4	667.2	668.0	668.8	669.6	669.5
130°	695.9	696.1	696.2	696.4	696.6	696.9	697.4	698.0	698.5	699.0	699.2
132.5°	724.0	724.3	724.7	725.0	725.3	725.8	726.4	727.1	727.7	728.4	728.6
135°	766.3	766.1	765.9	765.7	765.6	765.8	766.5	767.2	767.9	768.6	768.9
137.5°	803.6	803.7	803.8	803.8	803.9	804.3	805.1	805.9	806.6	807.4	807.8
140°	828.0	828.4	828.7	829.1	829.4	829.8	830.1	830.5	830.8	831.1	831.7
142.5°	849.9	850.5	851.2	851.8	852.4	852.8	853.0	853.3	853.5	853.7	854.1
145°	883.5	884.1	884.6	885.1	885.6	885.9	885.9	885.9	885.9	885.9	886.1
147.5°	910.3	911.3	912.2	913.2	914.2	914.6	914.4	914.2	914.0	913.9	914.0
150°	929.7	930.4	931.1	931.8	932.4	932.7	932.5	932.4	932.2	932.0	932.0
152.5°	945.9	946.5	947.0	947.6	948.2	948.3	948.0	947.7	947.3	947.0	947.3
155°	968.8	968.9	969.1	969.3	969.5	969.3	968.8	968.2	967.7	967.2	967.9
157.5°	988.0	987.9	987.8	987.7	987.6	987.2	986.6	986.1	985.5	984.9	985.8
160°	999.3	998.7	998.2	997.7	997.2	996.8	996.7	996.5	996.3	996.1	997.2
162.5°	1009.3	1008.6	1007.9	1007.3	1006.6	1006.2	1006.0	1005.9	1005.7	1005.5	1006.6
165°	1021.9	1021.1	1020.2	1019.3	1018.5	1018.0	1018.0	1018.0	1018.0	1018.0	1019.4
167.5°	1031.9	1031.0	1030.1	1029.2	1028.3	1027.8	1027.7	1027.6	1027.5	1027.4	1028.9
170°	1037.6	1036.5	1035.5	1034.4	1033.4	1033.0	1033.1	1033.3	1033.5	1033.7	1035.0
172.5°	1041.3	1040.3	1039.2	1038.2	1037.2	1036.7	1036.9	1037.1	1037.2	1037.4	1038.8
175°	1045.4	1044.3	1043.3	1042.3	1041.2	1040.8	1041.0	1041.1	1041.3	1041.5	1043.0
177.5°	1047.3	1046.3	1045.3	1044.3	1043.4	1043.0	1043.3	1043.6	1043.9	1044.1	1045.2
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332559

CATALOG NUMBER: SA4XXDIP-C575D810U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	18.8	19.0	19.2	19.4	19.4	19.5	19.6	19.6
90°	19.3	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	18.7	19.7	20.7	21.3	21.4	21.4	21.5	21.6
95°	19.3	20.3	21.4	22.0	22.2	22.3	22.5	22.7
97.5°	20.9	21.0	21.1	21.2	21.4	21.5	21.7	21.9
100°	28.5	25.5	22.6	21.2	21.4	21.5	21.7	21.9
102.5°	102.0	70.2	38.3	22.4	22.4	22.4	22.5	22.5
105°	247.1	248.6	250.2	247.9	241.6	235.3	229.1	222.8
107.5°	305.7	306.4	307.2	307.9	308.6	309.2	309.9	310.6
110°	345.5	345.9	346.2	346.6	347.2	347.7	348.2	348.7





TEST NUMBER: P332559

CATALOG NUMBER: SA4XXDIP-C575D810U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	384.1	384.0	383.9	384.2	384.9	385.6	386.2	386.9
115°	441.7	442.0	442.4	442.6	442.6	442.6	442.6	442.6
117.5°	499.6	499.6	499.5	499.4	499.4	499.3	499.2	499.2
120°	535.5	535.9	536.2	536.2	535.9	535.5	535.2	534.8
122.5°	570.9	571.1	571.3	571.2	570.9	570.5	570.2	569.8
125°	620.3	620.8	621.3	621.7	621.9	622.0	622.2	622.4
127.5°	669.4	669.3	669.2	669.1	668.9	668.8	668.7	668.5
130°	699.4	699.5	699.7	699.8	699.8	699.8	699.8	699.8
132.5°	728.8	728.9	729.1	729.1	729.0	728.8	728.7	728.6
135°	769.3	769.6	770.0	770.3	770.7	771.0	771.4	771.7
137.5°	808.1	808.5	808.9	809.0	808.9	808.8	808.7	808.6
140°	832.2	832.7	833.2	833.6	833.8	833.9	834.1	834.3
142.5°	854.4	854.8	855.2	855.4	855.4	855.5	855.5	855.5
145°	886.2	886.4	886.6	886.8	887.2	887.5	887.9	888.2
147.5°	914.2	914.3	914.4	914.6	914.8	914.9	915.1	915.3
150°	932.0	932.0	932.0	932.1	932.3	932.4	932.6	932.8
152.5°	947.6	947.9	948.1	948.2	948.1	948.0	947.9	947.8
155°	968.6	969.3	970.0	970.1	969.5	969.0	968.5	968.0
157.5°	986.7	987.6	988.5	988.5	987.6	986.7	985.8	984.9
160°	998.2	999.3	1000.3	1000.3	999.3	998.2	997.2	996.1
162.5°	1007.6	1008.6	1009.7	1009.6	1008.4	1007.2	1006.1	1004.9
165°	1020.8	1022.2	1023.6	1023.5	1021.9	1020.4	1018.8	1017.2
167.5°	1030.5	1032.0	1033.5	1033.4	1031.7	1029.9	1028.2	1026.5
170°	1036.4	1037.8	1039.2	1039.0	1037.3	1035.6	1033.8	1032.1
172.5°	1040.2	1041.6	1043.0	1042.7	1040.9	1039.0	1037.1	1035.2
175°	1044.6	1046.2	1047.7	1047.5	1045.4	1043.3	1041.2	1039.1
177.5°	1046.4	1047.5	1048.6	1048.3	1046.6	1045.0	1043.3	1041.6
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4

(END OF REPORT)