

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904866

Luminaire Tested: DFN2DIP-4P2F0-020D020US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904866
REPORT IS A COMBINATION OF REPORTS P899011 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D020US835-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3750.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904866

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904866

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1949	1949	1949
5°	1948	1916	1931
10°	1928	1886	1902
15°	1896	1850	1858
20°	1854	1802	1813
25°	1812	1745	1761
30°	1760	1692	1697
35°	1711	1631	1628
40°	1650	1568	1563
45°	1590	1506	1497
50°	1524	1440	1420
55°	1455	1363	1348
60°	1376	1274	1266
65°	1290	1180	1169
70°	1180	1065	1065
75°	1031	928	963
80°	848	755	779
85°	567	471	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1590 cd/sqm

TEST NUMBER: P904866

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.2	2.0
10°-20°	206.1	5.5
20°-30°	302.9	8.1
30°-40°	351.8	9.4
40°-50°	351.3	9.4
50°-60°	306.3	8.2
60°-70°	226.5	6.0
70°-80°	128.1	3.4
80°-90°	35.6	0.9
90°-100°	39.1	1.0
100°-110°	124.4	3.3
110°-120°	212.8	5.7
120°-130°	279.9	7.5
130°-140°	314.2	8.4
140°-150°	308.1	8.2
150°-160°	258.4	6.9
160°-170°	171.4	4.6
170°-180°	59.9	1.6
0°-30°	582.2	15.5
0°-40°	934.0	24.9
0°-60°	1591.6	42.4
0°-90°	1981.8	52.8
90°-120°	376.3	10.0
90°-150°	1278.5	34.1
90°-180°	1768.0	47.1
0°-180°	3750.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	775	767	773	772	74
15°	741	736	727	730	726	209
25°	670	664	652	653	652	309
35°	578	571	559	554	551	361
45°	471	466	454	446	443	363
55°	356	352	343	334	330	318
65°	240	236	228	222	218	238
75°	126	124	120	116	118	134
85°	31	30	29	27	26	34
90°	1	7	19	18	18	4
95°	28	33	34	34	33	31
105°	115	116	118	118	118	121
115°	214	217	216	215	214	211
125°	311	315	314	312	312	278
135°	402	408	409	408	407	311
145°	488	492	495	495	493	305
155°	558	559	561	564	562	257
165°	607	606	606	610	607	171
175°	631	630	629	632	629	60
180°	632	632	632	632	632	

TEST NUMBER: P904866

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	778.2	778.2	778.2	778.2	778.2
2.5°	782.7	779.0	770.7	778.2	776.8
5°	778.2	775.3	767.0	773.0	771.5
7.5°	773.0	768.5	760.3	766.3	764.8
10°	764.8	759.6	750.6	756.5	754.3
12.5°	753.5	749.1	740.1	743.8	742.3
15°	740.8	736.4	726.6	729.6	725.9
17.5°	725.1	720.7	710.9	714.6	710.9
20°	707.9	703.4	692.9	695.2	692.2
22.5°	690.7	684.0	674.2	674.2	672.7
25°	670.5	664.5	651.8	653.2	651.8
27.5°	648.0	642.8	633.1	630.9	627.1
30°	625.6	619.6	608.4	606.2	603.1
32.5°	601.6	597.2	585.2	580.7	577.7
35°	578.5	571.0	559.0	554.5	550.7
37.5°	552.3	545.5	533.5	528.3	524.5
40°	525.3	519.3	507.3	500.7	497.6
42.5°	499.1	493.1	481.2	473.7	469.2
45°	470.7	465.5	454.2	446.0	443.0
47.5°	443.0	437.8	425.8	417.5	413.1
50°	413.8	410.1	399.6	389.1	385.4
52.5°	385.4	380.1	370.4	362.2	357.0
55°	356.2	351.7	342.7	333.8	330.0
57.5°	327.0	323.3	313.5	304.6	301.5
60°	297.8	294.9	284.4	276.1	273.9
62.5°	269.4	264.1	256.7	249.2	246.2
65°	240.2	235.7	228.3	221.5	217.8
67.5°	210.3	206.5	199.8	194.6	191.6
70°	182.6	179.6	172.8	167.6	164.7
72.5°	154.2	151.2	147.4	142.2	140.0
75°	125.7	124.3	120.4	116.0	117.5
77.5°	100.3	97.3	95.7	93.5	91.3
80°	74.9	74.1	72.6	70.3	68.8
82.5°	50.9	50.9	50.2	47.2	47.2
85°	30.6	29.9	29.2	26.9	26.2
87.5°	13.5	12.0	10.5	8.3	7.5
90°	0.6	6.9	18.7	17.5	18.1
92.5°	11.8	16.0	16.6	17.2	17.2
95°	27.8	33.2	34.1	34.1	33.2
97.5°	46.3	51.3	53.4	53.4	53.4
100°	67.7	72.1	73.6	73.6	73.0
102.5°	90.2	93.4	95.5	96.1	95.5
105°	114.8	116.3	117.5	118.4	118.4
107.5°	139.2	141.5	141.5	141.9	139.2
110°	162.9	165.9	165.9	165.9	164.4



TEST NUMBER: P904866

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.4	191.6	191.1	189.5	188.4
115°	213.6	216.6	215.7	215.1	213.6
117.5°	238.6	242.8	240.1	238.6	237.0
120°	263.7	267.9	263.7	263.7	262.0
122.5°	286.6	291.9	289.3	287.8	286.6
125°	310.6	315.4	313.9	312.2	311.6
127.5°	334.1	340.0	337.9	335.6	334.1
130°	356.0	362.9	361.9	360.8	358.7
132.5°	380.6	386.0	386.3	383.7	382.1
135°	401.8	407.7	408.8	408.3	406.7
137.5°	425.4	430.2	431.2	430.8	428.5
140°	446.2	451.0	453.7	453.7	451.6
142.5°	467.6	472.3	473.9	474.4	472.3
145°	487.8	491.6	494.7	495.2	493.1
147.5°	505.9	510.7	513.0	513.9	511.8
150°	524.6	527.8	529.9	531.6	529.9
152.5°	541.2	544.4	547.1	549.2	547.1
155°	557.8	559.3	561.0	563.7	562.0
157.5°	572.1	573.2	574.2	578.0	575.3
160°	584.9	586.0	586.6	589.8	587.5
162.5°	596.7	596.7	597.2	600.9	598.2
165°	606.8	606.2	606.2	610.0	607.4
167.5°	615.9	614.2	614.2	618.0	615.4
170°	622.8	621.3	620.7	624.5	621.3
172.5°	627.6	626.0	625.5	629.3	626.0
175°	631.4	629.9	628.7	632.5	629.3
177.5°	633.5	632.0	630.8	634.0	630.8
180°	632.5	632.5	632.5	632.5	632.5

TEST NUMBER: P904866

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.71	10.60	10.65	11.55	12.78	9.27	10.16	10.20	11.11	12.34
	3H	11.35	12.15	12.30	13.11	14.36	10.86	11.66	11.81	12.62	13.87
	4H	11.93	12.68	12.89	13.64	14.91	11.43	12.19	12.39	13.15	14.41
	6H	12.31	13.01	13.28	13.97	15.25	11.81	12.51	12.78	13.47	14.75
	8H	12.41	13.07	13.38	14.06	15.33	11.91	12.57	12.88	13.55	14.83
	12H	12.45	13.08	13.43	14.06	15.36	11.94	12.57	12.92	13.55	14.85
4H	2H	10.17	10.92	11.13	11.88	13.15	9.81	10.56	10.77	11.53	12.79
	3H	12.01	12.64	12.98	13.63	14.91	11.60	12.23	12.57	13.22	14.50
	4H	12.70	13.28	13.69	14.27	15.57	12.28	12.86	13.26	13.84	15.14
	6H	13.20	13.70	14.19	14.71	16.00	12.77	13.26	13.76	14.27	15.57
	8H	13.34	13.80	14.34	14.81	16.12	12.90	13.36	13.90	14.37	15.68
	12H	13.40	13.82	14.42	14.84	16.16	12.95	13.37	13.97	14.39	15.71
8H	4H	12.89	13.35	13.89	14.36	15.67	12.51	12.97	13.51	13.98	15.29
	6H	13.49	13.88	14.52	14.92	16.23	13.11	13.49	14.13	14.54	15.85
	8H	13.70	14.04	14.73	15.07	16.40	13.31	13.64	14.34	14.68	16.01
	12H	13.82	14.11	14.85	15.14	16.51	13.41	13.70	14.44	14.73	16.10
12H	4H	12.87	13.29	13.89	14.31	15.63	12.50	12.92	13.52	13.94	15.26
	6H	13.52	13.86	14.55	14.89	16.22	13.14	13.48	14.17	14.51	15.84
	8H	13.74	14.04	14.78	15.07	16.44	13.36	13.66	14.40	14.69	16.06