

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332623

Luminaire Tested: **SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332623
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7578.7 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332623
CATALOG NUMBER: SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332623

CATALOG NUMBER: SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45						45														
1	97	92	88	85	88	85	81	78	71	68	66	57	56	54	45	44	43	38						38														
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	37	32						32														
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27						27														
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23						23														
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20						20														
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18						18														
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16						16														
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14						14														
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13						13														
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11						11														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10717	10717	10717
5°	10749	10619	10697
10°	10681	10533	10585
15°	10552	10384	10410
20°	10381	10198	10207
25°	10185	9986	9958
30°	9945	9737	9648
35°	9697	9477	9351
40°	9438	9180	9013
45°	9169	8889	8719
50°	8871	8629	8363
55°	8549	8294	8024
60°	8226	7918	7677
65°	7862	7559	7253
70°	7456	7081	6805
75°	6834	6503	6338
80°	6081	5835	5686
85°	5317	5122	5020



TEST NUMBER: P332623

CATALOG NUMBER: SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	1.6
10°-20°	352.2	4.6
20°-30°	518.4	6.8
30°-40°	602.7	8.0
40°-50°	602.7	8.0
50°-60°	527.2	7.0
60°-70°	391.5	5.2
70°-80°	222.4	2.9
80°-90°	68.7	0.9
90°-100°	99.1	1.3
100°-110°	293.5	3.9
110°-120°	498.2	6.6
120°-130°	656.9	8.7
130°-140°	737.7	9.7
140°-150°	724.9	9.6
150°-160°	609.7	8.0
160°-170°	405.7	5.4
170°-180°	142.1	1.9
0°-30°	995.7	13.1
0°-40°	1598.4	21.1
0°-60°	2728.3	36.0
0°-90°	3411.0	45.0
90°-120°	890.8	11.8
90°-150°	3010.3	39.7
90°-180°	4168.0	55.0
0°-180°	7578.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1328	1328	1328	1328	1328	
5°	1326	1322	1310	1321	1320	126
15°	1263	1258	1242	1248	1246	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	962	954	949	615
45°	803	795	779	767	764	619
55°	607	604	589	577	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	233
85°	57	57	55	55	54	63
90°	4	16	26	32	35	7
95°	70	80	88	92	92	78
105°	271	272	276	280	284	287
115°	506	506	504	503	502	499
125°	738	738	737	734	732	657
135°	952	958	958	956	953	736
145°	1156	1160	1162	1160	1157	723
155°	1324	1324	1323	1327	1323	609
165°	1442	1438	1436	1442	1438	406
175°	1500	1494	1493	1500	1493	142
180°	1502	1502	1502	1502	1502	



TEST NUMBER: P332623

CATALOG NUMBER: SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1330.9	1330.3	1329.7	1329.2	1328.6	1327.3	1325.2	1323.1	1321.0	1319.0	1320.8
5°	1326.4	1325.5	1324.5	1323.6	1322.6	1320.8	1318.2	1315.6	1313.0	1310.4	1313.0
7.5°	1314.1	1313.1	1312.2	1311.2	1310.3	1308.4	1305.5	1302.6	1299.7	1296.8	1298.9
10°	1303.0	1302.1	1301.1	1300.2	1299.2	1297.2	1294.1	1291.1	1288.0	1284.9	1286.8
12.5°	1288.5	1287.6	1286.6	1285.7	1284.8	1282.6	1279.4	1276.1	1272.9	1269.6	1271.7
15°	1262.6	1261.6	1260.7	1259.7	1258.8	1256.6	1253.0	1249.5	1245.9	1242.4	1243.8
17.5°	1231.3	1230.1	1228.9	1227.8	1226.6	1224.3	1221.0	1217.6	1214.2	1210.9	1211.8
20°	1208.3	1207.1	1206.0	1204.8	1203.6	1201.2	1197.7	1194.1	1190.6	1187.1	1187.8
22.5°	1183.7	1182.1	1180.5	1179.0	1177.4	1174.9	1171.3	1167.8	1164.2	1160.7	1162.0
25°	1143.4	1141.8	1140.1	1138.5	1136.8	1134.3	1131.0	1127.7	1124.4	1121.1	1121.3
27.5°	1097.5	1095.8	1094.1	1092.4	1090.7	1088.3	1085.2	1082.2	1079.1	1076.0	1075.4
30°	1066.9	1065.0	1063.1	1061.2	1059.3	1056.8	1053.7	1050.7	1047.6	1044.5	1043.6
32.5°	1034.5	1032.8	1031.1	1029.4	1027.7	1025.2	1022.0	1018.7	1015.5	1012.2	1011.1
35°	983.9	982.2	980.6	978.9	977.3	974.8	971.5	968.2	964.9	961.6	959.9
37.5°	930.5	929.0	927.5	926.0	924.4	921.9	918.4	914.8	911.3	907.7	905.9
40°	895.6	893.7	891.8	889.9	888.0	885.3	881.8	878.2	874.7	871.1	868.8
42.5°	858.2	857.0	855.9	854.8	853.6	851.1	847.2	843.3	839.3	835.4	832.7
45°	803.1	801.4	799.8	798.1	796.5	793.7	790.0	786.2	782.4	778.6	776.0
47.5°	745.4	744.3	743.2	742.0	740.9	738.6	735.1	731.6	728.1	724.6	721.6
50°	706.3	705.3	704.4	703.4	702.5	700.4	697.1	693.8	690.4	687.1	683.8
52.5°	668.0	666.9	665.7	664.6	663.4	661.1	657.6	654.1	650.6	647.1	644.2
55°	607.4	606.6	605.9	605.2	604.5	602.5	599.2	595.9	592.6	589.3	586.4
57.5°	549.5	548.7	547.9	547.1	546.3	544.2	541.0	537.7	534.5	531.2	528.5
60°	509.5	508.3	507.1	506.0	504.8	502.6	499.6	496.5	493.4	490.4	488.2
62.5°	470.4	469.4	468.4	467.4	466.4	464.3	461.0	457.7	454.5	451.2	449.3
65°	411.6	410.5	409.3	408.1	406.9	405.1	402.8	400.4	398.0	395.7	393.3
67.5°	352.5	351.4	350.3	349.2	348.2	346.5	344.2	341.9	339.7	337.4	335.1
70°	315.9	314.3	312.6	310.9	309.3	307.5	305.6	303.7	301.8	300.0	298.1
72.5°	276.8	275.1	273.5	271.8	270.1	268.6	267.1	265.5	264.0	262.5	261.0
75°	219.1	217.9	216.8	215.6	214.4	213.2	212.0	210.8	209.7	208.5	207.5
77.5°	164.0	163.5	163.0	162.5	161.9	161.2	160.1	159.1	158.0	157.0	156.7
80°	130.8	130.1	129.4	128.7	128.0	127.4	126.9	126.5	126.0	125.5	125.0
82.5°	98.5	98.2	97.8	97.5	97.2	97.0	96.9	96.8	96.7	96.6	96.3
85°	57.4	57.4	57.4	57.4	57.4	57.2	56.7	56.3	55.8	55.3	55.3
87.5°	22.8	23.2	23.6	24.0	24.3	24.6	24.9	25.1	25.3	25.5	25.8
90°	3.5	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1
92.5°	24.9	28.1	31.4	34.6	37.9	40.2	41.7	43.1	44.6	46.0	46.9
95°	69.7	72.0	74.4	76.7	79.0	81.1	82.9	84.7	86.5	88.3	89.1
97.5°	121.8	123.6	125.5	127.3	129.2	131.2	133.3	135.4	137.5	139.6	140.6
100°	162.7	163.7	164.7	165.7	166.8	168.5	170.8	173.1	175.4	177.8	178.3
102.5°	205.4	205.8	206.2	206.6	207.1	208.3	210.4	212.6	214.7	216.8	217.5
105°	270.7	271.0	271.2	271.5	271.7	272.4	273.4	274.4	275.5	276.5	277.3
107.5°	339.2	339.6	339.9	340.2	340.5	340.7	340.9	341.0	341.2	341.3	342.1
110°	385.7	386.2	386.7	387.3	387.8	387.9	387.7	387.4	387.1	386.9	386.4



TEST NUMBER: P332623

CATALOG NUMBER: SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.0	434.2	434.3	434.4	434.5	434.3	433.8	433.4	432.9	432.4	432.3
115°	506.5	506.5	506.5	506.5	506.5	506.3	505.8	505.3	504.7	504.2	504.0
117.5°	574.9	575.1	575.3	575.5	575.7	575.6	575.2	574.9	574.5	574.2	573.3
120°	620.4	621.4	622.5	623.5	624.5	624.7	623.9	623.1	622.3	621.6	620.3
122.5°	667.8	668.2	668.6	669.0	669.5	669.5	669.1	668.8	668.4	668.0	667.2
125°	737.7	737.7	737.7	737.7	737.7	737.6	737.4	737.1	736.8	736.6	736.1
127.5°	801.2	802.0	802.7	803.5	804.3	804.5	804.0	803.6	803.2	802.8	802.3
130°	845.8	846.6	847.3	848.1	848.9	849.3	849.3	849.3	849.3	849.3	848.8
132.5°	891.3	891.9	892.5	893.0	893.6	893.8	893.6	893.4	893.2	893.0	892.4
135°	951.5	953.1	954.6	956.2	957.7	958.5	958.5	958.5	958.5	958.5	958.0
137.5°	1017.0	1017.8	1018.5	1019.2	1019.9	1020.5	1020.9	1021.3	1021.7	1022.1	1021.5
140°	1060.7	1061.2	1061.8	1062.3	1062.8	1063.0	1063.0	1063.0	1063.0	1063.0	1062.8
142.5°	1100.7	1101.2	1101.7	1102.2	1102.8	1102.9	1102.7	1102.5	1102.3	1102.1	1102.0
145°	1156.0	1157.0	1158.1	1159.1	1160.1	1160.8	1161.0	1161.3	1161.5	1161.8	1161.5
147.5°	1210.8	1212.1	1213.3	1214.5	1215.8	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3
150°	1244.3	1245.3	1246.4	1247.4	1248.4	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9
152.5°	1275.9	1276.5	1277.1	1277.7	1278.4	1278.8	1279.0	1279.2	1279.4	1279.6	1280.2
155°	1324.4	1324.4	1324.4	1324.4	1324.4	1324.3	1324.1	1323.8	1323.5	1323.3	1324.3
157.5°	1365.3	1364.9	1364.4	1364.0	1363.5	1363.2	1363.2	1363.1	1363.1	1363.0	1363.8
160°	1389.5	1389.3	1389.0	1388.7	1388.5	1388.2	1388.0	1387.7	1387.4	1387.2	1388.0
162.5°	1411.8	1411.1	1410.5	1409.8	1409.1	1408.7	1408.4	1408.2	1407.9	1407.6	1409.0
165°	1441.8	1441.0	1440.2	1439.5	1438.7	1438.0	1437.5	1437.0	1436.5	1436.0	1437.5
167.5°	1464.8	1463.7	1462.6	1461.5	1460.5	1459.9	1460.0	1460.0	1460.1	1460.1	1461.7
170°	1477.8	1476.5	1475.2	1473.9	1472.6	1472.1	1472.4	1472.6	1472.9	1473.2	1474.7
172.5°	1487.1	1486.0	1484.9	1483.8	1482.8	1482.2	1482.3	1482.4	1482.4	1482.5	1484.2
175°	1499.9	1498.6	1497.3	1496.0	1494.7	1493.9	1493.7	1493.4	1493.2	1492.9	1494.7
177.5°	1504.1	1503.0	1502.0	1501.0	1499.9	1499.4	1499.4	1499.4	1499.4	1499.4	1500.9
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332623

CATALOG NUMBER: SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1322.7	1324.6	1326.5	1327.4	1327.2	1327.0	1326.8	1326.6
5°	1315.6	1318.2	1320.8	1321.9	1321.4	1321.0	1320.5	1320.0
7.5°	1301.0	1303.1	1305.1	1306.0	1305.8	1305.5	1305.2	1304.9
10°	1288.7	1290.6	1292.5	1293.2	1292.7	1292.2	1291.8	1291.3
12.5°	1273.8	1275.8	1277.9	1278.6	1278.0	1277.3	1276.6	1276.0
15°	1245.2	1246.6	1248.0	1248.4	1247.7	1247.0	1246.3	1245.6
17.5°	1212.7	1213.6	1214.5	1214.7	1214.2	1213.7	1213.3	1212.8
20°	1188.5	1189.2	1189.9	1190.0	1189.5	1189.1	1188.6	1188.1
22.5°	1163.2	1164.5	1165.8	1166.0	1165.1	1164.3	1163.4	1162.6
25°	1121.6	1121.8	1122.1	1121.7	1120.8	1119.8	1118.9	1117.9
27.5°	1074.9	1074.3	1073.7	1072.9	1071.7	1070.5	1069.3	1068.1
30°	1042.6	1041.7	1040.7	1039.7	1038.5	1037.3	1036.1	1035.0
32.5°	1009.9	1008.8	1007.7	1006.5	1005.3	1004.1	1002.9	1001.8
35°	958.3	956.6	954.9	953.5	952.3	951.2	950.0	948.8
37.5°	904.1	902.3	900.6	898.9	897.3	895.8	894.2	892.6
40°	866.4	864.1	861.7	859.9	858.7	857.6	856.4	855.2
42.5°	829.9	827.2	824.4	822.7	821.9	821.1	820.3	819.5
45°	773.4	770.8	768.2	766.6	765.8	765.1	764.4	763.7
47.5°	718.7	715.8	712.8	710.5	708.7	706.9	705.1	703.3
50°	680.5	677.2	673.9	671.5	670.1	668.7	667.3	665.9
52.5°	641.3	638.3	635.4	633.1	631.3	629.5	627.7	625.9
55°	583.6	580.8	577.9	575.8	574.4	573.0	571.5	570.1
57.5°	525.8	523.1	520.4	518.4	517.0	515.6	514.3	512.9
60°	486.1	484.0	481.8	480.2	479.0	477.8	476.6	475.5
62.5°	447.3	445.4	443.5	441.9	440.7	439.5	438.4	437.2
65°	391.0	388.6	386.2	384.5	383.3	382.1	380.9	379.7
67.5°	332.9	330.6	328.3	327.0	326.7	326.4	326.0	325.7
70°	296.2	294.3	292.4	291.1	290.4	289.7	289.0	288.3
72.5°	259.5	258.0	256.5	255.4	254.6	253.9	253.2	252.5
75°	206.6	205.6	204.7	204.1	203.9	203.6	203.4	203.2
77.5°	156.4	156.1	155.9	155.4	154.8	154.2	153.6	153.0
80°	124.6	124.1	123.6	123.3	123.0	122.8	122.6	122.3
82.5°	96.0	95.7	95.4	95.2	95.0	94.7	94.5	94.2
85°	55.3	55.3	55.3	55.2	55.0	54.7	54.5	54.2
87.5°	26.2	26.5	26.8	27.0	27.1	27.2	27.3	27.4
90°	28.7	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	47.9	48.8	49.7	50.3	50.7	51.0	51.3	51.6
95°	89.8	90.6	91.4	91.8	91.8	91.8	91.8	91.8
97.5°	141.5	142.4	143.4	143.8	143.8	143.8	143.8	143.8
100°	178.8	179.3	179.8	180.1	180.1	180.1	180.1	180.1
102.5°	218.2	219.0	219.7	220.1	220.4	220.6	220.8	221.0
105°	278.1	278.8	279.6	280.4	281.2	281.9	282.7	283.5
107.5°	342.8	343.5	344.2	344.6	344.5	344.5	344.4	344.4
110°	385.8	385.3	384.8	384.9	385.7	386.5	387.3	388.0



TEST NUMBER: P332623

CATALOG NUMBER: SA4XXDIP-C795D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.2	432.1	432.0	432.0	432.2	432.3	432.5	432.7
115°	503.7	503.4	503.2	502.9	502.7	502.4	502.2	501.9
117.5°	572.4	571.5	570.6	570.0	569.4	568.9	568.4	567.9
120°	619.0	617.7	616.4	616.0	616.5	617.0	617.6	618.1
122.5°	666.3	665.4	664.5	663.6	662.7	661.8	660.8	659.9
125°	735.5	735.0	734.5	734.0	733.5	733.0	732.4	731.9
127.5°	801.8	801.3	800.7	800.3	799.9	799.4	799.0	798.6
130°	848.2	847.7	847.2	846.4	845.4	844.4	843.3	842.3
132.5°	891.9	891.4	890.9	890.4	890.0	889.6	889.2	888.8
135°	957.5	956.9	956.4	955.8	955.0	954.2	953.4	952.7
137.5°	1020.8	1020.1	1019.5	1019.2	1019.4	1019.5	1019.7	1019.8
140°	1062.5	1062.3	1062.0	1061.8	1061.5	1061.2	1061.0	1060.7
142.5°	1102.0	1101.9	1101.9	1101.8	1101.8	1101.7	1101.7	1101.6
145°	1161.3	1161.0	1160.8	1160.2	1159.5	1158.7	1157.9	1157.2
147.5°	1215.1	1214.9	1214.6	1214.4	1214.2	1213.9	1213.6	1213.4
150°	1248.9	1248.9	1248.9	1248.8	1248.5	1248.3	1248.0	1247.8
152.5°	1280.8	1281.5	1282.1	1282.1	1281.4	1280.7	1280.0	1279.4
155°	1325.4	1326.4	1327.4	1327.4	1326.4	1325.4	1324.3	1323.3
157.5°	1364.6	1365.3	1366.1	1366.1	1365.2	1364.3	1363.4	1362.6
160°	1388.7	1389.5	1390.3	1390.0	1388.7	1387.4	1386.2	1384.9
162.5°	1410.4	1411.8	1413.2	1413.3	1412.0	1410.7	1409.4	1408.1
165°	1439.1	1440.6	1442.2	1442.4	1441.4	1440.4	1439.3	1438.3
167.5°	1463.2	1464.8	1466.3	1466.3	1464.7	1463.1	1461.5	1459.9
170°	1476.3	1477.8	1479.4	1479.2	1477.4	1475.6	1473.8	1472.0
172.5°	1486.0	1487.7	1489.5	1489.5	1487.6	1485.8	1484.0	1482.2
175°	1496.5	1498.3	1500.1	1500.1	1498.3	1496.5	1494.7	1492.9
177.5°	1502.3	1503.8	1505.2	1505.1	1503.4	1501.8	1500.1	1498.5
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2

(END OF REPORT)