

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904882

Luminaire Tested: DFN2DIP-4P2F0-030D030US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904882
REPORT IS A COMBINATION OF REPORTS P899019 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D030US835-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5625.0 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904882

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904882

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		100	100	100	100		85	85	85		71	71	71		59	59	59
1	98	94	90	87		91	87	84	81		74	72	70		63	61	59		52	51	50
2	90	82	76	71		83	76	71	66		65	61	58		55	52	50		46	44	42
3	82	72	65	59		75	67	61	55		58	53	49		49	45	42		41	38	36
4	75	64	56	50		69	60	52	47		51	46	41		43	39	36		36	33	31
5	69	57	49	43		63	53	46	40		46	40	36		39	35	31		33	29	27
6	63	51	43	37		58	48	40	35		41	36	31		35	31	27		30	26	24
7	59	46	38	33		54	43	36	31		37	32	28		32	28	24		27	24	21
8	54	42	34	29		50	39	32	27		34	29	24		29	25	22		25	21	19
9	51	38	31	26		47	36	29	24		31	26	22		27	23	19		23	20	17
10	47	35	28	23		44	33	26	22		29	23	20		25	21	18		21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2923	2923	2923
5°	2922	2875	2897
10°	2892	2829	2853
15°	2844	2775	2787
20°	2781	2703	2719
25°	2717	2618	2642
30°	2640	2539	2545
35°	2566	2446	2443
40°	2476	2353	2345
45°	2385	2259	2245
50°	2287	2159	2130
55°	2183	2045	2022
60°	2065	1911	1899
65°	1935	1770	1754
70°	1771	1599	1597
75°	1545	1393	1445
80°	1272	1131	1170
85°	852	707	728

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2385 cd/sqm

TEST NUMBER: P904882

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US835-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	2.0
10°-20°	309.1	5.5
20°-30°	454.3	8.1
30°-40°	527.6	9.4
40°-50°	527.0	9.4
50°-60°	459.5	8.2
60°-70°	339.7	6.0
70°-80°	192.2	3.4
80°-90°	53.4	0.9
90°-100°	58.7	1.0
100°-110°	186.5	3.3
110°-120°	319.2	5.7
120°-130°	419.8	7.5
130°-140°	471.2	8.4
140°-150°	462.1	8.2
150°-160°	387.7	6.9
160°-170°	257.1	4.6
170°-180°	89.9	1.6
0°-30°	873.3	15.5
0°-40°	1400.9	24.9
0°-60°	2387.4	42.4
0°-90°	2972.7	52.8
90°-120°	564.5	10.0
90°-150°	1917.7	34.1
90°-180°	2652.0	47.1
0°-180°	5625.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1167	1167	1167	1167	1167	
5°	1167	1163	1150	1160	1157	111
15°	1111	1105	1090	1094	1089	313
25°	1006	997	978	980	978	463
35°	868	856	838	832	826	542
45°	706	698	681	669	664	545
55°	534	528	514	501	495	478
65°	360	354	342	332	327	356
75°	188	186	181	174	176	201
85°	46	45	44	40	39	51
90°	1	10	28	26	27	5
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	

TEST NUMBER: P904882

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1167.3	1167.3	1167.3	1167.3	1167.3
2.5°	1174.1	1168.5	1156.1	1167.3	1165.2
5°	1167.3	1162.9	1150.5	1159.5	1157.3
7.5°	1159.5	1152.8	1140.4	1149.5	1147.2
10°	1147.2	1139.3	1125.9	1134.8	1131.5
12.5°	1130.3	1123.6	1110.2	1115.7	1113.5
15°	1111.2	1104.6	1089.9	1094.4	1088.8
17.5°	1087.6	1081.0	1066.3	1071.9	1066.3
20°	1061.8	1055.1	1039.4	1042.7	1038.3
22.5°	1036.1	1026.0	1011.3	1011.3	1009.0
25°	1005.7	996.8	977.7	979.9	977.7
27.5°	972.0	964.1	949.6	946.3	940.7
30°	938.4	929.4	912.6	909.2	904.7
32.5°	902.5	895.8	877.8	871.0	866.5
35°	867.7	856.5	838.5	831.7	826.1
37.5°	828.4	818.3	800.3	792.4	786.8
40°	788.0	779.0	761.0	751.0	746.5
42.5°	748.7	739.7	721.8	710.5	703.8
45°	706.1	698.2	681.3	669.0	664.5
47.5°	664.5	656.7	638.7	626.3	619.6
50°	620.7	615.1	599.4	583.7	578.1
52.5°	578.1	570.2	555.7	543.3	535.4
55°	534.4	527.6	514.1	500.7	495.1
57.5°	490.5	484.9	470.3	456.8	452.3
60°	446.7	442.3	426.6	414.2	410.9
62.5°	404.1	396.2	385.0	373.8	369.3
65°	360.4	353.6	342.4	332.3	326.7
67.5°	315.5	309.8	299.7	291.9	287.4
70°	273.9	269.4	259.3	251.4	247.0
72.5°	231.3	226.7	221.1	213.3	210.0
75°	188.5	186.4	180.7	174.0	176.3
77.5°	150.4	145.9	143.6	140.3	137.0
80°	112.3	111.1	108.8	105.5	103.3
82.5°	76.3	76.3	75.3	70.7	70.7
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6

TEST NUMBER: P904882

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8

TEST NUMBER: P904882

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.12	12.01	12.05	12.96	14.19	10.68	11.57	11.61	12.52	13.74
	3H	12.76	13.56	13.71	14.52	15.77	12.27	13.07	13.22	14.03	15.28
	4H	13.34	14.09	14.29	15.05	16.31	12.84	13.60	13.80	14.56	15.82
	6H	13.72	14.41	14.69	15.38	16.66	13.22	13.91	14.19	14.88	16.16
	8H	13.82	14.48	14.79	15.46	16.74	13.32	13.98	14.29	14.96	16.23
	12H	13.86	14.49	14.84	15.47	16.76	13.35	13.98	14.33	14.96	16.26
4H	2H	11.57	12.33	12.54	13.29	14.55	11.22	11.97	12.18	12.94	14.20
	3H	13.42	14.04	14.39	15.04	16.31	13.01	13.64	13.98	14.63	15.91
	4H	14.11	14.69	15.10	15.67	16.97	13.69	14.26	14.67	15.25	16.55
	6H	14.61	15.10	15.60	16.11	17.41	14.18	14.67	15.17	15.68	16.98
	8H	14.75	15.21	15.74	16.21	17.53	14.31	14.77	15.31	15.78	17.09
	12H	14.81	15.23	15.83	16.25	17.57	14.36	14.78	15.38	15.80	17.12
8H	4H	14.30	14.76	15.29	15.76	17.08	13.92	14.38	14.92	15.39	16.70
	6H	14.90	15.29	15.92	16.33	17.64	14.52	14.90	15.54	15.95	17.26
	8H	15.11	15.45	16.14	16.48	17.81	14.71	15.05	15.74	16.08	17.41
	12H	15.23	15.52	16.26	16.55	17.92	14.82	15.11	15.85	16.14	17.51
12H	4H	14.28	14.70	15.30	15.72	17.04	13.91	14.33	14.93	15.35	16.67
	6H	14.93	15.27	15.96	16.30	17.63	14.55	14.89	15.58	15.92	17.25
	8H	15.15	15.45	16.19	16.48	17.85	14.77	15.07	15.80	16.09	17.47