

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332981

Luminaire Tested: **SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332981
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8642.0 lumens
Efficiency: N/A
Efficacy: 132.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332981
CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	49	48	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	43	40	38	36	32
4	75	65	57	51	69	60	54	48	52	47	43	44	40	37	36	33	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	39	59	49	42	37	42	36	32	36	32	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19
8	55	43	35	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13852	13852	13852	13852
5°	16067	13893	12280	13893
10°	19007	13833	10960	13833
15°	21956	13705	9417	13705
20°	24445	13529	8516	13529
25°	25235	13356	7906	13356
30°	22091	13147	7539	13147
35°	17196	12835	7318	12835
40°	12895	12480	7198	12480
45°	10182	11910	7134	11910
50°	8596	11252	6929	11252
55°	7492	10528	6557	10528
60°	6741	9778	5804	9778
65°	5943	8967	4991	8967
70°	5351	8127	4504	8127
75°	4485	7202	3840	7202
80°	3794	6137	3598	6137
85°	3205	4798	3205	4798



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.3	1.9
10°-20°	501.5	5.8
20°-30°	784.4	9.1
30°-40°	872.0	10.1
40°-50°	773.6	9.0
50°-60°	602.8	7.0
60°-70°	394.7	4.6
70°-80°	194.1	2.2
80°-90°	51.2	0.6
90°-100°	427.2	4.9
100°-110°	889.1	10.3
110°-120°	796.4	9.2
120°-130°	669.9	7.8
130°-140°	558.5	6.5
140°-150°	426.7	4.9
150°-160°	299.9	3.5
160°-170°	176.4	2.0
170°-180°	57.4	0.7
0°-30°	1452.1	16.8
0°-40°	2324.1	26.9
0°-60°	3700.5	42.8
0°-90°	4340.4	50.2
90°-120°	2112.7	24.4
90°-150°	3767.8	43.6
90°-180°	4302.0	49.8
0°-180°	8642.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1716	1716	1716	1716	1716	
5°	1983	1714	1515	1714	1983	201
15°	2627	1640	1127	1640	2627	747
25°	2833	1499	888	1499	2833	1257
35°	1745	1302	742	1302	1745	1094
45°	892	1043	625	1043	892	706
55°	532	748	466	748	532	484
65°	311	469	261	469	311	313
75°	144	231	123	231	144	158
85°	35	52	35	52	35	40
90°	24	1	24	1	24	21
95°	284	38	284	38	284	440
105°	1635	136	1635	136	1635	1616
115°	1570	239	1570	239	1570	1558
125°	1253	334	1253	334	1253	1138
135°	1120	396	1120	396	1120	865
145°	914	457	914	457	914	580
155°	766	519	766	519	766	357
165°	668	566	668	566	668	191
175°	602	590	602	590	602	59
180°	592	592	592	592	592	



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1809.8	1814.8	1809.8	1809.3	1803.8	1802.1	1799.9	1792.7	1779.4	1771.7	1773.3
5°	1982.7	1999.9	1990.3	1988.9	1973.7	1958.5	1948.8	1926.7	1903.2	1887.3	1874.1
7.5°	2182.6	2192.5	2186.5	2176.8	2152.2	2138.2	2115.8	2086.6	2044.5	2012.2	1982.8
10°	2318.6	2326.9	2324.2	2306.2	2288.2	2251.6	2230.8	2190.1	2136.8	2094.7	2055.2
12.5°	2452.5	2461.3	2437.0	2437.8	2403.8	2374.9	2342.0	2290.7	2229.2	2174.8	2125.5
15°	2627.0	2615.9	2615.9	2602.1	2564.0	2524.0	2490.1	2436.2	2358.7	2293.7	2225.3
17.5°	2763.6	2767.4	2761.8	2729.1	2699.3	2657.8	2595.7	2532.8	2460.9	2373.7	2303.7
20°	2845.4	2845.4	2839.2	2817.1	2778.4	2734.1	2667.1	2598.6	2507.4	2419.6	2340.8
22.5°	2878.6	2880.8	2873.5	2855.2	2820.4	2777.2	2720.1	2650.6	2556.6	2457.7	2360.1
25°	2833.0	2846.1	2847.5	2842.6	2832.3	2806.0	2756.9	2685.7	2601.4	2494.2	2389.1
27.5°	2601.0	2617.6	2632.1	2656.0	2687.8	2704.4	2706.6	2670.4	2596.8	2493.7	2387.9
30°	2369.8	2383.6	2428.6	2487.3	2532.9	2574.4	2610.4	2620.0	2578.6	2485.9	2374.6
32.5°	2113.2	2132.0	2176.9	2240.1	2316.1	2386.4	2467.1	2508.3	2507.2	2451.6	2348.6
35°	1744.9	1758.7	1800.2	1866.5	1957.8	2062.2	2190.1	2289.6	2357.3	2352.5	2289.6
37.5°	1407.2	1422.8	1464.7	1519.8	1608.3	1737.5	1861.3	1998.4	2123.7	2194.1	2173.0
40°	1223.6	1224.3	1265.1	1321.8	1404.7	1517.4	1652.2	1804.3	1943.9	2058.0	2080.1
42.5°	1078.7	1078.8	1105.8	1166.9	1226.7	1332.7	1461.4	1612.4	1775.8	1907.6	1966.2
45°	891.8	898.0	920.1	956.8	1003.8	1093.6	1196.6	1337.0	1520.2	1676.4	1773.9
47.5°	755.2	764.3	778.4	808.3	845.7	905.6	990.8	1116.9	1265.9	1437.8	1576.5
50°	684.4	685.8	703.7	720.3	752.8	800.5	875.2	980.3	1117.1	1282.4	1436.5
52.5°	623.6	623.3	634.1	655.1	681.5	718.7	779.0	874.6	996.0	1144.1	1303.2
55°	532.3	535.8	544.1	560.6	580.7	607.0	654.7	726.6	822.0	948.5	1093.0
57.5°	462.9	464.7	471.2	478.2	496.6	515.7	551.5	601.4	681.9	785.5	920.1
60°	417.5	418.2	420.3	430.7	445.2	463.2	487.4	529.5	597.3	692.0	798.5
62.5°	373.3	374.5	377.7	385.3	396.5	409.0	434.3	468.2	524.3	605.2	701.1
65°	311.1	311.8	316.6	319.4	328.4	339.4	358.1	380.9	419.6	487.4	560.0
67.5°	259.9	259.9	260.2	263.9	270.2	277.5	288.7	306.9	336.1	377.7	441.7
70°	226.7	226.7	228.1	230.2	233.7	239.9	246.1	259.9	281.4	315.2	364.3
72.5°	195.8	196.3	197.7	198.1	199.9	205.0	209.6	218.5	234.4	259.9	299.6
75°	143.8	145.9	149.3	152.1	155.5	154.9	159.7	165.2	170.1	185.3	208.1
77.5°	107.0	105.9	106.3	108.7	109.1	109.8	113.2	117.5	121.1	128.3	136.5
80°	81.6	81.6	83.6	84.3	83.6	84.3	87.8	89.9	91.3	94.0	101.6
82.5°	61.7	62.8	62.1	62.8	63.2	63.9	66.8	67.2	68.6	69.7	72.9
85°	34.6	35.3	35.9	34.6	34.6	34.6	35.9	36.6	38.0	37.3	38.7
87.5°	17.0	16.5	17.3	17.0	17.4	16.8	17.1	18.0	16.7	17.5	17.0
90°	24.4	24.4	25.6	24.4	23.2	23.2	22.1	20.9	19.8	20.9	18.6
92.5°	89.5	89.5	93.4	99.7	113.4	136.7	171.7	228.2	307.0	368.6	322.6
95°	283.5	298.6	319.6	355.6	412.5	525.2	680.9	861.0	973.8	947.0	714.6
97.5°	757.9	782.0	816.9	886.8	970.3	1091.6	1205.2	1272.2	1223.4	997.5	668.8
100°	1065.6	1074.9	1109.7	1180.6	1281.7	1367.7	1424.6	1401.4	1231.7	934.2	606.6
102.5°	1333.3	1340.7	1377.4	1428.8	1490.8	1526.6	1510.1	1394.9	1162.0	855.2	564.7
105°	1634.9	1641.9	1658.2	1667.5	1665.1	1617.5	1502.5	1301.4	1035.3	762.3	528.7
107.5°	1747.0	1743.9	1732.3	1705.8	1648.4	1544.8	1382.8	1168.7	933.1	710.2	522.2
110°	1748.8	1738.4	1717.4	1668.6	1586.1	1458.3	1289.8	1088.8	882.0	692.6	524.1



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1694.0	1677.0	1647.7	1588.7	1495.0	1367.2	1208.0	1030.2	853.1	684.2	529.6
115°	1569.9	1560.6	1523.4	1453.7	1361.9	1250.3	1114.4	971.4	826.2	679.8	540.3
117.5°	1444.1	1436.9	1399.3	1340.7	1262.4	1167.8	1060.9	942.6	814.1	678.6	551.7
120°	1373.5	1360.7	1330.5	1279.4	1213.1	1130.6	1037.7	929.6	807.6	678.6	560.1
122.5°	1317.7	1304.9	1279.4	1235.7	1179.7	1107.4	1022.8	918.4	800.2	677.7	568.5
125°	1252.6	1245.7	1223.6	1189.9	1143.4	1079.5	999.3	899.4	787.8	676.3	581.0
127.5°	1214.5	1207.6	1189.0	1159.0	1112.3	1051.6	971.7	876.1	771.3	673.7	591.0
130°	1192.2	1185.2	1166.6	1137.6	1090.0	1028.4	949.4	857.6	761.1	672.8	598.4
132.5°	1167.1	1160.1	1142.5	1109.7	1063.0	1001.4	924.3	838.0	751.8	671.9	604.9
135°	1120.2	1113.2	1094.6	1062.1	1015.6	957.5	886.6	811.1	737.9	670.5	614.7
137.5°	1062.1	1053.7	1038.4	1006.3	962.8	910.3	850.6	786.7	725.8	670.2	620.5
140°	1020.2	1010.9	994.7	969.1	928.4	879.6	827.3	772.7	719.3	669.3	625.2
142.5°	975.6	969.1	954.7	931.0	895.0	852.7	807.8	759.7	713.7	669.3	628.9
145°	914.5	908.7	897.1	877.3	848.3	815.7	780.9	741.4	704.2	667.0	631.0
147.5°	860.3	858.3	849.4	832.5	811.1	785.5	757.6	726.3	695.6	662.8	632.1
150°	829.7	828.5	821.5	806.4	787.8	766.9	743.7	717.0	689.1	660.0	632.1
152.5°	801.8	800.6	796.4	784.1	768.3	751.1	729.7	706.7	681.6	655.4	630.3
155°	765.8	765.8	762.3	753.0	741.4	727.4	710.0	691.4	670.5	648.4	627.5
157.5°	734.2	734.2	732.1	725.1	716.3	705.1	690.5	674.9	659.1	641.2	624.5
160°	714.6	714.6	713.5	706.5	699.5	690.2	677.4	664.7	650.7	635.6	621.7
162.5°	696.0	697.0	695.8	688.8	683.7	675.4	665.4	654.4	643.3	630.0	618.9
165°	668.2	669.3	670.5	665.8	661.2	655.4	647.2	640.3	631.0	621.7	613.5
167.5°	646.1	647.0	647.2	644.2	641.9	638.4	631.9	626.6	619.8	613.3	608.0
170°	632.1	632.1	633.3	632.1	629.8	626.3	621.7	618.2	612.4	607.7	604.2
172.5°	618.2	620.0	621.2	620.0	618.6	616.1	613.3	610.7	605.9	602.1	600.5
175°	601.9	604.2	606.6	604.2	604.2	604.2	601.9	600.8	598.4	596.1	596.1
177.5°	592.4	594.2	596.1	595.2	596.1	595.2	595.2	594.2	593.3	592.4	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1767.8	1760.1	1756.2	1747.3	1736.8	1731.3	1726.3	1719.1	1709.7	1699.8	1692.6
5°	1857.5	1840.9	1820.2	1795.3	1773.2	1751.8	1733.1	1714.4	1693.0	1670.9	1648.8
7.5°	1949.6	1917.0	1881.7	1840.9	1801.3	1765.2	1732.0	1700.2	1664.2	1632.0	1602.7
10°	2013.8	1969.5	1920.4	1868.6	1816.7	1771.8	1727.6	1687.5	1643.2	1603.8	1570.6
12.5°	2065.8	2013.8	1954.7	1890.2	1827.8	1773.5	1722.6	1670.3	1620.0	1577.3	1533.0
15°	2152.0	2080.8	2001.3	1923.9	1843.0	1769.0	1700.6	1639.8	1582.4	1522.3	1480.1
17.5°	2211.3	2126.9	2030.2	1937.2	1841.6	1754.4	1675.4	1603.0	1536.8	1475.4	1425.2
20°	2246.7	2153.4	2046.3	1940.5	1833.3	1740.0	1655.0	1574.8	1506.4	1440.0	1388.1
22.5°	2266.6	2163.4	2046.3	1935.5	1824.5	1723.4	1630.1	1546.6	1472.1	1405.7	1348.3
25°	2273.0	2162.4	2042.8	1915.6	1793.9	1686.8	1590.0	1499.4	1416.5	1350.1	1289.3
27.5°	2264.2	2133.9	2011.4	1880.9	1755.4	1642.4	1540.8	1445.7	1362.6	1291.4	1229.0
30°	2250.9	2111.2	1979.9	1844.4	1717.2	1608.7	1501.5	1410.3	1323.8	1249.9	1187.0
32.5°	2222.1	2083.6	1942.3	1803.5	1674.6	1562.8	1461.1	1369.3	1284.6	1209.0	1142.2
35°	2165.2	2024.8	1871.4	1729.0	1602.4	1486.3	1390.9	1302.4	1221.5	1140.7	1070.1
37.5°	2090.1	1946.7	1794.1	1638.1	1511.5	1401.8	1314.3	1231.2	1152.3	1078.4	1000.3
40°	2019.3	1888.6	1731.0	1576.2	1446.2	1340.4	1259.6	1184.2	1104.7	1031.4	953.3
42.5°	1933.6	1822.3	1663.0	1507.6	1379.3	1277.4	1202.0	1128.3	1056.0	985.0	903.5
45°	1790.5	1706.1	1556.8	1407.5	1278.2	1177.3	1108.2	1043.2	979.6	911.8	835.1
47.5°	1626.5	1569.4	1440.5	1287.6	1168.0	1077.2	1010.4	957.3	903.5	835.8	768.5
50°	1512.6	1475.9	1351.5	1211.9	1097.8	1014.1	945.7	895.9	851.0	786.0	725.9
52.5°	1390.9	1371.4	1266.3	1132.8	1022.6	940.6	882.1	837.3	791.8	737.9	681.6
55°	1205.6	1216.0	1126.8	1011.4	907.7	838.6	785.3	748.0	709.3	663.7	620.1
57.5°	1016.2	1054.1	994.2	892.9	795.7	731.8	691.7	660.3	627.8	590.0	552.8
60°	902.8	934.6	900.8	811.6	726.6	667.1	629.8	605.6	573.1	538.5	510.2
62.5°	792.2	826.2	806.2	734.2	655.2	604.1	571.2	548.6	524.4	494.3	464.8
65°	653.3	675.4	665.7	616.0	560.0	516.4	486.0	469.4	447.3	425.2	398.9
67.5°	500.4	543.1	537.4	511.0	462.6	428.6	408.7	394.0	373.9	357.4	339.6
70°	411.3	450.7	450.0	428.6	402.3	370.5	356.7	344.3	326.3	310.4	295.9
72.5°	336.7	372.8	378.1	361.7	343.7	319.7	306.4	297.8	280.4	269.5	257.7
75°	235.7	262.0	268.9	268.9	260.6	248.2	236.4	230.9	218.5	208.8	201.9
77.5°	154.6	171.2	182.0	184.4	185.7	181.5	171.9	168.0	158.4	155.0	148.4
80°	109.2	120.3	132.7	136.9	140.3	139.0	134.8	132.0	123.1	119.6	116.8
82.5°	75.5	81.6	91.8	100.9	100.0	103.6	100.0	97.8	91.0	89.7	87.0
85°	39.4	40.1	41.5	47.7	51.2	52.5	53.2	51.8	49.8	49.8	44.9
87.5°	16.5	16.0	15.7	15.7	16.0	18.0	18.9	19.0	17.8	16.9	15.5
90°	16.3	16.3	9.3	9.3	8.1	7.0	3.5	1.2	3.5	7.0	8.1
92.5°	234.7	144.6	85.5	61.4	44.4	30.2	19.3	13.2	19.3	30.2	44.4
95°	436.9	246.3	145.3	96.4	68.6	53.5	41.8	38.3	41.8	53.5	68.6
97.5°	392.8	235.4	157.6	116.7	92.7	78.8	68.8	68.8	68.8	78.8	92.7
100°	369.5	238.2	169.7	132.5	110.4	96.4	88.3	88.3	88.3	96.4	110.4
102.5°	363.0	247.5	185.5	150.1	129.0	116.0	108.8	106.9	108.8	116.0	129.0
105°	366.0	269.6	213.8	180.1	159.2	145.3	139.4	136.0	139.4	145.3	159.2
107.5°	383.2	295.4	244.3	211.0	191.0	176.2	170.3	168.0	170.3	176.2	191.0
110°	396.2	314.9	263.8	232.4	211.5	197.5	191.7	189.4	191.7	197.5	211.5



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.2	333.5	284.2	252.9	231.9	218.9	212.2	209.9	212.2	218.9	231.9
115°	432.3	362.5	316.1	284.7	262.6	251.0	242.9	239.4	242.9	251.0	262.6
117.5°	454.8	390.7	346.5	314.0	293.3	280.5	273.3	270.0	273.3	280.5	293.3
120°	470.6	410.2	366.0	333.5	313.7	301.0	292.8	290.5	292.8	301.0	313.7
122.5°	485.5	428.8	384.6	353.0	331.4	319.6	311.4	309.1	311.4	319.6	331.4
125°	507.8	454.3	412.5	380.0	357.9	345.1	338.1	333.5	338.1	345.1	357.9
127.5°	527.1	478.0	437.6	404.8	381.8	367.2	358.8	355.1	358.8	367.2	381.8
130°	539.2	493.9	454.3	420.6	398.6	381.1	371.8	367.2	371.8	381.1	398.6
132.5°	551.3	506.9	467.4	435.5	411.6	395.1	383.0	379.3	383.0	395.1	411.6
135°	567.1	525.2	486.9	456.7	432.3	412.5	400.9	396.2	400.9	412.5	432.3
137.5°	578.2	539.2	503.4	474.6	449.2	430.4	417.6	413.2	417.6	430.4	449.2
140°	585.6	548.5	513.6	485.7	461.3	441.6	428.8	425.3	428.8	441.6	461.3
142.5°	591.2	556.8	522.9	495.9	472.5	453.6	441.8	438.3	441.8	453.6	472.5
145°	597.3	565.9	535.7	510.1	488.0	471.8	460.2	456.7	460.2	471.8	488.0
147.5°	602.6	575.2	546.8	523.8	505.5	488.7	478.5	477.3	478.5	488.7	505.5
150°	605.4	579.8	554.3	532.2	514.8	500.8	491.5	490.4	491.5	500.8	514.8
152.5°	607.3	583.6	560.8	540.6	525.0	512.0	502.7	502.4	502.7	512.0	525.0
155°	608.9	589.1	569.4	552.0	539.2	527.5	520.6	519.4	520.6	527.5	539.2
157.5°	608.9	593.1	576.4	562.6	551.5	542.4	535.9	535.9	535.9	542.4	551.5
160°	608.9	594.9	581.0	568.2	558.9	550.8	546.1	546.1	546.1	550.8	558.9
162.5°	608.9	596.8	583.8	573.8	565.4	558.2	554.5	555.4	554.5	558.2	565.4
165°	606.6	597.3	586.8	579.8	574.0	568.2	565.9	565.9	565.9	568.2	574.0
167.5°	603.8	597.0	589.4	584.0	580.8	576.4	575.2	576.4	575.2	576.4	580.8
170°	601.9	596.1	590.3	586.8	584.5	581.0	579.8	581.0	579.8	581.0	584.5
172.5°	600.1	595.2	591.2	588.7	587.3	584.7	584.5	585.6	584.5	584.7	587.3
175°	597.3	593.8	591.5	591.5	590.3	589.1	589.1	590.3	589.1	589.1	590.3
177.5°	594.2	592.4	591.5	591.5	591.5	590.5	591.5	592.4	591.5	590.5	591.5
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1684.8	1679.3	1672.1	1663.8	1653.9	1645.0	1641.2	1644.5	1646.1	1641.7	1641.2
5°	1633.6	1616.3	1602.4	1581.7	1565.1	1551.3	1541.6	1537.5	1538.8	1527.8	1525.0
7.5°	1575.9	1555.4	1532.8	1508.1	1485.2	1464.9	1454.2	1448.4	1436.7	1431.7	1423.3
10°	1538.8	1511.2	1489.1	1460.0	1433.8	1409.6	1397.8	1388.1	1376.4	1370.9	1359.1
12.5°	1500.7	1468.6	1444.3	1414.1	1387.3	1358.1	1346.9	1329.0	1310.6	1299.0	1283.9
15°	1446.9	1408.2	1378.5	1342.5	1310.7	1277.5	1247.8	1214.6	1202.2	1175.9	1160.7
17.5°	1384.0	1344.7	1307.9	1259.7	1210.6	1169.4	1137.7	1105.9	1086.9	1070.1	1062.4
20°	1342.5	1306.6	1255.4	1199.4	1144.8	1099.2	1073.6	1052.9	1032.1	1020.4	1012.1
22.5°	1303.2	1257.3	1197.9	1137.5	1082.9	1047.2	1025.5	1004.2	987.3	976.1	965.1
25°	1237.4	1177.3	1114.4	1045.3	1007.9	976.8	953.3	936.0	925.7	911.1	905.6
27.5°	1169.8	1097.0	1027.6	981.1	942.2	913.8	893.3	880.3	867.2	857.9	850.7
30°	1117.8	1043.9	981.7	937.4	898.0	874.5	857.9	842.7	832.3	824.7	819.2
32.5°	1066.4	992.4	940.2	892.6	861.5	838.6	820.9	809.5	801.4	791.5	788.2
35°	992.0	926.3	880.7	837.9	806.1	785.3	771.5	759.7	752.8	750.1	748.0
37.5°	920.5	866.8	817.7	782.6	754.2	737.9	721.6	715.8	711.1	706.1	708.3
40°	875.2	824.7	781.2	743.8	721.0	703.1	693.4	686.5	682.3	682.3	682.3
42.5°	835.9	786.6	744.1	710.7	687.8	672.6	661.9	656.0	654.7	654.1	657.4
45°	775.0	729.3	686.5	658.8	639.5	624.2	618.0	613.2	613.2	616.0	616.6
47.5°	714.5	671.8	637.4	606.4	588.7	579.2	573.8	571.3	571.6	574.3	577.5
50°	677.5	635.3	601.4	573.8	557.2	548.2	543.4	542.0	543.4	543.4	548.2
52.5°	637.1	599.4	566.0	542.8	524.0	515.6	512.9	511.0	511.8	514.1	516.1
55°	577.9	544.1	512.3	490.1	476.3	470.8	464.6	465.2	463.9	465.2	465.2
57.5°	518.6	488.2	458.6	441.1	428.9	420.9	414.1	416.0	414.0	413.7	412.6
60°	480.5	447.3	423.8	407.9	394.0	387.1	380.9	382.3	380.2	378.8	376.1
62.5°	439.0	411.3	388.9	373.6	362.5	354.5	348.3	346.9	342.1	337.4	331.3
65°	378.8	356.0	336.0	321.5	311.1	304.9	300.0	295.9	285.5	274.4	268.9
67.5°	320.4	303.9	285.2	272.9	264.5	256.3	247.1	240.0	230.3	224.3	220.8
70°	282.7	266.8	250.9	239.2	230.2	222.6	212.2	207.4	200.5	197.7	194.3
72.5°	246.8	232.0	217.2	206.6	197.0	191.1	182.9	178.1	175.0	173.9	170.5
75°	192.2	180.4	169.4	159.7	152.1	147.9	144.5	141.0	139.6	133.4	130.0
77.5°	140.2	132.5	125.5	118.6	113.2	110.5	103.8	99.8	97.5	94.6	93.9
80°	109.2	103.7	96.8	92.6	85.0	82.3	79.5	78.8	78.1	77.4	76.7
82.5°	82.1	76.6	69.7	67.2	65.1	63.5	61.8	61.1	60.4	60.8	60.7
85°	41.5	38.7	38.7	38.0	37.3	36.6	35.9	35.9	35.3	35.9	35.3
87.5°	15.7	15.1	16.5	15.4	16.4	16.9	16.1	16.4	17.1	16.3	16.3
90°	9.3	9.3	16.3	16.3	18.6	20.9	19.8	20.9	22.1	23.2	23.2
92.5°	61.4	85.5	144.6	234.7	322.6	368.6	307.0	228.2	171.7	136.7	113.4
95°	96.4	145.3	246.3	436.9	714.6	947.0	973.8	861.0	680.9	525.2	412.5
97.5°	116.7	157.6	235.4	392.8	668.8	997.5	1223.4	1272.2	1205.2	1091.6	970.3
100°	132.5	169.7	238.2	369.5	606.6	934.2	1231.7	1401.4	1424.6	1367.7	1281.7
102.5°	150.1	185.5	247.5	363.0	564.7	855.2	1162.0	1394.9	1510.1	1526.6	1490.8
105°	180.1	213.8	269.6	366.0	528.7	762.3	1035.3	1301.4	1502.5	1617.5	1665.1
107.5°	211.0	244.3	295.4	383.2	522.2	710.2	933.1	1168.7	1382.8	1544.8	1648.4
110°	232.4	263.8	314.9	396.2	524.1	692.6	882.0	1088.8	1289.8	1458.3	1586.1



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	252.9	284.2	333.5	410.2	529.6	684.2	853.1	1030.2	1208.0	1367.2	1495.0
115°	284.7	316.1	362.5	432.3	540.3	679.8	826.2	971.4	1114.4	1250.3	1361.9
117.5°	314.0	346.5	390.7	454.8	551.7	678.6	814.1	942.6	1060.9	1167.8	1262.4
120°	333.5	366.0	410.2	470.6	560.1	678.6	807.6	929.6	1037.7	1130.6	1213.1
122.5°	353.0	384.6	428.8	485.5	568.5	677.7	800.2	918.4	1022.8	1107.4	1179.7
125°	380.0	412.5	454.3	507.8	581.0	676.3	787.8	899.4	999.3	1079.5	1143.4
127.5°	404.8	437.6	478.0	527.1	591.0	673.7	771.3	876.1	971.7	1051.6	1112.3
130°	420.6	454.3	493.9	539.2	598.4	672.8	761.1	857.6	949.4	1028.4	1090.0
132.5°	435.5	467.4	506.9	551.3	604.9	671.9	751.8	838.0	924.3	1001.4	1063.0
135°	456.7	486.9	525.2	567.1	614.7	670.5	737.9	811.1	886.6	957.5	1015.6
137.5°	474.6	503.4	539.2	578.2	620.5	670.2	725.8	786.7	850.6	910.3	962.8
140°	485.7	513.6	548.5	585.6	625.2	669.3	719.3	772.7	827.3	879.6	928.4
142.5°	495.9	522.9	556.8	591.2	628.9	669.3	713.7	759.7	807.8	852.7	895.0
145°	510.1	535.7	565.9	597.3	631.0	667.0	704.2	741.4	780.9	815.7	848.3
147.5°	523.8	546.8	575.2	602.6	632.1	662.8	695.6	726.3	757.6	785.5	811.1
150°	532.2	554.3	579.8	605.4	632.1	660.0	689.1	717.0	743.7	766.9	787.8
152.5°	540.6	560.8	583.6	607.3	630.3	655.4	681.6	706.7	729.7	751.1	768.3
155°	552.0	569.4	589.1	608.9	627.5	648.4	670.5	691.4	710.0	727.4	741.4
157.5°	562.6	576.4	593.1	608.9	624.5	641.2	659.1	674.9	690.5	705.1	716.3
160°	568.2	581.0	594.9	608.9	621.7	635.6	650.7	664.7	677.4	690.2	699.5
162.5°	573.8	583.8	596.8	608.9	618.9	630.0	643.3	654.4	665.4	675.4	683.7
165°	579.8	586.8	597.3	606.6	613.5	621.7	631.0	640.3	647.2	655.4	661.2
167.5°	584.0	589.4	597.0	603.8	608.0	613.3	619.8	626.6	631.9	638.4	641.9
170°	586.8	590.3	596.1	601.9	604.2	607.7	612.4	618.2	621.7	626.3	629.8
172.5°	588.7	591.2	595.2	600.1	600.5	602.1	605.9	610.7	613.3	616.1	618.6
175°	591.5	591.5	593.8	597.3	596.1	596.1	598.4	600.8	601.9	604.2	604.2
177.5°	591.5	591.5	592.4	594.2	592.4	592.4	593.3	594.2	595.2	595.2	596.1
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1637.8	1638.9	1635.1	1634.0	1635.1	1638.9	1637.8	1641.2	1641.7	1646.1	1644.5
5°	1519.5	1518.1	1514.6	1515.3	1514.6	1518.1	1519.5	1525.0	1527.8	1538.8	1537.5
7.5°	1418.3	1412.9	1414.4	1408.9	1414.4	1412.9	1418.3	1423.3	1431.7	1436.7	1448.4
10°	1356.3	1348.7	1342.5	1337.0	1342.5	1348.7	1356.3	1359.1	1370.9	1376.4	1388.1
12.5°	1271.7	1265.2	1256.8	1258.5	1256.8	1265.2	1271.7	1283.9	1299.0	1310.6	1329.0
15°	1151.7	1141.3	1124.8	1126.8	1124.8	1141.3	1151.7	1160.7	1175.9	1202.2	1214.6
17.5°	1050.1	1050.2	1042.6	1044.4	1042.6	1050.2	1050.1	1062.4	1070.1	1086.9	1105.9
20°	997.6	992.7	993.4	991.3	993.4	992.7	997.6	1012.1	1020.4	1032.1	1052.9
22.5°	961.1	955.1	950.3	946.0	950.3	955.1	961.1	965.1	976.1	987.3	1004.2
25°	899.4	895.2	889.0	887.6	889.0	895.2	899.4	905.6	911.1	925.7	936.0
27.5°	845.2	844.4	841.9	838.7	841.9	844.4	845.2	850.7	857.9	867.2	880.3
30°	813.7	812.3	810.9	808.8	810.9	812.3	813.7	819.2	824.7	832.3	842.7
32.5°	785.5	784.6	783.2	783.4	783.2	784.6	785.5	788.2	791.5	801.4	809.5
35°	745.2	744.5	743.2	742.5	743.2	744.5	745.2	748.0	750.1	752.8	759.7
37.5°	707.6	709.4	708.6	708.4	708.6	709.4	707.6	708.3	706.1	711.1	715.8
40°	681.6	682.3	683.7	683.0	683.7	682.3	681.6	682.3	682.3	682.3	686.5
42.5°	660.1	660.2	662.1	659.8	662.1	660.2	660.1	657.4	654.1	654.7	656.0
45°	621.5	625.6	624.9	624.9	624.9	625.6	621.5	616.6	616.0	613.2	613.2
47.5°	579.3	582.9	583.9	583.7	583.9	582.9	579.3	577.5	574.3	571.6	571.3
50°	551.7	550.3	552.4	551.7	552.4	550.3	551.7	548.2	543.4	543.4	542.0
52.5°	517.9	518.2	518.1	517.4	518.1	518.2	517.9	516.1	514.1	511.8	511.0
55°	465.9	466.6	465.2	465.9	465.2	466.6	465.9	465.2	465.2	463.9	465.2
57.5°	409.5	406.2	407.6	405.9	407.6	406.2	409.5	412.6	413.7	414.0	416.0
60°	369.2	363.6	362.2	359.5	362.2	363.6	369.2	376.1	378.8	380.2	382.3
62.5°	323.8	319.9	315.2	317.4	315.2	319.9	323.8	331.3	337.4	342.1	346.9
65°	263.4	260.6	258.5	261.3	258.5	260.6	263.4	268.9	274.4	285.5	295.9
67.5°	218.0	216.5	216.5	215.1	216.5	216.5	218.0	220.8	224.3	230.3	240.0
70°	194.3	192.2	192.2	190.8	192.2	192.2	194.3	194.3	197.7	200.5	207.4
72.5°	169.9	167.8	168.4	167.6	168.4	167.8	169.9	170.5	173.9	175.0	178.1
75°	125.8	122.4	122.4	123.1	122.4	122.4	125.8	130.0	133.4	139.6	141.0
77.5°	93.9	93.2	94.2	92.9	94.2	93.2	93.9	93.9	94.6	97.5	99.8
80°	76.7	76.0	75.4	77.4	75.4	76.0	76.7	76.7	77.4	78.1	78.8
82.5°	59.6	59.5	59.3	61.9	59.3	59.5	59.6	60.7	60.8	60.4	61.1
85°	35.9	34.6	35.9	34.6	35.9	34.6	35.9	35.3	35.9	35.3	35.9
87.5°	17.6	17.3	16.5	17.0	16.5	17.3	17.6	16.3	16.3	17.1	16.4
90°	24.4	25.6	24.4	24.4	24.4	25.6	24.4	23.2	23.2	22.1	20.9
92.5°	99.7	93.4	89.5	89.5	89.5	93.4	99.7	113.4	136.7	171.7	228.2
95°	355.6	319.6	298.6	283.5	298.6	319.6	355.6	412.5	525.2	680.9	861.0
97.5°	886.8	816.9	782.0	757.9	782.0	816.9	886.8	970.3	1091.6	1205.2	1272.2
100°	1180.6	1109.7	1074.9	1065.6	1074.9	1109.7	1180.6	1281.7	1367.7	1424.6	1401.4
102.5°	1428.8	1377.4	1340.7	1333.3	1340.7	1377.4	1428.8	1490.8	1526.6	1510.1	1394.9
105°	1667.5	1658.2	1641.9	1634.9	1641.9	1658.2	1667.5	1665.1	1617.5	1502.5	1301.4
107.5°	1705.8	1732.3	1743.9	1747.0	1743.9	1732.3	1705.8	1648.4	1544.8	1382.8	1168.7
110°	1668.6	1717.4	1738.4	1748.8	1738.4	1717.4	1668.6	1586.1	1458.3	1289.8	1088.8



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1588.7	1647.7	1677.0	1694.0	1677.0	1647.7	1588.7	1495.0	1367.2	1208.0	1030.2
115°	1453.7	1523.4	1560.6	1569.9	1560.6	1523.4	1453.7	1361.9	1250.3	1114.4	971.4
117.5°	1340.7	1399.3	1436.9	1444.1	1436.9	1399.3	1340.7	1262.4	1167.8	1060.9	942.6
120°	1279.4	1330.5	1360.7	1373.5	1360.7	1330.5	1279.4	1213.1	1130.6	1037.7	929.6
122.5°	1235.7	1279.4	1304.9	1317.7	1304.9	1279.4	1235.7	1179.7	1107.4	1022.8	918.4
125°	1189.9	1223.6	1245.7	1252.6	1245.7	1223.6	1189.9	1143.4	1079.5	999.3	899.4
127.5°	1159.0	1189.0	1207.6	1214.5	1207.6	1189.0	1159.0	1112.3	1051.6	971.7	876.1
130°	1137.6	1166.6	1185.2	1192.2	1185.2	1166.6	1137.6	1090.0	1028.4	949.4	857.6
132.5°	1109.7	1142.5	1160.1	1167.1	1160.1	1142.5	1109.7	1063.0	1001.4	924.3	838.0
135°	1062.1	1094.6	1113.2	1120.2	1113.2	1094.6	1062.1	1015.6	957.5	886.6	811.1
137.5°	1006.3	1038.4	1053.7	1062.1	1053.7	1038.4	1006.3	962.8	910.3	850.6	786.7
140°	969.1	994.7	1010.9	1020.2	1010.9	994.7	969.1	928.4	879.6	827.3	772.7
142.5°	931.0	954.7	969.1	975.6	969.1	954.7	931.0	895.0	852.7	807.8	759.7
145°	877.3	897.1	908.7	914.5	908.7	897.1	877.3	848.3	815.7	780.9	741.4
147.5°	832.5	849.4	858.3	860.3	858.3	849.4	832.5	811.1	785.5	757.6	726.3
150°	806.4	821.5	828.5	829.7	828.5	821.5	806.4	787.8	766.9	743.7	717.0
152.5°	784.1	796.4	800.6	801.8	800.6	796.4	784.1	768.3	751.1	729.7	706.7
155°	753.0	762.3	765.8	765.8	765.8	762.3	753.0	741.4	727.4	710.0	691.4
157.5°	725.1	732.1	734.2	734.2	734.2	732.1	725.1	716.3	705.1	690.5	674.9
160°	706.5	713.5	714.6	714.6	714.6	713.5	706.5	699.5	690.2	677.4	664.7
162.5°	688.8	695.8	697.0	696.0	697.0	695.8	688.8	683.7	675.4	665.4	654.4
165°	665.8	670.5	669.3	668.2	669.3	670.5	665.8	661.2	655.4	647.2	640.3
167.5°	644.2	647.2	647.0	646.1	647.0	647.2	644.2	641.9	638.4	631.9	626.6
170°	632.1	633.3	632.1	632.1	632.1	633.3	632.1	629.8	626.3	621.7	618.2
172.5°	620.0	621.2	620.0	618.2	620.0	621.2	620.0	618.6	616.1	613.3	610.7
175°	604.2	606.6	604.2	601.9	604.2	606.6	604.2	604.2	604.2	601.9	600.8
177.5°	595.2	596.1	594.2	592.4	594.2	596.1	595.2	596.1	595.2	595.2	594.2
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1641.2	1645.0	1653.9	1663.8	1672.1	1679.3	1684.8	1692.6	1699.8	1709.7	1719.1
5°	1541.6	1551.3	1565.1	1581.7	1602.4	1616.3	1633.6	1648.8	1670.9	1693.0	1714.4
7.5°	1454.2	1464.9	1485.2	1508.1	1532.8	1555.4	1575.9	1602.7	1632.0	1664.2	1700.2
10°	1397.8	1409.6	1433.8	1460.0	1489.1	1511.2	1538.8	1570.6	1603.8	1643.2	1687.5
12.5°	1346.9	1358.1	1387.3	1414.1	1444.3	1468.6	1500.7	1533.0	1577.3	1620.0	1670.3
15°	1247.8	1277.5	1310.7	1342.5	1378.5	1408.2	1446.9	1480.1	1522.3	1582.4	1639.8
17.5°	1137.7	1169.4	1210.6	1259.7	1307.9	1344.7	1384.0	1425.2	1475.4	1536.8	1603.0
20°	1073.6	1099.2	1144.8	1199.4	1255.4	1306.6	1342.5	1388.1	1440.0	1506.4	1574.8
22.5°	1025.5	1047.2	1082.9	1137.5	1197.9	1257.3	1303.2	1348.3	1405.7	1472.1	1546.6
25°	953.3	976.8	1007.9	1045.3	1114.4	1177.3	1237.4	1289.3	1350.1	1416.5	1499.4
27.5°	893.3	913.8	942.2	981.1	1027.6	1097.0	1169.8	1229.0	1291.4	1362.6	1445.7
30°	857.9	874.5	898.0	937.4	981.7	1043.9	1117.8	1187.0	1249.9	1323.8	1410.3
32.5°	820.9	838.6	861.5	892.6	940.2	992.4	1066.4	1142.2	1209.0	1284.6	1369.3
35°	771.5	785.3	806.1	837.9	880.7	926.3	992.0	1070.1	1140.7	1221.5	1302.4
37.5°	721.6	737.9	754.2	782.6	817.7	866.8	920.5	1000.3	1078.4	1152.3	1231.2
40°	693.4	703.1	721.0	743.8	781.2	824.7	875.2	953.3	1031.4	1104.7	1184.2
42.5°	661.9	672.6	687.8	710.7	744.1	786.6	835.9	903.5	985.0	1056.0	1128.3
45°	618.0	624.2	639.5	658.8	686.5	729.3	775.0	835.1	911.8	979.6	1043.2
47.5°	573.8	579.2	588.7	606.4	637.4	671.8	714.5	768.5	835.8	903.5	957.3
50°	543.4	548.2	557.2	573.8	601.4	635.3	677.5	725.9	786.0	851.0	895.9
52.5°	512.9	515.6	524.0	542.8	566.0	599.4	637.1	681.6	737.9	791.8	837.3
55°	464.6	470.8	476.3	490.1	512.3	544.1	577.9	620.1	663.7	709.3	748.0
57.5°	414.1	420.9	428.9	441.1	458.6	488.2	518.6	552.8	590.0	627.8	660.3
60°	380.9	387.1	394.0	407.9	423.8	447.3	480.5	510.2	538.5	573.1	605.6
62.5°	348.3	354.5	362.5	373.6	388.9	411.3	439.0	464.8	494.3	524.4	548.6
65°	300.0	304.9	311.1	321.5	336.0	356.0	378.8	398.9	425.2	447.3	469.4
67.5°	247.1	256.3	264.5	272.9	285.2	303.9	320.4	339.6	357.4	373.9	394.0
70°	212.2	222.6	230.2	239.2	250.9	266.8	282.7	295.9	310.4	326.3	344.3
72.5°	182.9	191.1	197.0	206.6	217.2	232.0	246.8	257.7	269.5	280.4	297.8
75°	144.5	147.9	152.1	159.7	169.4	180.4	192.2	201.9	208.8	218.5	230.9
77.5°	103.8	110.5	113.2	118.6	125.5	132.5	140.2	148.4	155.0	158.4	168.0
80°	79.5	82.3	85.0	92.6	96.8	103.7	109.2	116.8	119.6	123.1	132.0
82.5°	61.8	63.5	65.1	67.2	69.7	76.6	82.1	87.0	89.7	91.0	97.8
85°	35.9	36.6	37.3	38.0	38.7	38.7	41.5	44.9	49.8	49.8	51.8
87.5°	16.1	16.9	16.4	15.4	16.5	15.1	15.7	15.5	16.9	17.8	19.0
90°	19.8	20.9	18.6	16.3	16.3	9.3	9.3	8.1	7.0	3.5	1.2
92.5°	307.0	368.6	322.6	234.7	144.6	85.5	61.4	44.4	30.2	19.3	13.2
95°	973.8	947.0	714.6	436.9	246.3	145.3	96.4	68.6	53.5	41.8	38.3
97.5°	1223.4	997.5	668.8	392.8	235.4	157.6	116.7	92.7	78.8	68.8	68.8
100°	1231.7	934.2	606.6	369.5	238.2	169.7	132.5	110.4	96.4	88.3	88.3
102.5°	1162.0	855.2	564.7	363.0	247.5	185.5	150.1	129.0	116.0	108.8	106.9
105°	1035.3	762.3	528.7	366.0	269.6	213.8	180.1	159.2	145.3	139.4	136.0
107.5°	933.1	710.2	522.2	383.2	295.4	244.3	211.0	191.0	176.2	170.3	168.0
110°	882.0	692.6	524.1	396.2	314.9	263.8	232.4	211.5	197.5	191.7	189.4



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	853.1	684.2	529.6	410.2	333.5	284.2	252.9	231.9	218.9	212.2	209.9
115°	826.2	679.8	540.3	432.3	362.5	316.1	284.7	262.6	251.0	242.9	239.4
117.5°	814.1	678.6	551.7	454.8	390.7	346.5	314.0	293.3	280.5	273.3	270.0
120°	807.6	678.6	560.1	470.6	410.2	366.0	333.5	313.7	301.0	292.8	290.5
122.5°	800.2	677.7	568.5	485.5	428.8	384.6	353.0	331.4	319.6	311.4	309.1
125°	787.8	676.3	581.0	507.8	454.3	412.5	380.0	357.9	345.1	338.1	333.5
127.5°	771.3	673.7	591.0	527.1	478.0	437.6	404.8	381.8	367.2	358.8	355.1
130°	761.1	672.8	598.4	539.2	493.9	454.3	420.6	398.6	381.1	371.8	367.2
132.5°	751.8	671.9	604.9	551.3	506.9	467.4	435.5	411.6	395.1	383.0	379.3
135°	737.9	670.5	614.7	567.1	525.2	486.9	456.7	432.3	412.5	400.9	396.2
137.5°	725.8	670.2	620.5	578.2	539.2	503.4	474.6	449.2	430.4	417.6	413.2
140°	719.3	669.3	625.2	585.6	548.5	513.6	485.7	461.3	441.6	428.8	425.3
142.5°	713.7	669.3	628.9	591.2	556.8	522.9	495.9	472.5	453.6	441.8	438.3
145°	704.2	667.0	631.0	597.3	565.9	535.7	510.1	488.0	471.8	460.2	456.7
147.5°	695.6	662.8	632.1	602.6	575.2	546.8	523.8	505.5	488.7	478.5	477.3
150°	689.1	660.0	632.1	605.4	579.8	554.3	532.2	514.8	500.8	491.5	490.4
152.5°	681.6	655.4	630.3	607.3	583.6	560.8	540.6	525.0	512.0	502.7	502.4
155°	670.5	648.4	627.5	608.9	589.1	569.4	552.0	539.2	527.5	520.6	519.4
157.5°	659.1	641.2	624.5	608.9	593.1	576.4	562.6	551.5	542.4	535.9	535.9
160°	650.7	635.6	621.7	608.9	594.9	581.0	568.2	558.9	550.8	546.1	546.1
162.5°	643.3	630.0	618.9	608.9	596.8	583.8	573.8	565.4	558.2	554.5	555.4
165°	631.0	621.7	613.5	606.6	597.3	586.8	579.8	574.0	568.2	565.9	565.9
167.5°	619.8	613.3	608.0	603.8	597.0	589.4	584.0	580.8	576.4	575.2	576.4
170°	612.4	607.7	604.2	601.9	596.1	590.3	586.8	584.5	581.0	579.8	581.0
172.5°	605.9	602.1	600.5	600.1	595.2	591.2	588.7	587.3	584.7	584.5	585.6
175°	598.4	596.1	596.1	597.3	593.8	591.5	591.5	590.3	589.1	589.1	590.3
177.5°	593.3	592.4	592.4	594.2	592.4	591.5	591.5	591.5	590.5	591.5	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1726.3	1731.3	1736.8	1747.3	1756.2	1760.1	1767.8	1773.3	1771.7	1779.4	1792.7
5°	1733.1	1751.8	1773.2	1795.3	1820.2	1840.9	1857.5	1874.1	1887.3	1903.2	1926.7
7.5°	1732.0	1765.2	1801.3	1840.9	1881.7	1917.0	1949.6	1982.8	2012.2	2044.5	2086.6
10°	1727.6	1771.8	1816.7	1868.6	1920.4	1969.5	2013.8	2055.2	2094.7	2136.8	2190.1
12.5°	1722.6	1773.5	1827.8	1890.2	1954.7	2013.8	2065.8	2125.5	2174.8	2229.2	2290.7
15°	1700.6	1769.0	1843.0	1923.9	2001.3	2080.8	2152.0	2225.3	2293.7	2358.7	2436.2
17.5°	1675.4	1754.4	1841.6	1937.2	2030.2	2126.9	2211.3	2303.7	2373.7	2460.9	2532.8
20°	1655.0	1740.0	1833.3	1940.5	2046.3	2153.4	2246.7	2340.8	2419.6	2507.4	2598.6
22.5°	1630.1	1723.4	1824.5	1935.5	2046.3	2163.4	2266.6	2360.1	2457.7	2556.6	2650.6
25°	1590.0	1686.8	1793.9	1915.6	2042.8	2162.4	2273.0	2389.1	2494.2	2601.4	2685.7
27.5°	1540.8	1642.4	1755.4	1880.9	2011.4	2133.9	2264.2	2387.9	2493.7	2596.8	2670.4
30°	1501.5	1608.7	1717.2	1844.4	1979.9	2111.2	2250.9	2374.6	2485.9	2578.6	2620.0
32.5°	1461.1	1562.8	1674.6	1803.5	1942.3	2083.6	2222.1	2348.6	2451.6	2507.2	2508.3
35°	1390.9	1486.3	1602.4	1729.0	1871.4	2024.8	2165.2	2289.6	2352.5	2357.3	2289.6
37.5°	1314.3	1401.8	1511.5	1638.1	1794.1	1946.7	2090.1	2173.0	2194.1	2123.7	1998.4
40°	1259.6	1340.4	1446.2	1576.2	1731.0	1888.6	2019.3	2080.1	2058.0	1943.9	1804.3
42.5°	1202.0	1277.4	1379.3	1507.6	1663.0	1822.3	1933.6	1966.2	1907.6	1775.8	1612.4
45°	1108.2	1177.3	1278.2	1407.5	1556.8	1706.1	1790.5	1773.9	1676.4	1520.2	1337.0
47.5°	1010.4	1077.2	1168.0	1287.6	1440.5	1569.4	1626.5	1576.5	1437.8	1265.9	1116.9
50°	945.7	1014.1	1097.8	1211.9	1351.5	1475.9	1512.6	1436.5	1282.4	1117.1	980.3
52.5°	882.1	940.6	1022.6	1132.8	1266.3	1371.4	1390.9	1303.2	1144.1	996.0	874.6
55°	785.3	838.6	907.7	1011.4	1126.8	1216.0	1205.6	1093.0	948.5	822.0	726.6
57.5°	691.7	731.8	795.7	892.9	994.2	1054.1	1016.2	920.1	785.5	681.9	601.4
60°	629.8	667.1	726.6	811.6	900.8	934.6	902.8	798.5	692.0	597.3	529.5
62.5°	571.2	604.1	655.2	734.2	806.2	826.2	792.2	701.1	605.2	524.3	468.2
65°	486.0	516.4	560.0	616.0	665.7	675.4	653.3	560.0	487.4	419.6	380.9
67.5°	408.7	428.6	462.6	511.0	537.4	543.1	500.4	441.7	377.7	336.1	306.9
70°	356.7	370.5	402.3	428.6	450.0	450.7	411.3	364.3	315.2	281.4	259.9
72.5°	306.4	319.7	343.7	361.7	378.1	372.8	336.7	299.6	259.9	234.4	218.5
75°	236.4	248.2	260.6	268.9	268.9	262.0	235.7	208.1	185.3	170.1	165.2
77.5°	171.9	181.5	185.7	184.4	182.0	171.2	154.6	136.5	128.3	121.1	117.5
80°	134.8	139.0	140.3	136.9	132.7	120.3	109.2	101.6	94.0	91.3	89.9
82.5°	100.0	103.6	100.0	100.9	91.8	81.6	75.5	72.9	69.7	68.6	67.2
85°	53.2	52.5	51.2	47.7	41.5	40.1	39.4	38.7	37.3	38.0	36.6
87.5°	18.9	18.0	16.0	15.7	15.7	16.0	16.5	17.0	17.5	16.7	18.0
90°	3.5	7.0	8.1	9.3	9.3	16.3	16.3	18.6	20.9	19.8	20.9
92.5°	19.3	30.2	44.4	61.4	85.5	144.6	234.7	322.6	368.6	307.0	228.2
95°	41.8	53.5	68.6	96.4	145.3	246.3	436.9	714.6	947.0	973.8	861.0
97.5°	68.8	78.8	92.7	116.7	157.6	235.4	392.8	668.8	997.5	1223.4	1272.2
100°	88.3	96.4	110.4	132.5	169.7	238.2	369.5	606.6	934.2	1231.7	1401.4
102.5°	108.8	116.0	129.0	150.1	185.5	247.5	363.0	564.7	855.2	1162.0	1394.9
105°	139.4	145.3	159.2	180.1	213.8	269.6	366.0	528.7	762.3	1035.3	1301.4
107.5°	170.3	176.2	191.0	211.0	244.3	295.4	383.2	522.2	710.2	933.1	1168.7
110°	191.7	197.5	211.5	232.4	263.8	314.9	396.2	524.1	692.6	882.0	1088.8



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.2	218.9	231.9	252.9	284.2	333.5	410.2	529.6	684.2	853.1	1030.2
115°	242.9	251.0	262.6	284.7	316.1	362.5	432.3	540.3	679.8	826.2	971.4
117.5°	273.3	280.5	293.3	314.0	346.5	390.7	454.8	551.7	678.6	814.1	942.6
120°	292.8	301.0	313.7	333.5	366.0	410.2	470.6	560.1	678.6	807.6	929.6
122.5°	311.4	319.6	331.4	353.0	384.6	428.8	485.5	568.5	677.7	800.2	918.4
125°	338.1	345.1	357.9	380.0	412.5	454.3	507.8	581.0	676.3	787.8	899.4
127.5°	358.8	367.2	381.8	404.8	437.6	478.0	527.1	591.0	673.7	771.3	876.1
130°	371.8	381.1	398.6	420.6	454.3	493.9	539.2	598.4	672.8	761.1	857.6
132.5°	383.0	395.1	411.6	435.5	467.4	506.9	551.3	604.9	671.9	751.8	838.0
135°	400.9	412.5	432.3	456.7	486.9	525.2	567.1	614.7	670.5	737.9	811.1
137.5°	417.6	430.4	449.2	474.6	503.4	539.2	578.2	620.5	670.2	725.8	786.7
140°	428.8	441.6	461.3	485.7	513.6	548.5	585.6	625.2	669.3	719.3	772.7
142.5°	441.8	453.6	472.5	495.9	522.9	556.8	591.2	628.9	669.3	713.7	759.7
145°	460.2	471.8	488.0	510.1	535.7	565.9	597.3	631.0	667.0	704.2	741.4
147.5°	478.5	488.7	505.5	523.8	546.8	575.2	602.6	632.1	662.8	695.6	726.3
150°	491.5	500.8	514.8	532.2	554.3	579.8	605.4	632.1	660.0	689.1	717.0
152.5°	502.7	512.0	525.0	540.6	560.8	583.6	607.3	630.3	655.4	681.6	706.7
155°	520.6	527.5	539.2	552.0	569.4	589.1	608.9	627.5	648.4	670.5	691.4
157.5°	535.9	542.4	551.5	562.6	576.4	593.1	608.9	624.5	641.2	659.1	674.9
160°	546.1	550.8	558.9	568.2	581.0	594.9	608.9	621.7	635.6	650.7	664.7
162.5°	554.5	558.2	565.4	573.8	583.8	596.8	608.9	618.9	630.0	643.3	654.4
165°	565.9	568.2	574.0	579.8	586.8	597.3	606.6	613.5	621.7	631.0	640.3
167.5°	575.2	576.4	580.8	584.0	589.4	597.0	603.8	608.0	613.3	619.8	626.6
170°	579.8	581.0	584.5	586.8	590.3	596.1	601.9	604.2	607.7	612.4	618.2
172.5°	584.5	584.7	587.3	588.7	591.2	595.2	600.1	600.5	602.1	605.9	610.7
175°	589.1	589.1	590.3	591.5	591.5	593.8	597.3	596.1	596.1	598.4	600.8
177.5°	591.5	590.5	591.5	591.5	591.5	592.4	594.2	592.4	592.4	593.3	594.2
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1799.9	1802.1	1803.8	1809.3	1809.8	1814.8	1809.8
5°	1948.8	1958.5	1973.7	1988.9	1990.3	1999.9	1982.7
7.5°	2115.8	2138.2	2152.2	2176.8	2186.5	2192.5	2182.6
10°	2230.8	2251.6	2288.2	2306.2	2324.2	2326.9	2318.6
12.5°	2342.0	2374.9	2403.8	2437.8	2437.0	2461.3	2452.5
15°	2490.1	2524.0	2564.0	2602.1	2615.9	2615.9	2627.0
17.5°	2595.7	2657.8	2699.3	2729.1	2761.8	2767.4	2763.6
20°	2667.1	2734.1	2778.4	2817.1	2839.2	2845.4	2845.4
22.5°	2720.1	2777.2	2820.4	2855.2	2873.5	2880.8	2878.6
25°	2756.9	2806.0	2832.3	2842.6	2847.5	2846.1	2833.0
27.5°	2706.6	2704.4	2687.8	2656.0	2632.1	2617.6	2601.0
30°	2610.4	2574.4	2532.9	2487.3	2428.6	2383.6	2369.8
32.5°	2467.1	2386.4	2316.1	2240.1	2176.9	2132.0	2113.2
35°	2190.1	2062.2	1957.8	1866.5	1800.2	1758.7	1744.9
37.5°	1861.3	1737.5	1608.3	1519.8	1464.7	1422.8	1407.2
40°	1652.2	1517.4	1404.7	1321.8	1265.1	1224.3	1223.6
42.5°	1461.4	1332.7	1226.7	1166.9	1105.8	1078.8	1078.7
45°	1196.6	1093.6	1003.8	956.8	920.1	898.0	891.8
47.5°	990.8	905.6	845.7	808.3	778.4	764.3	755.2
50°	875.2	800.5	752.8	720.3	703.7	685.8	684.4
52.5°	779.0	718.7	681.5	655.1	634.1	623.3	623.6
55°	654.7	607.0	580.7	560.6	544.1	535.8	532.3
57.5°	551.5	515.7	496.6	478.2	471.2	464.7	462.9
60°	487.4	463.2	445.2	430.7	420.3	418.2	417.5
62.5°	434.3	409.0	396.5	385.3	377.7	374.5	373.3
65°	358.1	339.4	328.4	319.4	316.6	311.8	311.1
67.5°	288.7	277.5	270.2	263.9	260.2	259.9	259.9
70°	246.1	239.9	233.7	230.2	228.1	226.7	226.7
72.5°	209.6	205.0	199.9	198.1	197.7	196.3	195.8
75°	159.7	154.9	155.5	152.1	149.3	145.9	143.8
77.5°	113.2	109.8	109.1	108.7	106.3	105.9	107.0
80°	87.8	84.3	83.6	84.3	83.6	81.6	81.6
82.5°	66.8	63.9	63.2	62.8	62.1	62.8	61.7
85°	35.9	34.6	34.6	34.6	35.9	35.3	34.6
87.5°	17.1	16.8	17.4	17.0	17.3	16.5	17.0
90°	22.1	23.2	23.2	24.4	25.6	24.4	24.4
92.5°	171.7	136.7	113.4	99.7	93.4	89.5	89.5
95°	680.9	525.2	412.5	355.6	319.6	298.6	283.5
97.5°	1205.2	1091.6	970.3	886.8	816.9	782.0	757.9
100°	1424.6	1367.7	1281.7	1180.6	1109.7	1074.9	1065.6
102.5°	1510.1	1526.6	1490.8	1428.8	1377.4	1340.7	1333.3
105°	1502.5	1617.5	1665.1	1667.5	1658.2	1641.9	1634.9
107.5°	1382.8	1544.8	1648.4	1705.8	1732.3	1743.9	1747.0
110°	1289.8	1458.3	1586.1	1668.6	1717.4	1738.4	1748.8



TEST NUMBER: P332981

CATALOG NUMBER: SA4XXRDIP-C1020D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1208.0	1367.2	1495.0	1588.7	1647.7	1677.0	1694.0
115°	1114.4	1250.3	1361.9	1453.7	1523.4	1560.6	1569.9
117.5°	1060.9	1167.8	1262.4	1340.7	1399.3	1436.9	1444.1
120°	1037.7	1130.6	1213.1	1279.4	1330.5	1360.7	1373.5
122.5°	1022.8	1107.4	1179.7	1235.7	1279.4	1304.9	1317.7
125°	999.3	1079.5	1143.4	1189.9	1223.6	1245.7	1252.6
127.5°	971.7	1051.6	1112.3	1159.0	1189.0	1207.6	1214.5
130°	949.4	1028.4	1090.0	1137.6	1166.6	1185.2	1192.2
132.5°	924.3	1001.4	1063.0	1109.7	1142.5	1160.1	1167.1
135°	886.6	957.5	1015.6	1062.1	1094.6	1113.2	1120.2
137.5°	850.6	910.3	962.8	1006.3	1038.4	1053.7	1062.1
140°	827.3	879.6	928.4	969.1	994.7	1010.9	1020.2
142.5°	807.8	852.7	895.0	931.0	954.7	969.1	975.6
145°	780.9	815.7	848.3	877.3	897.1	908.7	914.5
147.5°	757.6	785.5	811.1	832.5	849.4	858.3	860.3
150°	743.7	766.9	787.8	806.4	821.5	828.5	829.7
152.5°	729.7	751.1	768.3	784.1	796.4	800.6	801.8
155°	710.0	727.4	741.4	753.0	762.3	765.8	765.8
157.5°	690.5	705.1	716.3	725.1	732.1	734.2	734.2
160°	677.4	690.2	699.5	706.5	713.5	714.6	714.6
162.5°	665.4	675.4	683.7	688.8	695.8	697.0	696.0
165°	647.2	655.4	661.2	665.8	670.5	669.3	668.2
167.5°	631.9	638.4	641.9	644.2	647.2	647.0	646.1
170°	621.7	626.3	629.8	632.1	633.3	632.1	632.1
172.5°	613.3	616.1	618.6	620.0	621.2	620.0	618.2
175°	601.9	604.2	604.2	604.2	606.6	604.2	601.9
177.5°	595.2	595.2	596.1	595.2	596.1	594.2	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5

(END OF REPORT)