

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333014

Luminaire Tested: **SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P333014  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9123.1 lumens  
Efficiency: N/A  
Efficacy: 127.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333014  
CATALOG NUMBER: SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333014

CATALOG NUMBER: SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	46	44	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	48	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16835	16835	16835
5°	16874	16667	16771
10°	16768	16467	16467
15°	16575	16121	16002
20°	16311	15667	15378
25°	15973	15134	14750
30°	15645	14573	13962
35°	15281	13991	13172
40°	14842	13328	12318
45°	14439	12670	11449
50°	13978	11912	10528
55°	13485	11125	9529
60°	12943	10261	8507
65°	12445	9181	7503
70°	11722	7990	6371
75°	10808	6625	5181
80°	9428	5049	4751
85°	7984	4585	4289



TEST NUMBER: P333014

CATALOG NUMBER: SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.9	2.1
10°-20°	546.3	6.0
20°-30°	788.8	8.6
30°-40°	894.2	9.8
40°-50°	863.5	9.5
50°-60°	718.0	7.9
60°-70°	495.8	5.4
70°-80°	251.3	2.8
80°-90°	67.7	0.7
90°-100°	427.2	4.7
100°-110°	889.1	9.7
110°-120°	796.4	8.7
120°-130°	669.9	7.3
130°-140°	558.5	6.1
140°-150°	426.7	4.7
150°-160°	299.9	3.3
160°-170°	176.4	1.9
170°-180°	57.4	0.6
0°-30°	1531.0	16.8
0°-40°	2425.2	26.6
0°-60°	4006.7	43.9
0°-90°	4821.5	52.8
90°-120°	2112.7	23.2
90°-150°	3767.8	41.3
90°-180°	4302.0	47.2
0°-180°	9123.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2057	2072	2070	197
15°	1983	1967	1929	1925	1915	559
25°	1793	1762	1699	1672	1656	826
35°	1550	1498	1420	1367	1336	968
45°	1265	1204	1110	1034	1003	975
55°	958	892	790	710	677	857
65°	652	581	481	415	393	643
75°	346	287	212	177	166	366
85°	86	56	50	46	46	97
90°	1	9	21	23	24	6
95°	38	121	947	469	284	43
105°	136	197	762	1641	1635	145
115°	239	300	680	1306	1570	237
125°	334	396	676	1111	1253	297
135°	396	472	670	987	1120	306
145°	457	523	667	832	914	287
155°	519	561	648	734	766	239
165°	566	583	622	658	668	160
175°	590	592	596	604	602	56
180°	592	592	592	592	592	



TEST NUMBER: P333014

CATALOG NUMBER: SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2090.5	2089.4	2088.3	2087.1	2086.0	2083.9	2080.8	2077.6	2074.5	2071.4	2074.5
5°	2082.2	2080.8	2079.4	2078.0	2076.6	2073.7	2069.5	2065.2	2061.0	2056.7	2060.2
7.5°	2063.4	2061.9	2060.4	2058.9	2057.4	2053.9	2048.4	2042.9	2037.3	2031.8	2034.1
10°	2045.5	2043.7	2042.0	2040.2	2038.4	2034.3	2028.0	2021.6	2015.2	2008.8	2010.2
12.5°	2022.5	2020.5	2018.4	2016.3	2014.3	2009.5	2002.0	1994.5	1986.9	1979.4	1980.3
15°	1983.2	1980.0	1976.9	1973.7	1970.5	1964.4	1955.6	1946.7	1937.8	1928.9	1928.2
17.5°	1935.7	1931.0	1926.4	1921.8	1917.2	1909.6	1898.9	1888.3	1877.6	1867.0	1865.0
20°	1898.6	1894.0	1889.4	1884.8	1880.2	1871.8	1859.8	1847.7	1835.6	1823.6	1820.7
22.5°	1857.7	1852.6	1847.4	1842.2	1837.0	1828.0	1815.0	1802.1	1789.2	1776.3	1772.0
25°	1793.2	1786.8	1780.4	1774.1	1767.7	1757.2	1742.7	1728.1	1713.6	1699.0	1693.0
27.5°	1725.5	1717.5	1709.5	1701.5	1693.4	1681.7	1666.1	1650.6	1635.0	1619.5	1612.0
30°	1678.3	1669.4	1660.5	1651.6	1642.8	1630.0	1613.3	1596.6	1580.0	1563.3	1554.4
32.5°	1628.4	1618.4	1608.4	1598.4	1588.4	1574.8	1557.5	1540.3	1523.0	1505.8	1495.5
35°	1550.5	1539.1	1527.8	1516.4	1505.1	1490.5	1472.8	1455.1	1437.3	1419.6	1407.5
37.5°	1467.2	1455.4	1443.7	1432.0	1420.3	1404.6	1385.0	1365.3	1345.7	1326.0	1312.5
40°	1408.4	1396.7	1385.0	1373.3	1361.5	1345.6	1325.4	1305.1	1284.9	1264.7	1249.8
42.5°	1352.2	1339.9	1327.6	1315.3	1303.1	1286.4	1265.3	1244.2	1223.2	1202.1	1186.9
45°	1264.7	1251.5	1238.4	1225.3	1212.2	1194.9	1173.7	1152.4	1131.1	1109.8	1092.4
47.5°	1174.3	1160.7	1147.2	1133.6	1120.1	1102.2	1080.1	1057.9	1035.8	1013.7	995.6
50°	1113.0	1099.1	1085.3	1071.5	1057.6	1039.3	1016.6	993.9	971.2	948.5	930.8
52.5°	1050.4	1036.8	1023.3	1009.7	996.2	977.7	954.5	931.2	907.9	884.6	866.6
55°	958.1	943.9	929.7	915.5	901.3	882.7	859.6	836.6	813.5	790.4	772.0
57.5°	866.7	852.0	837.2	822.5	807.7	789.0	766.3	743.5	720.8	698.1	679.4
60°	801.6	787.4	773.2	759.0	744.8	726.4	703.7	681.0	658.2	635.5	617.1
62.5°	742.8	728.1	713.3	698.6	683.8	664.8	641.5	618.2	594.9	571.7	554.6
65°	651.5	636.2	621.0	605.7	590.5	571.5	548.8	526.1	503.4	480.6	465.4
67.5°	556.6	542.0	527.4	512.8	498.2	480.3	459.2	438.2	417.1	396.0	382.9
70°	496.6	481.7	466.8	451.9	437.0	419.4	399.2	379.0	358.8	338.5	326.8
72.5°	432.7	419.3	405.8	392.3	378.8	362.5	343.4	324.3	305.2	286.1	276.1
75°	346.5	333.4	320.2	307.1	294.0	279.1	262.4	245.7	229.1	212.4	204.2
77.5°	259.0	247.9	236.7	225.6	214.4	202.1	188.6	175.2	161.7	148.2	143.4
80°	202.8	192.5	182.2	171.9	161.6	151.2	140.5	129.9	119.2	108.6	107.5
82.5°	154.3	144.8	135.4	125.9	116.5	108.7	102.6	96.5	90.4	84.3	83.5
85°	86.2	79.1	72.0	64.9	57.8	53.8	52.7	51.6	50.6	49.5	48.8
87.5°	29.6	27.8	26.2	24.2	22.2	20.9	22.0	21.7	21.9	22.1	21.6
90°	1.2	3.5	7.0	8.1	9.3	9.3	16.3	16.3	18.6	20.9	19.8
92.5°	13.2	19.3	30.2	44.4	61.4	85.5	144.6	234.7	322.6	368.6	307.0
95°	38.3	41.8	53.5	68.6	96.4	145.3	246.3	436.9	714.6	947.0	973.8
97.5°	68.8	68.8	78.8	92.7	116.7	157.6	235.4	392.8	668.8	997.5	1223.4
100°	88.3	88.3	96.4	110.4	132.5	169.7	238.2	369.5	606.6	934.2	1231.7
102.5°	106.9	108.8	116.0	129.0	150.1	185.5	247.5	363.0	564.7	855.2	1162.0
105°	136.0	139.4	145.3	159.2	180.1	213.8	269.6	366.0	528.7	762.3	1035.3
107.5°	168.0	170.3	176.2	191.0	211.0	244.3	295.4	383.2	522.2	710.2	933.1
110°	189.4	191.7	197.5	211.5	232.4	263.8	314.9	396.2	524.1	692.6	882.0



TEST NUMBER: P333014

CATALOG NUMBER: SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	209.9	212.2	218.9	231.9	252.9	284.2	333.5	410.2	529.6	684.2	853.1
115°	239.4	242.9	251.0	262.6	284.7	316.1	362.5	432.3	540.3	679.8	826.2
117.5°	270.0	273.3	280.5	293.3	314.0	346.5	390.7	454.8	551.7	678.6	814.1
120°	290.5	292.8	301.0	313.7	333.5	366.0	410.2	470.6	560.1	678.6	807.6
122.5°	309.1	311.4	319.6	331.4	353.0	384.6	428.8	485.5	568.5	677.7	800.2
125°	333.5	338.1	345.1	357.9	380.0	412.5	454.3	507.8	581.0	676.3	787.8
127.5°	355.1	358.8	367.2	381.8	404.8	437.6	478.0	527.1	591.0	673.7	771.3
130°	367.2	371.8	381.1	398.6	420.6	454.3	493.9	539.2	598.4	672.8	761.1
132.5°	379.3	383.0	395.1	411.6	435.5	467.4	506.9	551.3	604.9	671.9	751.8
135°	396.2	400.9	412.5	432.3	456.7	486.9	525.2	567.1	614.7	670.5	737.9
137.5°	413.2	417.6	430.4	449.2	474.6	503.4	539.2	578.2	620.5	670.2	725.8
140°	425.3	428.8	441.6	461.3	485.7	513.6	548.5	585.6	625.2	669.3	719.3
142.5°	438.3	441.8	453.6	472.5	495.9	522.9	556.8	591.2	628.9	669.3	713.7
145°	456.7	460.2	471.8	488.0	510.1	535.7	565.9	597.3	631.0	667.0	704.2
147.5°	477.3	478.5	488.7	505.5	523.8	546.8	575.2	602.6	632.1	662.8	695.6
150°	490.4	491.5	500.8	514.8	532.2	554.3	579.8	605.4	632.1	660.0	689.1
152.5°	502.4	502.7	512.0	525.0	540.6	560.8	583.6	607.3	630.3	655.4	681.6
155°	519.4	520.6	527.5	539.2	552.0	569.4	589.1	608.9	627.5	648.4	670.5
157.5°	535.9	535.9	542.4	551.5	562.6	576.4	593.1	608.9	624.5	641.2	659.1
160°	546.1	546.1	550.8	558.9	568.2	581.0	594.9	608.9	621.7	635.6	650.7
162.5°	555.4	554.5	558.2	565.4	573.8	583.8	596.8	608.9	618.9	630.0	643.3
165°	565.9	565.9	568.2	574.0	579.8	586.8	597.3	606.6	613.5	621.7	631.0
167.5°	576.4	575.2	576.4	580.8	584.0	589.4	597.0	603.8	608.0	613.3	619.8
170°	581.0	579.8	581.0	584.5	586.8	590.3	596.1	601.9	604.2	607.7	612.4
172.5°	585.6	584.5	584.7	587.3	588.7	591.2	595.2	600.1	600.5	602.1	605.9
175°	590.3	589.1	589.1	590.3	591.5	591.5	593.8	597.3	596.1	596.1	598.4
177.5°	592.4	591.5	590.5	591.5	591.5	591.5	592.4	594.2	592.4	592.4	593.3
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P333014

CATALOG NUMBER: SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2077.6	2080.8	2083.9	2085.3	2085.0	2084.7	2084.4	2084.2
5°	2063.8	2067.3	2070.9	2072.3	2071.6	2070.9	2070.2	2069.5
7.5°	2036.3	2038.6	2040.9	2041.4	2040.3	2039.2	2038.0	2036.9
10°	2011.6	2013.0	2014.5	2014.5	2013.0	2011.6	2010.2	2008.8
12.5°	1981.1	1982.0	1982.8	1982.2	1980.3	1978.3	1976.3	1974.3
15°	1927.5	1926.8	1926.1	1924.5	1922.0	1919.5	1917.1	1914.6
17.5°	1863.0	1861.0	1859.0	1856.2	1852.4	1848.6	1844.9	1841.1
20°	1817.9	1815.0	1812.2	1808.5	1803.9	1799.3	1794.6	1790.0
22.5°	1767.8	1763.5	1759.3	1755.3	1751.5	1747.7	1744.0	1740.2
25°	1686.9	1680.9	1674.9	1670.1	1666.5	1663.0	1659.4	1655.9
27.5°	1604.6	1597.1	1589.7	1583.4	1578.3	1573.2	1568.1	1563.0
30°	1545.5	1536.7	1527.8	1520.5	1514.8	1509.2	1503.5	1497.8
32.5°	1485.2	1474.9	1464.6	1456.8	1451.4	1446.0	1440.6	1435.2
35°	1395.4	1383.4	1371.3	1362.1	1355.7	1349.3	1342.9	1336.5
37.5°	1299.0	1285.5	1272.1	1262.1	1255.7	1249.3	1243.0	1236.6
40°	1234.9	1220.0	1205.1	1194.4	1188.0	1181.6	1175.3	1168.9
42.5°	1171.7	1156.5	1141.3	1130.4	1123.7	1117.1	1110.4	1103.7
45°	1075.0	1057.6	1040.2	1028.3	1022.0	1015.6	1009.2	1002.8
47.5°	977.6	959.6	941.6	929.0	922.0	915.0	907.9	900.9
50°	913.0	895.3	877.5	865.3	858.6	851.8	845.1	838.3
52.5°	848.6	830.6	812.5	800.0	793.0	786.0	778.9	771.9
55°	753.5	735.1	716.6	704.0	697.3	690.5	683.8	677.0
57.5°	660.7	641.9	623.2	611.3	606.2	601.0	595.9	590.8
60°	598.6	580.2	561.7	549.7	544.0	538.3	532.6	526.9
62.5°	537.6	520.6	503.5	492.7	488.2	483.7	479.1	474.6
65°	450.1	434.9	419.6	409.8	405.6	401.3	397.1	392.8
67.5°	369.8	356.6	343.5	334.6	329.9	325.2	320.5	315.8
70°	315.1	303.4	291.7	284.1	280.5	277.0	273.4	269.9
72.5°	266.1	256.1	246.1	239.5	236.2	233.0	229.7	226.4
75°	196.1	187.9	179.7	174.6	172.5	170.3	168.2	166.1
77.5°	138.7	133.9	129.2	126.5	125.8	125.2	124.6	123.9
80°	106.5	105.4	104.3	103.6	103.3	102.9	102.6	102.2
82.5°	82.8	82.0	81.2	80.6	80.3	79.9	79.6	79.2
85°	48.1	47.4	46.7	46.3	46.3	46.3	46.3	46.3
87.5°	21.5	21.4	21.4	21.4	21.9	22.4	22.5	22.8
90°	20.9	22.1	23.2	23.2	24.4	25.6	24.4	24.4
92.5°	228.2	171.7	136.7	113.4	99.7	93.4	89.5	89.5
95°	861.0	680.9	525.2	412.5	355.6	319.6	298.6	283.5
97.5°	1272.2	1205.2	1091.6	970.3	886.8	816.9	782.0	757.9
100°	1401.4	1424.6	1367.7	1281.7	1180.6	1109.7	1074.9	1065.6
102.5°	1394.9	1510.1	1526.6	1490.8	1428.8	1377.4	1340.7	1333.3
105°	1301.4	1502.5	1617.5	1665.1	1667.5	1658.2	1641.9	1634.9
107.5°	1168.7	1382.8	1544.8	1648.4	1705.8	1732.3	1743.9	1747.0
110°	1088.8	1289.8	1458.3	1586.1	1668.6	1717.4	1738.4	1748.8





TEST NUMBER: P333014

CATALOG NUMBER: SA4XXRDIP-C1195D1205U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1030.2	1208.0	1367.2	1495.0	1588.7	1647.7	1677.0	1694.0
115°	971.4	1114.4	1250.3	1361.9	1453.7	1523.4	1560.6	1569.9
117.5°	942.6	1060.9	1167.8	1262.4	1340.7	1399.3	1436.9	1444.1
120°	929.6	1037.7	1130.6	1213.1	1279.4	1330.5	1360.7	1373.5
122.5°	918.4	1022.8	1107.4	1179.7	1235.7	1279.4	1304.9	1317.7
125°	899.4	999.3	1079.5	1143.4	1189.9	1223.6	1245.7	1252.6
127.5°	876.1	971.7	1051.6	1112.3	1159.0	1189.0	1207.6	1214.5
130°	857.6	949.4	1028.4	1090.0	1137.6	1166.6	1185.2	1192.2
132.5°	838.0	924.3	1001.4	1063.0	1109.7	1142.5	1160.1	1167.1
135°	811.1	886.6	957.5	1015.6	1062.1	1094.6	1113.2	1120.2
137.5°	786.7	850.6	910.3	962.8	1006.3	1038.4	1053.7	1062.1
140°	772.7	827.3	879.6	928.4	969.1	994.7	1010.9	1020.2
142.5°	759.7	807.8	852.7	895.0	931.0	954.7	969.1	975.6
145°	741.4	780.9	815.7	848.3	877.3	897.1	908.7	914.5
147.5°	726.3	757.6	785.5	811.1	832.5	849.4	858.3	860.3
150°	717.0	743.7	766.9	787.8	806.4	821.5	828.5	829.7
152.5°	706.7	729.7	751.1	768.3	784.1	796.4	800.6	801.8
155°	691.4	710.0	727.4	741.4	753.0	762.3	765.8	765.8
157.5°	674.9	690.5	705.1	716.3	725.1	732.1	734.2	734.2
160°	664.7	677.4	690.2	699.5	706.5	713.5	714.6	714.6
162.5°	654.4	665.4	675.4	683.7	688.8	695.8	697.0	696.0
165°	640.3	647.2	655.4	661.2	665.8	670.5	669.3	668.2
167.5°	626.6	631.9	638.4	641.9	644.2	647.2	647.0	646.1
170°	618.2	621.7	626.3	629.8	632.1	633.3	632.1	632.1
172.5°	610.7	613.3	616.1	618.6	620.0	621.2	620.0	618.2
175°	600.8	601.9	604.2	604.2	604.2	606.6	604.2	601.9
177.5°	594.2	595.2	595.2	596.1	595.2	596.1	594.2	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5

(END OF REPORT)