

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907601

Luminaire Tested: DFN2DIP-4P2F0-020D030US840-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907601
REPORT IS A COMBINATION OF REPORTS P900538 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D030US840-RLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4716.1 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 40
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907601
CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907601

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				36
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31				31
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32	27				27
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28	23				23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20				20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18				18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16				16
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14				14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13				13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12				12
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2090	2090	2090
5°	2089	2052	2067
10°	2065	2006	1996
15°	2032	1935	1889
20°	1990	1839	1759
25°	1947	1731	1633
30°	1891	1622	1475
35°	1836	1505	1336
40°	1780	1385	1177
45°	1715	1252	1033
50°	1648	1119	894
55°	1577	977	759
60°	1495	829	622
65°	1399	680	556
70°	1284	540	498
75°	1140	466	446
80°	932	377	376
85°	600	231	265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1715 cd/sqm



TEST NUMBER: P907601

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	1.7
10°-20°	214.8	4.6
20°-30°	301.5	6.4
30°-40°	328.7	7.0
40°-50°	302.1	6.4
50°-60°	237.3	5.0
60°-70°	154.4	3.3
70°-80°	79.5	1.7
80°-90°	22.1	0.5
90°-100°	33.7	0.7
100°-110°	125.7	2.7
110°-120°	333.3	7.1
120°-130°	552.9	11.7
130°-140°	587.3	12.5
140°-150°	545.8	11.6
150°-160°	438.8	9.3
160°-170°	282.8	6.0
170°-180°	97.3	2.1
0°-30°	594.5	12.6
0°-40°	923.2	19.6
0°-60°	1462.6	31.0
0°-90°	1718.6	36.4
90°-120°	492.7	10.4
90°-150°	2178.7	46.2
90°-180°	2998.0	63.6
0°-180°	4716.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	835	835	835	835	835	
5°	835	831	821	828	826	79
15°	794	786	760	746	738	224
25°	721	696	647	616	604	331
35°	621	582	516	468	452	389
45°	508	457	378	324	306	392
55°	386	327	246	200	186	345
65°	261	199	132	106	104	258
75°	139	86	60	55	54	147
85°	32	17	14	14	14	37
90°	1	9	15	19	20	4
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P907601

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	834.8	834.8	834.8	834.8	834.8
2.5°	838.5	834.8	826.4	834.0	832.5
5°	834.8	831.0	821.1	828.0	825.7
7.5°	828.0	823.4	812.8	815.9	812.0
10°	818.9	813.5	798.5	796.2	791.7
12.5°	807.6	800.7	780.3	775.9	767.5
15°	794.0	785.6	759.9	745.6	738.1
17.5°	778.1	766.0	734.3	717.6	705.6
20°	759.9	744.8	707.1	688.2	671.6
22.5°	740.3	723.0	679.1	653.5	642.2
25°	720.7	696.5	646.6	615.7	604.3
27.5°	697.3	671.6	616.4	580.9	563.5
30°	672.4	643.6	583.2	544.7	524.2
32.5°	648.1	613.4	551.5	506.1	487.3
35°	621.0	582.5	516.0	468.4	451.7
37.5°	594.5	552.9	482.7	430.6	411.7
40°	566.5	521.3	448.0	394.4	374.7
42.5°	537.9	489.6	413.2	357.3	338.5
45°	507.7	457.0	377.8	324.1	305.9
47.5°	479.0	425.4	343.8	290.0	273.5
50°	447.3	393.6	310.5	258.3	242.6
52.5°	416.2	359.5	278.7	228.9	214.6
55°	386.0	327.1	245.5	200.3	185.8
57.5°	355.1	294.6	216.1	173.8	161.7
60°	323.4	262.9	185.1	146.6	134.5
62.5°	292.4	232.0	158.6	122.4	116.3
65°	260.6	199.4	131.5	105.8	103.5
67.5°	230.5	169.2	105.8	92.9	90.7
70°	198.6	139.8	87.6	80.1	77.1
72.5°	168.4	112.5	73.2	67.3	65.7
75°	139.0	86.0	60.4	55.1	54.4
77.5°	109.6	61.2	47.6	44.5	43.0
80°	82.3	43.8	36.3	33.2	33.2
82.5°	57.4	29.5	24.9	23.4	23.4
85°	32.4	16.6	14.3	14.3	14.3
87.5°	12.1	6.1	6.1	5.3	5.3
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P907601

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P907601
 CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.16	8.89	9.23	9.96	11.41	4.12	4.85	5.19	5.92	7.38
	3H	9.81	10.46	10.89	11.54	13.01	5.28	5.93	6.36	7.01	8.49
	4H	10.39	11.01	11.49	12.09	13.57	5.71	6.33	6.80	7.41	8.89
	6H	10.79	11.36	11.89	12.44	13.94	6.01	6.58	7.11	7.66	9.15
	8H	10.91	11.45	12.01	12.55	14.03	6.09	6.63	7.19	7.73	9.21
	12H	10.96	11.47	12.06	12.56	14.07	6.12	6.63	7.23	7.72	9.23
4H	2H	8.16	8.78	9.26	9.86	11.34	4.69	5.31	5.79	6.39	7.87
	3H	9.95	10.47	11.06	11.57	13.07	6.01	6.52	7.11	7.63	9.12
	4H	10.62	11.10	11.73	12.19	13.70	6.53	7.01	7.64	8.10	9.62
	6H	11.11	11.52	12.23	12.63	14.14	6.92	7.33	8.04	8.45	9.95
	8H	11.27	11.65	12.39	12.76	14.28	7.04	7.42	8.16	8.53	10.05
	12H	11.35	11.69	12.48	12.81	14.34	7.09	7.43	8.22	8.55	10.08
8H	4H	10.58	10.96	11.69	12.07	13.59	6.79	7.17	7.91	8.28	9.80
	6H	11.12	11.43	12.25	12.58	14.10	7.28	7.59	8.42	8.74	10.26
	8H	11.32	11.59	12.46	12.72	14.26	7.45	7.73	8.60	8.86	10.40
	12H	11.43	11.67	12.58	12.80	14.38	7.55	7.79	8.70	8.92	10.49
12H	4H	10.52	10.87	11.66	11.99	13.52	6.79	7.13	7.92	8.26	9.78
	6H	11.09	11.36	12.23	12.50	14.03	7.32	7.59	8.46	8.73	10.27
	8H	11.29	11.53	12.44	12.66	14.23	7.51	7.75	8.66	8.88	10.45