

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332870

Luminaire Tested: **SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332870
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2737.6 lumens
Efficiency: N/A
Efficacy: 134.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332870
CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332870

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	55	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P332870

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	2.1
10°-20°	161.9	5.9
20°-30°	233.8	8.5
30°-40°	265.1	9.7
40°-50°	255.9	9.3
50°-60°	212.8	7.8
60°-70°	147.0	5.4
70°-80°	74.5	2.7
80°-90°	20.1	0.7
90°-100°	129.9	4.7
100°-110°	270.4	9.9
110°-120°	242.2	8.8
120°-130°	203.7	7.4
130°-140°	169.9	6.2
140°-150°	129.8	4.7
150°-160°	91.2	3.3
160°-170°	53.7	2.0
170°-180°	17.5	0.6
0°-30°	453.8	16.6
0°-40°	718.9	26.3
0°-60°	1187.7	43.4
0°-90°	1429.2	52.2
90°-120°	642.6	23.5
90°-150°	1146.0	41.9
90°-180°	1308.0	47.8
0°-180°	2737.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	0	3	6	7	7	2
95°	12	37	288	143	86	13
105°	41	60	232	499	497	44
115°	73	91	207	397	478	72
125°	101	121	206	338	381	90
135°	120	144	204	300	341	93
145°	139	159	203	253	278	87
155°	158	171	197	223	233	73
165°	172	177	189	200	203	49
175°	180	180	181	184	183	17
180°	180	180	180	180	180	



TEST NUMBER: P332870

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	8.8	8.2	7.8	7.2	6.6	6.2	6.5	6.5	6.5	6.6	6.4
90°	0.4	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.7	6.4	6.0
92.5°	4.0	5.9	9.2	13.5	18.7	26.0	44.0	71.4	98.1	112.1	93.4
95°	11.7	12.7	16.3	20.9	29.3	44.2	74.9	132.9	217.4	288.0	296.2
97.5°	20.9	20.9	24.0	28.2	35.5	47.9	71.6	119.5	203.4	303.4	372.1
100°	26.9	26.9	29.3	33.6	40.3	51.6	72.5	112.4	184.5	284.2	374.6
102.5°	32.5	33.1	35.3	39.2	45.7	56.4	75.3	110.4	171.8	260.1	353.4
105°	41.4	42.4	44.2	48.4	54.8	65.0	82.0	111.3	160.8	231.8	314.9
107.5°	51.1	51.8	53.6	58.1	64.2	74.3	89.8	116.6	158.8	216.0	283.8
110°	57.6	58.3	60.1	64.3	70.7	80.2	95.8	120.5	159.4	210.6	268.3



TEST NUMBER: P332870

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	63.8	64.5	66.6	70.5	76.9	86.4	101.4	124.8	161.1	208.1	259.5
115°	72.8	73.9	76.3	79.9	86.6	96.1	110.3	131.5	164.3	206.8	251.3
117.5°	82.1	83.1	85.3	89.2	95.5	105.4	118.8	138.3	167.8	206.4	247.6
120°	88.4	89.1	91.5	95.4	101.4	111.3	124.8	143.1	170.4	206.4	245.6
122.5°	94.0	94.7	97.2	100.8	107.4	117.0	130.4	147.7	172.9	206.1	243.4
125°	101.4	102.8	105.0	108.9	115.6	125.5	138.2	154.4	176.7	205.7	239.6
127.5°	108.0	109.1	111.7	116.1	123.1	133.1	145.4	160.3	179.8	204.9	234.6
130°	111.7	113.1	115.9	121.2	127.9	138.2	150.2	164.0	182.0	204.6	231.5
132.5°	115.4	116.5	120.2	125.2	132.5	142.1	154.2	167.7	184.0	204.4	228.7
135°	120.5	121.9	125.5	131.5	138.9	148.1	159.7	172.5	187.0	203.9	224.4
137.5°	125.7	127.0	130.9	136.6	144.3	153.1	164.0	175.9	188.7	203.9	220.8
140°	129.4	130.4	134.3	140.3	147.7	156.2	166.8	178.1	190.1	203.6	218.8
142.5°	133.3	134.4	138.0	143.7	150.8	159.0	169.4	179.8	191.3	203.6	217.1
145°	138.9	140.0	143.5	148.4	155.2	162.9	172.1	181.7	191.9	202.9	214.2
147.5°	145.2	145.5	148.7	153.7	159.3	166.3	174.9	183.3	192.3	201.6	211.6
150°	149.1	149.5	152.3	156.6	161.9	168.6	176.4	184.1	192.3	200.7	209.6
152.5°	152.8	152.9	155.7	159.7	164.4	170.6	177.5	184.7	191.7	199.3	207.3
155°	158.0	158.3	160.5	164.0	167.9	173.2	179.2	185.2	190.9	197.2	203.9
157.5°	163.0	163.0	165.0	167.7	171.1	175.3	180.4	185.2	189.9	195.0	200.5
160°	166.1	166.1	167.5	170.0	172.8	176.7	181.0	185.2	189.1	193.3	197.9
162.5°	168.9	168.7	169.8	172.0	174.5	177.6	181.5	185.2	188.2	191.6	195.7
165°	172.1	172.1	172.8	174.6	176.4	178.5	181.7	184.5	186.6	189.1	191.9
167.5°	175.3	174.9	175.3	176.6	177.6	179.3	181.6	183.6	184.9	186.5	188.5
170°	176.7	176.4	176.7	177.8	178.5	179.5	181.3	183.1	183.8	184.8	186.3
172.5°	178.1	177.8	177.8	178.6	179.0	179.8	181.0	182.5	182.7	183.1	184.3
175°	179.5	179.2	179.2	179.5	179.9	179.9	180.6	181.7	181.3	181.3	182.0
177.5°	180.2	179.9	179.6	179.9	179.9	179.9	180.2	180.7	180.2	180.2	180.5
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332870

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	6.4	6.4	6.4	6.4	6.5	6.7	6.7	6.8
90°	6.4	6.7	7.1	7.1	7.4	7.8	7.4	7.4
92.5°	69.4	52.2	41.6	34.5	30.3	28.4	27.2	27.2
95°	261.9	207.1	159.7	125.5	108.1	97.2	90.8	86.2
97.5°	386.9	366.6	332.0	295.1	269.7	248.5	237.9	230.5
100°	426.2	433.3	416.0	389.8	359.1	337.5	326.9	324.1
102.5°	424.3	459.3	464.3	453.4	434.6	419.0	407.8	405.5
105°	395.8	457.0	492.0	506.5	507.2	504.3	499.4	497.3
107.5°	355.5	420.6	469.8	501.4	518.8	526.9	530.4	531.3
110°	331.2	392.3	443.6	482.4	507.5	522.4	528.7	531.9



TEST NUMBER: P332870

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.3	367.4	415.8	454.7	483.2	501.2	510.1	515.2
115°	295.5	338.9	380.3	414.2	442.1	463.3	474.7	477.5
117.5°	286.7	322.7	355.2	384.0	407.8	425.6	437.0	439.2
120°	282.7	315.6	343.9	369.0	389.1	404.7	413.9	417.8
122.5°	279.3	311.1	336.8	358.8	375.8	389.1	396.9	400.8
125°	273.6	303.9	328.3	347.8	361.9	372.2	378.9	381.0
127.5°	266.5	295.5	319.9	338.3	352.5	361.6	367.3	369.4
130°	260.8	288.8	312.8	331.5	346.0	354.8	360.5	362.6
132.5°	254.9	281.1	304.6	323.3	337.5	347.5	352.9	355.0
135°	246.7	269.7	291.2	308.9	323.0	332.9	338.6	340.7
137.5°	239.3	258.7	276.9	292.8	306.1	315.8	320.5	323.0
140°	235.0	251.6	267.5	282.4	294.8	302.5	307.5	310.3
142.5°	231.1	245.7	259.3	272.2	283.2	290.4	294.8	296.7
145°	225.5	237.5	248.1	258.0	266.8	272.8	276.4	278.1
147.5°	220.9	230.4	238.9	246.7	253.2	258.4	261.0	261.7
150°	218.1	226.2	233.3	239.6	245.3	249.9	252.0	252.3
152.5°	215.0	222.0	228.5	233.7	238.5	242.2	243.5	243.9
155°	210.3	215.9	221.2	225.5	229.0	231.8	232.9	232.9
157.5°	205.3	210.0	214.5	217.9	220.5	222.7	223.3	223.3
160°	202.2	206.0	209.9	212.8	214.9	217.0	217.4	217.4
162.5°	199.1	202.4	205.4	208.0	209.5	211.6	212.0	211.7
165°	194.7	196.9	199.3	201.1	202.5	203.9	203.6	203.2
167.5°	190.6	192.2	194.2	195.2	195.9	196.9	196.8	196.5
170°	188.0	189.1	190.5	191.6	192.3	192.6	192.3	192.3
172.5°	185.8	186.5	187.4	188.2	188.6	188.9	188.6	188.0
175°	182.7	183.1	183.8	183.8	183.8	184.5	183.8	183.1
177.5°	180.7	181.0	181.0	181.3	181.0	181.3	180.7	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)