

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910327

Luminaire Tested: DFN2DIP-4P2F0-020D030US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910327
REPORT IS A COMBINATION OF REPORTS P900537 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D030US850-FLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5489.6 lumens
Efficiency: N/A
Efficacy: 137.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 40
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910327

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910327

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	21
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2161	2161	2161
5°	2160	2125	2142
10°	2138	2091	2109
15°	2102	2051	2060
20°	2056	1998	2010
25°	2009	1935	1953
30°	1952	1877	1881
35°	1897	1809	1806
40°	1830	1739	1734
45°	1763	1670	1660
50°	1690	1597	1574
55°	1613	1512	1495
60°	1527	1413	1404
65°	1430	1309	1297
70°	1309	1181	1181
75°	1143	1029	1068
80°	941	837	864
85°	628	523	539

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1763 cd/sqm

TEST NUMBER: P910327

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.5
10°-20°	228.6	4.2
20°-30°	335.9	6.1
30°-40°	390.1	7.1
40°-50°	389.6	7.1
50°-60°	339.7	6.2
60°-70°	251.1	4.6
70°-80°	142.1	2.6
80°-90°	39.5	0.7
90°-100°	37.0	0.7
100°-110°	138.0	2.5
110°-120°	366.1	6.7
120°-130°	607.1	11.1
130°-140°	644.9	11.7
140°-150°	599.4	10.9
150°-160°	481.9	8.8
160°-170°	310.5	5.7
170°-180°	106.9	1.9
0°-30°	645.7	11.8
0°-40°	1035.8	18.9
0°-60°	1765.1	32.2
0°-90°	2197.8	40.0
90°-120°	541.1	9.9
90°-150°	2392.5	43.6
90°-180°	3292.0	60.0
0°-180°	5489.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	1	10	16	20	22	5
95°	53	26	32	36	35	63
105°	247	271	50	58	62	264
115°	467	481	501	125	67	460
125°	660	671	687	692	695	589
135°	817	830	838	846	844	631
145°	948	947	961	967	963	593
155°	1044	1037	1046	1051	1045	481
165°	1100	1095	1098	1103	1098	311
175°	1125	1120	1121	1127	1119	107
180°	1123	1123	1123	1123	1123	

TEST NUMBER: P910327

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	0.8	9.8	16.2	20.4	21.8
92.5°	20.4	17.1	19.5	21.2	21.8
95°	52.8	26.0	31.6	35.8	34.9
97.5°	95.0	28.5	41.4	43.9	44.7
100°	143.8	32.5	46.4	52.8	54.5
102.5°	197.4	195.8	47.9	56.8	59.3
105°	247.0	271.4	49.6	58.4	61.8
107.5°	304.6	324.9	51.2	60.1	63.4
110°	360.0	376.9	142.2	61.0	64.2

TEST NUMBER: P910327

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	412.0	426.5	412.8	62.5	65.0
115°	467.1	481.0	501.3	125.1	66.7
117.5°	515.1	531.3	545.2	429.0	216.1
120°	568.7	580.9	595.5	605.3	495.6
122.5°	614.2	627.3	643.6	648.3	649.2
125°	660.5	671.1	686.6	692.2	694.7
127.5°	702.8	714.1	726.4	734.5	735.3
130°	742.6	755.7	764.5	773.4	772.8
132.5°	783.2	793.8	802.7	810.0	809.2
135°	817.3	830.4	837.6	845.8	844.2
137.5°	853.0	862.8	871.0	879.1	876.7
140°	888.0	894.5	903.4	910.7	906.7
142.5°	917.4	923.0	933.6	940.0	936.0
145°	948.2	947.3	961.2	966.8	962.7
147.5°	974.9	972.5	986.3	990.3	987.1
150°	1001.0	995.3	1008.3	1013.1	1009.1
152.5°	1022.8	1016.4	1028.6	1033.5	1027.8
155°	1044.0	1036.8	1046.5	1051.3	1044.9
157.5°	1061.1	1054.7	1062.0	1067.6	1061.1
160°	1075.7	1070.9	1075.7	1080.6	1074.8
162.5°	1088.7	1083.8	1087.9	1093.6	1086.3
165°	1100.0	1095.2	1097.7	1103.3	1097.7
167.5°	1109.0	1104.1	1106.6	1112.3	1105.0
170°	1116.3	1111.4	1113.1	1118.8	1111.4
172.5°	1121.2	1116.3	1118.0	1123.6	1116.3
175°	1125.2	1119.5	1121.2	1126.9	1118.8
177.5°	1126.9	1121.2	1122.1	1127.7	1120.4
180°	1122.9	1122.9	1122.9	1122.9	1122.9

TEST NUMBER: P910327

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.82	9.60	9.86	10.64	12.05	8.37	9.15	9.41	10.20	11.60
	3H	10.45	11.15	11.50	12.20	13.63	9.96	10.66	11.01	11.71	13.14
	4H	11.02	11.68	12.08	12.73	14.17	10.52	11.19	11.58	12.24	13.67
	6H	11.40	12.00	12.47	13.06	14.51	10.90	11.51	11.97	12.56	14.01
	8H	11.49	12.07	12.56	13.14	14.58	10.99	11.57	12.06	12.64	14.08
	12H	11.53	12.08	12.61	13.15	14.61	11.02	11.57	12.10	12.64	14.10
4H	2H	9.26	9.92	10.32	10.97	12.41	8.90	9.56	9.97	10.62	12.05
	3H	11.09	11.64	12.16	12.72	14.17	10.68	11.23	11.75	12.31	13.76
	4H	11.78	12.29	12.86	13.36	14.83	11.36	11.86	12.44	12.94	14.40
	6H	12.27	12.70	13.36	13.80	15.26	11.84	12.27	12.93	13.37	14.83
	8H	12.41	12.81	13.49	13.90	15.38	11.97	12.37	13.06	13.46	14.94
	12H	12.46	12.83	13.57	13.93	15.42	12.02	12.38	13.12	13.49	14.97
8H	4H	11.96	12.36	13.05	13.45	14.93	11.58	11.98	12.67	13.07	14.55
	6H	12.56	12.89	13.67	14.02	15.50	12.17	12.51	13.28	13.64	15.11
	8H	12.76	13.06	13.88	14.17	15.66	12.37	12.66	13.49	13.77	15.27
	12H	12.87	13.13	14.00	14.24	15.77	12.46	12.72	13.59	13.83	15.36
12H	4H	11.94	12.30	13.04	13.41	14.89	11.57	11.93	12.67	13.04	14.52
	6H	12.58	12.87	13.70	13.99	15.48	12.21	12.50	13.32	13.61	15.11
	8H	12.80	13.06	13.92	14.17	15.70	12.42	12.68	13.54	13.79	15.32