

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910328

Luminaire Tested: DFN2DIP-4P2F0-020D030US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910328
REPORT IS A COMBINATION OF REPORTS P899018 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D030US850-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4829.7 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 40
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910328

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910328

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2295	2295	2295
5°	2294	2253	2269
10°	2267	2203	2192
15°	2231	2124	2075
20°	2185	2019	1931
25°	2139	1901	1793
30°	2077	1781	1619
35°	2016	1653	1467
40°	1954	1521	1292
45°	1883	1375	1135
50°	1809	1229	981
55°	1731	1072	834
60°	1641	911	683
65°	1537	746	611
70°	1410	593	547
75°	1251	511	490
80°	1024	414	413
85°	659	253	291

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1883 cd/sqm

TEST NUMBER: P910328

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.9	1.8
10°-20°	235.8	4.9
20°-30°	331.1	6.9
30°-40°	361.0	7.5
40°-50°	331.8	6.9
50°-60°	260.6	5.4
60°-70°	169.6	3.5
70°-80°	87.3	1.8
80°-90°	25.3	0.5
90°-100°	65.1	1.3
100°-110°	206.9	4.3
110°-120°	354.0	7.3
120°-130°	465.6	9.6
130°-140°	522.6	10.8
140°-150°	512.5	10.6
150°-160°	429.9	8.9
160°-170°	285.1	5.9
170°-180°	99.7	2.1
0°-30°	652.9	13.5
0°-40°	1013.8	21.0
0°-60°	1606.2	33.3
0°-90°	1888.3	39.1
90°-120°	626.0	13.0
90°-150°	2126.7	44.0
90°-180°	2941.0	60.9
0°-180°	4829.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	917	917	917	917	917	
5°	917	913	902	909	907	87
15°	872	863	834	819	811	246
25°	792	765	710	676	664	364
35°	682	640	567	514	496	427
45°	558	502	415	356	336	431
55°	424	359	270	220	204	379
65°	286	219	144	116	114	284
75°	153	94	66	61	60	161
85°	36	18	16	16	16	41
90°	1	11	31	29	30	5
95°	46	55	57	57	55	52
105°	191	194	195	197	197	202
115°	355	360	359	358	355	351
125°	517	525	522	519	518	462
135°	668	678	680	679	677	517
145°	812	818	823	824	820	507
155°	928	930	933	938	935	427
165°	1009	1008	1008	1015	1010	285
175°	1050	1048	1046	1052	1047	100
180°	1052	1052	1052	1052	1052	

TEST NUMBER: P910328

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	916.7	916.7	916.7	916.7	916.7
2.5°	920.8	916.7	907.5	915.9	914.3
5°	916.7	912.6	901.7	909.3	906.7
7.5°	909.3	904.3	892.6	896.0	891.7
10°	899.3	893.4	876.9	874.3	869.5
12.5°	886.9	879.3	856.9	852.0	842.8
15°	871.9	862.7	834.5	818.8	810.6
17.5°	854.5	841.2	806.4	788.1	774.9
20°	834.5	817.9	776.5	755.8	737.5
22.5°	813.0	793.9	745.8	717.6	705.2
25°	791.5	764.9	710.1	676.2	663.6
27.5°	765.8	737.5	676.9	637.9	618.8
30°	738.4	706.8	640.4	598.2	575.7
32.5°	711.8	673.6	605.6	555.8	535.1
35°	681.9	639.7	566.7	514.4	496.1
37.5°	652.9	607.2	530.1	472.9	452.1
40°	622.1	572.5	492.0	433.1	411.4
42.5°	590.7	537.6	453.8	392.4	371.7
45°	557.5	501.8	414.9	355.9	335.9
47.5°	526.0	467.1	377.5	318.5	300.3
50°	491.2	432.3	341.0	283.7	266.4
52.5°	457.0	394.8	306.1	251.4	235.7
55°	423.9	359.2	269.6	219.9	204.1
57.5°	389.9	323.5	237.3	190.9	177.6
60°	355.1	288.7	203.3	161.0	147.7
62.5°	321.1	254.7	174.2	134.4	127.8
65°	286.2	219.0	144.4	116.2	113.7
67.5°	253.1	185.8	116.2	102.0	99.6
70°	218.1	153.5	96.2	87.9	84.6
72.5°	185.0	123.5	80.4	73.9	72.2
75°	152.6	94.5	66.3	60.6	59.8
77.5°	120.3	67.2	52.2	48.9	47.2
80°	90.4	48.1	39.8	36.5	36.5
82.5°	63.0	32.4	27.4	25.7	25.7
85°	35.6	18.2	15.7	15.7	15.7
87.5°	13.3	6.7	6.7	5.8	5.8
90°	1.0	11.4	31.1	29.2	30.2
92.5°	19.6	26.6	27.6	28.5	28.5
95°	46.4	55.2	56.8	56.8	55.2
97.5°	77.1	85.3	88.8	88.8	88.8
100°	112.6	119.9	122.4	122.4	121.5
102.5°	150.0	155.5	158.9	159.9	158.9
105°	191.0	193.5	195.4	197.0	197.0
107.5°	231.6	235.3	235.3	236.0	231.6
110°	270.9	276.0	276.0	276.0	273.5

TEST NUMBER: P910328

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	318.8	317.8	315.3	313.4
115°	355.3	360.3	358.8	357.9	355.3
117.5°	396.8	403.8	399.4	396.8	394.2
120°	438.7	445.7	438.7	438.7	435.8
122.5°	476.8	485.6	481.2	478.6	476.8
125°	516.8	524.7	522.1	519.2	518.3
127.5°	555.7	565.6	562.2	558.3	555.7
130°	592.2	603.6	602.1	600.2	596.6
132.5°	633.1	642.0	642.7	638.2	635.7
135°	668.4	678.2	680.1	679.2	676.6
137.5°	707.7	715.6	717.2	716.6	712.8
140°	742.3	750.2	754.7	754.7	751.1
142.5°	777.9	785.7	788.3	789.3	785.7
145°	811.5	817.8	822.9	823.8	820.3
147.5°	841.6	849.5	853.3	854.9	851.4
150°	872.7	878.1	881.5	884.4	881.5
152.5°	900.3	905.6	910.0	913.6	910.0
155°	927.9	930.3	933.2	937.7	934.9
157.5°	951.6	953.5	955.2	961.5	957.1
160°	972.9	974.8	975.8	981.1	977.4
162.5°	992.6	992.6	993.6	999.5	995.1
165°	1009.4	1008.4	1008.4	1014.7	1010.3
167.5°	1024.6	1021.7	1021.7	1028.0	1023.6
170°	1036.0	1033.5	1032.6	1038.9	1033.5
172.5°	1043.9	1041.5	1040.5	1046.8	1041.5
175°	1050.3	1047.8	1045.9	1052.2	1046.8
177.5°	1053.8	1051.2	1049.3	1054.8	1049.3
180°	1052.2	1052.2	1052.2	1052.2	1052.2

TEST NUMBER: P910328

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.79	9.53	9.84	10.59	12.01	4.75	5.50	5.80	6.55	7.97
	3H	10.43	11.10	11.50	12.16	13.60	5.91	6.58	6.97	7.64	9.08
	4H	11.02	11.66	12.10	12.72	14.17	6.34	6.98	7.41	8.04	9.49
	6H	11.42	12.01	12.50	13.07	14.53	6.64	7.22	7.72	8.29	9.75
	8H	11.54	12.09	12.62	13.17	14.63	6.72	7.27	7.80	8.35	9.81
	12H	11.59	12.11	12.68	13.19	14.66	6.75	7.28	7.84	8.35	9.83
4H	2H	8.79	9.42	9.87	10.49	11.93	5.32	5.96	6.40	7.02	8.47
	3H	10.58	11.11	11.67	12.20	13.66	6.64	7.17	7.73	8.26	9.72
	4H	11.25	11.74	12.35	12.82	14.30	7.17	7.65	8.26	8.73	10.21
	6H	11.74	12.16	12.84	13.26	14.74	7.56	7.97	8.66	9.08	10.55
	8H	11.90	12.29	13.00	13.39	14.88	7.67	8.06	8.77	9.16	10.65
	12H	11.98	12.33	13.10	13.44	14.94	7.72	8.07	8.84	9.18	10.68
8H	4H	11.21	11.60	12.31	12.69	14.18	7.43	7.81	8.53	8.91	10.40
	6H	11.75	12.07	12.87	13.21	14.69	7.91	8.23	9.03	9.37	10.86
	8H	11.95	12.23	13.08	13.35	14.86	8.09	8.37	9.22	9.49	10.99
	12H	12.07	12.31	13.20	13.43	14.97	8.19	8.43	9.32	9.55	11.09
12H	4H	11.16	11.51	12.27	12.62	14.11	7.42	7.77	8.54	8.88	10.38
	6H	11.72	12.00	12.85	13.12	14.63	7.96	8.24	9.08	9.35	10.86
	8H	11.92	12.17	13.05	13.28	14.83	8.14	8.39	9.27	9.51	11.05