

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332882

Luminaire Tested: **SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332882
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4325.0 lumens
Efficiency: N/A
Efficacy: 138.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332882
CATALOG NUMBER: SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332882

CATALOG NUMBER: SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28				
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29	24				
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20				
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	23	22	18				
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15				
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12				
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11				
9	48	36	29	24	43	33	27	23	27	22	19	22	18	16	16	14	12	10				
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P332882

CATALOG NUMBER: SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.3
10°-20°	161.9	3.7
20°-30°	233.8	5.4
30°-40°	265.1	6.1
40°-50°	255.9	5.9
50°-60°	212.8	4.9
60°-70°	147.0	3.4
70°-80°	74.5	1.7
80°-90°	21.3	0.5
90°-100°	287.5	6.6
100°-110°	598.3	13.8
110°-120°	535.9	12.4
120°-130°	450.8	10.4
130°-140°	375.9	8.7
140°-150°	287.1	6.6
150°-160°	201.8	4.7
160°-170°	118.7	2.7
170°-180°	38.6	0.9
0°-30°	453.8	10.5
0°-40°	718.9	16.6
0°-60°	1187.7	27.5
0°-90°	1430.4	33.1
90°-120°	1421.6	32.9
90°-150°	2535.4	58.6
90°-180°	2895.0	66.9
0°-180°	4325.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	1	6	14	16	16	3
95°	26	81	637	316	191	29
105°	92	133	513	1104	1100	98
115°	161	202	457	879	1056	160
125°	224	267	455	748	843	200
135°	267	317	451	664	754	206
145°	307	352	449	560	615	193
155°	350	377	436	494	515	161
165°	381	393	418	443	450	107
175°	397	398	401	407	405	38
180°	398	398	398	398	398	



TEST NUMBER: P332882

CATALOG NUMBER: SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	8.9	8.5	8.3	7.8	7.3	6.9	7.7	7.7	7.9	8.1	7.9
90°	0.8	2.3	4.7	5.5	6.3	6.3	10.9	10.9	12.5	14.1	13.3
92.5°	8.9	13.0	20.3	29.9	41.3	57.5	97.3	157.9	217.1	248.0	206.6
95°	25.8	28.1	36.0	46.1	64.9	97.7	165.8	294.0	480.9	637.3	655.3
97.5°	46.3	46.3	53.0	62.4	78.5	106.0	158.4	264.3	450.1	671.2	823.2
100°	59.4	59.4	64.9	74.3	89.1	114.2	160.3	248.7	408.2	628.7	828.8
102.5°	71.9	73.2	78.0	86.8	101.0	124.8	166.5	244.3	380.0	575.5	781.9
105°	91.5	93.8	97.7	107.1	121.2	143.9	181.4	246.3	355.8	512.9	696.7
107.5°	113.1	114.6	118.5	128.5	142.0	164.4	198.8	257.9	351.4	477.9	627.9
110°	127.5	129.0	132.9	142.3	156.4	177.5	211.9	266.6	352.6	466.0	593.5



TEST NUMBER: P332882

CATALOG NUMBER: SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	141.2	142.8	147.3	156.1	170.1	191.3	224.4	276.0	356.4	460.4	574.1
115°	161.1	163.4	168.9	176.7	191.6	212.7	244.0	290.9	363.6	457.4	555.9
117.5°	181.7	183.9	188.8	197.4	211.3	233.2	262.9	306.0	371.3	456.6	547.8
120°	195.5	197.0	202.5	211.1	224.4	246.3	276.0	316.7	376.9	456.6	543.4
122.5°	208.0	209.6	215.0	223.0	237.5	258.8	288.5	326.7	382.5	456.0	538.4
125°	224.4	227.5	232.2	240.8	255.7	277.6	305.7	341.7	391.0	455.1	530.1
127.5°	239.0	241.5	247.1	256.9	272.4	294.5	321.7	354.7	397.7	453.4	519.0
130°	247.1	250.2	256.5	268.2	283.1	305.7	332.3	362.8	402.7	452.7	512.2
132.5°	255.2	257.7	265.9	277.0	293.1	314.5	341.1	370.9	407.1	452.1	505.9
135°	266.6	269.8	277.6	290.9	307.3	327.6	353.4	381.6	413.6	451.2	496.5
137.5°	278.1	281.0	289.6	302.3	319.3	338.7	362.8	389.1	417.5	451.0	488.4
140°	286.2	288.5	297.1	310.4	326.8	345.6	369.1	394.1	420.7	450.4	484.0
142.5°	294.9	297.3	305.3	317.9	333.7	351.9	374.7	397.8	423.2	450.4	480.3
145°	307.3	309.6	317.5	328.4	343.3	360.5	380.8	401.9	424.6	448.8	473.8
147.5°	321.2	322.0	328.9	340.1	352.5	368.0	387.1	405.5	425.4	446.0	468.1
150°	330.0	330.8	337.0	346.4	358.1	373.0	390.2	407.4	425.4	444.1	463.7
152.5°	338.1	338.3	344.5	353.3	363.8	377.4	392.7	408.6	424.1	441.0	458.7
155°	349.5	350.3	355.0	362.8	371.4	383.1	396.4	409.7	422.2	436.3	451.2
157.5°	360.6	360.6	365.0	371.1	378.6	387.8	399.1	409.7	420.2	431.5	443.5
160°	367.5	367.5	370.6	376.1	382.4	391.0	400.3	409.7	418.3	427.7	437.9
162.5°	373.8	373.1	375.6	380.5	386.1	392.8	401.6	409.7	416.5	424.0	432.9
165°	380.8	380.8	382.4	386.3	390.2	394.9	401.9	408.2	412.9	418.3	424.6
167.5°	387.8	387.1	387.8	390.8	393.0	396.6	401.8	406.3	409.1	412.7	417.1
170°	391.0	390.2	391.0	393.3	394.9	397.2	401.1	405.0	406.6	408.9	412.1
172.5°	394.1	393.3	393.5	395.2	396.1	397.8	400.5	403.8	404.1	405.2	407.7
175°	397.2	396.4	396.4	397.2	398.0	398.0	399.6	401.9	401.1	401.1	402.7
177.5°	398.6	398.0	397.4	398.0	398.0	398.0	398.6	399.9	398.6	398.6	399.2
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332882

CATALOG NUMBER: SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	7.9	8.0	8.1	8.1	8.3	8.6	8.5	8.6
90°	14.1	14.9	15.6	15.6	16.4	17.2	16.4	16.4
92.5°	153.6	115.6	92.0	76.3	67.1	62.9	60.2	60.2
95°	579.4	458.2	353.4	277.6	239.3	215.0	201.0	190.8
97.5°	856.0	811.0	734.5	652.9	596.8	549.7	526.2	510.0
100°	943.0	958.6	920.3	862.5	794.4	746.7	723.3	717.0
102.5°	938.6	1016.2	1027.3	1003.2	961.5	926.9	902.2	897.2
105°	875.8	1011.0	1088.4	1120.5	1122.1	1115.8	1104.9	1100.2
107.5°	786.5	930.5	1039.5	1109.2	1147.9	1165.7	1173.5	1175.5
110°	732.7	867.9	981.3	1067.3	1122.8	1155.7	1169.8	1176.8



TEST NUMBER: P332882

CATALOG NUMBER: SA4XXRDIP-C350D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	693.3	812.9	920.0	1006.0	1069.0	1108.8	1128.5	1139.9
115°	653.7	749.9	841.3	916.4	978.2	1025.1	1050.1	1056.4
117.5°	634.3	713.9	785.8	849.5	902.2	941.6	966.9	971.8
120°	625.5	698.3	760.8	816.3	860.9	895.3	915.6	924.2
122.5°	618.0	688.2	745.2	793.8	831.5	860.9	878.1	886.7
125°	605.2	672.5	726.4	769.4	800.7	823.4	838.2	842.9
127.5°	589.6	653.8	707.6	748.5	779.9	800.1	812.6	817.3
130°	577.1	638.8	692.0	733.4	765.5	785.1	797.6	802.3
132.5°	563.9	621.9	673.9	715.3	746.7	768.8	780.7	785.4
135°	545.8	596.6	644.3	683.4	714.7	736.6	749.1	753.8
137.5°	529.4	572.4	612.6	647.9	677.1	698.7	709.0	714.7
140°	520.0	556.7	591.9	624.8	652.1	669.3	680.3	686.5
142.5°	511.2	543.6	573.8	602.2	626.5	642.4	652.1	656.5
145°	498.9	525.5	548.9	570.8	590.4	603.6	611.5	615.4
147.5°	488.7	509.8	528.6	545.8	560.2	571.6	577.5	578.9
150°	482.4	500.4	516.1	530.1	542.7	552.8	557.5	558.3
152.5°	475.6	491.0	505.4	517.0	527.6	535.9	538.7	539.5
155°	465.2	477.8	489.5	498.9	506.7	512.9	515.3	515.3
157.5°	454.1	464.6	474.5	482.0	487.9	492.6	494.0	494.0
160°	447.3	455.9	464.5	470.7	475.4	480.1	480.9	480.9
162.5°	440.4	447.7	454.5	460.1	463.5	468.2	469.0	468.4
165°	430.8	435.5	441.0	444.9	448.0	451.2	450.4	449.6
167.5°	421.6	425.2	429.6	431.9	433.5	435.5	435.4	434.7
170°	416.0	418.3	421.5	423.8	425.4	426.1	425.4	425.4
172.5°	411.0	412.7	414.6	416.3	417.2	418.0	417.2	416.0
175°	404.3	405.0	406.6	406.6	406.6	408.2	406.6	405.0
177.5°	399.9	400.5	400.5	401.1	400.5	401.1	399.9	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0

(END OF REPORT)