

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910330

Luminaire Tested: DFN2DIP-4P2F0-020D040US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910330
REPORT IS A COMBINATION OF REPORTS P899023 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D040US850-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6121.6 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 49.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910330

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910330

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2161	2161	2161
5°	2160	2125	2142
10°	2138	2091	2109
15°	2102	2051	2060
20°	2056	1998	2010
25°	2009	1935	1953
30°	1952	1877	1881
35°	1897	1809	1806
40°	1830	1739	1734
45°	1763	1670	1660
50°	1690	1597	1574
55°	1613	1512	1495
60°	1527	1413	1404
65°	1430	1309	1297
70°	1309	1181	1181
75°	1143	1029	1068
80°	941	837	864
85°	628	523	539

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2082 cd/sqm

TEST NUMBER: P910330

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US850-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.3
10°-20°	228.6	3.7
20°-30°	335.9	5.5
30°-40°	390.1	6.4
40°-50°	389.6	6.4
50°-60°	339.7	5.5
60°-70°	251.1	4.1
70°-80°	142.1	2.3
80°-90°	41.5	0.7
90°-100°	86.8	1.4
100°-110°	275.8	4.5
110°-120°	472.0	7.7
120°-130°	620.8	10.1
130°-140°	696.8	11.4
140°-150°	683.3	11.2
150°-160°	573.2	9.4
160°-170°	380.1	6.2
170°-180°	132.9	2.2
0°-30°	645.7	10.5
0°-40°	1035.8	16.9
0°-60°	1765.1	28.8
0°-90°	2199.8	35.9
90°-120°	834.7	13.6
90°-150°	2835.6	46.3
90°-180°	3922.0	64.1
0°-180°	6121.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	1	15	42	39	40	6
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	

TEST NUMBER: P910330

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6

TEST NUMBER: P910330

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9

TEST NUMBER: P910330

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.35	9.10	9.42	10.17	11.63	7.91	8.65	8.98	9.73	11.18
	3H	9.98	10.65	11.06	11.73	13.21	9.49	10.16	10.57	11.24	12.72
	4H	10.55	11.18	11.64	12.26	13.75	10.05	10.69	11.14	11.77	13.25
	6H	10.92	11.51	12.02	12.59	14.09	10.42	11.01	11.52	12.09	13.59
	8H	11.02	11.57	12.12	12.67	14.16	10.52	11.07	11.62	12.17	13.66
	12H	11.05	11.58	12.16	12.67	14.19	10.54	11.07	11.65	12.17	13.68
4H	2H	8.79	9.42	9.88	10.50	11.99	8.43	9.07	9.53	10.15	11.63
	3H	10.61	11.14	11.72	12.25	13.75	10.21	10.74	11.31	11.85	13.34
	4H	11.31	11.79	12.41	12.89	14.41	10.88	11.37	11.99	12.47	13.98
	6H	11.79	12.21	12.91	13.33	14.84	11.36	11.78	12.48	12.90	14.41
	8H	11.93	12.32	13.04	13.43	14.96	11.49	11.88	12.61	12.99	14.52
	12H	11.98	12.34	13.12	13.46	14.99	11.54	11.89	12.67	13.02	14.55
8H	4H	11.48	11.87	12.59	12.98	14.51	11.10	11.49	12.22	12.60	14.13
	6H	12.08	12.40	13.21	13.56	15.08	11.69	12.02	12.83	13.17	14.69
	8H	12.28	12.56	13.43	13.70	15.24	11.89	12.17	13.03	13.31	14.85
	12H	12.39	12.64	13.54	13.77	15.35	11.98	12.23	13.13	13.36	14.94
12H	4H	11.46	11.81	12.59	12.94	14.47	11.09	11.44	12.22	12.57	14.10
	6H	12.10	12.38	13.24	13.52	15.06	11.73	12.01	12.87	13.15	14.69
	8H	12.32	12.57	13.47	13.70	15.28	11.94	12.19	13.09	13.32	14.90

END OF REPORT