

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332922

Luminaire Tested: **SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332922
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7158.0 lumens
Efficiency: N/A
Efficacy: 144.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332922
CATALOG NUMBER: SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332922

CATALOG NUMBER: SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33				
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24				
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20				
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	25	23	22	18				
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15				
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11				
9	48	36	29	24	43	33	27	23	27	22	19	21	18	16	16	14	12	10				
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8205	8205	8205
5°	8223	8122	8173
10°	8171	8025	8025
15°	8078	7856	7798
20°	7948	7635	7494
25°	7784	7375	7187
30°	7623	7101	6804
35°	7447	6818	6419
40°	7233	6495	6003
45°	7036	6174	5579
50°	6812	5805	5130
55°	6572	5422	4643
60°	6307	5000	4146
65°	6065	4474	3656
70°	5712	3895	3104
75°	5268	3228	2523
80°	4593	2459	2315
85°	3890	2232	2093



TEST NUMBER: P332922

CATALOG NUMBER: SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	1.3
10°-20°	266.2	3.7
20°-30°	384.4	5.4
30°-40°	435.7	6.1
40°-50°	420.8	5.9
50°-60°	349.9	4.9
60°-70°	241.6	3.4
70°-80°	122.5	1.7
80°-90°	35.9	0.5
90°-100°	53.1	0.7
100°-110°	338.8	4.7
110°-120°	648.1	9.1
120°-130°	822.7	11.5
130°-140°	880.2	12.3
140°-150°	823.1	11.5
150°-160°	663.8	9.3
160°-170°	428.1	6.0
170°-180°	147.6	2.1
0°-30°	746.1	10.4
0°-40°	1181.8	16.5
0°-60°	1952.5	27.3
0°-90°	2352.5	32.9
90°-120°	1040.0	14.5
90°-150°	3566.1	49.8
90°-180°	4806.0	67.1
0°-180°	7158.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1015	1011	1002	1010	1008	96
15°	966	959	940	938	933	272
25°	874	859	828	815	807	402
35°	756	730	692	666	651	472
45°	616	586	541	504	489	475
55°	467	435	385	346	330	418
65°	318	283	234	202	191	313
75°	169	140	104	86	81	178
85°	42	27	24	23	23	47
90°	4	16	26	32	35	5
95°	64	27	26	32	34	82
105°	350	357	362	370	331	366
115°	653	656	655	658	658	642
125°	918	922	920	924	925	819
135°	1139	1138	1142	1145	1147	877
145°	1313	1316	1316	1318	1320	820
155°	1440	1441	1437	1442	1438	663
165°	1519	1513	1513	1521	1512	429
175°	1554	1547	1548	1557	1544	148
180°	1554	1554	1554	1554	1554	



TEST NUMBER: P332922

CATALOG NUMBER: SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1018.8	1018.2	1017.7	1017.1	1016.6	1015.5	1014.0	1012.5	1010.9	1009.4	1010.9
5°	1014.7	1014.0	1013.3	1012.6	1012.0	1010.6	1008.5	1006.4	1004.3	1002.3	1004.0
7.5°	1005.5	1004.8	1004.1	1003.4	1002.6	1000.9	998.2	995.5	992.8	990.1	991.2
10°	996.8	996.0	995.1	994.2	993.4	991.4	988.3	985.1	982.0	978.9	979.6
12.5°	985.6	984.6	983.6	982.6	981.6	979.3	975.6	971.9	968.3	964.6	965.0
15°	966.5	964.9	963.4	961.8	960.2	957.3	953.0	948.7	944.3	940.0	939.7
17.5°	943.3	941.0	938.8	936.5	934.3	930.6	925.4	920.2	915.0	909.8	908.9
20°	925.2	923.0	920.7	918.5	916.2	912.2	906.3	900.4	894.5	888.7	887.3
22.5°	905.3	902.8	900.3	897.7	895.2	890.8	884.5	878.2	871.9	865.6	863.5
25°	873.9	870.8	867.6	864.5	861.4	856.3	849.2	842.1	835.0	828.0	825.0
27.5°	840.9	837.0	833.1	829.2	825.2	819.5	811.9	804.4	796.8	789.2	785.6
30°	817.8	813.5	809.2	804.9	800.6	794.3	786.2	778.1	769.9	761.8	757.5
32.5°	793.6	788.7	783.8	778.9	774.1	767.4	759.0	750.6	742.2	733.8	728.8
35°	755.6	750.1	744.5	739.0	733.5	726.4	717.7	709.1	700.4	691.8	685.9
37.5°	715.0	709.3	703.6	697.9	692.1	684.5	674.9	665.3	655.8	646.2	639.6
40°	686.3	680.6	674.9	669.2	663.5	655.7	645.9	636.0	626.2	616.3	609.0
42.5°	658.9	653.0	647.0	641.0	635.0	626.9	616.6	606.3	596.1	585.8	578.4
45°	616.3	609.9	603.5	597.1	590.7	582.3	571.9	561.6	551.2	540.8	532.3
47.5°	572.3	565.7	559.0	552.4	545.8	537.1	526.3	515.6	504.8	494.0	485.2
50°	542.4	535.6	528.9	522.1	515.4	506.5	495.4	484.4	473.3	462.2	453.6
52.5°	511.9	505.3	498.7	492.1	485.4	476.5	465.1	453.8	442.4	431.1	422.3
55°	466.9	460.0	453.1	446.1	439.2	430.1	418.9	407.7	396.4	385.2	376.2
57.5°	422.4	415.2	408.0	400.8	393.6	384.5	373.4	362.3	351.3	340.2	331.1
60°	390.6	383.7	376.8	369.9	363.0	354.0	342.9	331.8	320.8	309.7	300.7
62.5°	362.0	354.8	347.6	340.4	333.2	324.0	312.6	301.3	289.9	278.6	270.3
65°	317.5	310.1	302.6	295.2	287.7	278.5	267.4	256.4	245.3	234.2	226.8
67.5°	271.3	264.1	257.0	249.9	242.8	234.1	223.8	213.5	203.3	193.0	186.6
70°	242.0	234.7	227.5	220.2	213.0	204.4	194.5	184.7	174.8	165.0	159.3
72.5°	210.9	204.3	197.7	191.2	184.6	176.7	167.4	158.1	148.7	139.4	134.6
75°	168.9	162.5	156.1	149.7	143.3	136.0	127.9	119.7	111.6	103.5	99.5
77.5°	126.2	120.8	115.4	109.9	104.5	98.5	91.9	85.4	78.8	72.2	69.9
80°	98.8	93.8	88.8	83.8	78.8	73.7	68.5	63.3	58.1	52.9	52.4
82.5°	75.2	70.6	66.0	61.4	56.8	53.0	50.0	47.0	44.1	41.1	40.7
85°	42.0	38.6	35.1	31.6	28.2	26.2	25.7	25.2	24.6	24.1	23.8
87.5°	15.0	14.5	13.9	13.4	12.9	12.7	13.0	13.3	13.6	13.8	14.0
90°	3.5	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1
92.5°	14.6	14.8	15.0	15.1	15.3	16.4	18.4	20.5	22.6	24.6	26.2
95°	63.9	55.1	46.3	37.6	28.8	24.5	24.8	25.0	25.3	25.6	27.1
97.5°	135.7	141.2	146.7	152.1	157.6	145.9	117.1	88.3	59.5	30.7	30.8
100°	190.6	195.2	199.9	204.5	209.2	193.7	158.0	122.4	86.8	51.1	46.7
102.5°	251.9	255.3	258.7	262.1	265.5	264.9	260.3	255.6	251.0	246.3	199.0
105°	349.7	351.3	352.8	354.4	355.9	357.4	358.7	359.9	361.2	362.5	364.9
107.5°	440.6	441.4	442.2	442.9	443.7	445.0	446.7	448.5	450.2	452.0	453.1
110°	502.0	502.7	503.5	504.3	505.1	506.2	507.8	509.3	510.9	512.4	512.9



TEST NUMBER: P332922

CATALOG NUMBER: SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	561.5	562.9	564.2	565.6	567.0	568.1	568.8	569.5	570.3	571.0	570.9
115°	653.0	653.8	654.6	655.3	656.1	656.4	656.1	655.9	655.6	655.3	655.9
117.5°	735.5	736.5	737.6	738.6	739.6	740.4	741.0	741.6	742.2	742.7	742.6
120°	791.3	792.3	793.4	794.4	795.4	795.8	795.6	795.3	795.0	794.8	795.3
122.5°	843.3	844.0	844.6	845.2	845.8	846.3	846.7	847.0	847.4	847.8	848.1
125°	917.9	919.0	920.0	921.0	922.1	922.3	921.8	921.3	920.8	920.3	921.0
127.5°	988.6	988.8	989.1	989.4	989.6	990.3	991.5	992.7	993.9	995.1	994.9
130°	1034.1	1034.4	1034.7	1034.9	1035.2	1035.7	1036.5	1037.2	1038.0	1038.8	1039.0
132.5°	1076.0	1076.4	1076.9	1077.4	1077.8	1078.6	1079.5	1080.5	1081.5	1082.5	1082.7
135°	1138.7	1138.5	1138.2	1137.9	1137.7	1138.1	1139.1	1140.1	1141.2	1142.2	1142.7
137.5°	1194.3	1194.4	1194.5	1194.6	1194.7	1195.3	1196.4	1197.6	1198.7	1199.8	1200.4
140°	1230.5	1231.0	1231.5	1232.1	1232.6	1233.1	1233.6	1234.1	1234.6	1235.2	1235.9
142.5°	1263.0	1264.0	1264.9	1265.8	1266.8	1267.4	1267.7	1268.0	1268.3	1268.6	1269.2
145°	1313.0	1313.8	1314.6	1315.3	1316.1	1316.5	1316.5	1316.5	1316.5	1316.5	1316.8
147.5°	1352.7	1354.2	1355.6	1357.1	1358.5	1359.1	1358.9	1358.6	1358.3	1358.1	1358.3
150°	1381.6	1382.6	1383.6	1384.7	1385.7	1386.1	1385.8	1385.6	1385.3	1385.0	1385.0
152.5°	1405.7	1406.6	1407.4	1408.2	1409.0	1409.2	1408.8	1408.3	1407.8	1407.4	1407.8
155°	1439.7	1439.9	1440.2	1440.4	1440.7	1440.4	1439.7	1438.9	1438.1	1437.3	1438.4
157.5°	1468.2	1468.1	1467.9	1467.8	1467.6	1467.1	1466.2	1465.4	1464.5	1463.6	1464.9
160°	1485.0	1484.2	1483.4	1482.7	1481.9	1481.4	1481.1	1480.8	1480.6	1480.3	1481.9
162.5°	1499.8	1498.9	1497.9	1496.9	1495.9	1495.3	1495.0	1494.8	1494.5	1494.3	1495.8
165°	1518.7	1517.4	1516.1	1514.8	1513.5	1512.9	1512.9	1512.9	1512.9	1512.9	1514.9
167.5°	1533.5	1532.2	1530.9	1529.5	1528.2	1527.4	1527.3	1527.1	1527.0	1526.8	1529.1
170°	1541.9	1540.4	1538.8	1537.3	1535.7	1535.1	1535.3	1535.6	1535.8	1536.1	1538.2
172.5°	1547.5	1545.9	1544.4	1542.8	1541.3	1540.6	1540.9	1541.2	1541.4	1541.7	1543.7
175°	1553.5	1552.0	1550.4	1548.9	1547.3	1546.7	1546.9	1547.2	1547.5	1547.7	1550.0
177.5°	1556.3	1554.9	1553.4	1552.0	1550.5	1550.0	1550.4	1550.8	1551.3	1551.7	1553.3
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5



TEST NUMBER: P332922

CATALOG NUMBER: SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1012.5	1014.0	1015.5	1016.2	1016.1	1015.9	1015.8	1015.7
5°	1005.7	1007.5	1009.2	1009.9	1009.5	1009.2	1008.8	1008.5
7.5°	992.3	993.4	994.6	994.8	994.3	993.7	993.2	992.6
10°	980.3	981.0	981.7	981.7	981.0	980.3	979.6	978.9
12.5°	965.4	965.8	966.3	966.0	965.0	964.1	963.1	962.1
15°	939.3	939.0	938.6	937.9	936.6	935.4	934.2	933.0
17.5°	907.9	906.9	905.9	904.5	902.7	900.9	899.0	897.2
20°	885.9	884.5	883.1	881.3	879.1	876.8	874.6	872.3
22.5°	861.5	859.4	857.3	855.4	853.5	851.7	849.9	848.0
25°	822.1	819.1	816.2	813.9	812.1	810.4	808.7	806.9
27.5°	781.9	778.3	774.7	771.6	769.1	766.6	764.2	761.7
30°	753.2	748.8	744.5	741.0	738.2	735.4	732.7	729.9
32.5°	723.8	718.8	713.7	709.9	707.3	704.7	702.0	699.4
35°	680.0	674.1	668.3	663.8	660.7	657.5	654.4	651.3
37.5°	633.0	626.5	619.9	615.1	611.9	608.8	605.7	602.6
40°	601.8	594.5	587.2	582.1	578.9	575.8	572.7	569.6
42.5°	571.0	563.6	556.2	550.9	547.6	544.4	541.1	537.9
45°	523.9	515.4	506.9	501.1	498.0	494.9	491.8	488.7
47.5°	476.4	467.6	458.8	452.7	449.3	445.9	442.5	439.0
50°	444.9	436.3	427.6	421.7	418.4	415.1	411.8	408.5
52.5°	413.5	404.7	396.0	389.9	386.4	383.0	379.6	376.2
55°	367.2	358.2	349.2	343.1	339.8	336.5	333.2	329.9
57.5°	321.9	312.8	303.7	297.9	295.4	292.9	290.4	287.9
60°	291.7	282.7	273.7	267.9	265.1	262.3	259.6	256.8
62.5°	262.0	253.7	245.4	240.1	237.9	235.7	233.5	231.3
65°	219.4	211.9	204.5	199.7	197.7	195.6	193.5	191.4
67.5°	180.2	173.8	167.4	163.1	160.8	158.5	156.2	153.9
70°	153.6	147.9	142.1	138.4	136.7	135.0	133.2	131.5
72.5°	129.7	124.8	119.9	116.7	115.1	113.5	111.9	110.3
75°	95.5	91.6	87.6	85.1	84.0	83.0	82.0	80.9
77.5°	67.6	65.3	62.9	61.6	61.3	61.0	60.7	60.4
80°	51.9	51.4	50.8	50.5	50.3	50.1	50.0	49.8
82.5°	40.3	39.9	39.6	39.3	39.1	38.9	38.8	38.6
85°	23.4	23.1	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	14.2	14.3	14.5	14.7	15.0	15.2	15.4	15.7
90°	28.7	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	27.7	29.3	30.8	31.7	31.8	31.9	32.0	32.1
95°	28.7	30.2	31.8	32.7	32.9	33.2	33.4	33.7
97.5°	31.0	31.1	31.3	31.5	31.8	32.0	32.3	32.5
100°	42.3	38.0	33.6	31.5	31.8	32.0	32.3	32.5
102.5°	151.6	104.3	56.9	33.3	33.3	33.4	33.4	33.5
105°	367.2	369.5	371.8	368.3	359.0	349.7	340.5	331.2
107.5°	454.3	455.4	456.5	457.6	458.6	459.6	460.5	461.5
110°	513.5	514.0	514.5	515.1	515.9	516.7	517.5	518.2



TEST NUMBER: P332922

CATALOG NUMBER: SA4XXRDIP-C575D1205U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	570.8	570.7	570.6	571.0	572.0	573.0	574.0	574.9
115°	656.4	656.9	657.4	657.7	657.7	657.7	657.7	657.7
117.5°	742.5	742.4	742.3	742.2	742.1	742.0	741.9	741.8
120°	795.8	796.3	796.8	796.8	796.3	795.8	795.3	794.8
122.5°	848.4	848.7	849.0	848.9	848.4	847.9	847.3	846.8
125°	921.8	922.6	923.4	923.9	924.1	924.4	924.7	924.9
127.5°	994.8	994.6	994.5	994.3	994.1	993.9	993.7	993.5
130°	1039.3	1039.6	1039.8	1039.9	1039.9	1039.9	1039.9	1039.9
132.5°	1083.0	1083.3	1083.5	1083.5	1083.3	1083.1	1082.9	1082.7
135°	1143.2	1143.7	1144.3	1144.8	1145.3	1145.8	1146.3	1146.8
137.5°	1201.0	1201.5	1202.1	1202.3	1202.2	1202.0	1201.8	1201.7
140°	1236.7	1237.5	1238.3	1238.8	1239.0	1239.3	1239.5	1239.8
142.5°	1269.8	1270.3	1270.9	1271.2	1271.3	1271.3	1271.4	1271.4
145°	1317.0	1317.3	1317.5	1317.9	1318.4	1318.9	1319.5	1320.0
147.5°	1358.5	1358.7	1358.9	1359.1	1359.4	1359.7	1359.9	1360.2
150°	1385.0	1385.0	1385.0	1385.2	1385.4	1385.7	1386.0	1386.2
152.5°	1408.2	1408.6	1409.0	1409.1	1409.0	1408.8	1408.7	1408.5
155°	1439.4	1440.4	1441.5	1441.6	1440.8	1440.0	1439.3	1438.5
157.5°	1466.3	1467.6	1469.0	1469.0	1467.6	1466.3	1464.9	1463.6
160°	1483.4	1485.0	1486.5	1486.5	1485.0	1483.4	1481.9	1480.3
162.5°	1497.4	1498.9	1500.5	1500.4	1498.6	1496.9	1495.1	1493.3
165°	1517.0	1519.1	1521.1	1521.0	1518.7	1516.3	1514.0	1511.7
167.5°	1531.4	1533.6	1535.9	1535.7	1533.2	1530.6	1528.0	1525.4
170°	1540.2	1542.3	1544.4	1544.1	1541.5	1538.9	1536.4	1533.8
172.5°	1545.8	1547.9	1549.9	1549.6	1546.8	1544.0	1541.2	1538.4
175°	1552.4	1554.7	1557.0	1556.6	1553.5	1550.4	1547.3	1544.2
177.5°	1555.0	1556.6	1558.3	1557.9	1555.4	1552.9	1550.4	1548.0
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5

(END OF REPORT)