

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332947

Luminaire Tested: **SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332947
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6794.0 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332947

CATALOG NUMBER: SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332947

CATALOG NUMBER: SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47	47	47	47	47														
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40	40	40	40	40	40	40														
2	89	82	76	71	82	75	70	66	63	60	56	52	50	47	42	41	39	34	34	34	34	34	34	34														
3	81	72	65	59	74	66	60	55	56	52	48	47	43	40	38	35	33	29	29	29	29	29	29	29														
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25	25	25	25	25	25	25														
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22	22	22	22	22	22	22														
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	19	19	19	19	19	19	19														
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	25	22	20	17	17	17	17	17	17	17														
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	23	20	18	16	16	16	16	16	16	16														
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	19	16	14	14	14	14	14	14	14														
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13	13	13	13	13														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11215	11215	11215
5°	11240	11102	11171
10°	11170	10969	10969
15°	11041	10739	10659
20°	10865	10436	10244
25°	10640	10081	9825
30°	10421	9707	9300
35°	10178	9319	8774
40°	9887	8878	8205
45°	9618	8440	7626
50°	9311	7935	7013
55°	8983	7410	6348
60°	8622	6835	5667
65°	8290	6117	4999
70°	7808	5323	4244
75°	7199	4414	3450
80°	6281	3361	3166
85°	5317	3057	2853



TEST NUMBER: P332947

CATALOG NUMBER: SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.5	1.9
10°-20°	363.9	5.4
20°-30°	525.5	7.7
30°-40°	595.6	8.8
40°-50°	575.2	8.5
50°-60°	478.3	7.0
60°-70°	330.3	4.9
70°-80°	167.4	2.5
80°-90°	46.8	0.7
90°-100°	85.1	1.3
100°-110°	252.2	3.7
110°-120°	428.0	6.3
120°-130°	564.3	8.3
130°-140°	633.8	9.3
140°-150°	622.8	9.2
150°-160°	523.8	7.7
160°-170°	348.5	5.1
170°-180°	122.0	1.8
0°-30°	1019.8	15.0
0°-40°	1615.5	23.8
0°-60°	2668.9	39.3
0°-90°	3213.4	47.3
90°-120°	765.3	11.3
90°-150°	2586.3	38.1
90°-180°	3581.0	52.7
0°-180°	6794.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1387	1382	1370	1380	1378	132
15°	1321	1311	1285	1282	1275	372
25°	1194	1174	1132	1114	1103	550
35°	1033	998	946	910	890	645
45°	842	802	739	689	668	649
55°	638	594	526	473	451	571
65°	434	387	320	276	262	428
75°	231	191	142	118	111	244
85°	57	37	33	31	31	65
90°	3	14	22	28	30	7
95°	60	69	76	79	79	67
105°	233	234	238	241	244	247
115°	435	435	433	432	431	429
125°	634	634	633	631	629	565
135°	818	823	824	821	818	632
145°	993	997	998	997	994	621
155°	1138	1138	1137	1140	1137	523
165°	1239	1236	1234	1239	1236	349
175°	1289	1284	1283	1289	1283	122
180°	1291	1291	1291	1291	1291	



TEST NUMBER: P332947

CATALOG NUMBER: SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1392.6	1391.8	1391.0	1390.3	1389.5	1388.1	1386.0	1384.0	1381.9	1379.8	1381.9
5°	1387.0	1386.1	1385.1	1384.2	1383.2	1381.4	1378.5	1375.7	1372.8	1370.0	1372.4
7.5°	1374.5	1373.5	1372.5	1371.5	1370.5	1368.2	1364.5	1360.8	1357.1	1353.4	1354.9
10°	1362.6	1361.4	1360.2	1359.0	1357.8	1355.1	1350.9	1346.6	1342.4	1338.1	1339.0
12.5°	1347.2	1345.9	1344.5	1343.1	1341.8	1338.6	1333.6	1328.5	1323.5	1318.5	1319.1
15°	1321.1	1319.0	1316.8	1314.7	1312.6	1308.6	1302.6	1296.7	1290.8	1284.9	1284.4
17.5°	1289.4	1286.3	1283.2	1280.2	1277.1	1272.0	1264.9	1257.8	1250.7	1243.6	1242.3
20°	1264.7	1261.6	1258.6	1255.5	1252.4	1246.9	1238.8	1230.8	1222.7	1214.7	1212.8
22.5°	1237.5	1234.0	1230.6	1227.1	1223.7	1217.6	1209.0	1200.4	1191.8	1183.2	1180.4
25°	1194.5	1190.2	1186.0	1181.7	1177.5	1170.5	1160.8	1151.1	1141.4	1131.7	1127.7
27.5°	1149.4	1144.1	1138.7	1133.4	1128.0	1120.2	1109.8	1099.5	1089.1	1078.8	1073.8
30°	1117.9	1112.0	1106.1	1100.2	1094.3	1085.8	1074.7	1063.6	1052.4	1041.3	1035.4
32.5°	1084.7	1078.1	1071.4	1064.7	1058.1	1049.0	1037.5	1026.0	1014.5	1003.0	996.2
35°	1032.8	1025.3	1017.7	1010.1	1002.6	992.9	981.1	969.2	957.4	945.6	937.6
37.5°	977.3	969.5	961.7	953.9	946.1	935.7	922.6	909.5	896.4	883.3	874.3
40°	938.2	930.4	922.6	914.8	907.0	896.3	882.8	869.4	855.9	842.4	832.5
42.5°	900.7	892.5	884.4	876.2	868.0	856.9	842.9	828.8	814.8	800.7	790.6
45°	842.4	833.7	824.9	816.2	807.4	796.0	781.8	767.6	753.4	739.3	727.7
47.5°	782.2	773.2	764.2	755.1	746.1	734.2	719.5	704.7	690.0	675.2	663.2
50°	741.4	732.2	722.9	713.7	704.5	692.3	677.2	662.1	646.9	631.8	620.0
52.5°	699.7	690.7	681.6	672.6	663.6	651.3	635.8	620.3	604.8	589.3	577.3
55°	638.2	628.7	619.3	609.8	600.4	588.0	572.6	557.2	541.9	526.5	514.2
57.5°	577.4	567.5	557.7	547.9	538.0	525.5	510.4	495.3	480.2	465.0	452.6
60°	534.0	524.5	515.1	505.6	496.1	483.9	468.7	453.6	438.5	423.3	411.0
62.5°	494.8	485.0	475.2	465.3	455.5	442.8	427.3	411.8	396.3	380.8	369.4
65°	434.0	423.8	413.6	403.5	393.3	380.7	365.5	350.4	335.3	320.2	310.0
67.5°	370.8	361.1	351.3	341.6	331.8	320.0	305.9	291.9	277.8	263.8	255.0
70°	330.8	320.9	310.9	301.0	291.1	279.4	265.9	252.4	239.0	225.5	217.7
72.5°	288.3	279.3	270.3	261.3	252.3	241.5	228.8	216.0	203.3	190.6	183.9
75°	230.8	222.1	213.3	204.6	195.8	185.9	174.8	163.7	152.6	141.5	136.0
77.5°	172.5	165.1	157.7	150.3	142.8	134.6	125.7	116.7	107.7	98.7	95.5
80°	135.1	128.2	121.4	114.5	107.7	100.7	93.6	86.5	79.4	72.3	71.6
82.5°	102.8	96.5	90.2	83.9	77.6	72.4	68.4	64.3	60.2	56.2	55.6
85°	57.4	52.7	48.0	43.3	38.5	35.8	35.1	34.4	33.7	33.0	32.5
87.5°	20.2	19.1	18.1	17.1	16.1	15.6	15.8	16.0	16.1	16.3	16.4
90°	3.0	5.4	7.9	10.3	12.8	14.9	16.6	18.4	20.2	22.0	23.3
92.5°	21.4	24.2	26.9	29.7	32.5	34.6	35.8	37.0	38.3	39.5	40.3
95°	59.9	61.9	63.9	65.9	67.9	69.6	71.2	72.8	74.3	75.9	76.5
97.5°	104.6	106.2	107.8	109.4	111.0	112.7	114.5	116.3	118.2	120.0	120.8
100°	139.7	140.6	141.5	142.4	143.3	144.7	146.7	148.7	150.7	152.7	153.2
102.5°	176.5	176.8	177.2	177.5	177.9	179.0	180.8	182.6	184.4	186.3	186.9
105°	232.6	232.8	233.0	233.2	233.5	234.0	234.9	235.8	236.7	237.6	238.2
107.5°	291.5	291.7	292.0	292.3	292.5	292.7	292.9	293.0	293.1	293.3	293.9
110°	331.4	331.8	332.3	332.7	333.2	333.3	333.0	332.8	332.6	332.4	331.9



TEST NUMBER: P332947

CATALOG NUMBER: SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.9	373.0	373.1	373.2	373.3	373.1	372.7	372.3	371.9	371.5	371.4
115°	435.2	435.2	435.2	435.2	435.2	435.0	434.5	434.1	433.6	433.2	433.0
117.5°	493.9	494.1	494.2	494.4	494.6	494.5	494.2	493.9	493.6	493.3	492.5
120°	533.0	533.9	534.8	535.7	536.6	536.7	536.0	535.3	534.7	534.0	532.9
122.5°	573.7	574.1	574.4	574.8	575.1	575.2	574.9	574.5	574.2	573.9	573.2
125°	633.8	633.8	633.8	633.8	633.8	633.7	633.5	633.3	633.0	632.8	632.4
127.5°	688.3	689.0	689.6	690.3	691.0	691.1	690.8	690.4	690.1	689.7	689.3
130°	726.6	727.3	728.0	728.6	729.3	729.6	729.6	729.6	729.6	729.6	729.2
132.5°	765.8	766.3	766.7	767.2	767.7	767.9	767.7	767.5	767.3	767.2	766.7
135°	817.5	818.8	820.1	821.5	822.8	823.5	823.5	823.5	823.5	823.5	823.0
137.5°	873.8	874.4	875.0	875.6	876.3	876.7	877.1	877.5	877.8	878.2	877.6
140°	911.3	911.7	912.2	912.6	913.1	913.3	913.3	913.3	913.3	913.3	913.1
142.5°	945.6	946.1	946.5	947.0	947.4	947.5	947.4	947.2	947.0	946.8	946.8
145°	993.1	994.0	994.9	995.8	996.7	997.2	997.5	997.7	997.9	998.1	997.9
147.5°	1040.3	1041.3	1042.4	1043.5	1044.5	1045.0	1044.8	1044.6	1044.4	1044.3	1044.1
150°	1069.0	1069.9	1070.8	1071.7	1072.6	1073.0	1073.0	1073.0	1073.0	1073.0	1073.0
152.5°	1096.2	1096.7	1097.2	1097.8	1098.3	1098.6	1098.8	1099.0	1099.2	1099.3	1099.9
155°	1137.9	1137.9	1137.9	1137.9	1137.9	1137.8	1137.5	1137.3	1137.1	1136.9	1137.8
157.5°	1173.0	1172.6	1172.2	1171.8	1171.4	1171.2	1171.1	1171.1	1171.1	1171.0	1171.7
160°	1193.8	1193.5	1193.3	1193.1	1192.9	1192.7	1192.4	1192.2	1192.0	1191.8	1192.4
162.5°	1212.9	1212.4	1211.8	1211.2	1210.6	1210.2	1210.0	1209.8	1209.6	1209.3	1210.5
165°	1238.7	1238.0	1237.4	1236.7	1236.0	1235.5	1235.0	1234.6	1234.1	1233.7	1235.0
167.5°	1258.5	1257.5	1256.6	1255.7	1254.7	1254.3	1254.3	1254.4	1254.4	1254.5	1255.8
170°	1269.6	1268.5	1267.4	1266.3	1265.2	1264.7	1265.0	1265.2	1265.4	1265.6	1267.0
172.5°	1277.6	1276.7	1275.8	1274.8	1273.9	1273.4	1273.5	1273.5	1273.6	1273.6	1275.1
175°	1288.6	1287.5	1286.4	1285.3	1284.2	1283.5	1283.3	1283.0	1282.8	1282.6	1284.2
177.5°	1292.2	1291.3	1290.4	1289.5	1288.6	1288.2	1288.2	1288.2	1288.2	1288.2	1289.4
180°	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6



TEST NUMBER: P332947

CATALOG NUMBER: SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1384.0	1386.0	1388.1	1389.1	1388.9	1388.7	1388.5	1388.3
5°	1374.7	1377.1	1379.5	1380.4	1379.9	1379.5	1379.0	1378.5
7.5°	1356.4	1358.0	1359.5	1359.8	1359.1	1358.3	1357.6	1356.8
10°	1340.0	1340.9	1341.9	1341.9	1340.9	1340.0	1339.0	1338.1
12.5°	1319.7	1320.2	1320.8	1320.4	1319.1	1317.8	1316.4	1315.1
15°	1284.0	1283.5	1283.0	1282.0	1280.3	1278.6	1277.0	1275.3
17.5°	1241.0	1239.7	1238.3	1236.4	1233.9	1231.4	1228.9	1226.4
20°	1210.9	1209.0	1207.1	1204.7	1201.6	1198.5	1195.4	1192.4
22.5°	1177.6	1174.7	1171.9	1169.2	1166.7	1164.2	1161.7	1159.2
25°	1123.7	1119.7	1115.7	1112.5	1110.1	1107.8	1105.4	1103.0
27.5°	1068.8	1063.9	1058.9	1054.7	1051.3	1047.9	1044.5	1041.1
30°	1029.5	1023.6	1017.7	1012.8	1009.1	1005.3	1001.5	997.7
32.5°	989.3	982.5	975.6	970.4	966.8	963.2	959.6	956.0
35°	929.5	921.5	913.5	907.3	903.1	898.8	894.5	890.3
37.5°	865.3	856.3	847.3	840.7	836.5	832.2	828.0	823.7
40°	822.6	812.6	802.7	795.6	791.4	787.1	782.9	778.6
42.5°	780.5	770.4	760.3	753.0	748.5	744.1	739.7	735.2
45°	716.1	704.5	692.9	685.0	680.7	676.5	672.2	668.0
47.5°	651.2	639.2	627.2	618.8	614.2	609.5	604.8	600.1
50°	608.2	596.4	584.5	576.4	571.9	567.4	562.9	558.4
52.5°	565.3	553.3	541.2	532.9	528.2	523.5	518.9	514.2
55°	501.9	489.6	477.4	469.0	464.5	460.0	455.5	451.0
57.5°	440.1	427.6	415.1	407.2	403.8	400.4	397.0	393.6
60°	398.8	386.5	374.2	366.1	362.4	358.6	354.8	351.0
62.5°	358.1	346.8	335.4	328.2	325.2	322.2	319.1	316.1
65°	299.8	289.7	279.5	273.0	270.2	267.3	264.5	261.7
67.5°	246.3	237.6	228.8	222.9	219.8	216.6	213.5	210.4
70°	209.9	202.1	194.3	189.2	186.9	184.5	182.1	179.8
72.5°	177.3	170.6	163.9	159.5	157.4	155.2	153.0	150.8
75°	130.6	125.2	119.7	116.3	114.9	113.5	112.0	110.6
77.5°	92.4	89.2	86.0	84.2	83.8	83.4	83.0	82.5
80°	70.9	70.2	69.5	69.0	68.8	68.5	68.3	68.1
82.5°	55.1	54.6	54.1	53.7	53.5	53.2	53.0	52.8
85°	32.0	31.6	31.1	30.8	30.8	30.8	30.8	30.8
87.5°	16.5	16.5	16.6	16.8	17.1	17.3	17.6	17.9
90°	24.6	26.0	27.3	28.2	28.6	29.1	29.5	29.9
92.5°	41.1	41.9	42.7	43.3	43.5	43.8	44.1	44.3
95°	77.2	77.9	78.5	78.9	78.9	78.9	78.9	78.9
97.5°	121.6	122.4	123.2	123.6	123.6	123.6	123.6	123.6
100°	153.6	154.0	154.5	154.7	154.7	154.7	154.7	154.7
102.5°	187.5	188.1	188.7	189.1	189.3	189.5	189.7	189.8
105°	238.9	239.6	240.2	240.9	241.5	242.2	242.9	243.5
107.5°	294.5	295.1	295.7	296.0	296.0	295.9	295.9	295.8
110°	331.5	331.0	330.6	330.7	331.4	332.0	332.7	333.4



TEST NUMBER: P332947

CATALOG NUMBER: SA4XXRDIP-C795D1035U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	371.3	371.2	371.2	371.2	371.3	371.4	371.6	371.7
115°	432.7	432.5	432.3	432.1	431.9	431.6	431.4	431.2
117.5°	491.8	491.0	490.3	489.7	489.2	488.8	488.3	487.9
120°	531.8	530.7	529.6	529.2	529.7	530.1	530.6	531.0
122.5°	572.4	571.7	570.9	570.1	569.3	568.5	567.7	566.9
125°	631.9	631.5	631.0	630.6	630.2	629.7	629.3	628.8
127.5°	688.8	688.4	687.9	687.5	687.2	686.8	686.5	686.1
130°	728.8	728.3	727.9	727.2	726.3	725.4	724.5	723.6
132.5°	766.3	765.8	765.4	765.0	764.6	764.3	763.9	763.6
135°	822.6	822.1	821.7	821.1	820.5	819.8	819.1	818.5
137.5°	877.0	876.4	875.9	875.6	875.8	875.9	876.0	876.2
140°	912.9	912.6	912.4	912.2	912.0	911.7	911.5	911.3
142.5°	946.7	946.7	946.7	946.6	946.6	946.5	946.5	946.4
145°	997.7	997.5	997.2	996.8	996.1	995.5	994.8	994.1
147.5°	1043.9	1043.7	1043.5	1043.3	1043.1	1042.9	1042.7	1042.5
150°	1073.0	1073.0	1073.0	1072.9	1072.7	1072.4	1072.2	1072.0
152.5°	1100.4	1100.9	1101.5	1101.5	1100.9	1100.3	1099.7	1099.1
155°	1138.7	1139.5	1140.4	1140.4	1139.5	1138.7	1137.8	1136.9
157.5°	1172.3	1173.0	1173.7	1173.6	1172.9	1172.1	1171.4	1170.6
160°	1193.1	1193.8	1194.4	1194.2	1193.1	1192.0	1190.9	1189.8
162.5°	1211.7	1212.9	1214.1	1214.2	1213.1	1212.0	1210.9	1209.7
165°	1236.4	1237.7	1239.0	1239.2	1238.4	1237.5	1236.6	1235.7
167.5°	1257.1	1258.5	1259.8	1259.8	1258.4	1257.0	1255.6	1254.3
170°	1268.3	1269.6	1271.0	1270.8	1269.3	1267.7	1266.2	1264.6
172.5°	1276.6	1278.1	1279.7	1279.6	1278.1	1276.5	1275.0	1273.4
175°	1285.7	1287.3	1288.8	1288.8	1287.3	1285.7	1284.2	1282.6
177.5°	1290.7	1291.9	1293.2	1293.1	1291.7	1290.2	1288.8	1287.4
180°	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6

(END OF REPORT)