

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332930

Luminaire Tested: **SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4518.9 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332930
CATALOG NUMBER: SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332930

CATALOG NUMBER: SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71				
1	103	99	95	91	97	94	90	87	84	81	79	75	73	72	67	66	65	61				
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	51				
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44				
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38				
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33				
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32	29				
7	62	50	42	36	59	48	40	35	44	37	33	40	34	31	36	32	28	26				
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	26	23				
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23	21				
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11215	11215	11215
5°	11240	11102	11171
10°	11170	10969	10969
15°	11041	10739	10659
20°	10865	10436	10244
25°	10640	10081	9825
30°	10421	9707	9300
35°	10178	9319	8774
40°	9887	8878	8205
45°	9618	8440	7626
50°	9311	7935	7013
55°	8983	7410	6348
60°	8622	6835	5667
65°	8290	6117	4999
70°	7808	5323	4244
75°	7199	4414	3450
80°	6281	3361	3166
85°	5317	3057	2853



TEST NUMBER: P332930

CATALOG NUMBER: SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.5	2.9
10°-20°	363.9	8.1
20°-30°	525.5	11.6
30°-40°	595.6	13.2
40°-50°	575.2	12.7
50°-60°	478.3	10.6
60°-70°	330.3	7.3
70°-80°	167.4	3.7
80°-90°	43.9	1.0
90°-100°	129.9	2.9
100°-110°	270.4	6.0
110°-120°	242.2	5.4
120°-130°	203.7	4.5
130°-140°	169.9	3.8
140°-150°	129.8	2.9
150°-160°	91.2	2.0
160°-170°	53.7	1.2
170°-180°	17.5	0.4
0°-30°	1019.8	22.6
0°-40°	1615.5	35.7
0°-60°	2668.9	59.1
0°-90°	3210.5	71.0
90°-120°	642.6	14.2
90°-150°	1146.0	25.4
90°-180°	1308.0	28.9
0°-180°	4518.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1387	1382	1370	1380	1378	132
15°	1321	1311	1285	1282	1275	372
25°	1194	1174	1132	1114	1103	550
35°	1033	998	946	910	890	645
45°	842	802	739	689	668	649
55°	638	594	526	473	451	571
65°	434	387	320	276	262	428
75°	231	191	142	118	111	244
85°	57	37	33	31	31	65
90°	0	3	6	7	7	3
95°	12	37	288	143	86	13
105°	41	60	232	499	497	44
115°	73	91	207	397	478	72
125°	101	121	206	338	381	90
135°	120	144	204	300	341	93
145°	139	159	203	253	278	87
155°	158	171	197	223	233	73
165°	172	177	189	200	203	49
175°	180	180	181	184	183	17
180°	180	180	180	180	180	



TEST NUMBER: P332930

CATALOG NUMBER: SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1392.6	1391.8	1391.0	1390.3	1389.5	1388.1	1386.0	1384.0	1381.9	1379.8	1381.9
5°	1387.0	1386.1	1385.1	1384.2	1383.2	1381.4	1378.5	1375.7	1372.8	1370.0	1372.4
7.5°	1374.5	1373.5	1372.5	1371.5	1370.5	1368.2	1364.5	1360.8	1357.1	1353.4	1354.9
10°	1362.6	1361.4	1360.2	1359.0	1357.8	1355.1	1350.9	1346.6	1342.4	1338.1	1339.0
12.5°	1347.2	1345.9	1344.5	1343.1	1341.8	1338.6	1333.6	1328.5	1323.5	1318.5	1319.1
15°	1321.1	1319.0	1316.8	1314.7	1312.6	1308.6	1302.6	1296.7	1290.8	1284.9	1284.4
17.5°	1289.4	1286.3	1283.2	1280.2	1277.1	1272.0	1264.9	1257.8	1250.7	1243.6	1242.3
20°	1264.7	1261.6	1258.6	1255.5	1252.4	1246.9	1238.8	1230.8	1222.7	1214.7	1212.8
22.5°	1237.5	1234.0	1230.6	1227.1	1223.7	1217.6	1209.0	1200.4	1191.8	1183.2	1180.4
25°	1194.5	1190.2	1186.0	1181.7	1177.5	1170.5	1160.8	1151.1	1141.4	1131.7	1127.7
27.5°	1149.4	1144.1	1138.7	1133.4	1128.0	1120.2	1109.8	1099.5	1089.1	1078.8	1073.8
30°	1117.9	1112.0	1106.1	1100.2	1094.3	1085.8	1074.7	1063.6	1052.4	1041.3	1035.4
32.5°	1084.7	1078.1	1071.4	1064.7	1058.1	1049.0	1037.5	1026.0	1014.5	1003.0	996.2
35°	1032.8	1025.3	1017.7	1010.1	1002.6	992.9	981.1	969.2	957.4	945.6	937.6
37.5°	977.3	969.5	961.7	953.9	946.1	935.7	922.6	909.5	896.4	883.3	874.3
40°	938.2	930.4	922.6	914.8	907.0	896.3	882.8	869.4	855.9	842.4	832.5
42.5°	900.7	892.5	884.4	876.2	868.0	856.9	842.9	828.8	814.8	800.7	790.6
45°	842.4	833.7	824.9	816.2	807.4	796.0	781.8	767.6	753.4	739.3	727.7
47.5°	782.2	773.2	764.2	755.1	746.1	734.2	719.5	704.7	690.0	675.2	663.2
50°	741.4	732.2	722.9	713.7	704.5	692.3	677.2	662.1	646.9	631.8	620.0
52.5°	699.7	690.7	681.6	672.6	663.6	651.3	635.8	620.3	604.8	589.3	577.3
55°	638.2	628.7	619.3	609.8	600.4	588.0	572.6	557.2	541.9	526.5	514.2
57.5°	577.4	567.5	557.7	547.9	538.0	525.5	510.4	495.3	480.2	465.0	452.6
60°	534.0	524.5	515.1	505.6	496.1	483.9	468.7	453.6	438.5	423.3	411.0
62.5°	494.8	485.0	475.2	465.3	455.5	442.8	427.3	411.8	396.3	380.8	369.4
65°	434.0	423.8	413.6	403.5	393.3	380.7	365.5	350.4	335.3	320.2	310.0
67.5°	370.8	361.1	351.3	341.6	331.8	320.0	305.9	291.9	277.8	263.8	255.0
70°	330.8	320.9	310.9	301.0	291.1	279.4	265.9	252.4	239.0	225.5	217.7
72.5°	288.3	279.3	270.3	261.3	252.3	241.5	228.8	216.0	203.3	190.6	183.9
75°	230.8	222.1	213.3	204.6	195.8	185.9	174.8	163.7	152.6	141.5	136.0
77.5°	172.5	165.1	157.7	150.3	142.8	134.6	125.7	116.7	107.7	98.7	95.5
80°	135.1	128.2	121.4	114.5	107.7	100.7	93.6	86.5	79.4	72.3	71.6
82.5°	102.8	96.5	90.2	83.9	77.6	72.4	68.4	64.3	60.2	56.2	55.6
85°	57.4	52.7	48.0	43.3	38.5	35.8	35.1	34.4	33.7	33.0	32.5
87.5°	19.6	18.3	17.0	15.5	14.1	13.2	13.5	13.3	13.2	13.2	12.9
90°	0.4	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.7	6.4	6.0
92.5°	4.0	5.9	9.2	13.5	18.7	26.0	44.0	71.4	98.1	112.1	93.4
95°	11.7	12.7	16.3	20.9	29.3	44.2	74.9	132.9	217.4	288.0	296.2
97.5°	20.9	20.9	24.0	28.2	35.5	47.9	71.6	119.5	203.4	303.4	372.1
100°	26.9	26.9	29.3	33.6	40.3	51.6	72.5	112.4	184.5	284.2	374.6
102.5°	32.5	33.1	35.3	39.2	45.7	56.4	75.3	110.4	171.8	260.1	353.4
105°	41.4	42.4	44.2	48.4	54.8	65.0	82.0	111.3	160.8	231.8	314.9
107.5°	51.1	51.8	53.6	58.1	64.2	74.3	89.8	116.6	158.8	216.0	283.8
110°	57.6	58.3	60.1	64.3	70.7	80.2	95.8	120.5	159.4	210.6	268.3



TEST NUMBER: P332930

CATALOG NUMBER: SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	63.8	64.5	66.6	70.5	76.9	86.4	101.4	124.8	161.1	208.1	259.5
115°	72.8	73.9	76.3	79.9	86.6	96.1	110.3	131.5	164.3	206.8	251.3
117.5°	82.1	83.1	85.3	89.2	95.5	105.4	118.8	138.3	167.8	206.4	247.6
120°	88.4	89.1	91.5	95.4	101.4	111.3	124.8	143.1	170.4	206.4	245.6
122.5°	94.0	94.7	97.2	100.8	107.4	117.0	130.4	147.7	172.9	206.1	243.4
125°	101.4	102.8	105.0	108.9	115.6	125.5	138.2	154.4	176.7	205.7	239.6
127.5°	108.0	109.1	111.7	116.1	123.1	133.1	145.4	160.3	179.8	204.9	234.6
130°	111.7	113.1	115.9	121.2	127.9	138.2	150.2	164.0	182.0	204.6	231.5
132.5°	115.4	116.5	120.2	125.2	132.5	142.1	154.2	167.7	184.0	204.4	228.7
135°	120.5	121.9	125.5	131.5	138.9	148.1	159.7	172.5	187.0	203.9	224.4
137.5°	125.7	127.0	130.9	136.6	144.3	153.1	164.0	175.9	188.7	203.9	220.8
140°	129.4	130.4	134.3	140.3	147.7	156.2	166.8	178.1	190.1	203.6	218.8
142.5°	133.3	134.4	138.0	143.7	150.8	159.0	169.4	179.8	191.3	203.6	217.1
145°	138.9	140.0	143.5	148.4	155.2	162.9	172.1	181.7	191.9	202.9	214.2
147.5°	145.2	145.5	148.7	153.7	159.3	166.3	174.9	183.3	192.3	201.6	211.6
150°	149.1	149.5	152.3	156.6	161.9	168.6	176.4	184.1	192.3	200.7	209.6
152.5°	152.8	152.9	155.7	159.7	164.4	170.6	177.5	184.7	191.7	199.3	207.3
155°	158.0	158.3	160.5	164.0	167.9	173.2	179.2	185.2	190.9	197.2	203.9
157.5°	163.0	163.0	165.0	167.7	171.1	175.3	180.4	185.2	189.9	195.0	200.5
160°	166.1	166.1	167.5	170.0	172.8	176.7	181.0	185.2	189.1	193.3	197.9
162.5°	168.9	168.7	169.8	172.0	174.5	177.6	181.5	185.2	188.2	191.6	195.7
165°	172.1	172.1	172.8	174.6	176.4	178.5	181.7	184.5	186.6	189.1	191.9
167.5°	175.3	174.9	175.3	176.6	177.6	179.3	181.6	183.6	184.9	186.5	188.5
170°	176.7	176.4	176.7	177.8	178.5	179.5	181.3	183.1	183.8	184.8	186.3
172.5°	178.1	177.8	177.8	178.6	179.0	179.8	181.0	182.5	182.7	183.1	184.3
175°	179.5	179.2	179.2	179.5	179.9	179.9	180.6	181.7	181.3	181.3	182.0
177.5°	180.2	179.9	179.6	179.9	179.9	179.9	180.2	180.7	180.2	180.2	180.5
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332930

CATALOG NUMBER: SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1384.0	1386.0	1388.1	1389.1	1388.9	1388.7	1388.5	1388.3
5°	1374.7	1377.1	1379.5	1380.4	1379.9	1379.5	1379.0	1378.5
7.5°	1356.4	1358.0	1359.5	1359.8	1359.1	1358.3	1357.6	1356.8
10°	1340.0	1340.9	1341.9	1341.9	1340.9	1340.0	1339.0	1338.1
12.5°	1319.7	1320.2	1320.8	1320.4	1319.1	1317.8	1316.4	1315.1
15°	1284.0	1283.5	1283.0	1282.0	1280.3	1278.6	1277.0	1275.3
17.5°	1241.0	1239.7	1238.3	1236.4	1233.9	1231.4	1228.9	1226.4
20°	1210.9	1209.0	1207.1	1204.7	1201.6	1198.5	1195.4	1192.4
22.5°	1177.6	1174.7	1171.9	1169.2	1166.7	1164.2	1161.7	1159.2
25°	1123.7	1119.7	1115.7	1112.5	1110.1	1107.8	1105.4	1103.0
27.5°	1068.8	1063.9	1058.9	1054.7	1051.3	1047.9	1044.5	1041.1
30°	1029.5	1023.6	1017.7	1012.8	1009.1	1005.3	1001.5	997.7
32.5°	989.3	982.5	975.6	970.4	966.8	963.2	959.6	956.0
35°	929.5	921.5	913.5	907.3	903.1	898.8	894.5	890.3
37.5°	865.3	856.3	847.3	840.7	836.5	832.2	828.0	823.7
40°	822.6	812.6	802.7	795.6	791.4	787.1	782.9	778.6
42.5°	780.5	770.4	760.3	753.0	748.5	744.1	739.7	735.2
45°	716.1	704.5	692.9	685.0	680.7	676.5	672.2	668.0
47.5°	651.2	639.2	627.2	618.8	614.2	609.5	604.8	600.1
50°	608.2	596.4	584.5	576.4	571.9	567.4	562.9	558.4
52.5°	565.3	553.3	541.2	532.9	528.2	523.5	518.9	514.2
55°	501.9	489.6	477.4	469.0	464.5	460.0	455.5	451.0
57.5°	440.1	427.6	415.1	407.2	403.8	400.4	397.0	393.6
60°	398.8	386.5	374.2	366.1	362.4	358.6	354.8	351.0
62.5°	358.1	346.8	335.4	328.2	325.2	322.2	319.1	316.1
65°	299.8	289.7	279.5	273.0	270.2	267.3	264.5	261.7
67.5°	246.3	237.6	228.8	222.9	219.8	216.6	213.5	210.4
70°	209.9	202.1	194.3	189.2	186.9	184.5	182.1	179.8
72.5°	177.3	170.6	163.9	159.5	157.4	155.2	153.0	150.8
75°	130.6	125.2	119.7	116.3	114.9	113.5	112.0	110.6
77.5°	92.4	89.2	86.0	84.2	83.8	83.4	83.0	82.5
80°	70.9	70.2	69.5	69.0	68.8	68.5	68.3	68.1
82.5°	55.1	54.6	54.1	53.7	53.5	53.2	53.0	52.8
85°	32.0	31.6	31.1	30.8	30.8	30.8	30.8	30.8
87.5°	12.8	12.7	12.6	12.6	12.8	13.1	13.2	13.4
90°	6.4	6.7	7.1	7.1	7.4	7.8	7.4	7.4
92.5°	69.4	52.2	41.6	34.5	30.3	28.4	27.2	27.2
95°	261.9	207.1	159.7	125.5	108.1	97.2	90.8	86.2
97.5°	386.9	366.6	332.0	295.1	269.7	248.5	237.9	230.5
100°	426.2	433.3	416.0	389.8	359.1	337.5	326.9	324.1
102.5°	424.3	459.3	464.3	453.4	434.6	419.0	407.8	405.5
105°	395.8	457.0	492.0	506.5	507.2	504.3	499.4	497.3
107.5°	355.5	420.6	469.8	501.4	518.8	526.9	530.4	531.3
110°	331.2	392.3	443.6	482.4	507.5	522.4	528.7	531.9



TEST NUMBER: P332930

CATALOG NUMBER: SA4XXRDIP-C795D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.3	367.4	415.8	454.7	483.2	501.2	510.1	515.2
115°	295.5	338.9	380.3	414.2	442.1	463.3	474.7	477.5
117.5°	286.7	322.7	355.2	384.0	407.8	425.6	437.0	439.2
120°	282.7	315.6	343.9	369.0	389.1	404.7	413.9	417.8
122.5°	279.3	311.1	336.8	358.8	375.8	389.1	396.9	400.8
125°	273.6	303.9	328.3	347.8	361.9	372.2	378.9	381.0
127.5°	266.5	295.5	319.9	338.3	352.5	361.6	367.3	369.4
130°	260.8	288.8	312.8	331.5	346.0	354.8	360.5	362.6
132.5°	254.9	281.1	304.6	323.3	337.5	347.5	352.9	355.0
135°	246.7	269.7	291.2	308.9	323.0	332.9	338.6	340.7
137.5°	239.3	258.7	276.9	292.8	306.1	315.8	320.5	323.0
140°	235.0	251.6	267.5	282.4	294.8	302.5	307.5	310.3
142.5°	231.1	245.7	259.3	272.2	283.2	290.4	294.8	296.7
145°	225.5	237.5	248.1	258.0	266.8	272.8	276.4	278.1
147.5°	220.9	230.4	238.9	246.7	253.2	258.4	261.0	261.7
150°	218.1	226.2	233.3	239.6	245.3	249.9	252.0	252.3
152.5°	215.0	222.0	228.5	233.7	238.5	242.2	243.5	243.9
155°	210.3	215.9	221.2	225.5	229.0	231.8	232.9	232.9
157.5°	205.3	210.0	214.5	217.9	220.5	222.7	223.3	223.3
160°	202.2	206.0	209.9	212.8	214.9	217.0	217.4	217.4
162.5°	199.1	202.4	205.4	208.0	209.5	211.6	212.0	211.7
165°	194.7	196.9	199.3	201.1	202.5	203.9	203.6	203.2
167.5°	190.6	192.2	194.2	195.2	195.9	196.9	196.8	196.5
170°	188.0	189.1	190.5	191.6	192.3	192.6	192.3	192.3
172.5°	185.8	186.5	187.4	188.2	188.6	188.9	188.6	188.0
175°	182.7	183.1	183.8	183.8	183.8	184.5	183.8	183.1
177.5°	180.7	181.0	181.0	181.3	181.0	181.3	180.7	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)