

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332937

Luminaire Tested: **SA4XXRDIP-C795D810U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332937  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6573.4 lumens  
Efficiency: N/A  
Efficacy: 143.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332937  
CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49				44	
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	45	44	42				37	
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	38	36				32	
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	37	34	32				28	
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28				25	
6	64	52	44	39	59	49	42	37	42	37	33	36	32	29	30	27	25				22	
7	59	47	40	34	55	44	37	32	38	33	29	33	29	25	28	24	22				19	
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	25	22	20				17	
9	51	39	32	27	48	37	30	26	32	27	23	28	23	20	24	20	18				16	
10	48	36	29	24	44	34	27	23	30	24	21	26	21	19	22	19	16				14	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10656	10656	10656	10656
5°	12361	10689	9447	10689
10°	14623	10642	8432	10642
15°	16891	10543	7245	10543
20°	18806	10408	6552	10408
25°	19414	10276	6083	10276
30°	16995	10113	5800	10113
35°	13230	9875	5629	9875
40°	9921	9601	5538	9601
45°	7833	9162	5489	9162
50°	6612	8657	5330	8657
55°	5764	8099	5046	8099
60°	5186	7522	4466	7522
65°	4571	6898	3840	6898
70°	4116	6253	3465	6253
75°	3450	5540	2954	5540
80°	2920	4723	2771	4723
85°	2464	3696	2464	3696



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.9	1.9
10°-20°	385.8	5.9
20°-30°	603.4	9.2
30°-40°	670.8	10.2
40°-50°	595.2	9.1
50°-60°	463.8	7.1
60°-70°	303.6	4.6
70°-80°	149.3	2.3
80°-90°	39.9	0.6
90°-100°	35.8	0.5
100°-110°	228.0	3.5
110°-120°	436.1	6.6
120°-130°	553.6	8.4
130°-140°	592.3	9.0
140°-150°	553.9	8.4
150°-160°	446.7	6.8
160°-170°	288.1	4.4
170°-180°	99.3	1.5
0°-30°	1117.1	17.0
0°-40°	1787.9	27.2
0°-60°	2846.9	43.3
0°-90°	3339.7	50.8
90°-120°	699.8	10.6
90°-150°	2399.6	36.5
90°-180°	3234.0	49.2
0°-180°	6573.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1320	1320	1320	1320	1320	
5°	1525	1319	1166	1319	1525	154
15°	2021	1262	867	1262	2021	575
25°	2180	1154	683	1154	2180	967
35°	1342	1002	571	1002	1342	841
45°	686	802	481	802	686	543
55°	410	575	358	575	410	372
65°	239	361	201	361	239	241
75°	111	178	95	178	111	122
85°	27	40	27	40	27	31
90°	24	2	24	2	24	11
95°	23	43	23	43	23	18
105°	223	235	223	235	223	194
115°	443	439	443	439	443	438
125°	622	618	622	618	622	554
135°	772	766	772	766	772	594
145°	888	884	888	884	888	555
155°	968	969	968	969	968	446
165°	1017	1022	1017	1022	1017	287
175°	1039	1045	1039	1045	1039	99
180°	1045	1045	1045	1045	1045	



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1392.3	1396.2	1392.3	1391.9	1387.7	1386.4	1384.7	1379.2	1368.9	1363.0	1364.3
5°	1525.3	1538.6	1531.2	1530.1	1518.4	1506.7	1499.2	1482.2	1464.1	1451.9	1441.8
7.5°	1679.1	1686.8	1682.1	1674.6	1655.7	1645.0	1627.7	1605.3	1572.9	1548.1	1525.4
10°	1783.8	1790.2	1788.0	1774.2	1760.4	1732.2	1716.2	1684.9	1643.9	1611.5	1581.2
12.5°	1886.7	1893.6	1874.8	1875.5	1849.3	1827.1	1801.8	1762.3	1715.0	1673.2	1635.2
15°	2021.0	2012.5	2012.5	2001.8	1972.6	1941.7	1915.7	1874.2	1814.6	1764.6	1712.0
17.5°	2126.1	2129.0	2124.7	2099.6	2076.6	2044.7	1996.9	1948.5	1893.2	1826.1	1772.3
20°	2189.0	2189.0	2184.3	2167.2	2137.5	2103.4	2051.8	1999.2	1929.0	1861.4	1800.8
22.5°	2214.6	2216.3	2210.6	2196.6	2169.8	2136.6	2092.7	2039.2	1966.8	1890.8	1815.7
25°	2179.5	2189.6	2190.6	2186.9	2178.9	2158.7	2121.0	2066.2	2001.3	1918.9	1838.0
27.5°	2001.0	2013.7	2024.9	2043.3	2067.8	2080.5	2082.2	2054.4	1997.8	1918.4	1837.1
30°	1823.1	1833.8	1868.3	1913.5	1948.7	1980.6	2008.2	2015.7	1983.8	1912.5	1826.9
32.5°	1625.7	1640.2	1674.8	1723.4	1781.9	1835.9	1898.0	1929.7	1928.9	1886.1	1806.9
35°	1342.4	1353.0	1384.9	1436.0	1506.2	1586.5	1684.9	1761.4	1813.6	1809.8	1761.4
37.5°	1082.6	1094.6	1126.9	1169.2	1237.3	1336.7	1431.9	1537.4	1633.8	1687.9	1671.8
40°	941.4	941.9	973.3	1016.9	1080.7	1167.4	1271.1	1388.1	1495.5	1583.3	1600.3
42.5°	829.9	830.0	850.7	897.7	943.7	1025.3	1124.3	1240.5	1366.2	1467.6	1512.7
45°	686.1	690.9	707.9	736.1	772.2	841.4	920.6	1028.6	1169.5	1289.7	1364.7
47.5°	581.0	588.0	598.8	621.8	650.6	696.7	762.2	859.2	973.9	1106.1	1212.8
50°	526.5	527.6	541.4	554.2	579.2	615.9	673.3	754.1	859.4	986.6	1105.2
52.5°	479.7	479.5	487.8	504.0	524.3	552.9	599.3	672.9	766.3	880.2	1002.6
55°	409.5	412.2	418.6	431.3	446.7	467.0	503.6	559.0	632.4	729.7	840.8
57.5°	356.1	357.5	362.5	367.9	382.1	396.8	424.3	462.7	524.6	604.3	707.9
60°	321.2	321.8	323.4	331.3	342.5	356.3	374.9	407.4	459.5	532.4	614.3
62.5°	287.2	288.1	290.6	296.4	305.1	314.6	334.1	360.2	403.3	465.6	539.4
65°	239.3	239.9	243.6	245.7	252.6	261.1	275.5	293.0	322.8	374.9	430.8
67.5°	200.0	200.0	200.2	203.1	207.8	213.5	222.1	236.1	258.6	290.6	339.8
70°	174.4	174.4	175.5	177.1	179.8	184.5	189.3	200.0	216.5	242.5	280.3
72.5°	150.6	151.0	152.1	152.4	153.8	157.7	161.3	168.1	180.3	200.0	230.5
75°	110.6	112.2	114.9	117.0	119.7	119.1	122.9	127.1	130.8	142.5	160.1
77.5°	82.3	81.5	81.8	83.6	83.9	84.5	87.1	90.4	93.2	98.7	105.0
80°	62.8	62.8	64.4	64.9	64.4	64.9	67.5	69.1	70.2	72.3	78.2
82.5°	47.4	48.3	47.8	48.3	48.6	49.1	51.4	51.7	52.8	53.6	56.1
85°	26.6	27.1	27.7	26.6	26.6	26.6	27.7	28.2	29.3	28.7	29.8
87.5°	14.1	13.6	13.9	13.8	14.2	13.6	13.9	14.5	13.4	13.7	13.4
90°	23.5	23.1	22.8	22.4	22.1	21.4	20.3	19.3	18.2	17.2	15.8
92.5°	21.6	21.5	21.4	21.4	21.3	20.7	19.7	18.7	17.6	16.6	15.2
95°	22.7	22.5	22.3	22.2	22.0	21.4	20.3	19.3	18.2	17.2	17.0
97.5°	21.9	21.7	21.5	21.4	21.2	21.1	21.0	20.9	20.7	20.6	40.0
100°	21.9	21.7	21.5	21.4	21.2	22.6	25.5	28.5	31.4	34.4	58.4
102.5°	22.5	22.5	22.4	22.4	22.4	38.3	70.2	102.0	133.9	165.8	168.9
105°	222.8	229.1	235.3	241.6	247.9	250.2	248.6	247.1	245.5	243.9	243.1
107.5°	310.6	309.9	309.2	308.6	307.9	307.2	306.4	305.7	304.9	304.2	303.0
110°	348.7	348.2	347.7	347.2	346.6	346.2	345.9	345.5	345.2	344.8	343.8



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	386.9	386.2	385.6	384.9	384.2	383.9	384.0	384.1	384.2	384.2	383.7
115°	442.6	442.6	442.6	442.6	442.6	442.4	442.0	441.7	441.3	441.0	441.2
117.5°	499.2	499.2	499.3	499.4	499.4	499.5	499.6	499.6	499.7	499.8	499.4
120°	534.8	535.2	535.5	535.9	536.2	536.2	535.9	535.5	535.2	534.8	535.0
122.5°	569.8	570.2	570.5	570.9	571.2	571.3	571.1	570.9	570.7	570.5	570.2
125°	622.4	622.2	622.0	621.9	621.7	621.3	620.8	620.3	619.8	619.3	619.6
127.5°	668.5	668.7	668.8	668.9	669.1	669.2	669.3	669.4	669.5	669.6	668.8
130°	699.8	699.8	699.8	699.8	699.8	699.7	699.5	699.4	699.2	699.0	698.5
132.5°	728.6	728.7	728.8	729.0	729.1	729.1	728.9	728.8	728.6	728.4	727.7
135°	771.7	771.4	771.0	770.7	770.3	770.0	769.6	769.3	768.9	768.6	767.9
137.5°	808.6	808.7	808.8	808.9	809.0	808.9	808.5	808.1	807.8	807.4	806.6
140°	834.3	834.1	833.9	833.8	833.6	833.2	832.7	832.2	831.7	831.1	830.8
142.5°	855.5	855.5	855.5	855.4	855.4	855.2	854.8	854.4	854.1	853.7	853.5
145°	888.2	887.9	887.5	887.2	886.8	886.6	886.4	886.2	886.1	885.9	885.9
147.5°	915.3	915.1	914.9	914.8	914.6	914.4	914.3	914.2	914.0	913.9	914.0
150°	932.8	932.6	932.4	932.3	932.1	932.0	932.0	932.0	932.0	932.0	932.2
152.5°	947.8	947.9	948.0	948.1	948.2	948.1	947.9	947.6	947.3	947.0	947.3
155°	968.0	968.5	969.0	969.5	970.1	970.0	969.3	968.6	967.9	967.2	967.7
157.5°	984.9	985.8	986.7	987.6	988.5	988.5	987.6	986.7	985.8	984.9	985.5
160°	996.1	997.2	998.2	999.3	1000.3	1000.3	999.3	998.2	997.2	996.1	996.3
162.5°	1004.9	1006.1	1007.2	1008.4	1009.6	1009.7	1008.6	1007.6	1006.6	1005.5	1005.7
165°	1017.2	1018.8	1020.4	1021.9	1023.5	1023.6	1022.2	1020.8	1019.4	1018.0	1018.0
167.5°	1026.5	1028.2	1029.9	1031.7	1033.4	1033.5	1032.0	1030.5	1028.9	1027.4	1027.5
170°	1032.1	1033.8	1035.6	1037.3	1039.0	1039.2	1037.8	1036.4	1035.0	1033.7	1033.5
172.5°	1035.2	1037.1	1039.0	1040.9	1042.7	1043.0	1041.6	1040.2	1038.8	1037.4	1037.2
175°	1039.1	1041.2	1043.3	1045.4	1047.5	1047.7	1046.2	1044.6	1043.0	1041.5	1041.3
177.5°	1041.6	1043.3	1045.0	1046.6	1048.3	1048.6	1047.5	1046.4	1045.2	1044.1	1043.9
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1360.0	1354.1	1351.1	1344.3	1336.2	1331.9	1328.1	1322.6	1315.3	1307.7	1302.1
5°	1429.0	1416.3	1400.3	1381.2	1364.2	1347.7	1333.3	1319.0	1302.5	1285.4	1268.4
7.5°	1499.9	1474.8	1447.7	1416.3	1385.8	1358.0	1332.5	1308.0	1280.3	1255.6	1233.0
10°	1549.2	1515.2	1477.4	1437.6	1397.7	1363.1	1329.1	1298.2	1264.2	1233.9	1208.3
12.5°	1589.2	1549.2	1503.8	1454.1	1406.2	1364.4	1325.2	1285.0	1246.3	1213.4	1179.4
15°	1655.6	1600.8	1539.7	1480.1	1417.9	1361.0	1308.3	1261.5	1217.4	1171.1	1138.7
17.5°	1701.2	1636.2	1561.9	1490.3	1416.8	1349.7	1289.0	1233.2	1182.3	1135.0	1096.4
20°	1728.5	1656.7	1574.2	1492.9	1410.4	1338.6	1273.2	1211.5	1158.9	1107.8	1067.9
22.5°	1743.8	1664.3	1574.2	1489.0	1403.6	1325.9	1254.1	1189.8	1132.5	1081.4	1037.3
25°	1748.7	1663.6	1571.6	1473.7	1380.1	1297.7	1223.2	1153.6	1089.7	1038.7	991.9
27.5°	1741.9	1641.7	1547.4	1447.0	1350.4	1263.5	1185.4	1112.2	1048.3	993.5	945.5
30°	1731.7	1624.2	1523.2	1418.9	1321.1	1237.6	1155.1	1084.9	1018.5	961.6	913.2
32.5°	1709.5	1603.0	1494.2	1387.5	1288.3	1202.3	1124.1	1053.5	988.3	930.1	878.7
35°	1665.7	1557.8	1439.7	1330.1	1232.8	1143.4	1070.1	1002.0	939.8	877.5	823.3
37.5°	1608.0	1497.7	1380.2	1260.2	1162.8	1078.5	1011.1	947.2	886.5	829.7	769.6
40°	1553.5	1453.0	1331.7	1212.6	1112.6	1031.2	969.0	911.0	849.9	793.5	733.4
42.5°	1487.5	1401.9	1279.4	1159.8	1061.1	982.7	924.8	868.1	812.4	757.8	695.1
45°	1377.5	1312.6	1197.7	1082.8	983.4	905.7	852.5	802.5	753.6	701.5	642.5
47.5°	1251.3	1207.4	1108.2	990.6	898.6	828.7	777.3	736.5	695.1	643.0	591.2
50°	1163.7	1135.5	1039.7	932.3	844.6	780.2	727.6	689.3	654.7	604.7	558.4
52.5°	1070.1	1055.1	974.2	871.5	786.7	723.6	678.6	644.2	609.2	567.7	524.4
55°	927.5	935.5	866.9	778.1	698.3	645.1	604.2	575.4	545.7	510.6	477.1
57.5°	781.8	810.9	764.9	686.9	612.1	563.0	532.2	508.0	483.0	453.9	425.3
60°	694.6	719.0	693.0	624.4	559.0	513.2	484.5	465.9	440.9	414.3	392.5
62.5°	609.5	635.7	620.2	564.8	504.1	464.7	439.4	422.1	403.5	380.3	357.6
65°	502.6	519.6	512.2	473.9	430.8	397.3	373.9	361.1	344.1	327.1	306.9
67.5°	384.9	417.8	413.5	393.1	355.9	329.7	314.4	303.1	287.6	275.0	261.2
70°	316.4	346.8	346.2	329.7	309.5	285.1	274.4	264.9	251.0	238.8	227.6
72.5°	259.0	286.8	290.9	278.3	264.4	245.9	235.7	229.1	215.7	207.3	198.3
75°	181.4	201.6	206.9	206.9	200.5	190.9	181.9	177.6	168.1	160.6	155.3
77.5°	118.9	131.7	140.0	141.9	142.9	139.7	132.2	129.2	121.9	119.2	114.1
80°	84.0	92.5	102.1	105.3	108.0	106.9	103.7	101.6	94.7	92.0	89.9
82.5°	58.1	62.8	70.6	77.6	76.9	79.7	76.9	75.2	70.0	69.0	66.9
85°	30.3	30.8	31.9	36.7	39.4	40.4	41.0	39.9	38.3	38.3	34.6
87.5°	13.1	12.4	13.0	12.6	12.7	14.0	14.9	14.9	14.0	13.1	12.3
90°	14.4	13.0	11.6	10.0	8.1	6.2	4.3	2.3	4.3	6.2	8.1
92.5°	13.8	12.4	11.0	10.3	10.2	10.1	10.0	9.9	10.0	10.1	10.2
95°	16.9	16.7	16.5	19.4	25.3	31.2	37.1	43.0	37.1	31.2	25.3
97.5°	59.4	78.8	98.2	106.1	102.4	98.7	95.0	91.3	95.0	98.7	102.4
100°	82.4	106.3	130.3	140.7	137.6	134.5	131.4	128.2	131.4	134.5	137.6
102.5°	172.0	175.1	178.3	178.7	176.4	174.1	171.8	169.5	171.8	174.1	176.4
105°	242.2	241.3	240.5	239.5	238.5	237.4	236.4	235.3	236.4	237.4	238.5
107.5°	301.8	300.6	299.4	298.6	298.1	297.5	297.0	296.5	297.0	297.5	298.1
110°	342.7	341.7	340.6	339.9	339.3	338.8	338.3	337.8	338.3	338.8	339.3





TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	383.2	382.8	382.3	381.6	380.6	379.7	378.7	377.8	378.7	379.7	380.6
115°	441.3	441.5	441.7	441.5	441.0	440.5	439.9	439.4	439.9	440.5	441.0
117.5°	499.0	498.6	498.3	497.7	497.0	496.3	495.6	494.9	495.6	496.3	497.0
120°	535.2	535.3	535.5	535.2	534.6	533.9	533.2	532.5	533.2	533.9	534.6
122.5°	570.0	569.7	569.5	569.2	568.7	568.3	567.9	567.5	567.9	568.3	568.7
125°	620.0	620.3	620.6	620.5	619.8	619.1	618.4	617.7	618.4	619.1	619.8
127.5°	668.0	667.2	666.4	665.9	665.8	665.6	665.4	665.2	665.4	665.6	665.8
130°	698.0	697.4	696.9	696.6	696.4	696.2	696.1	695.9	696.1	696.2	696.4
132.5°	727.1	726.4	725.8	725.3	725.0	724.7	724.3	724.0	724.3	724.7	725.0
135°	767.2	766.5	765.8	765.6	765.7	765.9	766.1	766.3	766.1	765.9	765.7
137.5°	805.9	805.1	804.3	803.9	803.8	803.8	803.7	803.6	803.7	803.8	803.8
140°	830.5	830.1	829.8	829.4	829.1	828.7	828.4	828.0	828.4	828.7	829.1
142.5°	853.3	853.0	852.8	852.4	851.8	851.2	850.5	849.9	850.5	851.2	851.8
145°	885.9	885.9	885.9	885.6	885.1	884.6	884.1	883.5	884.1	884.6	885.1
147.5°	914.2	914.4	914.6	914.2	913.2	912.2	911.3	910.3	911.3	912.2	913.2
150°	932.4	932.5	932.7	932.4	931.8	931.1	930.4	929.7	930.4	931.1	931.8
152.5°	947.7	948.0	948.3	948.2	947.6	947.0	946.5	945.9	946.5	947.0	947.6
155°	968.2	968.8	969.3	969.5	969.3	969.1	968.9	968.8	968.9	969.1	969.3
157.5°	986.1	986.6	987.2	987.6	987.7	987.8	987.9	988.0	987.9	987.8	987.7
160°	996.5	996.7	996.8	997.2	997.7	998.2	998.7	999.3	998.7	998.2	997.7
162.5°	1005.9	1006.0	1006.2	1006.6	1007.3	1007.9	1008.6	1009.3	1008.6	1007.9	1007.3
165°	1018.0	1018.0	1018.0	1018.5	1019.3	1020.2	1021.1	1021.9	1021.1	1020.2	1019.3
167.5°	1027.6	1027.7	1027.8	1028.3	1029.2	1030.1	1031.0	1031.9	1031.0	1030.1	1029.2
170°	1033.3	1033.1	1033.0	1033.4	1034.4	1035.5	1036.5	1037.6	1036.5	1035.5	1034.4
172.5°	1037.1	1036.9	1036.7	1037.2	1038.2	1039.2	1040.3	1041.3	1040.3	1039.2	1038.2
175°	1041.1	1041.0	1040.8	1041.2	1042.3	1043.3	1044.3	1045.4	1044.3	1043.3	1042.3
177.5°	1043.6	1043.3	1043.0	1043.4	1044.3	1045.3	1046.3	1047.3	1046.3	1045.3	1044.3
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1296.2	1291.9	1286.4	1280.0	1272.4	1265.6	1262.6	1265.1	1266.4	1263.0	1262.6
5°	1256.7	1243.4	1232.8	1216.8	1204.1	1193.4	1186.0	1182.8	1183.9	1175.4	1173.2
7.5°	1212.4	1196.6	1179.2	1160.3	1142.6	1127.0	1118.8	1114.3	1105.3	1101.4	1094.9
10°	1183.9	1162.6	1145.6	1123.2	1103.0	1084.4	1075.4	1067.9	1058.9	1054.6	1045.6
12.5°	1154.5	1129.8	1111.1	1087.9	1067.3	1044.8	1036.2	1022.4	1008.3	999.3	987.7
15°	1113.1	1083.4	1060.5	1032.8	1008.4	982.8	960.0	934.4	924.9	904.7	893.0
17.5°	1064.7	1034.5	1006.2	969.1	931.4	899.7	875.3	850.8	836.2	823.3	817.3
20°	1032.8	1005.2	965.8	922.7	880.7	845.6	825.9	810.0	794.0	785.0	778.6
22.5°	1002.6	967.3	921.6	875.1	833.1	805.6	788.9	772.5	759.6	751.0	742.4
25°	952.0	905.7	857.3	804.1	775.4	751.5	733.4	720.1	712.1	701.0	696.7
27.5°	900.0	843.9	790.5	754.8	724.9	703.0	687.2	677.2	667.1	660.0	654.5
30°	860.0	803.1	755.2	721.2	690.9	672.8	660.0	648.3	640.3	634.5	630.2
32.5°	820.4	763.5	723.3	686.7	662.8	645.1	631.5	622.8	616.5	609.0	606.4
35°	763.2	712.7	677.6	644.6	620.1	604.2	593.5	584.5	579.2	577.0	575.4
37.5°	708.2	666.8	629.1	602.0	580.2	567.7	555.1	550.7	547.0	543.2	544.9
40°	673.3	634.5	601.0	572.3	554.7	540.9	533.4	528.1	524.9	524.9	524.9
42.5°	643.1	605.1	572.5	546.7	529.2	517.5	509.2	504.7	503.6	503.2	505.8
45°	596.2	561.1	528.1	506.8	491.9	480.2	475.5	471.7	471.7	473.9	474.4
47.5°	549.7	516.8	490.4	466.5	452.9	445.6	441.4	439.5	439.7	441.9	444.3
50°	521.2	488.8	462.7	441.4	428.7	421.7	418.0	417.0	418.0	418.0	421.7
52.5°	490.1	461.1	435.5	417.6	403.1	396.6	394.6	393.1	393.8	395.5	397.1
55°	444.6	418.6	394.1	377.1	366.4	362.2	357.4	357.9	356.9	357.9	357.9
57.5°	399.0	375.6	352.8	339.3	330.0	323.8	318.6	320.1	318.5	318.3	317.4
60°	369.6	344.1	326.0	313.8	303.1	297.8	293.0	294.1	292.5	291.4	289.3
62.5°	337.7	316.4	299.2	287.4	278.9	272.7	267.9	266.9	263.2	259.5	254.9
65°	291.4	273.9	258.5	247.3	239.3	234.5	230.8	227.6	219.6	211.1	206.9
67.5°	246.5	233.8	219.4	210.0	203.5	197.2	190.1	184.7	177.2	172.5	169.9
70°	217.5	205.3	193.1	184.0	177.1	171.3	163.3	159.6	154.2	152.1	149.4
72.5°	189.9	178.5	167.1	158.9	151.6	147.0	140.7	137.0	134.7	133.8	131.2
75°	147.9	138.8	130.3	122.9	117.0	113.8	111.2	108.5	107.4	102.6	100.0
77.5°	107.9	101.9	96.6	91.3	87.1	85.0	79.9	76.8	75.0	72.8	72.2
80°	84.0	79.8	74.5	71.3	65.4	63.3	61.2	60.6	60.1	59.6	59.0
82.5°	63.2	58.9	53.6	51.7	50.1	48.8	47.5	47.0	46.5	46.8	46.7
85°	31.9	29.8	29.8	29.3	28.7	28.2	27.7	27.7	27.1	27.7	27.1
87.5°	12.6	12.5	12.8	12.2	12.9	13.2	13.0	13.2	13.9	13.2	13.3
90°	10.0	11.6	13.0	14.4	15.8	17.2	18.2	19.3	20.3	21.4	22.1
92.5°	10.3	11.0	12.4	13.8	15.2	16.6	17.6	18.7	19.7	20.7	21.3
95°	19.4	16.5	16.7	16.9	17.0	17.2	18.2	19.3	20.3	21.4	22.0
97.5°	106.1	98.2	78.8	59.4	40.0	20.6	20.7	20.9	21.0	21.1	21.2
100°	140.7	130.3	106.3	82.4	58.4	34.4	31.4	28.5	25.5	22.6	21.2
102.5°	178.7	178.3	175.1	172.0	168.9	165.8	133.9	102.0	70.2	38.3	22.4
105°	239.5	240.5	241.3	242.2	243.1	243.9	245.5	247.1	248.6	250.2	247.9
107.5°	298.6	299.4	300.6	301.8	303.0	304.2	304.9	305.7	306.4	307.2	307.9
110°	339.9	340.6	341.7	342.7	343.8	344.8	345.2	345.5	345.9	346.2	346.6



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	381.6	382.3	382.8	383.2	383.7	384.2	384.2	384.1	384.0	383.9	384.2
115°	441.5	441.7	441.5	441.3	441.2	441.0	441.3	441.7	442.0	442.4	442.6
117.5°	497.7	498.3	498.6	499.0	499.4	499.8	499.7	499.6	499.6	499.5	499.4
120°	535.2	535.5	535.3	535.2	535.0	534.8	535.2	535.5	535.9	536.2	536.2
122.5°	569.2	569.5	569.7	570.0	570.2	570.5	570.7	570.9	571.1	571.3	571.2
125°	620.5	620.6	620.3	620.0	619.6	619.3	619.8	620.3	620.8	621.3	621.7
127.5°	665.9	666.4	667.2	668.0	668.8	669.6	669.5	669.4	669.3	669.2	669.1
130°	696.6	696.9	697.4	698.0	698.5	699.0	699.2	699.4	699.5	699.7	699.8
132.5°	725.3	725.8	726.4	727.1	727.7	728.4	728.6	728.8	728.9	729.1	729.1
135°	765.6	765.8	766.5	767.2	767.9	768.6	768.9	769.3	769.6	770.0	770.3
137.5°	803.9	804.3	805.1	805.9	806.6	807.4	807.8	808.1	808.5	808.9	809.0
140°	829.4	829.8	830.1	830.5	830.8	831.1	831.7	832.2	832.7	833.2	833.6
142.5°	852.4	852.8	853.0	853.3	853.5	853.7	854.1	854.4	854.8	855.2	855.4
145°	885.6	885.9	885.9	885.9	885.9	885.9	886.1	886.2	886.4	886.6	886.8
147.5°	914.2	914.6	914.4	914.2	914.0	913.9	914.0	914.2	914.3	914.4	914.6
150°	932.4	932.7	932.5	932.4	932.2	932.0	932.0	932.0	932.0	932.0	932.1
152.5°	948.2	948.3	948.0	947.7	947.3	947.0	947.3	947.6	947.9	948.1	948.2
155°	969.5	969.3	968.8	968.2	967.7	967.2	967.9	968.6	969.3	970.0	970.1
157.5°	987.6	987.2	986.6	986.1	985.5	984.9	985.8	986.7	987.6	988.5	988.5
160°	997.2	996.8	996.7	996.5	996.3	996.1	997.2	998.2	999.3	1000.3	1000.3
162.5°	1006.6	1006.2	1006.0	1005.9	1005.7	1005.5	1006.6	1007.6	1008.6	1009.7	1009.6
165°	1018.5	1018.0	1018.0	1018.0	1018.0	1018.0	1019.4	1020.8	1022.2	1023.6	1023.5
167.5°	1028.3	1027.8	1027.7	1027.6	1027.5	1027.4	1028.9	1030.5	1032.0	1033.5	1033.4
170°	1033.4	1033.0	1033.1	1033.3	1033.5	1033.7	1035.0	1036.4	1037.8	1039.2	1039.0
172.5°	1037.2	1036.7	1036.9	1037.1	1037.2	1037.4	1038.8	1040.2	1041.6	1043.0	1042.7
175°	1041.2	1040.8	1041.0	1041.1	1041.3	1041.5	1043.0	1044.6	1046.2	1047.7	1047.5
177.5°	1043.4	1043.0	1043.3	1043.6	1043.9	1044.1	1045.2	1046.4	1047.5	1048.6	1048.3
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1260.0	1260.9	1257.9	1257.0	1257.9	1260.9	1260.0	1262.6	1263.0	1266.4	1265.1
5°	1169.0	1167.9	1165.3	1165.8	1165.3	1167.9	1169.0	1173.2	1175.4	1183.9	1182.8
7.5°	1091.1	1087.0	1088.1	1083.9	1088.1	1087.0	1091.1	1094.9	1101.4	1105.3	1114.3
10°	1043.5	1037.6	1032.8	1028.6	1032.8	1037.6	1043.5	1045.6	1054.6	1058.9	1067.9
12.5°	978.4	973.4	966.9	968.2	966.9	973.4	978.4	987.7	999.3	1008.3	1022.4
15°	886.0	878.1	865.3	866.9	865.3	878.1	886.0	893.0	904.7	924.9	934.4
17.5°	807.9	808.0	802.1	803.5	802.1	808.0	807.9	817.3	823.3	836.2	850.8
20°	767.4	763.7	764.2	762.7	764.2	763.7	767.4	778.6	785.0	794.0	810.0
22.5°	739.4	734.8	731.1	727.8	731.1	734.8	739.4	742.4	751.0	759.6	772.5
25°	691.9	688.7	683.9	682.9	683.9	688.7	691.9	696.7	701.0	712.1	720.1
27.5°	650.2	649.6	647.7	645.2	647.7	649.6	650.2	654.5	660.0	667.1	677.2
30°	626.0	624.9	623.8	622.2	623.8	624.9	626.0	630.2	634.5	640.3	648.3
32.5°	604.3	603.6	602.6	602.7	602.6	603.6	604.3	606.4	609.0	616.5	622.8
35°	573.3	572.8	571.7	571.2	571.7	572.8	573.3	575.4	577.0	579.2	584.5
37.5°	544.4	545.8	545.1	545.0	545.1	545.8	544.4	544.9	543.2	547.0	550.7
40°	524.4	524.9	526.0	525.5	526.0	524.9	524.4	524.9	524.9	524.9	528.1
42.5°	507.8	507.9	509.4	507.6	509.4	507.9	507.8	505.8	503.2	503.6	504.7
45°	478.1	481.3	480.8	480.8	480.8	481.3	478.1	474.4	473.9	471.7	471.7
47.5°	445.7	448.4	449.2	449.1	449.2	448.4	445.7	444.3	441.9	439.7	439.5
50°	424.4	423.3	424.9	424.4	424.9	423.3	424.4	421.7	418.0	418.0	417.0
52.5°	398.5	398.7	398.6	398.0	398.6	398.7	398.5	397.1	395.5	393.8	393.1
55°	358.5	359.0	357.9	358.5	357.9	359.0	358.5	357.9	357.9	356.9	357.9
57.5°	315.1	312.5	313.6	312.3	313.6	312.5	315.1	317.4	318.3	318.5	320.1
60°	284.0	279.7	278.7	276.6	278.7	279.7	284.0	289.3	291.4	292.5	294.1
62.5°	249.1	246.1	242.5	244.2	242.5	246.1	249.1	254.9	259.5	263.2	266.9
65°	202.6	200.5	198.9	201.0	198.9	200.5	202.6	206.9	211.1	219.6	227.6
67.5°	167.7	166.6	166.6	165.5	166.6	166.6	167.7	169.9	172.5	177.2	184.7
70°	149.4	147.9	147.9	146.8	147.9	147.9	149.4	149.4	152.1	154.2	159.6
72.5°	130.7	129.1	129.6	128.9	129.6	129.1	130.7	131.2	133.8	134.7	137.0
75°	96.8	94.1	94.1	94.7	94.1	94.1	96.8	100.0	102.6	107.4	108.5
77.5°	72.2	71.7	72.4	71.5	72.4	71.7	72.2	72.2	72.8	75.0	76.8
80°	59.0	58.5	58.0	59.6	58.0	58.5	59.0	59.0	59.6	60.1	60.6
82.5°	45.8	45.7	45.6	47.7	45.6	45.7	45.8	46.7	46.8	46.5	47.0
85°	27.7	26.6	27.7	26.6	27.7	26.6	27.7	27.1	27.7	27.1	27.7
87.5°	14.3	13.9	13.6	14.1	13.6	13.9	14.3	13.3	13.2	13.9	13.2
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.4	20.3	19.3
92.5°	21.4	21.4	21.5	21.6	21.5	21.4	21.4	21.3	20.7	19.7	18.7
95°	22.2	22.3	22.5	22.7	22.5	22.3	22.2	22.0	21.4	20.3	19.3
97.5°	21.4	21.5	21.7	21.9	21.7	21.5	21.4	21.2	21.1	21.0	20.9
100°	21.4	21.5	21.7	21.9	21.7	21.5	21.4	21.2	22.6	25.5	28.5
102.5°	22.4	22.4	22.5	22.5	22.5	22.4	22.4	22.4	38.3	70.2	102.0
105°	241.6	235.3	229.1	222.8	229.1	235.3	241.6	247.9	250.2	248.6	247.1
107.5°	308.6	309.2	309.9	310.6	309.9	309.2	308.6	307.9	307.2	306.4	305.7
110°	347.2	347.7	348.2	348.7	348.2	347.7	347.2	346.6	346.2	345.9	345.5



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	384.9	385.6	386.2	386.9	386.2	385.6	384.9	384.2	383.9	384.0	384.1
115°	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.4	442.0	441.7
117.5°	499.4	499.3	499.2	499.2	499.2	499.3	499.4	499.4	499.5	499.6	499.6
120°	535.9	535.5	535.2	534.8	535.2	535.5	535.9	536.2	536.2	535.9	535.5
122.5°	570.9	570.5	570.2	569.8	570.2	570.5	570.9	571.2	571.3	571.1	570.9
125°	621.9	622.0	622.2	622.4	622.2	622.0	621.9	621.7	621.3	620.8	620.3
127.5°	668.9	668.8	668.7	668.5	668.7	668.8	668.9	669.1	669.2	669.3	669.4
130°	699.8	699.8	699.8	699.8	699.8	699.8	699.8	699.8	699.7	699.5	699.4
132.5°	729.0	728.8	728.7	728.6	728.7	728.8	729.0	729.1	729.1	728.9	728.8
135°	770.7	771.0	771.4	771.7	771.4	771.0	770.7	770.3	770.0	769.6	769.3
137.5°	808.9	808.8	808.7	808.6	808.7	808.8	808.9	809.0	808.9	808.5	808.1
140°	833.8	833.9	834.1	834.3	834.1	833.9	833.8	833.6	833.2	832.7	832.2
142.5°	855.4	855.5	855.5	855.5	855.5	855.5	855.4	855.4	855.2	854.8	854.4
145°	887.2	887.5	887.9	888.2	887.9	887.5	887.2	886.8	886.6	886.4	886.2
147.5°	914.8	914.9	915.1	915.3	915.1	914.9	914.8	914.6	914.4	914.3	914.2
150°	932.3	932.4	932.6	932.8	932.6	932.4	932.3	932.1	932.0	932.0	932.0
152.5°	948.1	948.0	947.9	947.8	947.9	948.0	948.1	948.2	948.1	947.9	947.6
155°	969.5	969.0	968.5	968.0	968.5	969.0	969.5	970.1	970.0	969.3	968.6
157.5°	987.6	986.7	985.8	984.9	985.8	986.7	987.6	988.5	988.5	987.6	986.7
160°	999.3	998.2	997.2	996.1	997.2	998.2	999.3	1000.3	1000.3	999.3	998.2
162.5°	1008.4	1007.2	1006.1	1004.9	1006.1	1007.2	1008.4	1009.6	1009.7	1008.6	1007.6
165°	1021.9	1020.4	1018.8	1017.2	1018.8	1020.4	1021.9	1023.5	1023.6	1022.2	1020.8
167.5°	1031.7	1029.9	1028.2	1026.5	1028.2	1029.9	1031.7	1033.4	1033.5	1032.0	1030.5
170°	1037.3	1035.6	1033.8	1032.1	1033.8	1035.6	1037.3	1039.0	1039.2	1037.8	1036.4
172.5°	1040.9	1039.0	1037.1	1035.2	1037.1	1039.0	1040.9	1042.7	1043.0	1041.6	1040.2
175°	1045.4	1043.3	1041.2	1039.1	1041.2	1043.3	1045.4	1047.5	1047.7	1046.2	1044.6
177.5°	1046.6	1045.0	1043.3	1041.6	1043.3	1045.0	1046.6	1048.3	1048.6	1047.5	1046.4
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1262.6	1265.6	1272.4	1280.0	1286.4	1291.9	1296.2	1302.1	1307.7	1315.3	1322.6
5°	1186.0	1193.4	1204.1	1216.8	1232.8	1243.4	1256.7	1268.4	1285.4	1302.5	1319.0
7.5°	1118.8	1127.0	1142.6	1160.3	1179.2	1196.6	1212.4	1233.0	1255.6	1280.3	1308.0
10°	1075.4	1084.4	1103.0	1123.2	1145.6	1162.6	1183.9	1208.3	1233.9	1264.2	1298.2
12.5°	1036.2	1044.8	1067.3	1087.9	1111.1	1129.8	1154.5	1179.4	1213.4	1246.3	1285.0
15°	960.0	982.8	1008.4	1032.8	1060.5	1083.4	1113.1	1138.7	1171.1	1217.4	1261.5
17.5°	875.3	899.7	931.4	969.1	1006.2	1034.5	1064.7	1096.4	1135.0	1182.3	1233.2
20°	825.9	845.6	880.7	922.7	965.8	1005.2	1032.8	1067.9	1107.8	1158.9	1211.5
22.5°	788.9	805.6	833.1	875.1	921.6	967.3	1002.6	1037.3	1081.4	1132.5	1189.8
25°	733.4	751.5	775.4	804.1	857.3	905.7	952.0	991.9	1038.7	1089.7	1153.6
27.5°	687.2	703.0	724.9	754.8	790.5	843.9	900.0	945.5	993.5	1048.3	1112.2
30°	660.0	672.8	690.9	721.2	755.2	803.1	860.0	913.2	961.6	1018.5	1084.9
32.5°	631.5	645.1	662.8	686.7	723.3	763.5	820.4	878.7	930.1	988.3	1053.5
35°	593.5	604.2	620.1	644.6	677.6	712.7	763.2	823.3	877.5	939.8	1002.0
37.5°	555.1	567.7	580.2	602.0	629.1	666.8	708.2	769.6	829.7	886.5	947.2
40°	533.4	540.9	554.7	572.3	601.0	634.5	673.3	733.4	793.5	849.9	911.0
42.5°	509.2	517.5	529.2	546.7	572.5	605.1	643.1	695.1	757.8	812.4	868.1
45°	475.5	480.2	491.9	506.8	528.1	561.1	596.2	642.5	701.5	753.6	802.5
47.5°	441.4	445.6	452.9	466.5	490.4	516.8	549.7	591.2	643.0	695.1	736.5
50°	418.0	421.7	428.7	441.4	462.7	488.8	521.2	558.4	604.7	654.7	689.3
52.5°	394.6	396.6	403.1	417.6	435.5	461.1	490.1	524.4	567.7	609.2	644.2
55°	357.4	362.2	366.4	377.1	394.1	418.6	444.6	477.1	510.6	545.7	575.4
57.5°	318.6	323.8	330.0	339.3	352.8	375.6	399.0	425.3	453.9	483.0	508.0
60°	293.0	297.8	303.1	313.8	326.0	344.1	369.6	392.5	414.3	440.9	465.9
62.5°	267.9	272.7	278.9	287.4	299.2	316.4	337.7	357.6	380.3	403.5	422.1
65°	230.8	234.5	239.3	247.3	258.5	273.9	291.4	306.9	327.1	344.1	361.1
67.5°	190.1	197.2	203.5	210.0	219.4	233.8	246.5	261.2	275.0	287.6	303.1
70°	163.3	171.3	177.1	184.0	193.1	205.3	217.5	227.6	238.8	251.0	264.9
72.5°	140.7	147.0	151.6	158.9	167.1	178.5	189.9	198.3	207.3	215.7	229.1
75°	111.2	113.8	117.0	122.9	130.3	138.8	147.9	155.3	160.6	168.1	177.6
77.5°	79.9	85.0	87.1	91.3	96.6	101.9	107.9	114.1	119.2	121.9	129.2
80°	61.2	63.3	65.4	71.3	74.5	79.8	84.0	89.9	92.0	94.7	101.6
82.5°	47.5	48.8	50.1	51.7	53.6	58.9	63.2	66.9	69.0	70.0	75.2
85°	27.7	28.2	28.7	29.3	29.8	29.8	31.9	34.6	38.3	38.3	39.9
87.5°	13.0	13.2	12.9	12.2	12.8	12.5	12.6	12.3	13.1	14.0	14.9
90°	18.2	17.2	15.8	14.4	13.0	11.6	10.0	8.1	6.2	4.3	2.3
92.5°	17.6	16.6	15.2	13.8	12.4	11.0	10.3	10.2	10.1	10.0	9.9
95°	18.2	17.2	17.0	16.9	16.7	16.5	19.4	25.3	31.2	37.1	43.0
97.5°	20.7	20.6	40.0	59.4	78.8	98.2	106.1	102.4	98.7	95.0	91.3
100°	31.4	34.4	58.4	82.4	106.3	130.3	140.7	137.6	134.5	131.4	128.2
102.5°	133.9	165.8	168.9	172.0	175.1	178.3	178.7	176.4	174.1	171.8	169.5
105°	245.5	243.9	243.1	242.2	241.3	240.5	239.5	238.5	237.4	236.4	235.3
107.5°	304.9	304.2	303.0	301.8	300.6	299.4	298.6	298.1	297.5	297.0	296.5
110°	345.2	344.8	343.8	342.7	341.7	340.6	339.9	339.3	338.8	338.3	337.8



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	384.2	384.2	383.7	383.2	382.8	382.3	381.6	380.6	379.7	378.7	377.8
115°	441.3	441.0	441.2	441.3	441.5	441.7	441.5	441.0	440.5	439.9	439.4
117.5°	499.7	499.8	499.4	499.0	498.6	498.3	497.7	497.0	496.3	495.6	494.9
120°	535.2	534.8	535.0	535.2	535.3	535.5	535.2	534.6	533.9	533.2	532.5
122.5°	570.7	570.5	570.2	570.0	569.7	569.5	569.2	568.7	568.3	567.9	567.5
125°	619.8	619.3	619.6	620.0	620.3	620.6	620.5	619.8	619.1	618.4	617.7
127.5°	669.5	669.6	668.8	668.0	667.2	666.4	665.9	665.8	665.6	665.4	665.2
130°	699.2	699.0	698.5	698.0	697.4	696.9	696.6	696.4	696.2	696.1	695.9
132.5°	728.6	728.4	727.7	727.1	726.4	725.8	725.3	725.0	724.7	724.3	724.0
135°	768.9	768.6	767.9	767.2	766.5	765.8	765.6	765.7	765.9	766.1	766.3
137.5°	807.8	807.4	806.6	805.9	805.1	804.3	803.9	803.8	803.8	803.7	803.6
140°	831.7	831.1	830.8	830.5	830.1	829.8	829.4	829.1	828.7	828.4	828.0
142.5°	854.1	853.7	853.5	853.3	853.0	852.8	852.4	851.8	851.2	850.5	849.9
145°	886.1	885.9	885.9	885.9	885.9	885.9	885.6	885.1	884.6	884.1	883.5
147.5°	914.0	913.9	914.0	914.2	914.4	914.6	914.2	913.2	912.2	911.3	910.3
150°	932.0	932.0	932.2	932.4	932.5	932.7	932.4	931.8	931.1	930.4	929.7
152.5°	947.3	947.0	947.3	947.7	948.0	948.3	948.2	947.6	947.0	946.5	945.9
155°	967.9	967.2	967.7	968.2	968.8	969.3	969.5	969.3	969.1	968.9	968.8
157.5°	985.8	984.9	985.5	986.1	986.6	987.2	987.6	987.7	987.8	987.9	988.0
160°	997.2	996.1	996.3	996.5	996.7	996.8	997.2	997.7	998.2	998.7	999.3
162.5°	1006.6	1005.5	1005.7	1005.9	1006.0	1006.2	1006.6	1007.3	1007.9	1008.6	1009.3
165°	1019.4	1018.0	1018.0	1018.0	1018.0	1018.0	1018.5	1019.3	1020.2	1021.1	1021.9
167.5°	1028.9	1027.4	1027.5	1027.6	1027.7	1027.8	1028.3	1029.2	1030.1	1031.0	1031.9
170°	1035.0	1033.7	1033.5	1033.3	1033.1	1033.0	1033.4	1034.4	1035.5	1036.5	1037.6
172.5°	1038.8	1037.4	1037.2	1037.1	1036.9	1036.7	1037.2	1038.2	1039.2	1040.3	1041.3
175°	1043.0	1041.5	1041.3	1041.1	1041.0	1040.8	1041.2	1042.3	1043.3	1044.3	1045.4
177.5°	1045.2	1044.1	1043.9	1043.6	1043.3	1043.0	1043.4	1044.3	1045.3	1046.3	1047.3
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1328.1	1331.9	1336.2	1344.3	1351.1	1354.1	1360.0	1364.3	1363.0	1368.9	1379.2
5°	1333.3	1347.7	1364.2	1381.2	1400.3	1416.3	1429.0	1441.8	1451.9	1464.1	1482.2
7.5°	1332.5	1358.0	1385.8	1416.3	1447.7	1474.8	1499.9	1525.4	1548.1	1572.9	1605.3
10°	1329.1	1363.1	1397.7	1437.6	1477.4	1515.2	1549.2	1581.2	1611.5	1643.9	1684.9
12.5°	1325.2	1364.4	1406.2	1454.1	1503.8	1549.2	1589.2	1635.2	1673.2	1715.0	1762.3
15°	1308.3	1361.0	1417.9	1480.1	1539.7	1600.8	1655.6	1712.0	1764.6	1814.6	1874.2
17.5°	1289.0	1349.7	1416.8	1490.3	1561.9	1636.2	1701.2	1772.3	1826.1	1893.2	1948.5
20°	1273.2	1338.6	1410.4	1492.9	1574.2	1656.7	1728.5	1800.8	1861.4	1929.0	1999.2
22.5°	1254.1	1325.9	1403.6	1489.0	1574.2	1664.3	1743.8	1815.7	1890.8	1966.8	2039.2
25°	1223.2	1297.7	1380.1	1473.7	1571.6	1663.6	1748.7	1838.0	1918.9	2001.3	2066.2
27.5°	1185.4	1263.5	1350.4	1447.0	1547.4	1641.7	1741.9	1837.1	1918.4	1997.8	2054.4
30°	1155.1	1237.6	1321.1	1418.9	1523.2	1624.2	1731.7	1826.9	1912.5	1983.8	2015.7
32.5°	1124.1	1202.3	1288.3	1387.5	1494.2	1603.0	1709.5	1806.9	1886.1	1928.9	1929.7
35°	1070.1	1143.4	1232.8	1330.1	1439.7	1557.8	1665.7	1761.4	1809.8	1813.6	1761.4
37.5°	1011.1	1078.5	1162.8	1260.2	1380.2	1497.7	1608.0	1671.8	1687.9	1633.8	1537.4
40°	969.0	1031.2	1112.6	1212.6	1331.7	1453.0	1553.5	1600.3	1583.3	1495.5	1388.1
42.5°	924.8	982.7	1061.1	1159.8	1279.4	1401.9	1487.5	1512.7	1467.6	1366.2	1240.5
45°	852.5	905.7	983.4	1082.8	1197.7	1312.6	1377.5	1364.7	1289.7	1169.5	1028.6
47.5°	777.3	828.7	898.6	990.6	1108.2	1207.4	1251.3	1212.8	1106.1	973.9	859.2
50°	727.6	780.2	844.6	932.3	1039.7	1135.5	1163.7	1105.2	986.6	859.4	754.1
52.5°	678.6	723.6	786.7	871.5	974.2	1055.1	1070.1	1002.6	880.2	766.3	672.9
55°	604.2	645.1	698.3	778.1	866.9	935.5	927.5	840.8	729.7	632.4	559.0
57.5°	532.2	563.0	612.1	686.9	764.9	810.9	781.8	707.9	604.3	524.6	462.7
60°	484.5	513.2	559.0	624.4	693.0	719.0	694.6	614.3	532.4	459.5	407.4
62.5°	439.4	464.7	504.1	564.8	620.2	635.7	609.5	539.4	465.6	403.3	360.2
65°	373.9	397.3	430.8	473.9	512.2	519.6	502.6	430.8	374.9	322.8	293.0
67.5°	314.4	329.7	355.9	393.1	413.5	417.8	384.9	339.8	290.6	258.6	236.1
70°	274.4	285.1	309.5	329.7	346.2	346.8	316.4	280.3	242.5	216.5	200.0
72.5°	235.7	245.9	264.4	278.3	290.9	286.8	259.0	230.5	200.0	180.3	168.1
75°	181.9	190.9	200.5	206.9	206.9	201.6	181.4	160.1	142.5	130.8	127.1
77.5°	132.2	139.7	142.9	141.9	140.0	131.7	118.9	105.0	98.7	93.2	90.4
80°	103.7	106.9	108.0	105.3	102.1	92.5	84.0	78.2	72.3	70.2	69.1
82.5°	76.9	79.7	76.9	77.6	70.6	62.8	58.1	56.1	53.6	52.8	51.7
85°	41.0	40.4	39.4	36.7	31.9	30.8	30.3	29.8	28.7	29.3	28.2
87.5°	14.9	14.0	12.7	12.6	13.0	12.4	13.1	13.4	13.7	13.4	14.5
90°	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2	19.3
92.5°	10.0	10.1	10.2	10.3	11.0	12.4	13.8	15.2	16.6	17.6	18.7
95°	37.1	31.2	25.3	19.4	16.5	16.7	16.9	17.0	17.2	18.2	19.3
97.5°	95.0	98.7	102.4	106.1	98.2	78.8	59.4	40.0	20.6	20.7	20.9
100°	131.4	134.5	137.6	140.7	130.3	106.3	82.4	58.4	34.4	31.4	28.5
102.5°	171.8	174.1	176.4	178.7	178.3	175.1	172.0	168.9	165.8	133.9	102.0
105°	236.4	237.4	238.5	239.5	240.5	241.3	242.2	243.1	243.9	245.5	247.1
107.5°	297.0	297.5	298.1	298.6	299.4	300.6	301.8	303.0	304.2	304.9	305.7
110°	338.3	338.8	339.3	339.9	340.6	341.7	342.7	343.8	344.8	345.2	345.5





TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	378.7	379.7	380.6	381.6	382.3	382.8	383.2	383.7	384.2	384.2	384.1
115°	439.9	440.5	441.0	441.5	441.7	441.5	441.3	441.2	441.0	441.3	441.7
117.5°	495.6	496.3	497.0	497.7	498.3	498.6	499.0	499.4	499.8	499.7	499.6
120°	533.2	533.9	534.6	535.2	535.5	535.3	535.2	535.0	534.8	535.2	535.5
122.5°	567.9	568.3	568.7	569.2	569.5	569.7	570.0	570.2	570.5	570.7	570.9
125°	618.4	619.1	619.8	620.5	620.6	620.3	620.0	619.6	619.3	619.8	620.3
127.5°	665.4	665.6	665.8	665.9	666.4	667.2	668.0	668.8	669.6	669.5	669.4
130°	696.1	696.2	696.4	696.6	696.9	697.4	698.0	698.5	699.0	699.2	699.4
132.5°	724.3	724.7	725.0	725.3	725.8	726.4	727.1	727.7	728.4	728.6	728.8
135°	766.1	765.9	765.7	765.6	765.8	766.5	767.2	767.9	768.6	768.9	769.3
137.5°	803.7	803.8	803.8	803.9	804.3	805.1	805.9	806.6	807.4	807.8	808.1
140°	828.4	828.7	829.1	829.4	829.8	830.1	830.5	830.8	831.1	831.7	832.2
142.5°	850.5	851.2	851.8	852.4	852.8	853.0	853.3	853.5	853.7	854.1	854.4
145°	884.1	884.6	885.1	885.6	885.9	885.9	885.9	885.9	885.9	886.1	886.2
147.5°	911.3	912.2	913.2	914.2	914.6	914.4	914.2	914.0	913.9	914.0	914.2
150°	930.4	931.1	931.8	932.4	932.7	932.5	932.4	932.2	932.0	932.0	932.0
152.5°	946.5	947.0	947.6	948.2	948.3	948.0	947.7	947.3	947.0	947.3	947.6
155°	968.9	969.1	969.3	969.5	969.3	968.8	968.2	967.7	967.2	967.9	968.6
157.5°	987.9	987.8	987.7	987.6	987.2	986.6	986.1	985.5	984.9	985.8	986.7
160°	998.7	998.2	997.7	997.2	996.8	996.7	996.5	996.3	996.1	997.2	998.2
162.5°	1008.6	1007.9	1007.3	1006.6	1006.2	1006.0	1005.9	1005.7	1005.5	1006.6	1007.6
165°	1021.1	1020.2	1019.3	1018.5	1018.0	1018.0	1018.0	1018.0	1018.0	1019.4	1020.8
167.5°	1031.0	1030.1	1029.2	1028.3	1027.8	1027.7	1027.6	1027.5	1027.4	1028.9	1030.5
170°	1036.5	1035.5	1034.4	1033.4	1033.0	1033.1	1033.3	1033.5	1033.7	1035.0	1036.4
172.5°	1040.3	1039.2	1038.2	1037.2	1036.7	1036.9	1037.1	1037.2	1037.4	1038.8	1040.2
175°	1044.3	1043.3	1042.3	1041.2	1040.8	1041.0	1041.1	1041.3	1041.5	1043.0	1044.6
177.5°	1046.3	1045.3	1044.3	1043.4	1043.0	1043.3	1043.6	1043.9	1044.1	1045.2	1046.4
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1384.7	1386.4	1387.7	1391.9	1392.3	1396.2	1392.3
5°	1499.2	1506.7	1518.4	1530.1	1531.2	1538.6	1525.3
7.5°	1627.7	1645.0	1655.7	1674.6	1682.1	1686.8	1679.1
10°	1716.2	1732.2	1760.4	1774.2	1788.0	1790.2	1783.8
12.5°	1801.8	1827.1	1849.3	1875.5	1874.8	1893.6	1886.7
15°	1915.7	1941.7	1972.6	2001.8	2012.5	2012.5	2021.0
17.5°	1996.9	2044.7	2076.6	2099.6	2124.7	2129.0	2126.1
20°	2051.8	2103.4	2137.5	2167.2	2184.3	2189.0	2189.0
22.5°	2092.7	2136.6	2169.8	2196.6	2210.6	2216.3	2214.6
25°	2121.0	2158.7	2178.9	2186.9	2190.6	2189.6	2179.5
27.5°	2082.2	2080.5	2067.8	2043.3	2024.9	2013.7	2001.0
30°	2008.2	1980.6	1948.7	1913.5	1868.3	1833.8	1823.1
32.5°	1898.0	1835.9	1781.9	1723.4	1674.8	1640.2	1625.7
35°	1684.9	1586.5	1506.2	1436.0	1384.9	1353.0	1342.4
37.5°	1431.9	1336.7	1237.3	1169.2	1126.9	1094.6	1082.6
40°	1271.1	1167.4	1080.7	1016.9	973.3	941.9	941.4
42.5°	1124.3	1025.3	943.7	897.7	850.7	830.0	829.9
45°	920.6	841.4	772.2	736.1	707.9	690.9	686.1
47.5°	762.2	696.7	650.6	621.8	598.8	588.0	581.0
50°	673.3	615.9	579.2	554.2	541.4	527.6	526.5
52.5°	599.3	552.9	524.3	504.0	487.8	479.5	479.7
55°	503.6	467.0	446.7	431.3	418.6	412.2	409.5
57.5°	424.3	396.8	382.1	367.9	362.5	357.5	356.1
60°	374.9	356.3	342.5	331.3	323.4	321.8	321.2
62.5°	334.1	314.6	305.1	296.4	290.6	288.1	287.2
65°	275.5	261.1	252.6	245.7	243.6	239.9	239.3
67.5°	222.1	213.5	207.8	203.1	200.2	200.0	200.0
70°	189.3	184.5	179.8	177.1	175.5	174.4	174.4
72.5°	161.3	157.7	153.8	152.4	152.1	151.0	150.6
75°	122.9	119.1	119.7	117.0	114.9	112.2	110.6
77.5°	87.1	84.5	83.9	83.6	81.8	81.5	82.3
80°	67.5	64.9	64.4	64.9	64.4	62.8	62.8
82.5°	51.4	49.1	48.6	48.3	47.8	48.3	47.4
85°	27.7	26.6	26.6	26.6	27.7	27.1	26.6
87.5°	13.9	13.6	14.2	13.8	13.9	13.6	14.1
90°	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	19.7	20.7	21.3	21.4	21.4	21.5	21.6
95°	20.3	21.4	22.0	22.2	22.3	22.5	22.7
97.5°	21.0	21.1	21.2	21.4	21.5	21.7	21.9
100°	25.5	22.6	21.2	21.4	21.5	21.7	21.9
102.5°	70.2	38.3	22.4	22.4	22.4	22.5	22.5
105°	248.6	250.2	247.9	241.6	235.3	229.1	222.8
107.5°	306.4	307.2	307.9	308.6	309.2	309.9	310.6
110°	345.9	346.2	346.6	347.2	347.7	348.2	348.7



TEST NUMBER: P332937

CATALOG NUMBER: SA4XXRDIP-C795D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	384.0	383.9	384.2	384.9	385.6	386.2	386.9
115°	442.0	442.4	442.6	442.6	442.6	442.6	442.6
117.5°	499.6	499.5	499.4	499.4	499.3	499.2	499.2
120°	535.9	536.2	536.2	535.9	535.5	535.2	534.8
122.5°	571.1	571.3	571.2	570.9	570.5	570.2	569.8
125°	620.8	621.3	621.7	621.9	622.0	622.2	622.4
127.5°	669.3	669.2	669.1	668.9	668.8	668.7	668.5
130°	699.5	699.7	699.8	699.8	699.8	699.8	699.8
132.5°	728.9	729.1	729.1	729.0	728.8	728.7	728.6
135°	769.6	770.0	770.3	770.7	771.0	771.4	771.7
137.5°	808.5	808.9	809.0	808.9	808.8	808.7	808.6
140°	832.7	833.2	833.6	833.8	833.9	834.1	834.3
142.5°	854.8	855.2	855.4	855.4	855.5	855.5	855.5
145°	886.4	886.6	886.8	887.2	887.5	887.9	888.2
147.5°	914.3	914.4	914.6	914.8	914.9	915.1	915.3
150°	932.0	932.0	932.1	932.3	932.4	932.6	932.8
152.5°	947.9	948.1	948.2	948.1	948.0	947.9	947.8
155°	969.3	970.0	970.1	969.5	969.0	968.5	968.0
157.5°	987.6	988.5	988.5	987.6	986.7	985.8	984.9
160°	999.3	1000.3	1000.3	999.3	998.2	997.2	996.1
162.5°	1008.6	1009.7	1009.6	1008.4	1007.2	1006.1	1004.9
165°	1022.2	1023.6	1023.5	1021.9	1020.4	1018.8	1017.2
167.5°	1032.0	1033.5	1033.4	1031.7	1029.9	1028.2	1026.5
170°	1037.8	1039.2	1039.0	1037.3	1035.6	1033.8	1032.1
172.5°	1041.6	1043.0	1042.7	1040.9	1039.0	1037.1	1035.2
175°	1046.2	1047.7	1047.5	1045.4	1043.3	1041.2	1039.1
177.5°	1047.5	1048.6	1048.3	1046.6	1045.0	1043.3	1041.6
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4

(END OF REPORT)