

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332661-935

Luminaire Tested: **SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332661-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8105.7 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332661-935
CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	42	40	35
3	81	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	53	47	51	45	41	42	38	35	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	28	34	28	24	29	25	21	24	21	18	16
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11599	11599	11599	11599
5°	13661	11629	10264	11629
10°	16356	11579	9241	11579
15°	19351	11462	8487	11462
20°	21549	11342	7814	11342
25°	21896	11166	7349	11166
30°	18632	10997	7202	10997
35°	14325	10723	7203	10723
40°	11166	10400	7339	10400
45°	9310	9914	7462	9914
50°	8194	9323	7714	9323
55°	7506	8612	8025	8612
60°	7035	7976	8399	7976
65°	6550	7265	8709	7265
70°	5986	6559	8908	6559
75°	5346	5774	8799	5774
80°	4482	4733	8522	4733
85°	3307	3418	8160	3418



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	1.7
10°-20°	431.5	5.3
20°-30°	684.2	8.4
30°-40°	761.4	9.4
40°-50°	693.1	8.6
50°-60°	566.4	7.0
60°-70°	404.3	5.0
70°-80°	222.6	2.7
80°-90°	64.7	0.8
90°-100°	45.8	0.6
100°-110°	291.7	3.6
110°-120°	558.0	6.9
120°-130°	708.4	8.7
130°-140°	757.9	9.3
140°-150°	708.7	8.7
150°-160°	571.5	7.1
160°-170°	368.6	4.5
170°-180°	127.0	1.6
0°-30°	1255.6	15.5
0°-40°	2017.1	24.9
0°-60°	3276.5	40.4
0°-90°	3968.2	49.0
90°-120°	895.4	11.0
90°-150°	3070.4	37.9
90°-180°	4138.0	51.1
0°-180°	8105.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1437	1437	1437	1437	1437	
5°	1686	1435	1267	1435	1686	171
15°	2315	1371	1016	1371	2315	654
25°	2458	1254	825	1254	2458	1084
35°	1454	1088	731	1088	1454	923
45°	816	868	654	868	816	642
55°	533	612	570	612	533	482
65°	343	380	456	380	343	339
75°	171	185	282	185	171	182
85°	36	37	88	37	36	44
90°	30	3	30	3	30	14
95°	29	55	29	55	29	23
105°	285	301	285	301	285	249
115°	566	562	566	562	566	561
125°	796	790	796	790	796	709
135°	987	980	987	980	987	760
145°	1136	1130	1136	1130	1136	710
155°	1238	1240	1238	1240	1238	571
165°	1302	1308	1302	1308	1302	368
175°	1330	1338	1330	1338	1330	127
180°	1338	1338	1338	1338	1338	



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1529.2	1528.8	1524.0	1523.0	1519.7	1515.4	1514.5	1506.8	1491.6	1484.5	1482.6
5°	1685.7	1697.5	1682.0	1679.1	1677.3	1657.7	1647.5	1635.6	1608.3	1592.2	1579.7
7.5°	1872.3	1873.7	1867.0	1861.5	1846.3	1829.2	1803.5	1776.2	1743.5	1709.6	1683.9
10°	1995.2	1999.9	1992.2	1991.0	1960.7	1941.6	1903.5	1871.4	1834.4	1793.4	1755.9
12.5°	2124.7	2118.0	2114.1	2088.6	2083.0	2048.2	2004.0	1970.9	1914.0	1866.7	1816.8
15°	2315.4	2302.3	2294.0	2258.8	2241.6	2193.4	2146.3	2110.1	2035.7	1964.8	1911.2
17.5°	2427.2	2440.4	2421.1	2406.7	2362.1	2328.2	2280.2	2204.0	2145.8	2057.8	1990.2
20°	2508.3	2509.4	2498.7	2483.8	2448.7	2405.9	2353.5	2270.1	2200.5	2113.0	2020.2
22.5°	2530.1	2530.4	2525.8	2511.9	2485.4	2450.6	2397.8	2328.2	2243.9	2148.7	2055.9
25°	2458.2	2455.8	2461.3	2476.7	2466.6	2455.8	2425.5	2373.7	2295.2	2194.5	2094.6
27.5°	2191.1	2207.5	2237.7	2275.9	2312.6	2340.5	2348.4	2337.8	2289.1	2206.3	2101.6
30°	1998.7	2019.0	2041.6	2079.7	2153.4	2195.7	2242.2	2277.3	2257.6	2191.6	2094.0
32.5°	1787.3	1792.3	1825.9	1869.2	1936.8	2018.1	2091.7	2163.0	2186.7	2152.1	2070.6
35°	1453.5	1461.8	1498.1	1541.0	1623.8	1723.1	1833.8	1932.7	2014.2	2046.9	2005.3
37.5°	1186.1	1210.0	1235.7	1281.8	1354.6	1444.1	1559.1	1687.0	1808.5	1889.9	1903.8
40°	1059.5	1074.4	1092.8	1127.9	1189.8	1277.9	1376.7	1523.2	1652.3	1769.0	1807.1
42.5°	959.5	968.2	979.5	1011.2	1058.4	1146.0	1236.2	1365.0	1494.7	1634.2	1698.1
45°	815.5	824.4	843.4	861.9	897.6	958.3	1042.2	1148.1	1278.5	1413.1	1530.9
47.5°	711.4	717.1	728.4	748.2	778.5	818.6	886.8	975.3	1096.1	1226.8	1352.3
50°	652.4	657.1	666.1	683.9	707.1	742.8	798.7	881.5	976.1	1107.7	1230.9
52.5°	605.7	607.6	614.2	626.3	644.7	674.8	720.7	789.1	877.1	994.4	1117.1
55°	533.3	535.7	541.7	550.6	566.6	585.7	620.8	672.0	748.8	850.6	957.1
57.5°	473.8	475.4	480.4	483.9	497.1	512.6	539.6	576.2	634.4	720.7	815.8
60°	435.7	434.5	440.5	443.4	452.4	465.5	486.3	521.4	572.0	641.6	729.1
62.5°	398.6	396.9	401.9	405.8	411.0	422.1	439.1	466.7	507.7	570.7	646.3
65°	342.9	340.4	343.5	348.2	352.9	359.0	371.4	395.8	428.5	473.8	531.5
67.5°	286.9	289.4	289.9	292.2	295.0	303.1	311.7	328.9	352.0	388.2	437.1
70°	253.6	254.2	256.6	256.6	258.3	265.4	272.6	282.8	305.3	338.7	378.6
72.5°	220.2	222.7	221.8	223.7	225.0	229.7	235.0	244.6	263.9	288.7	322.4
75°	171.4	173.2	173.2	173.8	175.6	177.4	181.5	188.6	202.3	220.8	244.0
77.5°	125.0	125.3	126.1	128.2	128.2	131.0	134.1	139.9	146.6	159.3	173.4
80°	96.4	97.6	97.0	98.2	98.2	100.6	101.8	108.9	111.9	120.2	131.6
82.5°	70.7	71.9	71.8	73.4	74.4	74.9	76.5	79.4	82.4	89.7	94.4
85°	35.7	36.9	35.7	36.9	38.7	39.3	41.1	41.7	44.1	45.8	50.0
87.5°	16.4	17.8	17.7	18.1	18.9	19.3	19.5	18.8	20.4	20.6	22.1
90°	30.0	29.5	29.1	28.7	28.2	27.4	26.0	24.7	23.3	22.0	20.2
92.5°	27.6	27.6	27.5	27.4	27.3	26.5	25.2	23.8	22.6	21.2	19.5
95°	29.0	28.8	28.6	28.3	28.2	27.4	26.0	24.7	23.3	22.0	21.8
97.5°	28.0	27.8	27.6	27.4	27.1	26.9	26.8	26.7	26.5	26.4	51.2
100°	28.0	27.8	27.6	27.4	27.1	28.9	32.7	36.4	40.2	44.0	74.7
102.5°	28.8	28.8	28.8	28.7	28.7	49.0	89.8	130.5	171.3	212.1	216.1
105°	285.2	293.2	301.1	309.1	317.1	320.1	318.1	316.2	314.2	312.1	311.0
107.5°	397.4	396.5	395.7	394.9	394.0	393.0	392.1	391.2	390.1	389.2	387.6
110°	446.2	445.6	444.9	444.2	443.5	443.0	442.6	442.1	441.6	441.2	439.9



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	495.0	494.2	493.4	492.5	491.6	491.3	491.4	491.5	491.5	491.6	491.0
115°	566.3	566.3	566.3	566.3	566.3	566.0	565.6	565.2	564.7	564.2	564.5
117.5°	638.7	638.8	638.9	638.9	639.0	639.1	639.2	639.3	639.4	639.5	639.0
120°	684.3	684.8	685.2	685.6	686.0	686.0	685.6	685.2	684.8	684.3	684.5
122.5°	729.1	729.5	730.0	730.5	730.9	731.0	730.7	730.5	730.2	730.0	729.6
125°	796.3	796.2	795.9	795.7	795.5	795.0	794.4	793.7	793.0	792.4	792.8
127.5°	855.4	855.6	855.7	855.9	856.1	856.3	856.4	856.5	856.6	856.8	855.7
130°	895.4	895.4	895.4	895.4	895.4	895.3	895.1	894.8	894.6	894.4	893.7
132.5°	932.2	932.4	932.5	932.7	932.9	932.9	932.7	932.5	932.2	932.0	931.2
135°	987.4	987.0	986.5	986.1	985.7	985.2	984.7	984.3	983.9	983.4	982.6
137.5°	1034.7	1034.7	1034.9	1035.1	1035.2	1035.0	1034.5	1034.1	1033.5	1033.0	1032.1
140°	1067.5	1067.2	1067.0	1066.8	1066.6	1066.2	1065.5	1064.8	1064.1	1063.5	1063.0
142.5°	1094.7	1094.7	1094.6	1094.6	1094.5	1094.2	1093.7	1093.3	1092.8	1092.3	1092.0
145°	1136.5	1136.1	1135.6	1135.1	1134.7	1134.4	1134.2	1133.9	1133.8	1133.5	1133.5
147.5°	1171.1	1170.9	1170.7	1170.4	1170.2	1170.0	1169.8	1169.7	1169.5	1169.3	1169.5
150°	1193.5	1193.3	1193.1	1192.8	1192.7	1192.5	1192.5	1192.5	1192.5	1192.5	1192.7
152.5°	1212.7	1212.9	1213.0	1213.1	1213.2	1213.1	1212.8	1212.5	1212.1	1211.8	1212.1
155°	1238.5	1239.2	1239.8	1240.5	1241.2	1241.1	1240.2	1239.3	1238.5	1237.5	1238.2
157.5°	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2	1260.9
160°	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5	1274.8
162.5°	1285.7	1287.3	1288.8	1290.3	1291.8	1291.9	1290.6	1289.3	1287.9	1286.6	1286.8
165°	1301.6	1303.6	1305.5	1307.6	1309.6	1309.7	1307.9	1306.1	1304.3	1302.6	1302.6
167.5°	1313.4	1315.6	1317.8	1320.1	1322.2	1322.4	1320.4	1318.5	1316.6	1314.6	1314.7
170°	1320.6	1322.8	1325.0	1327.2	1329.5	1329.7	1327.9	1326.1	1324.4	1322.6	1322.3
172.5°	1324.6	1327.0	1329.4	1331.8	1334.2	1334.5	1332.7	1330.9	1329.1	1327.4	1327.1
175°	1329.6	1332.2	1334.9	1337.6	1340.2	1340.6	1338.6	1336.6	1334.6	1332.6	1332.4
177.5°	1332.8	1334.9	1337.0	1339.2	1341.4	1341.7	1340.2	1338.9	1337.4	1336.0	1335.7
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1483.1	1476.4	1471.6	1467.8	1457.3	1451.1	1446.4	1439.7	1432.1	1424.0	1414.0
5°	1567.2	1547.0	1532.1	1509.5	1488.1	1470.2	1451.7	1435.0	1414.8	1392.8	1376.7
7.5°	1655.6	1625.6	1587.0	1553.5	1515.9	1483.2	1453.9	1423.8	1392.7	1362.4	1334.7
10°	1711.8	1673.2	1630.3	1579.7	1532.1	1489.8	1450.5	1412.5	1375.5	1338.6	1307.1
12.5°	1772.3	1724.1	1660.8	1601.6	1548.3	1491.8	1444.3	1397.7	1353.1	1314.3	1277.6
15°	1853.5	1783.8	1710.6	1631.5	1561.3	1495.2	1430.3	1371.4	1321.4	1270.1	1234.5
17.5°	1903.4	1817.2	1733.5	1650.8	1565.7	1482.5	1412.5	1344.5	1281.9	1231.1	1186.0
20°	1936.2	1850.5	1746.4	1663.6	1562.5	1476.7	1395.8	1320.2	1254.7	1200.6	1154.1
22.5°	1964.8	1865.8	1761.6	1652.7	1552.0	1461.0	1372.4	1296.4	1229.5	1172.4	1127.9
25°	1980.3	1866.6	1753.5	1645.2	1530.9	1423.1	1342.8	1253.5	1182.1	1122.0	1074.4
27.5°	1981.9	1860.4	1732.4	1612.1	1494.1	1393.8	1292.4	1212.5	1138.4	1074.9	1029.2
30°	1976.7	1849.9	1712.4	1582.1	1463.6	1354.7	1266.6	1179.7	1104.1	1041.0	993.4
32.5°	1960.1	1828.0	1686.7	1548.8	1426.0	1319.5	1228.6	1145.9	1072.2	1010.0	960.1
35°	1911.9	1781.5	1630.9	1487.5	1361.8	1254.1	1172.0	1088.0	1014.3	955.3	907.1
37.5°	1836.5	1718.6	1565.6	1417.1	1293.7	1185.5	1104.1	1028.3	961.7	901.9	852.5
40°	1770.7	1667.2	1513.6	1369.0	1235.7	1132.7	1056.5	986.9	920.8	864.3	817.3
42.5°	1695.1	1604.8	1463.2	1309.9	1181.4	1078.0	1003.7	941.2	878.9	826.6	779.6
45°	1560.0	1500.6	1367.2	1225.5	1091.7	994.0	923.2	868.4	816.1	764.8	725.6
47.5°	1404.8	1375.3	1263.1	1128.5	1001.4	905.2	843.8	793.2	747.3	703.9	669.3
50°	1300.5	1286.2	1189.2	1059.5	938.1	847.6	785.7	742.3	702.9	664.9	632.1
52.5°	1197.7	1197.2	1109.7	990.9	878.6	791.4	730.0	689.4	655.3	624.4	595.0
55°	1040.4	1057.1	988.7	882.7	782.1	703.5	648.2	611.9	588.1	562.5	540.4
57.5°	896.0	923.7	867.2	773.9	690.0	617.6	569.4	542.1	516.8	501.3	485.3
60°	801.8	827.9	783.9	705.3	626.2	564.3	518.4	494.0	472.0	461.3	450.0
62.5°	718.0	741.3	708.7	635.8	567.1	507.6	468.9	445.5	430.6	418.9	411.4
65°	598.2	617.9	589.9	536.9	477.9	430.3	398.8	380.3	366.1	361.3	352.9
67.5°	483.5	501.4	486.3	441.3	394.0	358.0	333.3	315.6	307.1	303.0	297.0
70°	415.4	433.3	417.2	378.0	341.6	311.3	288.1	277.9	269.1	267.3	258.9
72.5°	357.8	370.0	354.0	323.2	292.1	266.6	248.6	238.0	233.3	230.1	225.6
75°	268.5	279.1	268.5	244.6	222.6	204.7	189.2	185.1	179.8	178.0	175.0
77.5°	190.0	199.2	191.1	176.2	159.7	145.9	137.6	132.2	131.0	127.9	129.4
80°	145.3	151.2	143.4	133.4	120.2	110.7	104.8	101.8	98.2	97.0	99.4
82.5°	104.3	106.9	103.0	96.2	86.4	80.2	76.2	72.8	72.0	72.2	72.2
85°	54.2	53.6	53.0	47.0	44.1	39.9	37.5	36.9	36.3	37.5	38.7
87.5°	21.8	21.9	21.1	18.8	16.8	14.9	13.9	13.0	13.9	14.9	15.8
90°	18.4	16.7	14.9	12.7	10.3	7.9	5.4	3.0	5.4	7.9	10.3
92.5°	17.7	15.8	14.1	13.2	13.0	12.9	12.7	12.6	12.7	12.9	13.0
95°	21.5	21.4	21.1	24.8	32.4	39.9	47.4	55.0	47.4	39.9	32.4
97.5°	76.0	100.8	125.6	135.7	131.0	126.3	121.6	116.8	121.6	126.3	131.0
100°	105.4	136.0	166.8	180.1	176.1	172.1	168.1	164.1	168.1	172.1	176.1
102.5°	220.1	224.1	228.1	228.6	225.7	222.7	219.8	216.9	219.8	222.7	225.7
105°	309.9	308.8	307.7	306.4	305.1	303.8	302.5	301.1	302.5	303.8	305.1
107.5°	386.2	384.6	383.1	382.0	381.3	380.7	380.0	379.4	380.0	380.7	381.3
110°	438.5	437.2	435.8	434.9	434.2	433.5	432.8	432.2	432.8	433.5	434.2



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	490.3	489.7	489.1	488.2	487.0	485.8	484.7	483.5	484.7	485.8	487.0
115°	564.7	564.9	565.2	564.9	564.2	563.6	562.9	562.2	562.9	563.6	564.2
117.5°	638.5	638.0	637.5	636.8	635.9	635.1	634.1	633.3	634.1	635.1	635.9
120°	684.8	685.0	685.2	684.8	684.0	683.1	682.2	681.3	682.2	683.1	684.0
122.5°	729.3	729.0	728.7	728.2	727.7	727.2	726.7	726.1	726.7	727.2	727.7
125°	793.2	793.7	794.1	793.9	793.0	792.1	791.3	790.3	791.3	792.1	793.0
127.5°	854.7	853.7	852.6	852.0	851.9	851.6	851.4	851.2	851.4	851.6	851.9
130°	893.0	892.4	891.7	891.3	891.0	890.9	890.6	890.4	890.6	890.9	891.0
132.5°	930.3	929.4	928.7	928.0	927.6	927.2	926.8	926.4	926.8	927.2	927.6
135°	981.6	980.8	979.9	979.6	979.7	980.0	980.2	980.4	980.2	980.0	979.7
137.5°	1031.1	1030.1	1029.2	1028.6	1028.6	1028.5	1028.4	1028.3	1028.4	1028.5	1028.6
140°	1062.6	1062.1	1061.7	1061.3	1060.8	1060.3	1059.9	1059.5	1059.9	1060.3	1060.8
142.5°	1091.7	1091.5	1091.2	1090.7	1089.9	1089.1	1088.3	1087.4	1088.3	1089.1	1089.9
145°	1133.5	1133.5	1133.5	1133.2	1132.5	1131.9	1131.2	1130.5	1131.2	1131.9	1132.5
147.5°	1169.8	1170.0	1170.2	1169.7	1168.5	1167.2	1166.0	1164.7	1166.0	1167.2	1168.5
150°	1193.0	1193.2	1193.4	1193.1	1192.2	1191.3	1190.4	1189.6	1190.4	1191.3	1192.2
152.5°	1212.5	1213.0	1213.3	1213.1	1212.5	1211.8	1211.1	1210.3	1211.1	1211.8	1212.5
155°	1238.9	1239.6	1240.2	1240.4	1240.2	1240.0	1239.8	1239.6	1239.8	1240.0	1240.2
157.5°	1261.7	1262.4	1263.2	1263.6	1263.8	1263.9	1264.0	1264.1	1264.0	1263.9	1263.8
160°	1275.0	1275.2	1275.5	1275.9	1276.6	1277.2	1277.9	1278.6	1277.9	1277.2	1276.6
162.5°	1287.0	1287.2	1287.5	1288.0	1288.8	1289.7	1290.6	1291.3	1290.6	1289.7	1288.8
165°	1302.6	1302.6	1302.6	1303.1	1304.2	1305.4	1306.5	1307.6	1306.5	1305.4	1304.2
167.5°	1314.8	1315.0	1315.1	1315.8	1316.9	1318.1	1319.2	1320.3	1319.2	1318.1	1316.9
170°	1322.2	1321.9	1321.7	1322.2	1323.6	1324.9	1326.3	1327.6	1326.3	1324.9	1323.6
172.5°	1327.0	1326.7	1326.5	1327.1	1328.4	1329.7	1331.0	1332.4	1331.0	1329.7	1328.4
175°	1332.1	1331.9	1331.7	1332.2	1333.6	1334.9	1336.3	1337.6	1336.3	1334.9	1333.6
177.5°	1335.2	1334.9	1334.6	1335.0	1336.3	1337.5	1338.8	1340.0	1338.8	1337.5	1336.3
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332661-935
 CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1409.2	1405.0	1398.8	1390.2	1383.0	1375.4	1373.6	1370.6	1376.4	1371.6	1370.2
5°	1363.0	1350.6	1334.5	1316.0	1305.3	1289.9	1286.9	1280.9	1275.0	1274.4	1268.4
7.5°	1314.1	1295.8	1274.7	1255.9	1238.5	1221.6	1210.6	1208.2	1199.4	1194.2	1188.3
10°	1282.7	1260.1	1235.7	1217.8	1197.6	1179.7	1167.3	1160.1	1154.1	1147.5	1141.6
12.5°	1245.5	1221.5	1201.4	1182.1	1158.0	1144.4	1123.9	1111.5	1110.3	1110.4	1094.9
15°	1202.3	1178.5	1147.5	1120.2	1107.1	1080.9	1069.6	1055.3	1046.4	1037.4	1030.4
17.5°	1153.0	1123.3	1099.2	1067.7	1042.7	1021.8	1007.0	998.4	985.0	972.3	963.2
20°	1122.0	1090.5	1064.8	1031.5	1004.1	978.5	966.0	954.2	944.0	933.3	923.2
22.5°	1090.5	1057.6	1026.2	993.9	968.5	941.4	929.4	913.2	903.5	897.6	887.4
25°	1041.0	1005.3	969.6	938.7	912.5	888.6	872.6	860.1	849.4	844.6	838.1
27.5°	987.2	951.7	917.2	882.1	852.4	835.1	822.3	812.8	806.7	800.3	797.4
30°	953.0	916.0	879.2	846.4	819.0	801.8	789.9	783.3	778.5	775.6	772.6
32.5°	918.2	881.8	842.9	813.0	788.5	773.2	764.1	757.6	755.2	754.1	753.0
35°	862.5	825.5	789.9	763.1	739.9	733.9	726.2	722.6	721.4	725.6	727.4
37.5°	808.6	774.3	741.4	715.4	700.3	691.6	688.9	689.1	693.3	697.0	701.3
40°	773.8	740.5	709.5	686.9	672.6	667.3	666.1	669.0	673.8	678.0	682.7
42.5°	739.9	707.1	679.0	657.8	647.8	642.9	643.7	646.6	653.3	658.4	665.6
45°	687.5	660.1	632.7	615.4	607.1	608.3	608.3	613.6	620.2	627.9	635.7
47.5°	638.1	610.4	588.0	573.4	569.1	568.1	571.4	578.4	587.8	597.4	608.2
50°	604.8	578.5	558.9	545.8	541.1	542.9	547.6	554.1	565.4	577.4	588.7
52.5°	570.9	547.1	528.9	516.8	513.4	516.7	521.4	531.8	541.7	554.5	568.2
55°	518.4	498.2	483.9	475.0	473.8	475.6	481.0	492.2	506.5	522.6	535.7
57.5°	466.1	449.3	436.2	430.0	430.6	432.2	441.1	454.5	469.8	486.9	503.8
60°	430.9	415.4	404.8	400.0	400.5	404.2	414.8	427.4	446.4	463.0	481.0
62.5°	397.6	384.0	373.8	369.5	368.7	376.5	386.8	399.8	418.8	437.4	456.7
65°	344.1	333.3	325.0	322.6	324.4	330.4	343.5	360.7	376.8	396.4	416.6
67.5°	291.6	282.8	277.2	278.2	280.3	289.1	300.1	315.0	333.2	353.5	373.6
70°	258.3	249.9	245.2	245.8	249.4	260.1	269.7	284.5	304.2	325.0	341.6
72.5°	224.0	218.5	214.3	216.8	220.3	227.7	239.6	254.5	271.8	291.2	308.8
75°	172.0	172.0	169.6	171.4	176.8	183.9	192.9	208.4	225.6	241.1	255.4
77.5°	127.6	126.3	127.9	130.0	133.1	141.5	151.8	162.8	175.8	191.3	203.1
80°	97.6	98.2	101.2	104.8	106.0	112.5	123.2	133.4	143.4	156.5	167.8
82.5°	73.4	74.0	75.5	80.0	81.2	88.3	95.1	105.2	114.4	123.2	132.6
85°	39.9	39.9	42.9	44.6	47.6	52.3	56.6	62.5	70.9	76.8	85.7
87.5°	17.8	18.3	20.5	21.8	23.6	26.3	27.6	33.1	35.2	37.9	42.3
90°	12.7	14.9	16.7	18.4	20.2	22.0	23.3	24.7	26.0	27.4	28.2
92.5°	13.2	14.1	15.8	17.7	19.5	21.2	22.6	23.8	25.2	26.5	27.3
95°	24.8	21.1	21.4	21.5	21.8	22.0	23.3	24.7	26.0	27.4	28.2
97.5°	135.7	125.6	100.8	76.0	51.2	26.4	26.5	26.7	26.8	26.9	27.1
100°	180.1	166.8	136.0	105.4	74.7	44.0	40.2	36.4	32.7	28.9	27.1
102.5°	228.6	228.1	224.1	220.1	216.1	212.1	171.3	130.5	89.8	49.0	28.7
105°	306.4	307.7	308.8	309.9	311.0	312.1	314.2	316.2	318.1	320.1	317.1
107.5°	382.0	383.1	384.6	386.2	387.6	389.2	390.1	391.2	392.1	393.0	394.0
110°	434.9	435.8	437.2	438.5	439.9	441.2	441.6	442.1	442.6	443.0	443.5



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.2	489.1	489.7	490.3	491.0	491.6	491.5	491.5	491.4	491.3	491.6
115°	564.9	565.2	564.9	564.7	564.5	564.2	564.7	565.2	565.6	566.0	566.3
117.5°	636.8	637.5	638.0	638.5	639.0	639.5	639.4	639.3	639.2	639.1	639.0
120°	684.8	685.2	685.0	684.8	684.5	684.3	684.8	685.2	685.6	686.0	686.0
122.5°	728.2	728.7	729.0	729.3	729.6	730.0	730.2	730.5	730.7	731.0	730.9
125°	793.9	794.1	793.7	793.2	792.8	792.4	793.0	793.7	794.4	795.0	795.5
127.5°	852.0	852.6	853.7	854.7	855.7	856.8	856.6	856.5	856.4	856.3	856.1
130°	891.3	891.7	892.4	893.0	893.7	894.4	894.6	894.8	895.1	895.3	895.4
132.5°	928.0	928.7	929.4	930.3	931.2	932.0	932.2	932.5	932.7	932.9	932.9
135°	979.6	979.9	980.8	981.6	982.6	983.4	983.9	984.3	984.7	985.2	985.7
137.5°	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5	1034.1	1034.5	1035.0	1035.2
140°	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1	1064.8	1065.5	1066.2	1066.6
142.5°	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8	1093.3	1093.7	1094.2	1094.5
145°	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8	1133.9	1134.2	1134.4	1134.7
147.5°	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5	1169.7	1169.8	1170.0	1170.2
150°	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5	1192.5	1192.5	1192.5	1192.7
152.5°	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1	1212.5	1212.8	1213.1	1213.2
155°	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5	1239.3	1240.2	1241.1	1241.2
157.5°	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8
160°	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9
162.5°	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9	1289.3	1290.6	1291.9	1291.8
165°	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3	1306.1	1307.9	1309.7	1309.6
167.5°	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6	1318.5	1320.4	1322.4	1322.2
170°	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4	1326.1	1327.9	1329.7	1329.5
172.5°	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1	1330.9	1332.7	1334.5	1334.2
175°	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6	1336.6	1338.6	1340.6	1340.2
177.5°	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4	1338.9	1340.2	1341.7	1341.4
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1369.2	1368.3	1364.9	1364.5	1364.9	1368.3	1369.2	1370.2	1371.6	1376.4	1370.6
5°	1264.8	1261.9	1260.1	1266.6	1260.1	1261.9	1264.8	1268.4	1274.4	1275.0	1280.9
7.5°	1186.1	1183.8	1178.5	1176.9	1178.5	1183.8	1186.1	1188.3	1194.2	1199.4	1208.2
10°	1135.7	1133.2	1128.5	1127.3	1128.5	1133.2	1135.7	1141.6	1147.5	1154.1	1160.1
12.5°	1087.1	1082.4	1081.4	1082.5	1081.4	1082.4	1087.1	1094.9	1110.4	1110.3	1111.5
15°	1022.6	1020.2	1013.7	1015.5	1013.7	1020.2	1022.6	1030.4	1037.4	1046.4	1055.3
17.5°	959.0	956.1	948.2	955.2	948.2	956.1	959.0	963.2	972.3	985.0	998.4
20°	919.0	914.2	910.1	909.5	910.1	914.2	919.0	923.2	933.3	944.0	954.2
22.5°	880.9	876.7	876.2	872.4	876.2	876.7	880.9	887.4	897.6	903.5	913.2
25°	833.3	829.1	827.9	825.0	827.9	829.1	833.3	838.1	844.6	849.4	860.1
27.5°	796.8	794.7	792.6	793.5	792.6	794.7	796.8	797.4	800.3	806.7	812.8
30°	774.4	773.8	772.6	772.6	772.6	773.8	774.4	772.6	775.6	778.5	783.3
32.5°	755.8	755.7	756.4	756.4	756.4	755.7	755.8	753.0	754.1	755.2	757.6
35°	729.7	731.5	732.7	730.9	732.7	731.5	729.7	727.4	725.6	721.4	722.6
37.5°	706.2	707.9	709.6	711.6	709.6	707.9	706.2	701.3	697.0	693.3	689.1
40°	688.0	692.2	693.4	696.4	693.4	692.2	688.0	682.7	678.0	673.8	669.0
42.5°	670.9	675.5	678.6	679.2	678.6	675.5	670.9	665.6	658.4	653.3	646.6
45°	644.6	649.4	653.6	653.6	653.6	649.4	644.6	635.7	627.9	620.2	613.6
47.5°	617.3	624.2	628.4	629.5	628.4	624.2	617.3	608.2	597.4	587.8	578.4
50°	598.8	607.1	611.3	614.2	611.3	607.1	598.8	588.7	577.4	565.4	554.1
52.5°	580.7	589.0	594.6	596.2	594.6	589.0	580.7	568.2	554.5	541.7	531.8
55°	549.4	561.3	567.8	570.2	567.8	561.3	549.4	535.7	522.6	506.5	492.2
57.5°	519.9	530.8	538.5	540.2	538.5	530.8	519.9	503.8	486.9	469.8	454.5
60°	497.0	508.9	518.4	520.2	518.4	508.9	497.0	481.0	463.0	446.4	427.4
62.5°	473.6	486.0	494.6	499.3	494.6	486.0	473.6	456.7	437.4	418.8	399.8
65°	433.3	445.8	454.2	455.9	454.2	445.8	433.3	416.6	396.4	376.8	360.7
67.5°	389.3	401.7	407.3	410.7	407.3	401.7	389.3	373.6	353.5	333.2	315.0
70°	358.3	368.4	374.4	377.4	374.4	368.4	358.3	341.6	325.0	304.2	284.5
72.5°	323.0	333.6	340.6	341.2	340.6	333.6	323.0	308.8	291.2	271.8	254.5
75°	269.1	278.5	282.1	282.1	282.1	278.5	269.1	255.4	241.1	225.6	208.4
77.5°	212.9	217.8	222.4	223.3	222.4	217.8	212.9	203.1	191.3	175.8	162.8
80°	176.8	179.8	183.3	183.3	183.3	179.8	176.8	167.8	156.5	143.4	133.4
82.5°	139.7	142.2	145.7	145.3	145.7	142.2	139.7	132.6	123.2	114.4	105.2
85°	84.6	89.9	89.3	88.1	89.3	89.9	84.6	85.7	76.8	70.9	62.5
87.5°	43.8	44.4	45.9	46.9	45.9	44.4	43.8	42.3	37.9	35.2	33.1
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.4	26.0	24.7
92.5°	27.4	27.5	27.6	27.6	27.6	27.5	27.4	27.3	26.5	25.2	23.8
95°	28.3	28.6	28.8	29.0	28.8	28.6	28.3	28.2	27.4	26.0	24.7
97.5°	27.4	27.6	27.8	28.0	27.8	27.6	27.4	27.1	26.9	26.8	26.7
100°	27.4	27.6	27.8	28.0	27.8	27.6	27.4	27.1	28.9	32.7	36.4
102.5°	28.7	28.8	28.8	28.8	28.8	28.8	28.7	28.7	49.0	89.8	130.5
105°	309.1	301.1	293.2	285.2	293.2	301.1	309.1	317.1	320.1	318.1	316.2
107.5°	394.9	395.7	396.5	397.4	396.5	395.7	394.9	394.0	393.0	392.1	391.2
110°	444.2	444.9	445.6	446.2	445.6	444.9	444.2	443.5	443.0	442.6	442.1



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.5	493.4	494.2	495.0	494.2	493.4	492.5	491.6	491.3	491.4	491.5
115°	566.3	566.3	566.3	566.3	566.3	566.3	566.3	566.3	566.0	565.6	565.2
117.5°	638.9	638.9	638.8	638.7	638.8	638.9	638.9	639.0	639.1	639.2	639.3
120°	685.6	685.2	684.8	684.3	684.8	685.2	685.6	686.0	686.0	685.6	685.2
122.5°	730.5	730.0	729.5	729.1	729.5	730.0	730.5	730.9	731.0	730.7	730.5
125°	795.7	795.9	796.2	796.3	796.2	795.9	795.7	795.5	795.0	794.4	793.7
127.5°	855.9	855.7	855.6	855.4	855.6	855.7	855.9	856.1	856.3	856.4	856.5
130°	895.4	895.4	895.4	895.4	895.4	895.4	895.4	895.4	895.3	895.1	894.8
132.5°	932.7	932.5	932.4	932.2	932.4	932.5	932.7	932.9	932.9	932.7	932.5
135°	986.1	986.5	987.0	987.4	987.0	986.5	986.1	985.7	985.2	984.7	984.3
137.5°	1035.1	1034.9	1034.7	1034.7	1034.7	1034.9	1035.1	1035.2	1035.0	1034.5	1034.1
140°	1066.8	1067.0	1067.2	1067.5	1067.2	1067.0	1066.8	1066.6	1066.2	1065.5	1064.8
142.5°	1094.6	1094.6	1094.7	1094.7	1094.7	1094.6	1094.6	1094.5	1094.2	1093.7	1093.3
145°	1135.1	1135.6	1136.1	1136.5	1136.1	1135.6	1135.1	1134.7	1134.4	1134.2	1133.9
147.5°	1170.4	1170.7	1170.9	1171.1	1170.9	1170.7	1170.4	1170.2	1170.0	1169.8	1169.7
150°	1192.8	1193.1	1193.3	1193.5	1193.3	1193.1	1192.8	1192.7	1192.5	1192.5	1192.5
152.5°	1213.1	1213.0	1212.9	1212.7	1212.9	1213.0	1213.1	1213.2	1213.1	1212.8	1212.5
155°	1240.5	1239.8	1239.2	1238.5	1239.2	1239.8	1240.5	1241.2	1241.1	1240.2	1239.3
157.5°	1263.6	1262.5	1261.3	1260.2	1261.3	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5
160°	1278.6	1277.2	1275.9	1274.5	1275.9	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2
162.5°	1290.3	1288.8	1287.3	1285.7	1287.3	1288.8	1290.3	1291.8	1291.9	1290.6	1289.3
165°	1307.6	1305.5	1303.6	1301.6	1303.6	1305.5	1307.6	1309.6	1309.7	1307.9	1306.1
167.5°	1320.1	1317.8	1315.6	1313.4	1315.6	1317.8	1320.1	1322.2	1322.4	1320.4	1318.5
170°	1327.2	1325.0	1322.8	1320.6	1322.8	1325.0	1327.2	1329.5	1329.7	1327.9	1326.1
172.5°	1331.8	1329.4	1327.0	1324.6	1327.0	1329.4	1331.8	1334.2	1334.5	1332.7	1330.9
175°	1337.6	1334.9	1332.2	1329.6	1332.2	1334.9	1337.6	1340.2	1340.6	1338.6	1336.6
177.5°	1339.2	1337.0	1334.9	1332.8	1334.9	1337.0	1339.2	1341.4	1341.7	1340.2	1338.9
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1373.6	1375.4	1383.0	1390.2	1398.8	1405.0	1409.2	1414.0	1424.0	1432.1	1439.7
5°	1286.9	1289.9	1305.3	1316.0	1334.5	1350.6	1363.0	1376.7	1392.8	1414.8	1435.0
7.5°	1210.6	1221.6	1238.5	1255.9	1274.7	1295.8	1314.1	1334.7	1362.4	1392.7	1423.8
10°	1167.3	1179.7	1197.6	1217.8	1235.7	1260.1	1282.7	1307.1	1338.6	1375.5	1412.5
12.5°	1123.9	1144.4	1158.0	1182.1	1201.4	1221.5	1245.5	1277.6	1314.3	1353.1	1397.7
15°	1069.6	1080.9	1107.1	1120.2	1147.5	1178.5	1202.3	1234.5	1270.1	1321.4	1371.4
17.5°	1007.0	1021.8	1042.7	1067.7	1099.2	1123.3	1153.0	1186.0	1231.1	1281.9	1344.5
20°	966.0	978.5	1004.1	1031.5	1064.8	1090.5	1122.0	1154.1	1200.6	1254.7	1320.2
22.5°	929.4	941.4	968.5	993.9	1026.2	1057.6	1090.5	1127.9	1172.4	1229.5	1296.4
25°	872.6	888.6	912.5	938.7	969.6	1005.3	1041.0	1074.4	1122.0	1182.1	1253.5
27.5°	822.3	835.1	852.4	882.1	917.2	951.7	987.2	1029.2	1074.9	1138.4	1212.5
30°	789.9	801.8	819.0	846.4	879.2	916.0	953.0	993.4	1041.0	1104.1	1179.7
32.5°	764.1	773.2	788.5	813.0	842.9	881.8	918.2	960.1	1010.0	1072.2	1145.9
35°	726.2	733.9	739.9	763.1	789.9	825.5	862.5	907.1	955.3	1014.3	1088.0
37.5°	688.9	691.6	700.3	715.4	741.4	774.3	808.6	852.5	901.9	961.7	1028.3
40°	666.1	667.3	672.6	686.9	709.5	740.5	773.8	817.3	864.3	920.8	986.9
42.5°	643.7	642.9	647.8	657.8	679.0	707.1	739.9	779.6	826.6	878.9	941.2
45°	608.3	608.3	607.1	615.4	632.7	660.1	687.5	725.6	764.8	816.1	868.4
47.5°	571.4	568.1	569.1	573.4	588.0	610.4	638.1	669.3	703.9	747.3	793.2
50°	547.6	542.9	541.1	545.8	558.9	578.5	604.8	632.1	664.9	702.9	742.3
52.5°	521.4	516.7	513.4	516.8	528.9	547.1	570.9	595.0	624.4	655.3	689.4
55°	481.0	475.6	473.8	475.0	483.9	498.2	518.4	540.4	562.5	588.1	611.9
57.5°	441.1	432.2	430.6	430.0	436.2	449.3	466.1	485.3	501.3	516.8	542.1
60°	414.8	404.2	400.5	400.0	404.8	415.4	430.9	450.0	461.3	472.0	494.0
62.5°	386.8	376.5	368.7	369.5	373.8	384.0	397.6	411.4	418.9	430.6	445.5
65°	343.5	330.4	324.4	322.6	325.0	333.3	344.1	352.9	361.3	366.1	380.3
67.5°	300.1	289.1	280.3	278.2	277.2	282.8	291.6	297.0	303.0	307.1	315.6
70°	269.7	260.1	249.4	245.8	245.2	249.9	258.3	258.9	267.3	269.1	277.9
72.5°	239.6	227.7	220.3	216.8	214.3	218.5	224.0	225.6	230.1	233.3	238.0
75°	192.9	183.9	176.8	171.4	169.6	172.0	172.0	175.0	178.0	179.8	185.1
77.5°	151.8	141.5	133.1	130.0	127.9	126.3	127.6	129.4	127.9	131.0	132.2
80°	123.2	112.5	106.0	104.8	101.2	98.2	97.6	99.4	97.0	98.2	101.8
82.5°	95.1	88.3	81.2	80.0	75.5	74.0	73.4	72.2	72.2	72.0	72.8
85°	56.6	52.3	47.6	44.6	42.9	39.9	39.9	38.7	37.5	36.3	36.9
87.5°	27.6	26.3	23.6	21.8	20.5	18.3	17.8	15.8	14.9	13.9	13.0
90°	23.3	22.0	20.2	18.4	16.7	14.9	12.7	10.3	7.9	5.4	3.0
92.5°	22.6	21.2	19.5	17.7	15.8	14.1	13.2	13.0	12.9	12.7	12.6
95°	23.3	22.0	21.8	21.5	21.4	21.1	24.8	32.4	39.9	47.4	55.0
97.5°	26.5	26.4	51.2	76.0	100.8	125.6	135.7	131.0	126.3	121.6	116.8
100°	40.2	44.0	74.7	105.4	136.0	166.8	180.1	176.1	172.1	168.1	164.1
102.5°	171.3	212.1	216.1	220.1	224.1	228.1	228.6	225.7	222.7	219.8	216.9
105°	314.2	312.1	311.0	309.9	308.8	307.7	306.4	305.1	303.8	302.5	301.1
107.5°	390.1	389.2	387.6	386.2	384.6	383.1	382.0	381.3	380.7	380.0	379.4
110°	441.6	441.2	439.9	438.5	437.2	435.8	434.9	434.2	433.5	432.8	432.2



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	491.5	491.6	491.0	490.3	489.7	489.1	488.2	487.0	485.8	484.7	483.5
115°	564.7	564.2	564.5	564.7	564.9	565.2	564.9	564.2	563.6	562.9	562.2
117.5°	639.4	639.5	639.0	638.5	638.0	637.5	636.8	635.9	635.1	634.1	633.3
120°	684.8	684.3	684.5	684.8	685.0	685.2	684.8	684.0	683.1	682.2	681.3
122.5°	730.2	730.0	729.6	729.3	729.0	728.7	728.2	727.7	727.2	726.7	726.1
125°	793.0	792.4	792.8	793.2	793.7	794.1	793.9	793.0	792.1	791.3	790.3
127.5°	856.6	856.8	855.7	854.7	853.7	852.6	852.0	851.9	851.6	851.4	851.2
130°	894.6	894.4	893.7	893.0	892.4	891.7	891.3	891.0	890.9	890.6	890.4
132.5°	932.2	932.0	931.2	930.3	929.4	928.7	928.0	927.6	927.2	926.8	926.4
135°	983.9	983.4	982.6	981.6	980.8	979.9	979.6	979.7	980.0	980.2	980.4
137.5°	1033.5	1033.0	1032.1	1031.1	1030.1	1029.2	1028.6	1028.6	1028.5	1028.4	1028.3
140°	1064.1	1063.5	1063.0	1062.6	1062.1	1061.7	1061.3	1060.8	1060.3	1059.9	1059.5
142.5°	1092.8	1092.3	1092.0	1091.7	1091.5	1091.2	1090.7	1089.9	1089.1	1088.3	1087.4
145°	1133.8	1133.5	1133.5	1133.5	1133.5	1133.5	1133.2	1132.5	1131.9	1131.2	1130.5
147.5°	1169.5	1169.3	1169.5	1169.8	1170.0	1170.2	1169.7	1168.5	1167.2	1166.0	1164.7
150°	1192.5	1192.5	1192.7	1193.0	1193.2	1193.4	1193.1	1192.2	1191.3	1190.4	1189.6
152.5°	1212.1	1211.8	1212.1	1212.5	1213.0	1213.3	1213.1	1212.5	1211.8	1211.1	1210.3
155°	1238.5	1237.5	1238.2	1238.9	1239.6	1240.2	1240.4	1240.2	1240.0	1239.8	1239.6
157.5°	1261.3	1260.2	1260.9	1261.7	1262.4	1263.2	1263.6	1263.8	1263.9	1264.0	1264.1
160°	1275.9	1274.5	1274.8	1275.0	1275.2	1275.5	1275.9	1276.6	1277.2	1277.9	1278.6
162.5°	1287.9	1286.6	1286.8	1287.0	1287.2	1287.5	1288.0	1288.8	1289.7	1290.6	1291.3
165°	1304.3	1302.6	1302.6	1302.6	1302.6	1302.6	1303.1	1304.2	1305.4	1306.5	1307.6
167.5°	1316.6	1314.6	1314.7	1314.8	1315.0	1315.1	1315.8	1316.9	1318.1	1319.2	1320.3
170°	1324.4	1322.6	1322.3	1322.2	1321.9	1321.7	1322.2	1323.6	1324.9	1326.3	1327.6
172.5°	1329.1	1327.4	1327.1	1327.0	1326.7	1326.5	1327.1	1328.4	1329.7	1331.0	1332.4
175°	1334.6	1332.6	1332.4	1332.1	1331.9	1331.7	1332.2	1333.6	1334.9	1336.3	1337.6
177.5°	1337.4	1336.0	1335.7	1335.2	1334.9	1334.6	1335.0	1336.3	1337.5	1338.8	1340.0
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1446.4	1451.1	1457.3	1467.8	1471.6	1476.4	1483.1	1482.6	1484.5	1491.6	1506.8
5°	1451.7	1470.2	1488.1	1509.5	1532.1	1547.0	1567.2	1579.7	1592.2	1608.3	1635.6
7.5°	1453.9	1483.2	1515.9	1553.5	1587.0	1625.6	1655.6	1683.9	1709.6	1743.5	1776.2
10°	1450.5	1489.8	1532.1	1579.7	1630.3	1673.2	1711.8	1755.9	1793.4	1834.4	1871.4
12.5°	1444.3	1491.8	1548.3	1601.6	1660.8	1724.1	1772.3	1816.8	1866.7	1914.0	1970.9
15°	1430.3	1495.2	1561.3	1631.5	1710.6	1783.8	1853.5	1911.2	1964.8	2035.7	2110.1
17.5°	1412.5	1482.5	1565.7	1650.8	1733.5	1817.2	1903.4	1990.2	2057.8	2145.8	2204.0
20°	1395.8	1476.7	1562.5	1663.6	1746.4	1850.5	1936.2	2020.2	2113.0	2200.5	2270.1
22.5°	1372.4	1461.0	1552.0	1652.7	1761.6	1865.8	1964.8	2055.9	2148.7	2243.9	2328.2
25°	1342.8	1423.1	1530.9	1645.2	1753.5	1866.6	1980.3	2094.6	2194.5	2295.2	2373.7
27.5°	1292.4	1393.8	1494.1	1612.1	1732.4	1860.4	1981.9	2101.6	2206.3	2289.1	2337.8
30°	1266.6	1354.7	1463.6	1582.1	1712.4	1849.9	1976.7	2094.0	2191.6	2257.6	2277.3
32.5°	1228.6	1319.5	1426.0	1548.8	1686.7	1828.0	1960.1	2070.6	2152.1	2186.7	2163.0
35°	1172.0	1254.1	1361.8	1487.5	1630.9	1781.5	1911.9	2005.3	2046.9	2014.2	1932.7
37.5°	1104.1	1185.5	1293.7	1417.1	1565.6	1718.6	1836.5	1903.8	1889.9	1808.5	1687.0
40°	1056.5	1132.7	1235.7	1369.0	1513.6	1667.2	1770.7	1807.1	1769.0	1652.3	1523.2
42.5°	1003.7	1078.0	1181.4	1309.9	1463.2	1604.8	1695.1	1698.1	1634.2	1494.7	1365.0
45°	923.2	994.0	1091.7	1225.5	1367.2	1500.6	1560.0	1530.9	1413.1	1278.5	1148.1
47.5°	843.8	905.2	1001.4	1128.5	1263.1	1375.3	1404.8	1352.3	1226.8	1096.1	975.3
50°	785.7	847.6	938.1	1059.5	1189.2	1286.2	1300.5	1230.9	1107.7	976.1	881.5
52.5°	730.0	791.4	878.6	990.9	1109.7	1197.2	1197.7	1117.1	994.4	877.1	789.1
55°	648.2	703.5	782.1	882.7	988.7	1057.1	1040.4	957.1	850.6	748.8	672.0
57.5°	569.4	617.6	690.0	773.9	867.2	923.7	896.0	815.8	720.7	634.4	576.2
60°	518.4	564.3	626.2	705.3	783.9	827.9	801.8	729.1	641.6	572.0	521.4
62.5°	468.9	507.6	567.1	635.8	708.7	741.3	718.0	646.3	570.7	507.7	466.7
65°	398.8	430.3	477.9	536.9	589.9	617.9	598.2	531.5	473.8	428.5	395.8
67.5°	333.3	358.0	394.0	441.3	486.3	501.4	483.5	437.1	388.2	352.0	328.9
70°	288.1	311.3	341.6	378.0	417.2	433.3	415.4	378.6	338.7	305.3	282.8
72.5°	248.6	266.6	292.1	323.2	354.0	370.0	357.8	322.4	288.7	263.9	244.6
75°	189.2	204.7	222.6	244.6	268.5	279.1	268.5	244.0	220.8	202.3	188.6
77.5°	137.6	145.9	159.7	176.2	191.1	199.2	190.0	173.4	159.3	146.6	139.9
80°	104.8	110.7	120.2	133.4	143.4	151.2	145.3	131.6	120.2	111.9	108.9
82.5°	76.2	80.2	86.4	96.2	103.0	106.9	104.3	94.4	89.7	82.4	79.4
85°	37.5	39.9	44.1	47.0	53.0	53.6	54.2	50.0	45.8	44.1	41.7
87.5°	13.9	14.9	16.8	18.8	21.1	21.9	21.8	22.1	20.6	20.4	18.8
90°	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3	24.7
92.5°	12.7	12.9	13.0	13.2	14.1	15.8	17.7	19.5	21.2	22.6	23.8
95°	47.4	39.9	32.4	24.8	21.1	21.4	21.5	21.8	22.0	23.3	24.7
97.5°	121.6	126.3	131.0	135.7	125.6	100.8	76.0	51.2	26.4	26.5	26.7
100°	168.1	172.1	176.1	180.1	166.8	136.0	105.4	74.7	44.0	40.2	36.4
102.5°	219.8	222.7	225.7	228.6	228.1	224.1	220.1	216.1	212.1	171.3	130.5
105°	302.5	303.8	305.1	306.4	307.7	308.8	309.9	311.0	312.1	314.2	316.2
107.5°	380.0	380.7	381.3	382.0	383.1	384.6	386.2	387.6	389.2	390.1	391.2
110°	432.8	433.5	434.2	434.9	435.8	437.2	438.5	439.9	441.2	441.6	442.1



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.7	485.8	487.0	488.2	489.1	489.7	490.3	491.0	491.6	491.5	491.5
115°	562.9	563.6	564.2	564.9	565.2	564.9	564.7	564.5	564.2	564.7	565.2
117.5°	634.1	635.1	635.9	636.8	637.5	638.0	638.5	639.0	639.5	639.4	639.3
120°	682.2	683.1	684.0	684.8	685.2	685.0	684.8	684.5	684.3	684.8	685.2
122.5°	726.7	727.2	727.7	728.2	728.7	729.0	729.3	729.6	730.0	730.2	730.5
125°	791.3	792.1	793.0	793.9	794.1	793.7	793.2	792.8	792.4	793.0	793.7
127.5°	851.4	851.6	851.9	852.0	852.6	853.7	854.7	855.7	856.8	856.6	856.5
130°	890.6	890.9	891.0	891.3	891.7	892.4	893.0	893.7	894.4	894.6	894.8
132.5°	926.8	927.2	927.6	928.0	928.7	929.4	930.3	931.2	932.0	932.2	932.5
135°	980.2	980.0	979.7	979.6	979.9	980.8	981.6	982.6	983.4	983.9	984.3
137.5°	1028.4	1028.5	1028.6	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5	1034.1
140°	1059.9	1060.3	1060.8	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1	1064.8
142.5°	1088.3	1089.1	1089.9	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8	1093.3
145°	1131.2	1131.9	1132.5	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8	1133.9
147.5°	1166.0	1167.2	1168.5	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5	1169.7
150°	1190.4	1191.3	1192.2	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5	1192.5
152.5°	1211.1	1211.8	1212.5	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1	1212.5
155°	1239.8	1240.0	1240.2	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5	1239.3
157.5°	1264.0	1263.9	1263.8	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3	1262.5
160°	1277.9	1277.2	1276.6	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9	1277.2
162.5°	1290.6	1289.7	1288.8	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9	1289.3
165°	1306.5	1305.4	1304.2	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3	1306.1
167.5°	1319.2	1318.1	1316.9	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6	1318.5
170°	1326.3	1324.9	1323.6	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4	1326.1
172.5°	1331.0	1329.7	1328.4	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1	1330.9
175°	1336.3	1334.9	1333.6	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6	1336.6
177.5°	1338.8	1337.5	1336.3	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4	1338.9
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332661-935
 CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1514.5	1515.4	1519.7	1523.0	1524.0	1528.8	1529.2
5°	1647.5	1657.7	1677.3	1679.1	1682.0	1697.5	1685.7
7.5°	1803.5	1829.2	1846.3	1861.5	1867.0	1873.7	1872.3
10°	1903.5	1941.6	1960.7	1991.0	1992.2	1999.9	1995.2
12.5°	2004.0	2048.2	2083.0	2088.6	2114.1	2118.0	2124.7
15°	2146.3	2193.4	2241.6	2258.8	2294.0	2302.3	2315.4
17.5°	2280.2	2328.2	2362.1	2406.7	2421.1	2440.4	2427.2
20°	2353.5	2405.9	2448.7	2483.8	2498.7	2509.4	2508.3
22.5°	2397.8	2450.6	2485.4	2511.9	2525.8	2530.4	2530.1
25°	2425.5	2455.8	2466.6	2476.7	2461.3	2455.8	2458.2
27.5°	2348.4	2340.5	2312.6	2275.9	2237.7	2207.5	2191.1
30°	2242.2	2195.7	2153.4	2079.7	2041.6	2019.0	1998.7
32.5°	2091.7	2018.1	1936.8	1869.2	1825.9	1792.3	1787.3
35°	1833.8	1723.1	1623.8	1541.0	1498.1	1461.8	1453.5
37.5°	1559.1	1444.1	1354.6	1281.8	1235.7	1210.0	1186.1
40°	1376.7	1277.9	1189.8	1127.9	1092.8	1074.4	1059.5
42.5°	1236.2	1146.0	1058.4	1011.2	979.5	968.2	959.5
45°	1042.2	958.3	897.6	861.9	843.4	824.4	815.5
47.5°	886.8	818.6	778.5	748.2	728.4	717.1	711.4
50°	798.7	742.8	707.1	683.9	666.1	657.1	652.4
52.5°	720.7	674.8	644.7	626.3	614.2	607.6	605.7
55°	620.8	585.7	566.6	550.6	541.7	535.7	533.3
57.5°	539.6	512.6	497.1	483.9	480.4	475.4	473.8
60°	486.3	465.5	452.4	443.4	440.5	434.5	435.7
62.5°	439.1	422.1	411.0	405.8	401.9	396.9	398.6
65°	371.4	359.0	352.9	348.2	343.5	340.4	342.9
67.5°	311.7	303.1	295.0	292.2	289.9	289.4	286.9
70°	272.6	265.4	258.3	256.6	256.6	254.2	253.6
72.5°	235.0	229.7	225.0	223.7	221.8	222.7	220.2
75°	181.5	177.4	175.6	173.8	173.2	173.2	171.4
77.5°	134.1	131.0	128.2	128.2	126.1	125.3	125.0
80°	101.8	100.6	98.2	98.2	97.0	97.6	96.4
82.5°	76.5	74.9	74.4	73.4	71.8	71.9	70.7
85°	41.1	39.3	38.7	36.9	35.7	36.9	35.7
87.5°	19.5	19.3	18.9	18.1	17.7	17.8	16.4
90°	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	25.2	26.5	27.3	27.4	27.5	27.6	27.6
95°	26.0	27.4	28.2	28.3	28.6	28.8	29.0
97.5°	26.8	26.9	27.1	27.4	27.6	27.8	28.0
100°	32.7	28.9	27.1	27.4	27.6	27.8	28.0
102.5°	89.8	49.0	28.7	28.7	28.8	28.8	28.8
105°	318.1	320.1	317.1	309.1	301.1	293.2	285.2
107.5°	392.1	393.0	394.0	394.9	395.7	396.5	397.4
110°	442.6	443.0	443.5	444.2	444.9	445.6	446.2



TEST NUMBER: P332661-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	491.4	491.3	491.6	492.5	493.4	494.2	495.0
115°	565.6	566.0	566.3	566.3	566.3	566.3	566.3
117.5°	639.2	639.1	639.0	638.9	638.9	638.8	638.7
120°	685.6	686.0	686.0	685.6	685.2	684.8	684.3
122.5°	730.7	731.0	730.9	730.5	730.0	729.5	729.1
125°	794.4	795.0	795.5	795.7	795.9	796.2	796.3
127.5°	856.4	856.3	856.1	855.9	855.7	855.6	855.4
130°	895.1	895.3	895.4	895.4	895.4	895.4	895.4
132.5°	932.7	932.9	932.9	932.7	932.5	932.4	932.2
135°	984.7	985.2	985.7	986.1	986.5	987.0	987.4
137.5°	1034.5	1035.0	1035.2	1035.1	1034.9	1034.7	1034.7
140°	1065.5	1066.2	1066.6	1066.8	1067.0	1067.2	1067.5
142.5°	1093.7	1094.2	1094.5	1094.6	1094.6	1094.7	1094.7
145°	1134.2	1134.4	1134.7	1135.1	1135.6	1136.1	1136.5
147.5°	1169.8	1170.0	1170.2	1170.4	1170.7	1170.9	1171.1
150°	1192.5	1192.5	1192.7	1192.8	1193.1	1193.3	1193.5
152.5°	1212.8	1213.1	1213.2	1213.1	1213.0	1212.9	1212.7
155°	1240.2	1241.1	1241.2	1240.5	1239.8	1239.2	1238.5
157.5°	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2
160°	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5
162.5°	1290.6	1291.9	1291.8	1290.3	1288.8	1287.3	1285.7
165°	1307.9	1309.7	1309.6	1307.6	1305.5	1303.6	1301.6
167.5°	1320.4	1322.4	1322.2	1320.1	1317.8	1315.6	1313.4
170°	1327.9	1329.7	1329.5	1327.2	1325.0	1322.8	1320.6
172.5°	1332.7	1334.5	1334.2	1331.8	1329.4	1327.0	1324.6
175°	1338.6	1340.6	1340.2	1337.6	1334.9	1332.2	1329.6
177.5°	1340.2	1341.7	1341.4	1339.2	1337.0	1334.9	1332.8
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6

(END OF REPORT)