

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913058

Luminaire Tested: DFN2DIP-4P2F0-020D040US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913058
REPORT IS A COMBINATION OF REPORTS P899023 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D040US927-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4372.9 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 49.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913058

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913058

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1544	1544	1544
5°	1543	1518	1530
10°	1528	1494	1506
15°	1502	1465	1472
20°	1469	1427	1436
25°	1435	1382	1395
30°	1394	1341	1344
35°	1355	1292	1290
40°	1307	1243	1238
45°	1260	1193	1185
50°	1208	1141	1125
55°	1153	1080	1068
60°	1090	1009	1003
65°	1022	935	926
70°	935	844	844
75°	817	736	763
80°	671	598	617
85°	448	373	385

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1490 cd/sqm

TEST NUMBER: P913058

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	1.3
10°-20°	163.3	3.7
20°-30°	239.9	5.5
30°-40°	278.7	6.4
40°-50°	278.3	6.4
50°-60°	242.7	5.5
60°-70°	179.4	4.1
70°-80°	101.5	2.3
80°-90°	29.6	0.7
90°-100°	62.0	1.4
100°-110°	197.0	4.5
110°-120°	337.2	7.7
120°-130°	443.5	10.1
130°-140°	497.8	11.4
140°-150°	488.1	11.2
150°-160°	409.5	9.4
160°-170°	271.5	6.2
170°-180°	94.9	2.2
0°-30°	461.2	10.5
0°-40°	739.9	16.9
0°-60°	1260.8	28.8
0°-90°	1571.4	35.9
90°-120°	596.2	13.6
90°-150°	2025.6	46.3
90°-180°	2801.0	64.1
0°-180°	4372.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	616	616	616	616	616	
5°	616	614	608	612	611	59
15°	587	583	576	578	575	165
25°	531	526	516	518	516	244
35°	458	452	443	439	436	286
45°	373	369	360	353	351	288
55°	282	279	272	264	261	252
65°	190	187	181	176	172	188
75°	100	98	95	92	93	106
85°	24	24	23	21	21	27
90°	1	11	30	28	29	4
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	

TEST NUMBER: P913058

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	616.5	616.5	616.5	616.5	616.5
2.5°	620.0	617.1	610.5	616.5	615.4
5°	616.5	614.2	607.6	612.4	611.2
7.5°	612.4	608.8	602.3	607.0	605.9
10°	605.9	601.7	594.6	599.3	597.5
12.5°	596.9	593.4	586.3	589.2	588.0
15°	586.8	583.4	575.6	578.0	575.0
17.5°	574.4	570.9	563.2	566.1	563.2
20°	560.8	557.2	548.9	550.7	548.3
22.5°	547.2	541.9	534.1	534.1	532.9
25°	531.2	526.4	516.3	517.5	516.3
27.5°	513.3	509.2	501.5	499.8	496.8
30°	495.6	490.8	482.0	480.2	477.8
32.5°	476.6	473.1	463.6	460.0	457.6
35°	458.3	452.3	442.8	439.3	436.3
37.5°	437.5	432.1	422.6	418.5	415.5
40°	416.1	411.4	401.9	396.6	394.2
42.5°	395.4	390.6	381.2	375.3	371.7
45°	372.9	368.8	359.8	353.3	350.9
47.5°	350.9	346.8	337.3	330.7	327.3
50°	327.8	324.9	316.6	308.2	305.3
52.5°	305.3	301.1	293.4	286.9	282.8
55°	282.2	278.6	271.5	264.4	261.4
57.5°	259.0	256.1	248.3	241.3	238.8
60°	235.9	233.6	225.3	218.7	217.0
62.5°	213.4	209.2	203.4	197.4	195.0
65°	190.3	186.7	180.9	175.5	172.5
67.5°	166.6	163.6	158.3	154.2	151.8
70°	144.7	142.3	136.9	132.8	130.5
72.5°	122.2	119.8	116.8	112.6	110.9
75°	99.6	98.5	95.4	91.9	93.1
77.5°	79.5	77.1	75.8	74.1	72.3
80°	59.3	58.7	57.5	55.7	54.5
82.5°	40.3	40.3	39.8	37.4	37.4
85°	24.2	23.7	23.1	21.3	20.8
87.5°	10.7	9.5	8.3	6.6	5.9
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5

TEST NUMBER: P913058

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1

TEST NUMBER: P913058

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.18	7.93	8.25	9.00	10.46	6.74	7.49	7.81	8.56	10.02
	3H	8.81	9.48	9.89	10.56	12.04	8.32	8.99	9.40	10.07	11.55
	4H	9.38	10.01	10.47	11.10	12.58	8.89	9.52	9.97	10.60	12.09
	6H	9.76	10.34	10.85	11.42	12.92	9.25	9.84	10.35	10.92	12.42
	8H	9.85	10.40	10.95	11.50	12.99	9.35	9.90	10.45	11.00	12.49
	12H	9.88	10.41	10.99	11.51	13.02	9.38	9.90	10.48	11.00	12.51
4H	2H	7.62	8.25	8.71	9.33	10.82	7.26	7.90	8.36	8.98	10.46
	3H	9.45	9.98	10.55	11.08	12.58	9.04	9.57	10.14	10.68	12.17
	4H	10.14	10.62	11.25	11.72	13.24	9.71	10.20	10.82	11.30	12.81
	6H	10.62	11.04	11.74	12.16	13.67	10.19	10.61	11.31	11.73	13.24
	8H	10.76	11.15	11.88	12.26	13.79	10.32	10.71	11.44	11.83	13.35
	12H	10.82	11.17	11.95	12.30	13.83	10.37	10.72	11.50	11.85	13.38
8H	4H	10.31	10.70	11.43	11.81	13.34	9.93	10.32	11.05	11.44	12.96
	6H	10.91	11.23	12.05	12.39	13.91	10.52	10.85	11.66	12.00	13.52
	8H	11.11	11.40	12.26	12.53	14.07	10.72	11.00	11.86	12.14	13.68
	12H	11.22	11.47	12.37	12.60	14.18	10.82	11.06	11.96	12.20	13.77
12H	4H	10.29	10.64	11.42	11.77	13.30	9.92	10.27	11.05	11.40	12.93
	6H	10.93	11.22	12.08	12.35	13.89	10.56	10.84	11.70	11.98	13.52
	8H	11.15	11.40	12.30	12.53	14.11	10.77	11.02	11.92	12.15	13.73