

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332668-935

Luminaire Tested: **SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332668-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7404.7 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332668-935
CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332668-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11994	11994	11994
5°	12030	11885	11972
10°	11954	11788	11847
15°	11810	11621	11651
20°	11618	11413	11424
25°	11399	11176	11144
30°	11130	10897	10797
35°	10852	10606	10465
40°	10564	10275	10086
45°	10261	9949	9758
50°	9928	9658	9359
55°	9568	9282	8981
60°	9206	8861	8591
65°	8800	8458	8118
70°	8344	7924	7615
75°	7648	7277	7093
80°	6811	6527	6365
85°	5956	5734	5622



TEST NUMBER: P332668-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.9	1.9
10°-20°	394.2	5.3
20°-30°	580.2	7.8
30°-40°	674.5	9.1
40°-50°	674.5	9.1
50°-60°	590.0	8.0
60°-70°	438.2	5.9
70°-80°	248.9	3.4
80°-90°	75.7	1.0
90°-100°	85.3	1.2
100°-110°	252.7	3.4
110°-120°	428.9	5.8
120°-130°	565.6	7.6
130°-140°	635.2	8.6
140°-150°	624.2	8.4
150°-160°	525.0	7.1
160°-170°	349.3	4.7
170°-180°	122.3	1.7
0°-30°	1114.3	15.0
0°-40°	1788.8	24.2
0°-60°	3053.4	41.2
0°-90°	3816.3	51.5
90°-120°	767.0	10.4
90°-150°	2591.9	35.0
90°-180°	3588.0	48.5
0°-180°	7404.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1486	1486	1486	1486	1486	
5°	1484	1479	1467	1479	1477	141
15°	1413	1408	1390	1397	1394	398
25°	1280	1271	1255	1256	1251	588
35°	1101	1092	1076	1068	1062	688
45°	899	890	871	859	855	693
55°	680	675	660	646	638	609
65°	461	454	443	431	425	456
75°	245	239	233	229	227	261
85°	64	64	62	62	61	71
90°	3	14	22	28	30	7
95°	60	69	76	79	79	67
105°	233	234	238	241	244	247
115°	436	436	434	433	432	430
125°	635	635	634	632	630	566
135°	819	825	825	823	820	634
145°	995	999	1000	999	996	623
155°	1140	1140	1139	1143	1139	524
165°	1241	1238	1236	1242	1238	350
175°	1291	1287	1285	1292	1285	123
180°	1293	1293	1293	1293	1293	



TEST NUMBER: P332668-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1489.4	1488.8	1488.2	1487.5	1486.9	1485.4	1483.1	1480.7	1478.4	1476.1	1478.3
5°	1484.5	1483.4	1482.4	1481.3	1480.2	1478.3	1475.3	1472.4	1469.6	1466.6	1469.6
7.5°	1470.7	1469.6	1468.5	1467.5	1466.5	1464.3	1461.0	1457.8	1454.6	1451.4	1453.7
10°	1458.3	1457.2	1456.1	1455.1	1454.1	1451.8	1448.4	1444.9	1441.5	1438.0	1440.1
12.5°	1442.1	1441.1	1439.9	1438.9	1437.9	1435.5	1431.8	1428.2	1424.5	1420.9	1423.2
15°	1413.1	1412.0	1410.9	1409.9	1408.8	1406.3	1402.3	1398.4	1394.4	1390.4	1392.0
17.5°	1378.0	1376.7	1375.4	1374.1	1372.8	1370.2	1366.4	1362.7	1358.9	1355.2	1356.2
20°	1352.3	1351.0	1349.7	1348.3	1347.0	1344.4	1340.4	1336.4	1332.5	1328.5	1329.3
22.5°	1324.7	1322.9	1321.2	1319.5	1317.8	1314.8	1310.9	1306.9	1303.0	1299.0	1300.5
25°	1279.7	1277.9	1276.0	1274.1	1272.3	1269.5	1265.8	1262.1	1258.4	1254.7	1255.0
27.5°	1228.3	1226.4	1224.4	1222.5	1220.6	1218.0	1214.5	1211.1	1207.6	1204.2	1203.6
30°	1194.0	1191.9	1189.7	1187.7	1185.5	1182.8	1179.3	1175.9	1172.4	1169.0	1167.9
32.5°	1157.8	1155.9	1154.0	1152.1	1150.2	1147.4	1143.8	1140.1	1136.4	1132.8	1131.5
35°	1101.1	1099.3	1097.4	1095.6	1093.7	1091.0	1087.3	1083.6	1079.9	1076.2	1074.3
37.5°	1041.4	1039.7	1038.0	1036.3	1034.6	1031.8	1027.8	1023.8	1019.9	1015.9	1013.9
40°	1002.4	1000.2	998.1	996.0	993.9	990.8	986.9	982.9	979.0	975.0	972.3
42.5°	960.4	959.2	957.9	956.7	955.4	952.5	948.1	943.7	939.4	935.0	931.9
45°	898.8	896.9	895.1	893.2	891.4	888.3	884.1	879.9	875.6	871.4	868.5
47.5°	834.2	833.0	831.7	830.4	829.1	826.6	822.7	818.7	814.9	810.9	807.6
50°	790.5	789.4	788.3	787.3	786.2	783.9	780.2	776.4	772.7	769.0	765.3
52.5°	747.6	746.3	745.0	743.8	742.5	739.9	736.0	732.1	728.1	724.3	721.0
55°	679.8	678.9	678.1	677.3	676.6	674.3	670.6	666.9	663.2	659.5	656.3
57.5°	615.0	614.1	613.2	612.3	611.4	609.1	605.5	601.8	598.1	594.5	591.5
60°	570.2	568.9	567.6	566.3	564.9	562.6	559.1	555.7	552.2	548.8	546.4
62.5°	526.4	525.3	524.2	523.1	521.9	519.6	515.9	512.3	508.6	505.0	502.8
65°	460.7	459.3	458.1	456.8	455.4	453.4	450.7	448.2	445.5	442.8	440.2
67.5°	394.5	393.3	392.1	390.9	389.6	387.8	385.2	382.7	380.1	377.6	375.1
70°	353.5	351.7	349.8	348.0	346.1	344.1	342.1	339.9	337.9	335.7	333.6
72.5°	309.8	307.9	306.1	304.2	302.4	300.6	298.9	297.2	295.5	293.8	292.1
75°	245.2	243.9	242.5	241.3	240.0	238.6	237.3	236.0	234.6	233.3	232.3
77.5°	183.6	183.0	182.4	181.8	181.2	180.4	179.2	178.1	176.8	175.7	175.4
80°	146.5	145.6	144.8	144.0	143.3	142.6	142.1	141.5	141.0	140.4	139.9
82.5°	110.2	109.9	109.5	109.1	108.7	108.5	108.4	108.3	108.2	108.1	107.8
85°	64.3	64.3	64.3	64.3	64.3	64.1	63.5	62.9	62.4	61.9	61.9
87.5°	25.4	25.7	25.9	26.2	26.4	26.7	26.9	26.9	27.1	27.3	27.6
90°	3.0	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3
92.5°	21.4	24.2	27.0	29.8	32.6	34.6	35.9	37.1	38.4	39.6	40.4
95°	60.0	62.0	64.1	66.0	68.0	69.8	71.4	72.9	74.5	76.0	76.7
97.5°	104.9	106.4	108.1	109.6	111.2	113.0	114.8	116.6	118.4	120.2	121.1
100°	140.1	140.9	141.8	142.7	143.6	145.1	147.1	149.0	151.0	153.1	153.5
102.5°	176.8	177.2	177.5	177.9	178.3	179.3	181.2	183.0	184.9	186.7	187.3
105°	233.1	233.3	233.5	233.8	233.9	234.5	235.4	236.3	237.2	238.1	238.8
107.5°	292.1	292.4	292.7	292.9	293.2	293.3	293.5	293.6	293.8	293.9	294.5
110°	332.1	332.5	332.9	333.5	333.9	334.0	333.8	333.6	333.3	333.1	332.7



TEST NUMBER: P332668-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.7	373.8	373.9	374.0	374.1	373.9	373.5	373.2	372.7	372.3	372.2
115°	436.1	436.1	436.1	436.1	436.1	435.9	435.5	435.1	434.5	434.1	433.9
117.5°	495.0	495.2	495.3	495.5	495.7	495.6	495.2	495.0	494.6	494.4	493.6
120°	534.2	535.0	536.0	536.8	537.7	537.9	537.2	536.5	535.8	535.2	534.1
122.5°	575.0	575.3	575.7	576.0	576.4	576.4	576.1	575.8	575.5	575.1	574.5
125°	635.2	635.2	635.2	635.2	635.2	635.1	634.9	634.6	634.4	634.2	633.8
127.5°	689.8	690.5	691.1	691.8	692.5	692.7	692.2	691.9	691.6	691.2	690.8
130°	728.2	728.9	729.5	730.2	730.9	731.2	731.2	731.2	731.2	731.2	730.8
132.5°	767.4	767.9	768.4	768.9	769.4	769.6	769.4	769.2	769.0	768.9	768.4
135°	819.2	820.6	821.9	823.3	824.6	825.3	825.3	825.3	825.3	825.3	824.8
137.5°	875.6	876.3	876.9	877.5	878.1	878.7	879.0	879.3	879.7	880.0	879.5
140°	913.3	913.7	914.2	914.6	915.1	915.2	915.2	915.2	915.2	915.2	915.1
142.5°	947.7	948.1	948.6	949.0	949.5	949.6	949.4	949.3	949.1	948.9	948.8
145°	995.3	996.2	997.1	998.0	998.8	999.4	999.6	999.9	1000.1	1000.3	1000.1
147.5°	1042.5	1043.6	1044.7	1045.7	1046.8	1047.2	1047.1	1046.9	1046.7	1046.5	1046.4
150°	1071.3	1072.2	1073.2	1074.0	1074.9	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3
152.5°	1098.5	1099.1	1099.6	1100.1	1100.7	1101.0	1101.2	1101.4	1101.6	1101.7	1102.3
155°	1140.3	1140.3	1140.3	1140.3	1140.3	1140.2	1140.1	1139.8	1139.5	1139.4	1140.2
157.5°	1175.5	1175.2	1174.7	1174.4	1174.0	1173.7	1173.7	1173.6	1173.6	1173.5	1174.2
160°	1196.4	1196.2	1195.9	1195.7	1195.5	1195.2	1195.1	1194.8	1194.6	1194.4	1195.1
162.5°	1215.6	1215.0	1214.4	1213.8	1213.2	1212.9	1212.6	1212.5	1212.2	1211.9	1213.1
165°	1241.4	1240.7	1240.0	1239.4	1238.7	1238.1	1237.7	1237.3	1236.8	1236.4	1237.7
167.5°	1261.2	1260.2	1259.3	1258.4	1257.5	1257.0	1257.1	1257.1	1257.1	1257.1	1258.5
170°	1272.4	1271.3	1270.1	1269.0	1267.9	1267.5	1267.7	1267.9	1268.2	1268.4	1269.7
172.5°	1280.4	1279.4	1278.5	1277.6	1276.7	1276.2	1276.3	1276.3	1276.3	1276.4	1277.9
175°	1291.4	1290.3	1289.2	1288.1	1286.9	1286.2	1286.1	1285.8	1285.6	1285.4	1286.9
177.5°	1295.0	1294.1	1293.2	1292.4	1291.4	1291.0	1291.0	1291.0	1291.0	1291.0	1292.3
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332668-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1480.3	1482.5	1484.6	1485.6	1485.3	1485.1	1484.9	1484.7
5°	1472.4	1475.3	1478.3	1479.5	1478.9	1478.3	1477.8	1477.3
7.5°	1456.0	1458.4	1460.7	1461.7	1461.4	1461.0	1460.7	1460.4
10°	1442.3	1444.4	1446.5	1447.3	1446.7	1446.2	1445.7	1445.2
12.5°	1425.6	1427.9	1430.2	1431.0	1430.3	1429.5	1428.7	1428.1
15°	1393.6	1395.2	1396.8	1397.1	1396.4	1395.6	1394.8	1394.0
17.5°	1357.2	1358.2	1359.2	1359.4	1358.9	1358.4	1357.9	1357.3
20°	1330.1	1330.9	1331.7	1331.8	1331.3	1330.8	1330.2	1329.7
22.5°	1301.8	1303.3	1304.7	1304.9	1304.0	1303.0	1302.1	1301.1
25°	1255.3	1255.5	1255.8	1255.3	1254.3	1253.3	1252.2	1251.1
27.5°	1203.0	1202.3	1201.7	1200.8	1199.4	1198.1	1196.7	1195.4
30°	1166.9	1165.8	1164.8	1163.6	1162.3	1160.9	1159.6	1158.3
32.5°	1130.2	1129.0	1127.7	1126.4	1125.1	1123.8	1122.5	1121.1
35°	1072.5	1070.6	1068.8	1067.1	1065.8	1064.5	1063.2	1061.9
37.5°	1011.8	1009.9	1007.9	1006.0	1004.3	1002.5	1000.7	999.0
40°	969.7	967.0	964.4	962.4	961.0	959.8	958.5	957.1
42.5°	928.8	925.7	922.6	920.7	919.8	918.9	918.0	917.1
45°	865.6	862.6	859.7	857.9	857.1	856.4	855.5	854.7
47.5°	804.3	801.1	797.8	795.1	793.2	791.1	789.1	787.1
50°	761.6	757.9	754.2	751.6	749.9	748.4	746.8	745.2
52.5°	717.7	714.4	711.1	708.5	706.5	704.5	702.5	700.4
55°	653.2	650.0	646.8	644.5	642.8	641.3	639.6	638.1
57.5°	588.5	585.5	582.5	580.1	578.6	577.1	575.6	574.0
60°	544.1	541.7	539.2	537.4	536.1	534.8	533.5	532.1
62.5°	500.7	498.4	496.3	494.6	493.3	491.9	490.6	489.3
65°	437.6	434.9	432.2	430.2	429.0	427.7	426.3	425.0
67.5°	372.6	370.0	367.5	366.0	365.6	365.2	364.9	364.5
70°	331.5	329.3	327.3	325.8	325.0	324.2	323.4	322.6
72.5°	290.4	288.7	287.1	285.8	285.0	284.2	283.4	282.6
75°	231.2	230.1	229.1	228.4	228.2	227.9	227.6	227.4
77.5°	175.0	174.8	174.4	173.9	173.2	172.5	171.9	171.2
80°	139.4	138.9	138.4	137.9	137.7	137.4	137.2	136.9
82.5°	107.5	107.1	106.9	106.5	106.2	106.0	105.7	105.5
85°	61.9	61.9	61.9	61.7	61.5	61.2	61.0	60.7
87.5°	27.8	28.1	28.3	28.5	28.6	28.7	28.8	28.8
90°	24.7	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	41.2	42.0	42.8	43.3	43.7	43.9	44.2	44.4
95°	77.3	78.0	78.7	79.0	79.0	79.0	79.0	79.0
97.5°	121.8	122.6	123.5	123.8	123.8	123.8	123.8	123.8
100°	153.9	154.4	154.8	155.1	155.1	155.1	155.1	155.1
102.5°	187.9	188.6	189.2	189.5	189.8	189.9	190.1	190.3
105°	239.4	240.0	240.7	241.4	242.1	242.7	243.4	244.1
107.5°	295.2	295.8	296.4	296.7	296.6	296.6	296.5	296.5
110°	332.2	331.7	331.3	331.4	332.1	332.8	333.5	334.1



TEST NUMBER: P332668-935

CATALOG NUMBER: SA4XXDIP-C1020D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	372.1	372.0	372.0	372.0	372.1	372.2	372.4	372.6
115°	433.7	433.4	433.3	433.0	432.8	432.6	432.4	432.1
117.5°	492.8	492.1	491.3	490.8	490.3	489.8	489.4	489.0
120°	533.0	531.8	530.7	530.4	530.8	531.2	531.8	532.2
122.5°	573.7	572.9	572.1	571.4	570.6	569.8	568.9	568.2
125°	633.3	632.8	632.4	632.0	631.5	631.1	630.6	630.2
127.5°	690.3	689.9	689.4	689.1	688.7	688.3	687.9	687.6
130°	730.3	729.9	729.4	728.8	727.9	727.0	726.1	725.2
132.5°	767.9	767.5	767.1	766.6	766.3	765.9	765.6	765.3
135°	824.4	823.9	823.5	822.9	822.3	821.6	820.9	820.3
137.5°	878.9	878.3	877.8	877.5	877.7	877.8	878.0	878.0
140°	914.8	914.6	914.4	914.2	914.0	913.7	913.5	913.3
142.5°	948.8	948.7	948.7	948.6	948.6	948.6	948.6	948.5
145°	999.9	999.6	999.4	998.9	998.3	997.6	997.0	996.3
147.5°	1046.2	1046.0	1045.8	1045.6	1045.4	1045.2	1044.9	1044.7
150°	1075.3	1075.3	1075.3	1075.2	1075.0	1074.8	1074.5	1074.4
152.5°	1102.8	1103.4	1103.9	1103.9	1103.3	1102.7	1102.1	1101.6
155°	1141.2	1142.0	1142.9	1142.9	1142.0	1141.2	1140.2	1139.4
157.5°	1174.9	1175.5	1176.2	1176.2	1175.4	1174.7	1173.9	1173.2
160°	1195.7	1196.4	1197.0	1196.8	1195.7	1194.6	1193.5	1192.4
162.5°	1214.4	1215.6	1216.8	1216.9	1215.7	1214.6	1213.5	1212.4
165°	1239.1	1240.4	1241.7	1241.9	1241.0	1240.2	1239.2	1238.4
167.5°	1259.8	1261.2	1262.5	1262.5	1261.1	1259.7	1258.4	1257.0
170°	1271.1	1272.4	1273.8	1273.6	1272.0	1270.5	1268.9	1267.4
172.5°	1279.4	1280.9	1282.5	1282.5	1280.8	1279.3	1277.7	1276.2
175°	1288.5	1290.0	1291.6	1291.6	1290.0	1288.5	1286.9	1285.4
177.5°	1293.5	1294.8	1296.0	1295.9	1294.4	1293.0	1291.6	1290.2
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4

(END OF REPORT)