

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332645-935

Luminaire Tested: **SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332645-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6458.4 lumens  
Efficiency: N/A  
Efficacy: 118.7 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332645-935  
CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48	44
3	84	74	67	61	78	70	64	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	44	39	44	39	35	38	34	31	29
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	22
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11599	11599	11599	11599
5°	13661	11629	10264	11629
10°	16356	11579	9241	11579
15°	19351	11462	8487	11462
20°	21549	11342	7814	11342
25°	21896	11166	7349	11166
30°	18632	10997	7202	10997
35°	14325	10723	7203	10723
40°	11166	10400	7339	10400
45°	9310	9914	7462	9914
50°	8194	9323	7714	9323
55°	7506	8612	8025	8612
60°	7035	7976	8399	7976
65°	6550	7265	8709	7265
70°	5986	6559	8908	6559
75°	5346	5774	8799	5774
80°	4482	4733	8522	4733
85°	3307	3418	8160	3418



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.0	2.2
10°-20°	431.5	6.7
20°-30°	684.2	10.6
30°-40°	761.4	11.8
40°-50°	693.1	10.7
50°-60°	566.4	8.8
60°-70°	404.3	6.3
70°-80°	222.6	3.4
80°-90°	62.7	1.0
90°-100°	247.5	3.8
100°-110°	515.1	8.0
110°-120°	461.4	7.1
120°-130°	388.1	6.0
130°-140°	323.6	5.0
140°-150°	247.2	3.8
150°-160°	173.8	2.7
160°-170°	102.2	1.6
170°-180°	33.3	0.5
0°-30°	1255.6	19.4
0°-40°	2017.1	31.2
0°-60°	3276.5	50.7
0°-90°	3966.2	61.4
90°-120°	1224.0	19.0
90°-150°	2183.0	33.8
90°-180°	2492.0	38.6
0°-180°	6458.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1437	1437	1437	1437	1437	
5°	1686	1435	1267	1435	1686	171
15°	2315	1371	1016	1371	2315	654
25°	2458	1254	825	1254	2458	1084
35°	1454	1088	731	1088	1454	923
45°	816	868	654	868	816	642
55°	533	612	570	612	533	482
65°	343	380	456	380	343	339
75°	171	185	282	185	171	182
85°	36	37	88	37	36	44
90°	14	1	14	1	14	13
95°	164	22	164	22	164	255
105°	947	79	947	79	947	937
115°	910	139	910	139	910	903
125°	726	193	726	193	726	659
135°	649	230	649	230	649	501
145°	530	265	530	265	530	336
155°	444	301	444	301	444	207
165°	387	328	387	328	387	111
175°	349	342	349	342	349	34
180°	343	343	343	343	343	



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1529.2	1528.8	1524.0	1523.0	1519.7	1515.4	1514.5	1506.8	1491.6	1484.5	1482.6
5°	1685.7	1697.5	1682.0	1679.1	1677.3	1657.7	1647.5	1635.6	1608.3	1592.2	1579.7
7.5°	1872.3	1873.7	1867.0	1861.5	1846.3	1829.2	1803.5	1776.2	1743.5	1709.6	1683.9
10°	1995.2	1999.9	1992.2	1991.0	1960.7	1941.6	1903.5	1871.4	1834.4	1793.4	1755.9
12.5°	2124.7	2118.0	2114.1	2088.6	2083.0	2048.2	2004.0	1970.9	1914.0	1866.7	1816.8
15°	2315.4	2302.3	2294.0	2258.8	2241.6	2193.4	2146.3	2110.1	2035.7	1964.8	1911.2
17.5°	2427.2	2440.4	2421.1	2406.7	2362.1	2328.2	2280.2	2204.0	2145.8	2057.8	1990.2
20°	2508.3	2509.4	2498.7	2483.8	2448.7	2405.9	2353.5	2270.1	2200.5	2113.0	2020.2
22.5°	2530.1	2530.4	2525.8	2511.9	2485.4	2450.6	2397.8	2328.2	2243.9	2148.7	2055.9
25°	2458.2	2455.8	2461.3	2476.7	2466.6	2455.8	2425.5	2373.7	2295.2	2194.5	2094.6
27.5°	2191.1	2207.5	2237.7	2275.9	2312.6	2340.5	2348.4	2337.8	2289.1	2206.3	2101.6
30°	1998.7	2019.0	2041.6	2079.7	2153.4	2195.7	2242.2	2277.3	2257.6	2191.6	2094.0
32.5°	1787.3	1792.3	1825.9	1869.2	1936.8	2018.1	2091.7	2163.0	2186.7	2152.1	2070.6
35°	1453.5	1461.8	1498.1	1541.0	1623.8	1723.1	1833.8	1932.7	2014.2	2046.9	2005.3
37.5°	1186.1	1210.0	1235.7	1281.8	1354.6	1444.1	1559.1	1687.0	1808.5	1889.9	1903.8
40°	1059.5	1074.4	1092.8	1127.9	1189.8	1277.9	1376.7	1523.2	1652.3	1769.0	1807.1
42.5°	959.5	968.2	979.5	1011.2	1058.4	1146.0	1236.2	1365.0	1494.7	1634.2	1698.1
45°	815.5	824.4	843.4	861.9	897.6	958.3	1042.2	1148.1	1278.5	1413.1	1530.9
47.5°	711.4	717.1	728.4	748.2	778.5	818.6	886.8	975.3	1096.1	1226.8	1352.3
50°	652.4	657.1	666.1	683.9	707.1	742.8	798.7	881.5	976.1	1107.7	1230.9
52.5°	605.7	607.6	614.2	626.3	644.7	674.8	720.7	789.1	877.1	994.4	1117.1
55°	533.3	535.7	541.7	550.6	566.6	585.7	620.8	672.0	748.8	850.6	957.1
57.5°	473.8	475.4	480.4	483.9	497.1	512.6	539.6	576.2	634.4	720.7	815.8
60°	435.7	434.5	440.5	443.4	452.4	465.5	486.3	521.4	572.0	641.6	729.1
62.5°	398.6	396.9	401.9	405.8	411.0	422.1	439.1	466.7	507.7	570.7	646.3
65°	342.9	340.4	343.5	348.2	352.9	359.0	371.4	395.8	428.5	473.8	531.5
67.5°	286.9	289.4	289.9	292.2	295.0	303.1	311.7	328.9	352.0	388.2	437.1
70°	253.6	254.2	256.6	256.6	258.3	265.4	272.6	282.8	305.3	338.7	378.6
72.5°	220.2	222.7	221.8	223.7	225.0	229.7	235.0	244.6	263.9	288.7	322.4
75°	171.4	173.2	173.2	173.8	175.6	177.4	181.5	188.6	202.3	220.8	244.0
77.5°	125.0	125.3	126.1	128.2	128.2	131.0	134.1	139.9	146.6	159.3	173.4
80°	96.4	97.6	97.0	98.2	98.2	100.6	101.8	108.9	111.9	120.2	131.6
82.5°	70.7	71.9	71.8	73.4	74.4	74.9	76.5	79.4	82.4	89.7	94.4
85°	35.7	36.9	35.7	36.9	38.7	39.3	41.1	41.7	44.1	45.8	50.0
87.5°	13.3	14.7	14.9	15.2	16.0	16.5	16.9	16.3	18.0	18.6	20.2
90°	14.1	14.1	14.8	14.1	13.4	13.4	12.8	12.1	11.5	12.1	10.8
92.5°	51.8	51.8	54.2	57.8	65.7	79.2	99.5	132.2	177.9	213.5	186.9
95°	164.3	173.1	185.1	206.0	239.0	304.3	394.5	498.9	564.2	548.7	414.1
97.5°	439.1	453.1	473.3	513.8	562.1	632.4	698.3	737.0	708.8	577.9	387.5
100°	617.3	622.8	642.9	684.0	742.6	792.4	825.4	811.9	713.6	541.3	351.5
102.5°	772.5	776.8	798.1	827.9	863.8	884.5	874.9	808.1	673.2	495.5	327.2
105°	947.3	951.3	960.7	966.1	964.8	937.1	870.5	754.1	599.9	441.6	306.3
107.5°	1012.1	1010.4	1003.7	988.3	955.0	895.0	801.2	677.2	540.6	411.5	302.6
110°	1013.2	1007.2	995.1	966.7	918.9	844.9	747.3	630.9	511.0	401.2	303.6



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	981.5	971.6	954.7	920.4	866.2	792.1	699.9	596.9	494.3	396.4	306.9
115°	909.6	904.1	882.6	842.2	789.0	724.4	645.7	562.8	478.6	393.8	313.1
117.5°	836.7	832.5	810.7	776.8	731.4	676.6	614.7	546.1	471.7	393.1	319.7
120°	795.7	788.3	770.9	741.2	702.8	655.0	601.2	538.6	467.9	393.1	324.5
122.5°	763.4	756.0	741.2	715.9	683.5	641.6	592.5	532.1	463.6	392.6	329.3
125°	725.7	721.7	708.9	689.4	662.5	625.4	579.0	521.1	456.4	391.8	336.7
127.5°	703.7	699.6	688.9	671.5	644.5	609.2	562.9	507.6	446.9	390.4	342.4
130°	690.8	686.7	676.0	659.1	631.5	595.8	550.0	496.9	441.0	389.8	346.7
132.5°	676.2	672.2	661.9	642.9	615.9	580.2	535.5	485.5	435.6	389.3	350.5
135°	649.0	645.0	634.2	615.4	588.4	554.7	513.7	469.9	427.5	388.5	356.1
137.5°	615.4	610.4	601.6	583.0	557.8	527.4	492.8	455.8	420.5	388.3	359.5
140°	591.1	585.7	576.3	561.5	538.0	509.6	479.3	447.7	416.7	387.8	362.2
142.5°	565.2	561.5	553.1	539.4	518.5	494.0	468.0	440.1	413.5	387.8	364.4
145°	529.9	526.5	519.7	508.3	491.5	472.6	452.5	429.6	407.9	386.4	365.6
147.5°	498.4	497.2	492.1	482.3	469.9	455.1	438.9	420.8	403.0	384.0	366.3
150°	480.7	480.0	476.0	467.3	456.4	444.4	430.8	415.3	399.2	382.4	366.3
152.5°	464.5	463.8	461.4	454.3	445.1	435.1	422.8	409.5	394.9	379.7	365.2
155°	443.7	443.7	441.6	436.3	429.6	421.5	411.4	400.5	388.5	375.7	363.5
157.5°	425.3	425.3	424.1	420.1	415.0	408.5	400.0	391.0	381.9	371.5	361.8
160°	414.1	414.1	413.4	409.3	405.3	399.9	392.5	385.1	377.0	368.2	360.2
162.5°	403.3	403.8	403.1	399.1	396.1	391.3	385.5	379.2	372.7	365.1	358.6
165°	387.1	387.8	388.5	385.7	383.1	379.7	375.0	370.9	365.6	360.2	355.5
167.5°	374.3	374.9	375.0	373.2	371.9	369.9	366.1	363.0	359.1	355.3	352.2
170°	366.3	366.3	366.9	366.3	364.9	362.9	360.2	358.2	354.8	352.1	350.1
172.5°	358.2	359.2	359.9	359.2	358.4	357.0	355.3	353.9	351.0	348.9	347.9
175°	348.7	350.1	351.5	350.1	350.1	350.1	348.7	348.1	346.7	345.3	345.3
177.5°	343.2	344.3	345.3	344.8	345.3	344.8	344.8	344.3	343.7	343.2	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1483.1	1476.4	1471.6	1467.8	1457.3	1451.1	1446.4	1439.7	1432.1	1424.0	1414.0
5°	1567.2	1547.0	1532.1	1509.5	1488.1	1470.2	1451.7	1435.0	1414.8	1392.8	1376.7
7.5°	1655.6	1625.6	1587.0	1553.5	1515.9	1483.2	1453.9	1423.8	1392.7	1362.4	1334.7
10°	1711.8	1673.2	1630.3	1579.7	1532.1	1489.8	1450.5	1412.5	1375.5	1338.6	1307.1
12.5°	1772.3	1724.1	1660.8	1601.6	1548.3	1491.8	1444.3	1397.7	1353.1	1314.3	1277.6
15°	1853.5	1783.8	1710.6	1631.5	1561.3	1495.2	1430.3	1371.4	1321.4	1270.1	1234.5
17.5°	1903.4	1817.2	1733.5	1650.8	1565.7	1482.5	1412.5	1344.5	1281.9	1231.1	1186.0
20°	1936.2	1850.5	1746.4	1663.6	1562.5	1476.7	1395.8	1320.2	1254.7	1200.6	1154.1
22.5°	1964.8	1865.8	1761.6	1652.7	1552.0	1461.0	1372.4	1296.4	1229.5	1172.4	1127.9
25°	1980.3	1866.6	1753.5	1645.2	1530.9	1423.1	1342.8	1253.5	1182.1	1122.0	1074.4
27.5°	1981.9	1860.4	1732.4	1612.1	1494.1	1393.8	1292.4	1212.5	1138.4	1074.9	1029.2
30°	1976.7	1849.9	1712.4	1582.1	1463.6	1354.7	1266.6	1179.7	1104.1	1041.0	993.4
32.5°	1960.1	1828.0	1686.7	1548.8	1426.0	1319.5	1228.6	1145.9	1072.2	1010.0	960.1
35°	1911.9	1781.5	1630.9	1487.5	1361.8	1254.1	1172.0	1088.0	1014.3	955.3	907.1
37.5°	1836.5	1718.6	1565.6	1417.1	1293.7	1185.5	1104.1	1028.3	961.7	901.9	852.5
40°	1770.7	1667.2	1513.6	1369.0	1235.7	1132.7	1056.5	986.9	920.8	864.3	817.3
42.5°	1695.1	1604.8	1463.2	1309.9	1181.4	1078.0	1003.7	941.2	878.9	826.6	779.6
45°	1560.0	1500.6	1367.2	1225.5	1091.7	994.0	923.2	868.4	816.1	764.8	725.6
47.5°	1404.8	1375.3	1263.1	1128.5	1001.4	905.2	843.8	793.2	747.3	703.9	669.3
50°	1300.5	1286.2	1189.2	1059.5	938.1	847.6	785.7	742.3	702.9	664.9	632.1
52.5°	1197.7	1197.2	1109.7	990.9	878.6	791.4	730.0	689.4	655.3	624.4	595.0
55°	1040.4	1057.1	988.7	882.7	782.1	703.5	648.2	611.9	588.1	562.5	540.4
57.5°	896.0	923.7	867.2	773.9	690.0	617.6	569.4	542.1	516.8	501.3	485.3
60°	801.8	827.9	783.9	705.3	626.2	564.3	518.4	494.0	472.0	461.3	450.0
62.5°	718.0	741.3	708.7	635.8	567.1	507.6	468.9	445.5	430.6	418.9	411.4
65°	598.2	617.9	589.9	536.9	477.9	430.3	398.8	380.3	366.1	361.3	352.9
67.5°	483.5	501.4	486.3	441.3	394.0	358.0	333.3	315.6	307.1	303.0	297.0
70°	415.4	433.3	417.2	378.0	341.6	311.3	288.1	277.9	269.1	267.3	258.9
72.5°	357.8	370.0	354.0	323.2	292.1	266.6	248.6	238.0	233.3	230.1	225.6
75°	268.5	279.1	268.5	244.6	222.6	204.7	189.2	185.1	179.8	178.0	175.0
77.5°	190.0	199.2	191.1	176.2	159.7	145.9	137.6	132.2	131.0	127.9	129.4
80°	145.3	151.2	143.4	133.4	120.2	110.7	104.8	101.8	98.2	97.0	99.4
82.5°	104.3	106.9	103.0	96.2	86.4	80.2	76.2	72.8	72.0	72.2	72.2
85°	54.2	53.6	53.0	47.0	44.1	39.9	37.5	36.9	36.3	37.5	38.7
87.5°	20.0	20.5	19.2	17.3	15.7	14.1	13.3	12.5	13.3	14.1	14.7
90°	9.4	9.4	5.4	5.4	4.7	4.0	2.0	0.7	2.0	4.0	4.7
92.5°	136.0	83.8	49.5	35.6	25.7	17.5	11.2	7.7	11.2	17.5	25.7
95°	253.1	142.8	84.1	55.9	39.7	31.0	24.2	22.2	24.2	31.0	39.7
97.5°	227.6	136.4	91.3	67.6	53.7	45.6	39.9	39.9	39.9	45.6	53.7
100°	214.1	138.0	98.3	76.7	64.0	55.9	51.1	51.1	51.1	55.9	64.0
102.5°	210.3	143.4	107.5	87.0	74.7	67.2	63.0	61.9	63.0	67.2	74.7
105°	212.1	156.2	123.9	104.4	92.2	84.1	80.8	78.8	80.8	84.1	92.2
107.5°	222.1	171.2	141.5	122.3	110.6	102.0	98.7	97.4	98.7	102.0	110.6
110°	229.5	182.4	152.8	134.7	122.5	114.4	111.1	109.8	111.1	114.4	122.5





TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	237.6	193.2	164.7	146.5	134.4	126.8	123.0	121.6	123.0	126.8	134.4
115°	250.5	210.1	183.1	165.0	152.1	145.4	140.7	138.7	140.7	145.4	152.1
117.5°	263.5	226.4	200.8	181.9	170.0	162.6	158.3	156.4	158.3	162.6	170.0
120°	272.7	237.6	212.1	193.2	181.8	174.4	169.6	168.3	169.6	174.4	181.8
122.5°	281.3	248.4	222.8	204.5	192.0	185.1	180.5	179.1	180.5	185.1	192.0
125°	294.2	263.2	239.0	220.2	207.3	199.9	195.9	193.2	195.9	199.9	207.3
127.5°	305.4	277.0	253.6	234.5	221.2	212.8	207.9	205.8	207.9	212.8	221.2
130°	312.4	286.1	263.2	243.7	230.9	220.8	215.4	212.8	215.4	220.8	230.9
132.5°	319.3	293.7	270.8	252.4	238.5	228.9	221.9	219.7	221.9	228.9	238.5
135°	328.6	304.3	282.1	264.6	250.5	239.0	232.3	229.5	232.3	239.0	250.5
137.5°	335.0	312.4	291.6	274.9	260.3	249.3	241.9	239.4	241.9	249.3	260.3
140°	339.3	317.8	297.6	281.4	267.3	255.8	248.4	246.4	248.4	255.8	267.3
142.5°	342.5	322.6	303.0	287.3	273.7	262.9	256.0	253.9	256.0	262.9	273.7
145°	346.0	327.9	310.4	295.6	282.8	273.4	266.6	264.6	266.6	273.4	282.8
147.5°	349.1	333.3	316.8	303.5	292.8	283.2	277.2	276.6	277.2	283.2	292.8
150°	350.8	336.0	321.2	308.3	298.3	290.2	284.8	284.1	284.8	290.2	298.3
152.5°	351.8	338.1	324.9	313.2	304.2	296.6	291.3	291.1	291.3	296.6	304.2
155°	352.8	341.3	329.8	319.8	312.4	305.7	301.6	300.9	301.6	305.7	312.4
157.5°	352.8	343.6	333.9	326.0	319.5	314.3	310.5	310.5	310.5	314.3	319.5
160°	352.8	344.7	336.7	329.2	323.8	319.1	316.4	316.4	316.4	319.1	323.8
162.5°	352.8	345.8	338.2	332.4	327.6	323.4	321.2	321.8	321.2	323.4	327.6
165°	351.5	346.0	340.0	336.0	332.6	329.2	327.9	327.9	327.9	329.2	332.6
167.5°	349.8	345.9	341.5	338.4	336.5	333.9	333.3	333.9	333.3	333.9	336.5
170°	348.7	345.3	342.0	340.0	338.6	336.7	336.0	336.7	336.0	336.7	338.6
172.5°	347.7	344.8	342.5	341.0	340.3	338.8	338.6	339.3	338.6	338.8	340.3
175°	346.0	344.1	342.7	342.7	342.0	341.3	341.3	342.0	341.3	341.3	342.0
177.5°	344.3	343.2	342.7	342.7	342.7	342.2	342.7	343.2	342.7	342.2	342.7
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1409.2	1405.0	1398.8	1390.2	1383.0	1375.4	1373.6	1370.6	1376.4	1371.6	1370.2
5°	1363.0	1350.6	1334.5	1316.0	1305.3	1289.9	1286.9	1280.9	1275.0	1274.4	1268.4
7.5°	1314.1	1295.8	1274.7	1255.9	1238.5	1221.6	1210.6	1208.2	1199.4	1194.2	1188.3
10°	1282.7	1260.1	1235.7	1217.8	1197.6	1179.7	1167.3	1160.1	1154.1	1147.5	1141.6
12.5°	1245.5	1221.5	1201.4	1182.1	1158.0	1144.4	1123.9	1111.5	1110.3	1110.4	1094.9
15°	1202.3	1178.5	1147.5	1120.2	1107.1	1080.9	1069.6	1055.3	1046.4	1037.4	1030.4
17.5°	1153.0	1123.3	1099.2	1067.7	1042.7	1021.8	1007.0	998.4	985.0	972.3	963.2
20°	1122.0	1090.5	1064.8	1031.5	1004.1	978.5	966.0	954.2	944.0	933.3	923.2
22.5°	1090.5	1057.6	1026.2	993.9	968.5	941.4	929.4	913.2	903.5	897.6	887.4
25°	1041.0	1005.3	969.6	938.7	912.5	888.6	872.6	860.1	849.4	844.6	838.1
27.5°	987.2	951.7	917.2	882.1	852.4	835.1	822.3	812.8	806.7	800.3	797.4
30°	953.0	916.0	879.2	846.4	819.0	801.8	789.9	783.3	778.5	775.6	772.6
32.5°	918.2	881.8	842.9	813.0	788.5	773.2	764.1	757.6	755.2	754.1	753.0
35°	862.5	825.5	789.9	763.1	739.9	733.9	726.2	722.6	721.4	725.6	727.4
37.5°	808.6	774.3	741.4	715.4	700.3	691.6	688.9	689.1	693.3	697.0	701.3
40°	773.8	740.5	709.5	686.9	672.6	667.3	666.1	669.0	673.8	678.0	682.7
42.5°	739.9	707.1	679.0	657.8	647.8	642.9	643.7	646.6	653.3	658.4	665.6
45°	687.5	660.1	632.7	615.4	607.1	608.3	608.3	613.6	620.2	627.9	635.7
47.5°	638.1	610.4	588.0	573.4	569.1	568.1	571.4	578.4	587.8	597.4	608.2
50°	604.8	578.5	558.9	545.8	541.1	542.9	547.6	554.1	565.4	577.4	588.7
52.5°	570.9	547.1	528.9	516.8	513.4	516.7	521.4	531.8	541.7	554.5	568.2
55°	518.4	498.2	483.9	475.0	473.8	475.6	481.0	492.2	506.5	522.6	535.7
57.5°	466.1	449.3	436.2	430.0	430.6	432.2	441.1	454.5	469.8	486.9	503.8
60°	430.9	415.4	404.8	400.0	400.5	404.2	414.8	427.4	446.4	463.0	481.0
62.5°	397.6	384.0	373.8	369.5	368.7	376.5	386.8	399.8	418.8	437.4	456.7
65°	344.1	333.3	325.0	322.6	324.4	330.4	343.5	360.7	376.8	396.4	416.6
67.5°	291.6	282.8	277.2	278.2	280.3	289.1	300.1	315.0	333.2	353.5	373.6
70°	258.3	249.9	245.2	245.8	249.4	260.1	269.7	284.5	304.2	325.0	341.6
72.5°	224.0	218.5	214.3	216.8	220.3	227.7	239.6	254.5	271.8	291.2	308.8
75°	172.0	172.0	169.6	171.4	176.8	183.9	192.9	208.4	225.6	241.1	255.4
77.5°	127.6	126.3	127.9	130.0	133.1	141.5	151.8	162.8	175.8	191.3	203.1
80°	97.6	98.2	101.2	104.8	106.0	112.5	123.2	133.4	143.4	156.5	167.8
82.5°	73.4	74.0	75.5	80.0	81.2	88.3	95.1	105.2	114.4	123.2	132.6
85°	39.9	39.9	42.9	44.6	47.6	52.3	56.6	62.5	70.9	76.8	85.7
87.5°	16.3	16.3	19.0	20.0	21.7	24.4	25.1	30.5	32.5	35.0	39.3
90°	5.4	5.4	9.4	9.4	10.8	12.1	11.5	12.1	12.8	13.4	13.4
92.5°	35.6	49.5	83.8	136.0	186.9	213.5	177.9	132.2	99.5	79.2	65.7
95°	55.9	84.1	142.8	253.1	414.1	548.7	564.2	498.9	394.5	304.3	239.0
97.5°	67.6	91.3	136.4	227.6	387.5	577.9	708.8	737.0	698.3	632.4	562.1
100°	76.7	98.3	138.0	214.1	351.5	541.3	713.6	811.9	825.4	792.4	742.6
102.5°	87.0	107.5	143.4	210.3	327.2	495.5	673.2	808.1	874.9	884.5	863.8
105°	104.4	123.9	156.2	212.1	306.3	441.6	599.9	754.1	870.5	937.1	964.8
107.5°	122.3	141.5	171.2	222.1	302.6	411.5	540.6	677.2	801.2	895.0	955.0
110°	134.7	152.8	182.4	229.5	303.6	401.2	511.0	630.9	747.3	844.9	918.9



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	146.5	164.7	193.2	237.6	306.9	396.4	494.3	596.9	699.9	792.1	866.2
115°	165.0	183.1	210.1	250.5	313.1	393.8	478.6	562.8	645.7	724.4	789.0
117.5°	181.9	200.8	226.4	263.5	319.7	393.1	471.7	546.1	614.7	676.6	731.4
120°	193.2	212.1	237.6	272.7	324.5	393.1	467.9	538.6	601.2	655.0	702.8
122.5°	204.5	222.8	248.4	281.3	329.3	392.6	463.6	532.1	592.5	641.6	683.5
125°	220.2	239.0	263.2	294.2	336.7	391.8	456.4	521.1	579.0	625.4	662.5
127.5°	234.5	253.6	277.0	305.4	342.4	390.4	446.9	507.6	562.9	609.2	644.5
130°	243.7	263.2	286.1	312.4	346.7	389.8	441.0	496.9	550.0	595.8	631.5
132.5°	252.4	270.8	293.7	319.3	350.5	389.3	435.6	485.5	535.5	580.2	615.9
135°	264.6	282.1	304.3	328.6	356.1	388.5	427.5	469.9	513.7	554.7	588.4
137.5°	274.9	291.6	312.4	335.0	359.5	388.3	420.5	455.8	492.8	527.4	557.8
140°	281.4	297.6	317.8	339.3	362.2	387.8	416.7	447.7	479.3	509.6	538.0
142.5°	287.3	303.0	322.6	342.5	364.4	387.8	413.5	440.1	468.0	494.0	518.5
145°	295.6	310.4	327.9	346.0	365.6	386.4	407.9	429.6	452.5	472.6	491.5
147.5°	303.5	316.8	333.3	349.1	366.3	384.0	403.0	420.8	438.9	455.1	469.9
150°	308.3	321.2	336.0	350.8	366.3	382.4	399.2	415.3	430.8	444.4	456.4
152.5°	313.2	324.9	338.1	351.8	365.2	379.7	394.9	409.5	422.8	435.1	445.1
155°	319.8	329.8	341.3	352.8	363.5	375.7	388.5	400.5	411.4	421.5	429.6
157.5°	326.0	333.9	343.6	352.8	361.8	371.5	381.9	391.0	400.0	408.5	415.0
160°	329.2	336.7	344.7	352.8	360.2	368.2	377.0	385.1	392.5	399.9	405.3
162.5°	332.4	338.2	345.8	352.8	358.6	365.1	372.7	379.2	385.5	391.3	396.1
165°	336.0	340.0	346.0	351.5	355.5	360.2	365.6	370.9	375.0	379.7	383.1
167.5°	338.4	341.5	345.9	349.8	352.2	355.3	359.1	363.0	366.1	369.9	371.9
170°	340.0	342.0	345.3	348.7	350.1	352.1	354.8	358.2	360.2	362.9	364.9
172.5°	341.0	342.5	344.8	347.7	347.9	348.9	351.0	353.9	355.3	357.0	358.4
175°	342.7	342.7	344.1	346.0	345.3	345.3	346.7	348.1	348.7	350.1	350.1
177.5°	342.7	342.7	343.2	344.3	343.2	343.2	343.7	344.3	344.8	344.8	345.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1369.2	1368.3	1364.9	1364.5	1364.9	1368.3	1369.2	1370.2	1371.6	1376.4	1370.6
5°	1264.8	1261.9	1260.1	1266.6	1260.1	1261.9	1264.8	1268.4	1274.4	1275.0	1280.9
7.5°	1186.1	1183.8	1178.5	1176.9	1178.5	1183.8	1186.1	1188.3	1194.2	1199.4	1208.2
10°	1135.7	1133.2	1128.5	1127.3	1128.5	1133.2	1135.7	1141.6	1147.5	1154.1	1160.1
12.5°	1087.1	1082.4	1081.4	1082.5	1081.4	1082.4	1087.1	1094.9	1110.4	1110.3	1111.5
15°	1022.6	1020.2	1013.7	1015.5	1013.7	1020.2	1022.6	1030.4	1037.4	1046.4	1055.3
17.5°	959.0	956.1	948.2	955.2	948.2	956.1	959.0	963.2	972.3	985.0	998.4
20°	919.0	914.2	910.1	909.5	910.1	914.2	919.0	923.2	933.3	944.0	954.2
22.5°	880.9	876.7	876.2	872.4	876.2	876.7	880.9	887.4	897.6	903.5	913.2
25°	833.3	829.1	827.9	825.0	827.9	829.1	833.3	838.1	844.6	849.4	860.1
27.5°	796.8	794.7	792.6	793.5	792.6	794.7	796.8	797.4	800.3	806.7	812.8
30°	774.4	773.8	772.6	772.6	772.6	773.8	774.4	772.6	775.6	778.5	783.3
32.5°	755.8	755.7	756.4	756.4	756.4	755.7	755.8	753.0	754.1	755.2	757.6
35°	729.7	731.5	732.7	730.9	732.7	731.5	729.7	727.4	725.6	721.4	722.6
37.5°	706.2	707.9	709.6	711.6	709.6	707.9	706.2	701.3	697.0	693.3	689.1
40°	688.0	692.2	693.4	696.4	693.4	692.2	688.0	682.7	678.0	673.8	669.0
42.5°	670.9	675.5	678.6	679.2	678.6	675.5	670.9	665.6	658.4	653.3	646.6
45°	644.6	649.4	653.6	653.6	653.6	649.4	644.6	635.7	627.9	620.2	613.6
47.5°	617.3	624.2	628.4	629.5	628.4	624.2	617.3	608.2	597.4	587.8	578.4
50°	598.8	607.1	611.3	614.2	611.3	607.1	598.8	588.7	577.4	565.4	554.1
52.5°	580.7	589.0	594.6	596.2	594.6	589.0	580.7	568.2	554.5	541.7	531.8
55°	549.4	561.3	567.8	570.2	567.8	561.3	549.4	535.7	522.6	506.5	492.2
57.5°	519.9	530.8	538.5	540.2	538.5	530.8	519.9	503.8	486.9	469.8	454.5
60°	497.0	508.9	518.4	520.2	518.4	508.9	497.0	481.0	463.0	446.4	427.4
62.5°	473.6	486.0	494.6	499.3	494.6	486.0	473.6	456.7	437.4	418.8	399.8
65°	433.3	445.8	454.2	455.9	454.2	445.8	433.3	416.6	396.4	376.8	360.7
67.5°	389.3	401.7	407.3	410.7	407.3	401.7	389.3	373.6	353.5	333.2	315.0
70°	358.3	368.4	374.4	377.4	374.4	368.4	358.3	341.6	325.0	304.2	284.5
72.5°	323.0	333.6	340.6	341.2	340.6	333.6	323.0	308.8	291.2	271.8	254.5
75°	269.1	278.5	282.1	282.1	282.1	278.5	269.1	255.4	241.1	225.6	208.4
77.5°	212.9	217.8	222.4	223.3	222.4	217.8	212.9	203.1	191.3	175.8	162.8
80°	176.8	179.8	183.3	183.3	183.3	179.8	176.8	167.8	156.5	143.4	133.4
82.5°	139.7	142.2	145.7	145.3	145.7	142.2	139.7	132.6	123.2	114.4	105.2
85°	84.6	89.9	89.3	88.1	89.3	89.9	84.6	85.7	76.8	70.9	62.5
87.5°	40.9	41.5	42.8	43.7	42.8	41.5	40.9	39.3	35.0	32.5	30.5
90°	14.1	14.8	14.1	14.1	14.1	14.8	14.1	13.4	13.4	12.8	12.1
92.5°	57.8	54.2	51.8	51.8	51.8	54.2	57.8	65.7	79.2	99.5	132.2
95°	206.0	185.1	173.1	164.3	173.1	185.1	206.0	239.0	304.3	394.5	498.9
97.5°	513.8	473.3	453.1	439.1	453.1	473.3	513.8	562.1	632.4	698.3	737.0
100°	684.0	642.9	622.8	617.3	622.8	642.9	684.0	742.6	792.4	825.4	811.9
102.5°	827.9	798.1	776.8	772.5	776.8	798.1	827.9	863.8	884.5	874.9	808.1
105°	966.1	960.7	951.3	947.3	951.3	960.7	966.1	964.8	937.1	870.5	754.1
107.5°	988.3	1003.7	1010.4	1012.1	1010.4	1003.7	988.3	955.0	895.0	801.2	677.2
110°	966.7	995.1	1007.2	1013.2	1007.2	995.1	966.7	918.9	844.9	747.3	630.9



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	920.4	954.7	971.6	981.5	971.6	954.7	920.4	866.2	792.1	699.9	596.9
115°	842.2	882.6	904.1	909.6	904.1	882.6	842.2	789.0	724.4	645.7	562.8
117.5°	776.8	810.7	832.5	836.7	832.5	810.7	776.8	731.4	676.6	614.7	546.1
120°	741.2	770.9	788.3	795.7	788.3	770.9	741.2	702.8	655.0	601.2	538.6
122.5°	715.9	741.2	756.0	763.4	756.0	741.2	715.9	683.5	641.6	592.5	532.1
125°	689.4	708.9	721.7	725.7	721.7	708.9	689.4	662.5	625.4	579.0	521.1
127.5°	671.5	688.9	699.6	703.7	699.6	688.9	671.5	644.5	609.2	562.9	507.6
130°	659.1	676.0	686.7	690.8	686.7	676.0	659.1	631.5	595.8	550.0	496.9
132.5°	642.9	661.9	672.2	676.2	672.2	661.9	642.9	615.9	580.2	535.5	485.5
135°	615.4	634.2	645.0	649.0	645.0	634.2	615.4	588.4	554.7	513.7	469.9
137.5°	583.0	601.6	610.4	615.4	610.4	601.6	583.0	557.8	527.4	492.8	455.8
140°	561.5	576.3	585.7	591.1	585.7	576.3	561.5	538.0	509.6	479.3	447.7
142.5°	539.4	553.1	561.5	565.2	561.5	553.1	539.4	518.5	494.0	468.0	440.1
145°	508.3	519.7	526.5	529.9	526.5	519.7	508.3	491.5	472.6	452.5	429.6
147.5°	482.3	492.1	497.2	498.4	497.2	492.1	482.3	469.9	455.1	438.9	420.8
150°	467.3	476.0	480.0	480.7	480.0	476.0	467.3	456.4	444.4	430.8	415.3
152.5°	454.3	461.4	463.8	464.5	463.8	461.4	454.3	445.1	435.1	422.8	409.5
155°	436.3	441.6	443.7	443.7	443.7	441.6	436.3	429.6	421.5	411.4	400.5
157.5°	420.1	424.1	425.3	425.3	425.3	424.1	420.1	415.0	408.5	400.0	391.0
160°	409.3	413.4	414.1	414.1	414.1	413.4	409.3	405.3	399.9	392.5	385.1
162.5°	399.1	403.1	403.8	403.3	403.8	403.1	399.1	396.1	391.3	385.5	379.2
165°	385.7	388.5	387.8	387.1	387.8	388.5	385.7	383.1	379.7	375.0	370.9
167.5°	373.2	375.0	374.9	374.3	374.9	375.0	373.2	371.9	369.9	366.1	363.0
170°	366.3	366.9	366.3	366.3	366.3	366.9	366.3	364.9	362.9	360.2	358.2
172.5°	359.2	359.9	359.2	358.2	359.2	359.9	359.2	358.4	357.0	355.3	353.9
175°	350.1	351.5	350.1	348.7	350.1	351.5	350.1	350.1	350.1	348.7	348.1
177.5°	344.8	345.3	344.3	343.2	344.3	345.3	344.8	345.3	344.8	344.8	344.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1373.6	1375.4	1383.0	1390.2	1398.8	1405.0	1409.2	1414.0	1424.0	1432.1	1439.7
5°	1286.9	1289.9	1305.3	1316.0	1334.5	1350.6	1363.0	1376.7	1392.8	1414.8	1435.0
7.5°	1210.6	1221.6	1238.5	1255.9	1274.7	1295.8	1314.1	1334.7	1362.4	1392.7	1423.8
10°	1167.3	1179.7	1197.6	1217.8	1235.7	1260.1	1282.7	1307.1	1338.6	1375.5	1412.5
12.5°	1123.9	1144.4	1158.0	1182.1	1201.4	1221.5	1245.5	1277.6	1314.3	1353.1	1397.7
15°	1069.6	1080.9	1107.1	1120.2	1147.5	1178.5	1202.3	1234.5	1270.1	1321.4	1371.4
17.5°	1007.0	1021.8	1042.7	1067.7	1099.2	1123.3	1153.0	1186.0	1231.1	1281.9	1344.5
20°	966.0	978.5	1004.1	1031.5	1064.8	1090.5	1122.0	1154.1	1200.6	1254.7	1320.2
22.5°	929.4	941.4	968.5	993.9	1026.2	1057.6	1090.5	1127.9	1172.4	1229.5	1296.4
25°	872.6	888.6	912.5	938.7	969.6	1005.3	1041.0	1074.4	1122.0	1182.1	1253.5
27.5°	822.3	835.1	852.4	882.1	917.2	951.7	987.2	1029.2	1074.9	1138.4	1212.5
30°	789.9	801.8	819.0	846.4	879.2	916.0	953.0	993.4	1041.0	1104.1	1179.7
32.5°	764.1	773.2	788.5	813.0	842.9	881.8	918.2	960.1	1010.0	1072.2	1145.9
35°	726.2	733.9	739.9	763.1	789.9	825.5	862.5	907.1	955.3	1014.3	1088.0
37.5°	688.9	691.6	700.3	715.4	741.4	774.3	808.6	852.5	901.9	961.7	1028.3
40°	666.1	667.3	672.6	686.9	709.5	740.5	773.8	817.3	864.3	920.8	986.9
42.5°	643.7	642.9	647.8	657.8	679.0	707.1	739.9	779.6	826.6	878.9	941.2
45°	608.3	608.3	607.1	615.4	632.7	660.1	687.5	725.6	764.8	816.1	868.4
47.5°	571.4	568.1	569.1	573.4	588.0	610.4	638.1	669.3	703.9	747.3	793.2
50°	547.6	542.9	541.1	545.8	558.9	578.5	604.8	632.1	664.9	702.9	742.3
52.5°	521.4	516.7	513.4	516.8	528.9	547.1	570.9	595.0	624.4	655.3	689.4
55°	481.0	475.6	473.8	475.0	483.9	498.2	518.4	540.4	562.5	588.1	611.9
57.5°	441.1	432.2	430.6	430.0	436.2	449.3	466.1	485.3	501.3	516.8	542.1
60°	414.8	404.2	400.5	400.0	404.8	415.4	430.9	450.0	461.3	472.0	494.0
62.5°	386.8	376.5	368.7	369.5	373.8	384.0	397.6	411.4	418.9	430.6	445.5
65°	343.5	330.4	324.4	322.6	325.0	333.3	344.1	352.9	361.3	366.1	380.3
67.5°	300.1	289.1	280.3	278.2	277.2	282.8	291.6	297.0	303.0	307.1	315.6
70°	269.7	260.1	249.4	245.8	245.2	249.9	258.3	258.9	267.3	269.1	277.9
72.5°	239.6	227.7	220.3	216.8	214.3	218.5	224.0	225.6	230.1	233.3	238.0
75°	192.9	183.9	176.8	171.4	169.6	172.0	172.0	175.0	178.0	179.8	185.1
77.5°	151.8	141.5	133.1	130.0	127.9	126.3	127.6	129.4	127.9	131.0	132.2
80°	123.2	112.5	106.0	104.8	101.2	98.2	97.6	99.4	97.0	98.2	101.8
82.5°	95.1	88.3	81.2	80.0	75.5	74.0	73.4	72.2	72.2	72.0	72.8
85°	56.6	52.3	47.6	44.6	42.9	39.9	39.9	38.7	37.5	36.3	36.9
87.5°	25.1	24.4	21.7	20.0	19.0	16.3	16.3	14.7	14.1	13.3	12.5
90°	11.5	12.1	10.8	9.4	9.4	5.4	5.4	4.7	4.0	2.0	0.7
92.5°	177.9	213.5	186.9	136.0	83.8	49.5	35.6	25.7	17.5	11.2	7.7
95°	564.2	548.7	414.1	253.1	142.8	84.1	55.9	39.7	31.0	24.2	22.2
97.5°	708.8	577.9	387.5	227.6	136.4	91.3	67.6	53.7	45.6	39.9	39.9
100°	713.6	541.3	351.5	214.1	138.0	98.3	76.7	64.0	55.9	51.1	51.1
102.5°	673.2	495.5	327.2	210.3	143.4	107.5	87.0	74.7	67.2	63.0	61.9
105°	599.9	441.6	306.3	212.1	156.2	123.9	104.4	92.2	84.1	80.8	78.8
107.5°	540.6	411.5	302.6	222.1	171.2	141.5	122.3	110.6	102.0	98.7	97.4
110°	511.0	401.2	303.6	229.5	182.4	152.8	134.7	122.5	114.4	111.1	109.8



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.3	396.4	306.9	237.6	193.2	164.7	146.5	134.4	126.8	123.0	121.6
115°	478.6	393.8	313.1	250.5	210.1	183.1	165.0	152.1	145.4	140.7	138.7
117.5°	471.7	393.1	319.7	263.5	226.4	200.8	181.9	170.0	162.6	158.3	156.4
120°	467.9	393.1	324.5	272.7	237.6	212.1	193.2	181.8	174.4	169.6	168.3
122.5°	463.6	392.6	329.3	281.3	248.4	222.8	204.5	192.0	185.1	180.5	179.1
125°	456.4	391.8	336.7	294.2	263.2	239.0	220.2	207.3	199.9	195.9	193.2
127.5°	446.9	390.4	342.4	305.4	277.0	253.6	234.5	221.2	212.8	207.9	205.8
130°	441.0	389.8	346.7	312.4	286.1	263.2	243.7	230.9	220.8	215.4	212.8
132.5°	435.6	389.3	350.5	319.3	293.7	270.8	252.4	238.5	228.9	221.9	219.7
135°	427.5	388.5	356.1	328.6	304.3	282.1	264.6	250.5	239.0	232.3	229.5
137.5°	420.5	388.3	359.5	335.0	312.4	291.6	274.9	260.3	249.3	241.9	239.4
140°	416.7	387.8	362.2	339.3	317.8	297.6	281.4	267.3	255.8	248.4	246.4
142.5°	413.5	387.8	364.4	342.5	322.6	303.0	287.3	273.7	262.9	256.0	253.9
145°	407.9	386.4	365.6	346.0	327.9	310.4	295.6	282.8	273.4	266.6	264.6
147.5°	403.0	384.0	366.3	349.1	333.3	316.8	303.5	292.8	283.2	277.2	276.6
150°	399.2	382.4	366.3	350.8	336.0	321.2	308.3	298.3	290.2	284.8	284.1
152.5°	394.9	379.7	365.2	351.8	338.1	324.9	313.2	304.2	296.6	291.3	291.1
155°	388.5	375.7	363.5	352.8	341.3	329.8	319.8	312.4	305.7	301.6	300.9
157.5°	381.9	371.5	361.8	352.8	343.6	333.9	326.0	319.5	314.3	310.5	310.5
160°	377.0	368.2	360.2	352.8	344.7	336.7	329.2	323.8	319.1	316.4	316.4
162.5°	372.7	365.1	358.6	352.8	345.8	338.2	332.4	327.6	323.4	321.2	321.8
165°	365.6	360.2	355.5	351.5	346.0	340.0	336.0	332.6	329.2	327.9	327.9
167.5°	359.1	355.3	352.2	349.8	345.9	341.5	338.4	336.5	333.9	333.3	333.9
170°	354.8	352.1	350.1	348.7	345.3	342.0	340.0	338.6	336.7	336.0	336.7
172.5°	351.0	348.9	347.9	347.7	344.8	342.5	341.0	340.3	338.8	338.6	339.3
175°	346.7	345.3	345.3	346.0	344.1	342.7	342.7	342.0	341.3	341.3	342.0
177.5°	343.7	343.2	343.2	344.3	343.2	342.7	342.7	342.7	342.2	342.7	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1446.4	1451.1	1457.3	1467.8	1471.6	1476.4	1483.1	1482.6	1484.5	1491.6	1506.8
5°	1451.7	1470.2	1488.1	1509.5	1532.1	1547.0	1567.2	1579.7	1592.2	1608.3	1635.6
7.5°	1453.9	1483.2	1515.9	1553.5	1587.0	1625.6	1655.6	1683.9	1709.6	1743.5	1776.2
10°	1450.5	1489.8	1532.1	1579.7	1630.3	1673.2	1711.8	1755.9	1793.4	1834.4	1871.4
12.5°	1444.3	1491.8	1548.3	1601.6	1660.8	1724.1	1772.3	1816.8	1866.7	1914.0	1970.9
15°	1430.3	1495.2	1561.3	1631.5	1710.6	1783.8	1853.5	1911.2	1964.8	2035.7	2110.1
17.5°	1412.5	1482.5	1565.7	1650.8	1733.5	1817.2	1903.4	1990.2	2057.8	2145.8	2204.0
20°	1395.8	1476.7	1562.5	1663.6	1746.4	1850.5	1936.2	2020.2	2113.0	2200.5	2270.1
22.5°	1372.4	1461.0	1552.0	1652.7	1761.6	1865.8	1964.8	2055.9	2148.7	2243.9	2328.2
25°	1342.8	1423.1	1530.9	1645.2	1753.5	1866.6	1980.3	2094.6	2194.5	2295.2	2373.7
27.5°	1292.4	1393.8	1494.1	1612.1	1732.4	1860.4	1981.9	2101.6	2206.3	2289.1	2337.8
30°	1266.6	1354.7	1463.6	1582.1	1712.4	1849.9	1976.7	2094.0	2191.6	2257.6	2277.3
32.5°	1228.6	1319.5	1426.0	1548.8	1686.7	1828.0	1960.1	2070.6	2152.1	2186.7	2163.0
35°	1172.0	1254.1	1361.8	1487.5	1630.9	1781.5	1911.9	2005.3	2046.9	2014.2	1932.7
37.5°	1104.1	1185.5	1293.7	1417.1	1565.6	1718.6	1836.5	1903.8	1889.9	1808.5	1687.0
40°	1056.5	1132.7	1235.7	1369.0	1513.6	1667.2	1770.7	1807.1	1769.0	1652.3	1523.2
42.5°	1003.7	1078.0	1181.4	1309.9	1463.2	1604.8	1695.1	1698.1	1634.2	1494.7	1365.0
45°	923.2	994.0	1091.7	1225.5	1367.2	1500.6	1560.0	1530.9	1413.1	1278.5	1148.1
47.5°	843.8	905.2	1001.4	1128.5	1263.1	1375.3	1404.8	1352.3	1226.8	1096.1	975.3
50°	785.7	847.6	938.1	1059.5	1189.2	1286.2	1300.5	1230.9	1107.7	976.1	881.5
52.5°	730.0	791.4	878.6	990.9	1109.7	1197.2	1197.7	1117.1	994.4	877.1	789.1
55°	648.2	703.5	782.1	882.7	988.7	1057.1	1040.4	957.1	850.6	748.8	672.0
57.5°	569.4	617.6	690.0	773.9	867.2	923.7	896.0	815.8	720.7	634.4	576.2
60°	518.4	564.3	626.2	705.3	783.9	827.9	801.8	729.1	641.6	572.0	521.4
62.5°	468.9	507.6	567.1	635.8	708.7	741.3	718.0	646.3	570.7	507.7	466.7
65°	398.8	430.3	477.9	536.9	589.9	617.9	598.2	531.5	473.8	428.5	395.8
67.5°	333.3	358.0	394.0	441.3	486.3	501.4	483.5	437.1	388.2	352.0	328.9
70°	288.1	311.3	341.6	378.0	417.2	433.3	415.4	378.6	338.7	305.3	282.8
72.5°	248.6	266.6	292.1	323.2	354.0	370.0	357.8	322.4	288.7	263.9	244.6
75°	189.2	204.7	222.6	244.6	268.5	279.1	268.5	244.0	220.8	202.3	188.6
77.5°	137.6	145.9	159.7	176.2	191.1	199.2	190.0	173.4	159.3	146.6	139.9
80°	104.8	110.7	120.2	133.4	143.4	151.2	145.3	131.6	120.2	111.9	108.9
82.5°	76.2	80.2	86.4	96.2	103.0	106.9	104.3	94.4	89.7	82.4	79.4
85°	37.5	39.9	44.1	47.0	53.0	53.6	54.2	50.0	45.8	44.1	41.7
87.5°	13.3	14.1	15.7	17.3	19.2	20.5	20.0	20.2	18.6	18.0	16.3
90°	2.0	4.0	4.7	5.4	5.4	9.4	9.4	10.8	12.1	11.5	12.1
92.5°	11.2	17.5	25.7	35.6	49.5	83.8	136.0	186.9	213.5	177.9	132.2
95°	24.2	31.0	39.7	55.9	84.1	142.8	253.1	414.1	548.7	564.2	498.9
97.5°	39.9	45.6	53.7	67.6	91.3	136.4	227.6	387.5	577.9	708.8	737.0
100°	51.1	55.9	64.0	76.7	98.3	138.0	214.1	351.5	541.3	713.6	811.9
102.5°	63.0	67.2	74.7	87.0	107.5	143.4	210.3	327.2	495.5	673.2	808.1
105°	80.8	84.1	92.2	104.4	123.9	156.2	212.1	306.3	441.6	599.9	754.1
107.5°	98.7	102.0	110.6	122.3	141.5	171.2	222.1	302.6	411.5	540.6	677.2
110°	111.1	114.4	122.5	134.7	152.8	182.4	229.5	303.6	401.2	511.0	630.9





TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.0	126.8	134.4	146.5	164.7	193.2	237.6	306.9	396.4	494.3	596.9
115°	140.7	145.4	152.1	165.0	183.1	210.1	250.5	313.1	393.8	478.6	562.8
117.5°	158.3	162.6	170.0	181.9	200.8	226.4	263.5	319.7	393.1	471.7	546.1
120°	169.6	174.4	181.8	193.2	212.1	237.6	272.7	324.5	393.1	467.9	538.6
122.5°	180.5	185.1	192.0	204.5	222.8	248.4	281.3	329.3	392.6	463.6	532.1
125°	195.9	199.9	207.3	220.2	239.0	263.2	294.2	336.7	391.8	456.4	521.1
127.5°	207.9	212.8	221.2	234.5	253.6	277.0	305.4	342.4	390.4	446.9	507.6
130°	215.4	220.8	230.9	243.7	263.2	286.1	312.4	346.7	389.8	441.0	496.9
132.5°	221.9	228.9	238.5	252.4	270.8	293.7	319.3	350.5	389.3	435.6	485.5
135°	232.3	239.0	250.5	264.6	282.1	304.3	328.6	356.1	388.5	427.5	469.9
137.5°	241.9	249.3	260.3	274.9	291.6	312.4	335.0	359.5	388.3	420.5	455.8
140°	248.4	255.8	267.3	281.4	297.6	317.8	339.3	362.2	387.8	416.7	447.7
142.5°	256.0	262.9	273.7	287.3	303.0	322.6	342.5	364.4	387.8	413.5	440.1
145°	266.6	273.4	282.8	295.6	310.4	327.9	346.0	365.6	386.4	407.9	429.6
147.5°	277.2	283.2	292.8	303.5	316.8	333.3	349.1	366.3	384.0	403.0	420.8
150°	284.8	290.2	298.3	308.3	321.2	336.0	350.8	366.3	382.4	399.2	415.3
152.5°	291.3	296.6	304.2	313.2	324.9	338.1	351.8	365.2	379.7	394.9	409.5
155°	301.6	305.7	312.4	319.8	329.8	341.3	352.8	363.5	375.7	388.5	400.5
157.5°	310.5	314.3	319.5	326.0	333.9	343.6	352.8	361.8	371.5	381.9	391.0
160°	316.4	319.1	323.8	329.2	336.7	344.7	352.8	360.2	368.2	377.0	385.1
162.5°	321.2	323.4	327.6	332.4	338.2	345.8	352.8	358.6	365.1	372.7	379.2
165°	327.9	329.2	332.6	336.0	340.0	346.0	351.5	355.5	360.2	365.6	370.9
167.5°	333.3	333.9	336.5	338.4	341.5	345.9	349.8	352.2	355.3	359.1	363.0
170°	336.0	336.7	338.6	340.0	342.0	345.3	348.7	350.1	352.1	354.8	358.2
172.5°	338.6	338.8	340.3	341.0	342.5	344.8	347.7	347.9	348.9	351.0	353.9
175°	341.3	341.3	342.0	342.7	342.7	344.1	346.0	345.3	345.3	346.7	348.1
177.5°	342.7	342.2	342.7	342.7	342.7	343.2	344.3	343.2	343.2	343.7	344.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1514.5	1515.4	1519.7	1523.0	1524.0	1528.8	1529.2
5°	1647.5	1657.7	1677.3	1679.1	1682.0	1697.5	1685.7
7.5°	1803.5	1829.2	1846.3	1861.5	1867.0	1873.7	1872.3
10°	1903.5	1941.6	1960.7	1991.0	1992.2	1999.9	1995.2
12.5°	2004.0	2048.2	2083.0	2088.6	2114.1	2118.0	2124.7
15°	2146.3	2193.4	2241.6	2258.8	2294.0	2302.3	2315.4
17.5°	2280.2	2328.2	2362.1	2406.7	2421.1	2440.4	2427.2
20°	2353.5	2405.9	2448.7	2483.8	2498.7	2509.4	2508.3
22.5°	2397.8	2450.6	2485.4	2511.9	2525.8	2530.4	2530.1
25°	2425.5	2455.8	2466.6	2476.7	2461.3	2455.8	2458.2
27.5°	2348.4	2340.5	2312.6	2275.9	2237.7	2207.5	2191.1
30°	2242.2	2195.7	2153.4	2079.7	2041.6	2019.0	1998.7
32.5°	2091.7	2018.1	1936.8	1869.2	1825.9	1792.3	1787.3
35°	1833.8	1723.1	1623.8	1541.0	1498.1	1461.8	1453.5
37.5°	1559.1	1444.1	1354.6	1281.8	1235.7	1210.0	1186.1
40°	1376.7	1277.9	1189.8	1127.9	1092.8	1074.4	1059.5
42.5°	1236.2	1146.0	1058.4	1011.2	979.5	968.2	959.5
45°	1042.2	958.3	897.6	861.9	843.4	824.4	815.5
47.5°	886.8	818.6	778.5	748.2	728.4	717.1	711.4
50°	798.7	742.8	707.1	683.9	666.1	657.1	652.4
52.5°	720.7	674.8	644.7	626.3	614.2	607.6	605.7
55°	620.8	585.7	566.6	550.6	541.7	535.7	533.3
57.5°	539.6	512.6	497.1	483.9	480.4	475.4	473.8
60°	486.3	465.5	452.4	443.4	440.5	434.5	435.7
62.5°	439.1	422.1	411.0	405.8	401.9	396.9	398.6
65°	371.4	359.0	352.9	348.2	343.5	340.4	342.9
67.5°	311.7	303.1	295.0	292.2	289.9	289.4	286.9
70°	272.6	265.4	258.3	256.6	256.6	254.2	253.6
72.5°	235.0	229.7	225.0	223.7	221.8	222.7	220.2
75°	181.5	177.4	175.6	173.8	173.2	173.2	171.4
77.5°	134.1	131.0	128.2	128.2	126.1	125.3	125.0
80°	101.8	100.6	98.2	98.2	97.0	97.6	96.4
82.5°	76.5	74.9	74.4	73.4	71.8	71.9	70.7
85°	41.1	39.3	38.7	36.9	35.7	36.9	35.7
87.5°	16.9	16.5	16.0	15.2	14.9	14.7	13.3
90°	12.8	13.4	13.4	14.1	14.8	14.1	14.1
92.5°	99.5	79.2	65.7	57.8	54.2	51.8	51.8
95°	394.5	304.3	239.0	206.0	185.1	173.1	164.3
97.5°	698.3	632.4	562.1	513.8	473.3	453.1	439.1
100°	825.4	792.4	742.6	684.0	642.9	622.8	617.3
102.5°	874.9	884.5	863.8	827.9	798.1	776.8	772.5
105°	870.5	937.1	964.8	966.1	960.7	951.3	947.3
107.5°	801.2	895.0	955.0	988.3	1003.7	1010.4	1012.1
110°	747.3	844.9	918.9	966.7	995.1	1007.2	1013.2



TEST NUMBER: P332645-935

CATALOG NUMBER: SA4XXDIP-C1020D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	699.9	792.1	866.2	920.4	954.7	971.6	981.5
115°	645.7	724.4	789.0	842.2	882.6	904.1	909.6
117.5°	614.7	676.6	731.4	776.8	810.7	832.5	836.7
120°	601.2	655.0	702.8	741.2	770.9	788.3	795.7
122.5°	592.5	641.6	683.5	715.9	741.2	756.0	763.4
125°	579.0	625.4	662.5	689.4	708.9	721.7	725.7
127.5°	562.9	609.2	644.5	671.5	688.9	699.6	703.7
130°	550.0	595.8	631.5	659.1	676.0	686.7	690.8
132.5°	535.5	580.2	615.9	642.9	661.9	672.2	676.2
135°	513.7	554.7	588.4	615.4	634.2	645.0	649.0
137.5°	492.8	527.4	557.8	583.0	601.6	610.4	615.4
140°	479.3	509.6	538.0	561.5	576.3	585.7	591.1
142.5°	468.0	494.0	518.5	539.4	553.1	561.5	565.2
145°	452.5	472.6	491.5	508.3	519.7	526.5	529.9
147.5°	438.9	455.1	469.9	482.3	492.1	497.2	498.4
150°	430.8	444.4	456.4	467.3	476.0	480.0	480.7
152.5°	422.8	435.1	445.1	454.3	461.4	463.8	464.5
155°	411.4	421.5	429.6	436.3	441.6	443.7	443.7
157.5°	400.0	408.5	415.0	420.1	424.1	425.3	425.3
160°	392.5	399.9	405.3	409.3	413.4	414.1	414.1
162.5°	385.5	391.3	396.1	399.1	403.1	403.8	403.3
165°	375.0	379.7	383.1	385.7	388.5	387.8	387.1
167.5°	366.1	369.9	371.9	373.2	375.0	374.9	374.3
170°	360.2	362.9	364.9	366.3	366.9	366.3	366.3
172.5°	355.3	357.0	358.4	359.2	359.9	359.2	358.2
175°	348.7	350.1	350.1	350.1	351.5	350.1	348.7
177.5°	344.8	344.8	345.3	344.8	345.3	344.3	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7

(END OF REPORT)