

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913072

Luminaire Tested: DFN2DIP-4P2F0-030D040US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913072
REPORT IS A COMBINATION OF REPORTS P899026 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D040US927-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4824.4 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 60.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913072
CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P913072

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	49	49	49	42
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42	42	42	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	36	36	36	31
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31	31	31	31	27
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	27	27	27	23
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24	24	24	24	20
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21	21	21	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	19	19	19	16
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17	17	17	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16	16	16	16	13
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14	14	14	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2459	2459	2459
5°	2458	2414	2432
10°	2429	2361	2349
15°	2391	2276	2223
20°	2342	2163	2069
25°	2291	2037	1921
30°	2226	1909	1735
35°	2161	1771	1572
40°	2094	1630	1385
45°	2018	1474	1216
50°	1938	1316	1051
55°	1855	1149	893
60°	1758	975	732
65°	1647	799	654
70°	1511	636	586
75°	1341	548	525
80°	1097	443	443
85°	707	273	313

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2018 cd/sqm



TEST NUMBER: P913072

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.1	1.9
10°-20°	252.7	5.2
20°-30°	354.8	7.4
30°-40°	386.8	8.0
40°-50°	355.5	7.4
50°-60°	279.2	5.8
60°-70°	181.7	3.8
70°-80°	93.5	1.9
80°-90°	26.7	0.6
90°-100°	62.0	1.3
100°-110°	197.0	4.1
110°-120°	337.2	7.0
120°-130°	443.5	9.2
130°-140°	497.8	10.3
140°-150°	488.1	10.1
150°-160°	409.5	8.5
160°-170°	271.5	5.6
170°-180°	94.9	2.0
0°-30°	699.6	14.5
0°-40°	1086.3	22.5
0°-60°	1720.9	35.7
0°-90°	2022.9	41.9
90°-120°	596.2	12.4
90°-150°	2025.6	42.0
90°-180°	2801.0	58.1
0°-180°	4824.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	982	982	982	982	982	
5°	982	978	966	974	972	93
15°	934	924	894	877	868	263
25°	848	820	761	724	711	390
35°	731	685	607	551	532	457
45°	597	538	444	381	360	461
55°	454	385	289	236	219	406
65°	307	235	155	124	122	304
75°	164	101	71	65	64	173
85°	38	20	17	17	17	44
90°	1	11	30	28	29	5
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P913072

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.2	982.2	982.2	982.2	982.2
2.5°	986.7	982.2	972.4	981.4	979.6
5°	982.2	977.8	966.2	974.2	971.5
7.5°	974.2	968.9	956.5	960.0	955.5
10°	963.5	957.4	939.6	936.8	931.6
12.5°	950.2	942.2	918.2	912.9	903.1
15°	934.2	924.4	894.2	877.3	868.5
17.5°	915.5	901.3	864.0	844.5	830.2
20°	894.2	876.4	831.9	809.8	790.2
22.5°	871.2	850.6	799.1	768.9	755.6
25°	848.0	819.5	760.9	724.4	711.1
27.5°	820.5	790.2	725.3	683.6	663.1
30°	791.2	757.3	686.2	641.0	616.9
32.5°	762.6	721.8	649.0	595.6	573.3
35°	730.7	685.3	607.1	551.1	531.6
37.5°	699.6	650.6	568.0	506.6	484.5
40°	666.7	613.4	527.1	464.0	440.9
42.5°	632.9	576.1	486.2	420.4	398.2
45°	597.4	537.7	444.5	381.3	360.0
47.5°	563.6	500.5	404.5	341.3	321.8
50°	526.2	463.1	365.4	304.0	285.3
52.5°	489.7	423.1	328.0	269.3	252.5
55°	454.2	384.8	288.8	235.6	218.7
57.5°	417.8	346.7	254.3	204.5	190.2
60°	380.4	309.3	217.8	172.5	158.3
62.5°	344.0	272.9	186.6	144.0	137.0
65°	306.7	234.6	154.6	124.5	121.8
67.5°	271.2	199.1	124.5	109.3	106.6
70°	233.8	164.5	103.1	94.2	90.6
72.5°	198.2	132.4	86.2	79.1	77.3
75°	163.5	101.3	71.1	64.9	64.0
77.5°	128.9	71.9	56.0	52.4	50.6
80°	96.9	51.6	42.6	39.1	39.1
82.5°	67.5	34.7	29.3	27.6	27.6
85°	38.2	19.5	16.9	16.9	16.9
87.5°	14.3	7.1	7.1	6.3	6.3
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5



TEST NUMBER: P913072

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1



TEST NUMBER: P913072
 CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.33	10.10	10.36	11.14	12.52	5.30	6.06	6.33	7.10	8.48
	3H	10.99	11.67	12.02	12.71	14.12	6.46	7.15	7.50	8.19	9.59
	4H	11.57	12.23	12.63	13.27	14.68	6.89	7.54	7.94	8.59	10.00
	6H	11.97	12.57	13.04	13.62	15.04	7.19	7.79	8.25	8.84	10.26
	8H	12.09	12.66	13.16	13.72	15.14	7.27	7.84	8.33	8.90	10.32
	12H	12.14	12.68	13.21	13.74	15.18	7.30	7.84	8.37	8.90	10.34
4H	2H	9.34	9.99	10.40	11.03	12.45	5.87	6.52	6.93	7.57	8.98
	3H	11.14	11.68	12.20	12.75	14.17	7.19	7.73	8.26	8.80	10.23
	4H	11.81	12.30	12.88	13.37	14.81	7.72	8.21	8.79	9.28	10.72
	6H	12.30	12.72	13.38	13.81	15.25	8.11	8.54	9.19	9.62	11.06
	8H	12.46	12.86	13.54	13.93	15.39	8.23	8.62	9.31	9.70	11.16
	12H	12.54	12.90	13.64	13.99	15.45	8.28	8.64	9.38	9.73	11.19
8H	4H	11.77	12.16	12.85	13.24	14.70	7.98	8.38	9.06	9.45	10.91
	6H	12.31	12.63	13.41	13.75	15.21	8.47	8.79	9.57	9.91	11.37
	8H	12.51	12.79	13.62	13.90	15.37	8.64	8.93	9.75	10.03	11.50
	12H	12.63	12.88	13.74	13.98	15.49	8.74	8.99	9.86	10.09	11.60
12H	4H	11.71	12.07	12.81	13.17	14.63	7.98	8.34	9.08	9.43	10.89
	6H	12.28	12.57	13.39	13.67	15.14	8.51	8.80	9.62	9.90	11.37
	8H	12.48	12.73	13.59	13.83	15.34	8.70	8.95	9.81	10.05	11.56