

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332696-935

Luminaire Tested: **SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332696-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6897.2 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332696-935
CATALOG NUMBER: SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332696-935

CATALOG NUMBER: SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	95	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	54	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	42	38
4	77	66	57	51	72	62	55	49	55	49	44	48	44	40	42	39	36	33
5	70	59	50	44	66	55	48	42	49	43	38	44	39	35	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	34	39	34	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332696-935

CATALOG NUMBER: SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.3
10°-20°	455.3	6.6
20°-30°	670.1	9.7
30°-40°	779.0	11.3
40°-50°	779.1	11.3
50°-60°	681.5	9.9
60°-70°	506.1	7.3
70°-80°	287.5	4.2
80°-90°	84.9	1.2
90°-100°	247.5	3.6
100°-110°	515.1	7.5
110°-120°	461.4	6.7
120°-130°	388.1	5.6
130°-140°	323.6	4.7
140°-150°	247.2	3.6
150°-160°	173.8	2.5
160°-170°	102.2	1.5
170°-180°	33.3	0.5
0°-30°	1287.0	18.7
0°-40°	2066.0	30.0
0°-60°	3526.5	51.1
0°-90°	4404.9	63.9
90°-120°	1224.0	17.7
90°-150°	2183.0	31.7
90°-180°	2492.0	36.1
0°-180°	6897.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	1	5	12	13	14	5
95°	22	70	549	272	164	25
105°	79	114	442	951	947	84
115°	139	174	394	757	910	138
125°	193	230	392	644	726	172
135°	230	273	388	572	649	177
145°	265	303	386	482	530	166
155°	301	325	376	426	444	139
165°	328	338	360	381	387	93
175°	342	343	345	350	349	32
180°	343	343	343	343	343	



TEST NUMBER: P332696-935

CATALOG NUMBER: SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	28.8	28.8	28.9	28.8	28.7	28.4	29.0	28.8	28.8	28.8	28.7
90°	0.7	2.0	4.0	4.7	5.4	5.4	9.4	9.4	10.8	12.1	11.5
92.5°	7.7	11.2	17.5	25.7	35.6	49.5	83.8	136.0	186.9	213.5	177.9
95°	22.2	24.2	31.0	39.7	55.9	84.1	142.8	253.1	414.1	548.7	564.2
97.5°	39.9	39.9	45.6	53.7	67.6	91.3	136.4	227.6	387.5	577.9	708.8
100°	51.1	51.1	55.9	64.0	76.7	98.3	138.0	214.1	351.5	541.3	713.6
102.5°	61.9	63.0	67.2	74.7	87.0	107.5	143.4	210.3	327.2	495.5	673.2
105°	78.8	80.8	84.1	92.2	104.4	123.9	156.2	212.1	306.3	441.6	599.9
107.5°	97.4	98.7	102.0	110.6	122.3	141.5	171.2	222.1	302.6	411.5	540.6
110°	109.8	111.1	114.4	122.5	134.7	152.8	182.4	229.5	303.6	401.2	511.0



TEST NUMBER: P332696-935

CATALOG NUMBER: SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.6	123.0	126.8	134.4	146.5	164.7	193.2	237.6	306.9	396.4	494.3
115°	138.7	140.7	145.4	152.1	165.0	183.1	210.1	250.5	313.1	393.8	478.6
117.5°	156.4	158.3	162.6	170.0	181.9	200.8	226.4	263.5	319.7	393.1	471.7
120°	168.3	169.6	174.4	181.8	193.2	212.1	237.6	272.7	324.5	393.1	467.9
122.5°	179.1	180.5	185.1	192.0	204.5	222.8	248.4	281.3	329.3	392.6	463.6
125°	193.2	195.9	199.9	207.3	220.2	239.0	263.2	294.2	336.7	391.8	456.4
127.5°	205.8	207.9	212.8	221.2	234.5	253.6	277.0	305.4	342.4	390.4	446.9
130°	212.8	215.4	220.8	230.9	243.7	263.2	286.1	312.4	346.7	389.8	441.0
132.5°	219.7	221.9	228.9	238.5	252.4	270.8	293.7	319.3	350.5	389.3	435.6
135°	229.5	232.3	239.0	250.5	264.6	282.1	304.3	328.6	356.1	388.5	427.5
137.5°	239.4	241.9	249.3	260.3	274.9	291.6	312.4	335.0	359.5	388.3	420.5
140°	246.4	248.4	255.8	267.3	281.4	297.6	317.8	339.3	362.2	387.8	416.7
142.5°	253.9	256.0	262.9	273.7	287.3	303.0	322.6	342.5	364.4	387.8	413.5
145°	264.6	266.6	273.4	282.8	295.6	310.4	327.9	346.0	365.6	386.4	407.9
147.5°	276.6	277.2	283.2	292.8	303.5	316.8	333.3	349.1	366.3	384.0	403.0
150°	284.1	284.8	290.2	298.3	308.3	321.2	336.0	350.8	366.3	382.4	399.2
152.5°	291.1	291.3	296.6	304.2	313.2	324.9	338.1	351.8	365.2	379.7	394.9
155°	300.9	301.6	305.7	312.4	319.8	329.8	341.3	352.8	363.5	375.7	388.5
157.5°	310.5	310.5	314.3	319.5	326.0	333.9	343.6	352.8	361.8	371.5	381.9
160°	316.4	316.4	319.1	323.8	329.2	336.7	344.7	352.8	360.2	368.2	377.0
162.5°	321.8	321.2	323.4	327.6	332.4	338.2	345.8	352.8	358.6	365.1	372.7
165°	327.9	327.9	329.2	332.6	336.0	340.0	346.0	351.5	355.5	360.2	365.6
167.5°	333.9	333.3	333.9	336.5	338.4	341.5	345.9	349.8	352.2	355.3	359.1
170°	336.7	336.0	336.7	338.6	340.0	342.0	345.3	348.7	350.1	352.1	354.8
172.5°	339.3	338.6	338.8	340.3	341.0	342.5	344.8	347.7	347.9	348.9	351.0
175°	342.0	341.3	341.3	342.0	342.7	342.7	344.1	346.0	345.3	345.3	346.7
177.5°	343.2	342.7	342.2	342.7	342.7	342.7	343.2	344.3	343.2	343.2	343.7
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332696-935

CATALOG NUMBER: SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	28.8	28.9	29.1	29.1	29.2	29.4	29.2	29.2
90°	12.1	12.8	13.4	13.4	14.1	14.8	14.1	14.1
92.5°	132.2	99.5	79.2	65.7	57.8	54.2	51.8	51.8
95°	498.9	394.5	304.3	239.0	206.0	185.1	173.1	164.3
97.5°	737.0	698.3	632.4	562.1	513.8	473.3	453.1	439.1
100°	811.9	825.4	792.4	742.6	684.0	642.9	622.8	617.3
102.5°	808.1	874.9	884.5	863.8	827.9	798.1	776.8	772.5
105°	754.1	870.5	937.1	964.8	966.1	960.7	951.3	947.3
107.5°	677.2	801.2	895.0	955.0	988.3	1003.7	1010.4	1012.1
110°	630.9	747.3	844.9	918.9	966.7	995.1	1007.2	1013.2



TEST NUMBER: P332696-935

CATALOG NUMBER: SA4XXDIP-C1195D810U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	596.9	699.9	792.1	866.2	920.4	954.7	971.6	981.5
115°	562.8	645.7	724.4	789.0	842.2	882.6	904.1	909.6
117.5°	546.1	614.7	676.6	731.4	776.8	810.7	832.5	836.7
120°	538.6	601.2	655.0	702.8	741.2	770.9	788.3	795.7
122.5°	532.1	592.5	641.6	683.5	715.9	741.2	756.0	763.4
125°	521.1	579.0	625.4	662.5	689.4	708.9	721.7	725.7
127.5°	507.6	562.9	609.2	644.5	671.5	688.9	699.6	703.7
130°	496.9	550.0	595.8	631.5	659.1	676.0	686.7	690.8
132.5°	485.5	535.5	580.2	615.9	642.9	661.9	672.2	676.2
135°	469.9	513.7	554.7	588.4	615.4	634.2	645.0	649.0
137.5°	455.8	492.8	527.4	557.8	583.0	601.6	610.4	615.4
140°	447.7	479.3	509.6	538.0	561.5	576.3	585.7	591.1
142.5°	440.1	468.0	494.0	518.5	539.4	553.1	561.5	565.2
145°	429.6	452.5	472.6	491.5	508.3	519.7	526.5	529.9
147.5°	420.8	438.9	455.1	469.9	482.3	492.1	497.2	498.4
150°	415.3	430.8	444.4	456.4	467.3	476.0	480.0	480.7
152.5°	409.5	422.8	435.1	445.1	454.3	461.4	463.8	464.5
155°	400.5	411.4	421.5	429.6	436.3	441.6	443.7	443.7
157.5°	391.0	400.0	408.5	415.0	420.1	424.1	425.3	425.3
160°	385.1	392.5	399.9	405.3	409.3	413.4	414.1	414.1
162.5°	379.2	385.5	391.3	396.1	399.1	403.1	403.8	403.3
165°	370.9	375.0	379.7	383.1	385.7	388.5	387.8	387.1
167.5°	363.0	366.1	369.9	371.9	373.2	375.0	374.9	374.3
170°	358.2	360.2	362.9	364.9	366.3	366.9	366.3	366.3
172.5°	353.9	355.3	357.0	358.4	359.2	359.9	359.2	358.2
175°	348.1	348.7	350.1	350.1	350.1	351.5	350.1	348.7
177.5°	344.3	344.8	344.8	345.3	344.8	345.3	344.3	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7

(END OF REPORT)