

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332525-935

Luminaire Tested: **SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332525-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4489.5 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332525-935
CATALOG NUMBER: SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332525-935

CATALOG NUMBER: SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	33	32	31	24				
2	85	78	72	67	76	70	65	60	55	51	48	41	39	37	29	27	26	20				
3	77	68	61	55	69	61	55	50	48	44	41	36	34	31	25	24	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15				
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	17	13				
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	15	11				
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	15	13	10				
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	12	9				
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8				
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4106	4106	4106
5°	4118	4068	4099
10°	4092	4036	4055
15°	4043	3978	3989
20°	3978	3907	3911
25°	3902	3827	3815
30°	3811	3731	3697
35°	3714	3631	3582
40°	3616	3518	3453
45°	3513	3406	3342
50°	3399	3307	3204
55°	3275	3178	3074
60°	3152	3034	2942
65°	3012	2896	2779
70°	2858	2712	2608
75°	2617	2492	2427
80°	2329	2236	2176
85°	2038	1964	1927



TEST NUMBER: P332525-935

CATALOG NUMBER: SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	1.1
10°-20°	135.0	3.0
20°-30°	198.6	4.4
30°-40°	230.9	5.1
40°-50°	230.9	5.1
50°-60°	202.0	4.5
60°-70°	150.0	3.3
70°-80°	85.2	1.9
80°-90°	27.0	0.6
90°-100°	316.0	7.0
100°-110°	657.7	14.6
110°-120°	589.1	13.1
120°-130°	495.5	11.0
130°-140°	413.2	9.2
140°-150°	315.7	7.0
150°-160°	221.9	4.9
160°-170°	130.5	2.9
170°-180°	42.5	0.9
0°-30°	381.5	8.5
0°-40°	612.4	13.6
0°-60°	1045.3	23.3
0°-90°	1307.6	29.1
90°-120°	1562.8	34.8
90°-150°	2787.1	62.1
90°-180°	3182.0	70.9
0°-180°	4489.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	508	506	502	506	506	48
15°	484	482	476	478	477	136
25°	438	435	430	430	428	201
35°	377	374	368	366	364	236
45°	308	305	298	294	293	237
55°	233	231	226	221	218	208
65°	158	156	152	148	146	156
75°	84	82	80	78	78	89
85°	22	22	21	21	21	24
90°	1	7	16	17	18	3
95°	28	89	700	347	210	32
105°	101	146	564	1214	1209	107
115°	177	222	503	966	1161	176
125°	247	293	500	822	927	220
135°	293	349	496	730	829	227
145°	338	387	493	615	676	212
155°	384	415	480	543	566	177
165°	419	432	460	487	494	118
175°	437	438	441	447	445	41
180°	438	438	438	438	438	



TEST NUMBER: P332525-935

CATALOG NUMBER: SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	509.9	509.7	509.5	509.3	509.0	508.5	507.7	507.0	506.2	505.3	506.1
5°	508.2	507.8	507.5	507.1	506.8	506.1	505.1	504.1	503.1	502.0	503.1
7.5°	503.5	503.1	502.7	502.4	502.0	501.3	500.2	499.1	498.0	496.9	497.7
10°	499.2	498.9	498.5	498.2	497.8	497.1	495.8	494.6	493.5	492.3	493.0
12.5°	493.7	493.4	493.0	492.6	492.2	491.5	490.2	489.0	487.7	486.5	487.2
15°	483.7	483.4	483.0	482.7	482.3	481.5	480.1	478.7	477.3	476.0	476.6
17.5°	471.7	471.3	470.9	470.5	469.9	469.1	467.8	466.5	465.2	463.9	464.3
20°	463.0	462.5	462.1	461.6	461.2	460.3	458.9	457.5	456.2	454.8	455.1
22.5°	453.5	452.9	452.3	451.7	451.1	450.1	448.8	447.5	446.1	444.7	445.2
25°	438.1	437.5	436.9	436.2	435.6	434.6	433.3	432.0	430.8	429.6	429.6
27.5°	420.5	419.8	419.2	418.5	417.9	417.0	415.8	414.7	413.5	412.2	412.1
30°	408.8	408.0	407.3	406.6	405.9	404.9	403.7	402.5	401.4	400.2	399.8
32.5°	396.4	395.7	395.0	394.4	393.7	392.8	391.6	390.3	389.1	387.8	387.4
35°	376.9	376.3	375.7	375.1	374.4	373.5	372.2	370.9	369.7	368.4	367.8
37.5°	356.5	355.9	355.3	354.8	354.2	353.3	351.9	350.5	349.1	347.8	347.1
40°	343.1	342.4	341.7	341.0	340.3	339.2	337.9	336.5	335.1	333.8	332.9
42.5°	328.8	328.4	328.0	327.5	327.1	326.1	324.6	323.0	321.6	320.1	319.0
45°	307.7	307.0	306.4	305.8	305.1	304.1	302.6	301.2	299.8	298.3	297.3
47.5°	285.6	285.2	284.7	284.3	283.9	283.0	281.6	280.3	279.0	277.6	276.5
50°	270.6	270.3	269.9	269.5	269.1	268.4	267.1	265.8	264.5	263.3	262.0
52.5°	256.0	255.5	255.0	254.6	254.2	253.3	251.9	250.6	249.3	248.0	246.8
55°	232.7	232.5	232.1	231.9	231.6	230.8	229.5	228.3	227.0	225.8	224.7
57.5°	210.5	210.3	209.9	209.7	209.3	208.5	207.2	206.0	204.7	203.5	202.5
60°	195.2	194.8	194.3	193.8	193.4	192.6	191.4	190.2	189.1	187.9	187.1
62.5°	180.2	179.9	179.4	179.1	178.7	177.9	176.6	175.4	174.1	172.9	172.1
65°	157.7	157.3	156.8	156.4	155.9	155.2	154.3	153.4	152.5	151.6	150.7
67.5°	135.1	134.7	134.2	133.8	133.4	132.8	131.9	131.0	130.2	129.2	128.4
70°	121.1	120.4	119.8	119.2	118.5	117.8	117.1	116.4	115.6	114.9	114.2
72.5°	106.1	105.4	104.8	104.2	103.5	102.9	102.3	101.8	101.2	100.6	100.0
75°	83.9	83.5	83.1	82.6	82.1	81.7	81.3	80.8	80.3	79.9	79.6
77.5°	62.9	62.7	62.4	62.3	62.1	61.7	61.4	61.0	60.5	60.2	60.0
80°	50.1	49.9	49.6	49.3	49.1	48.8	48.6	48.5	48.3	48.1	47.9
82.5°	37.7	37.6	37.5	37.4	37.2	37.1	37.1	37.1	37.0	37.0	36.9
85°	22.0	22.0	22.0	22.0	22.0	22.0	21.7	21.5	21.4	21.2	21.2
87.5°	8.6	9.0	9.4	9.5	9.6	9.5	10.4	10.4	10.7	10.9	10.8
90°	0.9	2.6	5.2	6.0	6.9	6.9	12.1	12.1	13.8	15.5	14.6
92.5°	9.8	14.3	22.4	32.8	45.4	63.3	106.9	173.7	238.6	272.7	227.1
95°	28.3	30.9	39.5	50.7	71.4	107.5	182.2	323.2	528.7	700.5	720.3
97.5°	50.9	50.9	58.3	68.6	86.3	116.6	174.2	290.5	494.7	737.8	904.9
100°	65.3	65.3	71.4	81.6	98.0	125.5	176.2	273.4	448.7	691.0	911.1
102.5°	79.0	80.4	85.8	95.4	111.1	137.2	183.0	268.5	417.8	632.7	859.5
105°	100.6	103.1	107.5	117.8	133.2	158.2	199.4	270.8	391.1	563.9	765.9
107.5°	124.3	126.1	130.3	141.3	156.1	180.6	218.5	283.4	386.2	525.4	690.2
110°	140.1	141.8	146.1	156.4	171.9	195.1	232.9	293.1	387.6	512.3	652.4



TEST NUMBER: P332525-935

CATALOG NUMBER: SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.2	157.0	162.0	171.6	187.0	210.3	246.7	303.4	391.8	506.1	631.1
115°	177.1	179.6	185.6	194.2	210.6	233.8	268.2	319.8	399.7	502.8	611.1
117.5°	199.8	202.2	207.5	217.0	232.2	256.3	289.0	336.4	408.1	502.0	602.2
120°	214.9	216.6	222.7	232.0	246.7	270.8	303.4	348.1	414.3	502.0	597.4
122.5°	228.7	230.3	236.3	245.1	261.1	284.5	317.2	359.1	420.5	501.3	591.9
125°	246.7	250.1	255.3	264.8	281.0	305.1	336.0	375.7	429.8	500.2	582.8
127.5°	262.7	265.4	271.6	282.4	299.5	323.7	353.6	389.9	437.1	498.3	570.6
130°	271.6	275.1	281.9	294.8	311.2	336.0	365.3	398.8	442.6	497.7	563.0
132.5°	280.5	283.3	292.2	304.4	322.2	345.7	375.0	407.8	447.5	497.0	556.1
135°	293.1	296.5	305.1	319.8	337.8	360.2	388.5	419.5	454.7	495.9	545.8
137.5°	305.7	308.9	318.4	332.3	351.0	372.4	398.8	427.7	459.0	495.8	536.8
140°	314.6	317.2	326.7	341.2	359.3	380.0	405.7	433.2	462.4	495.1	532.1
142.5°	324.3	326.8	335.5	349.5	366.9	386.8	411.9	437.3	465.2	495.1	528.0
145°	337.8	340.4	349.0	361.0	377.4	396.2	418.6	441.8	466.7	493.4	520.9
147.5°	353.1	354.0	361.5	373.9	387.4	404.5	425.5	445.7	467.6	490.3	514.5
150°	362.7	363.6	370.5	380.8	393.6	410.0	429.0	447.8	467.6	488.2	509.7
152.5°	371.7	371.9	378.8	388.3	399.8	414.8	431.7	449.2	466.2	484.7	504.2
155°	384.2	385.0	390.2	398.8	408.3	421.2	435.8	450.4	464.2	479.7	495.9
157.5°	396.4	396.4	401.2	407.9	416.2	426.4	438.7	450.4	461.9	474.3	487.5
160°	404.0	404.0	407.4	413.5	420.3	429.8	440.1	450.4	459.9	470.2	481.4
162.5°	410.9	410.2	412.9	418.3	424.5	431.9	441.4	450.4	457.8	466.1	475.9
165°	418.6	418.6	420.3	424.6	429.0	434.0	441.8	448.7	453.8	459.9	466.7
167.5°	426.4	425.5	426.4	429.6	432.0	435.9	441.6	446.6	449.7	453.7	458.5
170°	429.8	429.0	429.8	432.4	434.0	436.6	440.9	445.2	446.9	449.5	453.0
172.5°	433.2	432.4	432.5	434.4	435.4	437.3	440.2	443.8	444.2	445.4	448.2
175°	436.6	435.8	435.8	436.6	437.5	437.5	439.2	441.8	440.9	440.9	442.6
177.5°	438.2	437.5	436.8	437.5	437.5	437.5	438.2	439.5	438.2	438.2	438.9
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332525-935

CATALOG NUMBER: SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	506.8	507.6	508.2	508.6	508.5	508.4	508.3	508.2
5°	504.1	505.1	506.1	506.4	506.3	506.1	505.9	505.8
7.5°	498.4	499.3	500.1	500.4	500.3	500.2	500.1	500.0
10°	493.8	494.5	495.2	495.5	495.3	495.1	494.9	494.7
12.5°	488.0	488.8	489.7	489.9	489.7	489.4	489.1	488.9
15°	477.1	477.6	478.2	478.3	478.0	477.8	477.5	477.3
17.5°	464.6	464.9	465.3	465.4	465.2	465.0	464.9	464.7
20°	455.4	455.6	455.9	456.0	455.7	455.6	455.4	455.2
22.5°	445.7	446.2	446.7	446.8	446.4	446.1	445.7	445.5
25°	429.7	429.8	429.9	429.8	429.4	429.0	428.7	428.3
27.5°	411.8	411.6	411.4	411.0	410.6	410.2	409.7	409.2
30°	399.5	399.2	398.7	398.4	397.9	397.4	397.0	396.6
32.5°	386.9	386.5	386.1	385.6	385.2	384.7	384.3	383.8
35°	367.1	366.5	365.8	365.3	364.9	364.5	363.9	363.5
37.5°	346.4	345.7	345.0	344.4	343.8	343.2	342.6	342.0
40°	332.0	331.1	330.2	329.5	329.0	328.6	328.1	327.7
42.5°	318.0	316.9	315.9	315.2	314.9	314.6	314.3	314.0
45°	296.4	295.3	294.4	293.7	293.4	293.2	292.9	292.7
47.5°	275.3	274.2	273.1	272.2	271.6	270.9	270.2	269.5
50°	260.7	259.5	258.2	257.3	256.8	256.2	255.6	255.1
52.5°	245.7	244.6	243.5	242.5	241.9	241.2	240.5	239.8
55°	223.6	222.5	221.4	220.6	220.1	219.6	219.0	218.4
57.5°	201.5	200.4	199.4	198.6	198.1	197.6	197.1	196.5
60°	186.2	185.5	184.6	184.0	183.6	183.0	182.6	182.2
62.5°	171.4	170.7	169.9	169.3	168.8	168.4	168.0	167.5
65°	149.8	148.9	148.0	147.3	146.9	146.4	145.9	145.5
67.5°	127.5	126.7	125.8	125.3	125.2	125.0	124.9	124.8
70°	113.5	112.8	112.0	111.5	111.2	111.0	110.7	110.5
72.5°	99.4	98.8	98.2	97.8	97.6	97.3	97.0	96.8
75°	79.1	78.8	78.4	78.2	78.1	78.0	77.9	77.8
77.5°	59.9	59.8	59.8	59.6	59.3	59.1	58.8	58.6
80°	47.7	47.5	47.4	47.3	47.1	47.0	46.9	46.8
82.5°	36.8	36.7	36.6	36.5	36.4	36.2	36.2	36.1
85°	21.2	21.2	21.2	21.2	21.1	21.0	20.8	20.8
87.5°	10.9	11.1	11.3	11.3	11.5	11.6	11.5	11.5
90°	15.5	16.4	17.2	17.2	18.1	18.9	18.1	18.1
92.5°	168.8	127.1	101.1	83.9	73.8	69.1	66.2	66.2
95°	636.9	503.7	388.5	305.1	263.0	236.3	220.9	209.7
97.5°	941.1	891.5	807.4	717.7	656.0	604.2	578.5	560.6
100°	1036.6	1053.8	1011.7	948.0	873.3	820.9	795.0	788.2
102.5°	1031.8	1117.1	1129.3	1102.8	1056.9	1018.9	991.8	986.3
105°	962.7	1111.4	1196.4	1231.7	1233.5	1226.6	1214.5	1209.4
107.5°	864.5	1022.9	1142.7	1219.3	1261.8	1281.4	1290.0	1292.3
110°	805.4	954.1	1078.7	1173.3	1234.3	1270.4	1285.9	1293.7



TEST NUMBER: P332525-935

CATALOG NUMBER: SA4XXDIP-C350D1035U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	762.1	893.5	1011.3	1105.9	1175.2	1218.8	1240.5	1253.0
115°	718.6	824.3	924.9	1007.4	1075.3	1126.9	1154.3	1161.2
117.5°	697.2	784.8	863.8	933.8	991.8	1035.1	1062.9	1068.2
120°	687.6	767.6	836.4	897.3	946.3	984.2	1006.5	1016.0
122.5°	679.4	756.6	819.2	872.6	914.0	946.3	965.3	974.7
125°	665.3	739.2	798.5	845.8	880.2	905.1	921.4	926.6
127.5°	648.1	718.8	777.9	822.8	857.3	879.5	893.2	898.4
130°	634.4	702.2	760.7	806.2	841.5	863.0	876.8	881.9
132.5°	619.9	683.7	740.7	786.4	820.9	845.1	858.2	863.3
135°	599.9	655.8	708.3	751.2	785.7	809.7	823.5	828.6
137.5°	581.9	629.2	673.4	712.2	744.3	768.1	779.5	785.7
140°	571.6	612.0	650.7	686.7	716.9	735.8	747.8	754.7
142.5°	562.0	597.5	630.8	662.0	688.6	706.2	716.9	721.7
145°	548.4	577.6	603.4	627.5	648.9	663.6	672.2	676.5
147.5°	537.2	560.4	581.1	599.9	615.8	628.4	634.9	636.4
150°	530.4	550.1	567.3	582.8	596.5	607.7	612.9	613.7
152.5°	522.8	539.8	555.6	568.3	580.1	589.1	592.2	593.1
155°	511.4	525.2	538.0	548.4	557.0	563.9	566.5	566.5
157.5°	499.2	510.7	521.6	529.9	536.3	541.5	543.0	543.0
160°	491.6	501.1	510.6	517.5	522.6	527.8	528.7	528.7
162.5°	484.1	492.1	499.6	505.8	509.5	514.7	515.6	514.9
165°	473.6	478.8	484.7	489.0	492.5	495.9	495.1	494.2
167.5°	463.5	467.4	472.3	474.8	476.6	478.8	478.6	477.9
170°	457.3	459.9	463.3	465.9	467.6	468.5	467.6	467.6
172.5°	451.8	453.7	455.7	457.6	458.7	459.5	458.7	457.3
175°	444.4	445.2	446.9	446.9	446.9	448.7	446.9	445.2
177.5°	439.5	440.2	440.2	440.9	440.2	440.9	439.5	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5

(END OF REPORT)