

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918507

Luminaire Tested: DFN2DIP-4P2F0-020D020US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918507
REPORT IS A COMBINATION OF REPORTS P900531 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D020US935-FLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3409.5 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918507

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918507

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1678	1678	1678
5°	1677	1650	1663
10°	1660	1624	1638
15°	1632	1593	1600
20°	1596	1551	1561
25°	1560	1503	1516
30°	1515	1457	1461
35°	1473	1404	1402
40°	1421	1350	1346
45°	1369	1297	1288
50°	1313	1240	1222
55°	1253	1174	1160
60°	1185	1097	1090
65°	1110	1016	1007
70°	1016	917	917
75°	887	800	830
80°	730	650	670
85°	487	405	419

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1369 cd/sqm

TEST NUMBER: P918507

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.8
10°-20°	177.4	5.2
20°-30°	260.8	7.6
30°-40°	302.9	8.9
40°-50°	302.5	8.9
50°-60°	263.8	7.7
60°-70°	195.0	5.7
70°-80°	110.3	3.2
80°-90°	30.1	0.9
90°-100°	19.2	0.6
100°-110°	71.4	2.1
110°-120°	189.5	5.6
120°-130°	314.2	9.2
130°-140°	333.8	9.8
140°-150°	310.2	9.1
150°-160°	249.4	7.3
160°-170°	160.7	4.7
170°-180°	55.3	1.6
0°-30°	501.3	14.7
0°-40°	804.1	23.6
0°-60°	1370.4	40.2
0°-90°	1705.8	50.0
90°-120°	280.0	8.2
90°-150°	1238.3	36.3
90°-180°	1704.0	50.0
0°-180°	3409.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	670	670	670	670	670	
5°	670	668	660	666	664	64
15°	638	634	626	628	625	180
25°	577	572	561	562	561	266
35°	498	492	481	477	474	311
45°	405	401	391	384	381	313
55°	307	303	295	287	284	274
65°	207	203	197	191	188	205
75°	108	107	104	100	101	116
85°	26	26	25	23	23	29
90°	0	5	8	10	11	3
95°	27	13	16	18	18	32
105°	128	140	26	30	32	137
115°	242	249	260	65	34	238
125°	342	347	355	358	360	305
135°	423	430	434	438	437	327
145°	491	490	498	500	498	307
155°	540	537	542	544	541	249
165°	569	567	568	571	568	161
175°	582	580	580	583	579	55
180°	581	581	581	581	581	

TEST NUMBER: P918507

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	670.0	670.0	670.0	670.0	670.0
2.5°	673.9	670.7	663.6	670.0	668.8
5°	670.0	667.5	660.4	665.6	664.3
7.5°	665.6	661.7	654.6	659.8	658.5
10°	658.5	654.0	646.3	651.3	649.5
12.5°	648.8	645.0	637.2	640.4	639.1
15°	637.8	634.0	625.6	628.2	625.0
17.5°	624.3	620.5	612.1	615.3	612.1
20°	609.5	605.6	596.6	598.6	596.0
22.5°	594.7	588.9	580.5	580.5	579.2
25°	577.3	572.1	561.2	562.4	561.2
27.5°	557.9	553.4	545.1	543.2	539.9
30°	538.6	533.5	523.8	521.9	519.3
32.5°	518.0	514.2	503.9	500.0	497.4
35°	498.1	491.6	481.3	477.4	474.2
37.5°	475.5	469.7	459.3	454.9	451.6
40°	452.3	447.1	436.8	431.1	428.4
42.5°	429.7	424.6	414.3	407.9	404.0
45°	405.3	400.8	391.1	384.0	381.4
47.5°	381.4	376.9	366.6	359.5	355.7
50°	356.3	353.1	344.1	335.0	331.8
52.5°	331.8	327.3	318.9	311.9	307.4
55°	306.7	302.8	295.1	287.4	284.1
57.5°	281.5	278.4	269.9	262.3	259.6
60°	256.4	253.9	244.9	237.7	235.8
62.5°	232.0	227.4	221.0	214.6	212.0
65°	206.8	202.9	196.6	190.7	187.5
67.5°	181.1	177.8	172.0	167.6	165.0
70°	157.2	154.6	148.8	144.3	141.8
72.5°	132.8	130.2	126.9	122.4	120.5
75°	108.2	107.0	103.7	99.9	101.2
77.5°	86.4	83.8	82.4	80.5	78.6
80°	64.5	63.8	62.5	60.5	59.2
82.5°	43.8	43.8	43.2	40.6	40.6
85°	26.3	25.7	25.1	23.2	22.6
87.5°	11.6	10.3	9.0	7.1	6.5
90°	0.4	5.1	8.4	10.5	11.4
92.5°	10.5	8.9	10.1	10.9	11.4
95°	27.3	13.4	16.4	18.5	18.1
97.5°	49.2	14.7	21.4	22.7	23.2
100°	74.5	16.8	23.9	27.3	28.2
102.5°	102.2	101.3	24.8	29.4	30.7
105°	127.9	140.4	25.7	30.2	31.9
107.5°	157.7	168.2	26.5	31.1	32.8
110°	186.3	195.1	73.6	31.6	33.2

TEST NUMBER: P918507

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.2	220.8	213.6	32.4	33.7
115°	241.8	248.9	259.5	64.7	34.5
117.5°	266.6	275.0	282.1	222.1	111.8
120°	294.4	300.7	308.2	313.3	256.5
122.5°	317.9	324.6	333.0	335.5	336.0
125°	341.9	347.3	355.3	358.3	359.6
127.5°	363.8	369.6	376.0	380.1	380.6
130°	384.3	391.1	395.7	400.4	399.9
132.5°	405.4	410.9	415.4	419.2	418.9
135°	423.1	429.8	433.5	437.8	437.0
137.5°	441.5	446.6	450.8	455.0	453.7
140°	459.6	463.0	467.6	471.4	469.3
142.5°	474.8	477.8	483.2	486.5	484.4
145°	490.8	490.3	497.5	500.4	498.3
147.5°	504.6	503.3	510.5	512.6	510.9
150°	518.1	515.1	521.9	524.3	522.3
152.5°	529.4	526.1	532.4	534.9	531.9
155°	540.4	536.6	541.7	544.2	540.8
157.5°	549.2	545.9	549.7	552.6	549.2
160°	556.8	554.2	556.8	559.3	556.4
162.5°	563.4	560.9	563.1	566.0	562.2
165°	569.4	566.9	568.1	571.1	568.1
167.5°	574.0	571.4	572.7	575.7	571.9
170°	577.8	575.2	576.1	579.0	575.2
172.5°	580.3	577.8	578.7	581.6	577.8
175°	582.4	579.5	580.3	583.2	579.0
177.5°	583.2	580.3	580.7	583.7	579.9
180°	581.2	581.2	581.2	581.2	581.2

TEST NUMBER: P918507

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.94	9.80	9.90	10.77	12.04	8.50	9.36	9.45	10.33	11.60
	3H	10.58	11.35	11.54	12.33	13.62	10.09	10.86	11.06	11.84	13.13
	4H	11.15	11.88	12.13	12.87	14.17	10.66	11.39	11.64	12.37	13.67
	6H	11.53	12.21	12.52	13.20	14.51	11.03	11.71	12.02	12.70	14.01
	8H	11.63	12.27	12.63	13.28	14.59	11.13	11.77	12.13	12.78	14.09
	12H	11.67	12.28	12.67	13.28	14.61	11.16	11.77	12.16	12.77	14.11
4H	2H	9.39	10.12	10.38	11.11	12.41	9.03	9.76	10.02	10.75	12.05
	3H	11.23	11.84	12.22	12.85	14.17	10.82	11.43	11.82	12.44	13.76
	4H	11.92	12.48	12.93	13.49	14.83	11.50	12.06	12.50	13.06	14.40
	6H	12.42	12.90	13.43	13.93	15.26	11.98	12.46	13.00	13.50	14.83
	8H	12.56	13.00	13.57	14.03	15.38	12.12	12.57	13.14	13.59	14.94
	12H	12.62	13.02	13.65	14.06	15.42	12.17	12.57	13.21	13.61	14.97
8H	4H	12.11	12.56	13.12	13.58	14.93	11.73	12.18	12.75	13.20	14.55
	6H	12.71	13.08	13.75	14.15	15.50	12.32	12.70	13.37	13.76	15.11
	8H	12.92	13.24	13.97	14.29	15.66	12.52	12.85	13.57	13.90	15.27
	12H	13.03	13.32	14.08	14.36	15.77	12.62	12.91	13.67	13.95	15.36
12H	4H	12.09	12.49	13.13	13.53	14.89	11.72	12.13	12.76	13.16	14.52
	6H	12.73	13.06	13.78	14.11	15.48	12.36	12.69	13.41	13.74	15.11
	8H	12.96	13.25	14.01	14.29	15.70	12.58	12.86	13.63	13.91	15.32