

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918513

Luminaire Tested: DFN2DIP-4P2F0-020D030US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918513
REPORT IS A COMBINATION OF REPORTS P900538 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D030US935-RLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4020.9 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 40
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918513

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918513

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1782	1782	1782
5°	1781	1749	1762
10°	1760	1710	1702
15°	1732	1649	1611
20°	1697	1568	1499
25°	1660	1476	1392
30°	1613	1383	1257
35°	1565	1284	1139
40°	1517	1181	1003
45°	1462	1068	881
50°	1405	954	762
55°	1344	833	647
60°	1274	707	530
65°	1193	579	474
70°	1095	460	425
75°	972	397	380
80°	795	321	320
85°	511	197	226

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1462 cd/sqm

TEST NUMBER: P918513

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.7
10°-20°	183.1	4.6
20°-30°	257.1	6.4
30°-40°	280.2	7.0
40°-50°	257.6	6.4
50°-60°	202.3	5.0
60°-70°	131.7	3.3
70°-80°	67.8	1.7
80°-90°	18.8	0.5
90°-100°	28.7	0.7
100°-110°	107.2	2.7
110°-120°	284.2	7.1
120°-130°	471.3	11.7
130°-140°	500.7	12.5
140°-150°	465.3	11.6
150°-160°	374.1	9.3
160°-170°	241.1	6.0
170°-180°	83.0	2.1
0°-30°	506.9	12.6
0°-40°	787.1	19.6
0°-60°	1247.0	31.0
0°-90°	1465.2	36.4
90°-120°	420.1	10.4
90°-150°	1857.5	46.2
90°-180°	2556.0	63.6
0°-180°	4020.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	1	8	13	16	17	4
95°	41	20	24	28	27	49
105°	192	211	38	45	48	205
115°	363	373	389	97	52	357
125°	513	521	533	537	539	457
135°	635	645	650	657	655	490
145°	736	736	746	751	747	460
155°	810	805	812	816	811	373
165°	854	850	852	857	852	241
175°	874	869	870	875	869	83
180°	872	872	872	872	872	

TEST NUMBER: P918513

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	0.6	7.6	12.6	15.8	17.0
92.5°	15.8	13.3	15.2	16.4	17.0
95°	41.0	20.1	24.5	27.8	27.1
97.5°	73.8	22.1	32.1	34.1	34.7
100°	111.7	25.2	36.0	41.0	42.3
102.5°	153.3	152.1	37.2	44.1	46.1
105°	191.7	210.7	38.5	45.4	48.0
107.5°	236.5	252.3	39.8	46.7	49.2
110°	279.5	292.7	110.4	47.4	49.9

TEST NUMBER: P918513

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	319.9	331.1	320.5	48.6	50.5
115°	362.7	373.4	389.2	97.1	51.7
117.5°	399.9	412.5	423.3	333.0	167.8
120°	441.5	451.0	462.4	469.9	384.8
122.5°	476.8	487.0	499.6	503.3	504.0
125°	512.8	521.0	533.0	537.4	539.3
127.5°	545.6	554.4	564.0	570.2	570.8
130°	576.5	586.7	593.6	600.5	599.9
132.5°	608.0	616.3	623.2	628.9	628.3
135°	634.6	644.7	650.3	656.7	655.4
137.5°	662.3	669.9	676.2	682.5	680.6
140°	689.4	694.5	701.4	707.1	704.0
142.5°	712.2	716.6	724.8	729.8	726.7
145°	736.2	735.5	746.2	750.6	747.4
147.5°	756.9	755.0	765.8	768.9	766.4
150°	777.1	772.7	782.8	786.5	783.4
152.5°	794.1	789.1	798.6	802.4	798.0
155°	810.5	804.9	812.4	816.2	811.2
157.5°	823.8	818.8	824.5	828.9	823.8
160°	835.2	831.4	835.2	839.0	834.5
162.5°	845.2	841.5	844.6	849.0	843.3
165°	854.0	850.3	852.2	856.6	852.2
167.5°	861.0	857.2	859.1	863.6	857.9
170°	866.7	862.9	864.2	868.6	862.9
172.5°	870.5	866.7	868.0	872.4	866.7
175°	873.6	869.2	870.5	874.9	868.6
177.5°	874.9	870.5	871.2	875.5	869.9
180°	871.8	871.8	871.8	871.8	871.8

TEST NUMBER: P918513

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.61	8.34	8.68	9.40	10.86	3.57	4.30	4.64	5.37	6.82
	3H	9.25	9.91	10.33	10.98	12.46	4.73	5.38	5.81	6.46	7.93
	4H	9.84	10.46	10.93	11.54	13.02	5.16	5.78	6.25	6.86	8.34
	6H	10.24	10.81	11.34	11.89	13.38	5.46	6.02	6.56	7.11	8.60
	8H	10.35	10.89	11.46	11.99	13.48	5.53	6.07	6.64	7.17	8.66
	12H	10.40	10.91	11.51	12.01	13.51	5.56	6.08	6.67	7.17	8.68
4H	2H	7.61	8.22	8.70	9.30	10.78	4.14	4.76	5.24	5.84	7.32
	3H	9.40	9.91	10.50	11.02	12.51	5.45	5.97	6.56	7.08	8.57
	4H	10.07	10.54	11.18	11.64	13.15	5.98	6.45	7.09	7.55	9.06
	6H	10.56	10.96	11.67	12.08	13.59	6.37	6.78	7.49	7.89	9.40
	8H	10.72	11.10	11.83	12.21	13.73	6.49	6.86	7.60	7.97	9.50
	12H	10.80	11.14	11.93	12.26	13.79	6.53	6.88	7.67	8.00	9.53
8H	4H	10.02	10.40	11.14	11.51	13.03	6.24	6.62	7.36	7.73	9.25
	6H	10.56	10.87	11.70	12.03	13.54	6.73	7.04	7.86	8.19	9.71
	8H	10.76	11.04	11.91	12.17	13.71	6.90	7.17	8.04	8.31	9.84
	12H	10.88	11.12	12.03	12.25	13.82	7.00	7.24	8.14	8.37	9.94
12H	4H	9.97	10.31	11.10	11.44	12.96	6.24	6.58	7.37	7.70	9.23
	6H	10.54	10.81	11.68	11.94	13.48	6.77	7.04	7.91	8.17	9.71
	8H	10.73	10.97	11.88	12.10	13.68	6.96	7.20	8.10	8.33	9.90

END OF REPORT