

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332507-935

Luminaire Tested: **SA4XXDIP-C350D590U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332507-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D590U935-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3124.8 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332507-935
CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332507-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42				
1	96	92	88	84	87	84	80	77	69	67	65	55	54	52	43	42	41	35				
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34	29				
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25				
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21				
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19				
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4106	4106	4106
5°	4118	4068	4099
10°	4092	4036	4055
15°	4043	3978	3989
20°	3978	3907	3911
25°	3902	3827	3815
30°	3811	3731	3697
35°	3714	3631	3582
40°	3616	3518	3453
45°	3513	3406	3342
50°	3399	3307	3204
55°	3275	3178	3074
60°	3152	3034	2942
65°	3012	2896	2779
70°	2858	2712	2608
75°	2617	2492	2427
80°	2329	2236	2176
85°	2038	1964	1927



TEST NUMBER: P332507-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	1.5
10°-20°	135.0	4.3
20°-30°	198.6	6.4
30°-40°	230.9	7.4
40°-50°	230.9	7.4
50°-60°	202.0	6.5
60°-70°	150.0	4.8
70°-80°	85.2	2.7
80°-90°	26.0	0.8
90°-100°	180.6	5.8
100°-110°	375.8	12.0
110°-120°	336.6	10.8
120°-130°	283.1	9.1
130°-140°	236.1	7.6
140°-150°	180.4	5.8
150°-160°	126.8	4.1
160°-170°	74.6	2.4
170°-180°	24.3	0.8
0°-30°	381.5	12.2
0°-40°	612.4	19.6
0°-60°	1045.3	33.5
0°-90°	1306.6	41.8
90°-120°	893.0	28.6
90°-150°	1592.6	51.0
90°-180°	1818.0	58.2
0°-180°	3124.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	508	506	502	506	506	48
15°	484	482	476	478	477	136
25°	438	435	430	430	428	201
35°	377	374	368	366	364	236
45°	308	305	298	294	293	237
55°	233	231	226	221	218	208
65°	158	156	152	148	146	156
75°	84	82	80	78	78	89
85°	22	22	21	21	21	24
90°	0	4	9	10	10	2
95°	16	51	400	198	120	18
105°	57	83	322	694	691	61
115°	101	127	287	552	664	100
125°	141	168	286	470	529	125
135°	168	199	283	417	474	129
145°	193	221	282	352	386	121
155°	220	237	274	310	324	101
165°	239	247	263	278	282	68
175°	250	250	252	255	254	24
180°	250	250	250	250	250	



TEST NUMBER: P332507-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	509.9	509.7	509.5	509.3	509.0	508.5	507.7	507.0	506.2	505.3	506.1
5°	508.2	507.8	507.5	507.1	506.8	506.1	505.1	504.1	503.1	502.0	503.1
7.5°	503.5	503.1	502.7	502.4	502.0	501.3	500.2	499.1	498.0	496.9	497.7
10°	499.2	498.9	498.5	498.2	497.8	497.1	495.8	494.6	493.5	492.3	493.0
12.5°	493.7	493.4	493.0	492.6	492.2	491.5	490.2	489.0	487.7	486.5	487.2
15°	483.7	483.4	483.0	482.7	482.3	481.5	480.1	478.7	477.3	476.0	476.6
17.5°	471.7	471.3	470.9	470.5	469.9	469.1	467.8	466.5	465.2	463.9	464.3
20°	463.0	462.5	462.1	461.6	461.2	460.3	458.9	457.5	456.2	454.8	455.1
22.5°	453.5	452.9	452.3	451.7	451.1	450.1	448.8	447.5	446.1	444.7	445.2
25°	438.1	437.5	436.9	436.2	435.6	434.6	433.3	432.0	430.8	429.6	429.6
27.5°	420.5	419.8	419.2	418.5	417.9	417.0	415.8	414.7	413.5	412.2	412.1
30°	408.8	408.0	407.3	406.6	405.9	404.9	403.7	402.5	401.4	400.2	399.8
32.5°	396.4	395.7	395.0	394.4	393.7	392.8	391.6	390.3	389.1	387.8	387.4
35°	376.9	376.3	375.7	375.1	374.4	373.5	372.2	370.9	369.7	368.4	367.8
37.5°	356.5	355.9	355.3	354.8	354.2	353.3	351.9	350.5	349.1	347.8	347.1
40°	343.1	342.4	341.7	341.0	340.3	339.2	337.9	336.5	335.1	333.8	332.9
42.5°	328.8	328.4	328.0	327.5	327.1	326.1	324.6	323.0	321.6	320.1	319.0
45°	307.7	307.0	306.4	305.8	305.1	304.1	302.6	301.2	299.8	298.3	297.3
47.5°	285.6	285.2	284.7	284.3	283.9	283.0	281.6	280.3	279.0	277.6	276.5
50°	270.6	270.3	269.9	269.5	269.1	268.4	267.1	265.8	264.5	263.3	262.0
52.5°	256.0	255.5	255.0	254.6	254.2	253.3	251.9	250.6	249.3	248.0	246.8
55°	232.7	232.5	232.1	231.9	231.6	230.8	229.5	228.3	227.0	225.8	224.7
57.5°	210.5	210.3	209.9	209.7	209.3	208.5	207.2	206.0	204.7	203.5	202.5
60°	195.2	194.8	194.3	193.8	193.4	192.6	191.4	190.2	189.1	187.9	187.1
62.5°	180.2	179.9	179.4	179.1	178.7	177.9	176.6	175.4	174.1	172.9	172.1
65°	157.7	157.3	156.8	156.4	155.9	155.2	154.3	153.4	152.5	151.6	150.7
67.5°	135.1	134.7	134.2	133.8	133.4	132.8	131.9	131.0	130.2	129.2	128.4
70°	121.1	120.4	119.8	119.2	118.5	117.8	117.1	116.4	115.6	114.9	114.2
72.5°	106.1	105.4	104.8	104.2	103.5	102.9	102.3	101.8	101.2	100.6	100.0
75°	83.9	83.5	83.1	82.6	82.1	81.7	81.3	80.8	80.3	79.9	79.6
77.5°	62.9	62.7	62.4	62.3	62.1	61.7	61.4	61.0	60.5	60.2	60.0
80°	50.1	49.9	49.6	49.3	49.1	48.8	48.6	48.5	48.3	48.1	47.9
82.5°	37.7	37.6	37.5	37.4	37.2	37.1	37.1	37.1	37.0	37.0	36.9
85°	22.0	22.0	22.0	22.0	22.0	22.0	21.7	21.5	21.4	21.2	21.2
87.5°	8.6	8.7	9.0	9.0	9.0	8.9	9.4	9.4	9.5	9.6	9.5
90°	0.5	1.5	2.9	3.4	4.0	4.0	6.9	6.9	7.8	8.9	8.4
92.5°	5.6	8.2	12.7	18.8	25.9	36.2	61.1	99.2	136.4	155.8	129.8
95°	16.2	17.7	22.6	29.0	40.7	61.4	104.1	184.7	302.0	400.3	411.6
97.5°	29.1	29.1	33.3	39.2	49.3	66.6	99.5	166.0	282.8	421.6	517.1
100°	37.4	37.4	40.7	46.7	56.0	71.7	100.7	156.2	256.4	394.9	520.6
102.5°	45.2	46.0	49.0	54.5	63.5	78.4	104.6	153.4	238.7	361.5	491.1
105°	57.4	59.0	61.4	67.3	76.1	90.4	113.9	154.7	223.5	322.2	437.6
107.5°	71.0	72.0	74.5	80.8	89.2	103.2	124.8	162.0	220.8	300.2	394.4
110°	80.1	81.0	83.5	89.4	98.2	111.5	133.1	167.5	221.5	292.7	372.8



TEST NUMBER: P332507-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	88.7	89.7	92.6	98.1	106.9	120.1	140.9	173.4	223.9	289.2	360.6
115°	101.2	102.6	106.1	111.0	120.4	133.6	153.3	182.7	228.4	287.3	349.2
117.5°	114.2	115.5	118.6	124.0	132.7	146.5	165.1	192.3	233.2	286.8	344.1
120°	122.8	123.8	127.2	132.6	140.9	154.7	173.4	198.9	236.8	286.8	341.4
122.5°	130.6	131.6	135.1	140.1	149.2	162.6	181.2	205.2	240.3	286.5	338.2
125°	140.9	142.9	145.9	151.3	160.6	174.4	192.0	214.6	245.6	285.9	333.0
127.5°	150.1	151.7	155.2	161.4	171.1	184.9	202.1	222.8	249.8	284.7	326.1
130°	155.2	157.1	161.1	168.5	177.8	192.0	208.7	227.9	253.0	284.4	321.7
132.5°	160.3	161.9	167.0	174.0	184.1	197.5	214.2	233.0	255.7	284.0	317.8
135°	167.5	169.4	174.4	182.7	193.0	205.8	222.0	239.7	259.8	283.4	311.9
137.5°	174.7	176.5	181.9	189.9	200.6	212.8	227.9	244.4	262.3	283.3	306.8
140°	179.8	181.2	186.7	195.0	205.3	217.1	231.9	247.5	264.2	282.9	304.0
142.5°	185.3	186.8	191.7	199.7	209.7	221.0	235.4	249.9	265.8	282.9	301.7
145°	193.0	194.5	199.4	206.3	215.6	226.4	239.2	252.4	266.7	281.9	297.6
147.5°	201.7	202.2	206.6	213.6	221.4	231.2	243.1	254.7	267.2	280.2	294.0
150°	207.2	207.8	211.7	217.6	225.0	234.3	245.1	255.9	267.2	279.0	291.3
152.5°	212.4	212.5	216.4	221.9	228.5	237.0	246.7	256.7	266.4	277.0	288.1
155°	219.6	220.1	223.0	227.9	233.3	240.6	249.0	257.4	265.2	274.1	283.4
157.5°	226.5	226.5	229.3	233.1	237.8	243.6	250.7	257.4	264.0	271.0	278.6
160°	230.8	230.8	232.8	236.3	240.1	245.6	251.5	257.4	262.8	268.6	275.1
162.5°	234.8	234.4	235.9	239.0	242.5	246.8	252.3	257.4	261.6	266.3	271.9
165°	239.2	239.2	240.1	242.6	245.1	248.1	252.4	256.4	259.3	262.8	266.7
167.5°	243.6	243.1	243.6	245.5	246.8	249.1	252.4	255.2	257.0	259.2	262.0
170°	245.6	245.1	245.6	247.0	248.1	249.5	251.9	254.4	255.4	256.8	258.8
172.5°	247.5	247.0	247.1	248.2	248.8	249.9	251.6	253.7	253.8	254.5	256.1
175°	249.5	249.0	249.0	249.5	250.0	250.0	251.0	252.4	251.9	251.9	253.0
177.5°	250.4	250.0	249.6	250.0	250.0	250.0	250.4	251.2	250.4	250.4	250.8
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332507-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	506.8	507.6	508.2	508.6	508.5	508.4	508.3	508.2
5°	504.1	505.1	506.1	506.4	506.3	506.1	505.9	505.8
7.5°	498.4	499.3	500.1	500.4	500.3	500.2	500.1	500.0
10°	493.8	494.5	495.2	495.5	495.3	495.1	494.9	494.7
12.5°	488.0	488.8	489.7	489.9	489.7	489.4	489.1	488.9
15°	477.1	477.6	478.2	478.3	478.0	477.8	477.5	477.3
17.5°	464.6	464.9	465.3	465.4	465.2	465.0	464.9	464.7
20°	455.4	455.6	455.9	456.0	455.7	455.6	455.4	455.2
22.5°	445.7	446.2	446.7	446.8	446.4	446.1	445.7	445.5
25°	429.7	429.8	429.9	429.8	429.4	429.0	428.7	428.3
27.5°	411.8	411.6	411.4	411.0	410.6	410.2	409.7	409.2
30°	399.5	399.2	398.7	398.4	397.9	397.4	397.0	396.6
32.5°	386.9	386.5	386.1	385.6	385.2	384.7	384.3	383.8
35°	367.1	366.5	365.8	365.3	364.9	364.5	363.9	363.5
37.5°	346.4	345.7	345.0	344.4	343.8	343.2	342.6	342.0
40°	332.0	331.1	330.2	329.5	329.0	328.6	328.1	327.7
42.5°	318.0	316.9	315.9	315.2	314.9	314.6	314.3	314.0
45°	296.4	295.3	294.4	293.7	293.4	293.2	292.9	292.7
47.5°	275.3	274.2	273.1	272.2	271.6	270.9	270.2	269.5
50°	260.7	259.5	258.2	257.3	256.8	256.2	255.6	255.1
52.5°	245.7	244.6	243.5	242.5	241.9	241.2	240.5	239.8
55°	223.6	222.5	221.4	220.6	220.1	219.6	219.0	218.4
57.5°	201.5	200.4	199.4	198.6	198.1	197.6	197.1	196.5
60°	186.2	185.5	184.6	184.0	183.6	183.0	182.6	182.2
62.5°	171.4	170.7	169.9	169.3	168.8	168.4	168.0	167.5
65°	149.8	148.9	148.0	147.3	146.9	146.4	145.9	145.5
67.5°	127.5	126.7	125.8	125.3	125.2	125.0	124.9	124.8
70°	113.5	112.8	112.0	111.5	111.2	111.0	110.7	110.5
72.5°	99.4	98.8	98.2	97.8	97.6	97.3	97.0	96.8
75°	79.1	78.8	78.4	78.2	78.1	78.0	77.9	77.8
77.5°	59.9	59.8	59.8	59.6	59.3	59.1	58.8	58.6
80°	47.7	47.5	47.4	47.3	47.1	47.0	46.9	46.8
82.5°	36.8	36.7	36.6	36.5	36.4	36.2	36.2	36.1
85°	21.2	21.2	21.2	21.2	21.1	21.0	20.8	20.8
87.5°	9.6	9.7	9.8	9.8	9.9	10.0	9.9	9.9
90°	8.9	9.3	9.8	9.8	10.3	10.8	10.3	10.3
92.5°	96.4	72.6	57.8	48.0	42.1	39.5	37.8	37.8
95°	363.9	287.8	222.0	174.4	150.3	135.1	126.2	119.9
97.5°	537.7	509.5	461.4	410.1	374.9	345.3	330.5	320.3
100°	592.4	602.2	578.1	541.7	499.0	469.1	454.3	450.4
102.5°	589.6	638.3	645.3	630.2	603.9	582.2	566.7	563.5
105°	550.1	635.1	683.7	703.9	704.8	700.9	694.0	691.0
107.5°	494.0	584.4	653.0	696.7	721.0	732.2	737.1	738.4
110°	460.2	545.2	616.4	670.5	705.3	725.9	734.8	739.2



TEST NUMBER: P332507-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.5	510.6	577.9	631.9	671.5	696.5	708.9	716.0
115°	410.6	471.1	528.5	575.7	614.4	643.9	659.6	663.6
117.5°	398.4	448.4	493.6	533.6	566.7	591.4	607.3	610.4
120°	393.0	438.6	477.9	512.7	540.8	562.4	575.1	580.6
122.5°	388.2	432.3	468.0	498.6	522.3	540.8	551.6	557.0
125°	380.1	422.4	456.2	483.3	502.9	517.2	526.5	529.4
127.5°	370.3	410.7	444.5	470.1	489.9	502.6	510.4	513.3
130°	362.5	401.3	434.6	460.7	480.9	493.1	501.0	503.9
132.5°	354.2	390.6	423.3	449.3	469.1	482.9	490.3	493.4
135°	342.9	374.8	404.7	429.3	448.9	462.7	470.5	473.5
137.5°	332.5	359.6	384.8	407.0	425.3	438.9	445.4	448.9
140°	326.6	349.7	371.8	392.4	409.7	420.4	427.3	431.3
142.5°	321.2	341.5	360.4	378.3	393.5	403.6	409.7	412.3
145°	313.3	330.0	344.8	358.5	370.8	379.2	384.1	386.5
147.5°	306.9	320.2	332.0	342.9	351.9	359.0	362.7	363.7
150°	303.1	314.4	324.2	333.0	340.9	347.2	350.2	350.7
152.5°	298.7	308.4	317.5	324.8	331.4	336.7	338.4	338.9
155°	292.2	300.1	307.5	313.3	318.3	322.2	323.6	323.6
157.5°	285.2	291.9	298.0	302.7	306.5	309.4	310.3	310.3
160°	280.9	286.4	291.7	295.7	298.6	301.6	302.0	302.0
162.5°	276.6	281.2	285.4	289.0	291.2	294.1	294.6	294.2
165°	270.6	273.5	277.0	279.5	281.5	283.4	282.9	282.4
167.5°	264.8	267.1	269.8	271.3	272.3	273.5	273.5	273.1
170°	261.3	262.8	264.8	266.2	267.2	267.7	267.2	267.2
172.5°	258.1	259.2	260.5	261.5	262.1	262.6	262.1	261.3
175°	253.9	254.4	255.4	255.4	255.4	256.4	255.4	254.4
177.5°	251.2	251.6	251.6	251.9	251.6	251.9	251.2	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0

(END OF REPORT)