

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332566-935

Luminaire Tested: **SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332566-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5125.8 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332566-935
CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P332566-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	94	90	85	82	85	81	78	74	65	63	61	51	49	48	38	37	36	29
2	85	78	71	66	77	70	65	60	57	53	50	44	42	39	33	31	29	24
3	78	68	61	55	70	62	55	50	50	45	41	39	36	33	29	27	25	20
4	71	60	52	46	64	54	47	42	44	39	35	34	31	28	25	23	21	17
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18	15
6	60	48	39	34	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14	11
8	51	39	31	26	46	35	28	24	29	24	20	23	19	16	17	14	12	10
9	47	35	28	23	43	32	26	21	26	21	18	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	19	24	19	16	19	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4830	4830	4830
5°	4845	4721	4734
10°	4816	4644	4639
15°	4772	4554	4529
20°	4707	4455	4422
25°	4634	4345	4302
30°	4555	4235	4181
35°	4464	4122	4074
40°	4393	4015	3964
45°	4286	3916	3867
50°	4195	3803	3767
55°	4102	3695	3648
60°	3957	3557	3541
65°	3798	3411	3409
70°	3603	3243	3253
75°	3334	3060	3114
80°	3035	2882	2977
85°	2656	2725	2896



TEST NUMBER: P332566-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.7	1.1
10°-20°	162.3	3.2
20°-30°	245.5	4.8
30°-40°	297.0	5.8
40°-50°	314.0	6.1
50°-60°	295.5	5.8
60°-70°	245.2	4.8
70°-80°	172.2	3.4
80°-90°	100.7	2.0
90°-100°	131.1	2.6
100°-110°	259.9	5.1
110°-120°	397.2	7.7
120°-130°	502.1	9.8
130°-140°	552.7	10.8
140°-150°	537.7	10.5
150°-160°	451.0	8.8
160°-170°	300.1	5.9
170°-180°	105.1	2.1
0°-30°	464.5	9.1
0°-40°	761.4	14.9
0°-60°	1370.9	26.7
0°-90°	1888.9	36.9
90°-120°	788.2	15.4
90°-150°	2380.7	46.4
90°-180°	3237.0	63.2
0°-180°	5125.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	599	597	592	597	597	57
15°	574	575	573	578	578	162
25°	525	529	531	538	539	242
35°	460	468	474	483	486	288
45°	383	396	409	420	423	296
55°	300	314	334	347	352	267
65°	208	229	252	268	274	206
75°	115	140	168	186	193	123
85°	36	64	94	113	121	38
90°	13	50	85	109	117	10
95°	60	90	124	143	150	64
105°	206	221	249	268	276	219
115°	379	386	404	418	422	374
125°	548	549	564	574	577	489
135°	705	710	715	724	726	546
145°	856	858	859	862	863	535
155°	980	980	979	982	979	451
165°	1066	1064	1062	1067	1064	301
175°	1110	1105	1104	1110	1104	105
180°	1111	1111	1111	1111	1111	



TEST NUMBER: P332566-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	598.3	598.3	598.3	598.3	598.3	598.3	598.3	598.3	598.3	598.3	598.3
2.5°	600.5	600.1	599.8	599.3	599.0	598.4	597.4	596.5	595.5	594.5	595.4
5°	599.0	598.6	598.1	597.6	597.2	596.4	595.4	594.3	593.3	592.3	593.5
7.5°	593.9	593.6	593.3	593.1	592.8	592.3	591.4	590.6	589.6	588.8	590.1
10°	589.6	589.4	589.3	589.2	589.0	588.6	587.8	587.0	586.3	585.6	586.9
12.5°	583.7	583.7	583.7	583.6	583.6	583.3	582.8	582.3	581.8	581.3	582.5
15°	574.2	574.4	574.5	574.6	574.8	574.6	574.2	573.8	573.3	572.8	574.2
17.5°	561.2	561.6	562.1	562.5	563.0	563.2	563.1	563.0	562.9	562.8	564.1
20°	552.1	552.5	552.9	553.5	553.9	554.1	554.3	554.5	554.6	554.7	556.2
22.5°	541.9	542.4	543.0	543.5	544.2	544.6	544.8	545.1	545.4	545.6	547.2
25°	525.3	526.2	527.1	528.0	528.8	529.5	529.9	530.4	530.9	531.3	533.0
27.5°	506.8	508.1	509.4	510.7	512.0	513.0	513.7	514.4	515.1	515.7	517.3
30°	494.5	495.7	496.8	498.0	499.2	500.3	501.4	502.4	503.4	504.5	506.2
32.5°	481.0	482.5	483.9	485.3	486.8	488.1	489.2	490.4	491.5	492.8	494.6
35°	459.6	461.4	463.2	464.9	466.7	468.4	469.8	471.4	472.9	474.3	476.5
37.5°	438.1	440.1	442.1	444.2	446.3	448.2	450.0	451.9	453.7	455.6	457.7
40°	424.1	426.0	428.0	429.9	431.9	433.9	435.9	438.0	440.1	442.2	444.4
42.5°	408.0	410.2	412.3	414.6	416.7	419.0	421.5	423.9	426.4	428.8	431.3
45°	383.2	386.1	388.9	391.8	394.5	397.4	400.2	403.0	405.9	408.7	411.2
47.5°	359.6	362.4	365.3	368.2	371.2	374.3	377.5	380.8	384.1	387.4	390.0
50°	342.3	345.6	348.9	352.2	355.5	358.8	362.1	365.3	368.6	371.9	374.8
52.5°	325.2	328.5	331.7	335.0	338.3	341.8	345.6	349.3	353.1	356.8	359.8
55°	300.1	303.2	306.4	309.5	312.6	316.4	320.9	325.4	329.8	334.3	337.3
57.5°	272.2	276.0	279.9	283.8	287.7	291.8	296.2	300.7	305.1	309.5	313.1
60°	253.9	257.8	261.7	265.5	269.4	273.8	278.7	283.6	288.5	293.4	296.9
62.5°	236.3	240.5	244.7	248.9	253.1	257.7	262.6	267.5	272.5	277.4	280.8
65°	207.7	212.5	217.2	222.0	226.8	231.7	236.7	241.8	246.8	251.9	255.6
67.5°	180.2	185.3	190.4	195.4	200.4	205.7	211.1	216.5	222.0	227.4	231.2
70°	161.4	166.5	171.6	176.7	181.8	187.1	192.7	198.4	204.1	209.7	213.7
72.5°	143.3	148.4	153.6	158.8	163.9	169.5	175.6	181.6	187.6	193.6	197.5
75°	115.2	120.7	126.2	131.7	137.2	143.2	149.4	155.7	162.0	168.2	172.4
77.5°	89.1	95.0	100.8	106.6	112.4	118.6	125.2	131.7	138.3	144.8	149.0
80°	73.0	79.0	85.0	90.9	96.9	103.1	109.7	116.2	122.8	129.3	133.8
82.5°	56.9	63.1	69.3	75.5	81.7	88.1	94.6	101.2	107.7	114.3	118.9
85°	35.5	41.8	48.0	54.2	60.5	67.0	73.7	80.4	87.1	93.8	98.2
87.5°	20.3	26.9	33.3	39.9	46.3	53.0	59.8	66.6	73.4	80.3	84.8
90°	13.3	21.4	29.4	37.5	45.5	53.6	61.5	69.4	77.3	85.2	90.7
92.5°	28.6	36.3	44.1	51.8	59.7	67.2	74.7	82.2	89.7	97.1	102.0
95°	60.3	66.9	73.5	80.2	86.8	93.8	101.3	108.7	116.1	123.6	128.2
97.5°	98.0	103.6	109.2	114.8	120.4	127.0	134.6	142.2	149.8	157.5	162.0
100°	127.7	132.3	137.0	141.5	146.2	152.3	159.8	167.4	174.9	182.4	186.8
102.5°	159.3	163.0	166.7	170.4	174.1	179.6	186.8	194.1	201.4	208.6	213.0
105°	206.3	209.4	212.6	215.8	219.0	223.7	230.0	236.2	242.5	248.7	253.0
107.5°	256.8	259.5	262.2	264.8	267.5	271.6	276.8	282.1	287.5	292.8	297.0
110°	290.7	293.2	295.6	298.1	300.6	304.3	309.3	314.4	319.3	324.3	327.4



TEST NUMBER: P332566-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.9	327.8	329.8	331.7	333.6	336.8	341.5	346.1	350.8	355.3	358.6
115°	378.8	380.0	381.4	382.7	384.1	386.9	391.3	395.7	400.1	404.5	407.5
117.5°	429.1	430.1	431.0	432.0	432.9	435.5	439.7	443.8	448.0	452.2	454.6
120°	462.3	463.5	464.7	465.9	467.1	469.6	473.3	477.1	480.8	484.6	486.6
122.5°	497.3	497.7	498.1	498.5	498.9	501.0	504.8	508.7	512.5	516.3	518.6
125°	548.4	548.3	548.1	547.9	547.8	549.5	553.0	556.6	560.1	563.6	566.0
127.5°	595.2	595.6	596.1	596.4	596.8	598.4	600.9	603.5	606.1	608.6	610.9
130°	627.7	628.1	628.5	629.0	629.3	630.8	633.1	635.5	637.9	640.2	642.6
132.5°	661.3	661.6	661.9	662.1	662.5	663.4	665.2	666.9	668.7	670.5	672.6
135°	705.2	706.4	707.5	708.6	709.8	710.8	711.9	712.9	714.0	715.1	717.0
137.5°	753.6	754.1	754.4	754.8	755.2	755.8	756.6	757.4	758.2	759.1	760.7
140°	786.0	786.2	786.4	786.7	786.9	787.1	787.2	787.4	787.6	787.7	789.5
142.5°	815.0	815.4	815.7	816.1	816.4	816.5	816.2	816.0	815.7	815.5	817.2
145°	855.7	856.4	857.0	857.6	858.2	858.6	858.8	859.0	859.2	859.4	860.1
147.5°	896.3	897.1	897.9	898.6	899.4	899.7	899.6	899.4	899.2	899.1	899.1
150°	921.1	921.7	922.3	922.9	923.5	923.9	923.9	923.9	923.9	923.9	923.9
152.5°	943.9	944.3	944.8	945.2	945.6	945.9	946.1	946.2	946.4	946.5	947.0
155°	979.7	979.7	979.7	979.7	979.7	979.6	979.4	979.2	979.0	978.9	979.6
157.5°	1010.0	1009.6	1009.3	1008.9	1008.6	1008.4	1008.3	1008.3	1008.3	1008.2	1008.8
160°	1027.9	1027.6	1027.4	1027.3	1027.1	1026.9	1026.7	1026.5	1026.3	1026.1	1026.7
162.5°	1044.3	1043.9	1043.4	1042.8	1042.3	1042.0	1041.8	1041.6	1041.5	1041.2	1042.2
165°	1066.5	1065.9	1065.4	1064.8	1064.2	1063.8	1063.3	1063.0	1062.6	1062.2	1063.3
167.5°	1083.6	1082.7	1081.9	1081.2	1080.3	1080.0	1080.0	1080.0	1080.0	1080.1	1081.2
170°	1093.1	1092.2	1091.2	1090.3	1089.3	1088.9	1089.2	1089.3	1089.5	1089.7	1090.9
172.5°	1100.0	1099.2	1098.5	1097.6	1096.8	1096.4	1096.5	1096.5	1096.6	1096.6	1097.9
175°	1109.5	1108.5	1107.6	1106.6	1105.7	1105.1	1104.9	1104.7	1104.5	1104.3	1105.7
177.5°	1112.6	1111.8	1111.0	1110.3	1109.5	1109.1	1109.1	1109.1	1109.1	1109.1	1110.2
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332566-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	598.3	598.3	598.3	598.3	598.3	598.3	598.3	598.3
2.5°	596.2	597.0	597.9	598.2	598.1	598.0	597.9	597.8
5°	594.7	595.8	597.0	597.5	597.4	597.3	597.1	596.9
7.5°	591.5	592.8	594.2	594.8	594.6	594.4	594.3	594.2
10°	588.2	589.6	590.9	591.5	591.4	591.2	591.1	590.9
12.5°	583.8	585.0	586.2	586.8	586.8	586.7	586.7	586.7
15°	575.5	576.9	578.2	578.8	578.7	578.5	578.3	578.2
17.5°	565.5	566.9	568.3	568.9	568.8	568.7	568.5	568.4
20°	557.8	559.2	560.7	561.5	561.5	561.5	561.5	561.5
22.5°	548.6	550.1	551.6	552.5	552.7	552.9	553.2	553.5
25°	534.6	536.2	537.9	538.7	538.9	539.1	539.2	539.3
27.5°	518.8	520.3	521.9	522.7	522.9	523.1	523.2	523.4
30°	507.8	509.5	511.1	512.0	512.3	512.6	512.9	513.2
32.5°	496.5	498.3	500.2	501.3	501.6	501.9	502.2	502.5
35°	478.5	480.6	482.7	484.0	484.4	484.8	485.3	485.8
37.5°	459.9	461.9	464.1	465.4	465.8	466.3	466.7	467.3
40°	446.7	448.9	451.2	452.5	453.1	453.7	454.3	455.0
42.5°	433.8	436.2	438.7	440.1	440.7	441.1	441.6	442.0
45°	413.8	416.3	418.8	420.4	421.2	422.0	422.7	423.4
47.5°	392.6	395.3	397.9	399.6	400.5	401.4	402.3	403.2
50°	377.8	380.8	383.7	385.7	386.6	387.4	388.4	389.3
52.5°	362.8	365.8	368.8	370.7	371.6	372.5	373.3	374.3
55°	340.3	343.3	346.2	348.2	349.0	350.0	350.9	351.7
57.5°	316.6	320.2	323.7	325.9	326.7	327.5	328.4	329.2
60°	300.3	303.8	307.1	309.4	310.6	311.9	313.1	314.3
62.5°	284.2	287.7	291.1	293.3	294.5	295.8	297.0	298.2
65°	259.3	263.1	266.8	269.2	270.4	271.6	272.9	274.1
67.5°	235.0	238.8	242.5	245.0	246.2	247.3	248.5	249.6
70°	217.7	221.8	225.8	228.3	229.4	230.4	231.4	232.5
72.5°	201.4	205.3	209.2	211.7	212.9	214.0	215.2	216.4
75°	176.5	180.6	184.9	187.6	188.9	190.3	191.7	193.0
77.5°	153.3	157.6	161.8	164.6	166.0	167.5	168.8	170.3
80°	138.3	142.7	147.1	150.0	151.2	152.4	153.6	154.8
82.5°	123.5	128.0	132.7	135.6	136.9	138.2	139.5	140.9
85°	102.7	107.2	111.7	114.7	116.1	117.6	119.1	120.6
87.5°	89.4	93.9	98.5	101.4	102.8	104.2	105.6	107.0
90°	96.2	101.6	107.1	110.6	112.2	113.7	115.3	116.9
92.5°	106.9	111.8	116.7	119.9	121.2	122.7	124.1	125.5
95°	132.8	137.4	142.0	144.9	146.3	147.7	149.0	150.3
97.5°	166.6	171.2	175.8	178.7	180.0	181.3	182.5	183.8
100°	191.2	195.6	200.0	202.8	203.8	204.8	205.9	206.9
102.5°	217.5	221.9	226.4	229.2	230.6	231.9	233.2	234.5
105°	257.4	261.7	266.0	269.0	270.7	272.5	274.2	276.0
107.5°	301.2	305.4	309.6	312.2	313.2	314.3	315.3	316.3
110°	330.5	333.5	336.6	339.0	340.7	342.5	344.2	346.0



TEST NUMBER: P332566-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	361.8	365.1	368.2	370.6	371.9	373.2	374.4	375.7
115°	410.6	413.7	416.8	418.8	419.7	420.5	421.3	422.1
117.5°	457.1	459.5	462.0	463.6	464.4	465.2	466.1	466.8
120°	488.6	490.6	492.7	494.5	496.0	497.6	499.2	500.8
122.5°	520.9	523.2	525.6	526.9	527.3	527.7	528.1	528.5
125°	568.5	570.9	573.4	574.9	575.4	575.9	576.4	577.0
127.5°	613.2	615.4	617.8	619.3	620.0	620.7	621.4	622.1
130°	644.9	647.2	649.5	650.7	650.8	650.9	651.1	651.2
132.5°	674.8	677.0	679.2	680.5	681.1	681.7	682.3	682.9
135°	719.0	721.0	723.1	724.2	724.5	724.9	725.1	725.5
137.5°	762.4	764.1	765.8	767.0	767.8	768.7	769.6	770.4
140°	791.2	792.9	794.7	795.8	796.3	796.9	797.5	798.1
142.5°	818.8	820.4	822.2	823.3	823.8	824.4	825.0	825.6
145°	860.8	861.5	862.2	862.5	862.5	862.6	862.6	862.6
147.5°	899.1	899.0	899.0	899.1	899.4	899.7	899.9	900.3
150°	923.9	923.9	923.9	923.8	923.6	923.3	923.2	923.0
152.5°	947.4	947.9	948.4	948.4	947.9	947.4	946.8	946.3
155°	980.4	981.1	981.9	981.9	981.1	980.4	979.6	978.9
157.5°	1009.4	1010.0	1010.6	1010.5	1009.9	1009.2	1008.6	1007.9
160°	1027.3	1027.9	1028.4	1028.2	1027.3	1026.3	1025.4	1024.4
162.5°	1043.3	1044.3	1045.3	1045.4	1044.5	1043.5	1042.6	1041.6
165°	1064.5	1065.7	1066.8	1067.0	1066.3	1065.5	1064.7	1063.9
167.5°	1082.4	1083.6	1084.7	1084.7	1083.5	1082.3	1081.1	1080.0
170°	1092.0	1093.1	1094.3	1094.2	1092.9	1091.5	1090.2	1088.8
172.5°	1099.2	1100.4	1101.8	1101.7	1100.4	1099.1	1097.8	1096.4
175°	1107.0	1108.4	1109.7	1109.7	1108.4	1107.0	1105.7	1104.3
177.5°	1111.3	1112.3	1113.4	1113.4	1112.2	1110.9	1109.7	1108.5
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2

(END OF REPORT)