

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332568-935

Luminaire Tested: **SA4XXDIP-C575D1035U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332568-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5703.7 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332568-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332568-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	40	39	38	32
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	26
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332568-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	1.4
10°-20°	221.9	3.9
20°-30°	326.6	5.7
30°-40°	379.6	6.7
40°-50°	379.6	6.7
50°-60°	332.1	5.8
60°-70°	246.6	4.3
70°-80°	140.1	2.5
80°-90°	43.8	0.8
90°-100°	39.3	0.7
100°-110°	250.6	4.4
110°-120°	479.4	8.4
120°-130°	608.6	10.7
130°-140°	651.1	11.4
140°-150°	608.9	10.7
150°-160°	491.0	8.6
160°-170°	316.7	5.6
170°-180°	109.2	1.9
0°-30°	627.2	11.0
0°-40°	1006.8	17.7
0°-60°	1718.5	30.1
0°-90°	2149.0	37.7
90°-120°	769.3	13.5
90°-150°	2637.9	46.2
90°-180°	3555.0	62.3
0°-180°	5703.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	3	12	19	24	26	4
95°	47	20	19	24	25	61
105°	259	264	268	274	245	271
115°	483	485	485	486	486	475
125°	679	682	681	683	684	606
135°	842	842	845	847	848	649
145°	971	974	974	975	976	607
155°	1065	1066	1063	1066	1064	491
165°	1123	1119	1119	1125	1118	317
175°	1149	1144	1145	1152	1142	109
180°	1149	1149	1149	1149	1149	



TEST NUMBER: P332568-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.5	14.7	15.1	15.3	15.7	15.9	16.1	16.3	16.4	16.6	16.9
90°	2.6	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1
92.5°	10.8	10.9	11.0	11.2	11.3	12.1	13.6	15.2	16.7	18.3	19.4
95°	47.3	40.8	34.3	27.8	21.3	18.2	18.3	18.5	18.7	18.9	20.1
97.5°	100.4	104.4	108.5	112.5	116.6	108.0	86.6	65.3	44.0	22.7	22.8
100°	140.9	144.4	147.8	151.3	154.7	143.3	116.9	90.6	64.1	37.8	34.6
102.5°	186.3	188.9	191.4	193.9	196.4	196.0	192.5	189.1	185.6	182.2	147.1
105°	258.7	259.8	261.0	262.2	263.3	264.3	265.3	266.2	267.3	268.2	269.9
107.5°	325.9	326.5	327.1	327.6	328.2	329.2	330.5	331.7	333.0	334.3	335.2
110°	371.3	371.9	372.5	373.0	373.6	374.4	375.6	376.8	377.9	379.0	379.4



TEST NUMBER: P332568-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.3	416.4	417.4	418.4	419.5	420.3	420.8	421.3	421.8	422.3	422.3
115°	483.0	483.6	484.2	484.7	485.3	485.5	485.3	485.2	484.9	484.7	485.2
117.5°	544.1	544.8	545.6	546.4	547.2	547.7	548.1	548.5	549.0	549.4	549.3
120°	585.3	586.1	586.9	587.6	588.4	588.7	588.5	588.3	588.1	587.9	588.3
122.5°	623.8	624.3	624.7	625.2	625.7	626.0	626.3	626.5	626.8	627.1	627.3
125°	679.0	679.8	680.5	681.3	682.1	682.3	681.9	681.5	681.1	680.7	681.3
127.5°	731.2	731.4	731.7	731.8	732.0	732.5	733.5	734.3	735.2	736.1	736.0
130°	765.0	765.2	765.3	765.5	765.7	766.1	766.7	767.2	767.8	768.4	768.6
132.5°	795.9	796.3	796.6	796.9	797.3	797.8	798.6	799.3	800.0	800.7	800.9
135°	842.3	842.1	842.0	841.7	841.5	841.8	842.6	843.3	844.1	844.9	845.2
137.5°	883.4	883.5	883.6	883.6	883.7	884.2	885.0	885.9	886.7	887.5	887.9
140°	910.2	910.6	911.0	911.4	911.7	912.1	912.5	912.9	913.3	913.7	914.2
142.5°	934.3	935.0	935.6	936.3	937.0	937.5	937.7	938.0	938.1	938.4	938.8
145°	971.2	971.8	972.4	972.9	973.5	973.8	973.8	973.8	973.8	973.8	974.0
147.5°	1000.7	1001.7	1002.8	1003.8	1005.0	1005.4	1005.1	1005.0	1004.8	1004.6	1004.8
150°	1021.9	1022.7	1023.5	1024.2	1025.0	1025.3	1025.1	1024.9	1024.8	1024.5	1024.5
152.5°	1039.8	1040.4	1041.0	1041.6	1042.2	1042.4	1042.1	1041.7	1041.4	1041.0	1041.4
155°	1065.0	1065.1	1065.3	1065.5	1065.7	1065.5	1065.0	1064.4	1063.8	1063.2	1063.9
157.5°	1086.1	1086.0	1085.8	1085.7	1085.6	1085.2	1084.6	1083.9	1083.3	1082.6	1083.7
160°	1098.5	1097.9	1097.3	1096.7	1096.1	1095.8	1095.6	1095.4	1095.2	1095.0	1096.1
162.5°	1109.5	1108.7	1108.0	1107.2	1106.6	1106.1	1105.9	1105.7	1105.5	1105.4	1106.5
165°	1123.3	1122.4	1121.5	1120.5	1119.6	1119.0	1119.0	1119.0	1119.0	1119.0	1120.6
167.5°	1134.4	1133.4	1132.4	1131.4	1130.4	1129.9	1129.7	1129.6	1129.5	1129.4	1131.1
170°	1140.6	1139.4	1138.2	1137.1	1136.0	1135.5	1135.7	1135.9	1136.1	1136.3	1137.8
172.5°	1144.7	1143.6	1142.4	1141.3	1140.1	1139.6	1139.8	1140.1	1140.2	1140.4	1141.9
175°	1149.2	1148.1	1146.9	1145.7	1144.6	1144.1	1144.3	1144.5	1144.7	1144.9	1146.6
177.5°	1151.2	1150.1	1149.1	1148.1	1146.9	1146.6	1146.9	1147.2	1147.5	1147.8	1149.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332568-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	17.1	17.3	17.6	17.7	17.8	17.9	17.9	18.0
90°	21.2	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	20.5	21.7	22.8	23.4	23.5	23.6	23.7	23.8
95°	21.2	22.4	23.5	24.2	24.4	24.5	24.7	24.9
97.5°	22.9	23.1	23.2	23.3	23.5	23.7	23.8	24.1
100°	31.3	28.1	24.8	23.3	23.5	23.7	23.8	24.1
102.5°	112.2	77.1	42.1	24.6	24.6	24.7	24.7	24.8
105°	271.6	273.3	275.0	272.5	265.6	258.7	251.8	245.0
107.5°	336.0	336.9	337.7	338.5	339.2	339.9	340.7	341.4
110°	379.8	380.2	380.6	381.1	381.6	382.2	382.8	383.3



TEST NUMBER: P332568-935

CATALOG NUMBER: SA4XXDIP-C575D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	422.2	422.1	422.1	422.4	423.1	423.9	424.6	425.2
115°	485.5	485.9	486.3	486.5	486.5	486.5	486.5	486.5
117.5°	549.2	549.1	549.1	549.1	549.0	548.9	548.8	548.7
120°	588.7	589.0	589.4	589.4	589.0	588.7	588.3	587.9
122.5°	627.6	627.8	628.0	627.9	627.6	627.2	626.8	626.4
125°	681.9	682.4	683.0	683.4	683.6	683.8	684.0	684.2
127.5°	735.9	735.7	735.6	735.5	735.4	735.2	735.0	734.9
130°	768.8	769.0	769.1	769.3	769.3	769.3	769.3	769.3
132.5°	801.1	801.3	801.5	801.5	801.3	801.2	801.1	800.9
135°	845.7	846.0	846.4	846.8	847.2	847.6	847.9	848.3
137.5°	888.4	888.8	889.2	889.3	889.2	889.2	889.0	888.9
140°	914.8	915.4	915.9	916.4	916.5	916.7	916.9	917.1
142.5°	939.3	939.7	940.1	940.3	940.4	940.4	940.5	940.5
145°	974.2	974.4	974.6	974.9	975.3	975.6	976.0	976.4
147.5°	1004.9	1005.0	1005.2	1005.4	1005.6	1005.7	1006.0	1006.2
150°	1024.5	1024.5	1024.5	1024.6	1024.8	1025.0	1025.2	1025.4
152.5°	1041.6	1042.0	1042.2	1042.3	1042.2	1042.2	1042.0	1041.9
155°	1064.7	1065.5	1066.3	1066.3	1065.8	1065.2	1064.6	1064.1
157.5°	1084.6	1085.6	1086.6	1086.6	1085.6	1084.6	1083.7	1082.6
160°	1097.3	1098.5	1099.6	1099.6	1098.5	1097.3	1096.1	1095.0
162.5°	1107.6	1108.8	1109.9	1109.8	1108.5	1107.2	1106.0	1104.7
165°	1122.1	1123.7	1125.2	1125.1	1123.3	1121.6	1119.9	1118.2
167.5°	1132.7	1134.5	1136.1	1136.0	1134.1	1132.2	1130.2	1128.3
170°	1139.4	1140.8	1142.4	1142.2	1140.3	1138.4	1136.4	1134.5
172.5°	1143.5	1145.0	1146.5	1146.2	1144.2	1142.1	1140.1	1138.0
175°	1148.3	1150.0	1151.8	1151.4	1149.2	1146.9	1144.6	1142.3
177.5°	1150.2	1151.4	1152.7	1152.4	1150.6	1148.7	1146.9	1145.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2

(END OF REPORT)