

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918527

Luminaire Tested: DFN2DIP-4P2F0-030D040US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918527
REPORT IS A COMBINATION OF REPORTS P900545 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D040US935-FLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5966.7 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 60.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918527

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918527

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	32	52	41	34	29	35	29	25	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2517	2517	2517
5°	2516	2475	2494
10°	2490	2436	2456
15°	2448	2389	2399
20°	2394	2327	2341
25°	2340	2254	2275
30°	2273	2186	2191
35°	2209	2106	2103
40°	2132	2026	2019
45°	2054	1945	1933
50°	1969	1859	1833
55°	1879	1761	1741
60°	1778	1645	1635
65°	1666	1524	1510
70°	1524	1377	1375
75°	1331	1200	1245
80°	1095	974	1007
85°	733	609	626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2054 cd/sqm

TEST NUMBER: P918527

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.6
10°-20°	266.2	4.5
20°-30°	391.1	6.6
30°-40°	454.3	7.6
40°-50°	453.7	7.6
50°-60°	395.6	6.6
60°-70°	292.5	4.9
70°-80°	165.5	2.8
80°-90°	45.7	0.8
90°-100°	38.3	0.6
100°-110°	142.9	2.4
110°-120°	378.9	6.4
120°-130°	628.5	10.5
130°-140°	667.6	11.2
140°-150°	620.4	10.4
150°-160°	498.8	8.4
160°-170°	321.4	5.4
170°-180°	110.6	1.9
0°-30°	751.9	12.6
0°-40°	1206.2	20.2
0°-60°	2055.6	34.5
0°-90°	2559.2	42.9
90°-120°	560.1	9.4
90°-150°	2476.6	41.5
90°-180°	3407.0	57.1
0°-180°	5966.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1005	1005	1005	1005	1005	
5°	1005	1001	991	998	996	95
15°	957	951	938	942	938	269
25°	866	858	842	844	842	398
35°	747	737	722	716	711	467
45°	608	601	587	576	572	469
55°	460	454	443	431	426	411
65°	310	304	295	286	281	307
75°	162	160	156	150	152	173
85°	40	39	38	35	34	44
90°	1	10	17	21	23	5
95°	55	27	33	37	36	65
105°	256	281	51	60	64	273
115°	484	498	519	130	69	476
125°	684	695	711	717	719	610
135°	846	860	867	876	874	654
145°	982	981	995	1001	997	614
155°	1081	1073	1083	1088	1082	498
165°	1139	1134	1136	1142	1136	322
175°	1165	1159	1161	1166	1158	111
180°	1162	1162	1162	1162	1162	

TEST NUMBER: P918527

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1005.0	1005.0	1005.0	1005.0	1005.0
2.5°	1010.9	1006.1	995.4	1005.0	1003.2
5°	1005.0	1001.3	990.6	998.3	996.4
7.5°	998.3	992.6	981.9	989.7	987.7
10°	987.7	980.9	969.4	977.1	974.2
12.5°	973.2	967.4	955.9	960.6	958.7
15°	956.7	951.1	938.4	942.3	937.5
17.5°	936.4	930.7	918.1	922.9	918.1
20°	914.2	908.4	894.9	897.8	894.0
22.5°	892.1	883.4	870.7	870.7	868.7
25°	865.9	858.2	841.8	843.7	841.8
27.5°	836.9	830.1	817.6	814.8	809.9
30°	808.0	800.2	785.7	782.8	778.9
32.5°	777.1	771.3	755.8	749.9	746.1
35°	747.1	737.4	721.9	716.1	711.3
37.5°	713.3	704.6	689.1	682.3	677.4
40°	678.5	670.7	655.2	646.6	642.7
42.5°	644.6	636.9	621.5	611.7	606.0
45°	608.0	601.1	586.6	576.0	572.1
47.5°	572.1	565.4	549.9	539.2	533.5
50°	534.4	529.6	516.1	502.6	497.7
52.5°	497.7	490.9	478.5	467.8	461.0
55°	460.1	454.3	442.6	431.1	426.3
57.5°	422.3	417.5	404.9	393.3	389.4
60°	384.6	380.8	367.3	356.6	353.8
62.5°	347.9	341.1	331.5	321.8	318.0
65°	310.3	304.4	294.8	286.1	281.3
67.5°	271.6	266.7	258.0	251.3	247.5
70°	235.8	232.0	223.3	216.5	212.7
72.5°	199.1	195.2	190.4	183.7	180.8
75°	162.3	160.5	155.6	149.8	151.8
77.5°	129.5	125.6	123.6	120.8	118.0
80°	96.7	95.7	93.7	90.8	88.9
82.5°	65.7	65.7	64.8	60.9	60.9
85°	39.6	38.7	37.7	34.8	33.8
87.5°	17.4	15.5	13.5	10.7	9.6
90°	0.8	10.1	16.8	21.1	22.6
92.5°	21.1	17.7	20.1	21.9	22.6
95°	54.6	26.9	32.7	37.0	36.2
97.5°	98.4	29.4	42.9	45.5	46.2
100°	148.9	33.7	48.0	54.6	56.3
102.5°	204.3	202.8	49.6	58.8	61.4
105°	255.6	280.9	51.3	60.5	63.9
107.5°	315.4	336.4	53.0	62.3	65.6
110°	372.6	390.2	147.2	63.1	66.4

TEST NUMBER: P918527

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	426.5	441.5	427.2	64.7	67.3
115°	483.5	497.8	518.9	129.5	69.1
117.5°	533.2	550.0	564.4	444.0	223.7
120°	588.8	601.3	616.5	626.6	513.1
122.5°	635.8	649.3	666.2	671.1	672.0
125°	683.7	694.7	710.7	716.6	719.1
127.5°	727.5	739.3	751.9	760.3	761.1
130°	768.7	782.2	791.3	800.6	799.9
132.5°	810.7	821.7	830.9	838.5	837.8
135°	846.1	859.6	867.1	875.5	873.9
137.5°	883.0	893.1	901.6	910.0	907.5
140°	919.2	926.0	935.2	942.8	938.6
142.5°	949.6	955.4	966.4	973.0	968.9
145°	981.5	980.7	994.9	1000.8	996.6
147.5°	1009.2	1006.7	1021.0	1025.2	1021.9
150°	1036.1	1030.3	1043.8	1048.8	1044.6
152.5°	1058.9	1052.1	1064.7	1069.8	1063.9
155°	1080.7	1073.2	1083.3	1088.3	1081.6
157.5°	1098.4	1091.7	1099.3	1105.2	1098.4
160°	1113.5	1108.4	1113.5	1118.5	1112.7
162.5°	1127.0	1122.0	1126.2	1132.0	1124.5
165°	1138.8	1133.8	1136.3	1142.1	1136.3
167.5°	1148.1	1142.9	1145.6	1151.4	1143.8
170°	1155.6	1150.6	1152.2	1158.1	1150.6
172.5°	1160.6	1155.6	1157.4	1163.2	1155.6
175°	1164.8	1158.9	1160.6	1166.5	1158.1
177.5°	1166.5	1160.6	1161.5	1167.4	1159.9
180°	1162.3	1162.3	1162.3	1162.3	1162.3

TEST NUMBER: P918527

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US935-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.65	10.45	10.66	11.47	12.84	9.20	10.01	10.22	11.03	12.40
	3H	11.28	12.00	12.31	13.03	14.42	10.79	11.51	11.82	12.54	13.93
	4H	11.85	12.53	12.89	13.57	14.97	11.36	12.04	12.40	13.08	14.47
	6H	12.23	12.86	13.28	13.90	15.31	11.73	12.36	12.78	13.40	14.81
	8H	12.33	12.92	13.38	13.98	15.38	11.82	12.42	12.88	13.48	14.88
	12H	12.36	12.93	13.42	13.98	15.41	11.86	12.42	12.91	13.47	14.90
4H	2H	10.09	10.77	11.14	11.81	13.20	9.73	10.41	10.78	11.45	12.85
	3H	11.92	12.49	12.98	13.56	14.97	11.52	12.08	12.57	13.15	14.56
	4H	12.62	13.14	13.68	14.19	15.63	12.19	12.71	13.25	13.77	15.20
	6H	13.11	13.55	14.18	14.63	16.06	12.68	13.12	13.74	14.20	15.63
	8H	13.24	13.66	14.31	14.73	16.18	12.81	13.23	13.88	14.30	15.74
	12H	13.30	13.68	14.39	14.77	16.21	12.86	13.23	13.94	14.32	15.77
8H	4H	12.80	13.21	13.87	14.29	15.73	12.42	12.84	13.49	13.91	15.35
	6H	13.40	13.74	14.49	14.86	16.29	13.01	13.36	14.10	14.47	15.91
	8H	13.60	13.90	14.70	15.00	16.46	13.21	13.51	14.31	14.61	16.07
	12H	13.72	13.98	14.82	15.07	16.57	13.31	13.57	14.41	14.66	16.16
12H	4H	12.78	13.15	13.86	14.24	15.69	12.41	12.78	13.49	13.87	15.32
	6H	13.42	13.72	14.52	14.82	16.28	13.05	13.35	14.15	14.45	15.91
	8H	13.64	13.91	14.75	15.00	16.50	13.26	13.53	14.36	14.62	16.12