

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332588-935

Luminaire Tested: **SA4XXDIP-C795D365U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332588-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D365U935-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4060.3 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332588-935
CATALOG NUMBER: SA4XXDIP-C795D365U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332588-935

CATALOG NUMBER: SA4XXDIP-C795D365U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72				72
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	68	66	65	61				61
2	94	86	79	74	88	82	76	71	74	69	65	66	63	60	60	57	54	51				51
3	85	75	68	62	81	72	65	59	65	59	55	59	54	51	53	49	46	43				43
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37				37
5	72	60	51	45	68	57	49	44	52	45	41	47	42	38	43	38	35	32				32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28				28
7	61	49	40	35	58	47	39	34	43	36	31	39	33	29	35	31	27	25				25
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	32	28	25	22				22
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	25	22	20				20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20	18				18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9227	9227	9227
5°	9255	9143	9210
10°	9197	9069	9114
15°	9086	8940	8964
20°	8937	8781	8789
25°	8769	8598	8573
30°	8563	8383	8307
35°	8348	8159	8051
40°	8126	7904	7759
45°	7895	7654	7507
50°	7637	7430	7200
55°	7361	7142	6909
60°	7083	6817	6610
65°	6770	6508	6245
70°	6420	6097	5858
75°	5883	5599	5459
80°	5235	5026	4895
85°	4576	4409	4326



TEST NUMBER: P332588-935

CATALOG NUMBER: SA4XXDIP-C795D365U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.6	2.7
10°-20°	303.3	7.5
20°-30°	446.4	11.0
30°-40°	518.9	12.8
40°-50°	518.9	12.8
50°-60°	453.9	11.2
60°-70°	337.1	8.3
70°-80°	191.5	4.7
80°-90°	56.1	1.4
90°-100°	111.9	2.8
100°-110°	232.8	5.7
110°-120°	208.5	5.1
120°-130°	175.4	4.3
130°-140°	146.3	3.6
140°-150°	111.7	2.8
150°-160°	78.5	1.9
160°-170°	46.2	1.1
170°-180°	15.0	0.4
0°-30°	857.3	21.1
0°-40°	1376.2	33.9
0°-60°	2349.1	57.9
0°-90°	2933.8	72.3
90°-120°	553.3	13.6
90°-150°	986.7	24.3
90°-180°	1126.0	27.7
0°-180°	4060.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1143	1143	1143	1143	1143	
5°	1142	1138	1128	1138	1136	108
15°	1087	1083	1070	1075	1072	306
25°	984	978	965	966	962	453
35°	847	840	828	822	817	529
45°	692	685	670	661	658	533
55°	523	520	507	497	491	468
65°	354	350	341	332	327	351
75°	189	184	180	176	175	200
85°	49	49	48	48	47	54
90°	0	2	6	6	6	3
95°	10	32	248	123	74	11
105°	36	52	200	430	428	38
115°	63	79	178	342	411	62
125°	87	104	177	291	328	78
135°	104	124	176	258	293	80
145°	120	137	175	218	239	75
155°	136	147	170	192	200	63
165°	148	153	163	172	175	42
175°	154	155	156	158	158	15
180°	155	155	155	155	155	



TEST NUMBER: P332588-935

CATALOG NUMBER: SA4XXDIP-C795D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0
2.5°	1145.9	1145.4	1144.9	1144.4	1143.9	1142.8	1141.0	1139.2	1137.4	1135.7	1137.2
5°	1142.0	1141.3	1140.4	1139.6	1138.8	1137.2	1135.0	1132.7	1130.5	1128.3	1130.5
7.5°	1131.4	1130.6	1129.8	1128.9	1128.2	1126.5	1124.0	1121.5	1119.0	1116.5	1118.4
10°	1121.9	1121.1	1120.2	1119.5	1118.6	1116.9	1114.2	1111.6	1109.0	1106.3	1107.9
12.5°	1109.4	1108.6	1107.8	1107.0	1106.2	1104.3	1101.6	1098.7	1096.0	1093.1	1094.9
15°	1087.1	1086.2	1085.5	1084.6	1083.8	1081.9	1078.8	1075.8	1072.7	1069.7	1070.9
17.5°	1060.1	1059.1	1058.1	1057.1	1056.1	1054.1	1051.3	1048.4	1045.4	1042.6	1043.4
20°	1040.3	1039.3	1038.4	1037.3	1036.3	1034.2	1031.2	1028.1	1025.1	1022.1	1022.7
22.5°	1019.2	1017.8	1016.4	1015.1	1013.7	1011.6	1008.5	1005.5	1002.4	999.4	1000.5
25°	984.5	983.1	981.6	980.2	978.8	976.6	973.8	970.9	968.1	965.3	965.4
27.5°	944.9	943.5	942.0	940.6	939.1	937.0	934.4	931.8	929.1	926.4	925.9
30°	918.6	917.0	915.3	913.7	912.1	909.9	907.2	904.7	902.0	899.3	898.5
32.5°	890.7	889.2	887.8	886.3	884.8	882.7	879.9	877.1	874.3	871.5	870.6
35°	847.1	845.7	844.3	842.8	841.5	839.3	836.5	833.6	830.8	827.9	826.5
37.5°	801.2	799.9	798.6	797.3	795.9	793.8	790.7	787.6	784.6	781.5	780.0
40°	771.1	769.5	767.8	766.2	764.6	762.2	759.2	756.1	753.1	750.0	748.0
42.5°	738.9	737.9	736.9	736.0	734.9	732.8	729.4	726.1	722.6	719.3	717.0
45°	691.5	690.0	688.6	687.2	685.8	683.4	680.2	676.9	673.6	670.4	668.1
47.5°	641.8	640.8	639.9	638.9	637.9	635.9	632.9	629.9	626.9	623.9	621.3
50°	608.1	607.3	606.5	605.6	604.9	603.0	600.2	597.4	594.4	591.6	588.8
52.5°	575.1	574.2	573.2	572.2	571.2	569.2	566.2	563.2	560.2	557.2	554.7
55°	523.0	522.3	521.7	521.1	520.5	518.8	515.9	513.1	510.2	507.4	504.9
57.5°	473.1	472.4	471.7	471.1	470.4	468.6	465.8	463.0	460.2	457.4	455.0
60°	438.7	437.6	436.6	435.7	434.6	432.7	430.2	427.5	424.8	422.2	420.3
62.5°	405.0	404.2	403.3	402.4	401.6	399.8	396.9	394.1	391.3	388.5	386.8
65°	354.4	353.4	352.4	351.4	350.3	348.8	346.8	344.7	342.7	340.7	338.6
67.5°	303.5	302.6	301.6	300.7	299.8	298.3	296.4	294.4	292.5	290.5	288.5
70°	272.0	270.6	269.1	267.7	266.3	264.8	263.1	261.5	259.8	258.3	256.7
72.5°	238.3	236.9	235.5	234.0	232.6	231.3	230.0	228.6	227.3	226.0	224.7
75°	188.6	187.6	186.7	185.6	184.6	183.6	182.5	181.5	180.6	179.5	178.7
77.5°	141.2	140.8	140.3	139.9	139.4	138.8	137.8	137.0	136.0	135.2	134.9
80°	112.6	112.0	111.4	110.8	110.2	109.7	109.3	108.9	108.5	108.1	107.6
82.5°	84.8	84.6	84.2	83.9	83.7	83.5	83.4	83.3	83.3	83.2	82.9
85°	49.4	49.4	49.4	49.4	49.4	49.2	48.8	48.5	48.0	47.6	47.6
87.5°	19.1	19.0	19.1	19.0	18.9	18.7	18.9	18.8	18.7	18.7	18.6
90°	0.3	0.9	1.8	2.2	2.4	2.4	4.2	4.2	4.9	5.5	5.2
92.5°	3.4	5.1	7.9	11.6	16.1	22.4	37.9	61.5	84.5	96.5	80.4
95°	10.1	10.9	14.0	18.0	25.2	38.1	64.5	114.4	187.2	248.0	255.0
97.5°	18.0	18.0	20.7	24.3	30.6	41.2	61.6	102.9	175.1	261.2	320.4
100°	23.2	23.2	25.2	28.9	34.7	44.4	62.4	96.8	158.9	244.7	322.5
102.5°	28.0	28.5	30.4	33.8	39.3	48.6	64.8	95.1	147.9	223.9	304.3
105°	35.6	36.5	38.1	41.7	47.2	56.0	70.6	95.8	138.4	199.6	271.1
107.5°	44.0	44.6	46.1	50.0	55.3	64.0	77.3	100.4	136.7	186.0	244.4
110°	49.6	50.2	51.7	55.4	60.9	69.1	82.5	103.8	137.2	181.3	231.0



TEST NUMBER: P332588-935

CATALOG NUMBER: SA4XXDIP-C795D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.9	55.5	57.3	60.7	66.2	74.4	87.3	107.5	138.7	179.2	223.4
115°	62.7	63.6	65.7	68.8	74.6	82.7	95.0	113.2	141.5	178.1	216.4
117.5°	70.7	71.5	73.4	76.8	82.2	90.7	102.3	119.1	144.5	177.7	213.2
120°	76.1	76.7	78.8	82.1	87.3	95.8	107.5	123.2	146.7	177.7	211.5
122.5°	80.9	81.5	83.7	86.8	92.5	100.7	112.3	127.2	148.9	177.5	209.6
125°	87.3	88.5	90.4	93.8	99.5	108.1	119.0	132.9	152.1	177.1	206.3
127.5°	93.0	93.9	96.2	100.0	106.0	114.6	125.2	138.0	154.8	176.4	202.0
130°	96.2	97.4	99.8	104.4	110.1	119.0	129.3	141.2	156.7	176.2	199.3
132.5°	99.4	100.3	103.5	107.8	114.1	122.3	132.8	144.4	158.4	176.0	196.9
135°	103.8	105.0	108.1	113.2	119.6	127.5	137.5	148.5	161.0	175.6	193.2
137.5°	108.2	109.3	112.7	117.6	124.2	131.8	141.2	151.4	162.5	175.6	190.1
140°	111.4	112.3	115.6	120.8	127.2	134.5	143.6	153.3	163.7	175.3	188.4
142.5°	114.8	115.7	118.8	123.7	129.8	136.9	145.9	154.8	164.7	175.3	186.9
145°	119.6	120.5	123.6	127.8	133.6	140.3	148.2	156.4	165.2	174.7	184.4
147.5°	125.0	125.3	128.0	132.3	137.2	143.2	150.6	157.8	165.6	173.6	182.2
150°	128.4	128.7	131.1	134.8	139.4	145.2	151.9	158.5	165.6	172.8	180.5
152.5°	131.6	131.6	134.1	137.5	141.5	146.9	152.8	159.0	165.1	171.6	178.5
155°	136.0	136.3	138.2	141.2	144.6	149.1	154.3	159.5	164.4	169.8	175.6
157.5°	140.3	140.3	142.1	144.4	147.3	150.9	155.3	159.5	163.5	167.9	172.6
160°	143.0	143.0	144.2	146.4	148.8	152.1	155.8	159.5	162.8	166.4	170.4
162.5°	145.4	145.3	146.2	148.1	150.2	152.9	156.3	159.5	162.0	165.0	168.5
165°	148.2	148.2	148.8	150.3	151.9	153.7	156.4	158.9	160.7	162.8	165.2
167.5°	150.9	150.6	150.9	152.1	152.9	154.4	156.4	158.1	159.2	160.6	162.3
170°	152.1	151.9	152.1	153.1	153.7	154.5	156.1	157.6	158.3	159.1	160.4
172.5°	153.3	153.1	153.1	153.8	154.1	154.8	155.8	157.1	157.3	157.6	158.7
175°	154.5	154.3	154.3	154.5	154.9	154.9	155.5	156.4	156.1	156.1	156.7
177.5°	155.2	154.9	154.6	154.9	154.9	154.9	155.2	155.6	155.2	155.2	155.4
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9



TEST NUMBER: P332588-935

CATALOG NUMBER: SA4XXDIP-C795D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0
2.5°	1138.8	1140.5	1142.1	1142.9	1142.7	1142.5	1142.4	1142.2
5°	1132.7	1135.0	1137.2	1138.2	1137.7	1137.4	1137.0	1136.5
7.5°	1120.2	1122.0	1123.7	1124.5	1124.3	1124.0	1123.8	1123.5
10°	1109.6	1111.2	1112.8	1113.4	1113.0	1112.6	1112.2	1111.8
12.5°	1096.7	1098.5	1100.3	1100.9	1100.4	1099.8	1099.2	1098.6
15°	1072.1	1073.3	1074.5	1074.9	1074.3	1073.7	1073.1	1072.5
17.5°	1044.1	1044.9	1045.7	1045.9	1045.4	1045.0	1044.7	1044.2
20°	1023.3	1023.9	1024.5	1024.6	1024.2	1023.8	1023.4	1023.0
22.5°	1001.5	1002.6	1003.8	1003.9	1003.2	1002.5	1001.7	1001.0
25°	965.7	965.9	966.1	965.8	965.0	964.1	963.4	962.5
27.5°	925.5	925.0	924.5	923.8	922.7	921.7	920.7	919.6
30°	897.7	896.9	896.0	895.2	894.1	893.1	892.1	891.1
32.5°	869.5	868.6	867.6	866.6	865.6	864.5	863.5	862.5
35°	825.1	823.6	822.2	821.0	819.9	819.0	817.9	816.9
37.5°	778.4	776.9	775.4	774.0	772.6	771.3	769.9	768.5
40°	746.0	744.0	741.9	740.4	739.3	738.4	737.4	736.3
42.5°	714.5	712.2	709.8	708.3	707.7	707.0	706.3	705.6
45°	665.9	663.7	661.4	660.0	659.4	658.8	658.1	657.5
47.5°	618.8	616.3	613.7	611.7	610.2	608.6	607.1	605.5
50°	585.9	583.1	580.2	578.2	577.0	575.8	574.5	573.3
52.5°	552.2	549.6	547.1	545.1	543.5	542.0	540.4	538.9
55°	502.5	500.1	497.6	495.8	494.6	493.4	492.1	490.9
57.5°	452.7	450.4	448.1	446.3	445.1	443.9	442.8	441.6
60°	418.5	416.7	414.8	413.5	412.4	411.4	410.4	409.4
62.5°	385.1	383.5	381.9	380.5	379.4	378.4	377.5	376.4
65°	336.7	334.6	332.5	331.1	330.0	329.0	328.0	326.9
67.5°	286.6	284.6	282.7	281.5	281.3	281.0	280.7	280.4
70°	255.0	253.4	251.8	250.6	250.0	249.4	248.8	248.2
72.5°	223.4	222.1	220.8	219.9	219.2	218.6	218.0	217.4
75°	177.9	177.0	176.2	175.7	175.6	175.3	175.1	175.0
77.5°	134.7	134.4	134.2	133.8	133.3	132.8	132.2	131.7
80°	107.3	106.9	106.4	106.2	105.9	105.7	105.6	105.3
82.5°	82.7	82.4	82.1	82.0	81.8	81.5	81.4	81.1
85°	47.6	47.6	47.6	47.5	47.4	47.1	46.9	46.7
87.5°	18.7	18.8	18.8	18.8	18.9	18.9	18.9	18.9
90°	5.5	5.8	6.1	6.1	6.4	6.7	6.4	6.4
92.5°	59.8	44.9	35.8	29.7	26.1	24.5	23.4	23.4
95°	225.5	178.3	137.5	108.1	93.1	83.7	78.2	74.2
97.5°	333.1	315.6	285.9	254.1	232.2	214.0	204.8	198.5
100°	367.0	373.1	358.2	335.6	309.2	290.6	281.5	279.1
102.5°	365.3	395.5	399.8	390.4	374.2	360.8	351.1	349.1
105°	340.8	393.5	423.6	436.1	436.7	434.2	430.0	428.2
107.5°	306.1	362.1	404.5	431.7	446.7	453.7	456.7	457.4
110°	285.2	337.8	381.9	415.3	437.0	449.8	455.2	458.0



TEST NUMBER: P332588-935

CATALOG NUMBER: SA4XXDIP-C795D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	269.8	316.3	358.0	391.5	416.0	431.5	439.2	443.6
115°	254.4	291.8	327.4	356.6	380.6	398.9	408.7	411.1
117.5°	246.8	277.8	305.8	330.6	351.1	366.4	376.3	378.2
120°	243.4	271.7	296.1	317.7	335.0	348.4	356.4	359.7
122.5°	240.5	267.9	290.0	308.9	323.6	335.0	341.7	345.1
125°	235.6	261.7	282.7	299.5	311.6	320.5	326.2	328.0
127.5°	229.5	254.4	275.4	291.3	303.5	311.3	316.2	318.1
130°	224.5	248.7	269.3	285.4	297.9	305.5	310.4	312.2
132.5°	219.5	242.0	262.3	278.4	290.6	299.2	303.8	305.7
135°	212.4	232.2	250.7	266.0	278.1	286.6	291.5	293.3
137.5°	206.0	222.7	238.4	252.1	263.6	271.9	276.0	278.1
140°	202.3	216.6	230.3	243.1	253.8	260.5	264.8	267.2
142.5°	199.0	211.5	223.3	234.4	243.8	250.0	253.8	255.5
145°	194.2	204.5	213.6	222.1	229.7	234.9	238.0	239.4
147.5°	190.2	198.4	205.7	212.4	218.0	222.5	224.7	225.3
150°	187.8	194.8	200.9	206.3	211.2	215.2	217.0	217.2
152.5°	185.1	191.1	196.7	201.2	205.3	208.5	209.7	210.0
155°	181.1	185.9	190.5	194.2	197.2	199.6	200.5	200.5
157.5°	176.8	180.8	184.7	187.6	189.9	191.7	192.3	192.3
160°	174.1	177.4	180.7	183.2	185.0	186.8	187.2	187.2
162.5°	171.4	174.3	176.8	179.1	180.4	182.2	182.5	182.3
165°	167.6	169.5	171.6	173.1	174.4	175.6	175.3	175.0
167.5°	164.1	165.5	167.2	168.1	168.7	169.5	169.4	169.2
170°	161.9	162.8	164.0	165.0	165.6	165.8	165.6	165.6
172.5°	160.0	160.6	161.4	162.0	162.4	162.6	162.4	161.9
175°	157.3	157.6	158.3	158.3	158.3	158.9	158.3	157.6
177.5°	155.6	155.8	155.8	156.1	155.8	156.1	155.6	155.2
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9

(END OF REPORT)