

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332595-935

Luminaire Tested: **SA4XXDIP-C795D590U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332595-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D590U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4966.1 lumens  
Efficiency: N/A  
Efficacy: 123.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332595-935  
CATALOG NUMBER: SA4XXDIP-C795D590U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332595-935

CATALOG NUMBER: SA4XXDIP-C795D590U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																											
	1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50																											
	2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46	42																											
	3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35																											
	4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30																											
	5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26																											
	6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23																											
	7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20																											
	8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18																											
	9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17																											
	10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9227	9227	9227
5°	9255	9143	9210
10°	9197	9069	9114
15°	9086	8940	8964
20°	8937	8781	8789
25°	8769	8598	8573
30°	8563	8383	8307
35°	8348	8159	8051
40°	8126	7904	7759
45°	7895	7654	7507
50°	7637	7430	7200
55°	7361	7142	6909
60°	7083	6817	6610
65°	6770	6508	6245
70°	6420	6097	5858
75°	5883	5599	5459
80°	5235	5026	4895
85°	4576	4409	4326



TEST NUMBER: P332595-935

CATALOG NUMBER: SA4XXDIP-C795D590U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.6	2.2
10°-20°	303.3	6.1
20°-30°	446.4	9.0
30°-40°	518.9	10.4
40°-50°	518.9	10.4
50°-60°	453.9	9.1
60°-70°	337.1	6.8
70°-80°	191.5	3.9
80°-90°	57.2	1.2
90°-100°	22.5	0.5
100°-110°	143.2	2.9
110°-120°	273.9	5.5
120°-130°	347.7	7.0
130°-140°	372.1	7.5
140°-150°	347.9	7.0
150°-160°	280.6	5.6
160°-170°	181.0	3.6
170°-180°	62.4	1.3
0°-30°	857.3	17.3
0°-40°	1376.2	27.7
0°-60°	2349.1	47.3
0°-90°	2934.9	59.1
90°-120°	439.6	8.9
90°-150°	1507.3	30.4
90°-180°	2031.0	40.9
0°-180°	4966.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1143	1143	1143	1143	1143	
5°	1142	1138	1128	1138	1136	108
15°	1087	1083	1070	1075	1072	306
25°	984	978	965	966	962	453
35°	847	840	828	822	817	529
45°	692	685	670	661	658	533
55°	523	520	507	497	491	468
65°	354	350	341	332	327	351
75°	189	184	180	176	175	200
85°	49	49	48	48	47	54
90°	2	7	11	14	15	4
95°	27	11	11	14	14	35
105°	148	151	153	156	140	155
115°	276	277	277	278	278	272
125°	388	390	389	390	391	346
135°	481	481	483	484	485	371
145°	555	556	556	557	558	347
155°	609	609	608	609	608	280
165°	642	640	640	643	639	181
175°	657	654	654	658	653	63
180°	657	657	657	657	657	



TEST NUMBER: P332595-935

CATALOG NUMBER: SA4XXDIP-C795D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0
2.5°	1145.9	1145.4	1144.9	1144.4	1143.9	1142.8	1141.0	1139.2	1137.4	1135.7	1137.2
5°	1142.0	1141.3	1140.4	1139.6	1138.8	1137.2	1135.0	1132.7	1130.5	1128.3	1130.5
7.5°	1131.4	1130.6	1129.8	1128.9	1128.2	1126.5	1124.0	1121.5	1119.0	1116.5	1118.4
10°	1121.9	1121.1	1120.2	1119.5	1118.6	1116.9	1114.2	1111.6	1109.0	1106.3	1107.9
12.5°	1109.4	1108.6	1107.8	1107.0	1106.2	1104.3	1101.6	1098.7	1096.0	1093.1	1094.9
15°	1087.1	1086.2	1085.5	1084.6	1083.8	1081.9	1078.8	1075.8	1072.7	1069.7	1070.9
17.5°	1060.1	1059.1	1058.1	1057.1	1056.1	1054.1	1051.3	1048.4	1045.4	1042.6	1043.4
20°	1040.3	1039.3	1038.4	1037.3	1036.3	1034.2	1031.2	1028.1	1025.1	1022.1	1022.7
22.5°	1019.2	1017.8	1016.4	1015.1	1013.7	1011.6	1008.5	1005.5	1002.4	999.4	1000.5
25°	984.5	983.1	981.6	980.2	978.8	976.6	973.8	970.9	968.1	965.3	965.4
27.5°	944.9	943.5	942.0	940.6	939.1	937.0	934.4	931.8	929.1	926.4	925.9
30°	918.6	917.0	915.3	913.7	912.1	909.9	907.2	904.7	902.0	899.3	898.5
32.5°	890.7	889.2	887.8	886.3	884.8	882.7	879.9	877.1	874.3	871.5	870.6
35°	847.1	845.7	844.3	842.8	841.5	839.3	836.5	833.6	830.8	827.9	826.5
37.5°	801.2	799.9	798.6	797.3	795.9	793.8	790.7	787.6	784.6	781.5	780.0
40°	771.1	769.5	767.8	766.2	764.6	762.2	759.2	756.1	753.1	750.0	748.0
42.5°	738.9	737.9	736.9	736.0	734.9	732.8	729.4	726.1	722.6	719.3	717.0
45°	691.5	690.0	688.6	687.2	685.8	683.4	680.2	676.9	673.6	670.4	668.1
47.5°	641.8	640.8	639.9	638.9	637.9	635.9	632.9	629.9	626.9	623.9	621.3
50°	608.1	607.3	606.5	605.6	604.9	603.0	600.2	597.4	594.4	591.6	588.8
52.5°	575.1	574.2	573.2	572.2	571.2	569.2	566.2	563.2	560.2	557.2	554.7
55°	523.0	522.3	521.7	521.1	520.5	518.8	515.9	513.1	510.2	507.4	504.9
57.5°	473.1	472.4	471.7	471.1	470.4	468.6	465.8	463.0	460.2	457.4	455.0
60°	438.7	437.6	436.6	435.7	434.6	432.7	430.2	427.5	424.8	422.2	420.3
62.5°	405.0	404.2	403.3	402.4	401.6	399.8	396.9	394.1	391.3	388.5	386.8
65°	354.4	353.4	352.4	351.4	350.3	348.8	346.8	344.7	342.7	340.7	338.6
67.5°	303.5	302.6	301.6	300.7	299.8	298.3	296.4	294.4	292.5	290.5	288.5
70°	272.0	270.6	269.1	267.7	266.3	264.8	263.1	261.5	259.8	258.3	256.7
72.5°	238.3	236.9	235.5	234.0	232.6	231.3	230.0	228.6	227.3	226.0	224.7
75°	188.6	187.6	186.7	185.6	184.6	183.6	182.5	181.5	180.6	179.5	178.7
77.5°	141.2	140.8	140.3	139.9	139.4	138.8	137.8	137.0	136.0	135.2	134.9
80°	112.6	112.0	111.4	110.8	110.2	109.7	109.3	108.9	108.5	108.1	107.6
82.5°	84.8	84.6	84.2	83.9	83.7	83.5	83.4	83.3	83.3	83.2	82.9
85°	49.4	49.4	49.4	49.4	49.4	49.2	48.8	48.5	48.0	47.6	47.6
87.5°	19.4	19.5	19.5	19.5	19.6	19.7	19.7	19.7	19.7	19.7	19.9
90°	1.5	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5
92.5°	6.2	6.3	6.3	6.4	6.5	6.9	7.8	8.7	9.6	10.4	11.1
95°	27.0	23.3	19.6	15.8	12.1	10.3	10.5	10.6	10.7	10.8	11.5
97.5°	57.3	59.7	62.0	64.3	66.6	61.6	49.5	37.4	25.1	13.0	13.0
100°	80.5	82.5	84.5	86.4	88.4	81.9	66.8	51.7	36.7	21.6	19.7
102.5°	106.5	107.9	109.3	110.8	112.3	112.0	110.0	108.1	106.1	104.1	84.1
105°	147.8	148.5	149.1	149.8	150.4	151.0	151.6	152.1	152.7	153.3	154.2
107.5°	186.2	186.6	186.9	187.2	187.5	188.0	188.8	189.6	190.3	191.1	191.6
110°	212.2	212.5	212.8	213.2	213.4	214.0	214.6	215.2	215.9	216.6	216.8



TEST NUMBER: P332595-935

CATALOG NUMBER: SA4XXDIP-C795D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	237.3	237.9	238.5	239.1	239.7	240.1	240.4	240.7	241.1	241.3	241.3
115°	276.0	276.4	276.6	277.0	277.3	277.4	277.3	277.2	277.1	277.0	277.2
117.5°	310.9	311.3	311.8	312.2	312.6	313.0	313.2	313.5	313.7	313.9	313.9
120°	334.5	334.9	335.4	335.8	336.2	336.4	336.3	336.1	336.0	336.0	336.1
122.5°	356.5	356.7	357.0	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4
125°	388.0	388.4	388.9	389.3	389.8	389.9	389.6	389.4	389.2	389.0	389.3
127.5°	417.8	417.9	418.1	418.2	418.3	418.6	419.1	419.6	420.1	420.6	420.5
130°	437.1	437.2	437.3	437.5	437.6	437.7	438.1	438.4	438.8	439.1	439.2
132.5°	454.8	455.0	455.2	455.4	455.6	455.9	456.3	456.7	457.1	457.5	457.6
135°	481.3	481.2	481.1	481.0	480.9	481.0	481.5	481.9	482.3	482.8	483.0
137.5°	504.8	504.8	504.9	504.9	505.0	505.2	505.7	506.2	506.7	507.1	507.4
140°	520.1	520.3	520.6	520.7	521.0	521.2	521.4	521.7	521.9	522.1	522.4
142.5°	533.9	534.3	534.7	535.0	535.5	535.7	535.8	536.0	536.1	536.2	536.5
145°	555.0	555.3	555.6	555.9	556.3	556.5	556.5	556.5	556.5	556.5	556.6
147.5°	571.8	572.4	573.0	573.6	574.2	574.5	574.4	574.3	574.1	574.0	574.1
150°	583.9	584.4	584.9	585.3	585.7	585.9	585.7	585.7	585.6	585.4	585.4
152.5°	594.2	594.5	594.9	595.2	595.6	595.6	595.5	595.3	595.0	594.9	595.0
155°	608.6	608.6	608.7	608.8	609.0	608.8	608.6	608.2	607.9	607.5	608.0
157.5°	620.6	620.5	620.4	620.4	620.4	620.1	619.7	619.4	619.0	618.6	619.2
160°	627.7	627.3	627.0	626.7	626.4	626.1	626.0	625.9	625.8	625.7	626.4
162.5°	634.0	633.5	633.1	632.7	632.3	632.1	631.9	631.8	631.7	631.6	632.2
165°	641.9	641.4	640.8	640.2	639.7	639.5	639.5	639.5	639.5	639.5	640.3
167.5°	648.2	647.6	647.0	646.5	645.9	645.6	645.6	645.5	645.4	645.3	646.4
170°	651.8	651.1	650.4	649.8	649.1	648.8	648.9	649.0	649.2	649.3	650.1
172.5°	654.1	653.4	652.8	652.1	651.5	651.2	651.3	651.4	651.5	651.6	652.6
175°	656.7	656.0	655.3	654.7	654.0	653.8	653.8	654.0	654.1	654.2	655.1
177.5°	657.8	657.2	656.6	656.0	655.4	655.1	655.3	655.5	655.7	655.8	656.6
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332595-935

CATALOG NUMBER: SA4XXDIP-C795D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0
2.5°	1138.8	1140.5	1142.1	1142.9	1142.7	1142.5	1142.4	1142.2
5°	1132.7	1135.0	1137.2	1138.2	1137.7	1137.4	1137.0	1136.5
7.5°	1120.2	1122.0	1123.7	1124.5	1124.3	1124.0	1123.8	1123.5
10°	1109.6	1111.2	1112.8	1113.4	1113.0	1112.6	1112.2	1111.8
12.5°	1096.7	1098.5	1100.3	1100.9	1100.4	1099.8	1099.2	1098.6
15°	1072.1	1073.3	1074.5	1074.9	1074.3	1073.7	1073.1	1072.5
17.5°	1044.1	1044.9	1045.7	1045.9	1045.4	1045.0	1044.7	1044.2
20°	1023.3	1023.9	1024.5	1024.6	1024.2	1023.8	1023.4	1023.0
22.5°	1001.5	1002.6	1003.8	1003.9	1003.2	1002.5	1001.7	1001.0
25°	965.7	965.9	966.1	965.8	965.0	964.1	963.4	962.5
27.5°	925.5	925.0	924.5	923.8	922.7	921.7	920.7	919.6
30°	897.7	896.9	896.0	895.2	894.1	893.1	892.1	891.1
32.5°	869.5	868.6	867.6	866.6	865.6	864.5	863.5	862.5
35°	825.1	823.6	822.2	821.0	819.9	819.0	817.9	816.9
37.5°	778.4	776.9	775.4	774.0	772.6	771.3	769.9	768.5
40°	746.0	744.0	741.9	740.4	739.3	738.4	737.4	736.3
42.5°	714.5	712.2	709.8	708.3	707.7	707.0	706.3	705.6
45°	665.9	663.7	661.4	660.0	659.4	658.8	658.1	657.5
47.5°	618.8	616.3	613.7	611.7	610.2	608.6	607.1	605.5
50°	585.9	583.1	580.2	578.2	577.0	575.8	574.5	573.3
52.5°	552.2	549.6	547.1	545.1	543.5	542.0	540.4	538.9
55°	502.5	500.1	497.6	495.8	494.6	493.4	492.1	490.9
57.5°	452.7	450.4	448.1	446.3	445.1	443.9	442.8	441.6
60°	418.5	416.7	414.8	413.5	412.4	411.4	410.4	409.4
62.5°	385.1	383.5	381.9	380.5	379.4	378.4	377.5	376.4
65°	336.7	334.6	332.5	331.1	330.0	329.0	328.0	326.9
67.5°	286.6	284.6	282.7	281.5	281.3	281.0	280.7	280.4
70°	255.0	253.4	251.8	250.6	250.0	249.4	248.8	248.2
72.5°	223.4	222.1	220.8	219.9	219.2	218.6	218.0	217.4
75°	177.9	177.0	176.2	175.7	175.6	175.3	175.1	175.0
77.5°	134.7	134.4	134.2	133.8	133.3	132.8	132.2	131.7
80°	107.3	106.9	106.4	106.2	105.9	105.7	105.6	105.3
82.5°	82.7	82.4	82.1	82.0	81.8	81.5	81.4	81.1
85°	47.6	47.6	47.6	47.5	47.4	47.1	46.9	46.7
87.5°	20.0	20.1	20.2	20.3	20.4	20.4	20.5	20.5
90°	12.1	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	11.7	12.4	13.0	13.3	13.4	13.4	13.5	13.5
95°	12.1	12.7	13.4	13.8	13.9	14.0	14.1	14.2
97.5°	13.1	13.2	13.3	13.3	13.4	13.5	13.6	13.8
100°	17.9	16.0	14.2	13.3	13.4	13.5	13.6	13.8
102.5°	64.1	44.1	24.0	14.0	14.1	14.1	14.1	14.1
105°	155.2	156.2	157.1	155.7	151.8	147.8	143.9	140.0
107.5°	192.0	192.5	193.0	193.4	193.8	194.2	194.7	195.1
110°	217.1	217.2	217.5	217.7	218.1	218.3	218.7	219.0





TEST NUMBER: P332595-935

CATALOG NUMBER: SA4XXDIP-C795D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	241.3	241.3	241.2	241.3	241.8	242.2	242.6	243.0
115°	277.4	277.7	277.8	278.0	278.0	278.0	278.0	278.0
117.5°	313.8	313.8	313.7	313.7	313.7	313.7	313.6	313.6
120°	336.4	336.6	336.8	336.8	336.6	336.4	336.1	336.0
122.5°	358.6	358.7	358.9	358.8	358.6	358.3	358.2	357.9
125°	389.6	389.9	390.3	390.5	390.6	390.7	390.8	391.0
127.5°	420.5	420.4	420.3	420.3	420.2	420.1	420.0	419.9
130°	439.3	439.4	439.5	439.5	439.5	439.5	439.5	439.5
132.5°	457.8	457.9	458.0	458.0	457.9	457.8	457.7	457.6
135°	483.2	483.5	483.6	483.9	484.1	484.3	484.6	484.7
137.5°	507.6	507.9	508.1	508.2	508.2	508.1	508.0	507.9
140°	522.7	523.1	523.4	523.6	523.7	523.8	523.9	524.0
142.5°	536.7	536.9	537.2	537.4	537.4	537.4	537.4	537.4
145°	556.6	556.8	556.9	557.1	557.2	557.5	557.8	557.9
147.5°	574.2	574.3	574.4	574.5	574.6	574.7	574.8	574.9
150°	585.4	585.4	585.4	585.5	585.6	585.7	585.8	585.9
152.5°	595.2	595.4	595.6	595.6	595.6	595.5	595.4	595.4
155°	608.4	608.8	609.2	609.3	609.0	608.6	608.4	608.0
157.5°	619.7	620.4	620.9	620.9	620.4	619.7	619.2	618.6
160°	627.0	627.7	628.4	628.4	627.7	627.0	626.4	625.7
162.5°	632.9	633.5	634.2	634.2	633.4	632.7	632.0	631.2
165°	641.2	642.0	643.0	642.9	641.9	640.9	640.0	638.9
167.5°	647.3	648.2	649.2	649.1	648.1	647.0	645.8	644.8
170°	651.0	651.9	652.8	652.6	651.6	650.5	649.4	648.3
172.5°	653.4	654.3	655.1	655.0	653.8	652.6	651.4	650.2
175°	656.2	657.1	658.1	658.0	656.7	655.3	654.0	652.7
177.5°	657.3	658.0	658.7	658.5	657.5	656.4	655.3	654.3
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7

(END OF REPORT)