

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902174

Luminaire Tested: DFN2DIP-4P3F0-020D020US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902174
REPORT IS A COMBINATION OF REPORTS P899029 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D020US830-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3534.5 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 31
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902174

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902174

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	836	836	836
5°	837	824	830
10°	829	812	818
15°	817	798	800
20°	800	779	782
25°	783	756	761
30°	762	735	734
35°	742	710	706
40°	717	685	679
45°	693	660	652
50°	666	633	620
55°	637	602	590
60°	606	566	557
65°	571	528	517
70°	526	482	475
75°	465	427	435
80°	391	356	359
85°	274	236	235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 693 cd/sqm

TEST NUMBER: P902174

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	2.0
10°-20°	194.2	5.5
20°-30°	285.5	8.1
30°-40°	331.5	9.4
40°-50°	331.1	9.4
50°-60°	288.7	8.2
60°-70°	213.4	6.0
70°-80°	120.8	3.4
80°-90°	33.6	0.9
90°-100°	36.9	1.0
100°-110°	117.2	3.3
110°-120°	200.6	5.7
120°-130°	263.8	7.5
130°-140°	296.1	8.4
140°-150°	290.4	8.2
150°-160°	243.6	6.9
160°-170°	161.5	4.6
170°-180°	56.5	1.6
0°-30°	548.7	15.5
0°-40°	880.3	24.9
0°-60°	1500.2	42.4
0°-90°	1867.9	52.8
90°-120°	354.7	10.0
90°-150°	1205.0	34.1
90°-180°	1667.0	47.2
0°-180°	3534.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	6	18	16	17	3
95°	26	31	32	32	31	29
105°	108	110	111	112	112	114
115°	201	204	203	203	201	199
125°	293	297	296	294	294	262
135°	379	384	385	385	383	293
145°	460	463	466	467	465	287
155°	526	527	529	531	530	242
165°	572	571	571	575	572	161
175°	595	594	593	596	593	57
180°	596	596	596	596	596	

TEST NUMBER: P902174

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	0.6	6.5	17.6	16.5	17.1
92.5°	11.1	15.1	15.6	16.2	16.2
95°	26.2	31.3	32.1	32.1	31.3
97.5°	43.6	48.4	50.3	50.3	50.3
100°	63.8	68.0	69.4	69.4	68.8
102.5°	85.0	88.0	90.0	90.6	90.0
105°	108.2	109.6	110.7	111.6	111.6
107.5°	131.2	133.4	133.4	133.7	131.2
110°	153.5	156.4	156.4	156.4	155.0



TEST NUMBER: P902174

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.6	180.6	180.1	178.6	177.6
115°	201.3	204.2	203.3	202.7	201.3
117.5°	224.9	228.8	226.3	224.9	223.4
120°	248.5	252.5	248.5	248.5	246.9
122.5°	270.1	275.1	272.7	271.3	270.1
125°	292.8	297.3	295.9	294.3	293.7
127.5°	314.9	320.5	318.5	316.3	314.9
130°	335.5	342.0	341.1	340.1	338.1
132.5°	358.7	363.8	364.1	361.7	360.1
135°	378.7	384.3	385.3	384.8	383.3
137.5°	401.0	405.5	406.4	406.0	403.9
140°	420.6	425.1	427.6	427.6	425.7
142.5°	440.7	445.2	446.7	447.1	445.2
145°	459.8	463.4	466.3	466.7	464.8
147.5°	476.8	481.4	483.5	484.4	482.4
150°	494.5	497.5	499.5	501.1	499.5
152.5°	510.1	513.1	515.7	517.6	515.7
155°	525.8	527.2	528.8	531.3	529.7
157.5°	539.2	540.3	541.2	544.8	542.2
160°	551.3	552.3	552.9	555.9	553.7
162.5°	562.4	562.4	562.9	566.4	563.8
165°	571.9	571.4	571.4	575.0	572.5
167.5°	580.5	578.9	578.9	582.5	580.0
170°	587.0	585.6	585.0	588.6	585.6
172.5°	591.5	590.0	589.6	593.1	590.0
175°	595.1	593.7	592.6	596.2	593.1
177.5°	597.1	595.7	594.6	597.6	594.6
180°	596.2	596.2	596.2	596.2	596.2

TEST NUMBER: P902174

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.87	7.76	7.81	8.71	9.94	6.43	7.32	7.36	8.27	9.50
	3H	8.53	9.33	9.48	10.29	11.54	8.04	8.84	8.99	9.80	11.05
	4H	9.12	9.87	10.08	10.83	12.10	8.62	9.38	9.58	10.34	11.60
	6H	9.52	10.21	10.48	11.18	12.45	9.02	9.71	9.98	10.68	11.95
	8H	9.62	10.28	10.60	11.27	12.54	9.12	9.78	10.09	10.77	12.04
	12H	9.67	10.30	10.65	11.28	12.57	9.16	9.79	10.14	10.77	12.06
4H	2H	7.33	8.09	8.30	9.05	10.31	6.98	7.73	7.94	8.70	9.96
	3H	9.20	9.83	10.17	10.82	12.10	8.79	9.42	9.76	10.41	11.69
	4H	9.91	10.48	10.89	11.47	12.77	9.49	10.06	10.47	11.05	12.35
	6H	10.42	10.92	11.42	11.93	13.23	9.99	10.48	10.98	11.49	12.79
	8H	10.57	11.03	11.57	12.04	13.35	10.13	10.59	11.13	11.60	12.91
	12H	10.64	11.06	11.66	12.08	13.40	10.19	10.61	11.21	11.63	12.95
8H	4H	10.10	10.57	11.10	11.57	12.88	9.73	10.19	10.72	11.19	12.51
	6H	10.73	11.11	11.75	12.16	13.47	10.35	10.73	11.37	11.77	13.08
	8H	10.95	11.29	11.98	12.32	13.65	10.55	10.89	11.58	11.92	13.25
	12H	11.08	11.37	12.11	12.40	13.77	10.67	10.96	11.70	11.99	13.36
12H	4H	10.09	10.51	11.11	11.53	12.85	9.72	10.14	10.74	11.16	12.48
	6H	10.76	11.10	11.79	12.13	13.46	10.39	10.72	11.41	11.76	13.09
	8H	11.00	11.30	12.03	12.32	13.70	10.62	10.91	11.65	11.94	13.31

END OF REPORT