

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332976-935

Luminaire Tested: **SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332976-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7150.0 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332976-935

CATALOG NUMBER: SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332976-935

CATALOG NUMBER: SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	36
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	27
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	24	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12551	12551	12551
5°	12580	12426	12503
10°	12500	12276	12276
15°	12357	12018	11929
20°	12160	11679	11465
25°	11908	11282	10996
30°	11663	10864	10409
35°	11392	10430	9819
40°	11065	9936	9183
45°	10764	9445	8535
50°	10420	8881	7850
55°	10054	8294	7104
60°	9649	7650	6344
65°	9278	6844	5593
70°	8738	5958	4749
75°	8057	4938	3862
80°	7029	3761	3543
85°	5956	3418	3196



TEST NUMBER: P332976-935

CATALOG NUMBER: SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	2.0
10°-20°	407.3	5.7
20°-30°	588.1	8.2
30°-40°	666.6	9.3
40°-50°	643.7	9.0
50°-60°	535.3	7.5
60°-70°	369.6	5.2
70°-80°	187.4	2.6
80°-90°	51.4	0.7
90°-100°	39.3	0.5
100°-110°	250.6	3.5
110°-120°	479.4	6.7
120°-130°	608.6	8.5
130°-140°	651.1	9.1
140°-150°	608.9	8.5
150°-160°	491.0	6.9
160°-170°	316.7	4.4
170°-180°	109.2	1.5
0°-30°	1141.4	16.0
0°-40°	1808.0	25.3
0°-60°	2987.0	41.8
0°-90°	3595.3	50.3
90°-120°	769.3	10.8
90°-150°	2637.9	36.9
90°-180°	3555.0	49.7
0°-180°	7150.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1555	1555	1555	1555	1555	
5°	1552	1547	1533	1544	1543	147
15°	1478	1467	1438	1435	1427	416
25°	1337	1314	1267	1247	1234	616
35°	1156	1117	1058	1019	996	722
45°	943	897	827	771	748	727
55°	714	665	589	530	505	639
65°	486	433	358	309	293	479
75°	258	214	158	132	124	273
85°	64	42	37	35	34	72
90°	3	12	19	24	26	5
95°	47	20	19	24	25	61
105°	259	264	268	274	245	271
115°	483	485	485	486	486	475
125°	679	682	681	683	684	606
135°	842	842	845	847	848	649
145°	971	974	974	975	976	607
155°	1065	1066	1063	1066	1064	491
165°	1123	1119	1119	1125	1118	317
175°	1149	1144	1145	1152	1142	109
180°	1149	1149	1149	1149	1149	



TEST NUMBER: P332976-935

CATALOG NUMBER: SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1558.5	1557.6	1556.8	1556.0	1555.1	1553.5	1551.2	1548.9	1546.5	1544.2	1546.5
5°	1552.3	1551.3	1550.2	1549.1	1548.1	1545.9	1542.8	1539.6	1536.5	1533.3	1535.9
7.5°	1538.3	1537.1	1536.0	1534.9	1533.8	1531.2	1527.1	1522.9	1518.8	1514.7	1516.4
10°	1524.9	1523.6	1522.2	1521.0	1519.7	1516.6	1511.8	1507.1	1502.3	1497.5	1498.6
12.5°	1507.8	1506.2	1504.7	1503.2	1501.7	1498.1	1492.5	1486.9	1481.3	1475.7	1476.3
15°	1478.5	1476.1	1473.8	1471.4	1469.0	1464.5	1457.8	1451.2	1444.7	1438.0	1437.5
17.5°	1443.0	1439.6	1436.1	1432.7	1429.3	1423.6	1415.7	1407.7	1399.8	1391.8	1390.3
20°	1415.4	1412.0	1408.5	1405.1	1401.6	1395.4	1386.5	1377.4	1368.5	1359.4	1357.4
22.5°	1384.9	1381.0	1377.2	1373.4	1369.5	1362.7	1353.1	1343.5	1333.9	1324.2	1321.0
25°	1336.9	1332.1	1327.3	1322.6	1317.8	1310.0	1299.2	1288.3	1277.5	1266.6	1262.1
27.5°	1286.3	1280.4	1274.5	1268.4	1262.5	1253.7	1242.1	1230.5	1218.9	1207.3	1201.8
30°	1251.1	1244.5	1237.9	1231.3	1224.7	1215.1	1202.7	1190.2	1177.8	1165.4	1158.8
32.5°	1214.0	1206.5	1199.0	1191.6	1184.1	1174.0	1161.1	1148.3	1135.4	1122.6	1114.9
35°	1155.9	1147.5	1138.9	1130.5	1122.1	1111.2	1097.9	1084.8	1071.5	1058.3	1049.3
37.5°	1093.7	1085.0	1076.3	1067.6	1058.9	1047.1	1032.5	1017.9	1003.2	988.5	978.4
40°	1050.0	1041.2	1032.5	1023.7	1015.0	1003.2	988.1	972.9	957.9	942.8	931.7
42.5°	1008.1	998.9	989.7	980.6	971.5	959.0	943.3	927.6	911.9	896.1	884.8
45°	942.8	933.1	923.3	913.4	903.6	890.8	874.9	859.1	843.2	827.3	814.4
47.5°	875.5	865.3	855.2	845.2	835.0	821.7	805.2	788.7	772.1	755.7	742.3
50°	829.7	819.4	809.1	798.7	788.4	774.8	757.9	741.0	724.0	707.1	693.9
52.5°	783.1	772.9	762.8	752.8	742.6	728.9	711.5	694.2	676.8	659.5	646.1
55°	714.3	703.7	693.1	682.5	671.9	658.1	640.8	623.6	606.5	589.3	575.5
57.5°	646.2	635.2	624.1	613.1	602.2	588.1	571.3	554.3	537.4	520.5	506.5
60°	597.6	587.0	576.4	565.8	555.3	541.5	524.6	507.6	490.7	473.8	460.0
62.5°	553.8	542.8	531.8	520.7	509.8	495.6	478.2	460.9	443.5	426.2	413.5
65°	485.7	474.3	463.0	451.6	440.2	426.0	409.1	392.2	375.2	358.3	347.0
67.5°	415.0	404.1	393.2	382.3	371.3	358.1	342.3	326.7	310.9	295.2	285.4
70°	370.2	359.1	348.0	336.9	325.8	312.7	297.6	282.5	267.4	252.4	243.7
72.5°	322.6	312.5	302.5	292.5	282.4	270.3	256.1	241.8	227.6	213.4	205.9
75°	258.3	248.6	238.8	228.9	219.2	208.0	195.6	183.2	170.7	158.3	152.2
77.5°	193.1	184.8	176.5	168.2	159.9	150.7	140.6	130.6	120.5	110.5	106.9
80°	151.2	143.5	135.9	128.2	120.5	112.7	104.8	96.9	88.9	80.9	80.2
82.5°	115.0	108.0	100.9	93.8	86.9	81.0	76.5	72.0	67.4	62.9	62.3
85°	64.3	59.0	53.7	48.4	43.1	40.0	39.3	38.5	37.7	36.9	36.3
87.5°	22.4	21.2	19.9	18.6	17.3	16.7	16.9	17.0	17.0	17.1	17.1
90°	2.6	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1
92.5°	10.8	10.9	11.0	11.2	11.3	12.1	13.6	15.2	16.7	18.3	19.4
95°	47.3	40.8	34.3	27.8	21.3	18.2	18.3	18.5	18.7	18.9	20.1
97.5°	100.4	104.4	108.5	112.5	116.6	108.0	86.6	65.3	44.0	22.7	22.8
100°	140.9	144.4	147.8	151.3	154.7	143.3	116.9	90.6	64.1	37.8	34.6
102.5°	186.3	188.9	191.4	193.9	196.4	196.0	192.5	189.1	185.6	182.2	147.1
105°	258.7	259.8	261.0	262.2	263.3	264.3	265.3	266.2	267.3	268.2	269.9
107.5°	325.9	326.5	327.1	327.6	328.2	329.2	330.5	331.7	333.0	334.3	335.2
110°	371.3	371.9	372.5	373.0	373.6	374.4	375.6	376.8	377.9	379.0	379.4



TEST NUMBER: P332976-935

CATALOG NUMBER: SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.3	416.4	417.4	418.4	419.5	420.3	420.8	421.3	421.8	422.3	422.3
115°	483.0	483.6	484.2	484.7	485.3	485.5	485.3	485.2	484.9	484.7	485.2
117.5°	544.1	544.8	545.6	546.4	547.2	547.7	548.1	548.5	549.0	549.4	549.3
120°	585.3	586.1	586.9	587.6	588.4	588.7	588.5	588.3	588.1	587.9	588.3
122.5°	623.8	624.3	624.7	625.2	625.7	626.0	626.3	626.5	626.8	627.1	627.3
125°	679.0	679.8	680.5	681.3	682.1	682.3	681.9	681.5	681.1	680.7	681.3
127.5°	731.2	731.4	731.7	731.8	732.0	732.5	733.5	734.3	735.2	736.1	736.0
130°	765.0	765.2	765.3	765.5	765.7	766.1	766.7	767.2	767.8	768.4	768.6
132.5°	795.9	796.3	796.6	796.9	797.3	797.8	798.6	799.3	800.0	800.7	800.9
135°	842.3	842.1	842.0	841.7	841.5	841.8	842.6	843.3	844.1	844.9	845.2
137.5°	883.4	883.5	883.6	883.6	883.7	884.2	885.0	885.9	886.7	887.5	887.9
140°	910.2	910.6	911.0	911.4	911.7	912.1	912.5	912.9	913.3	913.7	914.2
142.5°	934.3	935.0	935.6	936.3	937.0	937.5	937.7	938.0	938.1	938.4	938.8
145°	971.2	971.8	972.4	972.9	973.5	973.8	973.8	973.8	973.8	973.8	974.0
147.5°	1000.7	1001.7	1002.8	1003.8	1005.0	1005.4	1005.1	1005.0	1004.8	1004.6	1004.8
150°	1021.9	1022.7	1023.5	1024.2	1025.0	1025.3	1025.1	1024.9	1024.8	1024.5	1024.5
152.5°	1039.8	1040.4	1041.0	1041.6	1042.2	1042.4	1042.1	1041.7	1041.4	1041.0	1041.4
155°	1065.0	1065.1	1065.3	1065.5	1065.7	1065.5	1065.0	1064.4	1063.8	1063.2	1063.9
157.5°	1086.1	1086.0	1085.8	1085.7	1085.6	1085.2	1084.6	1083.9	1083.3	1082.6	1083.7
160°	1098.5	1097.9	1097.3	1096.7	1096.1	1095.8	1095.6	1095.4	1095.2	1095.0	1096.1
162.5°	1109.5	1108.7	1108.0	1107.2	1106.6	1106.1	1105.9	1105.7	1105.5	1105.4	1106.5
165°	1123.3	1122.4	1121.5	1120.5	1119.6	1119.0	1119.0	1119.0	1119.0	1119.0	1120.6
167.5°	1134.4	1133.4	1132.4	1131.4	1130.4	1129.9	1129.7	1129.6	1129.5	1129.4	1131.1
170°	1140.6	1139.4	1138.2	1137.1	1136.0	1135.5	1135.7	1135.9	1136.1	1136.3	1137.8
172.5°	1144.7	1143.6	1142.4	1141.3	1140.1	1139.6	1139.8	1140.1	1140.2	1140.4	1141.9
175°	1149.2	1148.1	1146.9	1145.7	1144.6	1144.1	1144.3	1144.5	1144.7	1144.9	1146.6
177.5°	1151.2	1150.1	1149.1	1148.1	1146.9	1146.6	1146.9	1147.2	1147.5	1147.8	1149.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332976-935

CATALOG NUMBER: SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1548.9	1551.2	1553.5	1554.6	1554.4	1554.2	1553.9	1553.8
5°	1538.5	1541.2	1543.9	1544.9	1544.4	1543.9	1543.3	1542.8
7.5°	1518.1	1519.8	1521.5	1521.9	1521.0	1520.2	1519.3	1518.5
10°	1499.7	1500.7	1501.8	1501.8	1500.7	1499.7	1498.6	1497.5
12.5°	1476.9	1477.6	1478.2	1477.7	1476.3	1474.8	1473.3	1471.9
15°	1437.0	1436.4	1435.9	1434.7	1432.9	1431.0	1429.2	1427.3
17.5°	1388.9	1387.4	1386.0	1383.8	1381.0	1378.2	1375.4	1372.5
20°	1355.2	1353.1	1351.0	1348.2	1344.8	1341.4	1337.9	1334.5
22.5°	1317.8	1314.7	1311.6	1308.5	1305.7	1303.0	1300.1	1297.4
25°	1257.6	1253.1	1248.6	1245.0	1242.4	1239.8	1237.1	1234.5
27.5°	1196.2	1190.7	1185.1	1180.4	1176.6	1172.8	1169.0	1165.2
30°	1152.2	1145.6	1138.9	1133.5	1129.3	1125.1	1120.8	1116.6
32.5°	1107.2	1099.6	1091.9	1086.1	1082.0	1078.0	1074.0	1070.0
35°	1040.3	1031.3	1022.3	1015.5	1010.6	1005.9	1001.2	996.3
37.5°	968.5	958.4	948.3	940.9	936.2	931.3	926.6	921.9
40°	920.6	909.5	898.4	890.4	885.7	880.9	876.2	871.4
42.5°	873.5	862.2	850.8	842.7	837.8	832.8	827.8	822.9
45°	801.4	788.4	775.5	766.6	761.9	757.1	752.3	747.6
47.5°	728.8	715.4	701.9	692.6	687.3	682.1	676.8	671.7
50°	680.6	667.4	654.2	645.1	640.1	635.0	630.0	625.0
52.5°	632.6	619.1	605.7	596.4	591.2	585.9	580.7	575.5
55°	561.7	548.0	534.3	524.9	519.8	514.8	509.8	504.7
57.5°	492.5	478.5	464.6	455.7	451.9	448.1	444.3	440.5
60°	446.3	432.5	418.8	409.7	405.5	401.3	397.1	392.9
62.5°	400.8	388.1	375.4	367.3	363.9	360.6	357.1	353.8
65°	335.5	324.2	312.8	305.6	302.4	299.2	296.0	292.8
67.5°	275.6	265.9	256.1	249.4	245.9	242.5	238.9	235.5
70°	234.9	226.2	217.5	211.7	209.1	206.5	203.8	201.2
72.5°	198.4	191.0	183.5	178.6	176.1	173.7	171.3	168.8
75°	146.2	140.1	134.0	130.2	128.5	127.0	125.4	123.8
77.5°	103.4	99.9	96.3	94.3	93.8	93.3	92.8	92.4
80°	79.4	78.6	77.7	77.2	77.0	76.7	76.5	76.2
82.5°	61.6	61.1	60.5	60.1	59.8	59.6	59.3	59.1
85°	35.8	35.3	34.8	34.5	34.5	34.5	34.5	34.5
87.5°	17.1	17.1	17.2	17.3	17.7	17.9	18.2	18.5
90°	21.2	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	20.5	21.7	22.8	23.4	23.5	23.6	23.7	23.8
95°	21.2	22.4	23.5	24.2	24.4	24.5	24.7	24.9
97.5°	22.9	23.1	23.2	23.3	23.5	23.7	23.8	24.1
100°	31.3	28.1	24.8	23.3	23.5	23.7	23.8	24.1
102.5°	112.2	77.1	42.1	24.6	24.6	24.7	24.7	24.8
105°	271.6	273.3	275.0	272.5	265.6	258.7	251.8	245.0
107.5°	336.0	336.9	337.7	338.5	339.2	339.9	340.7	341.4
110°	379.8	380.2	380.6	381.1	381.6	382.2	382.8	383.3



TEST NUMBER: P332976-935

CATALOG NUMBER: SA4XXRDIP-C1020D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	422.2	422.1	422.1	422.4	423.1	423.9	424.6	425.2
115°	485.5	485.9	486.3	486.5	486.5	486.5	486.5	486.5
117.5°	549.2	549.1	549.1	549.1	549.0	548.9	548.8	548.7
120°	588.7	589.0	589.4	589.4	589.0	588.7	588.3	587.9
122.5°	627.6	627.8	628.0	627.9	627.6	627.2	626.8	626.4
125°	681.9	682.4	683.0	683.4	683.6	683.8	684.0	684.2
127.5°	735.9	735.7	735.6	735.5	735.4	735.2	735.0	734.9
130°	768.8	769.0	769.1	769.3	769.3	769.3	769.3	769.3
132.5°	801.1	801.3	801.5	801.5	801.3	801.2	801.1	800.9
135°	845.7	846.0	846.4	846.8	847.2	847.6	847.9	848.3
137.5°	888.4	888.8	889.2	889.3	889.2	889.2	889.0	888.9
140°	914.8	915.4	915.9	916.4	916.5	916.7	916.9	917.1
142.5°	939.3	939.7	940.1	940.3	940.4	940.4	940.5	940.5
145°	974.2	974.4	974.6	974.9	975.3	975.6	976.0	976.4
147.5°	1004.9	1005.0	1005.2	1005.4	1005.6	1005.7	1006.0	1006.2
150°	1024.5	1024.5	1024.5	1024.6	1024.8	1025.0	1025.2	1025.4
152.5°	1041.6	1042.0	1042.2	1042.3	1042.2	1042.2	1042.0	1041.9
155°	1064.7	1065.5	1066.3	1066.3	1065.8	1065.2	1064.6	1064.1
157.5°	1084.6	1085.6	1086.6	1086.6	1085.6	1084.6	1083.7	1082.6
160°	1097.3	1098.5	1099.6	1099.6	1098.5	1097.3	1096.1	1095.0
162.5°	1107.6	1108.8	1109.9	1109.8	1108.5	1107.2	1106.0	1104.7
165°	1122.1	1123.7	1125.2	1125.1	1123.3	1121.6	1119.9	1118.2
167.5°	1132.7	1134.5	1136.1	1136.0	1134.1	1132.2	1130.2	1128.3
170°	1139.4	1140.8	1142.4	1142.2	1140.3	1138.4	1136.4	1134.5
172.5°	1143.5	1145.0	1146.5	1146.2	1144.2	1142.1	1140.1	1138.0
175°	1148.3	1150.0	1151.8	1151.4	1149.2	1146.9	1144.6	1142.3
177.5°	1150.2	1151.4	1152.7	1152.4	1150.6	1148.7	1146.9	1145.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2

(END OF REPORT)